Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590761

Luminaire Tested: 24CGTX-20-L92765-W2A-3000K

Issue Date: 9/7/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590761
	TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G3-2510-586-4)
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/7/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	24CGTX-20-L92765-W2A-3000K
Description:	2X4 2000 LUMEN CGTX TROFFER WITH VividTune LEDS AT 3000K CCT WITH FROSTED SMOOTH LENS
Light Source:	3000K CCT, 90 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	2106.1 lumens
Efficiency:	N/A
Efficacy:	116.4 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.26 / 1.39
Luminous Opening:	Rectangular (W 2' x L: 4' x H: 0')
CIE Type:	Direct
Input Watts (W):	18.1
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590761
CATALOG NUMBER: 24CGTX-20-L92765-W2A-3000K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590761
CATALOG NUMBER: 24CGTX-20-L92765-W2A-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	94	97	94	91	93	90	88	89	87	85	83
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69
3	90	79	70	64	87	77	69	63	74	68	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	45	39	50	44	39	37
7	64	51	42	36	63	50	41	35	48	41	35	47	40	35	45	39	35	33
8	60	46	38	32	58	45	37	32	44	37	31	43	36	31	42	36	31	29
9	56	42	34	28	54	42	34	28	41	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	39	31	26	38	30	26	37	30	25	36	30	25	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	964	964	964
5°	962	962	966
10°	963	959	962
15°	965	962	961
20°	962	956	962
25°	958	955	959
30°	952	949	952
35°	947	943	940
40°	936	934	931
45°	929	927	925
50°	922	912	912
55°	908	896	894
60°	891	875	864
65°	874	855	835
70°	837	817	805
75°	801	779	758
80°	753	730	699
85°	673	656	610

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 929 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590761
CATALOG NUMBER: 24CGTX-20-L92765-W2A-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.8	3.2
10°-20°	194.9	9.3
20°-30°	296.2	14.1
30°-40°	358.8	17.0
40°-50°	375.0	17.8
50°-60°	342.1	16.2
60°-70°	265.1	12.6
70°-80°	158.6	7.5
80°-90°	47.7	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	558.9	26.5
0°-40°	917.7	43.6
0°-60°	1634.8	77.6
0°-90°	2106.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2106.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	716	716	716	716	716	
5°	712	714	712	714	715	68
15°	693	691	691	690	690	196
25°	645	643	643	641	646	297
35°	576	574	574	572	572	361
45°	488	487	487	484	486	378
55°	387	384	382	380	381	345
65°	274	270	268	265	262	270
75°	154	153	150	146	146	163
85°	44	44	42	40	40	50
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590761
CATALOG NUMBER: 24CGTX-20-L92765-W2A-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*716.2*	716.2	716.2	716.2	716.2
2.5°	*720.2*	*717.2*	*713.1*	*712.1*	*715.2*
5°	*712.1*	714.2	712.1	714.2	715.2
7.5°	*714.2*	710.1	711.1	705.0	706.0
10°	*705.0*	706.0	702.0	705.0	704.0
12.5°	*703.0*	697.9	697.9	694.9	696.9
15°	*692.9*	690.9	690.9	689.8	689.8
17.5°	*683.8*	682.7	679.7	679.7	683.8
20°	*671.6*	670.6	667.6	668.6	671.6
22.5°	*659.5*	656.4	656.4	654.4	657.4
25°	*645.3*	643.2	643.2	641.2	646.3
27.5°	*628.0*	629.1	625.0	627.0	624.0
30°	*612.9*	610.8	610.8	608.8	612.9
32.5°	*595.6*	594.6	591.6	590.6	590.6
35°	*576.4*	574.4	574.4	572.3	572.3
37.5°	*559.2*	554.1	552.1	551.1	552.1
40°	*532.8*	533.8	531.8	530.8	529.8
42.5°	*514.6*	510.5	509.5	508.5	506.5
45°	*488.3*	487.2	487.2	484.2	486.2
47.5°	*466.0*	463.9	460.9	459.9	456.9
50°	*440.6*	438.6	435.6	434.6	435.6
52.5°	*413.3*	413.3	411.3	408.2	407.2
55°	*387.0*	383.9	381.9	379.9	380.9
57.5°	*356.6*	357.6	354.5	353.5	350.5
60°	*331.2*	329.2	325.2	324.2	321.1
62.5°	*300.9*	300.9	298.8	294.8	292.8
65°	*274.5*	270.5	268.4	265.4	262.4
67.5°	*242.1*	241.1	239.1	234.0	233.0
70°	*212.7*	211.7	207.7	204.6	204.6
72.5°	*183.3*	182.3	178.3	175.2	173.2
75°	*154.0*	153.0	149.9	145.9	145.9
77.5°	*125.6*	126.6	121.6	118.5	116.5
80°	*97.2*	97.2	94.2	91.2	90.2
82.5°	*70.9*	69.9	67.9	65.8	63.8
85°	*43.6*	43.6	42.5	40.5	39.5
87.5°	*20.3*	19.2	18.2	18.2	17.2
90°	*0.0*	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590761
CATALOG NUMBER: 24CGTX-20-L92765-W2A-3000K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.85	13.51	12.22	13.83	14.14	11.76	13.42	12.13	13.74	14.05
	3H	13.76	15.27	14.14	15.59	15.95	13.61	15.11	13.98	15.44	15.80
	4H	14.51	15.93	14.91	16.28	16.65	14.31	15.73	14.71	16.08	16.45
	6H	15.10	16.42	15.51	16.78	17.17	14.85	16.17	15.26	16.53	16.92
	8H	15.31	16.56	15.73	16.95	17.35	15.04	16.29	15.46	16.68	17.08
	12H	15.45	16.66	15.88	17.04	17.47	15.16	16.37	15.59	16.75	17.18
4H	2H	12.51	13.92	12.90	14.27	14.65	12.44	13.85	12.83	14.20	14.57
	3H	14.64	15.83	15.05	16.23	16.63	14.50	15.69	14.91	16.09	16.49
	4H	15.53	16.61	15.96	17.02	17.46	15.34	16.42	15.77	16.83	17.27
	6H	16.26	17.21	16.71	17.65	18.10	16.01	16.96	16.47	17.40	17.85
	8H	16.52	17.41	16.98	17.85	18.31	16.25	17.14	16.71	17.58	18.04
	12H	16.72	17.52	17.20	17.99	18.46	16.42	17.22	16.90	17.70	18.16
8H	4H	15.86	16.75	16.32	17.19	17.65	15.70	16.58	16.16	17.03	17.49
	6H	16.73	17.47	17.23	17.96	18.43	16.51	17.25	17.00	17.73	18.21
	8H	17.08	17.74	17.59	18.25	18.73	16.82	17.49	17.33	17.99	18.48
	12H	17.36	17.95	17.87	18.44	19.00	17.08	17.67	17.58	18.16	18.71
12H	4H	15.90	16.70	16.38	17.18	17.64	15.75	16.55	16.23	17.02	17.49
	6H	16.80	17.47	17.31	17.97	18.46	16.58	17.25	17.09	17.76	18.24
	8H	17.21	17.80	17.72	18.29	18.85	16.97	17.55	17.47	18.04	18.60

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2510-566-5-R2

Test Date: 10/14/2025

Luminaire Tested: 22CGTX-50-L92765-W2A-3000K

Data in this report applies to families of products including 22CGTX


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2510-566-5-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**22CGTX-50-L92765-W2A-3000K**
Description:	*THIS IS A REVISION OF REPORT SP1-2512-566-5-R2 TO UPDATE THE CATALOG INFORMATION* 2X2 50000 Lumen CGTX TUNABLE WHITE FROM 2700K TO 6500K - 8 V

Spectral Parameters

CCT (K):	3030	CRI (Ra):	94.5		
CIE u':	0.2507	R1:	97.4	R9:	65.0
CIE v':	0.5162	R2:	97.5	R10:	92.8
Duv:	-0.0032	R3:	96.3	R11:	94.3
CIE x:	0.4302	R4:	95.0	R12:	89.2
CIE y:	0.3938	R5:	97.0	R13:	97.4
CIE z:	0.1760	R6:	96.2	R14:	96.7
Peak Wavelength (nm):	630	R7:	91.9	R15:	93.2
Dominant Wavelength (nm):	583	R8:	85.1		
Purity:	47.31087				
Rf:	90.9				
Rg:	103.1				



Test Conditions


Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.0

REPORT NUMBER: SP1-2510-566-5-R2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2510-566-5-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3030K
CIE x = 0.4302
CIE y = 0.3938
Duv = -0.0032

Point lies inside the ANSI 3000K 7-step quadrangle

REPORT NUMBER: SP1-2510-566-5-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	91	NR	620	289	NR	750	7	NR	880	0	NR
365	0	NR	495	111	NR	625	296	NR	755	6	NR	885	0	NR
370	0	NR	500	132	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	149	NR	635	601	NR	765	4	NR	895	0	NR
380	0	NR	510	163	NR	640	189	NR	770	4	NR	900	0	NR
385	0	NR	515	174	NR	645	189	NR	775	3	NR	905	0	NR
390	1	NR	520	181	NR	650	159	NR	780	3	NR	910	0	NR
395	1	NR	525	186	NR	655	133	NR	785	2	NR	915	0	NR
400	2	NR	530	191	NR	660	113	NR	790	2	NR	920	0	NR
405	3	NR	535	195	NR	665	95	NR	795	2	NR	925	0	NR
410	5	NR	540	200	NR	670	88	NR	800	1	NR	930	0	NR
415	8	NR	545	205	NR	675	72	NR	805	1	NR	935	0	NR
420	15	NR	550	210	NR	680	62	NR	810	1	NR	940	0	NR
425	26	NR	555	218	NR	685	53	NR	815	1	NR	945	0	NR
430	43	NR	560	226	NR	690	45	NR	820	1	NR	950	0	NR
435	72	NR	565	233	NR	695	39	NR	825	1	NR	955	0	NR
440	120	NR	570	241	NR	700	33	NR	830	1	NR	960	0	NR
445	178	NR	575	249	NR	705	28	NR	835	1	NR	965	0	NR
450	191	NR	580	257	NR	710	24	NR	840	0	NR	970	0	NR
455	156	NR	585	264	NR	715	20	NR	845	0	NR	975	0	NR
460	117	NR	590	270	NR	720	17	NR	850	0	NR	980	0	NR
465	91	NR	595	273	NR	725	15	NR	855	0	NR	985	0	NR
470	72	NR	600	276	NR	730	13	NR	860	0	NR	990	0	NR
475	63	NR	605	280	NR	735	11	NR	865	0	NR	995	0	NR
480	64	NR	610	311	NR	740	9	NR	870	0	NR	1000	0	NR
485	74	NR	615	331	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2510-566-5-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.45**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	91	NR	620	289	NR	750	7	NR	880	0	NR
365	0	NR	495	111	NR	625	296	NR	755	6	NR	885	0	NR
370	0	NR	500	132	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	149	NR	635	601	NR	765	4	NR	895	0	NR
380	0	NR	510	163	NR	640	189	NR	770	4	NR	900	0	NR
385	0	NR	515	174	NR	645	189	NR	775	3	NR	905	0	NR
390	1	NR	520	181	NR	650	159	NR	780	3	NR	910	0	NR
395	1	NR	525	186	NR	655	133	NR	785	2	NR	915	0	NR
400	2	NR	530	191	NR	660	113	NR	790	2	NR	920	0	NR
405	3	NR	535	195	NR	665	95	NR	795	2	NR	925	0	NR
410	5	NR	540	200	NR	670	88	NR	800	1	NR	930	0	NR
415	8	NR	545	205	NR	675	72	NR	805	1	NR	935	0	NR
420	15	NR	550	210	NR	680	62	NR	810	1	NR	940	0	NR
425	26	NR	555	218	NR	685	53	NR	815	1	NR	945	0	NR
430	43	NR	560	226	NR	690	45	NR	820	1	NR	950	0	NR
435	72	NR	565	233	NR	695	39	NR	825	1	NR	955	0	NR
440	120	NR	570	241	NR	700	33	NR	830	1	NR	960	0	NR
445	178	NR	575	249	NR	705	28	NR	835	1	NR	965	0	NR
450	191	NR	580	257	NR	710	24	NR	840	0	NR	970	0	NR
455	156	NR	585	264	NR	715	20	NR	845	0	NR	975	0	NR
460	117	NR	590	270	NR	720	17	NR	850	0	NR	980	0	NR
465	91	NR	595	273	NR	725	15	NR	855	0	NR	985	0	NR
470	72	NR	600	276	NR	730	13	NR	860	0	NR	990	0	NR
475	63	NR	605	280	NR	735	11	NR	865	0	NR	995	0	NR
480	64	NR	610	311	NR	740	9	NR	870	0	NR	1000	0	NR
485	74	NR	615	331	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2510-566-5-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.84**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	91	NR	620	289	NR	750	7	NR	880	0	NR
365	0	NR	495	111	NR	625	296	NR	755	6	NR	885	0	NR
370	0	NR	500	132	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	149	NR	635	601	NR	765	4	NR	895	0	NR
380	0	NR	510	163	NR	640	189	NR	770	4	NR	900	0	NR
385	0	NR	515	174	NR	645	189	NR	775	3	NR	905	0	NR
390	1	NR	520	181	NR	650	159	NR	780	3	NR	910	0	NR
395	1	NR	525	186	NR	655	133	NR	785	2	NR	915	0	NR
400	2	NR	530	191	NR	660	113	NR	790	2	NR	920	0	NR
405	3	NR	535	195	NR	665	95	NR	795	2	NR	925	0	NR
410	5	NR	540	200	NR	670	88	NR	800	1	NR	930	0	NR
415	8	NR	545	205	NR	675	72	NR	805	1	NR	935	0	NR
420	15	NR	550	210	NR	680	62	NR	810	1	NR	940	0	NR
425	26	NR	555	218	NR	685	53	NR	815	1	NR	945	0	NR
430	43	NR	560	226	NR	690	45	NR	820	1	NR	950	0	NR
435	72	NR	565	233	NR	695	39	NR	825	1	NR	955	0	NR
440	120	NR	570	241	NR	700	33	NR	830	1	NR	960	0	NR
445	178	NR	575	249	NR	705	28	NR	835	1	NR	965	0	NR
450	191	NR	580	257	NR	710	24	NR	840	0	NR	970	0	NR
455	156	NR	585	264	NR	715	20	NR	845	0	NR	975	0	NR
460	117	NR	590	270	NR	720	17	NR	850	0	NR	980	0	NR
465	91	NR	595	273	NR	725	15	NR	855	0	NR	985	0	NR
470	72	NR	600	276	NR	730	13	NR	860	0	NR	990	0	NR
475	63	NR	605	280	NR	735	11	NR	865	0	NR	995	0	NR
480	64	NR	610	311	NR	740	9	NR	870	0	NR	1000	0	NR
485	74	NR	615	331	NR	745	8	NR	875	0	NR			


REPORT NUMBER: SP1-2510-566-5-R2

TM-30-18


Summary


R_f = 90.9
R_g = 103.1
CIE R_a = 94.5
R_9 = 65.0


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2510-566-5-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 89	CES51 = 94	CES76 = 87
CES02 = 63	CES27 = 97	CES52 = 93	CES77 = 86
CES03 = 32	CES28 = 95	CES53 = 90	CES78 = 84
CES04 = 70	CES29 = 86	CES54 = 99	CES79 = 90
CES05 = 51	CES30 = 91	CES55 = 99	CES80 = 91
CES06 = 51	CES31 = 87	CES56 = 92	CES81 = 74
CES07 = 44	CES32 = 81	CES57 = 91	CES82 = 96
CES08 = 42	CES33 = 88	CES58 = 92	CES83 = 93
CES09 = 29	CES34 = 90	CES59 = 99	CES84 = 96
CES10 = 76	CES35 = 95	CES60 = 98	CES85 = 82
CES11 = 59	CES36 = 93	CES61 = 97	CES86 = 79
CES12 = 65	CES37 = 92	CES62 = 96	CES87 = 91
CES13 = 44	CES38 = 96	CES63 = 92	CES88 = 96
CES14 = 74	CES39 = 96	CES64 = 96	CES89 = 82
CES15 = 72	CES40 = 92	CES65 = 92	CES90 = 96
CES16 = 48	CES41 = 93	CES66 = 94	CES91 = 85
CES17 = 50	CES42 = 88	CES67 = 94	CES92 = 80
CES18 = 57	CES43 = 86	CES68 = 93	CES93 = 88
CES19 = 72	CES44 = 99	CES69 = 95	CES94 = 74
CES20 = 67	CES45 = 90	CES70 = 90	CES95 = 86
CES21 = 86	CES46 = 90	CES71 = 90	CES96 = 92
CES22 = 79	CES47 = 84	CES72 = 96	CES97 = 91
CES23 = 92	CES48 = 92	CES73 = 85	CES98 = 92
CES24 = 90	CES49 = 89	CES74 = 90	CES99 = 94
CES25 = 72	CES50 = 94	CES75 = 90	





REPORT NUMBER: SP1-2510-566-5-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2510-566-5-R2

TM-30-18

Measure Comparisons





(END OF REPORT)