Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590768

Luminaire Tested: 24CGTX-30-L92765-W2A-2700K

Issue Date: 9/7/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590768
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/7/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	24CGTX-30-L92765-W2A-2700K
Description:	2X4 3000 LUMEN CGTX TROFFER WITH VividTune LEDS AT 2700K CCT WITH FROSTED SMOOTH LENS
Light Source:	2700K CCT, 90 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	2984.4 lumens
Efficiency:	N/A
Efficacy:	115.2 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.27 / 1.39
Luminous Opening:	Rectangular (W 1.83' x L: 3.83' x H: 0')
CIE Type:	Direct
Input Watts (W):	25.9
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590768
CATALOG NUMBER: 24CGTX-30-L92765-W2A-2700K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590768
CATALOG NUMBER: 24CGTX-30-L92765-W2A-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	94	97	94	91	93	90	88	89	87	85	83
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69
3	90	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	45	39	50	44	39	37
7	64	51	42	35	63	50	41	35	48	41	35	47	40	35	45	39	35	33
8	60	46	38	32	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	41	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	39	31	26	38	30	26	37	30	25	36	30	25	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1552	1552	1552
5°	1556	1550	1554
10°	1554	1547	1555
15°	1554	1546	1551
20°	1548	1542	1547
25°	1543	1533	1540
30°	1535	1526	1532
35°	1526	1515	1516
40°	1512	1504	1504
45°	1499	1488	1488
50°	1482	1475	1463
55°	1458	1450	1439
60°	1427	1418	1403
65°	1395	1377	1352
70°	1352	1321	1285
75°	1296	1255	1213
80°	1217	1182	1129
85°	1125	1054	984

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1499 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590768
CATALOG NUMBER: 24CGTX-30-L92765-W2A-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.0	3.2
10°-20°	275.7	9.2
20°-30°	419.5	14.1
30°-40°	508.1	17.0
40°-50°	531.1	17.8
50°-60°	484.9	16.2
60°-70°	375.8	12.6
70°-80°	225.2	7.5
80°-90°	68.1	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	791.1	26.5
0°-40°	1299.2	43.5
0°-60°	2315.2	77.6
0°-90°	2984.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2984.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1013	1013	1013	1013	1013	
5°	1012	1011	1008	1008	1011	96
15°	980	978	975	976	978	276
25°	913	911	907	908	911	421
35°	816	814	810	810	811	510
45°	692	692	687	687	687	534
55°	546	546	543	539	539	489
65°	385	385	380	375	373	381
75°	219	218	212	208	205	232
85°	64	63	60	58	56	71
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590768
CATALOG NUMBER: 24CGTX-30-L92765-W2A-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*1013*	1013	1013	1013	1013
2.5°	*1016*	*1014*	*1011*	*1011*	*1014*
5°	*1012*	1011	1008	1008	1011
7.5°	*1007*	1006	1002	1003	1005
10°	*999*	998	995	996	1000
12.5°	*991*	989	986	987	990
15°	*980*	978	975	976	978
17.5°	*965*	964	961	962	964
20°	*950*	949	946	947	949
22.5°	*932*	931	928	929	932
25°	*913*	911	907	908	911
27.5°	*891*	890	887	888	889
30°	*868*	867	863	863	866
32.5°	*843*	842	838	838	840
35°	*816*	814	810	810	811
37.5°	*785*	785	782	781	783
40°	*756*	756	752	752	752
42.5°	*725*	724	721	719	719
45°	*692*	692	687	687	687
47.5°	*658*	657	653	651	653
50°	*622*	621	619	616	614
52.5°	*586*	584	580	579	576
55°	*546*	546	543	539	539
57.5°	*508*	507	504	500	498
60°	*466*	467	463	459	458
62.5°	*427*	427	422	417	416
65°	*385*	385	380	375	373
67.5°	*344*	343	339	333	332
70°	*302*	300	295	291	287
72.5°	*261*	259	253	249	249
75°	*219*	218	212	208	205
77.5°	*178*	178	173	168	166
80°	*138*	139	134	129	128
82.5°	*101*	100	96	93	90
85°	*64*	63	60	58	56
87.5°	*28*	28	27	27	26
90°	*0*	0	0	0	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590768
CATALOG NUMBER: 24CGTX-30-L92765-W2A-2700K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.52	15.18	13.89	15.50	15.81	13.42	15.08	13.78	15.39	15.71
	3H	15.44	16.94	15.81	17.27	17.63	15.27	16.77	15.65	17.10	17.46
	4H	16.19	17.61	16.59	17.95	18.33	15.98	17.40	16.38	17.74	18.12
	6H	16.78	18.09	17.19	18.46	18.85	16.52	17.84	16.93	18.20	18.59
	8H	16.98	18.24	17.41	18.63	19.03	16.70	17.96	17.13	18.35	18.75
	12H	17.13	18.34	17.56	18.72	19.15	16.83	18.03	17.25	18.41	18.84
4H	2H	14.17	15.59	14.57	15.94	16.31	14.09	15.51	14.49	15.85	16.23
	3H	16.31	17.50	16.72	17.90	18.30	16.16	17.36	16.57	17.75	18.15
	4H	17.20	18.28	17.63	18.70	19.13	17.01	18.09	17.44	18.50	18.94
	6H	17.93	18.88	18.39	19.32	19.77	17.68	18.63	18.14	19.07	19.52
	8H	18.20	19.08	18.66	19.53	19.99	17.92	18.80	18.37	19.24	19.71
	12H	18.40	19.20	18.88	19.67	20.14	18.09	18.89	18.57	19.36	19.83
8H	4H	17.54	18.42	18.00	18.87	19.33	17.36	18.25	17.82	18.69	19.16
	6H	18.41	19.15	18.90	19.63	20.11	18.17	18.91	18.67	19.40	19.88
	8H	18.76	19.42	19.26	19.93	20.41	18.49	19.15	19.00	19.66	20.14
	12H	19.05	19.64	19.55	20.13	20.69	18.74	19.33	19.25	19.82	20.38
12H	4H	17.58	18.38	18.06	18.85	19.32	17.41	18.21	17.89	18.69	19.16
	6H	18.47	19.14	18.98	19.65	20.13	18.25	18.92	18.76	19.42	19.91
	8H	18.89	19.48	19.39	19.97	20.53	18.63	19.22	19.14	19.71	20.27

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2510-566-2-R2

Test Date: 10/14/2025

Luminaire Tested: 22CGTX-50-L92765-W2A-2700K

Data in this report applies to families of products including 22CGTX


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2510-566-2-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**22CGTX-50-L92765-W2A-2700K**
Description:	*THIS IS A REVISION OF REPORT SP1-2512-566-2-R2 TO UPDATE THE CATALOG INFORMATION* 2X2 50000 Lumen CGTX TUNABLE WHITE FROM 2700K TO 6500K - 9.5V

Spectral Parameters

CCT (K):	2769	CRI (Ra):	93.3		
CIE u':	0.2597	R1:	95.3	R9:	56.5
CIE v':	0.5252	R2:	96.1	R10:	89.8
Duv:	-0.0006	R3:	96.0	R11:	95.2
CIE x:	0.4534	R4:	94.8	R12:	89.7
CIE y:	0.4074	R5:	94.9	R13:	95.3
CIE z:	0.1392	R6:	97.1	R14:	96.4
Peak Wavelength (nm):	630	R7:	91.2	R15:	89.6
Dominant Wavelength (nm):	584	R8:	81.4		
Purity:	58.37672				
Rf:	89.8				
Rg:	102.5				



Test Conditions


Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.0

REPORT NUMBER: SP1-2510-566-2-R2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2510-566-2-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2769K
CIE x = 0.4534
CIE y = 0.4074
Duv = -0.0006

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2510-566-2-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	74	NR	620	290	NR	750	7	NR	880	0	NR
365	0	NR	495	94	NR	625	297	NR	755	6	NR	885	0	NR
370	0	NR	500	113	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	130	NR	635	606	NR	765	4	NR	895	0	NR
380	0	NR	510	143	NR	640	189	NR	770	3	NR	900	0	NR
385	0	NR	515	154	NR	645	190	NR	775	3	NR	905	0	NR
390	1	NR	520	162	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	166	NR	655	134	NR	785	2	NR	915	0	NR
400	2	NR	530	171	NR	660	114	NR	790	2	NR	920	0	NR
405	3	NR	535	176	NR	665	96	NR	795	2	NR	925	0	NR
410	4	NR	540	182	NR	670	89	NR	800	1	NR	930	0	NR
415	7	NR	545	187	NR	675	72	NR	805	1	NR	935	0	NR
420	14	NR	550	194	NR	680	62	NR	810	1	NR	940	0	NR
425	23	NR	555	202	NR	685	53	NR	815	1	NR	945	0	NR
430	38	NR	560	210	NR	690	46	NR	820	1	NR	950	0	NR
435	63	NR	565	219	NR	695	39	NR	825	1	NR	955	0	NR
440	102	NR	570	228	NR	700	33	NR	830	1	NR	960	0	NR
445	144	NR	575	238	NR	705	28	NR	835	1	NR	965	0	NR
450	128	NR	580	247	NR	710	24	NR	840	0	NR	970	0	NR
455	83	NR	585	257	NR	715	20	NR	845	0	NR	975	0	NR
460	68	NR	590	264	NR	720	18	NR	850	0	NR	980	0	NR
465	55	NR	595	267	NR	725	15	NR	855	0	NR	985	0	NR
470	43	NR	600	273	NR	730	13	NR	860	0	NR	990	0	NR
475	42	NR	605	278	NR	735	11	NR	865	0	NR	995	0	NR
480	47	NR	610	311	NR	740	9	NR	870	0	NR	1000	0	NR
485	58	NR	615	333	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2510-566-2-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.3**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	74	NR	620	290	NR	750	7	NR	880	0	NR
365	0	NR	495	94	NR	625	297	NR	755	6	NR	885	0	NR
370	0	NR	500	113	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	130	NR	635	606	NR	765	4	NR	895	0	NR
380	0	NR	510	143	NR	640	189	NR	770	3	NR	900	0	NR
385	0	NR	515	154	NR	645	190	NR	775	3	NR	905	0	NR
390	1	NR	520	162	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	166	NR	655	134	NR	785	2	NR	915	0	NR
400	2	NR	530	171	NR	660	114	NR	790	2	NR	920	0	NR
405	3	NR	535	176	NR	665	96	NR	795	2	NR	925	0	NR
410	4	NR	540	182	NR	670	89	NR	800	1	NR	930	0	NR
415	7	NR	545	187	NR	675	72	NR	805	1	NR	935	0	NR
420	14	NR	550	194	NR	680	62	NR	810	1	NR	940	0	NR
425	23	NR	555	202	NR	685	53	NR	815	1	NR	945	0	NR
430	38	NR	560	210	NR	690	46	NR	820	1	NR	950	0	NR
435	63	NR	565	219	NR	695	39	NR	825	1	NR	955	0	NR
440	102	NR	570	228	NR	700	33	NR	830	1	NR	960	0	NR
445	144	NR	575	238	NR	705	28	NR	835	1	NR	965	0	NR
450	128	NR	580	247	NR	710	24	NR	840	0	NR	970	0	NR
455	83	NR	585	257	NR	715	20	NR	845	0	NR	975	0	NR
460	68	NR	590	264	NR	720	18	NR	850	0	NR	980	0	NR
465	55	NR	595	267	NR	725	15	NR	855	0	NR	985	0	NR
470	43	NR	600	273	NR	730	13	NR	860	0	NR	990	0	NR
475	42	NR	605	278	NR	735	11	NR	865	0	NR	995	0	NR
480	47	NR	610	311	NR	740	9	NR	870	0	NR	1000	0	NR
485	58	NR	615	333	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2510-566-2-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.45**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	74	NR	620	290	NR	750	7	NR	880	0	NR
365	0	NR	495	94	NR	625	297	NR	755	6	NR	885	0	NR
370	0	NR	500	113	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	130	NR	635	606	NR	765	4	NR	895	0	NR
380	0	NR	510	143	NR	640	189	NR	770	3	NR	900	0	NR
385	0	NR	515	154	NR	645	190	NR	775	3	NR	905	0	NR
390	1	NR	520	162	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	166	NR	655	134	NR	785	2	NR	915	0	NR
400	2	NR	530	171	NR	660	114	NR	790	2	NR	920	0	NR
405	3	NR	535	176	NR	665	96	NR	795	2	NR	925	0	NR
410	4	NR	540	182	NR	670	89	NR	800	1	NR	930	0	NR
415	7	NR	545	187	NR	675	72	NR	805	1	NR	935	0	NR
420	14	NR	550	194	NR	680	62	NR	810	1	NR	940	0	NR
425	23	NR	555	202	NR	685	53	NR	815	1	NR	945	0	NR
430	38	NR	560	210	NR	690	46	NR	820	1	NR	950	0	NR
435	63	NR	565	219	NR	695	39	NR	825	1	NR	955	0	NR
440	102	NR	570	228	NR	700	33	NR	830	1	NR	960	0	NR
445	144	NR	575	238	NR	705	28	NR	835	1	NR	965	0	NR
450	128	NR	580	247	NR	710	24	NR	840	0	NR	970	0	NR
455	83	NR	585	257	NR	715	20	NR	845	0	NR	975	0	NR
460	68	NR	590	264	NR	720	18	NR	850	0	NR	980	0	NR
465	55	NR	595	267	NR	725	15	NR	855	0	NR	985	0	NR
470	43	NR	600	273	NR	730	13	NR	860	0	NR	990	0	NR
475	42	NR	605	278	NR	735	11	NR	865	0	NR	995	0	NR
480	47	NR	610	311	NR	740	9	NR	870	0	NR	1000	0	NR
485	58	NR	615	333	NR	745	8	NR	875	0	NR			


REPORT NUMBER: SP1-2510-566-2-R2

TM-30-18


Summary


R_f = 89.8
R_g = 102.5
CIE R_a = 93.3
R_9 = 56.5


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2510-566-2-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 88	CES51 = 92	CES76 = 89
CES02 = 64	CES27 = 97	CES52 = 93	CES77 = 85
CES03 = 32	CES28 = 95	CES53 = 88	CES78 = 86
CES04 = 70	CES29 = 83	CES54 = 96	CES79 = 89
CES05 = 51	CES30 = 84	CES55 = 95	CES80 = 91
CES06 = 51	CES31 = 85	CES56 = 89	CES81 = 70
CES07 = 44	CES32 = 80	CES57 = 87	CES82 = 96
CES08 = 43	CES33 = 83	CES58 = 88	CES83 = 92
CES09 = 29	CES34 = 91	CES59 = 98	CES84 = 97
CES10 = 77	CES35 = 95	CES60 = 99	CES85 = 82
CES11 = 59	CES36 = 99	CES61 = 99	CES86 = 75
CES12 = 66	CES37 = 93	CES62 = 91	CES87 = 91
CES13 = 44	CES38 = 88	CES63 = 89	CES88 = 93
CES14 = 74	CES39 = 95	CES64 = 93	CES89 = 80
CES15 = 72	CES40 = 91	CES65 = 90	CES90 = 92
CES16 = 48	CES41 = 90	CES66 = 92	CES91 = 92
CES17 = 50	CES42 = 89	CES67 = 93	CES92 = 80
CES18 = 57	CES43 = 87	CES68 = 96	CES93 = 88
CES19 = 72	CES44 = 98	CES69 = 98	CES94 = 71
CES20 = 68	CES45 = 91	CES70 = 92	CES95 = 87
CES21 = 87	CES46 = 89	CES71 = 93	CES96 = 92
CES22 = 79	CES47 = 80	CES72 = 97	CES97 = 90
CES23 = 92	CES48 = 86	CES73 = 87	CES98 = 90
CES24 = 91	CES49 = 87	CES74 = 89	CES99 = 91
CES25 = 72	CES50 = 92	CES75 = 92	





REPORT NUMBER: SP1-2510-566-2-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2510-566-2-R2

TM-30-18

Measure Comparisons





(END OF REPORT)