Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590776

Luminaire Tested: 24CGTX-35-L92765-W2A-2700K

Issue Date: 9/7/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590776
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/7/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	24CGTX-35-L92765-W2A-2700K
Description:	2X4 3500 LUMEN CGTX TROFFER WITH VividTune LEDS AT 2700K CCT WITH FROSTED SMOOTH LENS
Light Source:	2700K CCT, 90 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	3788.2 lumens
Efficiency:	N/A
Efficacy:	113.8 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.27 / 1.39
Luminous Opening:	Rectangular (W 1.83' x L: 3.83' x H: 0')
CIE Type:	Direct
Input Watts (W):	33.3
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590776
CATALOG NUMBER: 24CGTX-35-L92765-W2A-2700K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590776
CATALOG NUMBER: 24CGTX-35-L92765-W2A-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	94	91	93	90	88	89	87	85	83
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69
3	90	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	45	39	50	44	39	37
7	64	51	42	35	63	50	41	35	48	41	35	47	40	35	45	39	35	33
8	60	46	38	32	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	41	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	39	31	26	37	30	26	37	30	25	36	30	25	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1968	1968	1968
5°	1974	1968	1973
10°	1972	1967	1972
15°	1969	1963	1968
20°	1964	1958	1961
25°	1955	1950	1952
30°	1949	1937	1942
35°	1931	1926	1926
40°	1919	1911	1907
45°	1904	1891	1887
50°	1878	1870	1861
55°	1856	1845	1826
60°	1820	1795	1777
65°	1772	1747	1718
70°	1715	1679	1643
75°	1651	1598	1539
80°	1579	1491	1429
85°	1423	1353	1283

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1904 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590776
CATALOG NUMBER: 24CGTX-35-L92765-W2A-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.8	3.2
10°-20°	349.9	9.2
20°-30°	532.4	14.1
30°-40°	644.8	17.0
40°-50°	674.1	17.8
50°-60°	615.6	16.3
60°-70°	476.9	12.6
70°-80°	285.8	7.5
80°-90°	86.8	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1004.1	26.5
0°-40°	1649.0	43.5
0°-60°	2938.6	77.6
0°-90°	3788.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3788.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1285	1285	1285	1285	1285	
5°	1284	1281	1280	1281	1283	122
15°	1242	1239	1238	1239	1241	351
25°	1157	1156	1154	1155	1155	534
35°	1033	1031	1030	1030	1030	647
45°	879	876	873	873	871	678
55°	695	692	691	687	684	621
65°	489	486	482	477	474	484
75°	279	275	270	263	260	295
85°	81	80	77	74	73	91
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590776
CATALOG NUMBER: 24CGTX-35-L92765-W2A-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*1285*	1285	1285	1285	1285
2.5°	*1288*	*1285*	*1283*	*1284*	*1287*
5°	*1284*	1281	1280	1281	1283
7.5°	*1278*	1275	1274	1274	1277
10°	*1268*	1266	1265	1265	1268
12.5°	*1257*	1254	1253	1253	1256
15°	*1242*	1239	1238	1239	1241
17.5°	*1225*	1223	1221	1222	1224
20°	*1205*	1203	1201	1202	1203
22.5°	*1183*	1181	1179	1180	1182
25°	*1157*	1156	1154	1155	1155
27.5°	*1130*	1128	1126	1127	1127
30°	*1102*	1098	1095	1098	1098
32.5°	*1067*	1065	1063	1065	1065
35°	*1033*	1031	1030	1030	1030
37.5°	*997*	996	994	994	992
40°	*960*	957	956	955	954
42.5°	*920*	917	915	914	914
45°	*879*	876	873	873	871
47.5°	*837*	833	829	828	827
50°	*788*	786	785	782	781
52.5°	*742*	740	737	735	733
55°	*695*	692	691	687	684
57.5°	*646*	642	639	636	633
60°	*594*	591	586	585	580
62.5°	*540*	540	537	532	528
65°	*489*	486	482	477	474
67.5°	*437*	434	429	423	422
70°	*383*	380	375	369	367
72.5°	*330*	328	321	318	314
75°	*279*	275	270	263	260
77.5°	*228*	225	221	213	211
80°	*179*	175	169	166	162
82.5°	*128*	126	124	119	116
85°	*81*	80	77	74	73
87.5°	*37*	35	34	33	33
90°	*0*	0	0	0	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590776
CATALOG NUMBER: 24CGTX-35-L92765-W2A-2700K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.34	16.00	14.71	16.31	16.63	14.26	15.92	14.63	16.23	16.55
	3H	16.26	17.76	16.63	18.09	18.44	16.11	17.62	16.49	17.94	18.30
	4H	17.01	18.43	17.41	18.77	19.15	16.82	18.23	17.21	18.58	18.96
	6H	17.61	18.92	18.02	19.29	19.68	17.36	18.67	17.77	19.04	19.43
	8H	17.81	19.07	18.24	19.46	19.86	17.54	18.80	17.96	19.19	19.59
	12H	17.96	19.17	18.39	19.55	19.98	17.67	18.88	18.10	19.26	19.69
4H	2H	14.99	16.41	15.39	16.76	17.13	14.93	16.35	15.33	16.69	17.07
	3H	17.13	18.32	17.54	18.72	19.12	17.00	18.20	17.41	18.59	18.99
	4H	18.02	19.10	18.45	19.51	19.95	17.84	18.92	18.27	19.33	19.77
	6H	18.76	19.71	19.21	20.15	20.60	18.52	19.47	18.97	19.90	20.36
	8H	19.02	19.91	19.48	20.35	20.82	18.76	19.64	19.21	20.08	20.55
	12H	19.22	20.02	19.70	20.50	20.97	18.93	19.73	19.41	20.21	20.68
8H	4H	18.36	19.24	18.81	19.68	20.15	18.20	19.09	18.66	19.53	19.99
	6H	19.23	19.97	19.72	20.46	20.93	19.01	19.75	19.50	20.24	20.71
	8H	19.58	20.25	20.09	20.75	21.24	19.33	20.00	19.84	20.50	20.99
	12H	19.87	20.46	20.38	20.95	21.51	19.59	20.18	20.10	20.67	21.23
12H	4H	18.40	19.20	18.88	19.67	20.14	18.25	19.05	18.73	19.52	19.99
	6H	19.30	19.97	19.81	20.47	20.96	19.09	19.76	19.60	20.26	20.75
	8H	19.71	20.30	20.22	20.79	21.35	19.48	20.06	19.98	20.55	21.11

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2510-566-2-R2

Test Date: 10/14/2025

Luminaire Tested: 22CGTX-50-L92765-W2A-2700K

Data in this report applies to families of products including 22CGTX


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2510-566-2-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**22CGTX-50-L92765-W2A-2700K**
Description:	*THIS IS A REVISION OF REPORT SP1-2512-566-2-R2 TO UPDATE THE CATALOG INFORMATION* 2X2 50000 Lumen CGTX TUNABLE WHITE FROM 2700K TO 6500K - 9.5V

Spectral Parameters

CCT (K):	2769	CRI (Ra):	93.3		
CIE u':	0.2597	R1:	95.3	R9:	56.5
CIE v':	0.5252	R2:	96.1	R10:	89.8
Duv:	-0.0006	R3:	96.0	R11:	95.2
CIE x:	0.4534	R4:	94.8	R12:	89.7
CIE y:	0.4074	R5:	94.9	R13:	95.3
CIE z:	0.1392	R6:	97.1	R14:	96.4
Peak Wavelength (nm):	630	R7:	91.2	R15:	89.6
Dominant Wavelength (nm):	584	R8:	81.4		
Purity:	58.37672				
Rf:	89.8				
Rg:	102.5				



Test Conditions


Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.0

REPORT NUMBER: SP1-2510-566-2-R2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2510-566-2-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2769K
CIE x = 0.4534
CIE y = 0.4074
Duv = -0.0006

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2510-566-2-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	74	NR	620	290	NR	750	7	NR	880	0	NR
365	0	NR	495	94	NR	625	297	NR	755	6	NR	885	0	NR
370	0	NR	500	113	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	130	NR	635	606	NR	765	4	NR	895	0	NR
380	0	NR	510	143	NR	640	189	NR	770	3	NR	900	0	NR
385	0	NR	515	154	NR	645	190	NR	775	3	NR	905	0	NR
390	1	NR	520	162	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	166	NR	655	134	NR	785	2	NR	915	0	NR
400	2	NR	530	171	NR	660	114	NR	790	2	NR	920	0	NR
405	3	NR	535	176	NR	665	96	NR	795	2	NR	925	0	NR
410	4	NR	540	182	NR	670	89	NR	800	1	NR	930	0	NR
415	7	NR	545	187	NR	675	72	NR	805	1	NR	935	0	NR
420	14	NR	550	194	NR	680	62	NR	810	1	NR	940	0	NR
425	23	NR	555	202	NR	685	53	NR	815	1	NR	945	0	NR
430	38	NR	560	210	NR	690	46	NR	820	1	NR	950	0	NR
435	63	NR	565	219	NR	695	39	NR	825	1	NR	955	0	NR
440	102	NR	570	228	NR	700	33	NR	830	1	NR	960	0	NR
445	144	NR	575	238	NR	705	28	NR	835	1	NR	965	0	NR
450	128	NR	580	247	NR	710	24	NR	840	0	NR	970	0	NR
455	83	NR	585	257	NR	715	20	NR	845	0	NR	975	0	NR
460	68	NR	590	264	NR	720	18	NR	850	0	NR	980	0	NR
465	55	NR	595	267	NR	725	15	NR	855	0	NR	985	0	NR
470	43	NR	600	273	NR	730	13	NR	860	0	NR	990	0	NR
475	42	NR	605	278	NR	735	11	NR	865	0	NR	995	0	NR
480	47	NR	610	311	NR	740	9	NR	870	0	NR	1000	0	NR
485	58	NR	615	333	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2510-566-2-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.3**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	74	NR	620	290	NR	750	7	NR	880	0	NR
365	0	NR	495	94	NR	625	297	NR	755	6	NR	885	0	NR
370	0	NR	500	113	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	130	NR	635	606	NR	765	4	NR	895	0	NR
380	0	NR	510	143	NR	640	189	NR	770	3	NR	900	0	NR
385	0	NR	515	154	NR	645	190	NR	775	3	NR	905	0	NR
390	1	NR	520	162	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	166	NR	655	134	NR	785	2	NR	915	0	NR
400	2	NR	530	171	NR	660	114	NR	790	2	NR	920	0	NR
405	3	NR	535	176	NR	665	96	NR	795	2	NR	925	0	NR
410	4	NR	540	182	NR	670	89	NR	800	1	NR	930	0	NR
415	7	NR	545	187	NR	675	72	NR	805	1	NR	935	0	NR
420	14	NR	550	194	NR	680	62	NR	810	1	NR	940	0	NR
425	23	NR	555	202	NR	685	53	NR	815	1	NR	945	0	NR
430	38	NR	560	210	NR	690	46	NR	820	1	NR	950	0	NR
435	63	NR	565	219	NR	695	39	NR	825	1	NR	955	0	NR
440	102	NR	570	228	NR	700	33	NR	830	1	NR	960	0	NR
445	144	NR	575	238	NR	705	28	NR	835	1	NR	965	0	NR
450	128	NR	580	247	NR	710	24	NR	840	0	NR	970	0	NR
455	83	NR	585	257	NR	715	20	NR	845	0	NR	975	0	NR
460	68	NR	590	264	NR	720	18	NR	850	0	NR	980	0	NR
465	55	NR	595	267	NR	725	15	NR	855	0	NR	985	0	NR
470	43	NR	600	273	NR	730	13	NR	860	0	NR	990	0	NR
475	42	NR	605	278	NR	735	11	NR	865	0	NR	995	0	NR
480	47	NR	610	311	NR	740	9	NR	870	0	NR	1000	0	NR
485	58	NR	615	333	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2510-566-2-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.45**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	74	NR	620	290	NR	750	7	NR	880	0	NR
365	0	NR	495	94	NR	625	297	NR	755	6	NR	885	0	NR
370	0	NR	500	113	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	130	NR	635	606	NR	765	4	NR	895	0	NR
380	0	NR	510	143	NR	640	189	NR	770	3	NR	900	0	NR
385	0	NR	515	154	NR	645	190	NR	775	3	NR	905	0	NR
390	1	NR	520	162	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	166	NR	655	134	NR	785	2	NR	915	0	NR
400	2	NR	530	171	NR	660	114	NR	790	2	NR	920	0	NR
405	3	NR	535	176	NR	665	96	NR	795	2	NR	925	0	NR
410	4	NR	540	182	NR	670	89	NR	800	1	NR	930	0	NR
415	7	NR	545	187	NR	675	72	NR	805	1	NR	935	0	NR
420	14	NR	550	194	NR	680	62	NR	810	1	NR	940	0	NR
425	23	NR	555	202	NR	685	53	NR	815	1	NR	945	0	NR
430	38	NR	560	210	NR	690	46	NR	820	1	NR	950	0	NR
435	63	NR	565	219	NR	695	39	NR	825	1	NR	955	0	NR
440	102	NR	570	228	NR	700	33	NR	830	1	NR	960	0	NR
445	144	NR	575	238	NR	705	28	NR	835	1	NR	965	0	NR
450	128	NR	580	247	NR	710	24	NR	840	0	NR	970	0	NR
455	83	NR	585	257	NR	715	20	NR	845	0	NR	975	0	NR
460	68	NR	590	264	NR	720	18	NR	850	0	NR	980	0	NR
465	55	NR	595	267	NR	725	15	NR	855	0	NR	985	0	NR
470	43	NR	600	273	NR	730	13	NR	860	0	NR	990	0	NR
475	42	NR	605	278	NR	735	11	NR	865	0	NR	995	0	NR
480	47	NR	610	311	NR	740	9	NR	870	0	NR	1000	0	NR
485	58	NR	615	333	NR	745	8	NR	875	0	NR			


REPORT NUMBER: SP1-2510-566-2-R2

TM-30-18


Summary


R_f = 89.8
R_g = 102.5
CIE R_a = 93.3
R_9 = 56.5


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2510-566-2-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 88	CES51 = 92	CES76 = 89
CES02 = 64	CES27 = 97	CES52 = 93	CES77 = 85
CES03 = 32	CES28 = 95	CES53 = 88	CES78 = 86
CES04 = 70	CES29 = 83	CES54 = 96	CES79 = 89
CES05 = 51	CES30 = 84	CES55 = 95	CES80 = 91
CES06 = 51	CES31 = 85	CES56 = 89	CES81 = 70
CES07 = 44	CES32 = 80	CES57 = 87	CES82 = 96
CES08 = 43	CES33 = 83	CES58 = 88	CES83 = 92
CES09 = 29	CES34 = 91	CES59 = 98	CES84 = 97
CES10 = 77	CES35 = 95	CES60 = 99	CES85 = 82
CES11 = 59	CES36 = 99	CES61 = 99	CES86 = 75
CES12 = 66	CES37 = 93	CES62 = 91	CES87 = 91
CES13 = 44	CES38 = 88	CES63 = 89	CES88 = 93
CES14 = 74	CES39 = 95	CES64 = 93	CES89 = 80
CES15 = 72	CES40 = 91	CES65 = 90	CES90 = 92
CES16 = 48	CES41 = 90	CES66 = 92	CES91 = 92
CES17 = 50	CES42 = 89	CES67 = 93	CES92 = 80
CES18 = 57	CES43 = 87	CES68 = 96	CES93 = 88
CES19 = 72	CES44 = 98	CES69 = 98	CES94 = 71
CES20 = 68	CES45 = 91	CES70 = 92	CES95 = 87
CES21 = 87	CES46 = 89	CES71 = 93	CES96 = 92
CES22 = 79	CES47 = 80	CES72 = 97	CES97 = 90
CES23 = 92	CES48 = 86	CES73 = 87	CES98 = 90
CES24 = 91	CES49 = 87	CES74 = 89	CES99 = 91
CES25 = 72	CES50 = 92	CES75 = 92	





REPORT NUMBER: SP1-2510-566-2-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2510-566-2-R2

TM-30-18

Measure Comparisons





(END OF REPORT)