Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590784

Luminaire Tested: 24CGTX-40-L92765-W2A-2700K

Issue Date: 9/7/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590784
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/7/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	24CGTX-40-L92765-W2A-2700K
Description:	2X4 4000 LUMEN CGTX TROFFER WITH VividTune LEDS AT 2700K CCT WITH FROSTED SMOOTH LENS
Light Source:	2700K CCT, 90 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	4526.8 lumens
Efficiency:	N/A
Efficacy:	112.0 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.27 / 1.39
Luminous Opening:	Rectangular (W 1.83' x L: 3.83' x H: 0')
CIE Type:	Direct
Input Watts (W):	40.4
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590784
CATALOG NUMBER: 24CGTX-40-L92765-W2A-2700K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590784
CATALOG NUMBER: 24CGTX-40-L92765-W2A-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	94	91	93	90	88	89	87	85	83
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69
3	90	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	45	39	50	44	39	37
7	64	51	42	35	63	50	41	35	48	41	35	47	40	35	45	39	35	33
8	60	46	38	32	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	41	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	39	31	26	37	30	26	37	30	25	36	30	25	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2353	2353	2353
5°	2365	2352	2354
10°	2362	2350	2353
15°	2358	2345	2350
20°	2350	2339	2344
25°	2341	2330	2334
30°	2331	2319	2317
35°	2317	2302	2300
40°	2297	2285	2279
45°	2281	2259	2253
50°	2249	2233	2221
55°	2216	2195	2187
60°	2175	2147	2129
65°	2120	2091	2051
70°	2060	2015	1961
75°	1965	1911	1835
80°	1870	1782	1720
85°	1705	1634	1529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2281 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590784
CATALOG NUMBER: 24CGTX-40-L92765-W2A-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.6	3.2
10°-20°	418.0	9.2
20°-30°	636.1	14.1
30°-40°	770.6	17.0
40°-50°	805.7	17.8
50°-60°	735.4	16.2
60°-70°	570.2	12.6
70°-80°	341.6	7.5
80°-90°	103.6	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1199.7	26.5
0°-40°	1970.3	43.5
0°-60°	3511.4	77.6
0°-90°	4526.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4526.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1536	1536	1536	1536	1536	
5°	1538	1533	1530	1527	1531	146
15°	1487	1481	1479	1478	1482	420
25°	1385	1381	1379	1377	1381	639
35°	1239	1234	1231	1227	1230	775
45°	1053	1049	1043	1038	1040	811
55°	830	826	822	818	819	743
65°	585	583	577	568	566	580
75°	332	331	323	314	310	353
85°	97	97	93	88	87	109
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590784
CATALOG NUMBER: 24CGTX-40-L92765-W2A-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*1536*	1536	1536	1536	1536
2.5°	*1542*	*1536*	*1534*	*1531*	*1535*
5°	*1538*	1533	1530	1527	1531
7.5°	*1530*	1525	1523	1520	1524
10°	*1519*	1513	1511	1509	1513
12.5°	*1504*	1499	1497	1495	1499
15°	*1487*	1481	1479	1478	1482
17.5°	*1468*	1462	1460	1458	1462
20°	*1442*	1437	1435	1433	1438
22.5°	*1415*	1411	1409	1407	1410
25°	*1385*	1381	1379	1377	1381
27.5°	*1354*	1348	1347	1345	1348
30°	*1318*	1312	1311	1308	1310
32.5°	*1278*	1274	1272	1269	1273
35°	*1239*	1234	1231	1227	1230
37.5°	*1196*	1190	1188	1185	1186
40°	*1149*	1145	1143	1139	1140
42.5°	*1103*	1098	1096	1090	1094
45°	*1053*	1049	1043	1038	1040
47.5°	*999*	996	992	989	988
50°	*944*	940	937	934	932
52.5°	*890*	886	881	876	873
55°	*830*	826	822	818	819
57.5°	*775*	768	766	759	756
60°	*710*	707	701	697	695
62.5°	*650*	647	640	632	634
65°	*585*	583	577	568	566
67.5°	*522*	520	515	504	504
70°	*460*	454	450	441	438
72.5°	*397*	392	386	379	375
75°	*332*	331	323	314	310
77.5°	*272*	269	262	254	252
80°	*212*	208	202	196	195
82.5°	*155*	151	147	141	140
85°	*97*	97	93	88	87
87.5°	*42*	41	41	39	40
90°	*0*	0	0	0	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590784
CATALOG NUMBER: 24CGTX-40-L92765-W2A-2700K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.97	16.63	15.34	16.94	17.26	14.87	16.53	15.24	16.84	17.16
	3H	16.89	18.39	17.26	18.72	19.07	16.72	18.23	17.10	18.55	18.91
	4H	17.64	19.06	18.04	19.40	19.78	17.43	18.84	17.82	19.19	19.57
	6H	18.23	19.55	18.64	19.91	20.30	17.97	19.28	18.38	19.65	20.04
	8H	18.44	19.70	18.86	20.09	20.48	18.16	19.41	18.58	19.80	20.20
	12H	18.59	19.80	19.02	20.18	20.61	18.29	19.49	18.71	19.87	20.30
4H	2H	15.62	17.04	16.02	17.39	17.76	15.54	16.96	15.94	17.31	17.68
	3H	17.76	18.95	18.17	19.35	19.75	17.62	18.81	18.03	19.21	19.61
	4H	18.65	19.73	19.08	20.15	20.58	18.45	19.53	18.88	19.95	20.38
	6H	19.38	20.33	19.84	20.77	21.22	19.13	20.08	19.58	20.52	20.97
	8H	19.65	20.54	20.11	20.98	21.44	19.37	20.26	19.83	20.70	21.16
	12H	19.85	20.65	20.33	21.13	21.60	19.55	20.35	20.03	20.82	21.29
8H	4H	18.99	19.87	19.45	20.32	20.78	18.81	19.70	19.27	20.14	20.61
	6H	19.85	20.59	20.35	21.08	21.56	19.62	20.36	20.11	20.85	21.32
	8H	20.21	20.87	20.71	21.38	21.86	19.94	20.61	20.45	21.11	21.60
	12H	20.50	21.09	21.01	21.58	22.14	20.20	20.79	20.71	21.28	21.84
12H	4H	19.03	19.83	19.51	20.30	20.77	18.86	19.66	19.34	20.13	20.60
	6H	19.92	20.59	20.43	21.09	21.58	19.70	20.37	20.21	20.87	21.36
	8H	20.34	20.93	20.84	21.42	21.98	20.09	20.67	20.59	21.16	21.72

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2510-566-2-R2

Test Date: 10/14/2025

Luminaire Tested: 22CGTX-50-L92765-W2A-2700K

Data in this report applies to families of products including 22CGTX


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2510-566-2-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**22CGTX-50-L92765-W2A-2700K**
Description:	*THIS IS A REVISION OF REPORT SP1-2512-566-2-R2 TO UPDATE THE CATALOG INFORMATION* 2X2 50000 Lumen CGTX TUNABLE WHITE FROM 2700K TO 6500K - 9.5V

Spectral Parameters

CCT (K):	2769	CRI (Ra):	93.3		
CIE u':	0.2597	R1:	95.3	R9:	56.5
CIE v':	0.5252	R2:	96.1	R10:	89.8
Duv:	-0.0006	R3:	96.0	R11:	95.2
CIE x:	0.4534	R4:	94.8	R12:	89.7
CIE y:	0.4074	R5:	94.9	R13:	95.3
CIE z:	0.1392	R6:	97.1	R14:	96.4
Peak Wavelength (nm):	630	R7:	91.2	R15:	89.6
Dominant Wavelength (nm):	584	R8:	81.4		
Purity:	58.37672				
Rf:	89.8				
Rg:	102.5				



Test Conditions


Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.0

REPORT NUMBER: SP1-2510-566-2-R2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2510-566-2-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2769K
CIE x = 0.4534
CIE y = 0.4074
Duv = -0.0006

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2510-566-2-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	74	NR	620	290	NR	750	7	NR	880	0	NR
365	0	NR	495	94	NR	625	297	NR	755	6	NR	885	0	NR
370	0	NR	500	113	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	130	NR	635	606	NR	765	4	NR	895	0	NR
380	0	NR	510	143	NR	640	189	NR	770	3	NR	900	0	NR
385	0	NR	515	154	NR	645	190	NR	775	3	NR	905	0	NR
390	1	NR	520	162	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	166	NR	655	134	NR	785	2	NR	915	0	NR
400	2	NR	530	171	NR	660	114	NR	790	2	NR	920	0	NR
405	3	NR	535	176	NR	665	96	NR	795	2	NR	925	0	NR
410	4	NR	540	182	NR	670	89	NR	800	1	NR	930	0	NR
415	7	NR	545	187	NR	675	72	NR	805	1	NR	935	0	NR
420	14	NR	550	194	NR	680	62	NR	810	1	NR	940	0	NR
425	23	NR	555	202	NR	685	53	NR	815	1	NR	945	0	NR
430	38	NR	560	210	NR	690	46	NR	820	1	NR	950	0	NR
435	63	NR	565	219	NR	695	39	NR	825	1	NR	955	0	NR
440	102	NR	570	228	NR	700	33	NR	830	1	NR	960	0	NR
445	144	NR	575	238	NR	705	28	NR	835	1	NR	965	0	NR
450	128	NR	580	247	NR	710	24	NR	840	0	NR	970	0	NR
455	83	NR	585	257	NR	715	20	NR	845	0	NR	975	0	NR
460	68	NR	590	264	NR	720	18	NR	850	0	NR	980	0	NR
465	55	NR	595	267	NR	725	15	NR	855	0	NR	985	0	NR
470	43	NR	600	273	NR	730	13	NR	860	0	NR	990	0	NR
475	42	NR	605	278	NR	735	11	NR	865	0	NR	995	0	NR
480	47	NR	610	311	NR	740	9	NR	870	0	NR	1000	0	NR
485	58	NR	615	333	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2510-566-2-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.3**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	74	NR	620	290	NR	750	7	NR	880	0	NR
365	0	NR	495	94	NR	625	297	NR	755	6	NR	885	0	NR
370	0	NR	500	113	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	130	NR	635	606	NR	765	4	NR	895	0	NR
380	0	NR	510	143	NR	640	189	NR	770	3	NR	900	0	NR
385	0	NR	515	154	NR	645	190	NR	775	3	NR	905	0	NR
390	1	NR	520	162	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	166	NR	655	134	NR	785	2	NR	915	0	NR
400	2	NR	530	171	NR	660	114	NR	790	2	NR	920	0	NR
405	3	NR	535	176	NR	665	96	NR	795	2	NR	925	0	NR
410	4	NR	540	182	NR	670	89	NR	800	1	NR	930	0	NR
415	7	NR	545	187	NR	675	72	NR	805	1	NR	935	0	NR
420	14	NR	550	194	NR	680	62	NR	810	1	NR	940	0	NR
425	23	NR	555	202	NR	685	53	NR	815	1	NR	945	0	NR
430	38	NR	560	210	NR	690	46	NR	820	1	NR	950	0	NR
435	63	NR	565	219	NR	695	39	NR	825	1	NR	955	0	NR
440	102	NR	570	228	NR	700	33	NR	830	1	NR	960	0	NR
445	144	NR	575	238	NR	705	28	NR	835	1	NR	965	0	NR
450	128	NR	580	247	NR	710	24	NR	840	0	NR	970	0	NR
455	83	NR	585	257	NR	715	20	NR	845	0	NR	975	0	NR
460	68	NR	590	264	NR	720	18	NR	850	0	NR	980	0	NR
465	55	NR	595	267	NR	725	15	NR	855	0	NR	985	0	NR
470	43	NR	600	273	NR	730	13	NR	860	0	NR	990	0	NR
475	42	NR	605	278	NR	735	11	NR	865	0	NR	995	0	NR
480	47	NR	610	311	NR	740	9	NR	870	0	NR	1000	0	NR
485	58	NR	615	333	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2510-566-2-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.45**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	74	NR	620	290	NR	750	7	NR	880	0	NR
365	0	NR	495	94	NR	625	297	NR	755	6	NR	885	0	NR
370	0	NR	500	113	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	130	NR	635	606	NR	765	4	NR	895	0	NR
380	0	NR	510	143	NR	640	189	NR	770	3	NR	900	0	NR
385	0	NR	515	154	NR	645	190	NR	775	3	NR	905	0	NR
390	1	NR	520	162	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	166	NR	655	134	NR	785	2	NR	915	0	NR
400	2	NR	530	171	NR	660	114	NR	790	2	NR	920	0	NR
405	3	NR	535	176	NR	665	96	NR	795	2	NR	925	0	NR
410	4	NR	540	182	NR	670	89	NR	800	1	NR	930	0	NR
415	7	NR	545	187	NR	675	72	NR	805	1	NR	935	0	NR
420	14	NR	550	194	NR	680	62	NR	810	1	NR	940	0	NR
425	23	NR	555	202	NR	685	53	NR	815	1	NR	945	0	NR
430	38	NR	560	210	NR	690	46	NR	820	1	NR	950	0	NR
435	63	NR	565	219	NR	695	39	NR	825	1	NR	955	0	NR
440	102	NR	570	228	NR	700	33	NR	830	1	NR	960	0	NR
445	144	NR	575	238	NR	705	28	NR	835	1	NR	965	0	NR
450	128	NR	580	247	NR	710	24	NR	840	0	NR	970	0	NR
455	83	NR	585	257	NR	715	20	NR	845	0	NR	975	0	NR
460	68	NR	590	264	NR	720	18	NR	850	0	NR	980	0	NR
465	55	NR	595	267	NR	725	15	NR	855	0	NR	985	0	NR
470	43	NR	600	273	NR	730	13	NR	860	0	NR	990	0	NR
475	42	NR	605	278	NR	735	11	NR	865	0	NR	995	0	NR
480	47	NR	610	311	NR	740	9	NR	870	0	NR	1000	0	NR
485	58	NR	615	333	NR	745	8	NR	875	0	NR			


REPORT NUMBER: SP1-2510-566-2-R2

TM-30-18


Summary


R_f = 89.8
R_g = 102.5
CIE R_a = 93.3
R_9 = 56.5


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2510-566-2-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 88	CES51 = 92	CES76 = 89
CES02 = 64	CES27 = 97	CES52 = 93	CES77 = 85
CES03 = 32	CES28 = 95	CES53 = 88	CES78 = 86
CES04 = 70	CES29 = 83	CES54 = 96	CES79 = 89
CES05 = 51	CES30 = 84	CES55 = 95	CES80 = 91
CES06 = 51	CES31 = 85	CES56 = 89	CES81 = 70
CES07 = 44	CES32 = 80	CES57 = 87	CES82 = 96
CES08 = 43	CES33 = 83	CES58 = 88	CES83 = 92
CES09 = 29	CES34 = 91	CES59 = 98	CES84 = 97
CES10 = 77	CES35 = 95	CES60 = 99	CES85 = 82
CES11 = 59	CES36 = 99	CES61 = 99	CES86 = 75
CES12 = 66	CES37 = 93	CES62 = 91	CES87 = 91
CES13 = 44	CES38 = 88	CES63 = 89	CES88 = 93
CES14 = 74	CES39 = 95	CES64 = 93	CES89 = 80
CES15 = 72	CES40 = 91	CES65 = 90	CES90 = 92
CES16 = 48	CES41 = 90	CES66 = 92	CES91 = 92
CES17 = 50	CES42 = 89	CES67 = 93	CES92 = 80
CES18 = 57	CES43 = 87	CES68 = 96	CES93 = 88
CES19 = 72	CES44 = 98	CES69 = 98	CES94 = 71
CES20 = 68	CES45 = 91	CES70 = 92	CES95 = 87
CES21 = 87	CES46 = 89	CES71 = 93	CES96 = 92
CES22 = 79	CES47 = 80	CES72 = 97	CES97 = 90
CES23 = 92	CES48 = 86	CES73 = 87	CES98 = 90
CES24 = 91	CES49 = 87	CES74 = 89	CES99 = 91
CES25 = 72	CES50 = 92	CES75 = 92	





REPORT NUMBER: SP1-2510-566-2-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2510-566-2-R2

TM-30-18

Measure Comparisons





(END OF REPORT)