

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29476)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV
Description: LUMIERE LANTERRA 1003 LED ACCENT/SIGN LUMINAIRE, FLUSH LENS, SPOT
OPTIC, WHITE HOUSING.
Light Source: (1) 4000K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp:	N/A	NEMA Type:	3H x 3V
Luminaire Lumens:	1345.9 lumens	Max Intensity:	10219.7 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	67.0 lumens/watt		
Luminous Opening:	Circular (Dia: 0.25' x H: 0')		
Beam Angle (50%):	16°H x 16°V	Field Angle (10%):	36.1°H x 36.1°V
Beam Lumens:	439.5 lumens	Field Lumens:	947.6 lumens
Beam Efficiency:	32.7%	Field Efficiency:	70.4%
Input Watts (W):	20.1		
Input Voltage (V):	120		
Input Current (Ain):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		

REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

Iso-Candela Plot






REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

Lumen Table

90	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0		
80	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0		
70	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	
60		0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0		
50	0.0	0.0	0.0	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.0	0.0	0.0
40		0.0	0.1	0.1	0.1	0.3	0.8	1.7	1.7	0.8	0.3	0.1	0.1	0.1	0.0	
30	0.0	0.0	0.1	0.1	0.3	1.9	9.9	17.3	17.3	9.9	1.9	0.3	0.1	0.1	0.0	0.0
20		0.0	0.1	0.1	0.7	9.3	24.9	42.2	42.2	24.9	9.3	0.7	0.1	0.1	0.0	
10	0.0	0.0	0.1	0.2	1.5	15.8	41.1	165.6	165.6	41.1	15.8	1.5	0.2	0.1	0.0	0.0
0		0.0	0.1	0.2	1.5	15.8	41.1	165.6	165.6	41.1	15.8	1.5	0.2	0.1	0.0	
-10	0.0	0.0	0.1	0.1	0.7	9.3	24.9	42.2	42.2	24.9	9.3	0.7	0.1	0.1	0.0	0.0
-20		0.0	0.1	0.1	0.3	1.9	9.9	17.3	17.3	9.9	1.9	0.3	0.1	0.1	0.0	
-30	0.0	0.0	0.1	0.1	0.1	0.3	0.8	1.7	1.7	0.8	0.3	0.1	0.1	0.1	0.0	0.0
-40		0.0	0.0	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.0	0.0	
-50	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0
-60		0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	
-70	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0
-80		0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	
-90	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0		


REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

Luminous Intensity Polar Plot



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

Luminous Intensity Plot



Beam:
H Angle: 16°
V Angle: 16°
Lumens: 439.5
Efficiency: 32.7%

Field:
H Angle: 36.1°
V Angle: 36.1°
Lumens: 947.6
Efficiency: 70.4%

Spill:
Lumens: 398.3
Efficiency: 29.6%

— Vertical Distribution through 0-Deg
- - Horizontal Distribution through 0-Deg



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	1
68.75°	0	0	0	0	0	0	0	0	0	0	1
67.5°	0	0	0	0	0	0	0	0	0	1	1
66.25°	0	0	0	0	0	0	0	0	0	1	1
65°	0	0	0	0	0	0	0	0	1	1	1
63.75°	0	0	0	0	0	0	0	0	1	1	1
62.5°	0	0	0	0	0	0	0	0	1	1	1
61.25°	0	0	0	0	0	0	0	1	1	1	1
60°	0	0	0	0	0	0	0	1	1	1	1
58.75°	0	0	0	0	0	0	0	1	1	1	1
57.5°	0	0	0	0	0	0	0	1	1	1	1
56.25°	0	0	0	0	0	0	1	1	1	1	1
55°	0	0	0	0	0	0	1	1	1	1	1
53.75°	0	0	0	0	0	0	1	1	1	1	1
52.5°	0	0	0	0	0	0	1	1	1	1	1
51.25°	0	0	0	0	0	0	1	1	1	1	1
50°	0	0	0	0	0	0	1	1	1	1	1
48.75°	0	0	0	0	0	1	1	1	1	1	1
47.5°	0	0	0	0	0	1	1	1	1	1	1
46.25°	0	0	0	0	0	1	1	1	1	1	1
45°	0	0	0	0	0	1	1	1	1	1	1
43.75°	0	0	0	0	0	1	1	1	1	1	1
42.5°	0	0	0	0	0	1	1	1	1	1	1
41.25°	0	0	0	0	0	1	1	1	1	1	1
40°	0	0	0	0	0	1	1	1	1	1	1
38.75°	0	0	0	0	0	1	1	1	1	1	1
37.5°	0	0	0	0	0	1	1	1	1	1	1
36.25°	0	0	0	0	0	1	1	1	1	1	1
35°	0	0	0	0	1	1	1	1	1	1	1



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	1	1	1	1	1	1	1
32.5°	0	0	0	0	1	1	1	1	1	1	1
31.25°	0	0	0	0	1	1	1	1	1	1	1
30°	0	0	0	0	1	1	1	1	1	1	1
28.75°	0	0	0	0	1	1	1	1	1	1	1
27.5°	0	0	0	0	1	1	1	1	1	1	1
26.25°	0	0	0	0	1	1	1	1	1	1	1
25°	0	0	0	0	1	1	1	1	1	1	1
23.75°	0	0	0	0	1	1	1	1	1	1	1
22.5°	0	0	0	0	1	1	1	1	1	1	1
21.25°	0	0	0	0	1	1	1	1	1	1	1
20°	0	0	0	0	1	1	1	1	1	1	1
18.75°	0	0	0	0	1	1	1	1	1	1	1
17.5°	0	0	0	0	1	1	1	1	1	1	1
16.25°	0	0	0	0	1	1	1	1	1	1	1
15°	0	0	0	0	1	1	1	1	1	1	1
13.75°	0	0	0	0	1	1	1	1	1	1	1
12.5°	0	0	0	0	1	1	1	1	1	1	1
11.25°	0	0	0	0	1	1	1	1	1	1	1
10°	0	0	0	0	1	1	1	1	1	1	1
8.75°	0	0	0	0	1	1	1	1	1	1	1
7.5°	0	0	0	0	1	1	1	1	1	1	1
6.25°	0	0	0	0	1	1	1	1	1	1	1
5°	0	0	0	0	1	1	1	1	1	1	1
3.75°	0	0	0	0	1	1	1	1	1	1	1
2.5°	0	0	0	0	1	1	1	1	1	1	1
1.25°	0	0	0	0	1	1	1	1	1	1	1
0°	0	0	0	0	1	1	1	1	1	1	1
-1.25°	0	0	0	0	1	1	1	1	1	1	1
-2.5°	0	0	0	0	1	1	1	1	1	1	1
-3.75°	0	0	0	0	1	1	1	1	1	1	1
-5°	0	0	0	0	1	1	1	1	1	1	1
-6.25°	0	0	0	0	1	1	1	1	1	1	1
-7.5°	0	0	0	0	1	1	1	1	1	1	1
-8.75°	0	0	0	0	1	1	1	1	1	1	1
-10°	0	0	0	0	1	1	1	1	1	1	1
-11.25°	0	0	0	0	1	1	1	1	1	1	1
-12.5°	0	0	0	0	1	1	1	1	1	1	1
-13.75°	0	0	0	0	1	1	1	1	1	1	1
-15°	0	0	0	0	1	1	1	1	1	1	1
-16.25°	0	0	0	0	1	1	1	1	1	1	1
-17.5°	0	0	0	0	1	1	1	1	1	1	1
-18.75°	0	0	0	0	1	1	1	1	1	1	1
-20°	0	0	0	0	1	1	1	1	1	1	1
-21.25°	0	0	0	0	1	1	1	1	1	1	1



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	1	1	1	1	1	1	1
-23.75°	0	0	0	0	1	1	1	1	1	1	1
-25°	0	0	0	0	1	1	1	1	1	1	1
-26.25°	0	0	0	0	1	1	1	1	1	1	1
-27.5°	0	0	0	0	1	1	1	1	1	1	1
-28.75°	0	0	0	0	1	1	1	1	1	1	1
-30°	0	0	0	0	1	1	1	1	1	1	1
-31.25°	0	0	0	0	1	1	1	1	1	1	1
-32.5°	0	0	0	0	1	1	1	1	1	1	1
-33.75°	0	0	0	0	1	1	1	1	1	1	1
-35°	0	0	0	0	1	1	1	1	1	1	1
-36.25°	0	0	0	0	0	1	1	1	1	1	1
-37.5°	0	0	0	0	0	1	1	1	1	1	1
-38.75°	0	0	0	0	0	1	1	1	1	1	1
-40°	0	0	0	0	0	1	1	1	1	1	1
-41.25°	0	0	0	0	0	1	1	1	1	1	1
-42.5°	0	0	0	0	0	1	1	1	1	1	1
-43.75°	0	0	0	0	0	1	1	1	1	1	1
-45°	0	0	0	0	0	1	1	1	1	1	1
-46.25°	0	0	0	0	0	1	1	1	1	1	1
-47.5°	0	0	0	0	0	1	1	1	1	1	1
-48.75°	0	0	0	0	0	1	1	1	1	1	1
-50°	0	0	0	0	0	0	1	1	1	1	1
-51.25°	0	0	0	0	0	0	1	1	1	1	1
-52.5°	0	0	0	0	0	0	1	1	1	1	1
-53.75°	0	0	0	0	0	0	1	1	1	1	1
-55°	0	0	0	0	0	0	1	1	1	1	1
-56.25°	0	0	0	0	0	0	1	1	1	1	1
-57.5°	0	0	0	0	0	0	0	1	1	1	1
-58.75°	0	0	0	0	0	0	0	1	1	1	1
-60°	0	0	0	0	0	0	0	1	1	1	1
-61.25°	0	0	0	0	0	0	0	1	1	1	1
-62.5°	0	0	0	0	0	0	0	0	1	1	1
-63.75°	0	0	0	0	0	0	0	0	1	1	1
-65°	0	0	0	0	0	0	0	0	1	1	1
-66.25°	0	0	0	0	0	0	0	0	0	1	1
-67.5°	0	0	0	0	0	0	0	0	0	1	1
-68.75°	0	0	0	0	0	0	0	0	0	0	1
-70°	0	0	0	0	0	0	0	0	0	0	1
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	1	1
78.75°	0	0	0	0	0	0	0	1	1	1	1
77.5°	0	0	0	0	0	1	1	1	1	1	1
76.25°	0	0	0	1	1	1	1	1	1	1	1
75°	0	0	1	1	1	1	1	1	1	1	1
73.75°	0	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	2
53.75°	1	1	1	1	1	1	1	1	1	1	2
52.5°	1	1	1	1	1	1	1	1	1	2	2
51.25°	1	1	1	1	1	1	1	1	1	2	2
50°	1	1	1	1	1	1	1	1	2	2	2
48.75°	1	1	1	1	1	1	1	1	2	2	2
47.5°	1	1	1	1	1	1	1	2	2	2	2
46.25°	1	1	1	1	1	1	1	2	2	2	2
45°	1	1	1	1	1	1	2	2	2	2	2
43.75°	1	1	1	1	1	1	2	2	2	2	2
42.5°	1	1	1	1	1	1	2	2	2	2	2
41.25°	1	1	1	1	1	2	2	2	2	2	2
40°	1	1	1	1	1	2	2	2	2	2	2
38.75°	1	1	1	1	1	2	2	2	2	2	2
37.5°	1	1	1	1	2	2	2	2	2	2	2
36.25°	1	1	1	1	2	2	2	2	2	2	2
35°	1	1	1	1	2	2	2	2	2	2	2



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	1	1	1	1	2	2	2	2	2	2	2
32.5°	1	1	1	2	2	2	2	2	2	2	2
31.25°	1	1	1	2	2	2	2	2	2	2	2
30°	1	1	1	2	2	2	2	2	2	2	2
28.75°	1	1	1	2	2	2	2	2	2	2	3
27.5°	1	1	1	2	2	2	2	2	2	2	3
26.25°	1	1	1	2	2	2	2	2	2	2	3
25°	1	1	2	2	2	2	2	2	2	2	3
23.75°	1	1	2	2	2	2	2	2	2	2	3
22.5°	1	1	2	2	2	2	2	2	2	3	3
21.25°	1	1	2	2	2	2	2	2	2	3	3
20°	1	1	2	2	2	2	2	2	2	3	3
18.75°	1	1	2	2	2	2	2	2	2	3	3
17.5°	1	1	2	2	2	2	2	2	2	3	3
16.25°	1	1	2	2	2	2	2	2	2	3	3
15°	1	1	2	2	2	2	2	2	3	3	3
13.75°	1	1	2	2	2	2	2	2	3	3	3
12.5°	1	1	2	2	2	2	2	2	3	3	3
11.25°	1	2	2	2	2	2	2	2	3	3	3
10°	1	2	2	2	2	2	2	2	3	3	3
8.75°	1	2	2	2	2	2	2	2	3	3	3
7.5°	1	2	2	2	2	2	2	2	3	3	3
6.25°	1	2	2	2	2	2	2	2	3	3	3
5°	1	2	2	2	2	2	2	2	3	3	3
3.75°	1	2	2	2	2	2	2	2	3	3	3
2.5°	1	2	2	2	2	2	2	2	3	3	3
1.25°	1	2	2	2	2	2	2	2	3	3	3
0°	1	2	2	2	2	2	2	2	3	3	3
-1.25°	1	2	2	2	2	2	2	2	3	3	3
-2.5°	1	2	2	2	2	2	2	2	3	3	3
-3.75°	1	2	2	2	2	2	2	2	3	3	3
-5°	1	2	2	2	2	2	2	2	3	3	3
-6.25°	1	2	2	2	2	2	2	2	3	3	3
-7.5°	1	2	2	2	2	2	2	2	3	3	3
-8.75°	1	2	2	2	2	2	2	2	3	3	3
-10°	1	2	2	2	2	2	2	2	3	3	3
-11.25°	1	2	2	2	2	2	2	2	3	3	3
-12.5°	1	1	2	2	2	2	2	2	3	3	3
-13.75°	1	1	2	2	2	2	2	2	3	3	3
-15°	1	1	2	2	2	2	2	2	3	3	3
-16.25°	1	1	2	2	2	2	2	2	2	3	3
-17.5°	1	1	2	2	2	2	2	2	2	3	3
-18.75°	1	1	2	2	2	2	2	2	2	3	3
-20°	1	1	2	2	2	2	2	2	2	3	3
-21.25°	1	1	2	2	2	2	2	2	2	3	3



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	1	1	2	2	2	2	2	2	2	3	3
-23.75°	1	1	2	2	2	2	2	2	2	2	3
-25°	1	1	2	2	2	2	2	2	2	2	3
-26.25°	1	1	1	2	2	2	2	2	2	2	3
-27.5°	1	1	1	2	2	2	2	2	2	2	3
-28.75°	1	1	1	2	2	2	2	2	2	2	3
-30°	1	1	1	2	2	2	2	2	2	2	2
-31.25°	1	1	1	2	2	2	2	2	2	2	2
-32.5°	1	1	1	2	2	2	2	2	2	2	2
-33.75°	1	1	1	1	2	2	2	2	2	2	2
-35°	1	1	1	1	2	2	2	2	2	2	2
-36.25°	1	1	1	1	2	2	2	2	2	2	2
-37.5°	1	1	1	1	2	2	2	2	2	2	2
-38.75°	1	1	1	1	1	2	2	2	2	2	2
-40°	1	1	1	1	1	2	2	2	2	2	2
-41.25°	1	1	1	1	1	2	2	2	2	2	2
-42.5°	1	1	1	1	1	1	2	2	2	2	2
-43.75°	1	1	1	1	1	1	2	2	2	2	2
-45°	1	1	1	1	1	1	2	2	2	2	2
-46.25°	1	1	1	1	1	1	1	2	2	2	2
-47.5°	1	1	1	1	1	1	1	2	2	2	2
-48.75°	1	1	1	1	1	1	1	1	2	2	2
-50°	1	1	1	1	1	1	1	1	2	2	2
-51.25°	1	1	1	1	1	1	1	1	1	2	2
-52.5°	1	1	1	1	1	1	1	1	1	2	2
-53.75°	1	1	1	1	1	1	1	1	1	1	2
-55°	1	1	1	1	1	1	1	1	1	1	2
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	0	1	1	1	1	1	1	1	1	1	1
-75°	0	0	1	1	1	1	1	1	1	1	1
-76.25°	0	0	0	1	1	1	1	1	1	1	1
-77.5°	0	0	0	0	0	1	1	1	1	1	1



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	1	1	1	1
-80°	0	0	0	0	0	0	0	0	0	1	1
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	1	1	1	1	1	1
81.25°	0	1	1	1	1	1	1	1	1	1	1
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	2
65°	1	1	1	1	1	1	1	1	2	2	2
63.75°	1	1	1	1	1	1	2	2	2	2	2
62.5°	1	1	1	1	1	2	2	2	2	2	2
61.25°	1	1	1	1	2	2	2	2	2	2	2
60°	1	1	1	2	2	2	2	2	2	2	2
58.75°	1	1	2	2	2	2	2	2	2	2	2
57.5°	1	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	2
53.75°	2	2	2	2	2	2	2	2	2	2	2
52.5°	2	2	2	2	2	2	2	2	2	2	3
51.25°	2	2	2	2	2	2	2	2	2	3	3
50°	2	2	2	2	2	2	2	2	3	3	3
48.75°	2	2	2	2	2	2	2	3	3	3	3
47.5°	2	2	2	2	2	2	2	3	3	3	3
46.25°	2	2	2	2	2	2	3	3	3	3	3
45°	2	2	2	2	2	3	3	3	3	3	3
43.75°	2	2	2	2	3	3	3	3	3	3	3
42.5°	2	2	2	2	3	3	3	3	3	3	3
41.25°	2	2	2	3	3	3	3	3	3	3	4
40°	2	2	2	3	3	3	3	3	3	4	4
38.75°	2	2	3	3	3	3	3	3	3	4	4
37.5°	2	2	3	3	3	3	3	3	4	4	4
36.25°	2	3	3	3	3	3	3	4	4	4	4
35°	2	3	3	3	3	3	3	4	4	4	4



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	2	3	3	3	3	3	4	4	4	4	4
32.5°	3	3	3	3	3	3	4	4	4	4	4
31.25°	3	3	3	3	3	3	4	4	4	4	4
30°	3	3	3	3	3	4	4	4	4	4	4
28.75°	3	3	3	3	3	4	4	4	4	4	4
27.5°	3	3	3	3	4	4	4	4	4	4	4
26.25°	3	3	3	3	4	4	4	4	4	4	4
25°	3	3	3	3	4	4	4	4	4	4	4
23.75°	3	3	3	3	4	4	4	4	4	4	4
22.5°	3	3	3	4	4	4	4	4	4	4	4
21.25°	3	3	3	4	4	4	4	4	4	4	5
20°	3	3	3	4	4	4	4	4	4	4	5
18.75°	3	3	3	4	4	4	4	4	4	4	5
17.5°	3	3	4	4	4	4	4	4	4	5	5
16.25°	3	3	4	4	4	4	4	4	4	5	5
15°	3	3	4	4	4	4	4	4	4	5	5
13.75°	3	3	4	4	4	4	4	4	4	5	5
12.5°	3	3	4	4	4	4	4	4	4	5	5
11.25°	3	3	4	4	4	4	4	4	5	5	5
10°	3	3	4	4	4	4	4	4	5	5	5
8.75°	3	3	4	4	4	4	4	4	5	5	5
7.5°	3	4	4	4	4	4	4	4	5	5	5
6.25°	3	4	4	4	4	4	4	4	5	5	5
5°	3	4	4	4	4	4	4	4	5	5	5
3.75°	3	4	4	4	4	4	4	4	5	5	5
2.5°	3	4	4	4	4	4	4	4	5	5	5
1.25°	3	4	4	4	4	4	4	4	5	5	5
0°	3	4	4	4	4	4	4	4	5	5	5
-1.25°	3	4	4	4	4	4	4	4	5	5	5
-2.5°	3	4	4	4	4	4	4	4	5	5	5
-3.75°	3	4	4	4	4	4	4	4	5	5	5
-5°	3	4	4	4	4	4	4	4	5	5	5
-6.25°	3	4	4	4	4	4	4	4	5	5	5
-7.5°	3	4	4	4	4	4	4	4	5	5	5
-8.75°	3	3	4	4	4	4	4	4	5	5	5
-10°	3	3	4	4	4	4	4	4	5	5	5
-11.25°	3	3	4	4	4	4	4	4	5	5	5
-12.5°	3	3	4	4	4	4	4	4	4	5	5
-13.75°	3	3	4	4	4	4	4	4	4	5	5
-15°	3	3	4	4	4	4	4	4	4	5	5
-16.25°	3	3	4	4	4	4	4	4	4	5	5
-17.5°	3	3	4	4	4	4	4	4	4	5	5
-18.75°	3	3	3	4	4	4	4	4	4	4	5
-20°	3	3	3	4	4	4	4	4	4	4	5
-21.25°	3	3	3	4	4	4	4	4	4	4	5



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	3	3	3	4	4	4	4	4	4	4	4
-23.75°	3	3	3	3	4	4	4	4	4	4	4
-25°	3	3	3	3	4	4	4	4	4	4	4
-26.25°	3	3	3	3	4	4	4	4	4	4	4
-27.5°	3	3	3	3	4	4	4	4	4	4	4
-28.75°	3	3	3	3	3	4	4	4	4	4	4
-30°	3	3	3	3	3	4	4	4	4	4	4
-31.25°	3	3	3	3	3	3	4	4	4	4	4
-32.5°	3	3	3	3	3	3	4	4	4	4	4
-33.75°	2	3	3	3	3	3	4	4	4	4	4
-35°	2	3	3	3	3	3	3	4	4	4	4
-36.25°	2	3	3	3	3	3	3	4	4	4	4
-37.5°	2	2	3	3	3	3	3	3	4	4	4
-38.75°	2	2	3	3	3	3	3	3	3	4	4
-40°	2	2	2	3	3	3	3	3	3	4	4
-41.25°	2	2	2	3	3	3	3	3	3	3	4
-42.5°	2	2	2	2	3	3	3	3	3	3	3
-43.75°	2	2	2	2	3	3	3	3	3	3	3
-45°	2	2	2	2	2	3	3	3	3	3	3
-46.25°	2	2	2	2	2	2	3	3	3	3	3
-47.5°	2	2	2	2	2	2	2	3	3	3	3
-48.75°	2	2	2	2	2	2	2	3	3	3	3
-50°	2	2	2	2	2	2	2	2	3	3	3
-51.25°	2	2	2	2	2	2	2	2	2	3	3
-52.5°	2	2	2	2	2	2	2	2	2	2	3
-53.75°	2	2	2	2	2	2	2	2	2	2	2
-55°	2	2	2	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	1	2	2	2	2	2	2	2	2	2	2
-58.75°	1	1	2	2	2	2	2	2	2	2	2
-60°	1	1	1	2	2	2	2	2	2	2	2
-61.25°	1	1	1	1	2	2	2	2	2	2	2
-62.5°	1	1	1	1	1	2	2	2	2	2	2
-63.75°	1	1	1	1	1	1	2	2	2	2	2
-65°	1	1	1	1	1	1	1	1	2	2	2
-66.25°	1	1	1	1	1	1	1	1	1	1	2
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	0	1	1	1	1	1	1	1	1	1	1
-82.5°	0	0	0	0	0	1	1	1	1	1	1
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	1	1	1	1	1	1	1	1	1	1	1
82.5°	1	1	1	1	1	1	1	1	1	1	1
81.25°	1	1	1	1	1	1	1	1	1	1	1
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	2	2
70°	1	1	1	1	1	1	2	2	2	2	2
68.75°	1	1	1	2	2	2	2	2	2	2	2
67.5°	1	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	3
60°	2	2	2	2	2	2	2	2	3	3	3
58.75°	2	2	2	2	2	2	3	3	3	3	3
57.5°	2	2	2	2	3	3	3	3	3	3	3
56.25°	2	2	2	3	3	3	3	3	3	3	3
55°	2	2	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	4
52.5°	3	3	3	3	3	3	3	3	3	4	4
51.25°	3	3	3	3	3	3	3	4	4	4	4
50°	3	3	3	3	3	3	4	4	4	4	4
48.75°	3	3	3	3	4	4	4	4	4	4	4
47.5°	3	3	3	4	4	4	4	4	4	4	4
46.25°	3	3	4	4	4	4	4	4	4	4	4
45°	3	4	4	4	4	4	4	4	4	4	4
43.75°	4	4	4	4	4	4	4	4	4	4	4
42.5°	4	4	4	4	4	4	4	4	4	4	4
41.25°	4	4	4	4	4	4	4	4	4	5	5
40°	4	4	4	4	4	4	4	4	5	5	5
38.75°	4	4	4	4	4	4	4	5	5	5	5
37.5°	4	4	4	4	4	4	5	5	5	5	5
36.25°	4	4	4	4	4	4	5	5	5	5	5
35°	4	4	4	4	4	5	5	5	5	5	5



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	4	4	4	4	5	5	5	5	5	5	5
32.5°	4	4	4	5	5	5	5	5	5	5	6
31.25°	4	4	4	5	5	5	5	5	5	6	6
30°	4	4	5	5	5	5	5	5	6	6	7
28.75°	4	4	5	5	5	5	5	6	6	7	7
27.5°	4	5	5	5	5	5	5	6	6	7	8
26.25°	4	5	5	5	5	5	6	6	7	7	8
25°	5	5	5	5	5	5	6	6	7	8	8
23.75°	5	5	5	5	5	6	6	7	7	8	9
22.5°	5	5	5	5	5	6	6	7	8	8	11
21.25°	5	5	5	5	6	6	7	7	8	9	13
20°	5	5	5	5	6	6	7	8	8	11	15
18.75°	5	5	5	5	6	7	7	8	9	13	17
17.5°	5	5	5	6	6	7	8	8	11	15	18
16.25°	5	5	5	6	6	7	8	9	12	16	20
15°	5	5	5	6	7	7	8	9	13	17	21
13.75°	5	5	6	6	7	8	8	11	15	19	22
12.5°	5	5	6	6	7	8	9	12	16	20	23
11.25°	5	5	6	6	7	8	9	13	17	21	24
10°	5	5	6	7	7	8	10	14	18	21	25
8.75°	5	5	6	7	7	8	10	15	19	22	26
7.5°	5	5	6	7	8	8	11	15	19	23	27
6.25°	5	6	6	7	8	8	12	16	20	23	28
5°	5	6	6	7	8	9	12	16	20	24	28
3.75°	5	6	6	7	8	9	13	17	21	24	29
2.5°	5	6	6	7	8	9	13	17	21	24	29
1.25°	5	6	6	7	8	9	13	17	21	25	29
0°	5	6	6	7	8	9	13	17	21	25	29
-1.25°	5	6	6	7	8	9	13	17	21	25	29
-2.5°	5	6	6	7	8	9	13	17	21	24	29
-3.75°	5	6	6	7	8	9	13	17	21	24	29
-5°	5	6	6	7	8	9	12	16	20	24	28
-6.25°	5	6	6	7	8	8	12	16	20	23	28
-7.5°	5	5	6	7	8	8	11	15	19	23	27
-8.75°	5	5	6	7	7	8	10	15	19	22	26
-10°	5	5	6	7	7	8	10	14	18	21	25
-11.25°	5	5	6	6	7	8	9	13	17	21	24
-12.5°	5	5	6	6	7	8	9	12	16	20	23
-13.75°	5	5	6	6	7	8	8	11	15	19	22
-15°	5	5	5	6	7	7	8	9	13	17	21
-16.25°	5	5	5	6	6	7	8	9	12	16	20
-17.5°	5	5	5	6	6	7	8	8	11	15	18
-18.75°	5	5	5	5	6	7	7	8	9	13	17
-20°	5	5	5	5	6	6	7	8	8	11	15
-21.25°	5	5	5	5	6	6	7	7	8	9	13



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	5	5	5	5	5	6	6	7	8	8	11
-23.75°	5	5	5	5	5	6	6	7	7	8	9
-25°	5	5	5	5	5	5	6	6	7	8	8
-26.25°	4	5	5	5	5	5	6	6	7	7	8
-27.5°	4	5	5	5	5	5	5	6	6	7	8
-28.75°	4	4	5	5	5	5	5	6	6	7	7
-30°	4	4	5	5	5	5	5	5	6	6	7
-31.25°	4	4	4	5	5	5	5	5	5	6	6
-32.5°	4	4	4	5	5	5	5	5	5	5	6
-33.75°	4	4	4	4	5	5	5	5	5	5	5
-35°	4	4	4	4	4	5	5	5	5	5	5
-36.25°	4	4	4	4	4	4	5	5	5	5	5
-37.5°	4	4	4	4	4	4	5	5	5	5	5
-38.75°	4	4	4	4	4	4	4	5	5	5	5
-40°	4	4	4	4	4	4	4	4	5	5	5
-41.25°	4	4	4	4	4	4	4	4	4	5	5
-42.5°	4	4	4	4	4	4	4	4	4	4	4
-43.75°	4	4	4	4	4	4	4	4	4	4	4
-45°	3	4	4	4	4	4	4	4	4	4	4
-46.25°	3	3	4	4	4	4	4	4	4	4	4
-47.5°	3	3	3	4	4	4	4	4	4	4	4
-48.75°	3	3	3	3	4	4	4	4	4	4	4
-50°	3	3	3	3	3	3	4	4	4	4	4
-51.25°	3	3	3	3	3	3	3	4	4	4	4
-52.5°	3	3	3	3	3	3	3	3	3	4	4
-53.75°	3	3	3	3	3	3	3	3	3	3	4
-55°	2	2	3	3	3	3	3	3	3	3	3
-56.25°	2	2	2	3	3	3	3	3	3	3	3
-57.5°	2	2	2	2	3	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	3	3	3	3	3
-60°	2	2	2	2	2	2	2	2	3	3	3
-61.25°	2	2	2	2	2	2	2	2	2	2	3
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	1	2	2	2	2	2	2	2	2	2	2
-68.75°	1	1	1	2	2	2	2	2	2	2	2
-70°	1	1	1	1	1	1	2	2	2	2	2
-71.25°	1	1	1	1	1	1	1	1	1	2	2
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	1	1	1	1	1	1	1	1	1	1	1
-82.5°	1	1	1	1	1	1	1	1	1	1	1
-83.75°	1	1	1	1	1	1	1	1	1	1	1
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	1	1	1	1	1	1	1	1	1	1	1
83.75°	1	1	1	1	1	1	1	1	1	1	1
82.5°	1	1	1	1	1	1	1	1	1	1	1
81.25°	1	1	1	1	1	1	1	1	1	1	1
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	2	2	2
72.5°	1	1	2	2	2	2	2	2	2	2	2
71.25°	2	2	2	2	2	2	2	2	2	2	2
70°	2	2	2	2	2	2	2	2	2	2	2
68.75°	2	2	2	2	2	2	2	2	2	2	2
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	3
63.75°	2	2	2	2	2	3	3	3	3	3	3
62.5°	2	2	3	3	3	3	3	3	3	3	3
61.25°	3	3	3	3	3	3	3	3	3	3	3
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	3	3	3	3	3	3	3	3	3	3	4
57.5°	3	3	3	3	3	3	4	4	4	4	4
56.25°	3	3	3	3	4	4	4	4	4	4	4
55°	3	4	4	4	4	4	4	4	4	4	4
53.75°	4	4	4	4	4	4	4	4	4	4	4
52.5°	4	4	4	4	4	4	4	4	4	4	4
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	5	5	5
47.5°	4	4	4	4	4	4	5	5	5	5	5
46.25°	4	4	4	4	5	5	5	5	5	5	5
45°	4	4	5	5	5	5	5	5	5	5	5
43.75°	4	5	5	5	5	5	5	5	5	5	5
42.5°	5	5	5	5	5	5	5	5	5	6	6
41.25°	5	5	5	5	5	5	5	6	6	6	6
40°	5	5	5	5	5	6	6	6	6	7	7
38.75°	5	5	5	5	6	6	6	7	7	7	8
37.5°	5	5	5	6	6	7	7	7	8	8	8
36.25°	5	5	6	6	7	7	8	8	8	9	11
35°	5	6	6	7	7	8	8	9	10	12	15



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	6	6	7	7	8	8	9	11	14	16	18
32.5°	6	7	7	8	8	9	12	14	17	19	21
31.25°	7	7	8	8	10	12	15	18	20	22	24
30°	7	8	8	10	12	15	18	20	22	24	27
28.75°	8	8	9	12	15	18	20	23	25	28	31
27.5°	8	9	12	15	18	20	23	25	28	31	35
26.25°	9	11	14	18	20	23	25	29	32	37	51
25°	10	14	17	20	22	25	28	32	38	53	67
23.75°	12	16	19	22	24	28	31	37	53	68	94
22.5°	15	18	21	24	27	31	35	51	67	94	148
21.25°	17	20	23	26	30	33	48	64	87	145	201
20°	18	21	24	28	32	42	60	77	135	194	256
18.75°	20	23	26	30	36	54	72	118	181	243	320
17.5°	21	25	29	33	46	65	96	161	224	301	384
16.25°	23	26	31	37	56	75	134	201	274	360	447
15°	24	28	32	46	66	102	171	239	325	416	505
13.75°	25	30	34	54	74	134	204	284	376	470	556
12.5°	27	31	42	62	93	165	236	327	424	517	602
11.25°	28	33	48	69	119	192	273	369	468	560	644
10°	29	34	55	76	143	217	307	407	506	596	676
8.75°	31	39	60	89	165	241	338	441	539	629	705
7.5°	31	43	65	107	183	266	367	471	568	656	725
6.25°	32	47	69	122	199	288	391	496	592	676	742
5°	33	51	72	135	213	305	411	516	611	694	755
3.75°	33	53	75	145	223	320	427	531	626	707	765
2.5°	34	55	77	152	230	330	438	542	637	715	772
1.25°	34	56	78	156	235	337	445	549	643	719	776
0°	34	56	79	157	236	339	447	551	645	721	777
-1.25°	34	56	78	156	235	337	445	549	643	719	776
-2.5°	34	55	77	152	230	330	438	542	637	715	772
-3.75°	33	53	75	145	223	320	427	531	626	707	765
-5°	33	51	72	135	213	305	411	516	611	694	755
-6.25°	32	47	69	122	199	288	391	496	592	676	742
-7.5°	31	43	65	107	183	266	367	471	568	656	725
-8.75°	31	39	60	89	165	241	338	441	539	629	705
-10°	29	34	55	76	143	217	307	407	506	596	676
-11.25°	28	33	48	69	119	192	273	369	468	560	644
-12.5°	27	31	42	62	93	165	236	327	424	517	602
-13.75°	25	30	34	54	74	134	204	284	376	470	556
-15°	24	28	32	46	66	102	171	239	325	416	505
-16.25°	23	26	31	37	56	75	134	201	274	360	447
-17.5°	21	25	29	33	46	65	96	161	224	301	384
-18.75°	20	23	26	30	36	54	72	118	181	243	320
-20°	18	21	24	28	32	42	60	77	135	194	256
-21.25°	17	20	23	26	30	33	48	64	87	145	201



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	15	18	21	24	27	31	35	51	67	94	148
-23.75°	12	16	19	22	24	28	31	37	53	68	94
-25°	10	14	17	20	22	25	28	32	38	53	67
-26.25°	9	11	14	18	20	23	25	29	32	37	51
-27.5°	8	9	12	15	18	20	23	25	28	31	35
-28.75°	8	8	9	12	15	18	20	23	25	28	31
-30°	7	8	8	10	12	15	18	20	22	24	27
-31.25°	7	7	8	8	10	12	15	18	20	22	24
-32.5°	6	7	7	8	8	9	12	14	17	19	21
-33.75°	6	6	7	7	8	8	9	11	14	16	18
-35°	5	6	6	7	7	8	8	9	10	12	15
-36.25°	5	5	6	6	7	7	8	8	8	9	11
-37.5°	5	5	5	6	6	7	7	7	8	8	8
-38.75°	5	5	5	5	6	6	6	7	7	7	8
-40°	5	5	5	5	5	6	6	6	6	7	7
-41.25°	5	5	5	5	5	5	5	6	6	6	6
-42.5°	5	5	5	5	5	5	5	5	5	6	6
-43.75°	4	5	5	5	5	5	5	5	5	5	5
-45°	4	4	5	5	5	5	5	5	5	5	5
-46.25°	4	4	4	4	5	5	5	5	5	5	5
-47.5°	4	4	4	4	4	4	5	5	5	5	5
-48.75°	4	4	4	4	4	4	4	4	5	5	5
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	4	4	4	4	4	4	4	4	4	4	4
-55°	3	4	4	4	4	4	4	4	4	4	4
-56.25°	3	3	3	3	4	4	4	4	4	4	4
-57.5°	3	3	3	3	3	3	4	4	4	4	4
-58.75°	3	3	3	3	3	3	3	3	3	3	4
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	3	3	3	3	3	3	3	3	3	3	3
-62.5°	2	2	3	3	3	3	3	3	3	3	3
-63.75°	2	2	2	2	2	3	3	3	3	3	3
-65°	2	2	2	2	2	2	2	2	2	2	3
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	2	2	2	2	2	2	2	2	2	2	2
-70°	2	2	2	2	2	2	2	2	2	2	2
-71.25°	2	2	2	2	2	2	2	2	2	2	2
-72.5°	1	1	2	2	2	2	2	2	2	2	2
-73.75°	1	1	1	1	1	1	1	1	2	2	2
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	1	1	1	1	1	1	1	1	1	1	1
-82.5°	1	1	1	1	1	1	1	1	1	1	1
-83.75°	1	1	1	1	1	1	1	1	1	1	1
-85°	1	1	1	1	1	1	1	1	1	1	1
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	1	1	1	1	1	1	1	1	1	1	1
83.75°	1	1	1	1	1	1	1	1	1	1	1
82.5°	1	1	1	1	1	1	1	1	1	1	1
81.25°	1	1	1	1	1	1	1	1	1	1	1
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	2	2	2
73.75°	2	2	2	2	2	2	2	2	2	2	2
72.5°	2	2	2	2	2	2	2	2	2	2	2
71.25°	2	2	2	2	2	2	2	2	2	2	2
70°	2	2	2	2	2	2	2	2	2	2	2
68.75°	2	2	2	2	2	2	2	2	2	2	2
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	3	3	3	3	3	3
65°	3	3	3	3	3	3	3	3	3	3	3
63.75°	3	3	3	3	3	3	3	3	3	3	3
62.5°	3	3	3	3	3	3	3	3	3	3	3
61.25°	3	3	3	3	3	3	3	3	3	3	3
60°	3	3	3	4	4	4	4	4	4	4	4
58.75°	4	4	4	4	4	4	4	4	4	4	4
57.5°	4	4	4	4	4	4	4	4	4	4	4
56.25°	4	4	4	4	4	4	4	4	4	4	4
55°	4	4	4	4	4	4	4	4	4	4	4
53.75°	4	4	4	4	4	4	4	4	4	4	4
52.5°	4	4	4	4	4	4	4	4	5	5	5
51.25°	4	4	4	5	5	5	5	5	5	5	5
50°	5	5	5	5	5	5	5	5	5	5	5
48.75°	5	5	5	5	5	5	5	5	5	5	5
47.5°	5	5	5	5	5	5	5	5	5	5	5
46.25°	5	5	5	5	5	5	6	6	6	6	6
45°	5	5	5	6	6	6	6	6	6	7	7
43.75°	6	6	6	6	6	7	7	7	7	7	7
42.5°	6	6	7	7	7	7	8	8	8	8	8
41.25°	7	7	7	8	8	8	8	9	9	10	10
40°	7	8	8	8	9	9	11	12	13	14	15
38.75°	8	8	9	11	12	13	15	16	17	18	19
37.5°	9	11	13	15	16	17	19	20	21	21	22
36.25°	13	15	17	18	20	21	22	23	24	25	26
35°	17	18	20	21	23	24	25	27	28	29	31

REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	20	21	23	25	26	28	30	31	33	34	39
32.5°	23	24	26	29	31	32	34	42	48	55	60
31.25°	26	28	30	33	37	46	54	62	69	76	89
30°	30	32	36	46	56	66	74	93	119	143	165
28.75°	33	42	54	65	75	102	134	165	192	217	241
27.5°	48	60	72	96	134	171	204	236	273	307	338
26.25°	64	77	118	161	201	239	284	327	369	407	441
25°	87	135	181	224	274	325	376	424	468	506	539
23.75°	145	194	243	301	360	416	470	517	560	596	629
22.5°	201	256	320	384	447	505	556	602	644	676	705
21.25°	261	329	399	467	529	585	635	677	713	738	760
20°	329	404	478	544	604	657	702	735	763	787	808
18.75°	399	478	549	613	670	716	751	781	808	835	861
17.5°	467	544	613	674	723	761	793	825	857	889	922
16.25°	529	604	670	723	764	799	835	873	912	951	995
15°	585	657	716	761	799	838	881	926	975	1027	1081
13.75°	635	702	751	793	835	881	931	988	1050	1114	1195
12.5°	677	735	781	825	873	926	988	1057	1136	1231	1349
11.25°	713	763	808	857	912	975	1050	1136	1247	1383	1536
10°	738	787	835	889	951	1027	1114	1231	1383	1558	1772
8.75°	760	808	861	922	995	1081	1195	1349	1536	1772	2068
7.5°	778	829	885	952	1036	1139	1284	1472	1711	2023	2428
6.25°	793	846	909	984	1076	1198	1372	1591	1892	2299	2846
5°	806	863	929	1011	1110	1257	1459	1723	2086	2590	3293
3.75°	817	876	945	1034	1147	1312	1532	1829	2262	2889	3735
2.5°	825	885	958	1052	1173	1352	1586	1930	2421	3135	4075
1.25°	829	891	967	1062	1190	1376	1629	1994	2518	3287	4306
0°	831	893	970	1066	1195	1384	1644	2015	2551	3338	4388
-1.25°	829	891	967	1062	1190	1376	1629	1994	2518	3287	4306
-2.5°	825	885	958	1052	1173	1352	1586	1930	2421	3135	4075
-3.75°	817	876	945	1034	1147	1312	1532	1829	2262	2889	3735
-5°	806	863	929	1011	1110	1257	1459	1723	2086	2590	3293
-6.25°	793	846	909	984	1076	1198	1372	1591	1892	2299	2846
-7.5°	778	829	885	952	1036	1139	1284	1472	1711	2023	2428
-8.75°	760	808	861	922	995	1081	1195	1349	1536	1772	2068
-10°	738	787	835	889	951	1027	1114	1231	1383	1558	1772
-11.25°	713	763	808	857	912	975	1050	1136	1247	1383	1536
-12.5°	677	735	781	825	873	926	988	1057	1136	1231	1349
-13.75°	635	702	751	793	835	881	931	988	1050	1114	1195
-15°	585	657	716	761	799	838	881	926	975	1027	1081
-16.25°	529	604	670	723	764	799	835	873	912	951	995
-17.5°	467	544	613	674	723	761	793	825	857	889	922
-18.75°	399	478	549	613	670	716	751	781	808	835	861
-20°	329	404	478	544	604	657	702	735	763	787	808
-21.25°	261	329	399	467	529	585	635	677	713	738	760



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	201	256	320	384	447	505	556	602	644	676	705
-23.75°	145	194	243	301	360	416	470	517	560	596	629
-25°	87	135	181	224	274	325	376	424	468	506	539
-26.25°	64	77	118	161	201	239	284	327	369	407	441
-27.5°	48	60	72	96	134	171	204	236	273	307	338
-28.75°	33	42	54	65	75	102	134	165	192	217	241
-30°	30	32	36	46	56	66	74	93	119	143	165
-31.25°	26	28	30	33	37	46	54	62	69	76	89
-32.5°	23	24	26	29	31	32	34	42	48	55	60
-33.75°	20	21	23	25	26	28	30	31	33	34	39
-35°	17	18	20	21	23	24	25	27	28	29	31
-36.25°	13	15	17	18	20	21	22	23	24	25	26
-37.5°	9	11	13	15	16	17	19	20	21	21	22
-38.75°	8	8	9	11	12	13	15	16	17	18	19
-40°	7	8	8	8	9	9	11	12	13	14	15
-41.25°	7	7	7	8	8	8	8	9	9	10	10
-42.5°	6	6	7	7	7	7	8	8	8	8	8
-43.75°	6	6	6	6	6	7	7	7	7	7	7
-45°	5	5	5	6	6	6	6	6	6	7	7
-46.25°	5	5	5	5	5	5	6	6	6	6	6
-47.5°	5	5	5	5	5	5	5	5	5	5	5
-48.75°	5	5	5	5	5	5	5	5	5	5	5
-50°	5	5	5	5	5	5	5	5	5	5	5
-51.25°	4	4	4	5	5	5	5	5	5	5	5
-52.5°	4	4	4	4	4	4	4	4	5	5	5
-53.75°	4	4	4	4	4	4	4	4	4	4	4
-55°	4	4	4	4	4	4	4	4	4	4	4
-56.25°	4	4	4	4	4	4	4	4	4	4	4
-57.5°	4	4	4	4	4	4	4	4	4	4	4
-58.75°	4	4	4	4	4	4	4	4	4	4	4
-60°	3	3	3	4	4	4	4	4	4	4	4
-61.25°	3	3	3	3	3	3	3	3	3	3	3
-62.5°	3	3	3	3	3	3	3	3	3	3	3
-63.75°	3	3	3	3	3	3	3	3	3	3	3
-65°	3	3	3	3	3	3	3	3	3	3	3
-66.25°	2	2	2	2	2	3	3	3	3	3	3
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	2	2	2	2	2	2	2	2	2	2	2
-70°	2	2	2	2	2	2	2	2	2	2	2
-71.25°	2	2	2	2	2	2	2	2	2	2	2
-72.5°	2	2	2	2	2	2	2	2	2	2	2
-73.75°	2	2	2	2	2	2	2	2	2	2	2
-75°	1	1	1	1	1	1	1	1	2	2	2
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	1	1	1	1	1	1	1	1	1	1	1
-82.5°	1	1	1	1	1	1	1	1	1	1	1
-83.75°	1	1	1	1	1	1	1	1	1	1	1
-85°	1	1	1	1	1	1	1	1	1	1	1
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	1	1	1	1	1	1	1	1	1	1	1
83.75°	1	1	1	1	1	1	1	1	1	1	1
82.5°	1	1	1	1	1	1	1	1	1	1	1
81.25°	1	1	1	1	1	1	1	1	1	1	1
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	2	2	2	2	2	2	2	2	2	2	2
73.75°	2	2	2	2	2	2	2	2	2	2	2
72.5°	2	2	2	2	2	2	2	2	2	2	2
71.25°	2	2	2	2	2	2	2	2	2	2	2
70°	2	2	2	2	2	2	2	2	2	2	2
68.75°	2	2	2	2	2	2	2	2	2	2	2
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	3	3	3	3	3	3	3	3	3	3	3
65°	3	3	3	3	3	3	3	3	3	3	3
63.75°	3	3	3	3	3	3	3	3	3	3	3
62.5°	3	3	3	3	3	3	3	3	3	3	3
61.25°	4	4	4	4	4	4	4	4	4	4	4
60°	4	4	4	4	4	4	4	4	4	4	4
58.75°	4	4	4	4	4	4	4	4	4	4	4
57.5°	4	4	4	4	4	4	4	4	4	4	4
56.25°	4	4	4	4	4	4	4	4	4	4	4
55°	4	4	4	4	4	4	4	4	4	4	4
53.75°	4	4	4	4	4	4	4	4	4	4	4
52.5°	5	5	5	5	5	5	5	5	5	5	5
51.25°	5	5	5	5	5	5	5	5	5	5	5
50°	5	5	5	5	5	5	5	5	5	5	5
48.75°	5	5	5	5	5	5	5	5	5	5	5
47.5°	5	6	6	6	6	6	6	6	6	6	6
46.25°	6	6	6	6	6	6	6	6	6	6	6
45°	7	7	7	7	7	7	7	7	7	7	7
43.75°	8	8	8	8	8	8	8	8	8	8	8
42.5°	8	8	9	9	9	9	9	9	9	9	9
41.25°	11	12	12	13	13	13	13	13	13	13	12
40°	15	16	16	17	17	17	17	17	17	17	16
38.75°	19	20	20	21	21	21	21	21	21	21	20
37.5°	23	23	24	24	24	25	25	25	24	24	24
36.25°	27	28	28	29	29	29	29	29	29	29	28
35°	31	32	33	33	34	34	34	34	34	33	33



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	43	47	51	53	55	56	56	56	55	53	51
32.5°	65	69	72	75	77	78	79	78	77	75	72
31.25°	107	122	135	145	152	156	157	156	152	145	135
30°	183	199	213	223	230	235	236	235	230	223	213
28.75°	266	288	305	320	330	337	339	337	330	320	305
27.5°	367	391	411	427	438	445	447	445	438	427	411
26.25°	471	496	516	531	542	549	551	549	542	531	516
25°	568	592	611	626	637	643	645	643	637	626	611
23.75°	656	676	694	707	715	719	721	719	715	707	694
22.5°	725	742	755	765	772	776	777	776	772	765	755
21.25°	778	793	806	817	825	829	831	829	825	817	806
20°	829	846	863	876	885	891	893	891	885	876	863
18.75°	885	909	929	945	958	967	970	967	958	945	929
17.5°	952	984	1011	1034	1052	1062	1066	1062	1052	1034	1011
16.25°	1036	1076	1110	1147	1173	1190	1195	1190	1173	1147	1110
15°	1139	1198	1257	1312	1352	1376	1384	1376	1352	1312	1257
13.75°	1284	1372	1459	1532	1586	1629	1644	1629	1586	1532	1459
12.5°	1472	1591	1723	1829	1930	1994	2015	1994	1930	1829	1723
11.25°	1711	1892	2086	2262	2421	2518	2551	2518	2421	2262	2086
10°	2023	2299	2590	2889	3135	3287	3338	3287	3135	2889	2590
8.75°	2428	2846	3293	3735	4075	4306	4388	4306	4075	3735	3293
7.5°	2944	3541	4150	4733	5180	5464	5561	5464	5180	4733	4150
6.25°	3541	4314	5091	5765	6292	6633	6751	6633	6292	5765	5091
5°	4150	5091	5971	6753	7366	7764	7904	7764	7366	6753	5971
3.75°	4733	5765	6753	7629	8298	8731	8862	8731	8298	7629	6753
2.5°	5180	6292	7366	8298	9001	9441	9578	9441	9001	8298	7366
1.25°	5464	6633	7764	8731	9441	9875	10021	9875	9441	8731	7764
0°	5561	6751	7904	8862	9578	10021	10220	10021	9578	8862	7904
-1.25°	5464	6633	7764	8731	9441	9875	10021	9875	9441	8731	7764
-2.5°	5180	6292	7366	8298	9001	9441	9578	9441	9001	8298	7366
-3.75°	4733	5765	6753	7629	8298	8731	8862	8731	8298	7629	6753
-5°	4150	5091	5971	6753	7366	7764	7904	7764	7366	6753	5971
-6.25°	3541	4314	5091	5765	6292	6633	6751	6633	6292	5765	5091
-7.5°	2944	3541	4150	4733	5180	5464	5561	5464	5180	4733	4150
-8.75°	2428	2846	3293	3735	4075	4306	4388	4306	4075	3735	3293
-10°	2023	2299	2590	2889	3135	3287	3338	3287	3135	2889	2590
-11.25°	1711	1892	2086	2262	2421	2518	2551	2518	2421	2262	2086
-12.5°	1472	1591	1723	1829	1930	1994	2015	1994	1930	1829	1723
-13.75°	1284	1372	1459	1532	1586	1629	1644	1629	1586	1532	1459
-15°	1139	1198	1257	1312	1352	1376	1384	1376	1352	1312	1257
-16.25°	1036	1076	1110	1147	1173	1190	1195	1190	1173	1147	1110
-17.5°	952	984	1011	1034	1052	1062	1066	1062	1052	1034	1011
-18.75°	885	909	929	945	958	967	970	967	958	945	929
-20°	829	846	863	876	885	891	893	891	885	876	863
-21.25°	778	793	806	817	825	829	831	829	825	817	806



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	725	742	755	765	772	776	777	776	772	765	755
-23.75°	656	676	694	707	715	719	721	719	715	707	694
-25°	568	592	611	626	637	643	645	643	637	626	611
-26.25°	471	496	516	531	542	549	551	549	542	531	516
-27.5°	367	391	411	427	438	445	447	445	438	427	411
-28.75°	266	288	305	320	330	337	339	337	330	320	305
-30°	183	199	213	223	230	235	236	235	230	223	213
-31.25°	107	122	135	145	152	156	157	156	152	145	135
-32.5°	65	69	72	75	77	78	79	78	77	75	72
-33.75°	43	47	51	53	55	56	56	56	55	53	51
-35°	31	32	33	33	34	34	34	34	34	33	33
-36.25°	27	28	28	29	29	29	29	29	29	29	28
-37.5°	23	23	24	24	24	25	25	25	24	24	24
-38.75°	19	20	20	21	21	21	21	21	21	21	20
-40°	15	16	16	17	17	17	17	17	17	17	16
-41.25°	11	12	12	13	13	13	13	13	13	13	12
-42.5°	8	8	9	9	9	9	9	9	9	9	9
-43.75°	8	8	8	8	8	8	8	8	8	8	8
-45°	7	7	7	7	7	7	7	7	7	7	7
-46.25°	6	6	6	6	6	6	6	6	6	6	6
-47.5°	5	6	6	6	6	6	6	6	6	6	6
-48.75°	5	5	5	5	5	5	5	5	5	5	5
-50°	5	5	5	5	5	5	5	5	5	5	5
-51.25°	5	5	5	5	5	5	5	5	5	5	5
-52.5°	5	5	5	5	5	5	5	5	5	5	5
-53.75°	4	4	4	4	4	4	4	4	4	4	4
-55°	4	4	4	4	4	4	4	4	4	4	4
-56.25°	4	4	4	4	4	4	4	4	4	4	4
-57.5°	4	4	4	4	4	4	4	4	4	4	4
-58.75°	4	4	4	4	4	4	4	4	4	4	4
-60°	4	4	4	4	4	4	4	4	4	4	4
-61.25°	4	4	4	4	4	4	4	4	4	4	4
-62.5°	3	3	3	3	3	3	3	3	3	3	3
-63.75°	3	3	3	3	3	3	3	3	3	3	3
-65°	3	3	3	3	3	3	3	3	3	3	3
-66.25°	3	3	3	3	3	3	3	3	3	3	3
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	2	2	2	2	2	2	2	2	2	2	2
-70°	2	2	2	2	2	2	2	2	2	2	2
-71.25°	2	2	2	2	2	2	2	2	2	2	2
-72.5°	2	2	2	2	2	2	2	2	2	2	2
-73.75°	2	2	2	2	2	2	2	2	2	2	2
-75°	2	2	2	2	2	2	2	2	2	2	2
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	1	1	1	1	1	1	1	1	1	1	1
-82.5°	1	1	1	1	1	1	1	1	1	1	1
-83.75°	1	1	1	1	1	1	1	1	1	1	1
-85°	1	1	1	1	1	1	1	1	1	1	1
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	1	1	1	1	1	1	1	1	1	1	1
83.75°	1	1	1	1	1	1	1	1	1	1	1
82.5°	1	1	1	1	1	1	1	1	1	1	1
81.25°	1	1	1	1	1	1	1	1	1	1	1
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	2	2	2	2	2	1	1	1	1	1	1
73.75°	2	2	2	2	2	2	2	2	2	2	2
72.5°	2	2	2	2	2	2	2	2	2	2	2
71.25°	2	2	2	2	2	2	2	2	2	2	2
70°	2	2	2	2	2	2	2	2	2	2	2
68.75°	2	2	2	2	2	2	2	2	2	2	2
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	3	3	3	3	3	3	3	3	2	2	2
65°	3	3	3	3	3	3	3	3	3	3	3
63.75°	3	3	3	3	3	3	3	3	3	3	3
62.5°	3	3	3	3	3	3	3	3	3	3	3
61.25°	4	4	3	3	3	3	3	3	3	3	3
60°	4	4	4	4	4	4	4	4	4	4	3
58.75°	4	4	4	4	4	4	4	4	4	4	4
57.5°	4	4	4	4	4	4	4	4	4	4	4
56.25°	4	4	4	4	4	4	4	4	4	4	4
55°	4	4	4	4	4	4	4	4	4	4	4
53.75°	4	4	4	4	4	4	4	4	4	4	4
52.5°	5	5	5	5	5	4	4	4	4	4	4
51.25°	5	5	5	5	5	5	5	5	5	5	4
50°	5	5	5	5	5	5	5	5	5	5	5
48.75°	5	5	5	5	5	5	5	5	5	5	5
47.5°	6	5	5	5	5	5	5	5	5	5	5
46.25°	6	6	6	6	6	6	6	5	5	5	5
45°	7	7	7	7	6	6	6	6	6	6	5
43.75°	8	8	7	7	7	7	7	7	6	6	6
42.5°	8	8	8	8	8	8	8	7	7	7	7
41.25°	12	11	10	10	9	9	8	8	8	8	7
40°	16	15	15	14	13	12	11	9	9	8	8
38.75°	20	19	19	18	17	16	15	13	12	11	9
37.5°	23	23	22	21	21	20	19	17	16	15	13
36.25°	28	27	26	25	24	23	22	21	20	18	17
35°	32	31	31	29	28	27	25	24	23	21	20



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	47	43	39	34	33	31	30	28	26	25	23
32.5°	69	65	60	55	48	42	34	32	31	29	26
31.25°	122	107	89	76	69	62	54	46	37	33	30
30°	199	183	165	143	119	93	74	66	56	46	36
28.75°	288	266	241	217	192	165	134	102	75	65	54
27.5°	391	367	338	307	273	236	204	171	134	96	72
26.25°	496	471	441	407	369	327	284	239	201	161	118
25°	592	568	539	506	468	424	376	325	274	224	181
23.75°	676	656	629	596	560	517	470	416	360	301	243
22.5°	742	725	705	676	644	602	556	505	447	384	320
21.25°	793	778	760	738	713	677	635	585	529	467	399
20°	846	829	808	787	763	735	702	657	604	544	478
18.75°	909	885	861	835	808	781	751	716	670	613	549
17.5°	984	952	922	889	857	825	793	761	723	674	613
16.25°	1076	1036	995	951	912	873	835	799	764	723	670
15°	1198	1139	1081	1027	975	926	881	838	799	761	716
13.75°	1372	1284	1195	1114	1050	988	931	881	835	793	751
12.5°	1591	1472	1349	1231	1136	1057	988	926	873	825	781
11.25°	1892	1711	1536	1383	1247	1136	1050	975	912	857	808
10°	2299	2023	1772	1558	1383	1231	1114	1027	951	889	835
8.75°	2846	2428	2068	1772	1536	1349	1195	1081	995	922	861
7.5°	3541	2944	2428	2023	1711	1472	1284	1139	1036	952	885
6.25°	4314	3541	2846	2299	1892	1591	1372	1198	1076	984	909
5°	5091	4150	3293	2590	2086	1723	1459	1257	1110	1011	929
3.75°	5765	4733	3735	2889	2262	1829	1532	1312	1147	1034	945
2.5°	6292	5180	4075	3135	2421	1930	1586	1352	1173	1052	958
1.25°	6633	5464	4306	3287	2518	1994	1629	1376	1190	1062	967
0°	6751	5561	4388	3338	2551	2015	1644	1384	1195	1066	970
-1.25°	6633	5464	4306	3287	2518	1994	1629	1376	1190	1062	967
-2.5°	6292	5180	4075	3135	2421	1930	1586	1352	1173	1052	958
-3.75°	5765	4733	3735	2889	2262	1829	1532	1312	1147	1034	945
-5°	5091	4150	3293	2590	2086	1723	1459	1257	1110	1011	929
-6.25°	4314	3541	2846	2299	1892	1591	1372	1198	1076	984	909
-7.5°	3541	2944	2428	2023	1711	1472	1284	1139	1036	952	885
-8.75°	2846	2428	2068	1772	1536	1349	1195	1081	995	922	861
-10°	2299	2023	1772	1558	1383	1231	1114	1027	951	889	835
-11.25°	1892	1711	1536	1383	1247	1136	1050	975	912	857	808
-12.5°	1591	1472	1349	1231	1136	1057	988	926	873	825	781
-13.75°	1372	1284	1195	1114	1050	988	931	881	835	793	751
-15°	1198	1139	1081	1027	975	926	881	838	799	761	716
-16.25°	1076	1036	995	951	912	873	835	799	764	723	670
-17.5°	984	952	922	889	857	825	793	761	723	674	613
-18.75°	909	885	861	835	808	781	751	716	670	613	549
-20°	846	829	808	787	763	735	702	657	604	544	478
-21.25°	793	778	760	738	713	677	635	585	529	467	399



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	742	725	705	676	644	602	556	505	447	384	320
-23.75°	676	656	629	596	560	517	470	416	360	301	243
-25°	592	568	539	506	468	424	376	325	274	224	181
-26.25°	496	471	441	407	369	327	284	239	201	161	118
-27.5°	391	367	338	307	273	236	204	171	134	96	72
-28.75°	288	266	241	217	192	165	134	102	75	65	54
-30°	199	183	165	143	119	93	74	66	56	46	36
-31.25°	122	107	89	76	69	62	54	46	37	33	30
-32.5°	69	65	60	55	48	42	34	32	31	29	26
-33.75°	47	43	39	34	33	31	30	28	26	25	23
-35°	32	31	31	29	28	27	25	24	23	21	20
-36.25°	28	27	26	25	24	23	22	21	20	18	17
-37.5°	23	23	22	21	21	20	19	17	16	15	13
-38.75°	20	19	19	18	17	16	15	13	12	11	9
-40°	16	15	15	14	13	12	11	9	9	8	8
-41.25°	12	11	10	10	9	9	8	8	8	8	7
-42.5°	8	8	8	8	8	8	8	7	7	7	7
-43.75°	8	8	7	7	7	7	7	7	6	6	6
-45°	7	7	7	7	6	6	6	6	6	6	5
-46.25°	6	6	6	6	6	6	6	5	5	5	5
-47.5°	6	5	5	5	5	5	5	5	5	5	5
-48.75°	5	5	5	5	5	5	5	5	5	5	5
-50°	5	5	5	5	5	5	5	5	5	5	5
-51.25°	5	5	5	5	5	5	5	5	5	5	4
-52.5°	5	5	5	5	5	4	4	4	4	4	4
-53.75°	4	4	4	4	4	4	4	4	4	4	4
-55°	4	4	4	4	4	4	4	4	4	4	4
-56.25°	4	4	4	4	4	4	4	4	4	4	4
-57.5°	4	4	4	4	4	4	4	4	4	4	4
-58.75°	4	4	4	4	4	4	4	4	4	4	4
-60°	4	4	4	4	4	4	4	4	4	4	3
-61.25°	4	4	3	3	3	3	3	3	3	3	3
-62.5°	3	3	3	3	3	3	3	3	3	3	3
-63.75°	3	3	3	3	3	3	3	3	3	3	3
-65°	3	3	3	3	3	3	3	3	3	3	3
-66.25°	3	3	3	3	3	3	3	3	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	2	2	2	2	2	2	2	2	2	2	2
-70°	2	2	2	2	2	2	2	2	2	2	2
-71.25°	2	2	2	2	2	2	2	2	2	2	2
-72.5°	2	2	2	2	2	2	2	2	2	2	2
-73.75°	2	2	2	2	2	2	2	2	2	2	2
-75°	2	2	2	2	2	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	1	1	1	1	1	1	1	1	1	1	1
-82.5°	1	1	1	1	1	1	1	1	1	1	1
-83.75°	1	1	1	1	1	1	1	1	1	1	1
-85°	1	1	1	1	1	1	1	1	1	1	1
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	1	1	1	1	1	1	1	1	1	1	1
83.75°	1	1	1	1	1	1	1	1	1	1	1
82.5°	1	1	1	1	1	1	1	1	1	1	1
81.25°	1	1	1	1	1	1	1	1	1	1	1
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	2	2	2	2	2	1	1	1	1	1	1
72.5°	2	2	2	2	2	2	2	2	2	2	2
71.25°	2	2	2	2	2	2	2	2	2	2	2
70°	2	2	2	2	2	2	2	2	2	2	2
68.75°	2	2	2	2	2	2	2	2	2	2	2
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	3	3	3	2	2	2	2	2	2	2	2
63.75°	3	3	3	3	3	3	3	3	2	2	2
62.5°	3	3	3	3	3	3	3	3	3	3	3
61.25°	3	3	3	3	3	3	3	3	3	3	3
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	4	4	4	3	3	3	3	3	3	3	3
57.5°	4	4	4	4	4	4	4	3	3	3	3
56.25°	4	4	4	4	4	4	4	4	4	3	3
55°	4	4	4	4	4	4	4	4	4	4	4
53.75°	4	4	4	4	4	4	4	4	4	4	4
52.5°	4	4	4	4	4	4	4	4	4	4	4
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	5	5	4	4	4	4	4	4	4	4	4
48.75°	5	5	5	5	5	4	4	4	4	4	4
47.5°	5	5	5	5	5	5	5	4	4	4	4
46.25°	5	5	5	5	5	5	5	5	5	4	4
45°	5	5	5	5	5	5	5	5	5	5	5
43.75°	6	6	5	5	5	5	5	5	5	5	5
42.5°	6	6	6	6	5	5	5	5	5	5	5
41.25°	7	7	6	6	6	6	5	5	5	5	5
40°	8	7	7	7	6	6	6	6	5	5	5
38.75°	8	8	8	7	7	7	6	6	6	5	5
37.5°	11	9	8	8	8	7	7	7	6	6	5
36.25°	15	13	11	9	8	8	8	7	7	6	6
35°	18	17	15	12	10	9	8	8	7	7	6

REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	21	20	18	16	14	11	9	8	8	7	7
32.5°	24	23	21	19	17	14	12	9	8	8	7
31.25°	28	26	24	22	20	18	15	12	10	8	8
30°	32	30	27	24	22	20	18	15	12	10	8
28.75°	42	33	31	28	25	23	20	18	15	12	9
27.5°	60	48	35	31	28	25	23	20	18	15	12
26.25°	77	64	51	37	32	29	25	23	20	18	14
25°	135	87	67	53	38	32	28	25	22	20	17
23.75°	194	145	94	68	53	37	31	28	24	22	19
22.5°	256	201	148	94	67	51	35	31	27	24	21
21.25°	329	261	201	145	87	64	48	33	30	26	23
20°	404	329	256	194	135	77	60	42	32	28	24
18.75°	478	399	320	243	181	118	72	54	36	30	26
17.5°	544	467	384	301	224	161	96	65	46	33	29
16.25°	604	529	447	360	274	201	134	75	56	37	31
15°	657	585	505	416	325	239	171	102	66	46	32
13.75°	702	635	556	470	376	284	204	134	74	54	34
12.5°	735	677	602	517	424	327	236	165	93	62	42
11.25°	763	713	644	560	468	369	273	192	119	69	48
10°	787	738	676	596	506	407	307	217	143	76	55
8.75°	808	760	705	629	539	441	338	241	165	89	60
7.5°	829	778	725	656	568	471	367	266	183	107	65
6.25°	846	793	742	676	592	496	391	288	199	122	69
5°	863	806	755	694	611	516	411	305	213	135	72
3.75°	876	817	765	707	626	531	427	320	223	145	75
2.5°	885	825	772	715	637	542	438	330	230	152	77
1.25°	891	829	776	719	643	549	445	337	235	156	78
0°	893	831	777	721	645	551	447	339	236	157	79
-1.25°	891	829	776	719	643	549	445	337	235	156	78
-2.5°	885	825	772	715	637	542	438	330	230	152	77
-3.75°	876	817	765	707	626	531	427	320	223	145	75
-5°	863	806	755	694	611	516	411	305	213	135	72
-6.25°	846	793	742	676	592	496	391	288	199	122	69
-7.5°	829	778	725	656	568	471	367	266	183	107	65
-8.75°	808	760	705	629	539	441	338	241	165	89	60
-10°	787	738	676	596	506	407	307	217	143	76	55
-11.25°	763	713	644	560	468	369	273	192	119	69	48
-12.5°	735	677	602	517	424	327	236	165	93	62	42
-13.75°	702	635	556	470	376	284	204	134	74	54	34
-15°	657	585	505	416	325	239	171	102	66	46	32
-16.25°	604	529	447	360	274	201	134	75	56	37	31
-17.5°	544	467	384	301	224	161	96	65	46	33	29
-18.75°	478	399	320	243	181	118	72	54	36	30	26
-20°	404	329	256	194	135	77	60	42	32	28	24
-21.25°	329	261	201	145	87	64	48	33	30	26	23



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	256	201	148	94	67	51	35	31	27	24	21
-23.75°	194	145	94	68	53	37	31	28	24	22	19
-25°	135	87	67	53	38	32	28	25	22	20	17
-26.25°	77	64	51	37	32	29	25	23	20	18	14
-27.5°	60	48	35	31	28	25	23	20	18	15	12
-28.75°	42	33	31	28	25	23	20	18	15	12	9
-30°	32	30	27	24	22	20	18	15	12	10	8
-31.25°	28	26	24	22	20	18	15	12	10	8	8
-32.5°	24	23	21	19	17	14	12	9	8	8	7
-33.75°	21	20	18	16	14	11	9	8	8	7	7
-35°	18	17	15	12	10	9	8	8	7	7	6
-36.25°	15	13	11	9	8	8	8	7	7	6	6
-37.5°	11	9	8	8	8	7	7	7	6	6	5
-38.75°	8	8	8	7	7	7	6	6	6	5	5
-40°	8	7	7	7	6	6	6	6	5	5	5
-41.25°	7	7	6	6	6	6	5	5	5	5	5
-42.5°	6	6	6	6	5	5	5	5	5	5	5
-43.75°	6	6	5	5	5	5	5	5	5	5	5
-45°	5	5	5	5	5	5	5	5	5	5	5
-46.25°	5	5	5	5	5	5	5	5	5	4	4
-47.5°	5	5	5	5	5	5	5	4	4	4	4
-48.75°	5	5	5	5	5	4	4	4	4	4	4
-50°	5	5	4	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	4	4	4	4	4	4	4	4	4	4	4
-55°	4	4	4	4	4	4	4	4	4	4	4
-56.25°	4	4	4	4	4	4	4	4	4	3	3
-57.5°	4	4	4	4	4	4	4	3	3	3	3
-58.75°	4	4	4	3	3	3	3	3	3	3	3
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	3	3	3	3	3	3	3	3	3	3	3
-62.5°	3	3	3	3	3	3	3	3	3	3	3
-63.75°	3	3	3	3	3	3	3	3	2	2	2
-65°	3	3	3	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	2	2	2	2	2	2	2	2	2	2	2
-70°	2	2	2	2	2	2	2	2	2	2	2
-71.25°	2	2	2	2	2	2	2	2	2	2	2
-72.5°	2	2	2	2	2	2	2	2	2	2	2
-73.75°	2	2	2	2	2	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	1	1	1	1	1	1	1	1	1	1	1
-82.5°	1	1	1	1	1	1	1	1	1	1	1
-83.75°	1	1	1	1	1	1	1	1	1	1	1
-85°	1	1	1	1	1	1	1	1	1	1	1
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	1	1	0	0	0	0	0	0	0	0	0
83.75°	1	1	1	1	1	1	1	1	1	1	1
82.5°	1	1	1	1	1	1	1	1	1	1	1
81.25°	1	1	1	1	1	1	1	1	1	1	1
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	2	2	2	2	1	1	1	1	1	1	1
70°	2	2	2	2	2	2	2	1	1	1	1
68.75°	2	2	2	2	2	2	2	2	2	2	1
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	3	3	3	2	2	2	2	2	2	2	2
60°	3	3	3	3	3	2	2	2	2	2	2
58.75°	3	3	3	3	3	3	3	2	2	2	2
57.5°	3	3	3	3	3	3	3	3	3	2	2
56.25°	3	3	3	3	3	3	3	3	3	3	2
55°	4	3	3	3	3	3	3	3	3	3	3
53.75°	4	4	4	3	3	3	3	3	3	3	3
52.5°	4	4	4	4	3	3	3	3	3	3	3
51.25°	4	4	4	4	4	4	3	3	3	3	3
50°	4	4	4	4	4	4	4	3	3	3	3
48.75°	4	4	4	4	4	4	4	4	4	3	3
47.5°	4	4	4	4	4	4	4	4	4	4	3
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	5	4	4	4	4	4	4	4	4	4	4
42.5°	5	5	4	4	4	4	4	4	4	4	4
41.25°	5	5	5	5	4	4	4	4	4	4	4
40°	5	5	5	5	5	4	4	4	4	4	4
38.75°	5	5	5	5	5	5	4	4	4	4	4
37.5°	5	5	5	5	5	5	5	4	4	4	4
36.25°	5	5	5	5	5	5	5	4	4	4	4
35°	6	5	5	5	5	5	5	5	4	4	4



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	6	6	5	5	5	5	5	5	5	4	4
32.5°	7	6	6	5	5	5	5	5	5	5	4
31.25°	7	7	6	6	5	5	5	5	5	5	4
30°	8	7	7	6	6	5	5	5	5	5	5
28.75°	8	8	7	7	6	6	5	5	5	5	5
27.5°	9	8	8	7	6	6	5	5	5	5	5
26.25°	11	9	8	7	7	6	6	5	5	5	5
25°	14	10	8	8	7	6	6	5	5	5	5
23.75°	16	12	9	8	7	7	6	6	5	5	5
22.5°	18	15	11	8	8	7	6	6	5	5	5
21.25°	20	17	13	9	8	7	7	6	6	5	5
20°	21	18	15	11	8	8	7	6	6	5	5
18.75°	23	20	17	13	9	8	7	7	6	5	5
17.5°	25	21	18	15	11	8	8	7	6	6	5
16.25°	26	23	20	16	12	9	8	7	6	6	5
15°	28	24	21	17	13	9	8	7	7	6	5
13.75°	30	25	22	19	15	11	8	8	7	6	6
12.5°	31	27	23	20	16	12	9	8	7	6	6
11.25°	33	28	24	21	17	13	9	8	7	6	6
10°	34	29	25	21	18	14	10	8	7	7	6
8.75°	39	31	26	22	19	15	10	8	7	7	6
7.5°	43	31	27	23	19	15	11	8	8	7	6
6.25°	47	32	28	23	20	16	12	8	8	7	6
5°	51	33	28	24	20	16	12	9	8	7	6
3.75°	53	33	29	24	21	17	13	9	8	7	6
2.5°	55	34	29	24	21	17	13	9	8	7	6
1.25°	56	34	29	25	21	17	13	9	8	7	6
0°	56	34	29	25	21	17	13	9	8	7	6
-1.25°	56	34	29	25	21	17	13	9	8	7	6
-2.5°	55	34	29	24	21	17	13	9	8	7	6
-3.75°	53	33	29	24	21	17	13	9	8	7	6
-5°	51	33	28	24	20	16	12	9	8	7	6
-6.25°	47	32	28	23	20	16	12	8	8	7	6
-7.5°	43	31	27	23	19	15	11	8	8	7	6
-8.75°	39	31	26	22	19	15	10	8	7	7	6
-10°	34	29	25	21	18	14	10	8	7	7	6
-11.25°	33	28	24	21	17	13	9	8	7	6	6
-12.5°	31	27	23	20	16	12	9	8	7	6	6
-13.75°	30	25	22	19	15	11	8	8	7	6	6
-15°	28	24	21	17	13	9	8	7	7	6	5
-16.25°	26	23	20	16	12	9	8	7	6	6	5
-17.5°	25	21	18	15	11	8	8	7	6	6	5
-18.75°	23	20	17	13	9	8	7	7	6	5	5
-20°	21	18	15	11	8	8	7	6	6	5	5
-21.25°	20	17	13	9	8	7	7	6	6	5	5



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	18	15	11	8	8	7	6	6	5	5	5
-23.75°	16	12	9	8	7	7	6	6	5	5	5
-25°	14	10	8	8	7	6	6	5	5	5	5
-26.25°	11	9	8	7	7	6	6	5	5	5	5
-27.5°	9	8	8	7	6	6	5	5	5	5	5
-28.75°	8	8	7	7	6	6	5	5	5	5	5
-30°	8	7	7	6	6	5	5	5	5	5	5
-31.25°	7	7	6	6	5	5	5	5	5	5	4
-32.5°	7	6	6	5	5	5	5	5	5	5	4
-33.75°	6	6	5	5	5	5	5	5	5	4	4
-35°	6	5	5	5	5	5	5	5	4	4	4
-36.25°	5	5	5	5	5	5	5	4	4	4	4
-37.5°	5	5	5	5	5	5	5	4	4	4	4
-38.75°	5	5	5	5	5	5	4	4	4	4	4
-40°	5	5	5	5	5	4	4	4	4	4	4
-41.25°	5	5	5	5	4	4	4	4	4	4	4
-42.5°	5	5	4	4	4	4	4	4	4	4	4
-43.75°	5	4	4	4	4	4	4	4	4	4	4
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	3
-48.75°	4	4	4	4	4	4	4	4	4	3	3
-50°	4	4	4	4	4	4	4	3	3	3	3
-51.25°	4	4	4	4	4	4	3	3	3	3	3
-52.5°	4	4	4	4	3	3	3	3	3	3	3
-53.75°	4	4	4	3	3	3	3	3	3	3	3
-55°	4	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	2
-57.5°	3	3	3	3	3	3	3	3	3	2	2
-58.75°	3	3	3	3	3	3	3	2	2	2	2
-60°	3	3	3	3	3	2	2	2	2	2	2
-61.25°	3	3	3	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	2	2	2	2	2	2	2	2	2	2	1
-70°	2	2	2	2	2	2	2	1	1	1	1
-71.25°	2	2	2	2	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	1	1	1	1	1	1	1	1	1	1	1
-82.5°	1	1	1	1	1	1	1	1	1	1	1
-83.75°	1	1	1	1	1	1	1	1	1	1	1
-85°	1	1	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	1	1	0	0	0	0	0	0	0	0	0
82.5°	1	1	1	1	1	1	1	1	0	0	0
81.25°	1	1	1	1	1	1	1	1	1	1	1
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	2	1	1	1	1	1	1	1	1	1	1
66.25°	2	2	2	1	1	1	1	1	1	1	1
65°	2	2	2	2	2	1	1	1	1	1	1
63.75°	2	2	2	2	2	2	2	1	1	1	1
62.5°	2	2	2	2	2	2	2	2	1	1	1
61.25°	2	2	2	2	2	2	2	2	2	1	1
60°	2	2	2	2	2	2	2	2	2	2	1
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	2
53.75°	3	3	2	2	2	2	2	2	2	2	2
52.5°	3	3	3	2	2	2	2	2	2	2	2
51.25°	3	3	3	3	2	2	2	2	2	2	2
50°	3	3	3	3	3	2	2	2	2	2	2
48.75°	3	3	3	3	3	3	2	2	2	2	2
47.5°	3	3	3	3	3	3	2	2	2	2	2
46.25°	3	3	3	3	3	3	3	2	2	2	2
45°	4	3	3	3	3	3	3	3	2	2	2
43.75°	4	4	3	3	3	3	3	3	3	2	2
42.5°	4	4	3	3	3	3	3	3	3	2	2
41.25°	4	4	4	3	3	3	3	3	3	3	2
40°	4	4	4	4	3	3	3	3	3	3	2
38.75°	4	4	4	4	3	3	3	3	3	3	3
37.5°	4	4	4	4	4	3	3	3	3	3	3
36.25°	4	4	4	4	4	4	3	3	3	3	3
35°	4	4	4	4	4	4	3	3	3	3	3



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	4	4	4	4	4	4	4	3	3	3	3
32.5°	4	4	4	4	4	4	4	3	3	3	3
31.25°	4	4	4	4	4	4	4	3	3	3	3
30°	4	4	4	4	4	4	4	4	3	3	3
28.75°	4	4	4	4	4	4	4	4	3	3	3
27.5°	5	4	4	4	4	4	4	4	4	3	3
26.25°	5	4	4	4	4	4	4	4	4	3	3
25°	5	5	4	4	4	4	4	4	4	3	3
23.75°	5	5	4	4	4	4	4	4	4	3	3
22.5°	5	5	4	4	4	4	4	4	4	4	3
21.25°	5	5	5	4	4	4	4	4	4	4	3
20°	5	5	5	4	4	4	4	4	4	4	3
18.75°	5	5	5	4	4	4	4	4	4	4	3
17.5°	5	5	5	5	4	4	4	4	4	4	4
16.25°	5	5	5	5	4	4	4	4	4	4	4
15°	5	5	5	5	4	4	4	4	4	4	4
13.75°	5	5	5	5	4	4	4	4	4	4	4
12.5°	5	5	5	5	4	4	4	4	4	4	4
11.25°	5	5	5	5	5	4	4	4	4	4	4
10°	5	5	5	5	5	4	4	4	4	4	4
8.75°	5	5	5	5	5	4	4	4	4	4	4
7.5°	5	5	5	5	5	4	4	4	4	4	4
6.25°	6	5	5	5	5	4	4	4	4	4	4
5°	6	5	5	5	5	4	4	4	4	4	4
3.75°	6	5	5	5	5	4	4	4	4	4	4
2.5°	6	5	5	5	5	4	4	4	4	4	4
1.25°	6	5	5	5	5	4	4	4	4	4	4
0°	6	5	5	5	5	4	4	4	4	4	4
-1.25°	6	5	5	5	5	4	4	4	4	4	4
-2.5°	6	5	5	5	5	4	4	4	4	4	4
-3.75°	6	5	5	5	5	4	4	4	4	4	4
-5°	6	5	5	5	5	4	4	4	4	4	4
-6.25°	6	5	5	5	5	4	4	4	4	4	4
-7.5°	5	5	5	5	5	4	4	4	4	4	4
-8.75°	5	5	5	5	5	4	4	4	4	4	4
-10°	5	5	5	5	5	4	4	4	4	4	4
-11.25°	5	5	5	5	5	4	4	4	4	4	4
-12.5°	5	5	5	5	4	4	4	4	4	4	4
-13.75°	5	5	5	5	4	4	4	4	4	4	4
-15°	5	5	5	5	4	4	4	4	4	4	4
-16.25°	5	5	5	5	4	4	4	4	4	4	4
-17.5°	5	5	5	5	4	4	4	4	4	4	4
-18.75°	5	5	5	4	4	4	4	4	4	4	3
-20°	5	5	5	4	4	4	4	4	4	4	3
-21.25°	5	5	5	4	4	4	4	4	4	4	3



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	5	5	4	4	4	4	4	4	4	4	3
-23.75°	5	5	4	4	4	4	4	4	4	3	3
-25°	5	5	4	4	4	4	4	4	4	3	3
-26.25°	5	4	4	4	4	4	4	4	4	3	3
-27.5°	5	4	4	4	4	4	4	4	4	3	3
-28.75°	4	4	4	4	4	4	4	4	3	3	3
-30°	4	4	4	4	4	4	4	4	3	3	3
-31.25°	4	4	4	4	4	4	4	3	3	3	3
-32.5°	4	4	4	4	4	4	4	3	3	3	3
-33.75°	4	4	4	4	4	4	4	3	3	3	3
-35°	4	4	4	4	4	4	3	3	3	3	3
-36.25°	4	4	4	4	4	4	3	3	3	3	3
-37.5°	4	4	4	4	4	3	3	3	3	3	3
-38.75°	4	4	4	4	3	3	3	3	3	3	3
-40°	4	4	4	4	3	3	3	3	3	3	2
-41.25°	4	4	4	3	3	3	3	3	3	3	2
-42.5°	4	4	3	3	3	3	3	3	3	2	2
-43.75°	4	4	3	3	3	3	3	3	3	2	2
-45°	4	3	3	3	3	3	3	3	2	2	2
-46.25°	3	3	3	3	3	3	3	2	2	2	2
-47.5°	3	3	3	3	3	3	2	2	2	2	2
-48.75°	3	3	3	3	3	3	2	2	2	2	2
-50°	3	3	3	3	3	2	2	2	2	2	2
-51.25°	3	3	3	3	2	2	2	2	2	2	2
-52.5°	3	3	3	2	2	2	2	2	2	2	2
-53.75°	3	3	2	2	2	2	2	2	2	2	2
-55°	2	2	2	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	1
-61.25°	2	2	2	2	2	2	2	2	2	1	1
-62.5°	2	2	2	2	2	2	2	2	1	1	1
-63.75°	2	2	2	2	2	2	2	1	1	1	1
-65°	2	2	2	2	2	1	1	1	1	1	1
-66.25°	2	2	2	1	1	1	1	1	1	1	1
-67.5°	2	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	1	1	1	1	1	1	1	1	1	1	1
-82.5°	1	1	1	1	1	1	1	1	0	0	0
-83.75°	1	1	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	1	0	0	0	0	0	0	0	0	0	0
80°	1	1	1	1	0	0	0	0	0	0	0
78.75°	1	1	1	1	1	1	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	0	0	0
76.25°	1	1	1	1	1	1	1	1	1	1	0
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	2	1	1	1	1	1	1	1	1	1	1
56.25°	2	2	1	1	1	1	1	1	1	1	1
55°	2	2	2	1	1	1	1	1	1	1	1
53.75°	2	2	2	1	1	1	1	1	1	1	1
52.5°	2	2	2	2	1	1	1	1	1	1	1
51.25°	2	2	2	2	1	1	1	1	1	1	1
50°	2	2	2	2	2	1	1	1	1	1	1
48.75°	2	2	2	2	2	1	1	1	1	1	1
47.5°	2	2	2	2	2	2	1	1	1	1	1
46.25°	2	2	2	2	2	2	1	1	1	1	1
45°	2	2	2	2	2	2	2	1	1	1	1
43.75°	2	2	2	2	2	2	2	1	1	1	1
42.5°	2	2	2	2	2	2	2	1	1	1	1
41.25°	2	2	2	2	2	2	2	2	1	1	1
40°	2	2	2	2	2	2	2	2	1	1	1
38.75°	2	2	2	2	2	2	2	2	1	1	1
37.5°	2	2	2	2	2	2	2	2	2	1	1
36.25°	3	2	2	2	2	2	2	2	2	1	1
35°	3	2	2	2	2	2	2	2	2	1	1



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	3	2	2	2	2	2	2	2	2	1	1
32.5°	3	3	2	2	2	2	2	2	2	2	1
31.25°	3	3	2	2	2	2	2	2	2	2	1
30°	3	3	2	2	2	2	2	2	2	2	1
28.75°	3	3	3	2	2	2	2	2	2	2	1
27.5°	3	3	3	2	2	2	2	2	2	2	1
26.25°	3	3	3	2	2	2	2	2	2	2	1
25°	3	3	3	2	2	2	2	2	2	2	2
23.75°	3	3	3	2	2	2	2	2	2	2	2
22.5°	3	3	3	3	2	2	2	2	2	2	2
21.25°	3	3	3	3	2	2	2	2	2	2	2
20°	3	3	3	3	2	2	2	2	2	2	2
18.75°	3	3	3	3	2	2	2	2	2	2	2
17.5°	3	3	3	3	2	2	2	2	2	2	2
16.25°	3	3	3	3	2	2	2	2	2	2	2
15°	3	3	3	3	3	2	2	2	2	2	2
13.75°	3	3	3	3	3	2	2	2	2	2	2
12.5°	3	3	3	3	3	2	2	2	2	2	2
11.25°	3	3	3	3	3	2	2	2	2	2	2
10°	3	3	3	3	3	2	2	2	2	2	2
8.75°	3	3	3	3	3	2	2	2	2	2	2
7.5°	4	3	3	3	3	2	2	2	2	2	2
6.25°	4	3	3	3	3	2	2	2	2	2	2
5°	4	3	3	3	3	2	2	2	2	2	2
3.75°	4	3	3	3	3	2	2	2	2	2	2
2.5°	4	3	3	3	3	2	2	2	2	2	2
1.25°	4	3	3	3	3	2	2	2	2	2	2
0°	4	3	3	3	3	2	2	2	2	2	2
-1.25°	4	3	3	3	3	2	2	2	2	2	2
-2.5°	4	3	3	3	3	2	2	2	2	2	2
-3.75°	4	3	3	3	3	2	2	2	2	2	2
-5°	4	3	3	3	3	2	2	2	2	2	2
-6.25°	4	3	3	3	3	2	2	2	2	2	2
-7.5°	4	3	3	3	3	2	2	2	2	2	2
-8.75°	3	3	3	3	3	2	2	2	2	2	2
-10°	3	3	3	3	3	2	2	2	2	2	2
-11.25°	3	3	3	3	3	2	2	2	2	2	2
-12.5°	3	3	3	3	3	2	2	2	2	2	2
-13.75°	3	3	3	3	3	2	2	2	2	2	2
-15°	3	3	3	3	3	2	2	2	2	2	2
-16.25°	3	3	3	3	2	2	2	2	2	2	2
-17.5°	3	3	3	3	2	2	2	2	2	2	2
-18.75°	3	3	3	3	2	2	2	2	2	2	2
-20°	3	3	3	3	2	2	2	2	2	2	2
-21.25°	3	3	3	3	2	2	2	2	2	2	2



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	3	3	3	3	2	2	2	2	2	2	2
-23.75°	3	3	3	2	2	2	2	2	2	2	2
-25°	3	3	3	2	2	2	2	2	2	2	2
-26.25°	3	3	3	2	2	2	2	2	2	2	1
-27.5°	3	3	3	2	2	2	2	2	2	2	1
-28.75°	3	3	3	2	2	2	2	2	2	2	1
-30°	3	3	2	2	2	2	2	2	2	2	1
-31.25°	3	3	2	2	2	2	2	2	2	2	1
-32.5°	3	3	2	2	2	2	2	2	2	2	1
-33.75°	3	2	2	2	2	2	2	2	2	1	1
-35°	3	2	2	2	2	2	2	2	2	1	1
-36.25°	3	2	2	2	2	2	2	2	2	1	1
-37.5°	2	2	2	2	2	2	2	2	2	1	1
-38.75°	2	2	2	2	2	2	2	2	1	1	1
-40°	2	2	2	2	2	2	2	2	1	1	1
-41.25°	2	2	2	2	2	2	2	2	1	1	1
-42.5°	2	2	2	2	2	2	2	1	1	1	1
-43.75°	2	2	2	2	2	2	2	1	1	1	1
-45°	2	2	2	2	2	2	2	1	1	1	1
-46.25°	2	2	2	2	2	2	1	1	1	1	1
-47.5°	2	2	2	2	2	2	1	1	1	1	1
-48.75°	2	2	2	2	2	1	1	1	1	1	1
-50°	2	2	2	2	2	1	1	1	1	1	1
-51.25°	2	2	2	2	1	1	1	1	1	1	1
-52.5°	2	2	2	2	1	1	1	1	1	1	1
-53.75°	2	2	2	1	1	1	1	1	1	1	1
-55°	2	2	2	1	1	1	1	1	1	1	1
-56.25°	2	2	1	1	1	1	1	1	1	1	1
-57.5°	2	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	0
-77.5°	1	1	1	1	1	1	1	1	0	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	1	1	1	1	1	1	0	0	0	0	0
-80°	1	1	1	1	0	0	0	0	0	0	0
-81.25°	1	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	1	0	0	0	0	0	0	0	0	0	0
72.5°	1	1	0	0	0	0	0	0	0	0	0
71.25°	1	1	0	0	0	0	0	0	0	0	0
70°	1	1	1	0	0	0	0	0	0	0	0
68.75°	1	1	1	0	0	0	0	0	0	0	0
67.5°	1	1	1	1	0	0	0	0	0	0	0
66.25°	1	1	1	1	0	0	0	0	0	0	0
65°	1	1	1	1	1	0	0	0	0	0	0
63.75°	1	1	1	1	1	0	0	0	0	0	0
62.5°	1	1	1	1	1	0	0	0	0	0	0
61.25°	1	1	1	1	1	1	0	0	0	0	0
60°	1	1	1	1	1	1	0	0	0	0	0
58.75°	1	1	1	1	1	1	0	0	0	0	0
57.5°	1	1	1	1	1	1	0	0	0	0	0
56.25°	1	1	1	1	1	1	1	0	0	0	0
55°	1	1	1	1	1	1	1	0	0	0	0
53.75°	1	1	1	1	1	1	1	0	0	0	0
52.5°	1	1	1	1	1	1	1	0	0	0	0
51.25°	1	1	1	1	1	1	1	0	0	0	0
50°	1	1	1	1	1	1	1	0	0	0	0
48.75°	1	1	1	1	1	1	1	1	0	0	0
47.5°	1	1	1	1	1	1	1	1	0	0	0
46.25°	1	1	1	1	1	1	1	1	0	0	0
45°	1	1	1	1	1	1	1	1	0	0	0
43.75°	1	1	1	1	1	1	1	1	0	0	0
42.5°	1	1	1	1	1	1	1	1	0	0	0
41.25°	1	1	1	1	1	1	1	1	0	0	0
40°	1	1	1	1	1	1	1	1	0	0	0
38.75°	1	1	1	1	1	1	1	1	0	0	0
37.5°	1	1	1	1	1	1	1	1	0	0	0
36.25°	1	1	1	1	1	1	1	1	0	0	0
35°	1	1	1	1	1	1	1	1	1	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	1	1	1	1	1	1	1	1	1	0	0
32.5°	1	1	1	1	1	1	1	1	1	0	0
31.25°	1	1	1	1	1	1	1	1	1	0	0
30°	1	1	1	1	1	1	1	1	1	0	0
28.75°	1	1	1	1	1	1	1	1	1	0	0
27.5°	1	1	1	1	1	1	1	1	1	0	0
26.25°	1	1	1	1	1	1	1	1	1	0	0
25°	1	1	1	1	1	1	1	1	1	0	0
23.75°	1	1	1	1	1	1	1	1	1	0	0
22.5°	1	1	1	1	1	1	1	1	1	0	0
21.25°	1	1	1	1	1	1	1	1	1	0	0
20°	1	1	1	1	1	1	1	1	1	0	0
18.75°	1	1	1	1	1	1	1	1	1	0	0
17.5°	1	1	1	1	1	1	1	1	1	0	0
16.25°	1	1	1	1	1	1	1	1	1	0	0
15°	1	1	1	1	1	1	1	1	1	0	0
13.75°	1	1	1	1	1	1	1	1	1	0	0
12.5°	1	1	1	1	1	1	1	1	1	0	0
11.25°	2	1	1	1	1	1	1	1	1	0	0
10°	2	1	1	1	1	1	1	1	1	0	0
8.75°	2	1	1	1	1	1	1	1	1	0	0
7.5°	2	1	1	1	1	1	1	1	1	0	0
6.25°	2	1	1	1	1	1	1	1	1	0	0
5°	2	1	1	1	1	1	1	1	1	0	0
3.75°	2	1	1	1	1	1	1	1	1	0	0
2.5°	2	1	1	1	1	1	1	1	1	0	0
1.25°	2	1	1	1	1	1	1	1	1	0	0
0°	2	1	1	1	1	1	1	1	1	0	0
-1.25°	2	1	1	1	1	1	1	1	1	0	0
-2.5°	2	1	1	1	1	1	1	1	1	0	0
-3.75°	2	1	1	1	1	1	1	1	1	0	0
-5°	2	1	1	1	1	1	1	1	1	0	0
-6.25°	2	1	1	1	1	1	1	1	1	0	0
-7.5°	2	1	1	1	1	1	1	1	1	0	0
-8.75°	2	1	1	1	1	1	1	1	1	0	0
-10°	2	1	1	1	1	1	1	1	1	0	0
-11.25°	2	1	1	1	1	1	1	1	1	0	0
-12.5°	1	1	1	1	1	1	1	1	1	0	0
-13.75°	1	1	1	1	1	1	1	1	1	0	0
-15°	1	1	1	1	1	1	1	1	1	0	0
-16.25°	1	1	1	1	1	1	1	1	1	0	0
-17.5°	1	1	1	1	1	1	1	1	1	0	0
-18.75°	1	1	1	1	1	1	1	1	1	0	0
-20°	1	1	1	1	1	1	1	1	1	0	0
-21.25°	1	1	1	1	1	1	1	1	1	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	1	1	1	1	1	1	1	1	1	0	0
-23.75°	1	1	1	1	1	1	1	1	1	0	0
-25°	1	1	1	1	1	1	1	1	1	0	0
-26.25°	1	1	1	1	1	1	1	1	1	0	0
-27.5°	1	1	1	1	1	1	1	1	1	0	0
-28.75°	1	1	1	1	1	1	1	1	1	0	0
-30°	1	1	1	1	1	1	1	1	1	0	0
-31.25°	1	1	1	1	1	1	1	1	1	0	0
-32.5°	1	1	1	1	1	1	1	1	1	0	0
-33.75°	1	1	1	1	1	1	1	1	1	0	0
-35°	1	1	1	1	1	1	1	1	1	0	0
-36.25°	1	1	1	1	1	1	1	1	0	0	0
-37.5°	1	1	1	1	1	1	1	1	0	0	0
-38.75°	1	1	1	1	1	1	1	1	0	0	0
-40°	1	1	1	1	1	1	1	1	0	0	0
-41.25°	1	1	1	1	1	1	1	1	0	0	0
-42.5°	1	1	1	1	1	1	1	1	0	0	0
-43.75°	1	1	1	1	1	1	1	1	0	0	0
-45°	1	1	1	1	1	1	1	1	0	0	0
-46.25°	1	1	1	1	1	1	1	1	0	0	0
-47.5°	1	1	1	1	1	1	1	1	0	0	0
-48.75°	1	1	1	1	1	1	1	1	0	0	0
-50°	1	1	1	1	1	1	1	0	0	0	0
-51.25°	1	1	1	1	1	1	1	0	0	0	0
-52.5°	1	1	1	1	1	1	1	0	0	0	0
-53.75°	1	1	1	1	1	1	1	0	0	0	0
-55°	1	1	1	1	1	1	1	0	0	0	0
-56.25°	1	1	1	1	1	1	1	0	0	0	0
-57.5°	1	1	1	1	1	1	0	0	0	0	0
-58.75°	1	1	1	1	1	1	0	0	0	0	0
-60°	1	1	1	1	1	1	0	0	0	0	0
-61.25°	1	1	1	1	1	1	0	0	0	0	0
-62.5°	1	1	1	1	1	0	0	0	0	0	0
-63.75°	1	1	1	1	1	0	0	0	0	0	0
-65°	1	1	1	1	1	0	0	0	0	0	0
-66.25°	1	1	1	1	0	0	0	0	0	0	0
-67.5°	1	1	1	1	0	0	0	0	0	0	0
-68.75°	1	1	1	0	0	0	0	0	0	0	0
-70°	1	1	1	0	0	0	0	0	0	0	0
-71.25°	1	1	0	0	0	0	0	0	0	0	0
-72.5°	1	1	0	0	0	0	0	0	0	0	0
-73.75°	1	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: P220586 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 1003-[A1, S1, SU1]-FL-LED4097-S-WT-L2-UNV

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)