Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590799

Luminaire Tested: 24CGTX-45-L92765-W2A-6500K

Issue Date: 9/7/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590799
	TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G3-2510-586-8)
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/7/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	24CGTX-45-L92765-W2A-6500K
Description:	2X4 4500 LUMEN CGTX TROFFER WITH VividTune LEDS AT 6500K CCT WITH FROSTED SMOOTH LENS
Light Source:	6500K CCT, 90 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	5266.2 lumens
Efficiency:	N/A
Efficacy:	118.6 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.27 / 1.39
Luminous Opening:	Rectangular (W 2' x L: 4' x H: 0')
CIE Type:	Direct
Input Watts (W):	44.4
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590799
CATALOG NUMBER: 24CGTX-45-L92765-W2A-6500K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590799
CATALOG NUMBER: 24CGTX-45-L92765-W2A-6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	94	91	93	90	88	89	87	85	83
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69
3	90	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	45	39	50	44	39	37
7	64	51	42	35	63	50	41	35	48	41	35	47	40	35	45	39	35	33
8	60	46	38	32	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	41	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	26	37	30	26	37	30	25	36	30	25	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2403	2403	2403
5°	2414	2404	2406
10°	2414	2401	2407
15°	2408	2397	2405
20°	2399	2388	2397
25°	2394	2378	2383
30°	2379	2368	2371
35°	2361	2349	2349
40°	2346	2333	2336
45°	2326	2310	2308
50°	2298	2281	2267
55°	2266	2246	2223
60°	2221	2198	2175
65°	2174	2133	2099
70°	2090	2053	2003
75°	2021	1954	1877
80°	1906	1832	1750
85°	1775	1661	1578

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2326 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590799
CATALOG NUMBER: 24CGTX-45-L92765-W2A-6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.3	3.2
10°-20°	486.3	9.2
20°-30°	739.8	14.0
30°-40°	896.6	17.0
40°-50°	937.1	17.8
50°-60°	855.4	16.2
60°-70°	662.9	12.6
70°-80°	397.7	7.6
80°-90°	121.0	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1395.5	26.5
0°-40°	2292.1	43.5
0°-60°	4084.6	77.6
0°-90°	5266.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5266.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1786	1786	1786	1786	1786	
5°	1787	1782	1780	1778	1782	170
15°	1728	1724	1721	1720	1726	488
25°	1612	1606	1602	1605	1605	743
35°	1438	1437	1430	1429	1430	900
45°	1223	1218	1214	1211	1213	942
55°	966	963	957	952	948	863
65°	683	678	670	661	659	674
75°	389	383	376	368	361	410
85°	115	112	108	103	102	127
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590799
CATALOG NUMBER: 24CGTX-45-L92765-W2A-6500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*1786.0*	1786.0	1786.0	1786.0	1786.0
2.5°	*1792.4*	*1786.0*	*1783.9*	*1781.7*	*1788.1*
5°	*1787.1*	1781.7	1779.6	1777.5	1781.7
7.5°	*1777.5*	1773.2	1771.1	1769.0	1774.3
10°	*1766.8*	1761.5	1757.2	1756.2	1761.5
12.5°	*1749.8*	1743.4	1741.3	1741.3	1745.5
15°	*1728.5*	1724.2	1721.0	1720.0	1726.4
17.5°	*1705.1*	1699.7	1695.5	1696.5	1700.8
20°	*1675.2*	1672.0	1667.8	1669.9	1674.2
22.5°	*1645.4*	1642.2	1638.0	1638.0	1641.2
25°	*1612.4*	1606.0	1601.8	1604.9	1604.9
27.5°	*1573.0*	1567.7	1563.4	1564.5	1567.7
30°	*1531.5*	1528.3	1524.0	1522.9	1526.1
32.5°	*1486.7*	1482.5	1479.3	1478.2	1481.4
35°	*1437.7*	1436.7	1430.3	1429.2	1430.3
37.5°	*1388.8*	1385.6	1380.2	1380.2	1382.4
40°	*1335.5*	1331.2	1328.0	1324.9	1330.2
42.5°	*1279.1*	1276.9	1271.6	1270.5	1271.6
45°	*1222.6*	1218.4	1214.1	1210.9	1213.0
47.5°	*1160.8*	1159.8	1153.4	1150.2	1149.1
50°	*1098.0*	1095.9	1089.5	1085.2	1083.1
52.5°	*1030.9*	1029.9	1026.7	1020.3	1020.3
55°	*966.0*	962.8	957.4	952.1	947.8
57.5°	*899.9*	893.5	888.2	880.8	879.7
60°	*825.4*	822.2	816.9	809.4	808.3
62.5°	*757.2*	750.8	744.4	737.0	733.8
65°	*682.7*	678.4	669.9	661.4	659.2
67.5°	*606.0*	603.9	597.5	585.7	584.7
70°	*531.4*	528.2	521.8	513.3	509.1
72.5°	*461.1*	456.9	447.3	442.0	437.7
75°	*388.7*	383.4	375.9	368.5	361.0
77.5°	*314.2*	313.1	306.7	297.1	292.9
80°	*246.0*	241.8	236.4	227.9	225.8
82.5°	*178.9*	176.8	172.5	164.0	162.9
85°	*115.0*	111.8	107.6	103.3	102.2
87.5°	*49.0*	49.0	49.0	46.9	46.9
90°	*0.0*	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590799
CATALOG NUMBER: 24CGTX-45-L92765-W2A-6500K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.04	16.70	15.41	17.02	17.33	14.93	16.59	15.30	16.91	17.22
	3H	16.95	18.46	17.33	18.78	19.14	16.79	18.29	17.16	18.62	18.98
	4H	17.71	19.13	18.11	19.47	19.85	17.50	18.91	17.89	19.26	19.64
	6H	18.30	19.61	18.71	19.98	20.37	18.04	19.36	18.45	19.72	20.11
	8H	18.51	19.76	18.93	20.15	20.55	18.23	19.48	18.65	19.87	20.27
	12H	18.66	19.86	19.09	20.25	20.67	18.36	19.56	18.79	19.95	20.37
4H	2H	15.69	17.11	16.09	17.46	17.83	15.60	17.02	16.00	17.37	17.74
	3H	17.83	19.02	18.23	19.42	19.82	17.68	18.88	18.09	19.27	19.67
	4H	18.72	19.80	19.15	20.21	20.65	18.53	19.61	18.96	20.02	20.46
	6H	19.45	20.40	19.90	20.84	21.29	19.21	20.15	19.66	20.59	21.05
	8H	19.71	20.60	20.17	21.04	21.51	19.44	20.33	19.90	20.77	21.24
	12H	19.92	20.72	20.40	21.20	21.66	19.63	20.43	20.11	20.90	21.37
8H	4H	19.06	19.94	19.52	20.39	20.85	18.89	19.78	19.35	20.22	20.68
	6H	19.92	20.66	20.42	21.15	21.62	19.70	20.44	20.19	20.93	21.40
	8H	20.28	20.94	20.78	21.45	21.93	20.02	20.69	20.53	21.19	21.67
	12H	20.57	21.16	21.08	21.65	22.21	20.28	20.87	20.79	21.36	21.92
12H	4H	19.10	19.90	19.58	20.37	20.84	18.94	19.74	19.42	20.21	20.68
	6H	19.99	20.66	20.50	21.16	21.65	19.78	20.45	20.29	20.95	21.44
	8H	20.41	21.00	20.91	21.49	22.05	20.16	20.75	20.67	21.24	21.80

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2510-566-18-R2

Test Date: 10/15/2025

Luminaire Tested: 22CGTX-50-L92765-W2A-6500K

Data in this report applies to families of products including 22CGTX

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2510-566-18-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**22CGTX-50-L92765-W2A-6500K**
Description:	*THIS IS A REVISION OF REPORT SP1-2512-566-18-R2 TO UPDATE THE CATALOG INFORMATION* 2X2 50000 Lumen CGTX TUNABLE WHITE FROM 2700K TO 6500K - 1.5 V

Spectral Parameters

CCT (K):	6661
CIE u':	0.1988
CIE v':	0.4648
Duv:	0.0010
CIE x:	0.3108
CIE y:	0.3230
CIE z:	0.3662
Peak Wavelength (nm):	453
Dominant Wavelength (nm):	485
Purity:	8.426951
Rf:	88.9
Rg:	97.8

CRI (Ra):	93.3				
R1:	94.6	R9:	71.5		
R2:	96.1	R10:	88.2		
R3:	93.9	R11:	93.9		
R4:	93.7	R12:	65.1		
R5:	92.6	R13:	96.0		
R6:	90.7	R14:	96.5		
R7:	95.1	R15:	93.4		
R8:	90.0				




Test Conditions

Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.0


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2510-566-18-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 6661K
CIE x = 0.3108
CIE y = 0.3230
Duv = 0.0010

Point lies inside the ANSI 6500K 4-step quadrangle

REPORT NUMBER: SP1-2510-566-18-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	277	NR	620	290	NR	750	7	NR	880	0	NR
365	0	NR	495	302	NR	625	288	NR	755	6	NR	885	0	NR
370	0	NR	500	334	NR	630	861	NR	760	5	NR	890	0	NR
375	0	NR	505	361	NR	635	516	NR	765	4	NR	895	0	NR
380	2	NR	510	383	NR	640	183	NR	770	4	NR	900	0	NR
385	2	NR	515	398	NR	645	180	NR	775	3	NR	905	0	NR
390	3	NR	520	406	NR	650	151	NR	780	3	NR	910	0	NR
395	5	NR	525	408	NR	655	128	NR	785	2	NR	915	0	NR
400	6	NR	530	410	NR	660	109	NR	790	2	NR	920	0	NR
405	9	NR	535	411	NR	665	92	NR	795	2	NR	925	0	NR
410	12	NR	540	411	NR	670	84	NR	800	2	NR	930	0	NR
415	18	NR	545	408	NR	675	69	NR	805	1	NR	935	0	NR
420	31	NR	550	405	NR	680	59	NR	810	1	NR	940	0	NR
425	54	NR	555	404	NR	685	51	NR	815	1	NR	945	0	NR
430	98	NR	560	400	NR	690	44	NR	820	1	NR	950	0	NR
435	179	NR	565	394	NR	695	38	NR	825	1	NR	955	0	NR
440	314	NR	570	386	NR	700	32	NR	830	1	NR	960	0	NR
445	557	NR	575	378	NR	705	28	NR	835	1	NR	965	0	NR
450	898	NR	580	370	NR	710	24	NR	840	1	NR	970	0	NR
455	970	NR	585	361	NR	715	20	NR	845	0	NR	975	0	NR
460	692	NR	590	351	NR	720	17	NR	850	0	NR	980	0	NR
465	510	NR	595	337	NR	725	15	NR	855	0	NR	985	0	NR
470	411	NR	600	326	NR	730	13	NR	860	0	NR	990	0	NR
475	313	NR	605	316	NR	735	11	NR	865	0	NR	995	0	NR
480	262	NR	610	328	NR	740	9	NR	870	0	NR	1000	0	NR
485	261	NR	615	331	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2510-566-18-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 2.39**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	277	NR	620	290	NR	750	7	NR	880	0	NR
365	0	NR	495	302	NR	625	288	NR	755	6	NR	885	0	NR
370	0	NR	500	334	NR	630	861	NR	760	5	NR	890	0	NR
375	0	NR	505	361	NR	635	516	NR	765	4	NR	895	0	NR
380	2	NR	510	383	NR	640	183	NR	770	4	NR	900	0	NR
385	2	NR	515	398	NR	645	180	NR	775	3	NR	905	0	NR
390	3	NR	520	406	NR	650	151	NR	780	3	NR	910	0	NR
395	5	NR	525	408	NR	655	128	NR	785	2	NR	915	0	NR
400	6	NR	530	410	NR	660	109	NR	790	2	NR	920	0	NR
405	9	NR	535	411	NR	665	92	NR	795	2	NR	925	0	NR
410	12	NR	540	411	NR	670	84	NR	800	2	NR	930	0	NR
415	18	NR	545	408	NR	675	69	NR	805	1	NR	935	0	NR
420	31	NR	550	405	NR	680	59	NR	810	1	NR	940	0	NR
425	54	NR	555	404	NR	685	51	NR	815	1	NR	945	0	NR
430	98	NR	560	400	NR	690	44	NR	820	1	NR	950	0	NR
435	179	NR	565	394	NR	695	38	NR	825	1	NR	955	0	NR
440	314	NR	570	386	NR	700	32	NR	830	1	NR	960	0	NR
445	557	NR	575	378	NR	705	28	NR	835	1	NR	965	0	NR
450	898	NR	580	370	NR	710	24	NR	840	1	NR	970	0	NR
455	970	NR	585	361	NR	715	20	NR	845	0	NR	975	0	NR
460	692	NR	590	351	NR	720	17	NR	850	0	NR	980	0	NR
465	510	NR	595	337	NR	725	15	NR	855	0	NR	985	0	NR
470	411	NR	600	326	NR	730	13	NR	860	0	NR	990	0	NR
475	313	NR	605	316	NR	735	11	NR	865	0	NR	995	0	NR
480	262	NR	610	328	NR	740	9	NR	870	0	NR	1000	0	NR
485	261	NR	615	331	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2510-566-18-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 5.37**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	277	NR	620	290	NR	750	7	NR	880	0	NR
365	0	NR	495	302	NR	625	288	NR	755	6	NR	885	0	NR
370	0	NR	500	334	NR	630	861	NR	760	5	NR	890	0	NR
375	0	NR	505	361	NR	635	516	NR	765	4	NR	895	0	NR
380	2	NR	510	383	NR	640	183	NR	770	4	NR	900	0	NR
385	2	NR	515	398	NR	645	180	NR	775	3	NR	905	0	NR
390	3	NR	520	406	NR	650	151	NR	780	3	NR	910	0	NR
395	5	NR	525	408	NR	655	128	NR	785	2	NR	915	0	NR
400	6	NR	530	410	NR	660	109	NR	790	2	NR	920	0	NR
405	9	NR	535	411	NR	665	92	NR	795	2	NR	925	0	NR
410	12	NR	540	411	NR	670	84	NR	800	2	NR	930	0	NR
415	18	NR	545	408	NR	675	69	NR	805	1	NR	935	0	NR
420	31	NR	550	405	NR	680	59	NR	810	1	NR	940	0	NR
425	54	NR	555	404	NR	685	51	NR	815	1	NR	945	0	NR
430	98	NR	560	400	NR	690	44	NR	820	1	NR	950	0	NR
435	179	NR	565	394	NR	695	38	NR	825	1	NR	955	0	NR
440	314	NR	570	386	NR	700	32	NR	830	1	NR	960	0	NR
445	557	NR	575	378	NR	705	28	NR	835	1	NR	965	0	NR
450	898	NR	580	370	NR	710	24	NR	840	1	NR	970	0	NR
455	970	NR	585	361	NR	715	20	NR	845	0	NR	975	0	NR
460	692	NR	590	351	NR	720	17	NR	850	0	NR	980	0	NR
465	510	NR	595	337	NR	725	15	NR	855	0	NR	985	0	NR
470	411	NR	600	326	NR	730	13	NR	860	0	NR	990	0	NR
475	313	NR	605	316	NR	735	11	NR	865	0	NR	995	0	NR
480	262	NR	610	328	NR	740	9	NR	870	0	NR	1000	0	NR
485	261	NR	615	331	NR	745	8	NR	875	0	NR			


REPORT NUMBER: SP1-2510-566-18-R2

TM-30-18


Summary


R_f = 88.9
R_g = 97.8
CIE R_a = 93.3
R_9 = 71.5


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2510-566-18-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 93	CES51 = 94	CES76 = 83
CES02 = 60	CES27 = 87	CES52 = 98	CES77 = 85
CES03 = 31	CES28 = 95	CES53 = 95	CES78 = 80
CES04 = 68	CES29 = 95	CES54 = 89	CES79 = 95
CES05 = 47	CES30 = 83	CES55 = 86	CES80 = 91
CES06 = 49	CES31 = 96	CES56 = 90	CES81 = 85
CES07 = 40	CES32 = 91	CES57 = 87	CES82 = 96
CES08 = 39	CES33 = 93	CES58 = 88	CES83 = 96
CES09 = 29	CES34 = 92	CES59 = 95	CES84 = 91
CES10 = 72	CES35 = 95	CES60 = 89	CES85 = 81
CES11 = 55	CES36 = 73	CES61 = 89	CES86 = 87
CES12 = 61	CES37 = 94	CES62 = 77	CES87 = 91
CES13 = 42	CES38 = 77	CES63 = 88	CES88 = 97
CES14 = 74	CES39 = 98	CES64 = 83	CES89 = 87
CES15 = 70	CES40 = 99	CES65 = 83	CES90 = 94
CES16 = 46	CES41 = 92	CES66 = 78	CES91 = 63
CES17 = 48	CES42 = 93	CES67 = 77	CES92 = 77
CES18 = 55	CES43 = 95	CES68 = 82	CES93 = 85
CES19 = 70	CES44 = 99	CES69 = 83	CES94 = 79
CES20 = 64	CES45 = 98	CES70 = 80	CES95 = 80
CES21 = 84	CES46 = 96	CES71 = 69	CES96 = 92
CES22 = 76	CES47 = 93	CES72 = 91	CES97 = 96
CES23 = 91	CES48 = 85	CES73 = 74	CES98 = 94
CES24 = 89	CES49 = 96	CES74 = 88	CES99 = 92
CES25 = 70	CES50 = 95	CES75 = 73	





REPORT NUMBER: SP1-2510-566-18-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2510-566-18-R2

TM-30-18

Measure Comparisons





(END OF REPORT)