Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590895

Luminaire Tested: 14CGTX-20-L93050-W2A-5000K

Issue Date: 9/7/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590895
	TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G3-2512-631-11)
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/7/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	14CGTX-20-L93050-W2A-5000K
Description:	1X4 2000 LUMEN CGTX TROFFER WITH VividTune LEDS AT 5000K CCT
Light Source:	5000K CCT, 90 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	2221.5 lumens
Efficiency:	N/A
Efficacy:	112.8 lumens/watt
Spacing Criteria (0/90/45):	1.26 / 1.26 / 1.38
Luminous Opening:	Rectangular (W 1' x L: 4' x H: 0')
CIE Type:	Direct
Input Watts (W):	19.7
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590895
CATALOG NUMBER: 14CGTX-20-L93050-W2A-5000K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590895
CATALOG NUMBER: 14CGTX-20-L93050-W2A-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	94	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	79	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	44	39	50	44	39	37
7	64	51	42	35	63	50	41	35	48	41	35	47	40	35	45	39	34	32
8	60	46	37	32	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	41	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	26	37	30	25	37	30	25	36	30	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2034	2034	2034
5°	2030	2022	2039
10°	2031	2022	2037
15°	2024	2021	2027
20°	2015	2015	2021
25°	2005	2005	2011
30°	1995	1995	1991
35°	1979	1979	1979
40°	1962	1962	1958
45°	1942	1942	1934
50°	1927	1923	1905
55°	1900	1886	1876
60°	1876	1854	1837
65°	1821	1801	1768
70°	1782	1741	1717
75°	1714	1671	1617
80°	1618	1585	1520
85°	1482	1417	1321

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
Vertical Angle: 45°
Luminance: 1950 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590895
CATALOG NUMBER: 14CGTX-20-L93050-W2A-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.5	3.2
10°-20°	205.2	9.2
20°-30°	311.8	14.0
30°-40°	376.9	17.0
40°-50°	393.8	17.7
50°-60°	360.0	16.2
60°-70°	280.7	12.6
70°-80°	170.0	7.7
80°-90°	51.5	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	588.5	26.5
0°-40°	965.4	43.5
0°-60°	1719.2	77.4
0°-90°	2221.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2221.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	756	756	756	756	756	
5°	752	752	748	753	755	72
15°	726	726	725	730	728	205
25°	675	676	675	678	677	311
35°	602	603	602	601	602	377
45°	510	512	510	508	508	394
55°	405	405	402	401	400	363
65°	286	286	283	281	278	285
75°	165	163	161	158	156	175
85°	48	47	46	44	43	55
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590895
CATALOG NUMBER: 14CGTX-20-L93050-W2A-5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	755.7	755.7	755.7	*755.7*	755.7
2.5°	*754.7*	*752.6*	*752.6*	*756.8*	*755.7*
5°	751.5	751.5	748.4	*752.6*	754.7
7.5°	749.5	748.4	746.3	*749.5*	749.5
10°	743.2	743.2	740.1	*745.3*	745.3
12.5°	735.9	735.9	732.8	*739.0*	738.0
15°	726.5	726.5	725.4	*729.6*	727.5
17.5°	715.0	716.1	714.0	*719.2*	720.2
20°	703.5	705.6	703.5	*705.6*	705.6
22.5°	692.0	692.0	690.0	*692.0*	694.1
25°	675.3	676.4	675.3	*678.5*	677.4
27.5°	658.6	660.7	659.7	*660.7*	660.7
30°	641.9	641.9	641.9	*640.9*	640.9
32.5°	623.2	624.2	622.1	*621.1*	623.2
35°	602.3	603.3	602.3	*601.2*	602.3
37.5°	582.4	583.5	580.4	*580.4*	580.4
40°	558.4	559.5	558.4	*558.4*	557.4
42.5°	535.5	537.6	535.5	*534.4*	532.3
45°	510.4	512.5	510.4	*508.3*	508.3
47.5°	485.4	487.5	486.4	*483.3*	482.2
50°	460.3	461.4	459.3	*455.1*	455.1
52.5°	433.2	434.2	431.1	*428.0*	428.0
55°	405.0	405.0	401.9	*400.8*	399.8
57.5°	378.9	376.8	374.7	*371.6*	370.6
60°	348.6	347.6	344.5	*341.3*	341.3
62.5°	320.4	318.4	315.2	*310.0*	311.1
65°	286.0	286.0	282.9	*280.8*	277.7
67.5°	257.8	256.8	253.6	*250.5*	249.5
70°	226.5	224.4	221.3	*218.2*	218.2
72.5°	197.3	194.1	192.1	*187.9*	187.9
75°	164.9	162.8	160.7	*157.6*	155.5
77.5°	134.7	133.6	131.5	*128.4*	126.3
80°	104.4	104.4	102.3	*99.2*	98.1
82.5°	78.3	75.2	73.1	*71.0*	69.9
85°	48.0	47.0	45.9	*43.8*	42.8
87.5°	21.9	19.8	19.8	*18.8*	18.8
90°	0.0	0.0	0.0	*0.0*	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590895
CATALOG NUMBER: 14CGTX-20-L93050-W2A-5000K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.45	16.11	14.81	16.42	16.74	14.34	16.00	14.70	16.31	16.63
	3H	16.38	17.89	16.76	18.22	18.57	16.23	17.74	16.61	18.06	18.42
	4H	17.15	18.57	17.54	18.91	19.29	16.96	18.38	17.35	18.72	19.10
	6H	17.75	19.06	18.16	19.43	19.82	17.52	18.84	17.93	19.20	19.59
	8H	17.96	19.22	18.39	19.61	20.01	17.71	18.97	18.13	19.36	19.76
	12H	18.12	19.32	18.55	19.71	20.13	17.84	19.05	18.27	19.43	19.86
4H	2H	15.10	16.52	15.50	16.87	17.24	15.01	16.43	15.41	16.78	17.16
	3H	17.26	18.46	17.67	18.85	19.25	17.13	18.32	17.54	18.72	19.12
	4H	18.16	19.24	18.59	19.66	20.09	17.99	19.07	18.42	19.49	19.92
	6H	18.90	19.85	19.36	20.29	20.75	18.69	19.64	19.14	20.08	20.54
	8H	19.18	20.07	19.64	20.51	20.97	18.94	19.83	19.40	20.27	20.73
	12H	19.39	20.19	19.86	20.66	21.13	19.12	19.92	19.60	20.39	20.86
8H	4H	18.51	19.39	18.96	19.84	20.30	18.36	19.25	18.82	19.69	20.15
	6H	19.39	20.13	19.88	20.62	21.09	19.20	19.94	19.69	20.42	20.90
	8H	19.75	20.42	20.26	20.92	21.40	19.52	20.19	20.03	20.69	21.18
	12H	20.04	20.63	20.55	21.12	21.68	19.78	20.37	20.29	20.86	21.42
12H	4H	18.55	19.35	19.03	19.82	20.29	18.41	19.21	18.89	19.68	20.15
	6H	19.46	20.13	19.97	20.63	21.12	19.28	19.94	19.78	20.45	20.93
	8H	19.88	20.47	20.39	20.96	21.52	19.67	20.26	20.17	20.75	21.31

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2512-631-24-R2

Test Date: 02/04/2026

Luminaire Tested: 22CGTX-50-L93050-W2A-5000K

Data in this report applies to families of products including 22CGTX

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2512-631-24-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**22CGTX-50-L93050-W2A-5000K**
Description:	*THIS IS A REVISION OF REPORT SP1-2512-631-24-R2 TO UPDATE THE CATALOG INFORMATION* 2X2 5000 LUMEN HE CGTX TUNABLE WHITE FROM 3000K TO 5000K - 1 Volt

Spectral Parameters

CCT (K):	5183
CIE u':	0.2084
CIE v':	0.4838
Duv:	0.0018
CIE x:	0.3404
CIE y:	0.3513
CIE z:	0.3084
Peak Wavelength (nm):	630
Dominant Wavelength (nm):	567
Purity:	7.523728
Rf:	89.8
Rg:	98.4

CRI (Ra):	93.0
R1:	94.0
R2:	95.9
R3:	95.1
R4:	93.5
R5:	92.7
R6:	92.2
R7:	94.0
R8:	86.9
R9:	64.0
R10:	88.2
R11:	93.7
R12:	69.8
R13:	94.9
R14:	97.0
R15:	92.0




Test Conditions

Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2512-631-24-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 5183K
CIE x = 0.3404
CIE y = 0.3513
Duv = 0.0018

Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2512-631-24-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	251	NR	620	335	NR	750	8	NR	880	0	NR
365	0	NR	495	277	NR	625	337	NR	755	7	NR	885	0	NR
370	0	NR	500	312	NR	630	1000	NR	760	6	NR	890	0	NR
375	1	NR	505	342	NR	635	569	NR	765	5	NR	895	0	NR
380	2	NR	510	365	NR	640	212	NR	770	4	NR	900	0	NR
385	2	NR	515	380	NR	645	218	NR	775	4	NR	905	0	NR
390	3	NR	520	392	NR	650	177	NR	780	3	NR	910	0	NR
395	4	NR	525	399	NR	655	148	NR	785	3	NR	915	0	NR
400	5	NR	530	402	NR	660	126	NR	790	2	NR	920	0	NR
405	7	NR	535	406	NR	665	106	NR	795	2	NR	925	0	NR
410	10	NR	540	407	NR	670	97	NR	800	2	NR	930	0	NR
415	15	NR	545	409	NR	675	80	NR	805	2	NR	935	0	NR
420	25	NR	550	410	NR	680	69	NR	810	1	NR	940	0	NR
425	43	NR	555	409	NR	685	59	NR	815	1	NR	945	0	NR
430	76	NR	560	409	NR	690	51	NR	820	1	NR	950	0	NR
435	135	NR	565	409	NR	695	44	NR	825	1	NR	955	0	NR
440	235	NR	570	405	NR	700	38	NR	830	1	NR	960	0	NR
445	412	NR	575	402	NR	705	32	NR	835	1	NR	965	0	NR
450	675	NR	580	396	NR	710	27	NR	840	1	NR	970	0	NR
455	756	NR	585	389	NR	715	23	NR	845	1	NR	975	0	NR
460	560	NR	590	382	NR	720	20	NR	850	0	NR	980	0	NR
465	418	NR	595	371	NR	725	17	NR	855	0	NR	985	0	NR
470	344	NR	600	363	NR	730	15	NR	860	0	NR	990	0	NR
475	268	NR	605	356	NR	735	13	NR	865	0	NR	995	0	NR
480	229	NR	610	379	NR	740	11	NR	870	0	NR	1000	0	NR
485	231	NR	615	379	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2512-631-24-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 2.11**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	251	NR	620	335	NR	750	8	NR	880	0	NR
365	0	NR	495	277	NR	625	337	NR	755	7	NR	885	0	NR
370	0	NR	500	312	NR	630	1000	NR	760	6	NR	890	0	NR
375	1	NR	505	342	NR	635	569	NR	765	5	NR	895	0	NR
380	2	NR	510	365	NR	640	212	NR	770	4	NR	900	0	NR
385	2	NR	515	380	NR	645	218	NR	775	4	NR	905	0	NR
390	3	NR	520	392	NR	650	177	NR	780	3	NR	910	0	NR
395	4	NR	525	399	NR	655	148	NR	785	3	NR	915	0	NR
400	5	NR	530	402	NR	660	126	NR	790	2	NR	920	0	NR
405	7	NR	535	406	NR	665	106	NR	795	2	NR	925	0	NR
410	10	NR	540	407	NR	670	97	NR	800	2	NR	930	0	NR
415	15	NR	545	409	NR	675	80	NR	805	2	NR	935	0	NR
420	25	NR	550	410	NR	680	69	NR	810	1	NR	940	0	NR
425	43	NR	555	409	NR	685	59	NR	815	1	NR	945	0	NR
430	76	NR	560	409	NR	690	51	NR	820	1	NR	950	0	NR
435	135	NR	565	409	NR	695	44	NR	825	1	NR	955	0	NR
440	235	NR	570	405	NR	700	38	NR	830	1	NR	960	0	NR
445	412	NR	575	402	NR	705	32	NR	835	1	NR	965	0	NR
450	675	NR	580	396	NR	710	27	NR	840	1	NR	970	0	NR
455	756	NR	585	389	NR	715	23	NR	845	1	NR	975	0	NR
460	560	NR	590	382	NR	720	20	NR	850	0	NR	980	0	NR
465	418	NR	595	371	NR	725	17	NR	855	0	NR	985	0	NR
470	344	NR	600	363	NR	730	15	NR	860	0	NR	990	0	NR
475	268	NR	605	356	NR	735	13	NR	865	0	NR	995	0	NR
480	229	NR	610	379	NR	740	11	NR	870	0	NR	1000	0	NR
485	231	NR	615	379	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2512-631-24-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 4.6**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	251	NR	620	335	NR	750	8	NR	880	0	NR
365	0	NR	495	277	NR	625	337	NR	755	7	NR	885	0	NR
370	0	NR	500	312	NR	630	1000	NR	760	6	NR	890	0	NR
375	1	NR	505	342	NR	635	569	NR	765	5	NR	895	0	NR
380	2	NR	510	365	NR	640	212	NR	770	4	NR	900	0	NR
385	2	NR	515	380	NR	645	218	NR	775	4	NR	905	0	NR
390	3	NR	520	392	NR	650	177	NR	780	3	NR	910	0	NR
395	4	NR	525	399	NR	655	148	NR	785	3	NR	915	0	NR
400	5	NR	530	402	NR	660	126	NR	790	2	NR	920	0	NR
405	7	NR	535	406	NR	665	106	NR	795	2	NR	925	0	NR
410	10	NR	540	407	NR	670	97	NR	800	2	NR	930	0	NR
415	15	NR	545	409	NR	675	80	NR	805	2	NR	935	0	NR
420	25	NR	550	410	NR	680	69	NR	810	1	NR	940	0	NR
425	43	NR	555	409	NR	685	59	NR	815	1	NR	945	0	NR
430	76	NR	560	409	NR	690	51	NR	820	1	NR	950	0	NR
435	135	NR	565	409	NR	695	44	NR	825	1	NR	955	0	NR
440	235	NR	570	405	NR	700	38	NR	830	1	NR	960	0	NR
445	412	NR	575	402	NR	705	32	NR	835	1	NR	965	0	NR
450	675	NR	580	396	NR	710	27	NR	840	1	NR	970	0	NR
455	756	NR	585	389	NR	715	23	NR	845	1	NR	975	0	NR
460	560	NR	590	382	NR	720	20	NR	850	0	NR	980	0	NR
465	418	NR	595	371	NR	725	17	NR	855	0	NR	985	0	NR
470	344	NR	600	363	NR	730	15	NR	860	0	NR	990	0	NR
475	268	NR	605	356	NR	735	13	NR	865	0	NR	995	0	NR
480	229	NR	610	379	NR	740	11	NR	870	0	NR	1000	0	NR
485	231	NR	615	379	NR	745	9	NR	875	0	NR			


REPORT NUMBER: SP1-2512-631-24-R2

TM-30-18


Summary


R_f = 89.8
R_g = 98.4
CIE R_a = 93.0
R_9 = 64.0


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2512-631-24-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 93	CES51 = 95	CES76 = 85
CES02 = 60	CES27 = 90	CES52 = 98	CES77 = 87
CES03 = 31	CES28 = 95	CES53 = 96	CES78 = 82
CES04 = 68	CES29 = 96	CES54 = 91	CES79 = 94
CES05 = 47	CES30 = 87	CES55 = 89	CES80 = 92
CES06 = 50	CES31 = 97	CES56 = 92	CES81 = 82
CES07 = 41	CES32 = 90	CES57 = 90	CES82 = 96
CES08 = 40	CES33 = 96	CES58 = 90	CES83 = 96
CES09 = 29	CES34 = 92	CES59 = 96	CES84 = 93
CES10 = 73	CES35 = 95	CES60 = 90	CES85 = 82
CES11 = 55	CES36 = 77	CES61 = 90	CES86 = 85
CES12 = 62	CES37 = 94	CES62 = 81	CES87 = 91
CES13 = 42	CES38 = 82	CES63 = 89	CES88 = 97
CES14 = 74	CES39 = 99	CES64 = 85	CES89 = 86
CES15 = 71	CES40 = 98	CES65 = 85	CES90 = 95
CES16 = 46	CES41 = 94	CES66 = 82	CES91 = 70
CES17 = 48	CES42 = 93	CES67 = 81	CES92 = 76
CES18 = 56	CES43 = 94	CES68 = 85	CES93 = 85
CES19 = 70	CES44 = 99	CES69 = 86	CES94 = 76
CES20 = 65	CES45 = 98	CES70 = 83	CES95 = 81
CES21 = 84	CES46 = 97	CES71 = 74	CES96 = 92
CES22 = 77	CES47 = 94	CES72 = 92	CES97 = 96
CES23 = 91	CES48 = 88	CES73 = 78	CES98 = 94
CES24 = 90	CES49 = 97	CES74 = 90	CES99 = 92
CES25 = 70	CES50 = 96	CES75 = 77	





REPORT NUMBER: SP1-2512-631-24-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2512-631-24-R2

TM-30-18

Measure Comparisons





(END OF REPORT)