Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590902

Luminaire Tested: 14CGTX-42-L93050-W2A-3500K

Issue Date: 9/7/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590902
	TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G3-2512-631-13)
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/7/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	14CGTX-42-L93050-W2A-3500K
Description:	1X4 4200 LUMEN CGTX TROFFER WITH VividTune LEDS AT 3500K CCT
Light Source:	3500K CCT, 90 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	4074.8 lumens
Efficiency:	N/A
Efficacy:	102.6 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.26 / 1.38
Luminous Opening:	Rectangular (W 1' x L: 4' x H: 0')
CIE Type:	Direct
Input Watts (W):	39.7
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590902
CATALOG NUMBER: 14CGTX-42-L93050-W2A-3500K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590902
CATALOG NUMBER: 14CGTX-42-L93050-W2A-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	94	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	79	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	44	39	50	44	39	37
7	64	51	42	35	63	50	41	35	48	41	35	47	40	35	45	39	34	32
8	60	46	37	32	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	41	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	26	37	30	25	37	30	25	36	30	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3723	3723	3723
5°	3723	3718	3737
10°	3719	3719	3730
15°	3712	3706	3726
20°	3698	3698	3716
25°	3680	3676	3692
30°	3663	3657	3657
35°	3634	3624	3624
40°	3599	3599	3584
45°	3576	3564	3545
50°	3527	3523	3502
55°	3478	3468	3439
60°	3423	3406	3346
65°	3353	3321	3249
70°	3275	3202	3113
75°	3147	3072	2966
80°	2996	2884	2820
85°	2714	2587	2430

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
Vertical Angle: 45°
Luminance: 3580 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590902
CATALOG NUMBER: 14CGTX-42-L93050-W2A-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.1	3.2
10°-20°	376.5	9.2
20°-30°	571.7	14.0
30°-40°	691.5	17.0
40°-50°	722.4	17.7
50°-60°	660.4	16.2
60°-70°	514.9	12.6
70°-80°	312.0	7.7
80°-90°	94.2	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1079.3	26.5
0°-40°	1770.7	43.5
0°-60°	3153.6	77.4
0°-90°	4074.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4074.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1383	1383	1383	1383	1383	
5°	1378	1379	1376	1381	1383	131
15°	1332	1332	1330	1336	1337	376
25°	1239	1240	1238	1241	1243	572
35°	1106	1107	1103	1105	1103	693
45°	940	941	937	935	932	724
55°	741	745	739	735	733	663
65°	527	528	522	515	510	522
75°	303	303	296	289	285	319
85°	88	87	84	80	79	98
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590902
CATALOG NUMBER: 14CGTX-42-L93050-W2A-3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1383.4	1383.4	1383.4	1383.4	*1383.4*
2.5°	*1384.5*	*1383.4*	*1381.4*	*1385.5*	*1387.5*
5°	1378.3	1379.3	1376.3	1381.4	*1383.4*
7.5°	1372.2	1372.2	1368.1	1376.3	*1374.2*
10°	1360.9	1363.0	1360.9	1365.0	*1365.0*
12.5°	1348.7	1349.7	1347.6	1352.8	*1354.8*
15°	1332.3	1332.3	1330.3	1336.4	*1337.4*
17.5°	1314.9	1313.9	1311.9	1317.0	*1317.0*
20°	1291.4	1292.4	1291.4	1293.5	*1297.5*
22.5°	1266.9	1267.9	1264.8	1268.9	*1271.0*
25°	1239.3	1240.3	1238.2	1241.3	*1243.4*
27.5°	1211.7	1210.6	1207.6	1211.7	*1211.7*
30°	1178.9	1178.9	1176.9	1177.9	*1176.9*
32.5°	1145.2	1143.1	1140.1	1142.1	*1141.1*
35°	1106.3	1107.4	1103.3	1105.3	*1103.3*
37.5°	1068.5	1067.5	1065.4	1065.4	*1064.4*
40°	1024.5	1027.6	1024.5	1023.5	*1020.4*
42.5°	983.6	985.7	981.6	979.5	*977.5*
45°	939.7	940.7	936.6	934.6	*931.5*
47.5°	893.7	894.7	889.6	887.5	*882.4*
50°	842.5	845.6	841.5	837.4	*836.4*
52.5°	793.5	795.5	790.4	788.3	*784.3*
55°	741.3	745.4	739.3	735.2	*733.1*
57.5°	691.2	693.3	687.1	680.0	*675.9*
60°	636.0	639.1	632.9	625.8	*621.7*
62.5°	582.8	583.8	574.6	570.6	*569.5*
65°	526.6	527.6	521.5	515.3	*510.2*
67.5°	472.4	471.4	465.2	457.1	*456.0*
70°	416.2	413.1	407.0	401.8	*395.7*
72.5°	356.9	357.9	350.7	344.6	*342.5*
75°	302.7	302.7	295.5	289.4	*285.3*
77.5°	246.4	246.4	240.3	234.2	*232.1*
80°	193.3	192.2	186.1	181.0	*182.0*
82.5°	139.1	138.0	132.9	129.9	*128.8*
85°	87.9	86.9	83.8	79.8	*78.7*
87.5°	37.8	37.8	35.8	34.8	*32.7*
90°	0.0	0.0	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590902
CATALOG NUMBER: 14CGTX-42-L93050-W2A-3500K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.57	18.23	16.93	18.54	18.86	16.43	18.09	16.79	18.40	18.72
	3H	18.50	20.01	18.88	20.33	20.69	18.31	19.82	18.69	20.15	20.50
	4H	19.26	20.68	19.66	21.03	21.40	19.04	20.46	19.44	20.81	21.19
	6H	19.86	21.18	20.27	21.54	21.94	19.61	20.93	20.02	21.29	21.68
	8H	20.07	21.33	20.50	21.72	22.12	19.81	21.07	20.23	21.46	21.85
	12H	20.22	21.43	20.65	21.81	22.24	19.94	21.15	20.37	21.53	21.96
4H	2H	17.22	18.64	17.62	18.99	19.36	17.11	18.53	17.51	18.88	19.25
	3H	19.38	20.58	19.79	20.97	21.37	19.22	20.42	19.63	20.81	21.21
	4H	20.29	21.37	20.72	21.78	22.22	20.09	21.17	20.52	21.58	22.02
	6H	21.03	21.98	21.48	22.42	22.87	20.79	21.74	21.24	22.18	22.63
	8H	21.30	22.19	21.76	22.63	23.09	21.04	21.93	21.50	22.37	22.83
	12H	21.50	22.30	21.98	22.77	23.24	21.22	22.02	21.70	22.50	22.96
8H	4H	20.63	21.52	21.09	21.96	22.42	20.46	21.34	20.91	21.79	22.25
	6H	21.51	22.25	22.00	22.74	23.22	21.29	22.04	21.79	22.52	23.00
	8H	21.87	22.53	22.37	23.04	23.52	21.62	22.29	22.13	22.79	23.28
	12H	22.16	22.75	22.66	23.24	23.79	21.88	22.47	22.39	22.96	23.52
12H	4H	20.67	21.47	21.15	21.95	22.42	20.51	21.31	20.99	21.78	22.25
	6H	21.58	22.25	22.09	22.75	23.24	21.37	22.04	21.88	22.55	23.03
	8H	22.00	22.59	22.50	23.08	23.64	21.77	22.36	22.27	22.85	23.41

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2512-631-36-R2

Test Date: 02/05/2026

Luminaire Tested: 22CGTX-50-L93050-W2A-3500K

Data in this report applies to families of products including 22CGTX

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2512-631-36-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**22CGTX-50-L93050-W2A-3500K**
Description:	*THIS IS A REVISION OF REPORT SP1-2512-631-36-R2 TO UPDATE THE CATALOG INFORMATION* 2X2 5000 LUMEN HE CGTX TUNABLE WHITE FROM 3000K TO 5000K - 7 Volt

Spectral Parameters

CCT (K):	3452
CIE u':	0.2375
CIE v':	0.5107
Duv:	-0.0011
CIE x:	0.4068
CIE y:	0.3888
CIE z:	0.2044
Peak Wavelength (nm):	630
Dominant Wavelength (nm):	581
Purity:	38.79211
Rf:	91.1
Rg:	101.1

CRI (Ra):	93.4
R1:	95.1
R2:	95.5
R3:	94.7
R4:	94.6
R5:	94.4
R6:	94.6
R7:	93.0
R8:	84.9
R9:	61.5
R10:	88.0
R11:	95.0
R12:	80.7
R13:	95.0
R14:	96.1
R15:	91.3




Test Conditions

Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2512-631-36-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3452K
CIE x = 0.4068
CIE y = 0.3888
Duv = -0.0011

Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2512-631-36-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	122	NR	620	312	NR	750	7	NR	880	0	NR
365	0	NR	495	147	NR	625	319	NR	755	6	NR	885	0	NR
370	0	NR	500	173	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	196	NR	635	559	NR	765	5	NR	895	0	NR
380	1	NR	510	213	NR	640	202	NR	770	4	NR	900	0	NR
385	1	NR	515	226	NR	645	211	NR	775	3	NR	905	0	NR
390	2	NR	520	235	NR	650	171	NR	780	3	NR	910	0	NR
395	2	NR	525	242	NR	655	144	NR	785	2	NR	915	0	NR
400	3	NR	530	246	NR	660	122	NR	790	2	NR	920	0	NR
405	4	NR	535	252	NR	665	103	NR	795	2	NR	925	0	NR
410	7	NR	540	257	NR	670	94	NR	800	2	NR	930	0	NR
415	11	NR	545	263	NR	675	78	NR	805	1	NR	935	0	NR
420	19	NR	550	268	NR	680	66	NR	810	1	NR	940	0	NR
425	34	NR	555	273	NR	685	57	NR	815	1	NR	945	0	NR
430	58	NR	560	281	NR	690	49	NR	820	1	NR	950	0	NR
435	97	NR	565	288	NR	695	42	NR	825	1	NR	955	0	NR
440	163	NR	570	293	NR	700	36	NR	830	1	NR	960	0	NR
445	243	NR	575	300	NR	705	31	NR	835	1	NR	965	0	NR
450	272	NR	580	305	NR	710	26	NR	840	1	NR	970	0	NR
455	234	NR	585	308	NR	715	22	NR	845	0	NR	975	0	NR
460	175	NR	590	311	NR	720	19	NR	850	0	NR	980	0	NR
465	134	NR	595	311	NR	725	16	NR	855	0	NR	985	0	NR
470	107	NR	600	312	NR	730	14	NR	860	0	NR	990	0	NR
475	92	NR	605	313	NR	735	12	NR	865	0	NR	995	0	NR
480	91	NR	610	343	NR	740	10	NR	870	0	NR	1000	0	NR
485	103	NR	615	349	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2512-631-36-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.59**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	122	NR	620	312	NR	750	7	NR	880	0	NR
365	0	NR	495	147	NR	625	319	NR	755	6	NR	885	0	NR
370	0	NR	500	173	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	196	NR	635	559	NR	765	5	NR	895	0	NR
380	1	NR	510	213	NR	640	202	NR	770	4	NR	900	0	NR
385	1	NR	515	226	NR	645	211	NR	775	3	NR	905	0	NR
390	2	NR	520	235	NR	650	171	NR	780	3	NR	910	0	NR
395	2	NR	525	242	NR	655	144	NR	785	2	NR	915	0	NR
400	3	NR	530	246	NR	660	122	NR	790	2	NR	920	0	NR
405	4	NR	535	252	NR	665	103	NR	795	2	NR	925	0	NR
410	7	NR	540	257	NR	670	94	NR	800	2	NR	930	0	NR
415	11	NR	545	263	NR	675	78	NR	805	1	NR	935	0	NR
420	19	NR	550	268	NR	680	66	NR	810	1	NR	940	0	NR
425	34	NR	555	273	NR	685	57	NR	815	1	NR	945	0	NR
430	58	NR	560	281	NR	690	49	NR	820	1	NR	950	0	NR
435	97	NR	565	288	NR	695	42	NR	825	1	NR	955	0	NR
440	163	NR	570	293	NR	700	36	NR	830	1	NR	960	0	NR
445	243	NR	575	300	NR	705	31	NR	835	1	NR	965	0	NR
450	272	NR	580	305	NR	710	26	NR	840	1	NR	970	0	NR
455	234	NR	585	308	NR	715	22	NR	845	0	NR	975	0	NR
460	175	NR	590	311	NR	720	19	NR	850	0	NR	980	0	NR
465	134	NR	595	311	NR	725	16	NR	855	0	NR	985	0	NR
470	107	NR	600	312	NR	730	14	NR	860	0	NR	990	0	NR
475	92	NR	605	313	NR	735	12	NR	865	0	NR	995	0	NR
480	91	NR	610	343	NR	740	10	NR	870	0	NR	1000	0	NR
485	103	NR	615	349	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2512-631-36-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.18**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	122	NR	620	312	NR	750	7	NR	880	0	NR
365	0	NR	495	147	NR	625	319	NR	755	6	NR	885	0	NR
370	0	NR	500	173	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	196	NR	635	559	NR	765	5	NR	895	0	NR
380	1	NR	510	213	NR	640	202	NR	770	4	NR	900	0	NR
385	1	NR	515	226	NR	645	211	NR	775	3	NR	905	0	NR
390	2	NR	520	235	NR	650	171	NR	780	3	NR	910	0	NR
395	2	NR	525	242	NR	655	144	NR	785	2	NR	915	0	NR
400	3	NR	530	246	NR	660	122	NR	790	2	NR	920	0	NR
405	4	NR	535	252	NR	665	103	NR	795	2	NR	925	0	NR
410	7	NR	540	257	NR	670	94	NR	800	2	NR	930	0	NR
415	11	NR	545	263	NR	675	78	NR	805	1	NR	935	0	NR
420	19	NR	550	268	NR	680	66	NR	810	1	NR	940	0	NR
425	34	NR	555	273	NR	685	57	NR	815	1	NR	945	0	NR
430	58	NR	560	281	NR	690	49	NR	820	1	NR	950	0	NR
435	97	NR	565	288	NR	695	42	NR	825	1	NR	955	0	NR
440	163	NR	570	293	NR	700	36	NR	830	1	NR	960	0	NR
445	243	NR	575	300	NR	705	31	NR	835	1	NR	965	0	NR
450	272	NR	580	305	NR	710	26	NR	840	1	NR	970	0	NR
455	234	NR	585	308	NR	715	22	NR	845	0	NR	975	0	NR
460	175	NR	590	311	NR	720	19	NR	850	0	NR	980	0	NR
465	134	NR	595	311	NR	725	16	NR	855	0	NR	985	0	NR
470	107	NR	600	312	NR	730	14	NR	860	0	NR	990	0	NR
475	92	NR	605	313	NR	735	12	NR	865	0	NR	995	0	NR
480	91	NR	610	343	NR	740	10	NR	870	0	NR	1000	0	NR
485	103	NR	615	349	NR	745	9	NR	875	0	NR			


REPORT NUMBER: SP1-2512-631-36-R2

TM-30-18


Summary


R_f = 91.1
R_g = 101.1
CIE R_a = 93.4
R_9 = 61.5


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2512-631-36-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 90	CES51 = 98	CES76 = 85
CES02 = 62	CES27 = 95	CES52 = 96	CES77 = 88
CES03 = 31	CES28 = 94	CES53 = 94	CES78 = 82
CES04 = 70	CES29 = 90	CES54 = 98	CES79 = 93
CES05 = 50	CES30 = 97	CES55 = 97	CES80 = 92
CES06 = 51	CES31 = 90	CES56 = 95	CES81 = 78
CES07 = 43	CES32 = 84	CES57 = 94	CES82 = 96
CES08 = 41	CES33 = 92	CES58 = 95	CES83 = 94
CES09 = 29	CES34 = 91	CES59 = 98	CES84 = 95
CES10 = 75	CES35 = 95	CES60 = 96	CES85 = 82
CES11 = 58	CES36 = 88	CES61 = 95	CES86 = 81
CES12 = 64	CES37 = 92	CES62 = 94	CES87 = 91
CES13 = 43	CES38 = 98	CES63 = 93	CES88 = 97
CES14 = 74	CES39 = 97	CES64 = 94	CES89 = 84
CES15 = 71	CES40 = 94	CES65 = 90	CES90 = 97
CES16 = 47	CES41 = 96	CES66 = 91	CES91 = 80
CES17 = 49	CES42 = 90	CES67 = 90	CES92 = 79
CES18 = 56	CES43 = 89	CES68 = 90	CES93 = 87
CES19 = 71	CES44 = 99	CES69 = 91	CES94 = 74
CES20 = 67	CES45 = 93	CES70 = 87	CES95 = 84
CES21 = 86	CES46 = 93	CES71 = 84	CES96 = 92
CES22 = 78	CES47 = 89	CES72 = 95	CES97 = 93
CES23 = 91	CES48 = 95	CES73 = 81	CES98 = 93
CES24 = 90	CES49 = 92	CES74 = 92	CES99 = 93
CES25 = 71	CES50 = 97	CES75 = 85	





REPORT NUMBER: SP1-2512-631-36-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2512-631-36-R2

TM-30-18

Measure Comparisons





(END OF REPORT)