Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590904

Luminaire Tested: 14CGTX-42-L93050-W2A-4500K

Issue Date: 9/7/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590904
	TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G3-2512-631-13)
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/7/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	14CGTX-42-L93050-W2A-4500K
Description:	1X4 4200 LUMEN CGTX TROFFER WITH VividTune LEDS AT 4500K CCT
Light Source:	4500K CCT, 90 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	4156.5 lumens
Efficiency:	N/A
Efficacy:	104.7 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.26 / 1.38
Luminous Opening:	Rectangular (W 1' x L: 4' x H: 0')
CIE Type:	Direct
Input Watts (W):	39.7
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590904
CATALOG NUMBER: 14CGTX-42-L93050-W2A-4500K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590904
CATALOG NUMBER: 14CGTX-42-L93050-W2A-4500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	94	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	79	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	44	39	50	44	39	37
7	64	51	42	35	63	50	41	35	48	41	35	47	40	35	45	39	34	32
8	60	46	37	32	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	41	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	26	37	30	25	37	30	25	36	30	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3798	3798	3798
5°	3798	3792	3812
10°	3793	3793	3805
15°	3786	3780	3801
20°	3772	3772	3790
25°	3753	3750	3766
30°	3737	3730	3730
35°	3707	3697	3697
40°	3671	3671	3656
45°	3648	3636	3616
50°	3598	3594	3572
55°	3548	3538	3508
60°	3491	3475	3413
65°	3420	3387	3314
70°	3340	3266	3175
75°	3210	3134	3026
80°	3054	2941	2878
85°	2770	2640	2479

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
Vertical Angle: 45°
Luminance: 3651 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590904
CATALOG NUMBER: 14CGTX-42-L93050-W2A-4500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.8	3.2
10°-20°	384.0	9.2
20°-30°	583.1	14.0
30°-40°	705.3	17.0
40°-50°	736.9	17.7
50°-60°	673.6	16.2
60°-70°	525.3	12.6
70°-80°	318.3	7.7
80°-90°	96.1	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1100.9	26.5
0°-40°	1806.2	43.5
0°-60°	3216.8	77.4
0°-90°	4156.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4156.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1411	1411	1411	1411	1411	
5°	1406	1407	1404	1409	1411	134
15°	1359	1359	1357	1363	1364	384
25°	1264	1265	1263	1266	1268	583
35°	1128	1130	1125	1128	1125	706
45°	958	960	955	953	950	739
55°	756	760	754	750	748	677
65°	537	538	532	526	520	532
75°	309	309	301	295	291	326
85°	90	89	86	81	80	100
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590904
CATALOG NUMBER: 14CGTX-42-L93050-W2A-4500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1411.2	1411.2	1411.2	1411.2	*1411.2*
2.5°	*1412.2*	*1411.2*	*1409.1*	*1413.2*	*1415.3*
5°	1405.9	1407.0	1403.9	1409.1	*1411.2*
7.5°	1399.7	1399.7	1395.5	1403.9	*1401.8*
10°	1388.2	1390.3	1388.2	1392.4	*1392.4*
12.5°	1375.7	1376.7	1374.7	1379.9	*1382.0*
15°	1359.0	1359.0	1356.9	1363.2	*1364.2*
17.5°	1341.3	1340.2	1338.2	1343.4	*1343.4*
20°	1317.3	1318.3	1317.3	1319.4	*1323.6*
22.5°	1292.3	1293.3	1290.2	1294.3	*1296.4*
25°	1264.1	1265.1	1263.1	1266.2	*1268.3*
27.5°	1235.9	1234.9	1231.8	1235.9	*1235.9*
30°	1202.6	1202.6	1200.5	1201.5	*1200.5*
32.5°	1168.1	1166.1	1162.9	1165.0	*1164.0*
35°	1128.5	1129.6	1125.4	1127.5	*1125.4*
37.5°	1089.9	1088.9	1086.8	1086.8	*1085.8*
40°	1045.1	1048.2	1045.1	1044.0	*1040.9*
42.5°	1003.4	1005.4	1001.3	999.2	*997.1*
45°	958.5	959.5	955.4	953.3	*950.2*
47.5°	911.6	912.6	907.4	905.3	*900.1*
50°	859.4	862.6	858.4	854.2	*853.2*
52.5°	809.4	811.4	806.2	804.1	*800.0*
55°	756.2	760.3	754.1	749.9	*747.8*
57.5°	705.1	707.1	700.9	693.6	*689.4*
60°	648.7	651.9	645.6	638.3	*634.1*
62.5°	594.5	595.5	586.2	582.0	*580.9*
65°	537.1	538.2	531.9	525.7	*520.5*
67.5°	481.9	480.8	474.6	466.2	*465.2*
70°	424.5	421.4	415.1	409.9	*403.6*
72.5°	364.0	365.0	357.7	351.5	*349.4*
75°	308.7	308.7	301.4	295.2	*291.0*
77.5°	251.4	251.4	245.1	238.8	*236.8*
80°	197.1	196.1	189.8	184.6	*185.7*
82.5°	141.8	140.8	135.6	132.5	*131.4*
85°	89.7	88.7	85.5	81.4	*80.3*
87.5°	38.6	38.6	36.5	35.5	*33.4*
90°	0.0	0.0	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590904
CATALOG NUMBER: 14CGTX-42-L93050-W2A-4500K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.64	18.30	17.00	18.61	18.92	16.50	18.16	16.86	18.47	18.79
	3H	18.57	20.07	18.95	20.40	20.76	18.38	19.89	18.76	20.21	20.57
	4H	19.33	20.75	19.73	21.10	21.47	19.11	20.53	19.51	20.88	21.25
	6H	19.93	21.25	20.34	21.61	22.00	19.68	21.00	20.09	21.36	21.75
	8H	20.14	21.40	20.57	21.79	22.19	19.88	21.14	20.30	21.53	21.92
	12H	20.29	21.50	20.72	21.88	22.31	20.01	21.22	20.44	21.60	22.03
4H	2H	17.29	18.71	17.69	19.06	19.43	17.18	18.60	17.58	18.95	19.32
	3H	19.45	20.64	19.86	21.04	21.44	19.29	20.49	19.70	20.88	21.28
	4H	20.35	21.44	20.79	21.85	22.29	20.16	21.24	20.59	21.65	22.09
	6H	21.10	22.05	21.55	22.49	22.94	20.86	21.81	21.31	22.25	22.70
	8H	21.37	22.25	21.82	22.70	23.16	21.11	22.00	21.57	22.44	22.90
	12H	21.57	22.37	22.05	22.84	23.31	21.29	22.09	21.77	22.56	23.03
8H	4H	20.70	21.59	21.16	22.03	22.49	20.52	21.41	20.98	21.86	22.32
	6H	21.58	22.32	22.07	22.81	23.28	21.36	22.10	21.85	22.59	23.07
	8H	21.93	22.60	22.44	23.10	23.59	21.69	22.36	22.20	22.86	23.35
	12H	22.22	22.81	22.73	23.30	23.86	21.95	22.54	22.46	23.03	23.59
12H	4H	20.74	21.54	21.22	22.02	22.48	20.58	21.38	21.05	21.85	22.32
	6H	21.65	22.32	22.16	22.82	23.31	21.44	22.11	21.95	22.62	23.10
	8H	22.07	22.66	22.57	23.15	23.71	21.84	22.43	22.34	22.92	23.47

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2512-631-28-R2

Test Date: 02/05/2026

Luminaire Tested: 22CGTX-50-L93050-W2A-4500K

Data in this report applies to families of products including 22CGTX

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2512-631-28-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**22CGTX-50-L93050-W2A-4500K**
Description:	*THIS IS A REVISION OF REPORT SP1-2512-631-28-R2 TO UPDATE THE CATALOG INFORMATION* 2X2 5000 LUMEN HE CGTX TUNABLE WHITE FROM 3000K TO 5000K - 3 Volt

Spectral Parameters

CCT (K):	4556
CIE u':	0.2166
CIE v':	0.4916
Duv:	-0.0001
CIE x:	0.3588
CIE y:	0.3619
CIE z:	0.2793
Peak Wavelength (nm):	630
Dominant Wavelength (nm):	576
Purity:	16.26758
Rf:	90.4
Rg:	99.5

CRI (Ra):	93.8		
R1:	95.1	R9:	68.4
R2:	96.4	R10:	89.0
R3:	95.1	R11:	94.6
R4:	94.5	R12:	68.9
R5:	93.5	R13:	95.8
R6:	93.0	R14:	96.7
R7:	94.8	R15:	92.7
R8:	88.3		



Test Conditions


Stabilization Time:	41M
Operation Time:	1H 41M
Sphere Temperature (°C):	25.1

REPORT NUMBER: SP1-2512-631-28-R2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2512-631-28-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4556K
CIE x = 0.3588
CIE y = 0.3619
Duv = -0.0001

Point lies inside the ANSI 4500K 4-step quadrangle

REPORT NUMBER: SP1-2512-631-28-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	198	NR	620	318	NR	750	7	NR	880	0	NR
365	0	NR	495	223	NR	625	321	NR	755	6	NR	885	0	NR
370	0	NR	500	254	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	282	NR	635	572	NR	765	5	NR	895	0	NR
380	1	NR	510	301	NR	640	202	NR	770	4	NR	900	0	NR
385	1	NR	515	316	NR	645	207	NR	775	3	NR	905	0	NR
390	2	NR	520	327	NR	650	170	NR	780	3	NR	910	0	NR
395	3	NR	525	332	NR	655	143	NR	785	2	NR	915	0	NR
400	4	NR	530	336	NR	660	121	NR	790	2	NR	920	0	NR
405	6	NR	535	340	NR	665	102	NR	795	2	NR	925	0	NR
410	8	NR	540	343	NR	670	94	NR	800	2	NR	930	0	NR
415	12	NR	545	346	NR	675	77	NR	805	1	NR	935	0	NR
420	21	NR	550	349	NR	680	66	NR	810	1	NR	940	0	NR
425	37	NR	555	349	NR	685	57	NR	815	1	NR	945	0	NR
430	66	NR	560	353	NR	690	49	NR	820	1	NR	950	0	NR
435	117	NR	565	355	NR	695	42	NR	825	1	NR	955	0	NR
440	203	NR	570	354	NR	700	36	NR	830	1	NR	960	0	NR
445	343	NR	575	354	NR	705	31	NR	835	1	NR	965	0	NR
450	516	NR	580	353	NR	710	26	NR	840	1	NR	970	0	NR
455	547	NR	585	349	NR	715	22	NR	845	0	NR	975	0	NR
460	402	NR	590	346	NR	720	19	NR	850	0	NR	980	0	NR
465	301	NR	595	340	NR	725	16	NR	855	0	NR	985	0	NR
470	248	NR	600	335	NR	730	14	NR	860	0	NR	990	0	NR
475	195	NR	605	330	NR	735	12	NR	865	0	NR	995	0	NR
480	172	NR	610	354	NR	740	10	NR	870	0	NR	1000	0	NR
485	178	NR	615	358	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2512-631-28-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.95**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	198	NR	620	318	NR	750	7	NR	880	0	NR
365	0	NR	495	223	NR	625	321	NR	755	6	NR	885	0	NR
370	0	NR	500	254	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	282	NR	635	572	NR	765	5	NR	895	0	NR
380	1	NR	510	301	NR	640	202	NR	770	4	NR	900	0	NR
385	1	NR	515	316	NR	645	207	NR	775	3	NR	905	0	NR
390	2	NR	520	327	NR	650	170	NR	780	3	NR	910	0	NR
395	3	NR	525	332	NR	655	143	NR	785	2	NR	915	0	NR
400	4	NR	530	336	NR	660	121	NR	790	2	NR	920	0	NR
405	6	NR	535	340	NR	665	102	NR	795	2	NR	925	0	NR
410	8	NR	540	343	NR	670	94	NR	800	2	NR	930	0	NR
415	12	NR	545	346	NR	675	77	NR	805	1	NR	935	0	NR
420	21	NR	550	349	NR	680	66	NR	810	1	NR	940	0	NR
425	37	NR	555	349	NR	685	57	NR	815	1	NR	945	0	NR
430	66	NR	560	353	NR	690	49	NR	820	1	NR	950	0	NR
435	117	NR	565	355	NR	695	42	NR	825	1	NR	955	0	NR
440	203	NR	570	354	NR	700	36	NR	830	1	NR	960	0	NR
445	343	NR	575	354	NR	705	31	NR	835	1	NR	965	0	NR
450	516	NR	580	353	NR	710	26	NR	840	1	NR	970	0	NR
455	547	NR	585	349	NR	715	22	NR	845	0	NR	975	0	NR
460	402	NR	590	346	NR	720	19	NR	850	0	NR	980	0	NR
465	301	NR	595	340	NR	725	16	NR	855	0	NR	985	0	NR
470	248	NR	600	335	NR	730	14	NR	860	0	NR	990	0	NR
475	195	NR	605	330	NR	735	12	NR	865	0	NR	995	0	NR
480	172	NR	610	354	NR	740	10	NR	870	0	NR	1000	0	NR
485	178	NR	615	358	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2512-631-28-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 4.17**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	198	NR	620	318	NR	750	7	NR	880	0	NR
365	0	NR	495	223	NR	625	321	NR	755	6	NR	885	0	NR
370	0	NR	500	254	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	282	NR	635	572	NR	765	5	NR	895	0	NR
380	1	NR	510	301	NR	640	202	NR	770	4	NR	900	0	NR
385	1	NR	515	316	NR	645	207	NR	775	3	NR	905	0	NR
390	2	NR	520	327	NR	650	170	NR	780	3	NR	910	0	NR
395	3	NR	525	332	NR	655	143	NR	785	2	NR	915	0	NR
400	4	NR	530	336	NR	660	121	NR	790	2	NR	920	0	NR
405	6	NR	535	340	NR	665	102	NR	795	2	NR	925	0	NR
410	8	NR	540	343	NR	670	94	NR	800	2	NR	930	0	NR
415	12	NR	545	346	NR	675	77	NR	805	1	NR	935	0	NR
420	21	NR	550	349	NR	680	66	NR	810	1	NR	940	0	NR
425	37	NR	555	349	NR	685	57	NR	815	1	NR	945	0	NR
430	66	NR	560	353	NR	690	49	NR	820	1	NR	950	0	NR
435	117	NR	565	355	NR	695	42	NR	825	1	NR	955	0	NR
440	203	NR	570	354	NR	700	36	NR	830	1	NR	960	0	NR
445	343	NR	575	354	NR	705	31	NR	835	1	NR	965	0	NR
450	516	NR	580	353	NR	710	26	NR	840	1	NR	970	0	NR
455	547	NR	585	349	NR	715	22	NR	845	0	NR	975	0	NR
460	402	NR	590	346	NR	720	19	NR	850	0	NR	980	0	NR
465	301	NR	595	340	NR	725	16	NR	855	0	NR	985	0	NR
470	248	NR	600	335	NR	730	14	NR	860	0	NR	990	0	NR
475	195	NR	605	330	NR	735	12	NR	865	0	NR	995	0	NR
480	172	NR	610	354	NR	740	10	NR	870	0	NR	1000	0	NR
485	178	NR	615	358	NR	745	9	NR	875	0	NR			


REPORT NUMBER: SP1-2512-631-28-R2

TM-30-18


Summary


R_f = 90.4
R_g = 99.5
CIE R_a = 93.8
R_9 = 68.4


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2512-631-28-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 92	CES51 = 96	CES76 = 85
CES02 = 61	CES27 = 90	CES52 = 99	CES77 = 87
CES03 = 31	CES28 = 95	CES53 = 97	CES78 = 82
CES04 = 69	CES29 = 96	CES54 = 92	CES79 = 94
CES05 = 48	CES30 = 89	CES55 = 90	CES80 = 92
CES06 = 50	CES31 = 97	CES56 = 93	CES81 = 81
CES07 = 41	CES32 = 88	CES57 = 92	CES82 = 96
CES08 = 40	CES33 = 98	CES58 = 92	CES83 = 96
CES09 = 29	CES34 = 92	CES59 = 97	CES84 = 93
CES10 = 74	CES35 = 95	CES60 = 91	CES85 = 82
CES11 = 56	CES36 = 79	CES61 = 91	CES86 = 84
CES12 = 62	CES37 = 94	CES62 = 83	CES87 = 91
CES13 = 43	CES38 = 84	CES63 = 91	CES88 = 98
CES14 = 74	CES39 = 99	CES64 = 87	CES89 = 86
CES15 = 71	CES40 = 98	CES65 = 86	CES90 = 96
CES16 = 47	CES41 = 96	CES66 = 84	CES91 = 71
CES17 = 49	CES42 = 92	CES67 = 83	CES92 = 77
CES18 = 56	CES43 = 93	CES68 = 86	CES93 = 86
CES19 = 70	CES44 = 99	CES69 = 87	CES94 = 76
CES20 = 65	CES45 = 97	CES70 = 83	CES95 = 82
CES21 = 85	CES46 = 97	CES71 = 76	CES96 = 92
CES22 = 77	CES47 = 95	CES72 = 92	CES97 = 95
CES23 = 91	CES48 = 90	CES73 = 78	CES98 = 95
CES24 = 90	CES49 = 96	CES74 = 91	CES99 = 93
CES25 = 70	CES50 = 98	CES75 = 79	





REPORT NUMBER: SP1-2512-631-28-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2512-631-28-R2

TM-30-18

Measure Comparisons





(END OF REPORT)