

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P246958

Luminaire Tested: **203-FL-8LED3025-12-BK-LVR**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246958  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-18)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 203-FL-8LED3025-12-BK-LVR  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 25 DEGREE NARROW OPTIC, FLUSH HOOD BLACK, HEX CELL LOUVER  
Light Source: (1) SORAA 3000K 90 CRI LED  
SM16-07-25D-930-03  
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 253.5 lumens  
Efficiency: N/A  
Efficacy: 32.5 lumens/watt  
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.29  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246958  
CATALOG NUMBER: 203-FL-8LED3025-12-BK-LVR

### Luminous Intensity Polar Plot





TEST NUMBER: P246958

CATALOG NUMBER: 203-FL-8LED3025-12-BK-LVR

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20							
RC	80				70				50				30				10							
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10				
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	111	106	106	106	106	102	102	102	102	100	100	100	100
1	115	113	112	110	113	111	110	108	107	106	105	105	104	103	102	102	100	100	99	99	97	97	97	97
2	112	109	106	104	110	107	105	103	104	102	100	100	101	100	98	98	99	97	96	96	95	95	95	95
3	109	105	102	99	107	103	101	98	101	99	97	97	99	97	95	95	97	95	94	94	93	93	93	93
4	106	101	98	95	105	100	97	95	98	96	93	93	97	94	92	92	95	93	91	91	90	90	90	90
5	103	98	95	92	102	97	94	91	96	93	91	91	94	92	90	90	93	91	89	89	88	88	88	88
6	101	96	92	89	100	95	91	89	94	91	88	88	92	90	88	88	91	89	87	87	86	86	86	86
7	99	93	89	87	98	92	89	87	91	88	86	86	90	88	86	86	90	87	85	85	84	84	84	84
8	97	91	87	85	96	90	87	84	89	86	84	84	89	86	84	84	88	85	84	84	83	83	83	83
9	95	89	85	83	94	88	85	83	88	85	82	82	87	84	82	82	86	84	82	82	81	81	81	81
10	93	87	83	81	92	86	83	81	86	83	81	81	85	82	81	81	85	82	80	80	80	80	80	80

**AVERAGE LUMINANCE (cd/sqm):**

0°	
0°	1047938
5°	773603
10°	386414
15°	167077
20°	72614
25°	27491
30°	10084
35°	4818
40°	2834
45°	1256
50°	691
55°	774
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P246958

CATALOG NUMBER: 203-FL-8LED3025-12-BK-LVR

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	122.9	48.5
10°-20°	95.9	37.8
20°-30°	26.7	10.5
30°-40°	5.6	2.2
40°-50°	1.7	0.7
50°-60°	0.7	0.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	245.4	96.8
0°-40°	251.0	99.1
0°-60°	253.5	100.0
0°-90°	253.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	253.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2124	
5°	1562	123
15°	327	96
25°	50	27
35°	8	6
45°	2	2
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P246958

CATALOG NUMBER: 203-FL-8LED3025-12-BK-LVR

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2124.0
1°	2078.8
2°	1987.5
3°	1866.1
4°	1723.3
5°	1562.0
6°	1397.1
7°	1231.3
8°	1067.3
9°	914.9
10°	771.3
11°	643.6
12°	537.2
13°	451.2
14°	383.9
15°	327.1
17.5°	219.0
20°	138.3
22.5°	83.3
25°	50.5
27.5°	31.9
30°	17.7
32.5°	11.5
35°	8.0
37.5°	6.2
40°	4.4
42.5°	2.7
45°	1.8
47.5°	1.8
50°	0.9
52.5°	0.9
55°	0.9
57.5°	0.9
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P246958

CATALOG NUMBER: 203-FL-8LED3025-12-BK-LVR

CANDELA DISTRIBUTION (continued):

90° |  $\frac{0^\circ}{0.0}$

(END OF REPORT)