Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590936

Luminaire Tested: 24CGTX-30-L93050-W2A-3000K

Issue Date: 9/7/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590936
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/7/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	24CGTX-30-L93050-W2A-3000K
Description:	2X4 3000 LUMEN CGTX TROFFER WITH VividTune LEDS AT 3000K CCT
Light Source:	3000K CCT, 90 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	3085.2 lumens
Efficiency:	N/A
Efficacy:	120.0 lumens/watt
Spacing Criteria (0/90/45):	1.28 / 1.27 / 1.39
Luminous Opening:	Rectangular (W 1.81' x L: 3.83' x H: 0')
CIE Type:	Direct
Input Watts (W):	25.7
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590936
CATALOG NUMBER: 24CGTX-30-L93050-W2A-3000K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590936
CATALOG NUMBER: 24CGTX-30-L93050-W2A-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	57
4	82	70	61	54	79	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	44	39	50	44	39	37
7	64	51	42	35	62	50	41	35	48	41	35	47	40	35	45	39	34	32
8	60	46	37	32	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	40	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	26	37	30	25	36	30	25	36	30	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1611	1611	1611
5°	1614	1613	1617
10°	1612	1619	1622
15°	1620	1614	1617
20°	1621	1607	1612
25°	1614	1605	1605
30°	1597	1597	1592
35°	1585	1585	1577
40°	1579	1569	1565
45°	1562	1553	1558
50°	1550	1538	1528
55°	1526	1515	1507
60°	1500	1484	1481
65°	1466	1448	1430
70°	1418	1391	1368
75°	1377	1329	1293
80°	1311	1249	1196
85°	1191	1155	1102

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1562 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590936
CATALOG NUMBER: 24CGTX-30-L93050-W2A-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.8	3.2
10°-20°	283.8	9.2
20°-30°	432.2	14.0
30°-40°	523.9	17.0
40°-50°	547.8	17.8
50°-60°	501.2	16.2
60°-70°	389.7	12.6
70°-80°	234.6	7.6
80°-90°	73.1	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	814.8	26.4
0°-40°	1338.6	43.4
0°-60°	2387.7	77.4
0°-90°	3085.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3085.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1040	1040	1040	1040	1040	
5°	1038	1040	1037	1033	1040	99
15°	1010	1004	1006	1001	1008	285
25°	944	939	939	934	939	434
35°	838	836	838	836	834	525
45°	713	713	709	709	711	550
55°	565	564	561	558	558	506
65°	400	396	395	390	390	395
75°	230	226	222	216	216	243
85°	67	69	65	64	62	76
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590936
CATALOG NUMBER: 24CGTX-30-L93050-W2A-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*1040*	1040	1040	1040	1040
2.5°	*1047*	*1043*	*1042*	*1043*	*1038*
5°	*1038*	1040	1037	1033	1040
7.5°	*1041*	1031	1033	1036	1033
10°	*1025*	1029	1029	1020	1031
12.5°	*1021*	1017	1015	1020	1017
15°	*1010*	1004	1006	1001	1008
17.5°	*990*	993	990	994	993
20°	*983*	975	975	971	978
22.5°	*959*	957	956	960	958
25°	*944*	939	939	934	939
27.5°	*917*	915	912	917	919
30°	*893*	891	893	887	890
32.5°	*869*	868	863	864	865
35°	*838*	836	838	836	834
37.5°	*810*	810	808	808	808
40°	*781*	780	776	774	774
42.5°	*745*	745	745	743	741
45°	*713*	713	709	709	711
47.5°	*677*	678	675	672	674
50°	*643*	638	638	636	634
52.5°	*607*	602	601	597	599
55°	*565*	564	561	558	558
57.5°	*526*	522	522	517	512
60°	*484*	484	479	476	478
62.5°	*442*	442	439	432	429
65°	*400*	396	395	390	390
67.5°	*357*	357	350	345	342
70°	*313*	310	307	303	302
72.5°	*273*	270	263	258	257
75°	*230*	226	222	216	216
77.5°	*187*	184	182	175	172
80°	*147*	146	140	136	134
82.5°	*107*	105	102	99	99
85°	*67*	69	65	64	62
87.5°	*32*	31	30	30	30
90°	*0*	0	0	0	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590936
CATALOG NUMBER: 24CGTX-30-L93050-W2A-3000K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.66	15.32	14.02	15.63	15.95	13.57	15.23	13.93	15.54	15.86
	3H	15.59	17.10	15.97	17.42	17.78	15.43	16.94	15.81	17.27	17.63
	4H	16.36	17.78	16.76	18.13	18.50	16.15	17.57	16.55	17.92	18.30
	6H	16.96	18.28	17.37	18.64	19.03	16.70	18.02	17.11	18.38	18.77
	8H	17.18	18.44	17.60	18.83	19.23	16.90	18.16	17.32	18.55	18.94
	12H	17.33	18.54	17.76	18.92	19.35	17.04	18.25	17.47	18.63	19.06
4H	2H	14.32	15.74	14.72	16.09	16.46	14.25	15.67	14.65	16.02	16.39
	3H	16.47	17.67	16.88	18.06	18.46	16.34	17.53	16.74	17.93	18.33
	4H	17.37	18.46	17.80	18.87	19.31	17.19	18.27	17.62	18.68	19.12
	6H	18.12	19.07	18.57	19.51	19.97	17.87	18.82	18.32	19.26	19.71
	8H	18.40	19.29	18.85	19.73	20.19	18.12	19.01	18.58	19.45	19.92
	12H	18.61	19.41	19.08	19.88	20.35	18.31	19.12	18.79	19.59	20.06
8H	4H	17.71	18.60	18.17	19.05	19.51	17.55	18.44	18.01	18.88	19.34
	6H	18.60	19.35	19.09	19.83	20.31	18.37	19.11	18.86	19.60	20.07
	8H	18.96	19.63	19.47	20.14	20.62	18.71	19.37	19.21	19.88	20.36
	12H	19.27	19.86	19.77	20.35	20.91	18.99	19.58	19.49	20.07	20.63
12H	4H	17.76	18.56	18.24	19.03	19.50	17.60	18.40	18.08	18.88	19.34
	6H	18.67	19.34	19.18	19.85	20.33	18.45	19.12	18.96	19.62	20.11
	8H	19.10	19.69	19.61	20.18	20.74	18.85	19.44	19.36	19.93	20.49

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2512-631-41-R2

Test Date: 02/05/2026

Luminaire Tested: 22CGTX-50-L93050-W2A-3000K

Data in this report applies to families of products including 22CGTX


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2512-631-41-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**22CGTX-50-L93050-W2A-3000K**
Description:	*THIS IS A REVISION OF REPORT SP1-2512-631-41-R2 TO UPDATE THE CATALOG INFORMATION* 2X2 5000 LUMEN HE CGTX TUNABLE WHITE FROM 3000K TO 5000K - 9.5 Volt

Spectral Parameters

CCT (K):	3066	CRI (Ra):	91.7		
CIE u':	0.2482	R1:	93.0	R9:	52.5
CIE v':	0.5206	R2:	94.0	R10:	85.0
Duv:	0.0004	R3:	94.3	R11:	94.8
CIE x:	0.4328	R4:	93.4	R12:	82.8
CIE y:	0.4036	R5:	92.4	R13:	92.9
CIE z:	0.1636	R6:	94.1	R14:	95.7
Peak Wavelength (nm):	630	R7:	91.5	R15:	87.8
Dominant Wavelength (nm):	582	R8:	80.7		
Purity:	51.0461				
Rf:	89.5				
Rg:	102				




Test Conditions

Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2512-631-41-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3066K
CIE x = 0.4328
CIE y = 0.4036
Duv = 0.0004

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2512-631-41-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	96	NR	620	317	NR	750	8	NR	880	0	NR
365	0	NR	495	121	NR	625	324	NR	755	7	NR	885	0	NR
370	0	NR	500	146	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	167	NR	635	572	NR	765	5	NR	895	0	NR
380	0	NR	510	183	NR	640	207	NR	770	4	NR	900	0	NR
385	1	NR	515	196	NR	645	215	NR	775	3	NR	905	0	NR
390	1	NR	520	205	NR	650	175	NR	780	3	NR	910	0	NR
395	2	NR	525	212	NR	655	147	NR	785	3	NR	915	0	NR
400	3	NR	530	218	NR	660	125	NR	790	2	NR	920	0	NR
405	4	NR	535	224	NR	665	106	NR	795	2	NR	925	0	NR
410	6	NR	540	230	NR	670	97	NR	800	2	NR	930	0	NR
415	11	NR	545	236	NR	675	80	NR	805	1	NR	935	0	NR
420	19	NR	550	244	NR	680	69	NR	810	1	NR	940	0	NR
425	34	NR	555	250	NR	685	59	NR	815	1	NR	945	0	NR
430	57	NR	560	260	NR	690	51	NR	820	1	NR	950	0	NR
435	92	NR	565	269	NR	695	44	NR	825	1	NR	955	0	NR
440	151	NR	570	277	NR	700	37	NR	830	1	NR	960	0	NR
445	208	NR	575	286	NR	705	32	NR	835	1	NR	965	0	NR
450	184	NR	580	294	NR	710	27	NR	840	1	NR	970	0	NR
455	122	NR	585	301	NR	715	23	NR	845	0	NR	975	0	NR
460	96	NR	590	307	NR	720	20	NR	850	0	NR	980	0	NR
465	76	NR	595	308	NR	725	17	NR	855	0	NR	985	0	NR
470	59	NR	600	312	NR	730	14	NR	860	0	NR	990	0	NR
475	57	NR	605	315	NR	735	12	NR	865	0	NR	995	0	NR
480	63	NR	610	347	NR	740	10	NR	870	0	NR	1000	0	NR
485	76	NR	615	356	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2512-631-41-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.41**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	96	NR	620	317	NR	750	8	NR	880	0	NR
365	0	NR	495	121	NR	625	324	NR	755	7	NR	885	0	NR
370	0	NR	500	146	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	167	NR	635	572	NR	765	5	NR	895	0	NR
380	0	NR	510	183	NR	640	207	NR	770	4	NR	900	0	NR
385	1	NR	515	196	NR	645	215	NR	775	3	NR	905	0	NR
390	1	NR	520	205	NR	650	175	NR	780	3	NR	910	0	NR
395	2	NR	525	212	NR	655	147	NR	785	3	NR	915	0	NR
400	3	NR	530	218	NR	660	125	NR	790	2	NR	920	0	NR
405	4	NR	535	224	NR	665	106	NR	795	2	NR	925	0	NR
410	6	NR	540	230	NR	670	97	NR	800	2	NR	930	0	NR
415	11	NR	545	236	NR	675	80	NR	805	1	NR	935	0	NR
420	19	NR	550	244	NR	680	69	NR	810	1	NR	940	0	NR
425	34	NR	555	250	NR	685	59	NR	815	1	NR	945	0	NR
430	57	NR	560	260	NR	690	51	NR	820	1	NR	950	0	NR
435	92	NR	565	269	NR	695	44	NR	825	1	NR	955	0	NR
440	151	NR	570	277	NR	700	37	NR	830	1	NR	960	0	NR
445	208	NR	575	286	NR	705	32	NR	835	1	NR	965	0	NR
450	184	NR	580	294	NR	710	27	NR	840	1	NR	970	0	NR
455	122	NR	585	301	NR	715	23	NR	845	0	NR	975	0	NR
460	96	NR	590	307	NR	720	20	NR	850	0	NR	980	0	NR
465	76	NR	595	308	NR	725	17	NR	855	0	NR	985	0	NR
470	59	NR	600	312	NR	730	14	NR	860	0	NR	990	0	NR
475	57	NR	605	315	NR	735	12	NR	865	0	NR	995	0	NR
480	63	NR	610	347	NR	740	10	NR	870	0	NR	1000	0	NR
485	76	NR	615	356	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2512-631-41-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.7**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	96	NR	620	317	NR	750	8	NR	880	0	NR
365	0	NR	495	121	NR	625	324	NR	755	7	NR	885	0	NR
370	0	NR	500	146	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	167	NR	635	572	NR	765	5	NR	895	0	NR
380	0	NR	510	183	NR	640	207	NR	770	4	NR	900	0	NR
385	1	NR	515	196	NR	645	215	NR	775	3	NR	905	0	NR
390	1	NR	520	205	NR	650	175	NR	780	3	NR	910	0	NR
395	2	NR	525	212	NR	655	147	NR	785	3	NR	915	0	NR
400	3	NR	530	218	NR	660	125	NR	790	2	NR	920	0	NR
405	4	NR	535	224	NR	665	106	NR	795	2	NR	925	0	NR
410	6	NR	540	230	NR	670	97	NR	800	2	NR	930	0	NR
415	11	NR	545	236	NR	675	80	NR	805	1	NR	935	0	NR
420	19	NR	550	244	NR	680	69	NR	810	1	NR	940	0	NR
425	34	NR	555	250	NR	685	59	NR	815	1	NR	945	0	NR
430	57	NR	560	260	NR	690	51	NR	820	1	NR	950	0	NR
435	92	NR	565	269	NR	695	44	NR	825	1	NR	955	0	NR
440	151	NR	570	277	NR	700	37	NR	830	1	NR	960	0	NR
445	208	NR	575	286	NR	705	32	NR	835	1	NR	965	0	NR
450	184	NR	580	294	NR	710	27	NR	840	1	NR	970	0	NR
455	122	NR	585	301	NR	715	23	NR	845	0	NR	975	0	NR
460	96	NR	590	307	NR	720	20	NR	850	0	NR	980	0	NR
465	76	NR	595	308	NR	725	17	NR	855	0	NR	985	0	NR
470	59	NR	600	312	NR	730	14	NR	860	0	NR	990	0	NR
475	57	NR	605	315	NR	735	12	NR	865	0	NR	995	0	NR
480	63	NR	610	347	NR	740	10	NR	870	0	NR	1000	0	NR
485	76	NR	615	356	NR	745	9	NR	875	0	NR			


REPORT NUMBER: SP1-2512-631-41-R2

TM-30-18


Summary


R_f = 89.5
R_g = 102
CIE R_a = 91.7
R_9 = 52.5


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2512-631-41-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 87	CES51 = 94	CES76 = 85
CES02 = 63	CES27 = 96	CES52 = 94	CES77 = 88
CES03 = 32	CES28 = 94	CES53 = 89	CES78 = 83
CES04 = 70	CES29 = 83	CES54 = 97	CES79 = 92
CES05 = 50	CES30 = 85	CES55 = 95	CES80 = 92
CES06 = 51	CES31 = 85	CES56 = 89	CES81 = 75
CES07 = 43	CES32 = 80	CES57 = 88	CES82 = 96
CES08 = 42	CES33 = 84	CES58 = 89	CES83 = 93
CES09 = 29	CES34 = 90	CES59 = 98	CES84 = 96
CES10 = 76	CES35 = 94	CES60 = 99	CES85 = 83
CES11 = 58	CES36 = 97	CES61 = 97	CES86 = 77
CES12 = 65	CES37 = 91	CES62 = 94	CES87 = 91
CES13 = 44	CES38 = 90	CES63 = 89	CES88 = 93
CES14 = 74	CES39 = 95	CES64 = 93	CES89 = 81
CES15 = 72	CES40 = 92	CES65 = 89	CES90 = 92
CES16 = 48	CES41 = 91	CES66 = 91	CES91 = 89
CES17 = 50	CES42 = 89	CES67 = 91	CES92 = 79
CES18 = 57	CES43 = 87	CES68 = 93	CES93 = 88
CES19 = 72	CES44 = 99	CES69 = 95	CES94 = 72
CES20 = 67	CES45 = 91	CES70 = 89	CES95 = 86
CES21 = 86	CES46 = 90	CES71 = 89	CES96 = 91
CES22 = 79	CES47 = 83	CES72 = 96	CES97 = 90
CES23 = 92	CES48 = 87	CES73 = 83	CES98 = 89
CES24 = 91	CES49 = 88	CES74 = 92	CES99 = 90
CES25 = 72	CES50 = 94	CES75 = 87	





REPORT NUMBER: SP1-2512-631-41-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2512-631-41-R2

TM-30-18

Measure Comparisons





(END OF REPORT)