Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1527709

Luminaire Tested: 14CGTX-42-B2750-W2A-2700K

Issue Date: 8/26/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1527709
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	8/26/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	14CGTX-42-B2750-W2A-2700K
Description:	1X4 4200 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 2700K CCT WITH FROSTED SMOOTH L
Light Source:	2700K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	3934.6 lumens
Efficiency:	N/A
Efficacy:	95.7 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.26 / 1.38
Luminous Opening:	Rectangular (W 0.82' x L: 3.83' x H: 0')
CIE Type:	Direct

Input Watts (W):	41.1
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527709
CATALOG NUMBER: 14CGTX-42-B2750-W2A-2700K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527709
CATALOG NUMBER: 14CGTX-42-B2750-W2A-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	94	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	79	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	44	39	50	44	39	37
7	64	51	42	35	63	50	41	35	48	41	35	47	40	35	45	39	34	32
8	60	46	37	32	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	41	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	26	37	30	26	37	30	25	36	30	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4566	4566	4566
5°	4569	4549	4576
10°	4567	4553	4570
15°	4550	4543	4564
20°	4532	4524	4539
25°	4510	4503	4514
30°	4492	4476	4476
35°	4457	4440	4436
40°	4428	4405	4392
45°	4382	4362	4324
50°	4337	4310	4284
55°	4271	4254	4206
60°	4190	4163	4115
65°	4126	4061	3972
70°	3991	3931	3811
75°	3863	3757	3665
80°	3635	3537	3399
85°	3289	3132	3054

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
Vertical Angle: 45°
Luminance: 4386 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527709
CATALOG NUMBER: 14CGTX-42-B2750-W2A-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.7	3.2
10°-20°	363.8	9.2
20°-30°	552.3	14.0
30°-40°	667.9	17.0
40°-50°	697.4	17.7
50°-60°	637.8	16.2
60°-70°	497.2	12.6
70°-80°	300.9	7.6
80°-90°	90.6	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1042.8	26.5
0°-40°	1710.8	43.5
0°-60°	3045.9	77.4
0°-90°	3934.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3934.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1338	1338	1338	1338	1338	
5°	1334	1333	1328	1336	1336	127
15°	1288	1289	1286	1292	1292	364
25°	1198	1198	1196	1201	1199	552
35°	1070	1069	1066	1067	1065	670
45°	908	909	904	902	896	700
55°	718	719	715	709	707	642
65°	511	509	503	498	492	504
75°	293	291	285	279	278	309
85°	84	83	80	77	78	95
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527709
CATALOG NUMBER: 14CGTX-42-B2750-W2A-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1338	1338	1338	1338	*1338*
2.5°	*1337*	*1336*	*1332*	*1337*	*1340*
5°	1334	1333	1328	1336	*1336*
7.5°	1327	1327	1324	1328	*1329*
10°	1318	1317	1314	1319	*1319*
12.5°	1303	1304	1301	1307	*1308*
15°	1288	1289	1286	1292	*1292*
17.5°	1270	1271	1267	1273	*1273*
20°	1248	1248	1246	1250	*1250*
22.5°	1225	1225	1223	1226	*1228*
25°	1198	1198	1196	1201	*1199*
27.5°	1170	1170	1167	1171	*1172*
30°	1140	1138	1136	1138	*1136*
32.5°	1107	1105	1102	1104	*1103*
35°	1070	1069	1066	1067	*1065*
37.5°	1032	1031	1029	1029	*1026*
40°	994	993	989	988	*986*
42.5°	950	950	949	945	*943*
45°	908	909	904	902	*896*
47.5°	863	863	859	855	*853*
50°	817	816	812	808	*807*
52.5°	767	770	763	761	*756*
55°	718	719	715	709	*707*
57.5°	668	668	663	658	*654*
60°	614	617	610	605	*603*
62.5°	562	563	558	551	*546*
65°	511	509	503	498	*492*
67.5°	455	455	449	443	*439*
70°	400	399	394	386	*382*
72.5°	347	344	339	332	*331*
75°	293	291	285	279	*278*
77.5°	238	236	231	226	*224*
80°	185	185	180	175	*173*
82.5°	134	132	128	126	*123*
85°	84	83	80	77	*78*
87.5°	37	36	34	32	*32*
90°	0	0	0	0	*0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1527709
CATALOG NUMBER: 14CGTX-42-B2750-W2A-2700K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.26	18.92	17.62	19.23	19.55	17.15	18.81	17.51	19.12	19.43
	3H	19.19	20.70	19.57	21.02	21.38	19.02	20.53	19.40	20.85	21.21
	4H	19.96	21.38	20.36	21.73	22.10	19.76	21.18	20.15	21.52	21.90
	6H	20.56	21.87	20.97	22.24	22.63	20.32	21.64	20.73	22.00	22.39
	8H	20.76	22.02	21.19	22.41	22.81	20.51	21.77	20.93	22.16	22.56
	12H	20.91	22.12	21.34	22.50	22.93	20.64	21.85	21.07	22.23	22.66
4H	2H	17.91	19.33	18.31	19.68	20.06	17.83	19.25	18.22	19.59	19.97
	3H	20.08	21.27	20.48	21.67	22.07	19.93	21.12	20.34	21.52	21.92
	4H	20.98	22.06	21.41	22.48	22.91	20.80	21.88	21.23	22.29	22.73
	6H	21.72	22.67	22.17	23.11	23.56	21.49	22.44	21.95	22.88	23.34
	8H	21.99	22.87	22.44	23.32	23.78	21.74	22.63	22.20	23.07	23.53
	12H	22.19	22.99	22.66	23.46	23.93	21.92	22.72	22.40	23.20	23.67
8H	4H	21.32	22.21	21.78	22.65	23.12	21.16	22.05	21.62	22.49	22.96
	6H	22.20	22.94	22.69	23.43	23.90	22.00	22.74	22.49	23.22	23.70
	8H	22.55	23.22	23.06	23.72	24.21	22.32	22.99	22.83	23.49	23.98
	12H	22.84	23.43	23.34	23.92	24.48	22.59	23.18	23.09	23.67	24.23
12H	4H	21.37	22.17	21.85	22.64	23.11	21.21	22.01	21.69	22.49	22.96
	6H	22.27	22.94	22.78	23.44	23.93	22.08	22.74	22.58	23.25	23.73
	8H	22.68	23.27	23.19	23.76	24.32	22.47	23.06	22.97	23.55	24.10

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2505-441-19-R2

Test Date: 06/13/2025

Luminaire Tested: 24CGTX-55-B2750-W2A-2700K

Data in this report applies to families of products including 24CGTX

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2505-441-19-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-55-B2750-W2A-2700K**
Description:	*THIS IS A REVISION OF REPORT SP1-2504-441-19-R2 TO UPDATE THE CATALOG INFORMATION* 2X4 5500 LUMEN CGTX AT 9.0V

Spectral Parameters

CCT (K):	2790
CIE u':	0.2594
CIE v':	0.5218
Duv:	-0.0026
CIE x:	0.4483
CIE y:	0.4008
CIE z:	0.1509
Peak Wavelength (nm):	630
Dominant Wavelength (nm):	584
Purity:	54.87344
Rf:	93.8
Rg:	102.2

CRI (Ra):	95.1				
R1:	96.3	R9:	82.2		
R2:	97.2	R10:	95.9		
R3:	99.0	R11:	90.1		
R4:	95.3	R12:	90.6		
R5:	95.9	R13:	96.2		
R6:	91.0	R14:	97.9		
R7:	93.9	R15:	99.0		
R8:	92.1				




Test Conditions

Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.0


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2024	6/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2505-441-19-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2790K
CIE x = 0.4483
CIE y = 0.4008
Duv = -0.0026

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2505-441-19-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	81	NR	620	239	NR	750	5	NR	880	0	NR
365	0	NR	495	96	NR	625	249	NR	755	4	NR	885	0	NR
370	0	NR	500	109	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	120	NR	635	641	NR	765	3	NR	895	0	NR
380	0	NR	510	127	NR	640	153	NR	770	3	NR	900	0	NR
385	0	NR	515	131	NR	645	152	NR	775	2	NR	905	0	NR
390	0	NR	520	135	NR	650	132	NR	780	2	NR	910	0	NR
395	0	NR	525	137	NR	655	109	NR	785	2	NR	915	0	NR
400	1	NR	530	140	NR	660	92	NR	790	1	NR	920	0	NR
405	1	NR	535	144	NR	665	76	NR	795	1	NR	925	0	NR
410	2	NR	540	149	NR	670	72	NR	800	1	NR	930	0	NR
415	4	NR	545	154	NR	675	57	NR	805	1	NR	935	0	NR
420	7	NR	550	158	NR	680	49	NR	810	1	NR	940	0	NR
425	13	NR	555	164	NR	685	42	NR	815	1	NR	945	0	NR
430	22	NR	560	170	NR	690	36	NR	820	1	NR	950	0	NR
435	34	NR	565	175	NR	695	31	NR	825	1	NR	955	0	NR
440	55	NR	570	181	NR	700	26	NR	830	0	NR	960	0	NR
445	94	NR	575	186	NR	705	22	NR	835	0	NR	965	0	NR
450	129	NR	580	192	NR	710	19	NR	840	0	NR	970	0	NR
455	99	NR	585	198	NR	715	16	NR	845	0	NR	975	0	NR
460	71	NR	590	203	NR	720	14	NR	850	0	NR	980	0	NR
465	68	NR	595	204	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	210	NR	730	10	NR	860	0	NR	990	0	NR
475	62	NR	605	216	NR	735	8	NR	865	0	NR	995	0	NR
480	64	NR	610	250	NR	740	7	NR	870	0	NR	1000	0	NR
485	71	NR	615	281	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-19-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.41**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	81	NR	620	239	NR	750	5	NR	880	0	NR
365	0	NR	495	96	NR	625	249	NR	755	4	NR	885	0	NR
370	0	NR	500	109	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	120	NR	635	641	NR	765	3	NR	895	0	NR
380	0	NR	510	127	NR	640	153	NR	770	3	NR	900	0	NR
385	0	NR	515	131	NR	645	152	NR	775	2	NR	905	0	NR
390	0	NR	520	135	NR	650	132	NR	780	2	NR	910	0	NR
395	0	NR	525	137	NR	655	109	NR	785	2	NR	915	0	NR
400	1	NR	530	140	NR	660	92	NR	790	1	NR	920	0	NR
405	1	NR	535	144	NR	665	76	NR	795	1	NR	925	0	NR
410	2	NR	540	149	NR	670	72	NR	800	1	NR	930	0	NR
415	4	NR	545	154	NR	675	57	NR	805	1	NR	935	0	NR
420	7	NR	550	158	NR	680	49	NR	810	1	NR	940	0	NR
425	13	NR	555	164	NR	685	42	NR	815	1	NR	945	0	NR
430	22	NR	560	170	NR	690	36	NR	820	1	NR	950	0	NR
435	34	NR	565	175	NR	695	31	NR	825	1	NR	955	0	NR
440	55	NR	570	181	NR	700	26	NR	830	0	NR	960	0	NR
445	94	NR	575	186	NR	705	22	NR	835	0	NR	965	0	NR
450	129	NR	580	192	NR	710	19	NR	840	0	NR	970	0	NR
455	99	NR	585	198	NR	715	16	NR	845	0	NR	975	0	NR
460	71	NR	590	203	NR	720	14	NR	850	0	NR	980	0	NR
465	68	NR	595	204	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	210	NR	730	10	NR	860	0	NR	990	0	NR
475	62	NR	605	216	NR	735	8	NR	865	0	NR	995	0	NR
480	64	NR	610	250	NR	740	7	NR	870	0	NR	1000	0	NR
485	71	NR	615	281	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-19-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.77**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	81	NR	620	239	NR	750	5	NR	880	0	NR
365	0	NR	495	96	NR	625	249	NR	755	4	NR	885	0	NR
370	0	NR	500	109	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	120	NR	635	641	NR	765	3	NR	895	0	NR
380	0	NR	510	127	NR	640	153	NR	770	3	NR	900	0	NR
385	0	NR	515	131	NR	645	152	NR	775	2	NR	905	0	NR
390	0	NR	520	135	NR	650	132	NR	780	2	NR	910	0	NR
395	0	NR	525	137	NR	655	109	NR	785	2	NR	915	0	NR
400	1	NR	530	140	NR	660	92	NR	790	1	NR	920	0	NR
405	1	NR	535	144	NR	665	76	NR	795	1	NR	925	0	NR
410	2	NR	540	149	NR	670	72	NR	800	1	NR	930	0	NR
415	4	NR	545	154	NR	675	57	NR	805	1	NR	935	0	NR
420	7	NR	550	158	NR	680	49	NR	810	1	NR	940	0	NR
425	13	NR	555	164	NR	685	42	NR	815	1	NR	945	0	NR
430	22	NR	560	170	NR	690	36	NR	820	1	NR	950	0	NR
435	34	NR	565	175	NR	695	31	NR	825	1	NR	955	0	NR
440	55	NR	570	181	NR	700	26	NR	830	0	NR	960	0	NR
445	94	NR	575	186	NR	705	22	NR	835	0	NR	965	0	NR
450	129	NR	580	192	NR	710	19	NR	840	0	NR	970	0	NR
455	99	NR	585	198	NR	715	16	NR	845	0	NR	975	0	NR
460	71	NR	590	203	NR	720	14	NR	850	0	NR	980	0	NR
465	68	NR	595	204	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	210	NR	730	10	NR	860	0	NR	990	0	NR
475	62	NR	605	216	NR	735	8	NR	865	0	NR	995	0	NR
480	64	NR	610	250	NR	740	7	NR	870	0	NR	1000	0	NR
485	71	NR	615	281	NR	745	6	NR	875	0	NR			


REPORT NUMBER: SP1-2505-441-19-R2

TM-30-18


Summary


R_f = 93.8
R_g = 102.2
CIE R_a = 95.1
R_9 = 82.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2505-441-19-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 98	CES51 = 94	CES76 = 95
CES02 = 64	CES27 = 94	CES52 = 94	CES77 = 80
CES03 = 32	CES28 = 99	CES53 = 94	CES78 = 92
CES04 = 70	CES29 = 97	CES54 = 95	CES79 = 84
CES05 = 51	CES30 = 99	CES55 = 95	CES80 = 89
CES06 = 51	CES31 = 97	CES56 = 96	CES81 = 66
CES07 = 45	CES32 = 90	CES57 = 97	CES82 = 95
CES08 = 43	CES33 = 97	CES58 = 95	CES83 = 91
CES09 = 29	CES34 = 97	CES59 = 98	CES84 = 98
CES10 = 77	CES35 = 99	CES60 = 96	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 96	CES86 = 79
CES12 = 66	CES37 = 96	CES62 = 91	CES87 = 95
CES13 = 45	CES38 = 95	CES63 = 97	CES88 = 99
CES14 = 74	CES39 = 98	CES64 = 96	CES89 = 85
CES15 = 72	CES40 = 95	CES65 = 98	CES90 = 98
CES16 = 48	CES41 = 94	CES66 = 97	CES91 = 85
CES17 = 50	CES42 = 94	CES67 = 97	CES92 = 83
CES18 = 57	CES43 = 94	CES68 = 96	CES93 = 89
CES19 = 72	CES44 = 99	CES69 = 96	CES94 = 77
CES20 = 68	CES45 = 95	CES70 = 96	CES95 = 90
CES21 = 86	CES46 = 96	CES71 = 95	CES96 = 96
CES22 = 79	CES47 = 83	CES72 = 98	CES97 = 94
CES23 = 92	CES48 = 98	CES73 = 93	CES98 = 97
CES24 = 90	CES49 = 94	CES74 = 86	CES99 = 96
CES25 = 72	CES50 = 94	CES75 = 95	





REPORT NUMBER: SP1-2505-441-19-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2505-441-19-R2

TM-30-18

Measure Comparisons





(END OF REPORT)