Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1527727

Luminaire Tested: 22CGTX-35-B2750-W2A-2700K

Issue Date: 8/26/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1527727
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	8/26/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	22CGTX-35-B2750-W2A-2700K
Description:	2X2 3500 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 2700K CCT WITH FROSTED SMOOTH L
Light Source:	2700K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	3502.3 lumens
Efficiency:	N/A
Efficacy:	107.4 lumens/watt
Spacing Criteria (0/90/45):	1.26 / 1.27 / 1.38
Luminous Opening:	Rectangular (W 1.81' x L: 1.81' x H: 0')
CIE Type:	Direct

Input Watts (W):	32.6
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527727
CATALOG NUMBER: 22CGTX-35-B2750-W2A-2700K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527727
CATALOG NUMBER: 22CGTX-35-B2750-W2A-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	94	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	79	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	44	39	50	44	39	37
7	64	51	42	35	63	50	41	35	48	41	35	47	40	35	45	39	34	32
8	60	46	37	32	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	41	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	26	37	30	25	37	30	25	36	30	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3902	3902	3902
5°	3901	3894	3904
10°	3903	3899	3896
15°	3891	3884	3891
20°	3870	3870	3881
25°	3847	3847	3861
30°	3829	3825	3840
35°	3792	3792	3808
40°	3772	3768	3772
45°	3726	3730	3739
50°	3685	3696	3706
55°	3622	3627	3633
60°	3552	3565	3558
65°	3442	3473	3473
70°	3315	3353	3372
75°	3165	3216	3254
80°	2962	3019	3057
85°	2632	2707	2744

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
Vertical Angle: 45°
Luminance: 3739 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527727
CATALOG NUMBER: 22CGTX-35-B2750-W2A-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.8	3.2
10°-20°	323.5	9.2
20°-30°	491.0	14.0
30°-40°	594.2	17.0
40°-50°	621.2	17.7
50°-60°	567.7	16.2
60°-70°	442.5	12.6
70°-80°	268.1	7.7
80°-90°	81.3	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	927.3	26.5
0°-40°	1521.5	43.4
0°-60°	2710.4	77.4
0°-90°	3502.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3502.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1191	1191	1191	1191	1191	
5°	1186	1184	1184	1188	1187	113
15°	1147	1146	1145	1147	1147	324
25°	1064	1064	1064	1066	1068	491
35°	948	949	948	950	952	595
45°	804	805	805	806	807	621
55°	634	634	635	638	636	566
65°	444	445	448	450	448	440
75°	250	252	254	256	257	265
85°	70	70	72	73	73	80
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527727
CATALOG NUMBER: 22CGTX-35-B2750-W2A-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*1191*	*1191*	*1191*	*1191*	*1191*
2.5°	*1191*	1190	1190	1191	1191
5°	*1186*	1184	1184	1188	1187
7.5°	*1181*	1180	1179	1181	1182
10°	*1173*	1173	1172	1172	1171
12.5°	*1162*	1160	1162	1161	1160
15°	*1147*	1146	1145	1147	1147
17.5°	*1130*	1128	1128	1131	1132
20°	*1110*	1110	1110	1111	1113
22.5°	*1090*	1089	1088	1090	1091
25°	*1064*	1064	1064	1066	1068
27.5°	*1040*	1038	1037	1040	1042
30°	*1012*	1011	1011	1012	1015
32.5°	*984*	982	980	983	985
35°	*948*	949	948	950	952
37.5°	*917*	916	915	916	916
40°	*882*	879	881	882	882
42.5°	*846*	842	844	845	847
45°	*804*	805	805	806	807
47.5°	*763*	765	765	764	767
50°	*723*	722	725	723	727
52.5°	*678*	678	679	682	685
55°	*634*	634	635	638	636
57.5°	*588*	587	588	591	593
60°	*542*	541	544	544	543
62.5°	*495*	494	497	497	498
65°	*444*	445	448	450	448
67.5°	*395*	398	398	400	401
70°	*346*	348	350	352	352
72.5°	*298*	298	300	304	304
75°	*250*	252	254	256	257
77.5°	*204*	203	207	209	211
80°	*157*	159	160	164	162
82.5°	*114*	113	115	118	118
85°	*70*	70	72	73	73
87.5°	*30*	30	32	32	33
90°	*0*	0	0	0	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1527727
CATALOG NUMBER: 22CGTX-35-B2750-W2A-2700K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.63	18.29	16.99	18.60	18.92	16.67	18.33	17.04	18.65	18.96
	3H	18.53	20.03	18.91	20.36	20.72	18.59	20.10	18.97	20.42	20.78
	4H	19.27	20.69	19.67	21.03	21.41	19.35	20.77	19.75	21.12	21.49
	6H	19.84	21.16	20.25	21.52	21.92	19.95	21.27	20.36	21.63	22.02
	8H	20.04	21.30	20.47	21.69	22.09	20.16	21.42	20.58	21.81	22.20
	12H	20.18	21.39	20.61	21.77	22.20	20.30	21.51	20.73	21.89	22.32
4H	2H	17.30	18.72	17.70	19.07	19.44	17.34	18.76	17.74	19.11	19.48
	3H	19.43	20.62	19.84	21.02	21.42	19.48	20.68	19.89	21.07	21.47
	4H	20.30	21.39	20.73	21.80	22.23	20.38	21.46	20.81	21.88	22.31
	6H	21.02	21.97	21.47	22.40	22.86	21.12	22.07	21.57	22.51	22.96
	8H	21.27	22.16	21.73	22.60	23.06	21.38	22.27	21.84	22.72	23.18
	12H	21.46	22.26	21.94	22.73	23.20	21.58	22.38	22.06	22.86	23.33
8H	4H	20.66	21.55	21.12	21.99	22.46	20.73	21.62	21.19	22.06	22.52
	6H	21.51	22.25	22.00	22.74	23.22	21.61	22.35	22.10	22.84	23.31
	8H	21.85	22.51	22.35	23.02	23.50	21.96	22.63	22.47	23.13	23.62
	12H	22.12	22.71	22.62	23.20	23.76	22.25	22.84	22.75	23.32	23.88
12H	4H	20.71	21.51	21.19	21.99	22.46	20.77	21.58	21.25	22.05	22.52
	6H	21.59	22.26	22.10	22.76	23.25	21.68	22.35	22.19	22.86	23.34
	8H	21.99	22.58	22.49	23.07	23.63	22.10	22.69	22.60	23.18	23.74

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2505-441-19-R2

Test Date: 06/13/2025

Luminaire Tested: 24CGTX-55-B2750-W2A-2700K

Data in this report applies to families of products including 24CGTX

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2505-441-19-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-55-B2750-W2A-2700K**
Description:	*THIS IS A REVISION OF REPORT SP1-2504-441-19-R2 TO UPDATE THE CATALOG INFORMATION* 2X4 5500 LUMEN CGTX AT 9.0V

Spectral Parameters

CCT (K):	2790
CIE u':	0.2594
CIE v':	0.5218
Duv:	-0.0026
CIE x:	0.4483
CIE y:	0.4008
CIE z:	0.1509
Peak Wavelength (nm):	630
Dominant Wavelength (nm):	584
Purity:	54.87344
Rf:	93.8
Rg:	102.2

CRI (Ra):	95.1				
R1:	96.3	R9:	82.2		
R2:	97.2	R10:	95.9		
R3:	99.0	R11:	90.1		
R4:	95.3	R12:	90.6		
R5:	95.9	R13:	96.2		
R6:	91.0	R14:	97.9		
R7:	93.9	R15:	99.0		
R8:	92.1				




Test Conditions

Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.0


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2024	6/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2505-441-19-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2790K
CIE x = 0.4483
CIE y = 0.4008
Duv = -0.0026

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2505-441-19-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	81	NR	620	239	NR	750	5	NR	880	0	NR
365	0	NR	495	96	NR	625	249	NR	755	4	NR	885	0	NR
370	0	NR	500	109	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	120	NR	635	641	NR	765	3	NR	895	0	NR
380	0	NR	510	127	NR	640	153	NR	770	3	NR	900	0	NR
385	0	NR	515	131	NR	645	152	NR	775	2	NR	905	0	NR
390	0	NR	520	135	NR	650	132	NR	780	2	NR	910	0	NR
395	0	NR	525	137	NR	655	109	NR	785	2	NR	915	0	NR
400	1	NR	530	140	NR	660	92	NR	790	1	NR	920	0	NR
405	1	NR	535	144	NR	665	76	NR	795	1	NR	925	0	NR
410	2	NR	540	149	NR	670	72	NR	800	1	NR	930	0	NR
415	4	NR	545	154	NR	675	57	NR	805	1	NR	935	0	NR
420	7	NR	550	158	NR	680	49	NR	810	1	NR	940	0	NR
425	13	NR	555	164	NR	685	42	NR	815	1	NR	945	0	NR
430	22	NR	560	170	NR	690	36	NR	820	1	NR	950	0	NR
435	34	NR	565	175	NR	695	31	NR	825	1	NR	955	0	NR
440	55	NR	570	181	NR	700	26	NR	830	0	NR	960	0	NR
445	94	NR	575	186	NR	705	22	NR	835	0	NR	965	0	NR
450	129	NR	580	192	NR	710	19	NR	840	0	NR	970	0	NR
455	99	NR	585	198	NR	715	16	NR	845	0	NR	975	0	NR
460	71	NR	590	203	NR	720	14	NR	850	0	NR	980	0	NR
465	68	NR	595	204	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	210	NR	730	10	NR	860	0	NR	990	0	NR
475	62	NR	605	216	NR	735	8	NR	865	0	NR	995	0	NR
480	64	NR	610	250	NR	740	7	NR	870	0	NR	1000	0	NR
485	71	NR	615	281	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-19-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.41**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	81	NR	620	239	NR	750	5	NR	880	0	NR
365	0	NR	495	96	NR	625	249	NR	755	4	NR	885	0	NR
370	0	NR	500	109	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	120	NR	635	641	NR	765	3	NR	895	0	NR
380	0	NR	510	127	NR	640	153	NR	770	3	NR	900	0	NR
385	0	NR	515	131	NR	645	152	NR	775	2	NR	905	0	NR
390	0	NR	520	135	NR	650	132	NR	780	2	NR	910	0	NR
395	0	NR	525	137	NR	655	109	NR	785	2	NR	915	0	NR
400	1	NR	530	140	NR	660	92	NR	790	1	NR	920	0	NR
405	1	NR	535	144	NR	665	76	NR	795	1	NR	925	0	NR
410	2	NR	540	149	NR	670	72	NR	800	1	NR	930	0	NR
415	4	NR	545	154	NR	675	57	NR	805	1	NR	935	0	NR
420	7	NR	550	158	NR	680	49	NR	810	1	NR	940	0	NR
425	13	NR	555	164	NR	685	42	NR	815	1	NR	945	0	NR
430	22	NR	560	170	NR	690	36	NR	820	1	NR	950	0	NR
435	34	NR	565	175	NR	695	31	NR	825	1	NR	955	0	NR
440	55	NR	570	181	NR	700	26	NR	830	0	NR	960	0	NR
445	94	NR	575	186	NR	705	22	NR	835	0	NR	965	0	NR
450	129	NR	580	192	NR	710	19	NR	840	0	NR	970	0	NR
455	99	NR	585	198	NR	715	16	NR	845	0	NR	975	0	NR
460	71	NR	590	203	NR	720	14	NR	850	0	NR	980	0	NR
465	68	NR	595	204	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	210	NR	730	10	NR	860	0	NR	990	0	NR
475	62	NR	605	216	NR	735	8	NR	865	0	NR	995	0	NR
480	64	NR	610	250	NR	740	7	NR	870	0	NR	1000	0	NR
485	71	NR	615	281	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-19-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.77**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	81	NR	620	239	NR	750	5	NR	880	0	NR
365	0	NR	495	96	NR	625	249	NR	755	4	NR	885	0	NR
370	0	NR	500	109	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	120	NR	635	641	NR	765	3	NR	895	0	NR
380	0	NR	510	127	NR	640	153	NR	770	3	NR	900	0	NR
385	0	NR	515	131	NR	645	152	NR	775	2	NR	905	0	NR
390	0	NR	520	135	NR	650	132	NR	780	2	NR	910	0	NR
395	0	NR	525	137	NR	655	109	NR	785	2	NR	915	0	NR
400	1	NR	530	140	NR	660	92	NR	790	1	NR	920	0	NR
405	1	NR	535	144	NR	665	76	NR	795	1	NR	925	0	NR
410	2	NR	540	149	NR	670	72	NR	800	1	NR	930	0	NR
415	4	NR	545	154	NR	675	57	NR	805	1	NR	935	0	NR
420	7	NR	550	158	NR	680	49	NR	810	1	NR	940	0	NR
425	13	NR	555	164	NR	685	42	NR	815	1	NR	945	0	NR
430	22	NR	560	170	NR	690	36	NR	820	1	NR	950	0	NR
435	34	NR	565	175	NR	695	31	NR	825	1	NR	955	0	NR
440	55	NR	570	181	NR	700	26	NR	830	0	NR	960	0	NR
445	94	NR	575	186	NR	705	22	NR	835	0	NR	965	0	NR
450	129	NR	580	192	NR	710	19	NR	840	0	NR	970	0	NR
455	99	NR	585	198	NR	715	16	NR	845	0	NR	975	0	NR
460	71	NR	590	203	NR	720	14	NR	850	0	NR	980	0	NR
465	68	NR	595	204	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	210	NR	730	10	NR	860	0	NR	990	0	NR
475	62	NR	605	216	NR	735	8	NR	865	0	NR	995	0	NR
480	64	NR	610	250	NR	740	7	NR	870	0	NR	1000	0	NR
485	71	NR	615	281	NR	745	6	NR	875	0	NR			


REPORT NUMBER: SP1-2505-441-19-R2

TM-30-18


Summary


R_f = 93.8
R_g = 102.2
CIE R_a = 95.1
R_9 = 82.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2505-441-19-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 98	CES51 = 94	CES76 = 95
CES02 = 64	CES27 = 94	CES52 = 94	CES77 = 80
CES03 = 32	CES28 = 99	CES53 = 94	CES78 = 92
CES04 = 70	CES29 = 97	CES54 = 95	CES79 = 84
CES05 = 51	CES30 = 99	CES55 = 95	CES80 = 89
CES06 = 51	CES31 = 97	CES56 = 96	CES81 = 66
CES07 = 45	CES32 = 90	CES57 = 97	CES82 = 95
CES08 = 43	CES33 = 97	CES58 = 95	CES83 = 91
CES09 = 29	CES34 = 97	CES59 = 98	CES84 = 98
CES10 = 77	CES35 = 99	CES60 = 96	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 96	CES86 = 79
CES12 = 66	CES37 = 96	CES62 = 91	CES87 = 95
CES13 = 45	CES38 = 95	CES63 = 97	CES88 = 99
CES14 = 74	CES39 = 98	CES64 = 96	CES89 = 85
CES15 = 72	CES40 = 95	CES65 = 98	CES90 = 98
CES16 = 48	CES41 = 94	CES66 = 97	CES91 = 85
CES17 = 50	CES42 = 94	CES67 = 97	CES92 = 83
CES18 = 57	CES43 = 94	CES68 = 96	CES93 = 89
CES19 = 72	CES44 = 99	CES69 = 96	CES94 = 77
CES20 = 68	CES45 = 95	CES70 = 96	CES95 = 90
CES21 = 86	CES46 = 96	CES71 = 95	CES96 = 96
CES22 = 79	CES47 = 83	CES72 = 98	CES97 = 94
CES23 = 92	CES48 = 98	CES73 = 93	CES98 = 97
CES24 = 90	CES49 = 94	CES74 = 86	CES99 = 96
CES25 = 72	CES50 = 94	CES75 = 95	





REPORT NUMBER: SP1-2505-441-19-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2505-441-19-R2

TM-30-18

Measure Comparisons





(END OF REPORT)