Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1527757

Luminaire Tested: 24CGTX-35-B2750-W2A-2700K

Issue Date: 8/26/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


Test Information

Test Method:	LM-79-2019
Report Number:	P1527757
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	8/26/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	24CGTX-35-B2750-W2A-2700K
Description:	2X4 3500 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 2700K CCT WITH FROSTED SMOOTH L
Light Source:	2700K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	3411.4 lumens
Efficiency:	N/A
Efficacy:	114.9 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.28 / 1.39
Luminous Opening:	Rectangular (W 1.81' x L: 3.83' x H: 0')
CIE Type:	Direct

Input Watts (W):	29.7
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527757
CATALOG NUMBER: 24CGTX-35-B2750-W2A-2700K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527757
CATALOG NUMBER: 24CGTX-35-B2750-W2A-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	68
3	89	79	70	63	87	77	69	63	74	67	62	71	65	61	69	64	60	57
4	82	69	60	54	79	68	60	53	66	58	52	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	39	51	44	39	50	44	39	37
7	64	50	42	35	62	50	41	35	48	40	35	47	40	35	45	39	34	32
8	60	46	37	31	58	45	37	31	44	36	31	43	36	31	41	35	31	29
9	56	42	34	28	54	42	34	28	40	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	26	37	30	25	36	30	25	36	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1782	1782	1782
5°	1788	1779	1778
10°	1773	1771	1782
15°	1785	1774	1785
20°	1772	1757	1799
25°	1776	1761	1774
30°	1773	1760	1748
35°	1757	1748	1746
40°	1731	1725	1719
45°	1722	1713	1716
50°	1714	1694	1690
55°	1691	1669	1658
60°	1670	1648	1630
65°	1624	1617	1591
70°	1576	1558	1522
75°	1514	1496	1461
80°	1427	1401	1374
85°	1315	1262	1227

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 47.5°
Luminance: 1724 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527757
CATALOG NUMBER: 24CGTX-35-B2750-W2A-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.8	3.2
10°-20°	312.8	9.2
20°-30°	476.3	14.0
30°-40°	578.0	16.9
40°-50°	603.9	17.7
50°-60°	553.8	16.2
60°-70°	433.3	12.7
70°-80°	263.3	7.7
80°-90°	81.3	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	897.8	26.3
0°-40°	1475.8	43.3
0°-60°	2633.4	77.2
0°-90°	3411.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3411.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1150	1150	1150	1150	1150	
5°	1150	1152	1144	1145	1143	109
15°	1113	1108	1106	1106	1113	313
25°	1039	1033	1030	1030	1038	478
35°	929	927	924	918	923	581
45°	786	784	782	779	783	608
55°	626	621	618	617	614	559
65°	443	443	441	435	434	437
75°	253	253	250	246	244	266
85°	74	73	71	70	69	83
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527757
CATALOG NUMBER: 24CGTX-35-B2750-W2A-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*1150*	1150	1150	1150	1150
2.5°	*1154*	*1154*	*1146*	*1144*	*1151*
5°	*1150*	1152	1144	1145	1143
7.5°	*1140*	1138	1134	1133	1142
10°	*1127*	1135	1126	1124	1133
12.5°	*1124*	1125	1124	1118	1125
15°	*1113*	1108	1106	1106	1113
17.5°	*1086*	1095	1093	1090	1095
20°	*1075*	1080	1066	1072	1091
22.5°	*1053*	1056	1055	1063	1054
25°	*1039*	1033	1030	1030	1038
27.5°	*1012*	1005	1008	1010	1010
30°	*991*	980	984	981	977
32.5°	*956*	959	954	951	960
35°	*929*	927	924	918	923
37.5°	*899*	895	894	889	889
40°	*856*	856	853	853	850
42.5°	*825*	822	821	815	828
45°	*786*	784	782	779	783
47.5°	*752*	745	746	742	741
50°	*711*	703	703	703	701
52.5°	*666*	667	662	659	660
55°	*626*	621	618	617	614
57.5°	*580*	577	579	573	573
60°	*539*	534	532	526	526
62.5°	*489*	489	484	480	478
65°	*443*	443	441	435	434
67.5°	*392*	394	391	386	388
70°	*348*	346	344	341	336
72.5°	*297*	299	296	292	291
75°	*253*	253	250	246	244
77.5°	*205*	207	203	201	198
80°	*160*	160	157	156	154
82.5°	*117*	116	115	112	113
85°	*74*	73	71	70	69
87.5°	*35*	33	35	35	34
90°	*0*	0	0	0	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1527757
CATALOG NUMBER: 24CGTX-35-B2750-W2A-2700K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.00	15.66	14.36	15.98	16.29	13.94	15.60	14.30	15.92	16.23
	3H	15.94	17.44	16.31	17.77	18.13	15.84	17.35	16.22	17.68	18.04
	4H	16.70	18.12	17.10	18.47	18.84	16.58	18.01	16.98	18.35	18.73
	6H	17.30	18.62	17.71	18.98	19.37	17.16	18.48	17.57	18.85	19.24
	8H	17.51	18.77	17.93	19.16	19.56	17.37	18.63	17.79	19.02	19.41
	12H	17.66	18.87	18.09	19.25	19.68	17.51	18.72	17.94	19.10	19.53
4H	2H	14.67	16.10	15.07	16.44	16.82	14.63	16.05	15.02	16.40	16.77
	3H	16.83	18.03	17.24	18.43	18.83	16.75	17.95	17.16	18.35	18.75
	4H	17.74	18.82	18.17	19.24	19.67	17.63	18.72	18.06	19.13	19.56
	6H	18.48	19.43	18.93	19.87	20.32	18.35	19.30	18.80	19.74	20.19
	8H	18.74	19.64	19.20	20.08	20.54	18.60	19.50	19.06	19.94	20.40
	12H	18.95	19.75	19.43	20.23	20.70	18.80	19.60	19.28	20.08	20.54
8H	4H	18.09	18.98	18.55	19.42	19.89	18.00	18.89	18.45	19.33	19.79
	6H	18.97	19.71	19.46	20.20	20.67	18.85	19.59	19.34	20.08	20.56
	8H	19.32	19.99	19.83	20.50	20.98	19.19	19.86	19.70	20.37	20.85
	12H	19.62	20.21	20.12	20.70	21.26	19.47	20.06	19.98	20.55	21.11
12H	4H	18.14	18.94	18.61	19.41	19.88	18.05	18.85	18.52	19.32	19.79
	6H	19.04	19.71	19.55	20.22	20.70	18.93	19.60	19.44	20.10	20.59
	8H	19.46	20.05	19.97	20.54	21.10	19.34	19.93	19.84	20.42	20.98

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2505-441-19-R2

Test Date: 06/13/2025

Luminaire Tested: 24CGTX-55-B2750-W2A-2700K

Data in this report applies to families of products including 24CGTX

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2505-441-19-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-55-B2750-W2A-2700K**
Description:	*THIS IS A REVISION OF REPORT SP1-2504-441-19-R2 TO UPDATE THE CATALOG INFORMATION* 2X4 5500 LUMEN CGTX AT 9.0V

Spectral Parameters

CCT (K):	2790
CIE u':	0.2594
CIE v':	0.5218
Duv:	-0.0026
CIE x:	0.4483
CIE y:	0.4008
CIE z:	0.1509
Peak Wavelength (nm):	630
Dominant Wavelength (nm):	584
Purity:	54.87344
Rf:	93.8
Rg:	102.2

CRI (Ra):	95.1				
R1:	96.3	R9:	82.2		
R2:	97.2	R10:	95.9		
R3:	99.0	R11:	90.1		
R4:	95.3	R12:	90.6		
R5:	95.9	R13:	96.2		
R6:	91.0	R14:	97.9		
R7:	93.9	R15:	99.0		
R8:	92.1				




Test Conditions

Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.0


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2024	6/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2505-441-19-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2790K
CIE x = 0.4483
CIE y = 0.4008
Duv = -0.0026

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2505-441-19-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	81	NR	620	239	NR	750	5	NR	880	0	NR
365	0	NR	495	96	NR	625	249	NR	755	4	NR	885	0	NR
370	0	NR	500	109	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	120	NR	635	641	NR	765	3	NR	895	0	NR
380	0	NR	510	127	NR	640	153	NR	770	3	NR	900	0	NR
385	0	NR	515	131	NR	645	152	NR	775	2	NR	905	0	NR
390	0	NR	520	135	NR	650	132	NR	780	2	NR	910	0	NR
395	0	NR	525	137	NR	655	109	NR	785	2	NR	915	0	NR
400	1	NR	530	140	NR	660	92	NR	790	1	NR	920	0	NR
405	1	NR	535	144	NR	665	76	NR	795	1	NR	925	0	NR
410	2	NR	540	149	NR	670	72	NR	800	1	NR	930	0	NR
415	4	NR	545	154	NR	675	57	NR	805	1	NR	935	0	NR
420	7	NR	550	158	NR	680	49	NR	810	1	NR	940	0	NR
425	13	NR	555	164	NR	685	42	NR	815	1	NR	945	0	NR
430	22	NR	560	170	NR	690	36	NR	820	1	NR	950	0	NR
435	34	NR	565	175	NR	695	31	NR	825	1	NR	955	0	NR
440	55	NR	570	181	NR	700	26	NR	830	0	NR	960	0	NR
445	94	NR	575	186	NR	705	22	NR	835	0	NR	965	0	NR
450	129	NR	580	192	NR	710	19	NR	840	0	NR	970	0	NR
455	99	NR	585	198	NR	715	16	NR	845	0	NR	975	0	NR
460	71	NR	590	203	NR	720	14	NR	850	0	NR	980	0	NR
465	68	NR	595	204	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	210	NR	730	10	NR	860	0	NR	990	0	NR
475	62	NR	605	216	NR	735	8	NR	865	0	NR	995	0	NR
480	64	NR	610	250	NR	740	7	NR	870	0	NR	1000	0	NR
485	71	NR	615	281	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-19-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.41**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	81	NR	620	239	NR	750	5	NR	880	0	NR
365	0	NR	495	96	NR	625	249	NR	755	4	NR	885	0	NR
370	0	NR	500	109	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	120	NR	635	641	NR	765	3	NR	895	0	NR
380	0	NR	510	127	NR	640	153	NR	770	3	NR	900	0	NR
385	0	NR	515	131	NR	645	152	NR	775	2	NR	905	0	NR
390	0	NR	520	135	NR	650	132	NR	780	2	NR	910	0	NR
395	0	NR	525	137	NR	655	109	NR	785	2	NR	915	0	NR
400	1	NR	530	140	NR	660	92	NR	790	1	NR	920	0	NR
405	1	NR	535	144	NR	665	76	NR	795	1	NR	925	0	NR
410	2	NR	540	149	NR	670	72	NR	800	1	NR	930	0	NR
415	4	NR	545	154	NR	675	57	NR	805	1	NR	935	0	NR
420	7	NR	550	158	NR	680	49	NR	810	1	NR	940	0	NR
425	13	NR	555	164	NR	685	42	NR	815	1	NR	945	0	NR
430	22	NR	560	170	NR	690	36	NR	820	1	NR	950	0	NR
435	34	NR	565	175	NR	695	31	NR	825	1	NR	955	0	NR
440	55	NR	570	181	NR	700	26	NR	830	0	NR	960	0	NR
445	94	NR	575	186	NR	705	22	NR	835	0	NR	965	0	NR
450	129	NR	580	192	NR	710	19	NR	840	0	NR	970	0	NR
455	99	NR	585	198	NR	715	16	NR	845	0	NR	975	0	NR
460	71	NR	590	203	NR	720	14	NR	850	0	NR	980	0	NR
465	68	NR	595	204	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	210	NR	730	10	NR	860	0	NR	990	0	NR
475	62	NR	605	216	NR	735	8	NR	865	0	NR	995	0	NR
480	64	NR	610	250	NR	740	7	NR	870	0	NR	1000	0	NR
485	71	NR	615	281	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-19-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.77**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	81	NR	620	239	NR	750	5	NR	880	0	NR
365	0	NR	495	96	NR	625	249	NR	755	4	NR	885	0	NR
370	0	NR	500	109	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	120	NR	635	641	NR	765	3	NR	895	0	NR
380	0	NR	510	127	NR	640	153	NR	770	3	NR	900	0	NR
385	0	NR	515	131	NR	645	152	NR	775	2	NR	905	0	NR
390	0	NR	520	135	NR	650	132	NR	780	2	NR	910	0	NR
395	0	NR	525	137	NR	655	109	NR	785	2	NR	915	0	NR
400	1	NR	530	140	NR	660	92	NR	790	1	NR	920	0	NR
405	1	NR	535	144	NR	665	76	NR	795	1	NR	925	0	NR
410	2	NR	540	149	NR	670	72	NR	800	1	NR	930	0	NR
415	4	NR	545	154	NR	675	57	NR	805	1	NR	935	0	NR
420	7	NR	550	158	NR	680	49	NR	810	1	NR	940	0	NR
425	13	NR	555	164	NR	685	42	NR	815	1	NR	945	0	NR
430	22	NR	560	170	NR	690	36	NR	820	1	NR	950	0	NR
435	34	NR	565	175	NR	695	31	NR	825	1	NR	955	0	NR
440	55	NR	570	181	NR	700	26	NR	830	0	NR	960	0	NR
445	94	NR	575	186	NR	705	22	NR	835	0	NR	965	0	NR
450	129	NR	580	192	NR	710	19	NR	840	0	NR	970	0	NR
455	99	NR	585	198	NR	715	16	NR	845	0	NR	975	0	NR
460	71	NR	590	203	NR	720	14	NR	850	0	NR	980	0	NR
465	68	NR	595	204	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	210	NR	730	10	NR	860	0	NR	990	0	NR
475	62	NR	605	216	NR	735	8	NR	865	0	NR	995	0	NR
480	64	NR	610	250	NR	740	7	NR	870	0	NR	1000	0	NR
485	71	NR	615	281	NR	745	6	NR	875	0	NR			


REPORT NUMBER: SP1-2505-441-19-R2

TM-30-18


Summary


R_f = 93.8
R_g = 102.2
CIE R_a = 95.1
R_9 = 82.2


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2505-441-19-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 98	CES51 = 94	CES76 = 95
CES02 = 64	CES27 = 94	CES52 = 94	CES77 = 80
CES03 = 32	CES28 = 99	CES53 = 94	CES78 = 92
CES04 = 70	CES29 = 97	CES54 = 95	CES79 = 84
CES05 = 51	CES30 = 99	CES55 = 95	CES80 = 89
CES06 = 51	CES31 = 97	CES56 = 96	CES81 = 66
CES07 = 45	CES32 = 90	CES57 = 97	CES82 = 95
CES08 = 43	CES33 = 97	CES58 = 95	CES83 = 91
CES09 = 29	CES34 = 97	CES59 = 98	CES84 = 98
CES10 = 77	CES35 = 99	CES60 = 96	CES85 = 80
CES11 = 59	CES36 = 89	CES61 = 96	CES86 = 79
CES12 = 66	CES37 = 96	CES62 = 91	CES87 = 95
CES13 = 45	CES38 = 95	CES63 = 97	CES88 = 99
CES14 = 74	CES39 = 98	CES64 = 96	CES89 = 85
CES15 = 72	CES40 = 95	CES65 = 98	CES90 = 98
CES16 = 48	CES41 = 94	CES66 = 97	CES91 = 85
CES17 = 50	CES42 = 94	CES67 = 97	CES92 = 83
CES18 = 57	CES43 = 94	CES68 = 96	CES93 = 89
CES19 = 72	CES44 = 99	CES69 = 96	CES94 = 77
CES20 = 68	CES45 = 95	CES70 = 96	CES95 = 90
CES21 = 86	CES46 = 96	CES71 = 95	CES96 = 96
CES22 = 79	CES47 = 83	CES72 = 98	CES97 = 94
CES23 = 92	CES48 = 98	CES73 = 93	CES98 = 97
CES24 = 90	CES49 = 94	CES74 = 86	CES99 = 96
CES25 = 72	CES50 = 94	CES75 = 95	





REPORT NUMBER: SP1-2505-441-19-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2505-441-19-R2

TM-30-18

Measure Comparisons





(END OF REPORT)