Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1527782

Luminaire Tested: 24CGTX-65-B2750-W2A2-3000K

Issue Date: 8/26/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report


Test Information

Test Method:	LM-79-2019
Report Number:	P1527782
	TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G3-2510-581-40)
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	8/26/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	24CGTX-65-B2750-W2A2-3000K
Description:	2X4 6500 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 3000K CCT WITH FROSTED SMOOTH L
Light Source:	3000K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	6088.3 lumens
Efficiency:	N/A
Efficacy:	108.7 lumens/watt
Spacing Criteria (0/90/45):	1.28 / 1.28 / 1.4
Luminous Opening:	Rectangular (W 2' x L: 4' x H: 0')
CIE Type:	Direct

Input Watts (W):	56
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527782
CATALOG NUMBER: 24CGTX-65-B2750-W2A2-3000K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527782
CATALOG NUMBER: 24CGTX-65-B2750-W2A2-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	97	93	96	93	90	92	90	87	89	87	84	82
2	98	89	82	76	95	87	81	75	84	78	73	80	76	72	77	74	70	68
3	89	78	70	63	86	76	69	62	73	67	61	71	65	60	68	63	59	57
4	81	69	60	53	79	68	59	53	65	58	52	63	56	51	60	55	50	48
5	75	61	52	45	73	60	52	45	58	50	45	56	49	44	54	48	44	41
6	69	55	46	39	67	54	46	39	52	45	39	51	44	39	49	43	38	36
7	64	50	41	35	62	49	41	35	48	40	34	46	39	34	45	39	34	32
8	59	46	37	31	58	45	37	31	44	36	31	42	35	30	41	35	30	28
9	55	42	33	28	54	41	33	28	40	33	28	39	32	27	38	32	27	25
10	52	39	30	25	51	38	30	25	37	30	25	36	29	25	35	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2676	2676	2676
5°	2690	2681	2686
10°	2693	2683	2691
15°	2695	2684	2689
20°	2693	2683	2688
25°	2689	2679	2689
30°	2680	2673	2676
35°	2671	2661	2668
40°	2654	2648	2645
45°	2654	2633	2635
50°	2636	2619	2611
55°	2609	2597	2592
60°	2580	2575	2553
65°	2558	2529	2517
70°	2503	2467	2444
75°	2474	2422	2396
80°	2407	2376	2321
85°	2397	2336	2351

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
Vertical Angle: 87.5°
Luminance: 2813 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527782
CATALOG NUMBER: 24CGTX-65-B2750-W2A2-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	3.1
10°-20°	544.6	8.9
20°-30°	832.6	13.7
30°-40°	1014.9	16.7
40°-50°	1070.0	17.6
50°-60°	990.3	16.3
60°-70°	785.6	12.9
70°-80°	492.9	8.1
80°-90°	168.4	2.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1566.1	25.7
0°-40°	2581.0	42.4
0°-60°	4641.3	76.2
0°-90°	6088.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6088.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1989	1989	1989	1989	1989	
5°	1992	1987	1985	1985	1989	190
15°	1935	1929	1927	1926	1931	546
25°	1812	1806	1804	1806	1812	835
35°	1626	1623	1620	1620	1624	1017
45°	1395	1389	1384	1385	1385	1074
55°	1112	1111	1107	1103	1105	995
65°	804	798	794	790	790	792
75°	476	473	466	463	461	500
85°	155	153	151	151	152	171
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1527782
CATALOG NUMBER: 24CGTX-65-B2750-W2A2-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*1988.9*	1988.9	1988.9	1988.9	1988.9
2.5°	*1995.9*	*1989.9*	*1988.9*	*1985.9*	*1990.9*
5°	*1991.9*	1986.9	1984.9	1984.9	1988.9
7.5°	*1985.9*	1979.8	1976.8	1974.8	1983.9
10°	*1970.8*	1966.8	1963.8	1964.8	1969.8
12.5°	*1953.8*	1948.8	1947.8	1948.8	1949.8
15°	*1934.8*	1928.7	1926.7	1925.7	1930.7
17.5°	*1909.7*	1904.7	1902.7	1903.7	1908.7
20°	*1880.7*	1873.6	1873.6	1871.6	1877.6
22.5°	*1848.6*	1841.6	1839.6	1840.6	1843.6
25°	*1811.5*	1806.5	1804.5	1805.5	1811.5
27.5°	*1771.4*	1765.4	1766.4	1761.4	1768.4
30°	*1725.3*	1720.3	1720.3	1721.3	1722.3
32.5°	*1674.2*	1673.2	1673.2	1671.2	1673.2
35°	*1626.2*	1623.2	1620.1	1620.1	1624.2
37.5°	*1574.1*	1568.0	1566.0	1566.0	1569.0
40°	*1510.9*	1511.9	1507.9	1510.9	1505.9
42.5°	*1454.8*	1452.8	1449.8	1449.8	1447.8
45°	*1394.7*	1388.7	1383.7	1384.7	1384.7
47.5°	*1325.6*	1325.6	1319.6	1318.6	1320.6
50°	*1259.4*	1256.4	1251.4	1250.4	1247.4
52.5°	*1188.3*	1185.3	1181.3	1179.3	1181.3
55°	*1112.2*	1111.2	1107.1	1103.1	1105.1
57.5°	*1037.0*	1035.0	1035.0	1028.0	1029.0
60°	*958.9*	957.9	956.9	949.8	948.8
62.5°	*880.7*	879.7	875.7	871.7	871.7
65°	*803.6*	797.5	794.5	789.5	790.5
67.5°	*718.4*	715.4	711.4	708.4	707.4
70°	*636.2*	634.2	627.2	625.2	621.2
72.5°	*557.1*	554.1	547.1	542.1	537.0
75°	*475.9*	472.9	465.9	462.9	460.9
77.5°	*389.8*	390.8	386.8	381.7	380.7
80°	*310.6*	308.6	306.6	300.6	299.6
82.5°	*232.5*	228.4	227.4	226.4	223.4
85°	*155.3*	153.3	151.3	151.3	152.3
87.5°	*86.2*	82.2	85.2	89.2	91.2
90°	*0.0*	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1527782
CATALOG NUMBER: 24CGTX-65-B2750-W2A2-3000K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.54	17.21	15.90	17.53	17.84	15.49	17.16	15.85	17.48	17.79
	3H	17.53	19.05	17.91	19.38	19.74	17.46	18.98	17.83	19.30	19.66
	4H	18.35	19.79	18.75	20.13	20.51	18.25	19.68	18.64	20.03	20.40
	6H	19.01	20.34	19.42	20.70	21.09	18.89	20.22	19.30	20.59	20.98
	8H	19.25	20.53	19.68	20.92	21.32	19.12	20.40	19.55	20.79	21.19
	12H	19.44	20.67	19.87	21.05	21.48	19.31	20.54	19.74	20.92	21.35
4H	2H	16.22	17.65	16.62	18.00	18.38	16.18	17.62	16.58	17.96	18.34
	3H	18.44	19.66	18.85	20.05	20.45	18.38	19.59	18.79	19.99	20.39
	4H	19.41	20.51	19.84	20.92	21.35	19.31	20.41	19.74	20.82	21.26
	6H	20.21	21.18	20.66	21.62	22.07	20.10	21.06	20.55	21.50	21.96
	8H	20.52	21.43	20.98	21.87	22.33	20.40	21.30	20.85	21.74	22.21
	12H	20.77	21.59	21.25	22.06	22.53	20.65	21.46	21.13	21.94	22.41
8H	4H	19.78	20.69	20.24	21.13	21.59	19.70	20.60	20.16	21.05	21.51
	6H	20.74	21.50	21.23	21.98	22.46	20.64	21.39	21.13	21.88	22.35
	8H	21.14	21.82	21.65	22.33	22.81	21.03	21.71	21.54	22.22	22.70
	12H	21.50	22.10	22.00	22.59	23.15	21.38	21.99	21.89	22.48	23.04
12H	4H	19.84	20.65	20.31	21.13	21.60	19.76	20.57	20.24	21.05	21.52
	6H	20.83	21.51	21.33	22.01	22.50	20.73	21.41	21.24	21.92	22.40
	8H	21.30	21.90	21.81	22.39	22.95	21.20	21.80	21.70	22.29	22.85

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2505-441-15-R2

Test Date: 06/12/2025

Luminaire Tested: 24CGTX-55-B2750-W2A-3000K

Data in this report applies to families of products including 24CGTX

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2505-441-15-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-55-B2750-W2A-3000K**
Description:	*THIS IS A REVISION OF REPORT SP1-2504-441-15-R2 TO UPDATE THE CATALOG INFORMATION* 2X4 5500 LUMEN CGTX AT 7.0V

Spectral Parameters

CCT (K):	3218
CIE u':	0.2471
CIE v':	0.5047
Duv:	-0.0090
CIE x:	0.4113
CIE y:	0.3733
CIE z:	0.2154
Peak Wavelength (nm):	630
Dominant Wavelength (nm):	586
Purity:	35.5
Rf:	92.4
Rg:	100.9

CRI (Ra):	92.1				
R1:	94.2	R9:	87.4		
R2:	92.2	R10:	85.6		
R3:	93.0	R11:	94.6		
R4:	97.8	R12:	78.5		
R5:	93.2	R13:	92.9		
R6:	85.3	R14:	97.6		
R7:	90.0	R15:	96.4		
R8:	91.4				




Test Conditions

Stabilization Time:	21M
Operation Time:	1H 21M
Sphere Temperature (°C):	25.0


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2024	6/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2505-441-15-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3218K
CIE x = 0.4113
CIE y = 0.3733
Duv = -0.0090

Point lies outside the range

REPORT NUMBER: SP1-2505-441-15-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	133	NR	620	266	NR	750	6	NR	880	0	NR
365	0	NR	495	136	NR	625	273	NR	755	5	NR	885	0	NR
370	0	NR	500	142	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	149	NR	635	627	NR	765	4	NR	895	0	NR
380	0	NR	510	155	NR	640	172	NR	770	3	NR	900	0	NR
385	0	NR	515	159	NR	645	169	NR	775	3	NR	905	0	NR
390	0	NR	520	162	NR	650	146	NR	780	2	NR	910	0	NR
395	1	NR	525	165	NR	655	122	NR	785	2	NR	915	0	NR
400	2	NR	530	169	NR	660	103	NR	790	2	NR	920	0	NR
405	2	NR	535	172	NR	665	86	NR	795	1	NR	925	0	NR
410	4	NR	540	177	NR	670	80	NR	800	1	NR	930	0	NR
415	6	NR	545	183	NR	675	65	NR	805	1	NR	935	0	NR
420	11	NR	550	189	NR	680	55	NR	810	1	NR	940	0	NR
425	20	NR	555	196	NR	685	47	NR	815	1	NR	945	0	NR
430	35	NR	560	203	NR	690	40	NR	820	1	NR	950	0	NR
435	57	NR	565	211	NR	695	35	NR	825	1	NR	955	0	NR
440	94	NR	570	219	NR	700	29	NR	830	1	NR	960	0	NR
445	163	NR	575	226	NR	705	25	NR	835	0	NR	965	0	NR
450	218	NR	580	233	NR	710	21	NR	840	0	NR	970	0	NR
455	167	NR	585	240	NR	715	18	NR	845	0	NR	975	0	NR
460	129	NR	590	244	NR	720	15	NR	850	0	NR	980	0	NR
465	143	NR	595	245	NR	725	13	NR	855	0	NR	985	0	NR
470	169	NR	600	249	NR	730	11	NR	860	0	NR	990	0	NR
475	177	NR	605	252	NR	735	9	NR	865	0	NR	995	0	NR
480	156	NR	610	282	NR	740	8	NR	870	0	NR	1000	0	NR
485	137	NR	615	306	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-15-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.68**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	133	NR	620	266	NR	750	6	NR	880	0	NR
365	0	NR	495	136	NR	625	273	NR	755	5	NR	885	0	NR
370	0	NR	500	142	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	149	NR	635	627	NR	765	4	NR	895	0	NR
380	0	NR	510	155	NR	640	172	NR	770	3	NR	900	0	NR
385	0	NR	515	159	NR	645	169	NR	775	3	NR	905	0	NR
390	0	NR	520	162	NR	650	146	NR	780	2	NR	910	0	NR
395	1	NR	525	165	NR	655	122	NR	785	2	NR	915	0	NR
400	2	NR	530	169	NR	660	103	NR	790	2	NR	920	0	NR
405	2	NR	535	172	NR	665	86	NR	795	1	NR	925	0	NR
410	4	NR	540	177	NR	670	80	NR	800	1	NR	930	0	NR
415	6	NR	545	183	NR	675	65	NR	805	1	NR	935	0	NR
420	11	NR	550	189	NR	680	55	NR	810	1	NR	940	0	NR
425	20	NR	555	196	NR	685	47	NR	815	1	NR	945	0	NR
430	35	NR	560	203	NR	690	40	NR	820	1	NR	950	0	NR
435	57	NR	565	211	NR	695	35	NR	825	1	NR	955	0	NR
440	94	NR	570	219	NR	700	29	NR	830	1	NR	960	0	NR
445	163	NR	575	226	NR	705	25	NR	835	0	NR	965	0	NR
450	218	NR	580	233	NR	710	21	NR	840	0	NR	970	0	NR
455	167	NR	585	240	NR	715	18	NR	845	0	NR	975	0	NR
460	129	NR	590	244	NR	720	15	NR	850	0	NR	980	0	NR
465	143	NR	595	245	NR	725	13	NR	855	0	NR	985	0	NR
470	169	NR	600	249	NR	730	11	NR	860	0	NR	990	0	NR
475	177	NR	605	252	NR	735	9	NR	865	0	NR	995	0	NR
480	156	NR	610	282	NR	740	8	NR	870	0	NR	1000	0	NR
485	137	NR	615	306	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-15-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.56**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	133	NR	620	266	NR	750	6	NR	880	0	NR
365	0	NR	495	136	NR	625	273	NR	755	5	NR	885	0	NR
370	0	NR	500	142	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	149	NR	635	627	NR	765	4	NR	895	0	NR
380	0	NR	510	155	NR	640	172	NR	770	3	NR	900	0	NR
385	0	NR	515	159	NR	645	169	NR	775	3	NR	905	0	NR
390	0	NR	520	162	NR	650	146	NR	780	2	NR	910	0	NR
395	1	NR	525	165	NR	655	122	NR	785	2	NR	915	0	NR
400	2	NR	530	169	NR	660	103	NR	790	2	NR	920	0	NR
405	2	NR	535	172	NR	665	86	NR	795	1	NR	925	0	NR
410	4	NR	540	177	NR	670	80	NR	800	1	NR	930	0	NR
415	6	NR	545	183	NR	675	65	NR	805	1	NR	935	0	NR
420	11	NR	550	189	NR	680	55	NR	810	1	NR	940	0	NR
425	20	NR	555	196	NR	685	47	NR	815	1	NR	945	0	NR
430	35	NR	560	203	NR	690	40	NR	820	1	NR	950	0	NR
435	57	NR	565	211	NR	695	35	NR	825	1	NR	955	0	NR
440	94	NR	570	219	NR	700	29	NR	830	1	NR	960	0	NR
445	163	NR	575	226	NR	705	25	NR	835	0	NR	965	0	NR
450	218	NR	580	233	NR	710	21	NR	840	0	NR	970	0	NR
455	167	NR	585	240	NR	715	18	NR	845	0	NR	975	0	NR
460	129	NR	590	244	NR	720	15	NR	850	0	NR	980	0	NR
465	143	NR	595	245	NR	725	13	NR	855	0	NR	985	0	NR
470	169	NR	600	249	NR	730	11	NR	860	0	NR	990	0	NR
475	177	NR	605	252	NR	735	9	NR	865	0	NR	995	0	NR
480	156	NR	610	282	NR	740	8	NR	870	0	NR	1000	0	NR
485	137	NR	615	306	NR	745	7	NR	875	0	NR			


REPORT NUMBER: SP1-2505-441-15-R2

TM-30-18


Summary


R_f = 92.4
R_g = 100.9
CIE R_a = 92.1
R_9 = 87.4


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2505-441-15-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 97	CES51 = 95	CES76 = 92
CES02 = 63	CES27 = 90	CES52 = 97	CES77 = 80
CES03 = 32	CES28 = 97	CES53 = 95	CES78 = 91
CES04 = 70	CES29 = 95	CES54 = 91	CES79 = 83
CES05 = 51	CES30 = 90	CES55 = 90	CES80 = 86
CES06 = 51	CES31 = 96	CES56 = 93	CES81 = 67
CES07 = 44	CES32 = 95	CES57 = 92	CES82 = 94
CES08 = 42	CES33 = 96	CES58 = 92	CES83 = 90
CES09 = 29	CES34 = 96	CES59 = 97	CES84 = 97
CES10 = 76	CES35 = 97	CES60 = 93	CES85 = 78
CES11 = 58	CES36 = 83	CES61 = 93	CES86 = 79
CES12 = 65	CES37 = 98	CES62 = 86	CES87 = 94
CES13 = 44	CES38 = 86	CES63 = 97	CES88 = 95
CES14 = 74	CES39 = 99	CES64 = 93	CES89 = 86
CES15 = 72	CES40 = 98	CES65 = 95	CES90 = 93
CES16 = 48	CES41 = 94	CES66 = 94	CES91 = 79
CES17 = 50	CES42 = 96	CES67 = 94	CES92 = 81
CES18 = 57	CES43 = 94	CES68 = 93	CES93 = 88
CES19 = 71	CES44 = 99	CES69 = 94	CES94 = 79
CES20 = 67	CES45 = 97	CES70 = 93	CES95 = 89
CES21 = 86	CES46 = 98	CES71 = 90	CES96 = 96
CES22 = 79	CES47 = 86	CES72 = 96	CES97 = 97
CES23 = 91	CES48 = 90	CES73 = 90	CES98 = 95
CES24 = 90	CES49 = 98	CES74 = 87	CES99 = 92
CES25 = 71	CES50 = 95	CES75 = 90	





REPORT NUMBER: SP1-2505-441-15-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2505-441-15-R2

TM-30-18

Measure Comparisons





(END OF REPORT)