Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590643

Luminaire Tested: 14CGTX-42-B50-HCD

Issue Date: 9/4/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590643
	TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G3-2510-581-29)
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/4/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	14CGTX-42-B50-HCD
Description:	1X4 4200 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 5000K CCT WITH FROSTED SMOOTH LENS
Light Source:	5000K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	3950.9 lumens
Efficiency:	N/A
Efficacy:	96.1 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.27 / 1.39
Luminous Opening:	Rectangular (W 1' x L: 4' x H: 0')
CIE Type:	Direct
Input Watts (W):	41.1
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590643
CATALOG NUMBER: 14CGTX-42-B50-HCD

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590643
CATALOG NUMBER: 14CGTX-42-B50-HCD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	68
3	89	79	70	63	87	77	69	63	74	67	62	71	65	61	69	64	60	57
4	82	69	60	54	79	68	60	53	66	58	52	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	39	51	44	39	50	44	39	37
7	64	50	42	35	62	50	41	35	48	40	35	47	40	35	45	39	34	32
8	60	46	37	31	58	45	37	31	44	36	31	43	36	31	41	35	31	29
9	56	42	34	28	54	42	34	28	40	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	25	37	30	25	36	30	25	36	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3572	3572	3572
5°	3587	3572	3579
10°	3595	3558	3581
15°	3591	3571	3556
20°	3592	3561	3552
25°	3561	3556	3559
30°	3531	3544	3522
35°	3540	3507	3507
40°	3511	3486	3460
45°	3452	3441	3455
50°	3437	3419	3379
55°	3383	3356	3349
60°	3324	3313	3297
65°	3279	3192	3178
70°	3193	3142	3107
75°	3054	2986	2963
80°	2892	2836	2802
85°	2680	2547	2479

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 47.5°
Luminance: 3457 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590643
CATALOG NUMBER: 14CGTX-42-B50-HCD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.1	3.2
10°-20°	362.0	9.2
20°-30°	551.4	14.0
30°-40°	668.9	16.9
40°-50°	699.1	17.7
50°-60°	641.7	16.2
60°-70°	501.1	12.7
70°-80°	305.7	7.7
80°-90°	95.0	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1039.6	26.3
0°-40°	1708.4	43.2
0°-60°	3049.2	77.2
0°-90°	3950.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3950.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1327	1327	1327	1327	1327	
5°	1328	1329	1322	1329	1325	127
15°	1289	1288	1282	1282	1277	363
25°	1199	1196	1198	1193	1198	553
35°	1078	1074	1068	1069	1068	672
45°	907	906	904	908	908	702
55°	721	719	715	720	714	644
65°	515	508	501	503	499	506
75°	294	293	287	286	285	310
85°	87	85	82	84	80	97
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590643
CATALOG NUMBER: 14CGTX-42-B50-HCD

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1327.3	1327.3	1327.3	1327.3	1327.3
2.5°	1330.2	1339.6	1322.9	1324.4	1328.0
5°	1328.0	1329.4	1322.2	1329.4	1325.1
7.5°	1327.3	1320.0	1322.2	1318.6	1325.1
10°	1315.7	1312.8	1302.0	1309.2	1310.6
12.5°	1300.5	1294.7	1299.8	1298.3	1295.4
15°	1288.9	1288.2	1281.7	1281.7	1276.6
17.5°	1267.2	1256.4	1267.2	1262.9	1265.1
20°	1254.2	1241.2	1243.4	1250.6	1240.5
22.5°	1233.2	1227.5	1220.9	1212.3	1222.4
25°	1199.2	1196.4	1197.8	1192.7	1198.5
27.5°	1166.7	1165.3	1161.6	1171.8	1171.0
30°	1136.3	1142.8	1140.7	1138.5	1133.4
32.5°	1105.9	1106.7	1098.7	1104.5	1098.7
35°	1077.7	1074.1	1067.6	1069.1	1067.6
37.5°	1036.5	1035.1	1028.5	1028.5	1030.7
40°	999.6	991.7	992.4	987.3	985.1
42.5°	952.6	952.6	949.0	945.4	954.0
45°	907.0	905.6	904.1	908.5	907.8
47.5°	868.0	862.9	856.4	858.6	861.5
50°	821.0	817.3	816.6	815.2	807.2
52.5°	768.9	767.4	766.0	768.2	765.3
55°	721.1	719.0	715.4	720.4	713.9
57.5°	671.2	667.6	669.8	664.0	664.0
60°	617.7	621.3	615.5	612.6	612.6
62.5°	568.5	561.3	564.2	556.9	554.8
65°	515.0	508.5	501.3	502.7	499.1
67.5°	451.3	455.0	450.6	448.5	445.6
70°	405.8	405.1	399.3	395.7	394.9
72.5°	348.6	348.6	340.0	342.1	338.5
75°	293.7	292.9	287.2	285.7	285.0
77.5°	237.2	240.1	235.1	230.7	230.7
80°	186.6	185.9	183.0	180.1	180.8
82.5°	137.4	133.8	133.1	130.9	130.2
85°	86.8	85.4	82.5	83.9	80.3
87.5°	40.5	39.8	41.2	41.2	41.2
90°	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590643
CATALOG NUMBER: 14CGTX-42-B50-HCD

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.42	18.09	16.79	18.40	18.71	16.37	18.04	16.74	18.35	18.67
	3H	18.36	19.87	18.74	20.20	20.56	18.28	19.79	18.66	20.11	20.47
	4H	19.13	20.56	19.53	20.90	21.28	19.03	20.45	19.43	20.80	21.17
	6H	19.73	21.05	20.14	21.42	21.81	19.61	20.93	20.02	21.29	21.68
	8H	19.95	21.21	20.37	21.60	22.00	19.81	21.08	20.24	21.46	21.86
	12H	20.10	21.32	20.53	21.70	22.13	19.95	21.17	20.38	21.55	21.98
4H	2H	17.07	18.50	17.47	18.84	19.22	17.04	18.46	17.43	18.81	19.18
	3H	19.25	20.45	19.66	20.85	21.25	19.18	20.38	19.59	20.77	21.17
	4H	20.16	21.25	20.60	21.66	22.10	20.06	21.15	20.49	21.56	22.00
	6H	20.91	21.86	21.36	22.30	22.75	20.78	21.73	21.23	22.17	22.63
	8H	21.18	22.07	21.64	22.51	22.98	21.04	21.93	21.50	22.37	22.84
	12H	21.39	22.19	21.87	22.67	23.14	21.24	22.04	21.71	22.51	22.98
8H	4H	20.52	21.41	20.97	21.85	22.31	20.43	21.32	20.88	21.76	22.22
	6H	21.40	22.14	21.89	22.63	23.10	21.28	22.03	21.77	22.51	22.99
	8H	21.76	22.43	22.26	22.93	23.41	21.63	22.30	22.13	22.80	23.29
	12H	22.06	22.65	22.56	23.14	23.70	21.91	22.50	22.42	22.99	23.55
12H	4H	20.56	21.37	21.04	21.84	22.31	20.48	21.28	20.96	21.75	22.22
	6H	21.47	22.14	21.98	22.65	23.13	21.36	22.03	21.87	22.54	23.02
	8H	21.90	22.49	22.40	22.98	23.54	21.77	22.37	22.28	22.86	23.41

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2510-581-5-R2

Test Date: 01/21/2026

Luminaire Tested: 24CGTX-55-B50-HCD

Data in this report applies to families of products including 24CGTX-55HE

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2510-581-5-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-55-B50-HCD**
Description:	*THIS IS A REVISION OF REPORT SP1-2510-581-5-R2 TO UPDATE THE CATALOG INFORMATION* 2X4 CGTX 5500 lumen with BioUp Boards with fixed CCT 5000K - Control Volatge at 2V

Spectral Parameters

CCT (K):	5035
CIE u':	0.2209
CIE v':	0.4693
Duv:	-0.0140
CIE x:	0.3418
CIE y:	0.3227
CIE z:	0.3355
Peak Wavelength (nm):	630
Dominant Wavelength (nm):	0
Purity:	0
Rf:	86.3
Rg:	96

CRI (Ra):	85.1
R1:	90.5
R2:	85.3
R3:	82.8
R4:	87.5
R5:	88.5
R6:	79.4
R7:	82.2
R8:	84.6
R9:	82.5
R10:	72.3
R11:	87.7
R12:	69.3
R13:	88.3
R14:	92.1
R15:	92.3



Test Conditions


Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.1

REPORT NUMBER: SP1-2510-581-5-R2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2510-581-5-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 5035K
CIE x = 0.3418
CIE y = 0.3227
Duv = -0.0140

Point lies outside the range

REPORT NUMBER: SP1-2510-581-5-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	444	NR	620	455	NR	750	10	NR	880	0	NR
365	0	NR	495	380	NR	625	444	NR	755	9	NR	885	0	NR
370	0	NR	500	341	NR	630	1000	NR	760	7	NR	890	0	NR
375	2	NR	505	328	NR	635	607	NR	765	6	NR	895	0	NR
380	2	NR	510	331	NR	640	299	NR	770	5	NR	900	0	NR
385	3	NR	515	335	NR	645	290	NR	775	5	NR	905	0	NR
390	5	NR	520	340	NR	650	243	NR	780	4	NR	910	0	NR
395	6	NR	525	344	NR	655	208	NR	785	3	NR	915	0	NR
400	8	NR	530	350	NR	660	178	NR	790	3	NR	920	0	NR
405	10	NR	535	358	NR	665	152	NR	795	3	NR	925	0	NR
410	13	NR	540	364	NR	670	136	NR	800	2	NR	930	0	NR
415	20	NR	545	375	NR	675	113	NR	805	2	NR	935	0	NR
420	37	NR	550	389	NR	680	97	NR	810	2	NR	940	0	NR
425	66	NR	555	405	NR	685	83	NR	815	1	NR	945	0	NR
430	115	NR	560	426	NR	690	71	NR	820	1	NR	950	0	NR
435	199	NR	565	447	NR	695	61	NR	825	1	NR	955	0	NR
440	332	NR	570	466	NR	700	52	NR	830	1	NR	960	0	NR
445	580	NR	575	484	NR	705	44	NR	835	1	NR	965	0	NR
450	730	NR	580	498	NR	710	37	NR	840	1	NR	970	0	NR
455	561	NR	585	508	NR	715	31	NR	845	1	NR	975	0	NR
460	469	NR	590	514	NR	720	27	NR	850	1	NR	980	0	NR
465	593	NR	595	513	NR	725	23	NR	855	0	NR	985	0	NR
470	784	NR	600	507	NR	730	19	NR	860	0	NR	990	0	NR
475	836	NR	605	499	NR	735	16	NR	865	0	NR	995	0	NR
480	689	NR	610	507	NR	740	14	NR	870	0	NR	1000	0	NR
485	529	NR	615	495	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP1-2510-581-5-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 2.29**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	444	NR	620	455	NR	750	10	NR	880	0	NR
365	0	NR	495	380	NR	625	444	NR	755	9	NR	885	0	NR
370	0	NR	500	341	NR	630	1000	NR	760	7	NR	890	0	NR
375	2	NR	505	328	NR	635	607	NR	765	6	NR	895	0	NR
380	2	NR	510	331	NR	640	299	NR	770	5	NR	900	0	NR
385	3	NR	515	335	NR	645	290	NR	775	5	NR	905	0	NR
390	5	NR	520	340	NR	650	243	NR	780	4	NR	910	0	NR
395	6	NR	525	344	NR	655	208	NR	785	3	NR	915	0	NR
400	8	NR	530	350	NR	660	178	NR	790	3	NR	920	0	NR
405	10	NR	535	358	NR	665	152	NR	795	3	NR	925	0	NR
410	13	NR	540	364	NR	670	136	NR	800	2	NR	930	0	NR
415	20	NR	545	375	NR	675	113	NR	805	2	NR	935	0	NR
420	37	NR	550	389	NR	680	97	NR	810	2	NR	940	0	NR
425	66	NR	555	405	NR	685	83	NR	815	1	NR	945	0	NR
430	115	NR	560	426	NR	690	71	NR	820	1	NR	950	0	NR
435	199	NR	565	447	NR	695	61	NR	825	1	NR	955	0	NR
440	332	NR	570	466	NR	700	52	NR	830	1	NR	960	0	NR
445	580	NR	575	484	NR	705	44	NR	835	1	NR	965	0	NR
450	730	NR	580	498	NR	710	37	NR	840	1	NR	970	0	NR
455	561	NR	585	508	NR	715	31	NR	845	1	NR	975	0	NR
460	469	NR	590	514	NR	720	27	NR	850	1	NR	980	0	NR
465	593	NR	595	513	NR	725	23	NR	855	0	NR	985	0	NR
470	784	NR	600	507	NR	730	19	NR	860	0	NR	990	0	NR
475	836	NR	605	499	NR	735	16	NR	865	0	NR	995	0	NR
480	689	NR	610	507	NR	740	14	NR	870	0	NR	1000	0	NR
485	529	NR	615	495	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP1-2510-581-5-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 5.37**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	444	NR	620	455	NR	750	10	NR	880	0	NR
365	0	NR	495	380	NR	625	444	NR	755	9	NR	885	0	NR
370	0	NR	500	341	NR	630	1000	NR	760	7	NR	890	0	NR
375	2	NR	505	328	NR	635	607	NR	765	6	NR	895	0	NR
380	2	NR	510	331	NR	640	299	NR	770	5	NR	900	0	NR
385	3	NR	515	335	NR	645	290	NR	775	5	NR	905	0	NR
390	5	NR	520	340	NR	650	243	NR	780	4	NR	910	0	NR
395	6	NR	525	344	NR	655	208	NR	785	3	NR	915	0	NR
400	8	NR	530	350	NR	660	178	NR	790	3	NR	920	0	NR
405	10	NR	535	358	NR	665	152	NR	795	3	NR	925	0	NR
410	13	NR	540	364	NR	670	136	NR	800	2	NR	930	0	NR
415	20	NR	545	375	NR	675	113	NR	805	2	NR	935	0	NR
420	37	NR	550	389	NR	680	97	NR	810	2	NR	940	0	NR
425	66	NR	555	405	NR	685	83	NR	815	1	NR	945	0	NR
430	115	NR	560	426	NR	690	71	NR	820	1	NR	950	0	NR
435	199	NR	565	447	NR	695	61	NR	825	1	NR	955	0	NR
440	332	NR	570	466	NR	700	52	NR	830	1	NR	960	0	NR
445	580	NR	575	484	NR	705	44	NR	835	1	NR	965	0	NR
450	730	NR	580	498	NR	710	37	NR	840	1	NR	970	0	NR
455	561	NR	585	508	NR	715	31	NR	845	1	NR	975	0	NR
460	469	NR	590	514	NR	720	27	NR	850	1	NR	980	0	NR
465	593	NR	595	513	NR	725	23	NR	855	0	NR	985	0	NR
470	784	NR	600	507	NR	730	19	NR	860	0	NR	990	0	NR
475	836	NR	605	499	NR	735	16	NR	865	0	NR	995	0	NR
480	689	NR	610	507	NR	740	14	NR	870	0	NR	1000	0	NR
485	529	NR	615	495	NR	745	12	NR	875	0	NR			


REPORT NUMBER: SP1-2510-581-5-R2

TM-30-18


Summary


R_f = 86.3
R_g = 96
CIE R_a = 85.1
R_9 = 82.5


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2510-581-5-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 93	CES51 = 85	CES76 = 86
CES02 = 62	CES27 = 85	CES52 = 87	CES77 = 80
CES03 = 31	CES28 = 94	CES53 = 80	CES78 = 86
CES04 = 69	CES29 = 85	CES54 = 85	CES79 = 82
CES05 = 48	CES30 = 80	CES55 = 81	CES80 = 82
CES06 = 50	CES31 = 85	CES56 = 78	CES81 = 66
CES07 = 41	CES32 = 93	CES57 = 75	CES82 = 93
CES08 = 40	CES33 = 86	CES58 = 76	CES83 = 87
CES09 = 29	CES34 = 91	CES59 = 90	CES84 = 95
CES10 = 74	CES35 = 94	CES60 = 88	CES85 = 78
CES11 = 57	CES36 = 78	CES61 = 86	CES86 = 73
CES12 = 63	CES37 = 94	CES62 = 79	CES87 = 89
CES13 = 43	CES38 = 75	CES63 = 92	CES88 = 89
CES14 = 74	CES39 = 92	CES64 = 81	CES89 = 83
CES15 = 71	CES40 = 87	CES65 = 89	CES90 = 86
CES16 = 47	CES41 = 89	CES66 = 83	CES91 = 73
CES17 = 49	CES42 = 86	CES67 = 83	CES92 = 76
CES18 = 56	CES43 = 84	CES68 = 86	CES93 = 85
CES19 = 71	CES44 = 99	CES69 = 87	CES94 = 77
CES20 = 66	CES45 = 87	CES70 = 88	CES95 = 86
CES21 = 85	CES46 = 88	CES71 = 85	CES96 = 93
CES22 = 77	CES47 = 84	CES72 = 93	CES97 = 82
CES23 = 91	CES48 = 79	CES73 = 86	CES98 = 83
CES24 = 90	CES49 = 88	CES74 = 89	CES99 = 86
CES25 = 70	CES50 = 86	CES75 = 86	





REPORT NUMBER: SP1-2510-581-5-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2510-581-5-R2

TM-30-18

Measure Comparisons





(END OF REPORT)