Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590691

Luminaire Tested: 24CGTX-65-B50-HCD2

Issue Date: 9/4/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590691
	TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G3-2510-581-29)
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/4/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	24CGTX-65-B50-HCD2
Description:	2X4 6500 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 5000K CCT WITH FROSTED SMOOTH LENS
Light Source:	5000K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	6100.6 lumens
Efficiency:	N/A
Efficacy:	108.9 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.27 / 1.39
Luminous Opening:	Rectangular (W 2' x L: 4' x H: 0')
CIE Type:	Direct
Input Watts (W):	56
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590691
CATALOG NUMBER: 24CGTX-65-B50-HCD2

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590691
CATALOG NUMBER: 24CGTX-65-B50-HCD2

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	68
3	89	79	70	63	87	77	69	63	74	67	62	71	65	61	69	64	60	57
4	82	69	60	54	79	68	60	53	66	58	52	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	39	51	44	39	50	44	39	37
7	64	50	42	35	62	50	41	35	48	40	35	47	40	35	45	39	34	32
8	60	46	37	31	58	45	37	31	44	36	31	43	36	31	41	35	31	29
9	56	42	34	28	54	42	34	28	40	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	25	37	30	25	36	30	25	36	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2757	2757	2757
5°	2769	2757	2764
10°	2776	2747	2765
15°	2772	2757	2746
20°	2773	2749	2743
25°	2749	2746	2747
30°	2726	2736	2719
35°	2733	2708	2708
40°	2711	2691	2672
45°	2665	2657	2667
50°	2653	2639	2609
55°	2612	2591	2586
60°	2567	2558	2546
65°	2532	2464	2453
70°	2465	2425	2399
75°	2357	2305	2287
80°	2232	2190	2163
85°	2069	1965	1914

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 47.5°
Luminance: 2669 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590691
CATALOG NUMBER: 24CGTX-65-B50-HCD2

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.8	3.2
10°-20°	559.0	9.2
20°-30°	851.4	14.0
30°-40°	1032.8	16.9
40°-50°	1079.5	17.7
50°-60°	990.8	16.2
60°-70°	773.7	12.7
70°-80°	472.0	7.7
80°-90°	146.7	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1605.2	26.3
0°-40°	2638.0	43.2
0°-60°	4708.3	77.2
0°-90°	6100.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6100.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2049	2049	2049	2049	2049	
5°	2050	2053	2042	2053	2046	195
15°	1990	1989	1979	1979	1971	561
25°	1852	1847	1850	1842	1851	854
35°	1664	1658	1648	1651	1648	1037
45°	1400	1398	1396	1403	1402	1085
55°	1114	1110	1105	1112	1102	995
65°	795	785	774	776	771	782
75°	453	452	443	441	440	479
85°	134	132	127	130	124	150
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590691
CATALOG NUMBER: 24CGTX-65-B50-HCD2

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2049.4	*2049.4*	2049.4	2049.4	2049.4
2.5°	*2053.9*	*2068.4*	*2042.7*	*2045.0*	*2050.5*
5°	2050.5	*2052.8*	2041.6	2052.8	2046.1
7.5°	2049.4	*2038.3*	2041.6	2036.0	2046.1
10°	2031.6	*2027.1*	2010.3	2021.5	2023.7
12.5°	2008.1	*1999.2*	2007.0	2004.8	2000.3
15°	1990.2	*1989.1*	1979.1	1979.1	1971.3
17.5°	1956.7	*1940.0*	1956.7	1950.0	1953.4
20°	1936.6	*1916.5*	1919.9	1931.0	1915.4
22.5°	1904.2	*1895.3*	1885.3	1871.9	1887.5
25°	1851.7	*1847.3*	1849.5	1841.7	1850.6
27.5°	1801.5	*1799.3*	1793.7	1809.3	1808.2
30°	1754.6	*1764.6*	1761.3	1757.9	1750.1
32.5°	1707.7	*1708.8*	1696.5	1705.4	1696.5
35°	1664.1	*1658.5*	1648.5	1650.7	1648.5
37.5°	1600.5	*1598.2*	1588.2	1588.2	1591.5
40°	1543.5	*1531.2*	1532.3	1524.5	1521.2
42.5°	1470.9	*1470.9*	1465.3	1459.7	1473.1
45°	1400.5	*1398.3*	1396.1	1402.8	1401.7
47.5°	1340.2	*1332.4*	1322.4	1325.7	1330.2
50°	1267.6	*1262.0*	1260.9	1258.7	1246.4
52.5°	1187.2	*1185.0*	1182.8	1186.1	1181.6
55°	1113.5	*1110.2*	1104.6	1112.4	1102.3
57.5°	1036.4	*1030.9*	1034.2	1025.3	1025.3
60°	953.8	*959.4*	950.4	946.0	946.0
62.5°	877.8	*866.7*	871.1	860.0	856.6
65°	795.2	*785.1*	774.0	776.2	770.6
67.5°	696.9	*702.5*	695.8	692.5	688.0
70°	626.6	*625.4*	616.5	610.9	609.8
72.5°	538.3	*538.3*	524.9	528.3	522.7
75°	453.4	*452.3*	443.4	441.2	440.0
77.5°	366.3	*370.8*	363.0	356.3	356.3
80°	288.1	*287.0*	282.6	278.1	279.2
82.5°	212.2	*206.6*	205.5	202.2	201.0
85°	134.0	*131.8*	127.3	129.6	124.0
87.5°	62.5	*61.4*	63.7	63.7	63.7
90°	0.0	*0.0*	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590691
CATALOG NUMBER: 24CGTX-65-B50-HCD2

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.52	17.19	15.89	17.50	17.82	15.48	17.14	15.84	17.45	17.77
	3H	17.46	18.97	17.84	19.30	19.66	17.38	18.89	17.76	19.22	19.58
	4H	18.24	19.66	18.63	20.01	20.38	18.13	19.55	18.53	19.90	20.27
	6H	18.83	20.16	19.24	20.52	20.91	18.71	20.03	19.12	20.39	20.78
	8H	19.05	20.31	19.47	20.70	21.10	18.91	20.18	19.34	20.57	20.96
	12H	19.21	20.42	19.63	20.80	21.23	19.06	20.27	19.48	20.65	21.08
4H	2H	16.17	17.60	16.57	17.94	18.32	16.14	17.56	16.53	17.91	18.28
	3H	18.36	19.55	18.76	19.95	20.35	18.28	19.48	18.69	19.87	20.27
	4H	19.27	20.35	19.70	20.77	21.20	19.16	20.25	19.59	20.66	21.10
	6H	20.01	20.96	20.46	21.40	21.86	19.88	20.83	20.33	21.27	21.73
	8H	20.28	21.17	20.74	21.61	22.08	20.14	21.03	20.60	21.48	21.94
	12H	20.49	21.29	20.97	21.77	22.24	20.34	21.14	20.82	21.61	22.08
8H	4H	19.62	20.51	20.08	20.95	21.41	19.53	20.42	19.99	20.86	21.33
	6H	20.50	21.25	20.99	21.73	22.21	20.38	21.13	20.88	21.61	22.09
	8H	20.86	21.53	21.36	22.03	22.52	20.73	21.40	21.24	21.90	22.39
	12H	21.16	21.75	21.66	22.24	22.80	21.01	21.60	21.52	22.09	22.65
12H	4H	19.66	20.47	20.14	20.94	21.41	19.58	20.38	20.06	20.86	21.32
	6H	20.57	21.25	21.08	21.75	22.23	20.46	21.13	20.97	21.64	22.12
	8H	21.00	21.59	21.50	22.08	22.64	20.87	21.47	21.38	21.96	22.52

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2510-581-5-R2

Test Date: 01/21/2026

Luminaire Tested: 24CGTX-55-B50-HCD

Data in this report applies to families of products including 24CGTX-55HE

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2510-581-5-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-55-B50-HCD**
Description:	*THIS IS A REVISION OF REPORT SP1-2510-581-5-R2 TO UPDATE THE CATALOG INFORMATION* 2X4 CGTX 5500 lumen with BioUp Boards with fixed CCT 5000K - Control Volatge at 2V

Spectral Parameters

CCT (K):	5035
CIE u':	0.2209
CIE v':	0.4693
Duv:	-0.0140
CIE x:	0.3418
CIE y:	0.3227
CIE z:	0.3355
Peak Wavelength (nm):	630
Dominant Wavelength (nm):	0
Purity:	0
Rf:	86.3
Rg:	96

CRI (Ra):	85.1
R1:	90.5
R2:	85.3
R3:	82.8
R4:	87.5
R5:	88.5
R6:	79.4
R7:	82.2
R8:	84.6
R9:	82.5
R10:	72.3
R11:	87.7
R12:	69.3
R13:	88.3
R14:	92.1
R15:	92.3



Test Conditions


Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.1

REPORT NUMBER: SP1-2510-581-5-R2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2510-581-5-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 5035K
CIE x = 0.3418
CIE y = 0.3227
Duv = -0.0140

Point lies outside the range

REPORT NUMBER: SP1-2510-581-5-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	444	NR	620	455	NR	750	10	NR	880	0	NR
365	0	NR	495	380	NR	625	444	NR	755	9	NR	885	0	NR
370	0	NR	500	341	NR	630	1000	NR	760	7	NR	890	0	NR
375	2	NR	505	328	NR	635	607	NR	765	6	NR	895	0	NR
380	2	NR	510	331	NR	640	299	NR	770	5	NR	900	0	NR
385	3	NR	515	335	NR	645	290	NR	775	5	NR	905	0	NR
390	5	NR	520	340	NR	650	243	NR	780	4	NR	910	0	NR
395	6	NR	525	344	NR	655	208	NR	785	3	NR	915	0	NR
400	8	NR	530	350	NR	660	178	NR	790	3	NR	920	0	NR
405	10	NR	535	358	NR	665	152	NR	795	3	NR	925	0	NR
410	13	NR	540	364	NR	670	136	NR	800	2	NR	930	0	NR
415	20	NR	545	375	NR	675	113	NR	805	2	NR	935	0	NR
420	37	NR	550	389	NR	680	97	NR	810	2	NR	940	0	NR
425	66	NR	555	405	NR	685	83	NR	815	1	NR	945	0	NR
430	115	NR	560	426	NR	690	71	NR	820	1	NR	950	0	NR
435	199	NR	565	447	NR	695	61	NR	825	1	NR	955	0	NR
440	332	NR	570	466	NR	700	52	NR	830	1	NR	960	0	NR
445	580	NR	575	484	NR	705	44	NR	835	1	NR	965	0	NR
450	730	NR	580	498	NR	710	37	NR	840	1	NR	970	0	NR
455	561	NR	585	508	NR	715	31	NR	845	1	NR	975	0	NR
460	469	NR	590	514	NR	720	27	NR	850	1	NR	980	0	NR
465	593	NR	595	513	NR	725	23	NR	855	0	NR	985	0	NR
470	784	NR	600	507	NR	730	19	NR	860	0	NR	990	0	NR
475	836	NR	605	499	NR	735	16	NR	865	0	NR	995	0	NR
480	689	NR	610	507	NR	740	14	NR	870	0	NR	1000	0	NR
485	529	NR	615	495	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP1-2510-581-5-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 2.29**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	444	NR	620	455	NR	750	10	NR	880	0	NR
365	0	NR	495	380	NR	625	444	NR	755	9	NR	885	0	NR
370	0	NR	500	341	NR	630	1000	NR	760	7	NR	890	0	NR
375	2	NR	505	328	NR	635	607	NR	765	6	NR	895	0	NR
380	2	NR	510	331	NR	640	299	NR	770	5	NR	900	0	NR
385	3	NR	515	335	NR	645	290	NR	775	5	NR	905	0	NR
390	5	NR	520	340	NR	650	243	NR	780	4	NR	910	0	NR
395	6	NR	525	344	NR	655	208	NR	785	3	NR	915	0	NR
400	8	NR	530	350	NR	660	178	NR	790	3	NR	920	0	NR
405	10	NR	535	358	NR	665	152	NR	795	3	NR	925	0	NR
410	13	NR	540	364	NR	670	136	NR	800	2	NR	930	0	NR
415	20	NR	545	375	NR	675	113	NR	805	2	NR	935	0	NR
420	37	NR	550	389	NR	680	97	NR	810	2	NR	940	0	NR
425	66	NR	555	405	NR	685	83	NR	815	1	NR	945	0	NR
430	115	NR	560	426	NR	690	71	NR	820	1	NR	950	0	NR
435	199	NR	565	447	NR	695	61	NR	825	1	NR	955	0	NR
440	332	NR	570	466	NR	700	52	NR	830	1	NR	960	0	NR
445	580	NR	575	484	NR	705	44	NR	835	1	NR	965	0	NR
450	730	NR	580	498	NR	710	37	NR	840	1	NR	970	0	NR
455	561	NR	585	508	NR	715	31	NR	845	1	NR	975	0	NR
460	469	NR	590	514	NR	720	27	NR	850	1	NR	980	0	NR
465	593	NR	595	513	NR	725	23	NR	855	0	NR	985	0	NR
470	784	NR	600	507	NR	730	19	NR	860	0	NR	990	0	NR
475	836	NR	605	499	NR	735	16	NR	865	0	NR	995	0	NR
480	689	NR	610	507	NR	740	14	NR	870	0	NR	1000	0	NR
485	529	NR	615	495	NR	745	12	NR	875	0	NR			

REPORT NUMBER: SP1-2510-581-5-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 5.37**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	444	NR	620	455	NR	750	10	NR	880	0	NR
365	0	NR	495	380	NR	625	444	NR	755	9	NR	885	0	NR
370	0	NR	500	341	NR	630	1000	NR	760	7	NR	890	0	NR
375	2	NR	505	328	NR	635	607	NR	765	6	NR	895	0	NR
380	2	NR	510	331	NR	640	299	NR	770	5	NR	900	0	NR
385	3	NR	515	335	NR	645	290	NR	775	5	NR	905	0	NR
390	5	NR	520	340	NR	650	243	NR	780	4	NR	910	0	NR
395	6	NR	525	344	NR	655	208	NR	785	3	NR	915	0	NR
400	8	NR	530	350	NR	660	178	NR	790	3	NR	920	0	NR
405	10	NR	535	358	NR	665	152	NR	795	3	NR	925	0	NR
410	13	NR	540	364	NR	670	136	NR	800	2	NR	930	0	NR
415	20	NR	545	375	NR	675	113	NR	805	2	NR	935	0	NR
420	37	NR	550	389	NR	680	97	NR	810	2	NR	940	0	NR
425	66	NR	555	405	NR	685	83	NR	815	1	NR	945	0	NR
430	115	NR	560	426	NR	690	71	NR	820	1	NR	950	0	NR
435	199	NR	565	447	NR	695	61	NR	825	1	NR	955	0	NR
440	332	NR	570	466	NR	700	52	NR	830	1	NR	960	0	NR
445	580	NR	575	484	NR	705	44	NR	835	1	NR	965	0	NR
450	730	NR	580	498	NR	710	37	NR	840	1	NR	970	0	NR
455	561	NR	585	508	NR	715	31	NR	845	1	NR	975	0	NR
460	469	NR	590	514	NR	720	27	NR	850	1	NR	980	0	NR
465	593	NR	595	513	NR	725	23	NR	855	0	NR	985	0	NR
470	784	NR	600	507	NR	730	19	NR	860	0	NR	990	0	NR
475	836	NR	605	499	NR	735	16	NR	865	0	NR	995	0	NR
480	689	NR	610	507	NR	740	14	NR	870	0	NR	1000	0	NR
485	529	NR	615	495	NR	745	12	NR	875	0	NR			


REPORT NUMBER: SP1-2510-581-5-R2

TM-30-18


Summary


R_f = 86.3
R_g = 96
CIE R_a = 85.1
R_9 = 82.5


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2510-581-5-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 93	CES51 = 85	CES76 = 86
CES02 = 62	CES27 = 85	CES52 = 87	CES77 = 80
CES03 = 31	CES28 = 94	CES53 = 80	CES78 = 86
CES04 = 69	CES29 = 85	CES54 = 85	CES79 = 82
CES05 = 48	CES30 = 80	CES55 = 81	CES80 = 82
CES06 = 50	CES31 = 85	CES56 = 78	CES81 = 66
CES07 = 41	CES32 = 93	CES57 = 75	CES82 = 93
CES08 = 40	CES33 = 86	CES58 = 76	CES83 = 87
CES09 = 29	CES34 = 91	CES59 = 90	CES84 = 95
CES10 = 74	CES35 = 94	CES60 = 88	CES85 = 78
CES11 = 57	CES36 = 78	CES61 = 86	CES86 = 73
CES12 = 63	CES37 = 94	CES62 = 79	CES87 = 89
CES13 = 43	CES38 = 75	CES63 = 92	CES88 = 89
CES14 = 74	CES39 = 92	CES64 = 81	CES89 = 83
CES15 = 71	CES40 = 87	CES65 = 89	CES90 = 86
CES16 = 47	CES41 = 89	CES66 = 83	CES91 = 73
CES17 = 49	CES42 = 86	CES67 = 83	CES92 = 76
CES18 = 56	CES43 = 84	CES68 = 86	CES93 = 85
CES19 = 71	CES44 = 99	CES69 = 87	CES94 = 77
CES20 = 66	CES45 = 87	CES70 = 88	CES95 = 86
CES21 = 85	CES46 = 88	CES71 = 85	CES96 = 93
CES22 = 77	CES47 = 84	CES72 = 93	CES97 = 82
CES23 = 91	CES48 = 79	CES73 = 86	CES98 = 83
CES24 = 90	CES49 = 88	CES74 = 89	CES99 = 86
CES25 = 70	CES50 = 86	CES75 = 86	





REPORT NUMBER: SP1-2510-581-5-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2510-581-5-R2

TM-30-18

Measure Comparisons





(END OF REPORT)