Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1559226

Luminaire Tested: 14CGTX-20-B2750-W2D-2700K

Issue Date: 8/30/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1559226
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	8/30/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	14CGTX-20-B2750-W2D-2700K
Description:	1X4 2000 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 2700K CCT WITH FROSTED SMOOTH L
Light Source:	2700K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	2119.4 lumens
Efficiency:	N/A
Efficacy:	107.0 lumens/watt
Spacing Criteria (0/90/45):	1.26 / 1.26 / 1.38
Luminous Opening:	Rectangular (W 0.82' x L: 3.83' x H: 0')
CIE Type:	Direct
Input Watts (W):	19.8
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559226
CATALOG NUMBER: 14CGTX-20-B2750-W2D-2700K

Luminous Intensity Polar Plot



LENS

0% Up

100% Dn

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559226
CATALOG NUMBER: 14CGTX-20-B2750-W2D-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	94	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	79	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	45	39	50	44	39	37
7	64	51	42	35	63	50	41	35	48	41	35	47	40	35	45	39	35	32
8	60	46	37	32	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	41	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	26	37	30	26	37	30	25	36	30	25	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2460	2460	2460
5°	2463	2456	2466
10°	2457	2453	2464
15°	2452	2448	2462
20°	2440	2440	2447
25°	2432	2428	2436
30°	2419	2411	2411
35°	2395	2391	2391
40°	2379	2374	2374
45°	2355	2350	2336
50°	2330	2330	2309
55°	2296	2290	2261
60°	2266	2245	2211
65°	2212	2188	2148
70°	2155	2115	2065
75°	2070	2030	1964
80°	1985	1886	1827
85°	1762	1683	1605

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
Vertical Angle: 45°
Luminance: 2360 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559226
CATALOG NUMBER: 14CGTX-20-B2750-W2D-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.3	3.2
10°-20°	196.0	9.2
20°-30°	297.7	14.0
30°-40°	359.8	17.0
40°-50°	375.6	17.7
50°-60°	343.5	16.2
60°-70°	267.5	12.6
70°-80°	162.2	7.7
80°-90°	48.8	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	562.0	26.5
0°-40°	921.8	43.5
0°-60°	1640.9	77.4
0°-90°	2119.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2119.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	721	721	721	721	721	
5°	719	718	717	719	720	68
15°	694	694	693	696	697	196
25°	646	646	645	647	647	298
35°	575	576	574	575	574	360
45°	488	489	487	485	484	376
55°	386	387	385	382	380	345
65°	274	274	271	267	266	271
75°	157	157	154	150	149	166
85°	45	44	43	42	41	51
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559226
CATALOG NUMBER: 14CGTX-20-B2750-W2D-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	721	721	721	721	*721*
2.5°	*721*	*720*	*719*	*721*	*722*
5°	719	718	717	719	*720*
7.5°	715	715	713	716	*717*
10°	709	709	708	711	*711*
12.5°	702	703	701	704	*705*
15°	694	694	693	696	*697*
17.5°	684	685	683	686	*686*
20°	672	673	672	674	*674*
22.5°	660	660	659	661	*661*
25°	646	646	645	647	*647*
27.5°	630	630	630	631	*631*
30°	614	613	612	613	*612*
32.5°	595	595	594	595	*594*
35°	575	576	574	575	*574*
37.5°	555	556	554	555	*553*
40°	534	535	533	532	*533*
42.5°	511	512	510	510	*508*
45°	488	489	487	485	*484*
47.5°	463	465	463	460	*459*
50°	439	440	439	436	*435*
52.5°	413	414	411	409	*407*
55°	386	387	385	382	*380*
57.5°	359	361	357	354	*353*
60°	332	331	329	326	*324*
62.5°	304	303	300	296	*295*
65°	274	274	271	267	*266*
67.5°	244	244	241	238	*237*
70°	216	215	212	208	*207*
72.5°	186	186	183	180	*178*
75°	157	157	154	150	*149*
77.5°	128	128	124	122	*120*
80°	101	99	96	94	*93*
82.5°	72	71	69	67	*68*
85°	45	44	43	42	*41*
87.5°	21	20	19	18	*17*
90°	0	0	0	0	*0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1559226
CATALOG NUMBER: 14CGTX-20-B2750-W2D-2700K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.12	16.78	15.49	17.10	17.41	14.99	16.65	15.36	16.97	17.28
	3H	17.04	18.55	17.42	18.88	19.24	16.88	18.38	17.25	18.71	19.07
	4H	17.81	19.23	18.20	19.57	19.95	17.61	19.02	18.00	19.37	19.75
	6H	18.41	19.73	18.82	20.09	20.48	18.16	19.48	18.58	19.85	20.24
	8H	18.62	19.88	19.04	20.27	20.66	18.36	19.62	18.78	20.01	20.41
	12H	18.76	19.97	19.19	20.35	20.78	18.49	19.70	18.92	20.08	20.51
4H	2H	15.78	17.20	16.17	17.54	17.92	15.67	17.09	16.07	17.44	17.81
	3H	17.93	19.12	18.34	19.52	19.92	17.78	18.98	18.19	19.37	19.77
	4H	18.83	19.92	19.26	20.33	20.76	18.65	19.73	19.08	20.14	20.58
	6H	19.58	20.52	20.03	20.96	21.42	19.34	20.29	19.79	20.73	21.18
	8H	19.84	20.73	20.30	21.17	21.63	19.59	20.48	20.05	20.92	21.38
	12H	20.04	20.84	20.52	21.31	21.78	19.77	20.57	20.25	21.05	21.52
8H	4H	19.17	20.06	19.63	20.51	20.97	19.01	19.90	19.47	20.34	20.81
	6H	20.05	20.80	20.55	21.28	21.76	19.84	20.58	20.33	21.07	21.54
	8H	20.40	21.07	20.91	21.57	22.06	20.17	20.84	20.68	21.34	21.83
	12H	20.69	21.28	21.19	21.77	22.32	20.44	21.02	20.94	21.51	22.07
12H	4H	19.22	20.02	19.70	20.49	20.96	19.06	19.86	19.54	20.34	20.80
	6H	20.12	20.79	20.63	21.30	21.78	19.92	20.59	20.43	21.09	21.58
	8H	20.54	21.12	21.04	21.61	22.17	20.31	20.90	20.82	21.39	21.95

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2505-441-28-R2

Test Date: 07/10/2025

Luminaire Tested: 24CGTX-45-B2750-W2D-2700K

Data in this report applies to families of products including 24CGTX


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2505-441-28-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-45-B2750-W2D-2700K**
Description:	*THIS IS A REVISION OF REPORT SP1-2504-441-28-R2 TO UPDATE THE CATALOG INFORMATION* 2X4 4500 LUMEN CGTX. Using WaveLinx PRO F1 sensor.

Spectral Parameters

CCT (K):	2694	CRI (Ra):	95.4		
CIE u':	0.2630	R1:	96.8	R9:	80.8
CIE v':	0.5264	R2:	98.3	R10:	98.3
Duv:	-0.0008	R3:	97.9	R11:	89.1
CIE x:	0.4590	R4:	94.6	R12:	93.4
CIE y:	0.4084	R5:	96.4	R13:	96.9
CIE z:	0.1326	R6:	92.3	R14:	97.1
Peak Wavelength (nm):	630	R7:	94.8	R15:	98.2
Dominant Wavelength (nm):	584	R8:	92.1		
Purity:	60.36523				
Rf:	93.8				
Rg:	102				




Test Conditions

Stabilization Time:	24M
Operation Time:	1H 24M
Sphere Temperature (°C):	24.0


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2505-441-28-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2694K
CIE x = 0.4590
CIE y = 0.4084
Duv = -0.0008

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2505-441-28-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	70	NR	620	228	NR	750	5	NR	880	0	NR
365	0	NR	495	86	NR	625	239	NR	755	4	NR	885	0	NR
370	0	NR	500	100	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	111	NR	635	614	NR	765	3	NR	895	0	NR
380	0	NR	510	118	NR	640	147	NR	770	3	NR	900	0	NR
385	0	NR	515	122	NR	645	148	NR	775	2	NR	905	0	NR
390	0	NR	520	126	NR	650	127	NR	780	2	NR	910	0	NR
395	0	NR	525	128	NR	655	105	NR	785	2	NR	915	0	NR
400	1	NR	530	130	NR	660	88	NR	790	1	NR	920	0	NR
405	1	NR	535	134	NR	665	73	NR	795	1	NR	925	0	NR
410	2	NR	540	139	NR	670	70	NR	800	1	NR	930	0	NR
415	3	NR	545	143	NR	675	55	NR	805	1	NR	935	0	NR
420	6	NR	550	148	NR	680	47	NR	810	1	NR	940	0	NR
425	10	NR	555	154	NR	685	41	NR	815	1	NR	945	0	NR
430	18	NR	560	159	NR	690	35	NR	820	1	NR	950	0	NR
435	28	NR	565	164	NR	695	30	NR	825	1	NR	955	0	NR
440	44	NR	570	169	NR	700	25	NR	830	0	NR	960	0	NR
445	75	NR	575	175	NR	705	22	NR	835	0	NR	965	0	NR
450	107	NR	580	179	NR	710	18	NR	840	0	NR	970	0	NR
455	82	NR	585	186	NR	715	16	NR	845	0	NR	975	0	NR
460	58	NR	590	190	NR	720	13	NR	850	0	NR	980	0	NR
465	53	NR	595	192	NR	725	11	NR	855	0	NR	985	0	NR
470	45	NR	600	198	NR	730	10	NR	860	0	NR	990	0	NR
475	41	NR	605	203	NR	735	8	NR	865	0	NR	995	0	NR
480	46	NR	610	237	NR	740	7	NR	870	0	NR	1000	0	NR
485	57	NR	615	264	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-28-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.34**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	70	NR	620	228	NR	750	5	NR	880	0	NR
365	0	NR	495	86	NR	625	239	NR	755	4	NR	885	0	NR
370	0	NR	500	100	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	111	NR	635	614	NR	765	3	NR	895	0	NR
380	0	NR	510	118	NR	640	147	NR	770	3	NR	900	0	NR
385	0	NR	515	122	NR	645	148	NR	775	2	NR	905	0	NR
390	0	NR	520	126	NR	650	127	NR	780	2	NR	910	0	NR
395	0	NR	525	128	NR	655	105	NR	785	2	NR	915	0	NR
400	1	NR	530	130	NR	660	88	NR	790	1	NR	920	0	NR
405	1	NR	535	134	NR	665	73	NR	795	1	NR	925	0	NR
410	2	NR	540	139	NR	670	70	NR	800	1	NR	930	0	NR
415	3	NR	545	143	NR	675	55	NR	805	1	NR	935	0	NR
420	6	NR	550	148	NR	680	47	NR	810	1	NR	940	0	NR
425	10	NR	555	154	NR	685	41	NR	815	1	NR	945	0	NR
430	18	NR	560	159	NR	690	35	NR	820	1	NR	950	0	NR
435	28	NR	565	164	NR	695	30	NR	825	1	NR	955	0	NR
440	44	NR	570	169	NR	700	25	NR	830	0	NR	960	0	NR
445	75	NR	575	175	NR	705	22	NR	835	0	NR	965	0	NR
450	107	NR	580	179	NR	710	18	NR	840	0	NR	970	0	NR
455	82	NR	585	186	NR	715	16	NR	845	0	NR	975	0	NR
460	58	NR	590	190	NR	720	13	NR	850	0	NR	980	0	NR
465	53	NR	595	192	NR	725	11	NR	855	0	NR	985	0	NR
470	45	NR	600	198	NR	730	10	NR	860	0	NR	990	0	NR
475	41	NR	605	203	NR	735	8	NR	865	0	NR	995	0	NR
480	46	NR	610	237	NR	740	7	NR	870	0	NR	1000	0	NR
485	57	NR	615	264	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-28-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.58**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	70	NR	620	228	NR	750	5	NR	880	0	NR
365	0	NR	495	86	NR	625	239	NR	755	4	NR	885	0	NR
370	0	NR	500	100	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	111	NR	635	614	NR	765	3	NR	895	0	NR
380	0	NR	510	118	NR	640	147	NR	770	3	NR	900	0	NR
385	0	NR	515	122	NR	645	148	NR	775	2	NR	905	0	NR
390	0	NR	520	126	NR	650	127	NR	780	2	NR	910	0	NR
395	0	NR	525	128	NR	655	105	NR	785	2	NR	915	0	NR
400	1	NR	530	130	NR	660	88	NR	790	1	NR	920	0	NR
405	1	NR	535	134	NR	665	73	NR	795	1	NR	925	0	NR
410	2	NR	540	139	NR	670	70	NR	800	1	NR	930	0	NR
415	3	NR	545	143	NR	675	55	NR	805	1	NR	935	0	NR
420	6	NR	550	148	NR	680	47	NR	810	1	NR	940	0	NR
425	10	NR	555	154	NR	685	41	NR	815	1	NR	945	0	NR
430	18	NR	560	159	NR	690	35	NR	820	1	NR	950	0	NR
435	28	NR	565	164	NR	695	30	NR	825	1	NR	955	0	NR
440	44	NR	570	169	NR	700	25	NR	830	0	NR	960	0	NR
445	75	NR	575	175	NR	705	22	NR	835	0	NR	965	0	NR
450	107	NR	580	179	NR	710	18	NR	840	0	NR	970	0	NR
455	82	NR	585	186	NR	715	16	NR	845	0	NR	975	0	NR
460	58	NR	590	190	NR	720	13	NR	850	0	NR	980	0	NR
465	53	NR	595	192	NR	725	11	NR	855	0	NR	985	0	NR
470	45	NR	600	198	NR	730	10	NR	860	0	NR	990	0	NR
475	41	NR	605	203	NR	735	8	NR	865	0	NR	995	0	NR
480	46	NR	610	237	NR	740	7	NR	870	0	NR	1000	0	NR
485	57	NR	615	264	NR	745	6	NR	875	0	NR			


REPORT NUMBER: SP1-2505-441-28-R2

TM-30-18


Summary


R_f = 93.8
R_g = 102
CIE R_a = 95.4
R_9 = 80.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2505-441-28-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 99	CES51 = 93	CES76 = 96
CES02 = 64	CES27 = 95	CES52 = 93	CES77 = 79
CES03 = 32	CES28 = 100	CES53 = 93	CES78 = 92
CES04 = 70	CES29 = 97	CES54 = 96	CES79 = 84
CES05 = 52	CES30 = 100	CES55 = 96	CES80 = 89
CES06 = 51	CES31 = 98	CES56 = 95	CES81 = 65
CES07 = 45	CES32 = 90	CES57 = 95	CES82 = 95
CES08 = 43	CES33 = 96	CES58 = 94	CES83 = 91
CES09 = 29	CES34 = 99	CES59 = 97	CES84 = 98
CES10 = 77	CES35 = 99	CES60 = 96	CES85 = 80
CES11 = 59	CES36 = 90	CES61 = 96	CES86 = 78
CES12 = 66	CES37 = 96	CES62 = 92	CES87 = 95
CES13 = 45	CES38 = 96	CES63 = 97	CES88 = 99
CES14 = 74	CES39 = 97	CES64 = 95	CES89 = 85
CES15 = 72	CES40 = 95	CES65 = 98	CES90 = 98
CES16 = 49	CES41 = 94	CES66 = 96	CES91 = 86
CES17 = 50	CES42 = 93	CES67 = 96	CES92 = 83
CES18 = 57	CES43 = 95	CES68 = 97	CES93 = 90
CES19 = 72	CES44 = 99	CES69 = 97	CES94 = 77
CES20 = 68	CES45 = 95	CES70 = 97	CES95 = 90
CES21 = 87	CES46 = 96	CES71 = 96	CES96 = 96
CES22 = 79	CES47 = 82	CES72 = 98	CES97 = 93
CES23 = 92	CES48 = 99	CES73 = 94	CES98 = 97
CES24 = 91	CES49 = 94	CES74 = 86	CES99 = 96
CES25 = 72	CES50 = 94	CES75 = 96	





REPORT NUMBER: SP1-2505-441-28-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2505-441-28-R2

TM-30-18

Measure Comparisons





(END OF REPORT)