Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1559240

Luminaire Tested: 14CGTX-42-B2750-W2D-3500K

Issue Date: 8/30/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1559240
	TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G3-2510-581-16)
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	8/30/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	14CGTX-42-B2750-W2D-3500K
Description:	1X4 4200 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 3500K CCT WITH FROSTED SMOOTH l
Light Source:	3500K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	4135.9 lumens
Efficiency:	N/A
Efficacy:	95.7 lumens/watt
Spacing Criteria (0/90/45):	1.26 / 1.26 / 1.38
Luminous Opening:	Rectangular (W 1' x L: 4' x H: 0')
CIE Type:	Direct
Input Watts (W):	43.2
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559240
CATALOG NUMBER: 14CGTX-42-B2750-W2D-3500K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559240
CATALOG NUMBER: 14CGTX-42-B2750-W2D-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	94	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	77	73	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	79	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	45	39	50	44	39	37
7	64	51	42	35	63	50	41	35	48	41	35	47	40	35	45	39	35	33
8	60	46	38	32	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	41	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	39	31	26	38	30	26	37	30	25	36	30	25	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3787	3787	3787
5°	3791	3783	3799
10°	3788	3780	3799
15°	3778	3772	3789
20°	3762	3756	3770
25°	3741	3738	3748
30°	3724	3718	3715
35°	3692	3682	3682
40°	3665	3658	3644
45°	3632	3621	3602
50°	3594	3578	3548
55°	3541	3521	3474
60°	3486	3448	3405
65°	3417	3354	3302
70°	3302	3246	3183
75°	3168	3094	3011
80°	2986	2940	2783
85°	2680	2649	2492

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3632 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559240
CATALOG NUMBER: 14CGTX-42-B2750-W2D-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.4	3.2
10°-20°	382.9	9.3
20°-30°	581.2	14.1
30°-40°	702.6	17.0
40°-50°	733.3	17.7
50°-60°	670.1	16.2
60°-70°	521.6	12.6
70°-80°	315.7	7.6
80°-90°	95.2	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1097.5	26.5
0°-40°	1800.1	43.5
0°-60°	3203.5	77.5
0°-90°	4135.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4135.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1407	1407	1407	1407	1407	
5°	1403	1403	1400	1405	1406	133
15°	1356	1356	1354	1359	1360	383
25°	1260	1260	1259	1263	1262	581
35°	1124	1125	1121	1122	1121	703
45°	954	953	951	948	946	735
55°	755	757	751	745	740	675
65°	537	535	527	521	519	530
75°	305	304	298	294	290	323
85°	87	86	86	82	81	100
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559240
CATALOG NUMBER: 14CGTX-42-B2750-W2D-3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1407.4	1407.4	1407.4	1407.4	*1407.4*
2.5°	*1407.4*	*1407.4*	*1403.4*	*1409.5*	*1410.5*
5°	1403.4	1403.4	1400.4	1405.4	*1406.4*
7.5°	1396.3	1395.3	1393.3	1398.4	*1400.4*
10°	1386.2	1386.2	1383.2	1388.3	*1390.3*
12.5°	1372.1	1373.1	1370.1	1375.2	*1376.2*
15°	1356.0	1356.0	1354.0	1359.0	*1360.0*
17.5°	1336.8	1335.8	1334.8	1338.8	*1338.8*
20°	1313.6	1314.6	1311.6	1316.6	*1316.6*
22.5°	1289.4	1289.4	1287.4	1290.4	*1291.4*
25°	1260.1	1260.1	1259.1	1263.2	*1262.2*
27.5°	1230.9	1230.9	1228.9	1230.9	*1231.9*
30°	1198.6	1196.6	1196.6	1196.6	*1195.6*
32.5°	1162.3	1163.3	1160.3	1161.3	*1159.2*
35°	1123.9	1124.9	1120.9	1121.9	*1120.9*
37.5°	1083.6	1086.6	1082.6	1081.6	*1079.5*
40°	1043.2	1044.2	1041.2	1038.2	*1037.2*
42.5°	997.8	999.8	997.8	994.8	*994.8*
45°	954.4	953.4	951.4	948.4	*946.4*
47.5°	905.0	907.0	903.0	897.9	*898.9*
50°	858.6	859.6	854.6	848.5	*847.5*
52.5°	807.1	808.1	803.1	798.1	*795.0*
55°	754.7	756.7	750.6	744.6	*740.5*
57.5°	701.2	702.2	695.1	691.1	*689.1*
60°	647.7	645.7	640.7	635.6	*632.6*
62.5°	593.2	589.2	583.2	579.1	*575.1*
65°	536.7	534.7	526.7	520.6	*518.6*
67.5°	478.2	475.2	471.2	464.1	*462.1*
70°	419.7	418.7	412.6	404.6	*404.6*
72.5°	364.2	361.2	356.1	351.1	*345.0*
75°	304.7	303.7	297.6	293.6	*289.6*
77.5°	248.2	248.2	243.1	239.1	*235.1*
80°	192.7	193.7	189.7	182.6	*179.6*
82.5°	142.3	140.2	136.2	130.1	*131.2*
85°	86.8	85.8	85.8	81.7	*80.7*
87.5°	40.4	36.3	35.3	34.3	*34.3*
90°	0.0	0.0	0.0	0.0	*0.0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1559240
CATALOG NUMBER: 14CGTX-42-B2750-W2D-3500K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.61	18.27	16.97	18.58	18.89	16.49	18.15	16.86	18.47	18.78
	3H	18.53	20.04	18.91	20.36	20.72	18.37	19.88	18.75	20.20	20.56
	4H	19.29	20.71	19.69	21.06	21.43	19.10	20.52	19.50	20.87	21.24
	6H	19.88	21.20	20.29	21.56	21.95	19.66	20.98	20.07	21.34	21.73
	8H	20.09	21.35	20.52	21.74	22.14	19.85	21.11	20.27	21.50	21.90
	12H	20.24	21.45	20.67	21.83	22.26	19.98	21.19	20.41	21.57	22.00
4H	2H	17.26	18.67	17.65	19.02	19.40	17.17	18.59	17.56	18.93	19.31
	3H	19.41	20.61	19.82	21.00	21.40	19.27	20.47	19.68	20.86	21.26
	4H	20.31	21.39	20.74	21.81	22.24	20.14	21.22	20.57	21.63	22.07
	6H	21.05	21.99	21.50	22.43	22.89	20.83	21.78	21.29	22.22	22.68
	8H	21.32	22.20	21.77	22.65	23.11	21.08	21.97	21.54	22.41	22.87
	12H	21.51	22.31	21.99	22.79	23.26	21.26	22.06	21.74	22.54	23.00
8H	4H	20.65	21.54	21.11	21.98	22.45	20.50	21.39	20.96	21.83	22.30
	6H	21.53	22.27	22.02	22.76	23.23	21.33	22.08	21.83	22.56	23.04
	8H	21.89	22.55	22.39	23.06	23.54	21.66	22.32	22.17	22.83	23.31
	12H	22.17	22.76	22.68	23.25	23.81	21.92	22.51	22.43	23.00	23.56
12H	4H	20.70	21.50	21.18	21.97	22.44	20.55	21.35	21.03	21.83	22.30
	6H	21.60	22.27	22.11	22.77	23.26	21.42	22.08	21.92	22.59	23.07
	8H	22.02	22.61	22.53	23.10	23.66	21.80	22.39	22.31	22.88	23.44

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2510-581-8-R2

Test Date: 02/03/2026

Luminaire Tested: 24CGTX-45-B2750-W2D-3500K

Data in this report applies to families of products including 24CGTX-45-UNV


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2510-581-8-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-45-B2750-W2D-3500K**
Description:	*THIS IS A REVISION OF REPORT SP1-2510-581-8-R2 TO UPDATE THE CATALOG INFORMATION*2X4 CGTX 4500 lumen with BioUp Boards - 3500K

Spectral Parameters

CCT (K):	3407	CRI (Ra):	90.6		
CIE u':	0.2428	R1:	93.7	R9:	86.5
CIE v':	0.4992	R2:	90.5	R10:	82.1
Duv:	-0.0104	R3:	90.2	R11:	96.0
CIE x:	0.3996	R4:	96.7	R12:	75.0
CIE y:	0.3651	R5:	92.5	R13:	92.1
CIE z:	0.2353	R6:	83.5	R14:	96.1
Peak Wavelength (nm):	630	R7:	88.1	R15:	95.7
Dominant Wavelength (nm):	587	R8:	89.8		
Purity:	29.46494				
Rf:	90.9				
Rg:	99.5				




Test Conditions

Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2510-581-8-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3407K
CIE x = 0.3996
CIE y = 0.3651
Duv = -0.0104

Point lies outside the range

REPORT NUMBER: SP1-2510-581-8-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	165	NR	620	285	NR	750	6	NR	880	0	NR
365	0	NR	495	161	NR	625	293	NR	755	5	NR	885	0	NR
370	0	NR	500	162	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	166	NR	635	530	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	184	NR	770	3	NR	900	0	NR
385	1	NR	515	175	NR	645	198	NR	775	3	NR	905	0	NR
390	1	NR	520	178	NR	650	156	NR	780	2	NR	910	0	NR
395	2	NR	525	182	NR	655	131	NR	785	2	NR	915	0	NR
400	3	NR	530	185	NR	660	110	NR	790	2	NR	920	0	NR
405	3	NR	535	189	NR	665	93	NR	795	2	NR	925	0	NR
410	5	NR	540	194	NR	670	85	NR	800	1	NR	930	0	NR
415	8	NR	545	201	NR	675	70	NR	805	1	NR	935	0	NR
420	13	NR	550	209	NR	680	60	NR	810	1	NR	940	0	NR
425	23	NR	555	216	NR	685	51	NR	815	1	NR	945	0	NR
430	40	NR	560	225	NR	690	44	NR	820	1	NR	950	0	NR
435	68	NR	565	234	NR	695	37	NR	825	1	NR	955	0	NR
440	114	NR	570	243	NR	700	32	NR	830	1	NR	960	0	NR
445	200	NR	575	251	NR	705	27	NR	835	1	NR	965	0	NR
450	260	NR	580	259	NR	710	23	NR	840	0	NR	970	0	NR
455	194	NR	585	266	NR	715	19	NR	845	0	NR	975	0	NR
460	155	NR	590	271	NR	720	17	NR	850	0	NR	980	0	NR
465	182	NR	595	273	NR	725	14	NR	855	0	NR	985	0	NR
470	226	NR	600	276	NR	730	12	NR	860	0	NR	990	0	NR
475	241	NR	605	279	NR	735	10	NR	865	0	NR	995	0	NR
480	211	NR	610	307	NR	740	9	NR	870	0	NR	1000	0	NR
485	177	NR	615	311	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2510-581-8-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.78**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	165	NR	620	285	NR	750	6	NR	880	0	NR
365	0	NR	495	161	NR	625	293	NR	755	5	NR	885	0	NR
370	0	NR	500	162	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	166	NR	635	530	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	184	NR	770	3	NR	900	0	NR
385	1	NR	515	175	NR	645	198	NR	775	3	NR	905	0	NR
390	1	NR	520	178	NR	650	156	NR	780	2	NR	910	0	NR
395	2	NR	525	182	NR	655	131	NR	785	2	NR	915	0	NR
400	3	NR	530	185	NR	660	110	NR	790	2	NR	920	0	NR
405	3	NR	535	189	NR	665	93	NR	795	2	NR	925	0	NR
410	5	NR	540	194	NR	670	85	NR	800	1	NR	930	0	NR
415	8	NR	545	201	NR	675	70	NR	805	1	NR	935	0	NR
420	13	NR	550	209	NR	680	60	NR	810	1	NR	940	0	NR
425	23	NR	555	216	NR	685	51	NR	815	1	NR	945	0	NR
430	40	NR	560	225	NR	690	44	NR	820	1	NR	950	0	NR
435	68	NR	565	234	NR	695	37	NR	825	1	NR	955	0	NR
440	114	NR	570	243	NR	700	32	NR	830	1	NR	960	0	NR
445	200	NR	575	251	NR	705	27	NR	835	1	NR	965	0	NR
450	260	NR	580	259	NR	710	23	NR	840	0	NR	970	0	NR
455	194	NR	585	266	NR	715	19	NR	845	0	NR	975	0	NR
460	155	NR	590	271	NR	720	17	NR	850	0	NR	980	0	NR
465	182	NR	595	273	NR	725	14	NR	855	0	NR	985	0	NR
470	226	NR	600	276	NR	730	12	NR	860	0	NR	990	0	NR
475	241	NR	605	279	NR	735	10	NR	865	0	NR	995	0	NR
480	211	NR	610	307	NR	740	9	NR	870	0	NR	1000	0	NR
485	177	NR	615	311	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2510-581-8-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 3.85**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	165	NR	620	285	NR	750	6	NR	880	0	NR
365	0	NR	495	161	NR	625	293	NR	755	5	NR	885	0	NR
370	0	NR	500	162	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	166	NR	635	530	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	184	NR	770	3	NR	900	0	NR
385	1	NR	515	175	NR	645	198	NR	775	3	NR	905	0	NR
390	1	NR	520	178	NR	650	156	NR	780	2	NR	910	0	NR
395	2	NR	525	182	NR	655	131	NR	785	2	NR	915	0	NR
400	3	NR	530	185	NR	660	110	NR	790	2	NR	920	0	NR
405	3	NR	535	189	NR	665	93	NR	795	2	NR	925	0	NR
410	5	NR	540	194	NR	670	85	NR	800	1	NR	930	0	NR
415	8	NR	545	201	NR	675	70	NR	805	1	NR	935	0	NR
420	13	NR	550	209	NR	680	60	NR	810	1	NR	940	0	NR
425	23	NR	555	216	NR	685	51	NR	815	1	NR	945	0	NR
430	40	NR	560	225	NR	690	44	NR	820	1	NR	950	0	NR
435	68	NR	565	234	NR	695	37	NR	825	1	NR	955	0	NR
440	114	NR	570	243	NR	700	32	NR	830	1	NR	960	0	NR
445	200	NR	575	251	NR	705	27	NR	835	1	NR	965	0	NR
450	260	NR	580	259	NR	710	23	NR	840	0	NR	970	0	NR
455	194	NR	585	266	NR	715	19	NR	845	0	NR	975	0	NR
460	155	NR	590	271	NR	720	17	NR	850	0	NR	980	0	NR
465	182	NR	595	273	NR	725	14	NR	855	0	NR	985	0	NR
470	226	NR	600	276	NR	730	12	NR	860	0	NR	990	0	NR
475	241	NR	605	279	NR	735	10	NR	865	0	NR	995	0	NR
480	211	NR	610	307	NR	740	9	NR	870	0	NR	1000	0	NR
485	177	NR	615	311	NR	745	7	NR	875	0	NR			


REPORT NUMBER: SP1-2510-581-8-R2

TM-30-18


Summary


R_f = 90.9
R_g = 99.5
CIE R_a = 90.6
R_9 = 86.5


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2510-581-8-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 95	CES51 = 93	CES76 = 90
CES02 = 63	CES27 = 88	CES52 = 97	CES77 = 79
CES03 = 32	CES28 = 96	CES53 = 92	CES78 = 90
CES04 = 70	CES29 = 92	CES54 = 89	CES79 = 82
CES05 = 50	CES30 = 87	CES55 = 87	CES80 = 85
CES06 = 51	CES31 = 92	CES56 = 89	CES81 = 65
CES07 = 43	CES32 = 97	CES57 = 88	CES82 = 94
CES08 = 42	CES33 = 92	CES58 = 88	CES83 = 89
CES09 = 29	CES34 = 95	CES59 = 95	CES84 = 97
CES10 = 76	CES35 = 96	CES60 = 91	CES85 = 78
CES11 = 58	CES36 = 81	CES61 = 92	CES86 = 77
CES12 = 65	CES37 = 97	CES62 = 83	CES87 = 93
CES13 = 44	CES38 = 82	CES63 = 95	CES88 = 93
CES14 = 74	CES39 = 98	CES64 = 91	CES89 = 86
CES15 = 72	CES40 = 96	CES65 = 93	CES90 = 91
CES16 = 48	CES41 = 93	CES66 = 91	CES91 = 76
CES17 = 49	CES42 = 95	CES67 = 91	CES92 = 80
CES18 = 57	CES43 = 93	CES68 = 92	CES93 = 88
CES19 = 71	CES44 = 99	CES69 = 93	CES94 = 79
CES20 = 67	CES45 = 96	CES70 = 92	CES95 = 88
CES21 = 86	CES46 = 96	CES71 = 88	CES96 = 96
CES22 = 78	CES47 = 86	CES72 = 95	CES97 = 94
CES23 = 91	CES48 = 86	CES73 = 90	CES98 = 92
CES24 = 90	CES49 = 97	CES74 = 87	CES99 = 91
CES25 = 71	CES50 = 94	CES75 = 89	





REPORT NUMBER: SP1-2510-581-8-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2510-581-8-R2

TM-30-18

Measure Comparisons





(END OF REPORT)