Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1559262

Luminaire Tested: 22CGTX-45-B2750-W2D-2700K

Issue Date: 8/30/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1559262
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	8/30/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	22CGTX-45-B2750-W2D-2700K
Description:	2X2 4500 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 2700K CCT WITH FROSTED SMOOTH L
Light Source:	2700K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	4508.0 lumens
Efficiency:	N/A
Efficacy:	101.5 lumens/watt
Spacing Criteria (0/90/45):	1.26 / 1.26 / 1.38
Luminous Opening:	Rectangular (W 1.81' x L: 1.81' x H: 0')
CIE Type:	Direct
Input Watts (W):	44.4
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559262
CATALOG NUMBER: 22CGTX-45-B2750-W2D-2700K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559262
CATALOG NUMBER: 22CGTX-45-B2750-W2D-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	94	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	79	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	44	39	50	44	39	37
7	64	51	42	35	63	50	41	35	48	41	35	47	40	35	45	39	34	32
8	60	46	37	32	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	41	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	26	37	30	25	37	30	25	36	30	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5023	5023	5023
5°	5029	5019	5029
10°	5024	5014	5024
15°	5010	5000	5014
20°	4983	4979	4993
25°	4964	4953	4971
30°	4926	4918	4941
35°	4884	4884	4900
40°	4850	4842	4859
45°	4801	4796	4805
50°	4751	4741	4761
55°	4656	4661	4684
60°	4587	4574	4613
65°	4435	4450	4497
70°	4282	4301	4359
75°	4089	4140	4203
80°	3793	3925	3981
85°	3421	3459	3496

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
Vertical Angle: 45°
Luminance: 4805 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559262
CATALOG NUMBER: 22CGTX-45-B2750-W2D-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.2	3.2
10°-20°	416.4	9.2
20°-30°	632.1	14.0
30°-40°	764.7	17.0
40°-50°	799.1	17.7
50°-60°	730.7	16.2
60°-70°	569.6	12.6
70°-80°	345.5	7.7
80°-90°	104.8	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1193.7	26.5
0°-40°	1958.4	43.4
0°-60°	3488.2	77.4
0°-90°	4508.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4508.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1533	1533	1533	1533	1533	
5°	1529	1527	1526	1527	1529	145
15°	1477	1475	1474	1475	1478	417
25°	1373	1370	1370	1372	1375	632
35°	1221	1222	1221	1223	1225	765
45°	1036	1035	1035	1036	1037	799
55°	815	817	816	818	820	731
65°	572	575	574	578	580	567
75°	323	324	327	329	332	342
85°	91	91	92	93	93	103
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559262
CATALOG NUMBER: 22CGTX-45-B2750-W2D-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*1533*	*1533*	*1533*	*1533*	*1533*
2.5°	*1533*	1531	1530	1532	1533
5°	*1529*	1527	1526	1527	1529
7.5°	*1521*	1520	1518	1520	1522
10°	*1510*	1508	1507	1509	1510
12.5°	*1495*	1493	1492	1494	1496
15°	*1477*	1475	1474	1475	1478
17.5°	*1455*	1454	1453	1454	1457
20°	*1429*	1429	1428	1430	1432
22.5°	*1403*	1401	1400	1403	1404
25°	*1373*	1370	1370	1372	1375
27.5°	*1338*	1338	1337	1339	1341
30°	*1302*	1300	1300	1303	1306
32.5°	*1264*	1262	1261	1264	1265
35°	*1221*	1222	1221	1223	1225
37.5°	*1183*	1177	1178	1180	1181
40°	*1134*	1134	1132	1133	1136
42.5°	*1084*	1086	1086	1086	1088
45°	*1036*	1035	1035	1036	1037
47.5°	*983*	984	984	986	986
50°	*932*	928	930	931	934
52.5°	*877*	873	875	877	879
55°	*815*	817	816	818	820
57.5°	*759*	757	759	761	760
60°	*700*	697	698	699	704
62.5°	*636*	635	638	640	641
65°	*572*	575	574	578	580
67.5°	*510*	512	513	516	517
70°	*447*	448	449	452	455
72.5°	*387*	384	388	391	392
75°	*323*	324	327	329	332
77.5°	*261*	265	268	268	267
80°	*201*	204	208	210	211
82.5°	*147*	146	149	149	154
85°	*91*	91	92	93	93
87.5°	*39*	39	41	43	44
90°	*0*	0	0	0	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1559262
CATALOG NUMBER: 22CGTX-45-B2750-W2D-2700K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.52	19.18	17.88	19.49	19.81	17.55	19.21	17.91	19.52	19.84
	3H	19.42	20.92	19.79	21.25	21.61	19.47	20.98	19.85	21.30	21.66
	4H	20.16	21.58	20.56	21.93	22.30	20.23	21.65	20.63	22.00	22.37
	6H	20.73	22.05	21.14	22.41	22.80	20.82	22.14	21.23	22.50	22.89
	8H	20.93	22.19	21.35	22.58	22.97	21.03	22.29	21.46	22.68	23.08
	12H	21.07	22.28	21.50	22.66	23.09	21.18	22.39	21.61	22.77	23.20
4H	2H	18.18	19.60	18.58	19.95	20.32	18.21	19.63	18.60	19.97	20.35
	3H	20.31	21.51	20.72	21.90	22.30	20.36	21.55	20.77	21.95	22.35
	4H	21.19	22.27	21.62	22.68	23.12	21.25	22.34	21.69	22.75	23.19
	6H	21.90	22.85	22.35	23.29	23.74	21.99	22.94	22.44	23.38	23.83
	8H	22.15	23.04	22.61	23.48	23.95	22.26	23.15	22.71	23.59	24.05
	12H	22.34	23.14	22.82	23.62	24.09	22.45	23.25	22.93	23.73	24.20
8H	4H	21.55	22.44	22.01	22.88	23.34	21.61	22.50	22.07	22.94	23.40
	6H	22.40	23.14	22.89	23.63	24.10	22.48	23.22	22.97	23.71	24.18
	8H	22.73	23.40	23.24	23.90	24.39	22.83	23.50	23.34	24.00	24.49
	12H	23.01	23.60	23.51	24.09	24.65	23.11	23.70	23.62	24.19	24.75
12H	4H	21.60	22.40	22.08	22.87	23.34	21.65	22.45	22.13	22.93	23.40
	6H	22.48	23.14	22.98	23.65	24.13	22.56	23.22	23.06	23.73	24.21
	8H	22.88	23.47	23.38	23.96	24.51	22.97	23.56	23.47	24.05	24.61

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2505-441-28-R2

Test Date: 07/10/2025

Luminaire Tested: 24CGTX-45-B2750-W2D-2700K

Data in this report applies to families of products including 24CGTX


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2505-441-28-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-45-B2750-W2D-2700K**
Description:	*THIS IS A REVISION OF REPORT SP1-2504-441-28-R2 TO UPDATE THE CATALOG INFORMATION* 2X4 4500 LUMEN CGTX. Using WaveLinx PRO F1 sensor.

Spectral Parameters

CCT (K):	2694	CRI (Ra):	95.4		
CIE u':	0.2630	R1:	96.8	R9:	80.8
CIE v':	0.5264	R2:	98.3	R10:	98.3
Duv:	-0.0008	R3:	97.9	R11:	89.1
CIE x:	0.4590	R4:	94.6	R12:	93.4
CIE y:	0.4084	R5:	96.4	R13:	96.9
CIE z:	0.1326	R6:	92.3	R14:	97.1
Peak Wavelength (nm):	630	R7:	94.8	R15:	98.2
Dominant Wavelength (nm):	584	R8:	92.1		
Purity:	60.36523				
Rf:	93.8				
Rg:	102				




Test Conditions

Stabilization Time:	24M
Operation Time:	1H 24M
Sphere Temperature (°C):	24.0


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2505-441-28-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2694K
CIE x = 0.4590
CIE y = 0.4084
Duv = -0.0008

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2505-441-28-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	70	NR	620	228	NR	750	5	NR	880	0	NR
365	0	NR	495	86	NR	625	239	NR	755	4	NR	885	0	NR
370	0	NR	500	100	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	111	NR	635	614	NR	765	3	NR	895	0	NR
380	0	NR	510	118	NR	640	147	NR	770	3	NR	900	0	NR
385	0	NR	515	122	NR	645	148	NR	775	2	NR	905	0	NR
390	0	NR	520	126	NR	650	127	NR	780	2	NR	910	0	NR
395	0	NR	525	128	NR	655	105	NR	785	2	NR	915	0	NR
400	1	NR	530	130	NR	660	88	NR	790	1	NR	920	0	NR
405	1	NR	535	134	NR	665	73	NR	795	1	NR	925	0	NR
410	2	NR	540	139	NR	670	70	NR	800	1	NR	930	0	NR
415	3	NR	545	143	NR	675	55	NR	805	1	NR	935	0	NR
420	6	NR	550	148	NR	680	47	NR	810	1	NR	940	0	NR
425	10	NR	555	154	NR	685	41	NR	815	1	NR	945	0	NR
430	18	NR	560	159	NR	690	35	NR	820	1	NR	950	0	NR
435	28	NR	565	164	NR	695	30	NR	825	1	NR	955	0	NR
440	44	NR	570	169	NR	700	25	NR	830	0	NR	960	0	NR
445	75	NR	575	175	NR	705	22	NR	835	0	NR	965	0	NR
450	107	NR	580	179	NR	710	18	NR	840	0	NR	970	0	NR
455	82	NR	585	186	NR	715	16	NR	845	0	NR	975	0	NR
460	58	NR	590	190	NR	720	13	NR	850	0	NR	980	0	NR
465	53	NR	595	192	NR	725	11	NR	855	0	NR	985	0	NR
470	45	NR	600	198	NR	730	10	NR	860	0	NR	990	0	NR
475	41	NR	605	203	NR	735	8	NR	865	0	NR	995	0	NR
480	46	NR	610	237	NR	740	7	NR	870	0	NR	1000	0	NR
485	57	NR	615	264	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-28-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.34**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	70	NR	620	228	NR	750	5	NR	880	0	NR
365	0	NR	495	86	NR	625	239	NR	755	4	NR	885	0	NR
370	0	NR	500	100	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	111	NR	635	614	NR	765	3	NR	895	0	NR
380	0	NR	510	118	NR	640	147	NR	770	3	NR	900	0	NR
385	0	NR	515	122	NR	645	148	NR	775	2	NR	905	0	NR
390	0	NR	520	126	NR	650	127	NR	780	2	NR	910	0	NR
395	0	NR	525	128	NR	655	105	NR	785	2	NR	915	0	NR
400	1	NR	530	130	NR	660	88	NR	790	1	NR	920	0	NR
405	1	NR	535	134	NR	665	73	NR	795	1	NR	925	0	NR
410	2	NR	540	139	NR	670	70	NR	800	1	NR	930	0	NR
415	3	NR	545	143	NR	675	55	NR	805	1	NR	935	0	NR
420	6	NR	550	148	NR	680	47	NR	810	1	NR	940	0	NR
425	10	NR	555	154	NR	685	41	NR	815	1	NR	945	0	NR
430	18	NR	560	159	NR	690	35	NR	820	1	NR	950	0	NR
435	28	NR	565	164	NR	695	30	NR	825	1	NR	955	0	NR
440	44	NR	570	169	NR	700	25	NR	830	0	NR	960	0	NR
445	75	NR	575	175	NR	705	22	NR	835	0	NR	965	0	NR
450	107	NR	580	179	NR	710	18	NR	840	0	NR	970	0	NR
455	82	NR	585	186	NR	715	16	NR	845	0	NR	975	0	NR
460	58	NR	590	190	NR	720	13	NR	850	0	NR	980	0	NR
465	53	NR	595	192	NR	725	11	NR	855	0	NR	985	0	NR
470	45	NR	600	198	NR	730	10	NR	860	0	NR	990	0	NR
475	41	NR	605	203	NR	735	8	NR	865	0	NR	995	0	NR
480	46	NR	610	237	NR	740	7	NR	870	0	NR	1000	0	NR
485	57	NR	615	264	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-28-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.58**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	70	NR	620	228	NR	750	5	NR	880	0	NR
365	0	NR	495	86	NR	625	239	NR	755	4	NR	885	0	NR
370	0	NR	500	100	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	111	NR	635	614	NR	765	3	NR	895	0	NR
380	0	NR	510	118	NR	640	147	NR	770	3	NR	900	0	NR
385	0	NR	515	122	NR	645	148	NR	775	2	NR	905	0	NR
390	0	NR	520	126	NR	650	127	NR	780	2	NR	910	0	NR
395	0	NR	525	128	NR	655	105	NR	785	2	NR	915	0	NR
400	1	NR	530	130	NR	660	88	NR	790	1	NR	920	0	NR
405	1	NR	535	134	NR	665	73	NR	795	1	NR	925	0	NR
410	2	NR	540	139	NR	670	70	NR	800	1	NR	930	0	NR
415	3	NR	545	143	NR	675	55	NR	805	1	NR	935	0	NR
420	6	NR	550	148	NR	680	47	NR	810	1	NR	940	0	NR
425	10	NR	555	154	NR	685	41	NR	815	1	NR	945	0	NR
430	18	NR	560	159	NR	690	35	NR	820	1	NR	950	0	NR
435	28	NR	565	164	NR	695	30	NR	825	1	NR	955	0	NR
440	44	NR	570	169	NR	700	25	NR	830	0	NR	960	0	NR
445	75	NR	575	175	NR	705	22	NR	835	0	NR	965	0	NR
450	107	NR	580	179	NR	710	18	NR	840	0	NR	970	0	NR
455	82	NR	585	186	NR	715	16	NR	845	0	NR	975	0	NR
460	58	NR	590	190	NR	720	13	NR	850	0	NR	980	0	NR
465	53	NR	595	192	NR	725	11	NR	855	0	NR	985	0	NR
470	45	NR	600	198	NR	730	10	NR	860	0	NR	990	0	NR
475	41	NR	605	203	NR	735	8	NR	865	0	NR	995	0	NR
480	46	NR	610	237	NR	740	7	NR	870	0	NR	1000	0	NR
485	57	NR	615	264	NR	745	6	NR	875	0	NR			


REPORT NUMBER: SP1-2505-441-28-R2

TM-30-18


Summary


R_f = 93.8
R_g = 102
CIE R_a = 95.4
R_9 = 80.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2505-441-28-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 99	CES51 = 93	CES76 = 96
CES02 = 64	CES27 = 95	CES52 = 93	CES77 = 79
CES03 = 32	CES28 = 100	CES53 = 93	CES78 = 92
CES04 = 70	CES29 = 97	CES54 = 96	CES79 = 84
CES05 = 52	CES30 = 100	CES55 = 96	CES80 = 89
CES06 = 51	CES31 = 98	CES56 = 95	CES81 = 65
CES07 = 45	CES32 = 90	CES57 = 95	CES82 = 95
CES08 = 43	CES33 = 96	CES58 = 94	CES83 = 91
CES09 = 29	CES34 = 99	CES59 = 97	CES84 = 98
CES10 = 77	CES35 = 99	CES60 = 96	CES85 = 80
CES11 = 59	CES36 = 90	CES61 = 96	CES86 = 78
CES12 = 66	CES37 = 96	CES62 = 92	CES87 = 95
CES13 = 45	CES38 = 96	CES63 = 97	CES88 = 99
CES14 = 74	CES39 = 97	CES64 = 95	CES89 = 85
CES15 = 72	CES40 = 95	CES65 = 98	CES90 = 98
CES16 = 49	CES41 = 94	CES66 = 96	CES91 = 86
CES17 = 50	CES42 = 93	CES67 = 96	CES92 = 83
CES18 = 57	CES43 = 95	CES68 = 97	CES93 = 90
CES19 = 72	CES44 = 99	CES69 = 97	CES94 = 77
CES20 = 68	CES45 = 95	CES70 = 97	CES95 = 90
CES21 = 87	CES46 = 96	CES71 = 96	CES96 = 96
CES22 = 79	CES47 = 82	CES72 = 98	CES97 = 93
CES23 = 92	CES48 = 99	CES73 = 94	CES98 = 97
CES24 = 91	CES49 = 94	CES74 = 86	CES99 = 96
CES25 = 72	CES50 = 94	CES75 = 96	





REPORT NUMBER: SP1-2505-441-28-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2505-441-28-R2

TM-30-18

Measure Comparisons





(END OF REPORT)