Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1559316

Luminaire Tested: 24CGTX-72-B2750-W2D2-2700K

Issue Date: 9/3/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1559316
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/3/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	24CGTX-72-B2750-W2D2-2700K
Description:	2X4 7200 LUMEN CGTX TROFFER WITH BIO UP LEDS AT 2700K CCT WITH FROSTED SMOOTH L
Light Source:	2700K CCT, 80 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	7277.2 lumens
Efficiency:	N/A
Efficacy:	106.7 lumens/watt
Spacing Criteria (0/90/45):	1.29 / 1.28 / 1.4
Luminous Opening:	Rectangular (W 1.81' x L: 3.83' x H: 0')
CIE Type:	Direct
Input Watts (W):	68.2
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559316
CATALOG NUMBER: 24CGTX-72-B2750-W2D2-2700K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559316
CATALOG NUMBER: 24CGTX-72-B2750-W2D2-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	98	94	105	101	97	93	96	93	90	92	90	87	89	87	84	82
2	98	89	82	76	95	87	81	75	84	78	73	80	76	72	77	74	70	68
3	89	78	70	63	86	76	69	62	73	67	61	71	65	60	68	63	59	57
4	81	69	60	53	79	68	59	53	65	58	52	63	56	51	60	55	50	48
5	75	61	52	45	73	60	52	45	58	50	45	56	49	44	54	48	44	41
6	69	55	46	39	67	54	46	39	52	45	39	51	44	39	49	43	38	36
7	64	50	41	35	62	49	41	35	48	40	34	46	39	34	45	39	34	32
8	59	46	37	31	58	45	37	31	44	36	31	42	35	30	41	35	30	28
9	55	42	33	28	54	41	33	28	40	33	28	39	32	27	38	32	27	25
10	52	39	30	25	51	38	30	25	37	30	25	36	29	25	35	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3686	3686	3686
5°	3707	3690	3695
10°	3709	3694	3700
15°	3708	3695	3702
20°	3708	3693	3703
25°	3701	3687	3697
30°	3690	3678	3682
35°	3679	3665	3667
40°	3665	3648	3650
45°	3650	3628	3628
50°	3618	3608	3608
55°	3587	3573	3568
60°	3551	3535	3507
65°	3501	3486	3464
70°	3465	3411	3356
75°	3364	3334	3286
80°	3337	3256	3221
85°	3342	3217	3164

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
Vertical Angle: 87.5°
Luminance: 3836 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559316
CATALOG NUMBER: 24CGTX-72-B2750-W2D2-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	225.9	3.1
10°-20°	651.1	8.9
20°-30°	995.2	13.7
30°-40°	1213.1	16.7
40°-50°	1278.7	17.6
50°-60°	1183.4	16.3
60°-70°	939.2	12.9
70°-80°	588.6	8.1
80°-90°	202.0	2.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1872.2	25.7
0°-40°	3085.3	42.4
0°-60°	5547.4	76.2
0°-90°	7277.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7277.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2379	2379	2379	2379	2379	
5°	2384	2376	2373	2371	2376	227
15°	2312	2306	2304	2302	2308	653
25°	2165	2158	2157	2156	2163	998
35°	1945	1940	1938	1937	1939	1216
45°	1666	1658	1656	1654	1656	1283
55°	1328	1327	1323	1321	1321	1189
65°	955	952	951	944	945	945
75°	562	562	557	551	549	597
85°	188	184	181	180	178	204
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1559316
CATALOG NUMBER: 24CGTX-72-B2750-W2D2-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2379	2379	2379	2379	2379
2.5°	2388	2381	2378	2376	2381
5°	2384	2376	2373	2371	2376
7.5°	2374	2366	2364	2362	2368
10°	2358	2351	2348	2348	2352
12.5°	2338	2331	2329	2327	2333
15°	2312	2306	2304	2302	2308
17.5°	2283	2277	2275	2274	2279
20°	2249	2241	2240	2241	2246
22.5°	2209	2202	2201	2201	2206
25°	2165	2158	2157	2156	2163
27.5°	2117	2110	2109	2108	2111
30°	2063	2057	2056	2055	2058
32.5°	2005	2000	1998	1996	2002
35°	1945	1940	1938	1937	1939
37.5°	1878	1876	1873	1872	1872
40°	1812	1807	1804	1803	1805
42.5°	1737	1736	1734	1731	1733
45°	1666	1658	1656	1654	1656
47.5°	1584	1578	1578	1575	1579
50°	1501	1502	1497	1494	1497
52.5°	1422	1415	1411	1410	1408
55°	1328	1327	1323	1321	1321
57.5°	1242	1237	1236	1229	1231
60°	1146	1142	1141	1136	1132
62.5°	1050	1050	1050	1040	1042
65°	955	952	951	944	945
67.5°	858	859	851	848	847
70°	765	757	753	749	741
72.5°	663	661	657	649	643
75°	562	562	557	551	549
77.5°	467	462	463	457	452
80°	374	368	365	363	361
82.5°	278	277	274	271	269
85°	188	184	181	180	178
87.5°	97	102	103	107	108
90°	0	0	0	0	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1559316
CATALOG NUMBER: 24CGTX-72-B2750-W2D2-2700K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.65	18.32	17.01	18.64	18.95	16.60	18.27	16.96	18.59	18.90
	3H	18.65	20.17	19.02	20.50	20.85	18.57	20.09	18.95	20.42	20.78
	4H	19.45	20.89	19.85	21.24	21.61	19.36	20.79	19.75	21.14	21.51
	6H	20.11	21.45	20.52	21.81	22.20	20.00	21.33	20.41	21.70	22.09
	8H	20.36	21.64	20.78	22.03	22.42	20.24	21.52	20.66	21.90	22.30
	12H	20.56	21.78	20.98	22.16	22.59	20.42	21.65	20.85	22.03	22.46
4H	2H	17.33	18.77	17.73	19.11	19.49	17.29	18.73	17.69	19.08	19.45
	3H	19.56	20.77	19.97	21.17	21.57	19.49	20.71	19.90	21.10	21.50
	4H	20.51	21.61	20.94	22.02	22.46	20.42	21.52	20.85	21.93	22.37
	6H	21.31	22.28	21.77	22.72	23.17	21.21	22.18	21.66	22.62	23.07
	8H	21.63	22.53	22.08	22.97	23.44	21.51	22.42	21.97	22.86	23.32
	12H	21.88	22.70	22.36	23.18	23.64	21.76	22.58	22.24	23.05	23.52
8H	4H	20.88	21.79	21.34	22.23	22.70	20.81	21.72	21.27	22.16	22.62
	6H	21.84	22.60	22.33	23.09	23.56	21.75	22.51	22.24	23.00	23.47
	8H	22.25	22.93	22.76	23.44	23.92	22.15	22.83	22.66	23.34	23.82
	12H	22.61	23.22	23.12	23.71	24.26	22.50	23.10	23.00	23.59	24.15
12H	4H	20.94	21.76	21.42	22.23	22.70	20.87	21.69	21.35	22.16	22.63
	6H	21.93	22.61	22.44	23.12	23.60	21.84	22.53	22.35	23.03	23.52
	8H	22.41	23.02	22.92	23.51	24.06	22.32	22.92	22.82	23.41	23.97

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2505-441-28-R2

Test Date: 07/10/2025

Luminaire Tested: 24CGTX-45-B2750-W2D-2700K

Data in this report applies to families of products including 24CGTX


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2505-441-28-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**24CGTX-45-B2750-W2D-2700K**
Description:	*THIS IS A REVISION OF REPORT SP1-2504-441-28-R2 TO UPDATE THE CATALOG INFORMATION* 2X4 4500 LUMEN CGTX. Using WaveLinx PRO F1 sensor.

Spectral Parameters

CCT (K):	2694	CRI (Ra):	95.4		
CIE u':	0.2630	R1:	96.8	R9:	80.8
CIE v':	0.5264	R2:	98.3	R10:	98.3
Duv:	-0.0008	R3:	97.9	R11:	89.1
CIE x:	0.4590	R4:	94.6	R12:	93.4
CIE y:	0.4084	R5:	96.4	R13:	96.9
CIE z:	0.1326	R6:	92.3	R14:	97.1
Peak Wavelength (nm):	630	R7:	94.8	R15:	98.2
Dominant Wavelength (nm):	584	R8:	92.1		
Purity:	60.36523				
Rf:	93.8				
Rg:	102				




Test Conditions

Stabilization Time:	24M
Operation Time:	1H 24M
Sphere Temperature (°C):	24.0


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2505-441-28-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2694K
CIE x = 0.4590
CIE y = 0.4084
Duv = -0.0008

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2505-441-28-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	70	NR	620	228	NR	750	5	NR	880	0	NR
365	0	NR	495	86	NR	625	239	NR	755	4	NR	885	0	NR
370	0	NR	500	100	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	111	NR	635	614	NR	765	3	NR	895	0	NR
380	0	NR	510	118	NR	640	147	NR	770	3	NR	900	0	NR
385	0	NR	515	122	NR	645	148	NR	775	2	NR	905	0	NR
390	0	NR	520	126	NR	650	127	NR	780	2	NR	910	0	NR
395	0	NR	525	128	NR	655	105	NR	785	2	NR	915	0	NR
400	1	NR	530	130	NR	660	88	NR	790	1	NR	920	0	NR
405	1	NR	535	134	NR	665	73	NR	795	1	NR	925	0	NR
410	2	NR	540	139	NR	670	70	NR	800	1	NR	930	0	NR
415	3	NR	545	143	NR	675	55	NR	805	1	NR	935	0	NR
420	6	NR	550	148	NR	680	47	NR	810	1	NR	940	0	NR
425	10	NR	555	154	NR	685	41	NR	815	1	NR	945	0	NR
430	18	NR	560	159	NR	690	35	NR	820	1	NR	950	0	NR
435	28	NR	565	164	NR	695	30	NR	825	1	NR	955	0	NR
440	44	NR	570	169	NR	700	25	NR	830	0	NR	960	0	NR
445	75	NR	575	175	NR	705	22	NR	835	0	NR	965	0	NR
450	107	NR	580	179	NR	710	18	NR	840	0	NR	970	0	NR
455	82	NR	585	186	NR	715	16	NR	845	0	NR	975	0	NR
460	58	NR	590	190	NR	720	13	NR	850	0	NR	980	0	NR
465	53	NR	595	192	NR	725	11	NR	855	0	NR	985	0	NR
470	45	NR	600	198	NR	730	10	NR	860	0	NR	990	0	NR
475	41	NR	605	203	NR	735	8	NR	865	0	NR	995	0	NR
480	46	NR	610	237	NR	740	7	NR	870	0	NR	1000	0	NR
485	57	NR	615	264	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-28-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.34**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	70	NR	620	228	NR	750	5	NR	880	0	NR
365	0	NR	495	86	NR	625	239	NR	755	4	NR	885	0	NR
370	0	NR	500	100	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	111	NR	635	614	NR	765	3	NR	895	0	NR
380	0	NR	510	118	NR	640	147	NR	770	3	NR	900	0	NR
385	0	NR	515	122	NR	645	148	NR	775	2	NR	905	0	NR
390	0	NR	520	126	NR	650	127	NR	780	2	NR	910	0	NR
395	0	NR	525	128	NR	655	105	NR	785	2	NR	915	0	NR
400	1	NR	530	130	NR	660	88	NR	790	1	NR	920	0	NR
405	1	NR	535	134	NR	665	73	NR	795	1	NR	925	0	NR
410	2	NR	540	139	NR	670	70	NR	800	1	NR	930	0	NR
415	3	NR	545	143	NR	675	55	NR	805	1	NR	935	0	NR
420	6	NR	550	148	NR	680	47	NR	810	1	NR	940	0	NR
425	10	NR	555	154	NR	685	41	NR	815	1	NR	945	0	NR
430	18	NR	560	159	NR	690	35	NR	820	1	NR	950	0	NR
435	28	NR	565	164	NR	695	30	NR	825	1	NR	955	0	NR
440	44	NR	570	169	NR	700	25	NR	830	0	NR	960	0	NR
445	75	NR	575	175	NR	705	22	NR	835	0	NR	965	0	NR
450	107	NR	580	179	NR	710	18	NR	840	0	NR	970	0	NR
455	82	NR	585	186	NR	715	16	NR	845	0	NR	975	0	NR
460	58	NR	590	190	NR	720	13	NR	850	0	NR	980	0	NR
465	53	NR	595	192	NR	725	11	NR	855	0	NR	985	0	NR
470	45	NR	600	198	NR	730	10	NR	860	0	NR	990	0	NR
475	41	NR	605	203	NR	735	8	NR	865	0	NR	995	0	NR
480	46	NR	610	237	NR	740	7	NR	870	0	NR	1000	0	NR
485	57	NR	615	264	NR	745	6	NR	875	0	NR			

REPORT NUMBER: SP1-2505-441-28-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.58**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	70	NR	620	228	NR	750	5	NR	880	0	NR
365	0	NR	495	86	NR	625	239	NR	755	4	NR	885	0	NR
370	0	NR	500	100	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	111	NR	635	614	NR	765	3	NR	895	0	NR
380	0	NR	510	118	NR	640	147	NR	770	3	NR	900	0	NR
385	0	NR	515	122	NR	645	148	NR	775	2	NR	905	0	NR
390	0	NR	520	126	NR	650	127	NR	780	2	NR	910	0	NR
395	0	NR	525	128	NR	655	105	NR	785	2	NR	915	0	NR
400	1	NR	530	130	NR	660	88	NR	790	1	NR	920	0	NR
405	1	NR	535	134	NR	665	73	NR	795	1	NR	925	0	NR
410	2	NR	540	139	NR	670	70	NR	800	1	NR	930	0	NR
415	3	NR	545	143	NR	675	55	NR	805	1	NR	935	0	NR
420	6	NR	550	148	NR	680	47	NR	810	1	NR	940	0	NR
425	10	NR	555	154	NR	685	41	NR	815	1	NR	945	0	NR
430	18	NR	560	159	NR	690	35	NR	820	1	NR	950	0	NR
435	28	NR	565	164	NR	695	30	NR	825	1	NR	955	0	NR
440	44	NR	570	169	NR	700	25	NR	830	0	NR	960	0	NR
445	75	NR	575	175	NR	705	22	NR	835	0	NR	965	0	NR
450	107	NR	580	179	NR	710	18	NR	840	0	NR	970	0	NR
455	82	NR	585	186	NR	715	16	NR	845	0	NR	975	0	NR
460	58	NR	590	190	NR	720	13	NR	850	0	NR	980	0	NR
465	53	NR	595	192	NR	725	11	NR	855	0	NR	985	0	NR
470	45	NR	600	198	NR	730	10	NR	860	0	NR	990	0	NR
475	41	NR	605	203	NR	735	8	NR	865	0	NR	995	0	NR
480	46	NR	610	237	NR	740	7	NR	870	0	NR	1000	0	NR
485	57	NR	615	264	NR	745	6	NR	875	0	NR			


REPORT NUMBER: SP1-2505-441-28-R2

TM-30-18


Summary


R_f = 93.8
R_g = 102
CIE R_a = 95.4
R_9 = 80.8


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2505-441-28-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 99	CES51 = 93	CES76 = 96
CES02 = 64	CES27 = 95	CES52 = 93	CES77 = 79
CES03 = 32	CES28 = 100	CES53 = 93	CES78 = 92
CES04 = 70	CES29 = 97	CES54 = 96	CES79 = 84
CES05 = 52	CES30 = 100	CES55 = 96	CES80 = 89
CES06 = 51	CES31 = 98	CES56 = 95	CES81 = 65
CES07 = 45	CES32 = 90	CES57 = 95	CES82 = 95
CES08 = 43	CES33 = 96	CES58 = 94	CES83 = 91
CES09 = 29	CES34 = 99	CES59 = 97	CES84 = 98
CES10 = 77	CES35 = 99	CES60 = 96	CES85 = 80
CES11 = 59	CES36 = 90	CES61 = 96	CES86 = 78
CES12 = 66	CES37 = 96	CES62 = 92	CES87 = 95
CES13 = 45	CES38 = 96	CES63 = 97	CES88 = 99
CES14 = 74	CES39 = 97	CES64 = 95	CES89 = 85
CES15 = 72	CES40 = 95	CES65 = 98	CES90 = 98
CES16 = 49	CES41 = 94	CES66 = 96	CES91 = 86
CES17 = 50	CES42 = 93	CES67 = 96	CES92 = 83
CES18 = 57	CES43 = 95	CES68 = 97	CES93 = 90
CES19 = 72	CES44 = 99	CES69 = 97	CES94 = 77
CES20 = 68	CES45 = 95	CES70 = 97	CES95 = 90
CES21 = 87	CES46 = 96	CES71 = 96	CES96 = 96
CES22 = 79	CES47 = 82	CES72 = 98	CES97 = 93
CES23 = 92	CES48 = 99	CES73 = 94	CES98 = 97
CES24 = 91	CES49 = 94	CES74 = 86	CES99 = 96
CES25 = 72	CES50 = 94	CES75 = 96	





REPORT NUMBER: SP1-2505-441-28-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2505-441-28-R2

TM-30-18

Measure Comparisons





(END OF REPORT)