Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590704

Luminaire Tested: 14CGTX-30-L92765-W2A-2700K

Issue Date: 9/7/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590704
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/7/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	14CGTX-30-L92765-W2A-2700K
Description:	1X4 3000 LUMEN CGTX TROFFER WITH VividTune LEDS AT 2700K CCT WITH FROSTED SMOOTH LENS
Light Source:	2700K CCT, 90 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	2959.1 lumens
Efficiency:	N/A
Efficacy:	100.3 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.27 / 1.39
Luminous Opening:	Rectangular (W 0.83' x L: 3.83' x H: 0')
CIE Type:	Direct
Input Watts (W):	29.5
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590704
CATALOG NUMBER: 14CGTX-30-L92765-W2A-2700K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590704
CATALOG NUMBER: 14CGTX-30-L92765-W2A-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	94	97	94	91	93	90	88	89	87	85	83
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69
3	90	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	45	39	50	44	39	37
7	64	51	42	36	63	50	41	35	48	41	35	47	40	35	45	39	35	33
8	60	46	38	32	58	45	37	32	44	37	31	43	36	31	42	36	31	29
9	56	42	34	28	54	42	34	28	41	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	39	31	26	38	30	26	37	30	25	36	30	25	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3380	3380	3380
5°	3386	3376	3389
10°	3394	3387	3404
15°	3387	3380	3398
20°	3374	3371	3381
25°	3354	3354	3361
30°	3338	3338	3338
35°	3324	3311	3311
40°	3290	3286	3277
45°	3264	3255	3236
50°	3224	3213	3182
55°	3172	3149	3119
60°	3113	3087	3053
65°	3038	2998	2958
70°	2956	2896	2818
75°	2812	2760	2669
80°	2639	2600	2484
85°	2358	2281	2126

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3264 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590704
CATALOG NUMBER: 14CGTX-30-L92765-W2A-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.2	3.2
10°-20°	274.1	9.3
20°-30°	416.4	14.1
30°-40°	504.1	17.0
40°-50°	526.1	17.8
50°-60°	479.8	16.2
60°-70°	372.5	12.6
70°-80°	224.0	7.6
80°-90°	66.8	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	785.7	26.6
0°-40°	1289.8	43.6
0°-60°	2295.7	77.6
0°-90°	2959.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2959.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1003	1003	1003	1003	1003	
5°	1001	1001	998	1002	1002	95
15°	971	971	969	973	974	274
25°	902	904	902	904	904	416
35°	808	808	805	806	805	505
45°	685	685	683	680	679	528
55°	540	541	536	535	531	483
65°	381	381	376	373	371	378
75°	216	216	212	206	205	230
85°	61	61	59	57	55	70
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590704
CATALOG NUMBER: 14CGTX-30-L92765-W2A-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1003	1003	1003	1003	*1003*
2.5°	*1003*	*1003*	*1000*	*1004*	*1005*
5°	1001	1001	998	1002	*1002*
7.5°	997	997	994	998	*999*
10°	992	992	990	994	*995*
12.5°	981	982	979	983	*984*
15°	971	971	969	973	*974*
17.5°	957	957	956	959	*959*
20°	941	941	940	943	*943*
22.5°	923	923	922	925	*925*
25°	902	904	902	904	*904*
27.5°	881	882	881	883	*882*
30°	858	858	858	858	*858*
32.5°	833	834	832	832	*832*
35°	808	808	805	806	*805*
37.5°	779	778	777	777	*775*
40°	748	748	747	745	*745*
42.5°	718	718	716	713	*712*
45°	685	685	683	680	*679*
47.5°	649	652	646	645	*642*
50°	615	616	613	609	*607*
52.5°	578	579	575	572	*569*
55°	540	541	536	535	*531*
57.5°	503	503	499	495	*491*
60°	462	462	458	453	*453*
62.5°	422	422	418	413	*411*
65°	381	381	376	373	*371*
67.5°	342	340	337	331	*329*
70°	300	299	294	289	*286*
72.5°	260	257	253	248	*245*
75°	216	216	212	206	*205*
77.5°	178	176	173	167	*167*
80°	136	136	134	129	*128*
82.5°	101	99	95	93	*90*
85°	61	61	59	57	*55*
87.5°	27	26	24	24	*24*
90°	0	0	0	0	*0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590704
CATALOG NUMBER: 14CGTX-30-L92765-W2A-2700K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.24	17.89	16.60	18.21	18.52	16.11	17.77	16.48	18.09	18.40
	3H	18.16	19.66	18.53	19.98	20.34	17.98	19.48	18.35	19.81	20.16
	4H	18.90	20.32	19.30	20.67	21.04	18.69	20.11	19.09	20.45	20.83
	6H	19.49	20.81	19.90	21.17	21.56	19.24	20.56	19.65	20.92	21.31
	8H	19.70	20.96	20.12	21.34	21.74	19.43	20.68	19.85	21.07	21.47
	12H	19.84	21.05	20.27	21.43	21.86	19.55	20.76	19.98	21.14	21.57
4H	2H	16.88	18.30	17.28	18.64	19.02	16.78	18.20	17.18	18.55	18.92
	3H	19.03	20.22	19.44	20.62	21.02	18.87	20.07	19.28	20.46	20.86
	4H	19.92	21.00	20.35	21.41	21.85	19.72	20.80	20.15	21.21	21.65
	6H	20.64	21.59	21.10	22.03	22.48	20.41	21.35	20.86	21.79	22.25
	8H	20.91	21.79	21.37	22.24	22.70	20.64	21.53	21.10	21.97	22.44
	12H	21.10	21.90	21.58	22.38	22.84	20.81	21.61	21.29	22.09	22.56
8H	4H	20.26	21.14	20.71	21.58	22.05	20.08	20.97	20.54	21.41	21.87
	6H	21.12	21.86	21.61	22.35	22.82	20.90	21.64	21.40	22.13	22.60
	8H	21.47	22.13	21.98	22.64	23.12	21.22	21.89	21.73	22.39	22.88
	12H	21.75	22.34	22.26	22.83	23.39	21.47	22.06	21.98	22.55	23.11
12H	4H	20.30	21.10	20.78	21.57	22.04	20.13	20.93	20.61	21.40	21.87
	6H	21.19	21.85	21.69	22.36	22.84	20.98	21.65	21.49	22.15	22.64
	8H	21.60	22.19	22.11	22.68	23.24	21.36	21.95	21.87	22.44	23.00

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2510-566-2-R2

Test Date: 10/14/2025

Luminaire Tested: 22CGTX-50-L92765-W2A-2700K

Data in this report applies to families of products including 22CGTX


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2510-566-2-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**22CGTX-50-L92765-W2A-2700K**
Description:	*THIS IS A REVISION OF REPORT SP1-2512-566-2-R2 TO UPDATE THE CATALOG INFORMATION* 2X2 50000 Lumen CGTX TUNABLE WHITE FROM 2700K TO 6500K - 9.5V

Spectral Parameters

CCT (K):	2769	CRI (Ra):	93.3		
CIE u':	0.2597	R1:	95.3	R9:	56.5
CIE v':	0.5252	R2:	96.1	R10:	89.8
Duv:	-0.0006	R3:	96.0	R11:	95.2
CIE x:	0.4534	R4:	94.8	R12:	89.7
CIE y:	0.4074	R5:	94.9	R13:	95.3
CIE z:	0.1392	R6:	97.1	R14:	96.4
Peak Wavelength (nm):	630	R7:	91.2	R15:	89.6
Dominant Wavelength (nm):	584	R8:	81.4		
Purity:	58.37672				
Rf:	89.8				
Rg:	102.5				



Test Conditions


Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.0

REPORT NUMBER: SP1-2510-566-2-R2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2510-566-2-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2769K
CIE x = 0.4534
CIE y = 0.4074
Duv = -0.0006

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2510-566-2-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	74	NR	620	290	NR	750	7	NR	880	0	NR
365	0	NR	495	94	NR	625	297	NR	755	6	NR	885	0	NR
370	0	NR	500	113	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	130	NR	635	606	NR	765	4	NR	895	0	NR
380	0	NR	510	143	NR	640	189	NR	770	3	NR	900	0	NR
385	0	NR	515	154	NR	645	190	NR	775	3	NR	905	0	NR
390	1	NR	520	162	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	166	NR	655	134	NR	785	2	NR	915	0	NR
400	2	NR	530	171	NR	660	114	NR	790	2	NR	920	0	NR
405	3	NR	535	176	NR	665	96	NR	795	2	NR	925	0	NR
410	4	NR	540	182	NR	670	89	NR	800	1	NR	930	0	NR
415	7	NR	545	187	NR	675	72	NR	805	1	NR	935	0	NR
420	14	NR	550	194	NR	680	62	NR	810	1	NR	940	0	NR
425	23	NR	555	202	NR	685	53	NR	815	1	NR	945	0	NR
430	38	NR	560	210	NR	690	46	NR	820	1	NR	950	0	NR
435	63	NR	565	219	NR	695	39	NR	825	1	NR	955	0	NR
440	102	NR	570	228	NR	700	33	NR	830	1	NR	960	0	NR
445	144	NR	575	238	NR	705	28	NR	835	1	NR	965	0	NR
450	128	NR	580	247	NR	710	24	NR	840	0	NR	970	0	NR
455	83	NR	585	257	NR	715	20	NR	845	0	NR	975	0	NR
460	68	NR	590	264	NR	720	18	NR	850	0	NR	980	0	NR
465	55	NR	595	267	NR	725	15	NR	855	0	NR	985	0	NR
470	43	NR	600	273	NR	730	13	NR	860	0	NR	990	0	NR
475	42	NR	605	278	NR	735	11	NR	865	0	NR	995	0	NR
480	47	NR	610	311	NR	740	9	NR	870	0	NR	1000	0	NR
485	58	NR	615	333	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2510-566-2-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.3**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	74	NR	620	290	NR	750	7	NR	880	0	NR
365	0	NR	495	94	NR	625	297	NR	755	6	NR	885	0	NR
370	0	NR	500	113	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	130	NR	635	606	NR	765	4	NR	895	0	NR
380	0	NR	510	143	NR	640	189	NR	770	3	NR	900	0	NR
385	0	NR	515	154	NR	645	190	NR	775	3	NR	905	0	NR
390	1	NR	520	162	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	166	NR	655	134	NR	785	2	NR	915	0	NR
400	2	NR	530	171	NR	660	114	NR	790	2	NR	920	0	NR
405	3	NR	535	176	NR	665	96	NR	795	2	NR	925	0	NR
410	4	NR	540	182	NR	670	89	NR	800	1	NR	930	0	NR
415	7	NR	545	187	NR	675	72	NR	805	1	NR	935	0	NR
420	14	NR	550	194	NR	680	62	NR	810	1	NR	940	0	NR
425	23	NR	555	202	NR	685	53	NR	815	1	NR	945	0	NR
430	38	NR	560	210	NR	690	46	NR	820	1	NR	950	0	NR
435	63	NR	565	219	NR	695	39	NR	825	1	NR	955	0	NR
440	102	NR	570	228	NR	700	33	NR	830	1	NR	960	0	NR
445	144	NR	575	238	NR	705	28	NR	835	1	NR	965	0	NR
450	128	NR	580	247	NR	710	24	NR	840	0	NR	970	0	NR
455	83	NR	585	257	NR	715	20	NR	845	0	NR	975	0	NR
460	68	NR	590	264	NR	720	18	NR	850	0	NR	980	0	NR
465	55	NR	595	267	NR	725	15	NR	855	0	NR	985	0	NR
470	43	NR	600	273	NR	730	13	NR	860	0	NR	990	0	NR
475	42	NR	605	278	NR	735	11	NR	865	0	NR	995	0	NR
480	47	NR	610	311	NR	740	9	NR	870	0	NR	1000	0	NR
485	58	NR	615	333	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2510-566-2-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.45**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	74	NR	620	290	NR	750	7	NR	880	0	NR
365	0	NR	495	94	NR	625	297	NR	755	6	NR	885	0	NR
370	0	NR	500	113	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	130	NR	635	606	NR	765	4	NR	895	0	NR
380	0	NR	510	143	NR	640	189	NR	770	3	NR	900	0	NR
385	0	NR	515	154	NR	645	190	NR	775	3	NR	905	0	NR
390	1	NR	520	162	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	166	NR	655	134	NR	785	2	NR	915	0	NR
400	2	NR	530	171	NR	660	114	NR	790	2	NR	920	0	NR
405	3	NR	535	176	NR	665	96	NR	795	2	NR	925	0	NR
410	4	NR	540	182	NR	670	89	NR	800	1	NR	930	0	NR
415	7	NR	545	187	NR	675	72	NR	805	1	NR	935	0	NR
420	14	NR	550	194	NR	680	62	NR	810	1	NR	940	0	NR
425	23	NR	555	202	NR	685	53	NR	815	1	NR	945	0	NR
430	38	NR	560	210	NR	690	46	NR	820	1	NR	950	0	NR
435	63	NR	565	219	NR	695	39	NR	825	1	NR	955	0	NR
440	102	NR	570	228	NR	700	33	NR	830	1	NR	960	0	NR
445	144	NR	575	238	NR	705	28	NR	835	1	NR	965	0	NR
450	128	NR	580	247	NR	710	24	NR	840	0	NR	970	0	NR
455	83	NR	585	257	NR	715	20	NR	845	0	NR	975	0	NR
460	68	NR	590	264	NR	720	18	NR	850	0	NR	980	0	NR
465	55	NR	595	267	NR	725	15	NR	855	0	NR	985	0	NR
470	43	NR	600	273	NR	730	13	NR	860	0	NR	990	0	NR
475	42	NR	605	278	NR	735	11	NR	865	0	NR	995	0	NR
480	47	NR	610	311	NR	740	9	NR	870	0	NR	1000	0	NR
485	58	NR	615	333	NR	745	8	NR	875	0	NR			


REPORT NUMBER: SP1-2510-566-2-R2

TM-30-18


Summary


R_f = 89.8
R_g = 102.5
CIE R_a = 93.3
R_9 = 56.5


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2510-566-2-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 88	CES51 = 92	CES76 = 89
CES02 = 64	CES27 = 97	CES52 = 93	CES77 = 85
CES03 = 32	CES28 = 95	CES53 = 88	CES78 = 86
CES04 = 70	CES29 = 83	CES54 = 96	CES79 = 89
CES05 = 51	CES30 = 84	CES55 = 95	CES80 = 91
CES06 = 51	CES31 = 85	CES56 = 89	CES81 = 70
CES07 = 44	CES32 = 80	CES57 = 87	CES82 = 96
CES08 = 43	CES33 = 83	CES58 = 88	CES83 = 92
CES09 = 29	CES34 = 91	CES59 = 98	CES84 = 97
CES10 = 77	CES35 = 95	CES60 = 99	CES85 = 82
CES11 = 59	CES36 = 99	CES61 = 99	CES86 = 75
CES12 = 66	CES37 = 93	CES62 = 91	CES87 = 91
CES13 = 44	CES38 = 88	CES63 = 89	CES88 = 93
CES14 = 74	CES39 = 95	CES64 = 93	CES89 = 80
CES15 = 72	CES40 = 91	CES65 = 90	CES90 = 92
CES16 = 48	CES41 = 90	CES66 = 92	CES91 = 92
CES17 = 50	CES42 = 89	CES67 = 93	CES92 = 80
CES18 = 57	CES43 = 87	CES68 = 96	CES93 = 88
CES19 = 72	CES44 = 98	CES69 = 98	CES94 = 71
CES20 = 68	CES45 = 91	CES70 = 92	CES95 = 87
CES21 = 87	CES46 = 89	CES71 = 93	CES96 = 92
CES22 = 79	CES47 = 80	CES72 = 97	CES97 = 90
CES23 = 92	CES48 = 86	CES73 = 87	CES98 = 90
CES24 = 91	CES49 = 87	CES74 = 89	CES99 = 91
CES25 = 72	CES50 = 92	CES75 = 92	





REPORT NUMBER: SP1-2510-566-2-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2510-566-2-R2

TM-30-18

Measure Comparisons





(END OF REPORT)