

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1432448

Luminaire Tested: EHBR1-42-UNV-W-L830-UPL36

Issue Date: 3/20/2026

Test Information

Test Method: LM-79-2019
Report Number: P1432448
REPORT IS A COMBINATION OF REPORTS P1431825 AND P1431635
Test Lab: INNOVATION CENTER
Issue Date: 3/20/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-42-UNV-W-L830-UPL36
Description: Elevate Round Highbay at, 42000 lumens, 3000K 80CRI LEDs with W lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 42052.5 lumens
Efficiency: N/A
Efficacy: 166.3 lumens/watt
Spacing Criteria (0/90/45): 1.54 / 1.54 / 1.31
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')
CIE Type: Direct

Input Watts (W): 252.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1432448
CATALOG NUMBER: EHBR1-42-UNV-W-L830-UPL36

Luminous Intensity Polar Plot





TEST NUMBER: P1432448

CATALOG NUMBER: EHBR1-42-UNV-W-L830-UPL36

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	113	113	113	113	107	107	107	100	100	100	95	95	95	95	95	95	92
1	109	106	102	99	106	103	100	97	97	95	92	92	90	88	87	86	84	87	86	84	82
2	101	95	89	85	98	92	87	83	88	84	80	83	80	77	79	77	74	79	77	74	72
3	94	86	79	74	91	83	77	73	80	74	70	76	72	68	73	69	66	73	69	66	64
4	87	78	70	65	85	76	69	64	72	67	62	69	64	61	66	62	59	66	62	59	57
5	81	70	63	57	79	69	62	57	66	60	55	63	58	54	61	56	53	61	56	53	51
6	76	64	57	51	73	63	56	51	61	54	50	58	53	49	56	51	48	56	51	48	46
7	71	59	51	46	69	58	51	46	56	49	45	54	48	44	52	47	43	52	47	43	41
8	66	54	47	42	64	53	46	41	51	45	40	50	44	40	48	43	39	48	43	39	37
9	62	50	43	38	60	49	42	37	47	41	37	46	40	36	44	39	36	44	39	36	34
10	58	46	39	34	57	45	39	34	44	38	34	43	37	33	41	36	33	41	36	33	31

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	75985	75985	75985
5°	76490	76490	76490
10°	79148	79148	79148
15°	84163	84163	84163
20°	91234	91234	91234
25°	99181	99181	99181
30°	103959	103959	103959
35°	98952	98952	98952
40°	78518	78518	78518
45°	48531	48531	48531
50°	28101	28101	28101
55°	21262	21262	21262
60°	18239	18239	18239
65°	16474	16474	16474
70°	15154	15154	15154
75°	13389	13389	13389
80°	10911	10911	10911
85°	6433	6433	6433

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 48531 cd/sqm



TEST NUMBER: P1432448

CATALOG NUMBER: EHBR1-42-UNV-W-L830-UPL36

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1574.3	3.7
10°-20°	5047.0	12.0
20°-30°	9110.0	21.7
30°-40°	11008.5	26.2
40°-50°	6289.5	15.0
50°-60°	2663.8	6.3
60°-70°	1718.2	4.1
70°-80°	999.0	2.4
80°-90°	270.5	0.6
90°-100°	96.7	0.2
100°-110°	599.5	1.4
110°-120°	1071.3	2.5
120°-130°	629.7	1.5
130°-140°	388.8	0.9
140°-150°	272.2	0.6
150°-160°	177.9	0.4
160°-170°	101.9	0.2
170°-180°	33.8	0.1
0°-30°	15731.3	37.4
0°-40°	26739.8	63.6
0°-60°	35693.1	84.9
0°-90°	38680.8	92.0
90°-120°	1767.5	4.2
90°-150°	3058.1	7.3
90°-180°	3372.0	8.0
0°-180°	42052.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	16180	16180	16180	16180	16180	
5°	16332	16332	16332	16332	16332	1574
15°	17657	17657	17657	17657	17657	5047
25°	19806	19806	19806	19806	19806	9110
35°	18161	18161	18161	18161	18161	11009
45°	7852	7852	7852	7852	7852	6289
55°	2873	2873	2873	2873	2873	2664
65°	1720	1720	1720	1720	1720	1718
75°	943	943	943	943	943	999
85°	221	221	221	221	221	255
90°	26	42	70	45	26	22
95°	44	72	156	78	49	42
105°	210	413	1053	455	277	281
115°	964	1014	1245	1194	1186	888
125°	696	650	668	677	759	634
135°	511	496	513	482	480	400
145°	424	418	443	438	436	269
155°	374	370	387	387	387	174
165°	352	352	362	362	360	100
175°	350	350	355	355	355	33
180°	354	354	354	354	354	



TEST NUMBER: P1432448

CATALOG NUMBER: EHBR1-42-UNV-W-L830-UPL36

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	16180.5	16180.5	16180.5	16180.5	16180.5
2.5°	16234.9	16234.9	16234.9	16234.9	16234.9
5°	16331.8	16331.8	16331.8	16331.8	16331.8
7.5°	16522.5	16522.5	16522.5	16522.5	16522.5
10°	16816.0	16816.0	16816.0	16816.0	16816.0
12.5°	17197.3	17197.3	17197.3	17197.3	17197.3
15°	17657.0	17657.0	17657.0	17657.0	17657.0
17.5°	18183.1	18183.1	18183.1	18183.1	18183.1
20°	18751.3	18751.3	18751.3	18751.3	18751.3
22.5°	19323.5	19323.5	19323.5	19323.5	19323.5
25°	19806.3	19806.3	19806.3	19806.3	19806.3
27.5°	20066.2	20066.2	20066.2	20066.2	20066.2
30°	19996.4	19996.4	19996.4	19996.4	19996.4
32.5°	19403.6	19403.6	19403.6	19403.6	19403.6
35°	18161.2	18161.2	18161.2	18161.2	18161.2
37.5°	16223.9	16223.9	16223.9	16223.9	16223.9
40°	13609.1	13609.1	13609.1	13609.1	13609.1
42.5°	10651.7	10651.7	10651.7	10651.7	10651.7
45°	7852.1	7852.1	7852.1	7852.1	7852.1
47.5°	5612.2	5612.2	5612.2	5612.2	5612.2
50°	4188.1	4188.1	4188.1	4188.1	4188.1
52.5°	3391.1	3391.1	3391.1	3391.1	3391.1
55°	2873.4	2873.4	2873.4	2873.4	2873.4
57.5°	2495.2	2495.2	2495.2	2495.2	2495.2
60°	2192.6	2192.6	2192.6	2192.6	2192.6
62.5°	1940.6	1940.6	1940.6	1940.6	1940.6
65°	1719.5	1719.5	1719.5	1719.5	1719.5
67.5°	1524.2	1524.2	1524.2	1524.2	1524.2
70°	1329.7	1329.7	1329.7	1329.7	1329.7
72.5°	1135.8	1135.8	1135.8	1135.8	1135.8
75°	943.2	943.2	943.2	943.2	943.2
77.5°	757.6	757.6	757.6	757.6	757.6
80°	574.0	574.0	574.0	574.0	574.0
82.5°	393.7	393.7	393.7	393.7	393.7
85°	221.1	221.1	221.1	221.1	221.1
87.5°	69.8	69.8	69.8	69.8	69.8
90°	26.2	41.6	70.3	45.3	26.2
92.5°	37.1	62.0	111.7	58.2	33.3
95°	43.5	72.2	156.5	77.9	49.2
97.5°	55.0	79.9	179.5	95.2	76.1
100°	72.2	93.3	279.1	116.2	101.0
102.5°	122.1	196.7	591.4	217.8	152.7
105°	210.1	413.3	1053.1	455.4	277.2
107.5°	363.4	739.0	1388.5	806.0	524.4
110°	678.3	981.0	1456.2	1107.5	839.2



TEST NUMBER: P1432448

CATALOG NUMBER: EHBR1-42-UNV-W-L830-UPL36

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	915.9	1053.8	1394.9	1222.4	1092.1
115°	963.8	1013.6	1245.4	1193.6	1186.1
117.5°	931.2	925.5	1057.6	1073.0	1145.8
120°	862.2	823.9	883.3	937.0	1034.7
122.5°	776.0	730.1	756.9	797.0	894.8
125°	696.2	650.2	667.5	677.1	759.4
127.5°	625.3	594.6	604.3	592.7	644.5
130°	578.0	551.3	564.6	537.9	562.8
132.5°	539.1	521.8	537.1	504.5	512.2
135°	511.0	495.6	512.8	482.2	480.3
137.5°	486.7	473.3	490.6	467.5	461.8
140°	465.1	453.6	472.7	455.4	451.6
142.5°	440.8	433.1	456.1	444.7	440.8
145°	424.2	418.4	443.3	437.6	435.7
147.5°	409.5	405.7	428.6	426.8	426.8
150°	396.1	392.3	415.2	413.4	415.2
152.5°	382.7	378.9	400.0	398.0	400.0
155°	373.7	369.9	387.1	387.1	387.1
157.5°	366.1	364.2	377.6	377.6	377.6
160°	360.9	359.0	370.5	370.5	368.6
162.5°	355.9	353.9	367.3	365.4	365.4
165°	352.0	352.0	361.6	361.6	359.7
167.5°	352.0	350.0	359.7	359.7	357.7
170°	350.0	350.0	357.7	355.9	353.9
172.5°	350.7	350.7	358.4	356.5	354.5
175°	349.5	349.5	355.2	355.2	355.2
177.5°	351.4	351.4	355.2	355.2	353.3
180°	354.0	354.0	354.0	354.0	354.0



TEST NUMBER: P1432448
 CATALOG NUMBER: EHBR1-42-UNV-W-L830-UPL36

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.91	20.08	19.41	20.56	21.07	18.91	20.08	19.41	20.56	21.07
	3H	20.40	21.45	20.92	21.94	22.50	20.40	21.45	20.92	21.94	22.50
	4H	20.96	21.94	21.50	22.45	23.02	20.96	21.94	21.50	22.45	23.02
	6H	21.35	22.24	21.90	22.77	23.35	21.35	22.24	21.90	22.77	23.35
	8H	21.44	22.29	22.01	22.84	23.43	21.44	22.29	22.01	22.84	23.43
	12H	21.48	22.29	22.05	22.83	23.45	21.48	22.29	22.05	22.83	23.45
4H	2H	19.35	20.32	19.88	20.83	21.40	19.35	20.32	19.88	20.83	21.40
	3H	21.06	21.87	21.61	22.42	23.01	21.06	21.87	21.61	22.42	23.01
	4H	21.74	22.46	22.31	23.03	23.65	21.74	22.46	22.31	23.03	23.65
	6H	22.24	22.86	22.83	23.45	24.09	22.24	22.86	22.83	23.45	24.09
	8H	22.37	22.95	22.97	23.54	24.19	22.37	22.95	22.97	23.54	24.19
	12H	22.43	22.94	23.04	23.56	24.22	22.43	22.94	23.04	23.56	24.22
8H	4H	21.94	22.52	22.54	23.11	23.76	21.94	22.52	22.54	23.11	23.76
	6H	22.54	23.01	23.17	23.65	24.31	22.54	23.01	23.17	23.65	24.31
	8H	22.73	23.15	23.37	23.80	24.47	22.73	23.15	23.37	23.80	24.47
	12H	22.83	23.21	23.47	23.83	24.58	22.83	23.21	23.47	23.83	24.58
12H	4H	21.94	22.45	22.55	23.07	23.73	21.94	22.45	22.55	23.07	23.73
	6H	22.55	22.98	23.20	23.62	24.30	22.55	22.98	23.20	23.62	24.30
	8H	22.78	23.15	23.42	23.78	24.52	22.78	23.15	23.42	23.78	24.52

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-2

Test Date: 07/31/2025

Luminaire Tested: EHBR-60-L830-N

Data in this report applies to families of products including EHBR-60-L830-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L830-N**
 Description: Elevate Round Highbay at, 60000 lumens, 3000K 80CRI LEDs with N lens

Spectral Parameters

CCT (K): 2983
 CIE u': 0.2516
 CIE v': 0.5201
 Duv: -0.0012
 CIE x: 0.4364
 CIE y: 0.4010
 CIE z: 0.1626
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 583
 Purity: 51.34918
 Rf: 81.2
 Rg: 101.5

CRI (Ra):	83.4		
R1:	84.0	R9:	29.4
R2:	87.5	R10:	68.6
R3:	88.9	R11:	82.2
R4:	83.8	R12:	61.6
R5:	81.9	R13:	83.9
R6:	83.1	R14:	92.5
R7:	87.1	R15:	79.8
R8:	70.9		



Test Conditions

Stabilization Time: 38M
 Operation Time: 1H 38M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-2

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-2

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	43	NR	620	294	NR	750	6	NR	880	0	NR
365	0	NR	495	59	NR	625	294	NR	755	5	NR	885	0	NR
370	0	NR	500	81	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	109	NR	635	637	NR	765	4	NR	895	0	NR
380	0	NR	510	135	NR	640	175	NR	770	3	NR	900	0	NR
385	0	NR	515	160	NR	645	171	NR	775	3	NR	905	0	NR
390	1	NR	520	180	NR	650	146	NR	780	2	NR	910	0	NR
395	1	NR	525	195	NR	655	119	NR	785	2	NR	915	0	NR
400	2	NR	530	207	NR	660	99	NR	790	2	NR	920	0	NR
405	3	NR	535	218	NR	665	82	NR	795	2	NR	925	0	NR
410	5	NR	540	227	NR	670	76	NR	800	1	NR	930	0	NR
415	10	NR	545	237	NR	675	61	NR	805	1	NR	935	0	NR
420	20	NR	550	247	NR	680	52	NR	810	1	NR	940	0	NR
425	35	NR	555	259	NR	685	44	NR	815	1	NR	945	0	NR
430	58	NR	560	271	NR	690	38	NR	820	1	NR	950	0	NR
435	90	NR	565	283	NR	695	33	NR	825	1	NR	955	0	NR
440	135	NR	570	293	NR	700	27	NR	830	1	NR	960	0	NR
445	204	NR	575	303	NR	705	24	NR	835	1	NR	965	0	NR
450	233	NR	580	310	NR	710	20	NR	840	0	NR	970	0	NR
455	153	NR	585	313	NR	715	17	NR	845	0	NR	975	0	NR
460	98	NR	590	314	NR	720	15	NR	850	0	NR	980	0	NR
465	76	NR	595	310	NR	725	13	NR	855	0	NR	985	0	NR
470	53	NR	600	307	NR	730	11	NR	860	0	NR	990	0	NR
475	39	NR	605	303	NR	735	9	NR	865	0	NR	995	0	NR
480	35	NR	610	331	NR	740	8	NR	870	0	NR	1000	0	NR
485	36	NR	615	353	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.27

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	43	NR	620	294	NR	750	6	NR	880	0	NR
365	0	NR	495	59	NR	625	294	NR	755	5	NR	885	0	NR
370	0	NR	500	81	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	109	NR	635	637	NR	765	4	NR	895	0	NR
380	0	NR	510	135	NR	640	175	NR	770	3	NR	900	0	NR
385	0	NR	515	160	NR	645	171	NR	775	3	NR	905	0	NR
390	1	NR	520	180	NR	650	146	NR	780	2	NR	910	0	NR
395	1	NR	525	195	NR	655	119	NR	785	2	NR	915	0	NR
400	2	NR	530	207	NR	660	99	NR	790	2	NR	920	0	NR
405	3	NR	535	218	NR	665	82	NR	795	2	NR	925	0	NR
410	5	NR	540	227	NR	670	76	NR	800	1	NR	930	0	NR
415	10	NR	545	237	NR	675	61	NR	805	1	NR	935	0	NR
420	20	NR	550	247	NR	680	52	NR	810	1	NR	940	0	NR
425	35	NR	555	259	NR	685	44	NR	815	1	NR	945	0	NR
430	58	NR	560	271	NR	690	38	NR	820	1	NR	950	0	NR
435	90	NR	565	283	NR	695	33	NR	825	1	NR	955	0	NR
440	135	NR	570	293	NR	700	27	NR	830	1	NR	960	0	NR
445	204	NR	575	303	NR	705	24	NR	835	1	NR	965	0	NR
450	233	NR	580	310	NR	710	20	NR	840	0	NR	970	0	NR
455	153	NR	585	313	NR	715	17	NR	845	0	NR	975	0	NR
460	98	NR	590	314	NR	720	15	NR	850	0	NR	980	0	NR
465	76	NR	595	310	NR	725	13	NR	855	0	NR	985	0	NR
470	53	NR	600	307	NR	730	11	NR	860	0	NR	990	0	NR
475	39	NR	605	303	NR	735	9	NR	865	0	NR	995	0	NR
480	35	NR	610	331	NR	740	8	NR	870	0	NR	1000	0	NR
485	36	NR	615	353	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.34

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	43	NR	620	294	NR	750	6	NR	880	0	NR
365	0	NR	495	59	NR	625	294	NR	755	5	NR	885	0	NR
370	0	NR	500	81	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	109	NR	635	637	NR	765	4	NR	895	0	NR
380	0	NR	510	135	NR	640	175	NR	770	3	NR	900	0	NR
385	0	NR	515	160	NR	645	171	NR	775	3	NR	905	0	NR
390	1	NR	520	180	NR	650	146	NR	780	2	NR	910	0	NR
395	1	NR	525	195	NR	655	119	NR	785	2	NR	915	0	NR
400	2	NR	530	207	NR	660	99	NR	790	2	NR	920	0	NR
405	3	NR	535	218	NR	665	82	NR	795	2	NR	925	0	NR
410	5	NR	540	227	NR	670	76	NR	800	1	NR	930	0	NR
415	10	NR	545	237	NR	675	61	NR	805	1	NR	935	0	NR
420	20	NR	550	247	NR	680	52	NR	810	1	NR	940	0	NR
425	35	NR	555	259	NR	685	44	NR	815	1	NR	945	0	NR
430	58	NR	560	271	NR	690	38	NR	820	1	NR	950	0	NR
435	90	NR	565	283	NR	695	33	NR	825	1	NR	955	0	NR
440	135	NR	570	293	NR	700	27	NR	830	1	NR	960	0	NR
445	204	NR	575	303	NR	705	24	NR	835	1	NR	965	0	NR
450	233	NR	580	310	NR	710	20	NR	840	0	NR	970	0	NR
455	153	NR	585	313	NR	715	17	NR	845	0	NR	975	0	NR
460	98	NR	590	314	NR	720	15	NR	850	0	NR	980	0	NR
465	76	NR	595	310	NR	725	13	NR	855	0	NR	985	0	NR
470	53	NR	600	307	NR	730	11	NR	860	0	NR	990	0	NR
475	39	NR	605	303	NR	735	9	NR	865	0	NR	995	0	NR
480	35	NR	610	331	NR	740	8	NR	870	0	NR	1000	0	NR
485	36	NR	615	353	NR	745	7	NR	875	0	NR			

Summary

$R_f = 81.2$
 $R_g = 101.5$
 $CIE R_a = 83.4$
 $R_9 = 29.4$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 71	CES51 = 89	CES76 = 65
CES02 = 63	CES27 = 89	CES52 = 89	CES77 = 82
CES03 = 31	CES28 = 86	CES53 = 80	CES78 = 67
CES04 = 70	CES29 = 68	CES54 = 92	CES79 = 89
CES05 = 50	CES30 = 77	CES55 = 90	CES80 = 85
CES06 = 51	CES31 = 70	CES56 = 81	CES81 = 75
CES07 = 43	CES32 = 64	CES57 = 79	CES82 = 93
CES08 = 41	CES33 = 74	CES58 = 81	CES83 = 89
CES09 = 29	CES34 = 76	CES59 = 92	CES84 = 91
CES10 = 76	CES35 = 87	CES60 = 96	CES85 = 81
CES11 = 59	CES36 = 99	CES61 = 91	CES86 = 74
CES12 = 65	CES37 = 81	CES62 = 93	CES87 = 83
CES13 = 44	CES38 = 83	CES63 = 79	CES88 = 86
CES14 = 74	CES39 = 94	CES64 = 81	CES89 = 74
CES15 = 72	CES40 = 89	CES65 = 78	CES90 = 85
CES16 = 48	CES41 = 88	CES66 = 76	CES91 = 87
CES17 = 50	CES42 = 80	CES67 = 74	CES92 = 73
CES18 = 57	CES43 = 75	CES68 = 79	CES93 = 84
CES19 = 72	CES44 = 99	CES69 = 83	CES94 = 64
CES20 = 67	CES45 = 83	CES70 = 72	CES95 = 80
CES21 = 87	CES46 = 82	CES71 = 70	CES96 = 86
CES22 = 79	CES47 = 79	CES72 = 90	CES97 = 85
CES23 = 92	CES48 = 78	CES73 = 65	CES98 = 83
CES24 = 91	CES49 = 79	CES74 = 94	CES99 = 82
CES25 = 72	CES50 = 88	CES75 = 70	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)