Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590712

Luminaire Tested: 14CGTX-42-L92765-W2A-2700K

Issue Date: 9/7/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590712
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/7/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	14CGTX-42-L92765-W2A-2700K
Description:	1X4 4200 LUMEN CGTX TROFFER WITH VividTune LEDS AT 2700K CCT WITH FROSTED SMOOTH LENS
Light Source:	2700K CCT, 90 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	3816.7 lumens
Efficiency:	N/A
Efficacy:	96.1 lumens/watt
Spacing Criteria (0/90/45):	1.26 / 1.26 / 1.38
Luminous Opening:	Rectangular (W 0.83' x L: 3.83' x H: 0')
CIE Type:	Direct
Input Watts (W):	39.7
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590712
CATALOG NUMBER: 14CGTX-42-L92765-W2A-2700K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590712
CATALOG NUMBER: 14CGTX-42-L92765-W2A-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	94	97	94	91	93	90	88	89	87	85	83
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69
3	90	79	70	64	87	77	69	63	74	68	62	71	66	61	69	64	60	58
4	82	70	61	54	80	68	60	53	66	59	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	68	55	46	40	53	45	40	51	45	39	50	44	39	37
7	64	51	42	36	63	50	41	35	48	41	35	47	40	35	45	39	35	33
8	60	46	38	32	58	45	37	32	44	37	31	43	36	31	42	36	31	29
9	56	42	34	28	55	42	34	28	41	33	28	40	33	28	39	32	28	26
10	52	39	31	26	51	39	31	26	38	30	26	37	30	25	36	30	25	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4404	4404	4404
5°	4407	4390	4417
10°	4393	4386	4407
15°	4385	4378	4399
20°	4364	4353	4368
25°	4339	4331	4346
30°	4307	4307	4303
35°	4282	4270	4266
40°	4254	4232	4214
45°	4203	4193	4165
50°	4157	4136	4089
55°	4077	4054	4024
60°	4023	3976	3909
65°	3923	3843	3795
70°	3803	3724	3645
75°	3658	3541	3437
80°	3435	3338	3182
85°	3016	2938	2745

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4203 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590712
CATALOG NUMBER: 14CGTX-42-L92765-W2A-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.7	3.2
10°-20°	354.8	9.3
20°-30°	538.0	14.1
30°-40°	650.1	17.0
40°-50°	677.8	17.8
50°-60°	617.8	16.2
60°-70°	479.7	12.6
70°-80°	288.6	7.6
80°-90°	86.1	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1016.5	26.6
0°-40°	1666.7	43.7
0°-60°	2962.2	77.6
0°-90°	3816.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3816.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1307	1307	1307	1307	1307	
5°	1303	1300	1298	1303	1306	124
15°	1257	1257	1255	1258	1261	355
25°	1167	1168	1165	1168	1169	538
35°	1041	1040	1038	1037	1037	651
45°	882	881	880	878	874	680
55°	694	696	690	687	685	622
65°	492	491	482	478	476	487
75°	281	279	272	267	264	297
85°	78	79	76	73	71	89
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590712
CATALOG NUMBER: 14CGTX-42-L92765-W2A-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1307	1307	1307	1307	*1307*
2.5°	*1307*	*1307*	*1303*	*1308*	*1311*
5°	1303	1300	1298	1303	*1306*
7.5°	1296	1295	1292	1297	*1299*
10°	1284	1285	1282	1287	*1288*
12.5°	1275	1273	1271	1276	*1275*
15°	1257	1257	1255	1258	*1261*
17.5°	1239	1238	1237	1241	*1241*
20°	1217	1216	1214	1220	*1218*
22.5°	1192	1193	1191	1194	*1196*
25°	1167	1168	1165	1168	*1169*
27.5°	1139	1139	1138	1140	*1141*
30°	1107	1108	1107	1109	*1106*
32.5°	1075	1075	1074	1075	*1074*
35°	1041	1040	1038	1037	*1037*
37.5°	1005	1004	1003	1001	*1001*
40°	967	965	962	961	*958*
42.5°	923	924	921	919	*917*
45°	882	881	880	878	*874*
47.5°	839	837	836	831	*830*
50°	793	793	789	783	*780*
52.5°	742	746	742	737	*734*
55°	694	696	690	687	*685*
57.5°	648	648	642	637	*633*
60°	597	596	590	584	*580*
62.5°	545	545	538	532	*530*
65°	492	491	482	478	*476*
67.5°	439	439	433	426	*425*
70°	386	385	378	374	*370*
72.5°	334	332	326	320	*317*
75°	281	279	272	267	*264*
77.5°	228	226	221	215	*213*
80°	177	177	172	168	*164*
82.5°	128	127	124	121	*119*
85°	78	79	76	73	*71*
87.5°	34	34	31	28	*29*
90°	0	0	0	0	*0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590712
CATALOG NUMBER: 14CGTX-42-L92765-W2A-2700K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.11	18.77	17.48	19.08	19.40	16.98	18.64	17.35	18.96	19.27
	3H	19.03	20.53	19.41	20.86	21.22	18.86	20.36	19.23	20.69	21.04
	4H	19.79	21.20	20.18	21.55	21.92	19.57	20.99	19.97	21.34	21.71
	6H	20.37	21.69	20.78	22.05	22.44	20.12	21.43	20.53	21.80	22.19
	8H	20.58	21.83	21.00	22.22	22.62	20.31	21.57	20.73	21.95	22.35
	12H	20.72	21.92	21.14	22.30	22.73	20.43	21.64	20.86	22.02	22.45
4H	2H	17.75	19.17	18.15	19.51	19.89	17.65	19.07	18.05	19.41	19.79
	3H	19.90	21.09	20.31	21.49	21.89	19.75	20.94	20.16	21.34	21.74
	4H	20.80	21.88	21.23	22.29	22.72	20.60	21.68	21.03	22.09	22.53
	6H	21.52	22.47	21.98	22.91	23.36	21.28	22.23	21.74	22.67	23.12
	8H	21.78	22.67	22.24	23.11	23.58	21.53	22.41	21.99	22.86	23.32
	12H	21.98	22.78	22.46	23.25	23.72	21.70	22.50	22.18	22.98	23.44
8H	4H	21.13	22.02	21.59	22.46	22.92	20.96	21.85	21.42	22.29	22.75
	6H	22.00	22.74	22.49	23.22	23.70	21.78	22.52	22.27	23.01	23.48
	8H	22.35	23.01	22.85	23.51	24.00	22.11	22.77	22.62	23.28	23.76
	12H	22.62	23.21	23.13	23.70	24.26	22.36	22.95	22.87	23.44	24.00
12H	4H	21.17	21.97	21.65	22.45	22.91	21.01	21.81	21.49	22.28	22.75
	6H	22.07	22.73	22.58	23.24	23.72	21.86	22.53	22.37	23.03	23.52
	8H	22.48	23.07	22.98	23.56	24.11	22.25	22.84	22.76	23.33	23.89

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2510-566-2-R2

Test Date: 10/14/2025

Luminaire Tested: 22CGTX-50-L92765-W2A-2700K

Data in this report applies to families of products including 22CGTX


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2510-566-2-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**22CGTX-50-L92765-W2A-2700K**
Description:	*THIS IS A REVISION OF REPORT SP1-2512-566-2-R2 TO UPDATE THE CATALOG INFORMATION* 2X2 50000 Lumen CGTX TUNABLE WHITE FROM 2700K TO 6500K - 9.5V

Spectral Parameters

CCT (K):	2769	CRI (Ra):	93.3		
CIE u':	0.2597	R1:	95.3	R9:	56.5
CIE v':	0.5252	R2:	96.1	R10:	89.8
Duv:	-0.0006	R3:	96.0	R11:	95.2
CIE x:	0.4534	R4:	94.8	R12:	89.7
CIE y:	0.4074	R5:	94.9	R13:	95.3
CIE z:	0.1392	R6:	97.1	R14:	96.4
Peak Wavelength (nm):	630	R7:	91.2	R15:	89.6
Dominant Wavelength (nm):	584	R8:	81.4		
Purity:	58.37672				
Rf:	89.8				
Rg:	102.5				



Test Conditions


Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.0

REPORT NUMBER: SP1-2510-566-2-R2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2510-566-2-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 2769K
CIE x = 0.4534
CIE y = 0.4074
Duv = -0.0006

Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2510-566-2-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	74	NR	620	290	NR	750	7	NR	880	0	NR
365	0	NR	495	94	NR	625	297	NR	755	6	NR	885	0	NR
370	0	NR	500	113	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	130	NR	635	606	NR	765	4	NR	895	0	NR
380	0	NR	510	143	NR	640	189	NR	770	3	NR	900	0	NR
385	0	NR	515	154	NR	645	190	NR	775	3	NR	905	0	NR
390	1	NR	520	162	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	166	NR	655	134	NR	785	2	NR	915	0	NR
400	2	NR	530	171	NR	660	114	NR	790	2	NR	920	0	NR
405	3	NR	535	176	NR	665	96	NR	795	2	NR	925	0	NR
410	4	NR	540	182	NR	670	89	NR	800	1	NR	930	0	NR
415	7	NR	545	187	NR	675	72	NR	805	1	NR	935	0	NR
420	14	NR	550	194	NR	680	62	NR	810	1	NR	940	0	NR
425	23	NR	555	202	NR	685	53	NR	815	1	NR	945	0	NR
430	38	NR	560	210	NR	690	46	NR	820	1	NR	950	0	NR
435	63	NR	565	219	NR	695	39	NR	825	1	NR	955	0	NR
440	102	NR	570	228	NR	700	33	NR	830	1	NR	960	0	NR
445	144	NR	575	238	NR	705	28	NR	835	1	NR	965	0	NR
450	128	NR	580	247	NR	710	24	NR	840	0	NR	970	0	NR
455	83	NR	585	257	NR	715	20	NR	845	0	NR	975	0	NR
460	68	NR	590	264	NR	720	18	NR	850	0	NR	980	0	NR
465	55	NR	595	267	NR	725	15	NR	855	0	NR	985	0	NR
470	43	NR	600	273	NR	730	13	NR	860	0	NR	990	0	NR
475	42	NR	605	278	NR	735	11	NR	865	0	NR	995	0	NR
480	47	NR	610	311	NR	740	9	NR	870	0	NR	1000	0	NR
485	58	NR	615	333	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2510-566-2-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.3**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	74	NR	620	290	NR	750	7	NR	880	0	NR
365	0	NR	495	94	NR	625	297	NR	755	6	NR	885	0	NR
370	0	NR	500	113	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	130	NR	635	606	NR	765	4	NR	895	0	NR
380	0	NR	510	143	NR	640	189	NR	770	3	NR	900	0	NR
385	0	NR	515	154	NR	645	190	NR	775	3	NR	905	0	NR
390	1	NR	520	162	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	166	NR	655	134	NR	785	2	NR	915	0	NR
400	2	NR	530	171	NR	660	114	NR	790	2	NR	920	0	NR
405	3	NR	535	176	NR	665	96	NR	795	2	NR	925	0	NR
410	4	NR	540	182	NR	670	89	NR	800	1	NR	930	0	NR
415	7	NR	545	187	NR	675	72	NR	805	1	NR	935	0	NR
420	14	NR	550	194	NR	680	62	NR	810	1	NR	940	0	NR
425	23	NR	555	202	NR	685	53	NR	815	1	NR	945	0	NR
430	38	NR	560	210	NR	690	46	NR	820	1	NR	950	0	NR
435	63	NR	565	219	NR	695	39	NR	825	1	NR	955	0	NR
440	102	NR	570	228	NR	700	33	NR	830	1	NR	960	0	NR
445	144	NR	575	238	NR	705	28	NR	835	1	NR	965	0	NR
450	128	NR	580	247	NR	710	24	NR	840	0	NR	970	0	NR
455	83	NR	585	257	NR	715	20	NR	845	0	NR	975	0	NR
460	68	NR	590	264	NR	720	18	NR	850	0	NR	980	0	NR
465	55	NR	595	267	NR	725	15	NR	855	0	NR	985	0	NR
470	43	NR	600	273	NR	730	13	NR	860	0	NR	990	0	NR
475	42	NR	605	278	NR	735	11	NR	865	0	NR	995	0	NR
480	47	NR	610	311	NR	740	9	NR	870	0	NR	1000	0	NR
485	58	NR	615	333	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2510-566-2-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.45**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	74	NR	620	290	NR	750	7	NR	880	0	NR
365	0	NR	495	94	NR	625	297	NR	755	6	NR	885	0	NR
370	0	NR	500	113	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	130	NR	635	606	NR	765	4	NR	895	0	NR
380	0	NR	510	143	NR	640	189	NR	770	3	NR	900	0	NR
385	0	NR	515	154	NR	645	190	NR	775	3	NR	905	0	NR
390	1	NR	520	162	NR	650	161	NR	780	3	NR	910	0	NR
395	1	NR	525	166	NR	655	134	NR	785	2	NR	915	0	NR
400	2	NR	530	171	NR	660	114	NR	790	2	NR	920	0	NR
405	3	NR	535	176	NR	665	96	NR	795	2	NR	925	0	NR
410	4	NR	540	182	NR	670	89	NR	800	1	NR	930	0	NR
415	7	NR	545	187	NR	675	72	NR	805	1	NR	935	0	NR
420	14	NR	550	194	NR	680	62	NR	810	1	NR	940	0	NR
425	23	NR	555	202	NR	685	53	NR	815	1	NR	945	0	NR
430	38	NR	560	210	NR	690	46	NR	820	1	NR	950	0	NR
435	63	NR	565	219	NR	695	39	NR	825	1	NR	955	0	NR
440	102	NR	570	228	NR	700	33	NR	830	1	NR	960	0	NR
445	144	NR	575	238	NR	705	28	NR	835	1	NR	965	0	NR
450	128	NR	580	247	NR	710	24	NR	840	0	NR	970	0	NR
455	83	NR	585	257	NR	715	20	NR	845	0	NR	975	0	NR
460	68	NR	590	264	NR	720	18	NR	850	0	NR	980	0	NR
465	55	NR	595	267	NR	725	15	NR	855	0	NR	985	0	NR
470	43	NR	600	273	NR	730	13	NR	860	0	NR	990	0	NR
475	42	NR	605	278	NR	735	11	NR	865	0	NR	995	0	NR
480	47	NR	610	311	NR	740	9	NR	870	0	NR	1000	0	NR
485	58	NR	615	333	NR	745	8	NR	875	0	NR			


REPORT NUMBER: SP1-2510-566-2-R2

TM-30-18


Summary


R_f = 89.8
R_g = 102.5
CIE R_a = 93.3
R_9 = 56.5


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2510-566-2-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 88	CES51 = 92	CES76 = 89
CES02 = 64	CES27 = 97	CES52 = 93	CES77 = 85
CES03 = 32	CES28 = 95	CES53 = 88	CES78 = 86
CES04 = 70	CES29 = 83	CES54 = 96	CES79 = 89
CES05 = 51	CES30 = 84	CES55 = 95	CES80 = 91
CES06 = 51	CES31 = 85	CES56 = 89	CES81 = 70
CES07 = 44	CES32 = 80	CES57 = 87	CES82 = 96
CES08 = 43	CES33 = 83	CES58 = 88	CES83 = 92
CES09 = 29	CES34 = 91	CES59 = 98	CES84 = 97
CES10 = 77	CES35 = 95	CES60 = 99	CES85 = 82
CES11 = 59	CES36 = 99	CES61 = 99	CES86 = 75
CES12 = 66	CES37 = 93	CES62 = 91	CES87 = 91
CES13 = 44	CES38 = 88	CES63 = 89	CES88 = 93
CES14 = 74	CES39 = 95	CES64 = 93	CES89 = 80
CES15 = 72	CES40 = 91	CES65 = 90	CES90 = 92
CES16 = 48	CES41 = 90	CES66 = 92	CES91 = 92
CES17 = 50	CES42 = 89	CES67 = 93	CES92 = 80
CES18 = 57	CES43 = 87	CES68 = 96	CES93 = 88
CES19 = 72	CES44 = 98	CES69 = 98	CES94 = 71
CES20 = 68	CES45 = 91	CES70 = 92	CES95 = 87
CES21 = 87	CES46 = 89	CES71 = 93	CES96 = 92
CES22 = 79	CES47 = 80	CES72 = 97	CES97 = 90
CES23 = 92	CES48 = 86	CES73 = 87	CES98 = 90
CES24 = 91	CES49 = 87	CES74 = 89	CES99 = 91
CES25 = 72	CES50 = 92	CES75 = 92	





REPORT NUMBER: SP1-2510-566-2-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2510-566-2-R2

TM-30-18

Measure Comparisons





(END OF REPORT)