Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590814

Luminaire Tested: 24CGTX-65-L92765-W2A2-5700K

Issue Date: 9/7/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590814
	TEST IS SCALED FROM IESNA LM-79-24 TEST DATA (G3-2510-586-10)
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/7/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	24CGTX-65-L92765-W2A2-5700K
Description:	2X4 6500 LUMEN CGTX TROFFER WITH VividTune LEDS AT 5700K CCT WITH FROSTED SMOOTH LENS
Light Source:	5700K CCT, 90 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	7623.9 lumens
Efficiency:	N/A
Efficacy:	119.3 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.27 / 1.39
Luminous Opening:	Rectangular (W 2' x L: 4' x H: 0')
CIE Type:	Direct
Input Watts (W):	63.9
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590814
CATALOG NUMBER: 24CGTX-65-L92765-W2A2-5700K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590814
CATALOG NUMBER: 24CGTX-65-L92765-W2A2-5700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	57
4	82	69	61	54	79	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	44	39	50	44	39	37
7	64	50	42	35	62	50	41	35	48	40	35	47	40	35	45	39	34	32
8	60	46	37	31	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	40	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	26	37	30	25	36	30	25	36	30	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3463	3463	3463
5°	3481	3462	3472
10°	3473	3457	3473
15°	3465	3458	3464
20°	3461	3449	3458
25°	3445	3434	3431
30°	3423	3412	3421
35°	3402	3395	3395
40°	3385	3363	3363
45°	3367	3333	3319
50°	3332	3304	3275
55°	3276	3247	3220
60°	3219	3182	3160
65°	3147	3094	3041
70°	3059	2982	2929
75°	2947	2861	2764
80°	2799	2687	2566
85°	2612	2549	2388

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3367 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590814
CATALOG NUMBER: 24CGTX-65-L92765-W2A2-5700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.0	3.2
10°-20°	701.2	9.2
20°-30°	1066.8	14.0
30°-40°	1293.2	17.0
40°-50°	1352.8	17.7
50°-60°	1237.3	16.2
60°-70°	963.4	12.6
70°-80°	582.6	7.6
80°-90°	182.8	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2011.9	26.4
0°-40°	3305.1	43.4
0°-60°	5895.1	77.3
0°-90°	7623.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7623.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2574	2574	2574	2574	2574	
5°	2577	2567	2564	2565	2571	245
15°	2488	2484	2483	2482	2487	703
25°	2321	2316	2313	2312	2311	1070
35°	2071	2070	2067	2063	2067	1297
45°	1769	1759	1752	1751	1744	1362
55°	1396	1392	1384	1378	1373	1248
65°	988	990	972	962	955	978
75°	567	563	550	539	532	600
85°	169	168	165	158	155	190
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590814
CATALOG NUMBER: 24CGTX-65-L92765-W2A2-5700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*2573.9*	2573.9	2573.9	2573.9	2573.9
2.5°	*2581.2*	*2572.9*	*2572.9*	*2571.9*	*2575.0*
5°	*2577.0*	2566.7	2563.5	2564.6	2570.8
7.5°	*2559.4*	2552.1	2550.1	2549.0	2556.3
10°	*2541.7*	2535.5	2530.3	2533.4	2541.7
12.5°	*2523.1*	2514.7	2510.6	2510.6	2514.7
15°	*2487.8*	2483.6	2482.6	2481.5	2486.7
17.5°	*2456.6*	2451.4	2448.3	2447.3	2449.3
20°	*2417.1*	2407.8	2408.8	2406.8	2415.1
22.5°	*2373.5*	2365.2	2359.0	2363.2	2368.3
25°	*2320.6*	2316.4	2313.3	2312.3	2311.2
27.5°	*2267.6*	2260.4	2257.3	2258.3	2264.5
30°	*2203.3*	2197.0	2196.0	2195.0	2202.2
32.5°	*2142.0*	2137.8	2133.7	2135.8	2136.8
35°	*2071.4*	2070.4	2067.2	2063.1	2067.2
37.5°	*2000.8*	1998.7	1992.5	1989.4	1992.5
40°	*1927.1*	1920.8	1914.6	1914.6	1914.6
42.5°	*1850.2*	1840.9	1837.8	1832.6	1827.4
45°	*1769.3*	1758.9	1751.6	1750.6	1744.3
47.5°	*1673.7*	1671.7	1665.4	1662.3	1663.3
50°	*1591.7*	1579.2	1578.2	1566.8	1564.7
52.5°	*1491.0*	1485.8	1482.7	1476.5	1472.3
55°	*1396.5*	1392.4	1384.0	1377.8	1372.6
57.5°	*1295.8*	1292.7	1284.4	1281.3	1274.0
60°	*1196.1*	1189.9	1182.6	1174.3	1174.3
62.5°	*1094.4*	1089.2	1079.8	1072.6	1065.3
65°	*988.5*	989.5	971.8	962.5	955.2
67.5°	*883.6*	879.4	864.9	857.6	851.4
70°	*777.7*	771.5	758.0	748.6	744.5
72.5°	*672.8*	667.6	657.2	643.7	641.7
75°	*566.9*	562.8	550.3	538.9	531.6
77.5°	*464.1*	462.0	445.4	438.2	430.9
80°	*361.3*	360.3	346.8	339.5	331.2
82.5°	*270.0*	263.7	255.4	246.1	241.9
85°	*169.2*	168.2	165.1	157.8	154.7
87.5°	*79.9*	78.9	78.9	78.9	79.9
90°	*0.0*	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590814
CATALOG NUMBER: 24CGTX-65-L92765-W2A2-5700K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.32	17.98	16.68	18.29	18.61	16.24	17.90	16.61	18.22	18.53
	3H	18.25	19.76	18.63	20.09	20.44	18.11	19.62	18.49	19.94	20.30
	4H	19.02	20.44	19.42	20.79	21.16	18.83	20.25	19.23	20.60	20.97
	6H	19.62	20.94	20.04	21.31	21.70	19.38	20.70	19.79	21.07	21.46
	8H	19.85	21.11	20.27	21.50	21.89	19.58	20.84	20.00	21.23	21.62
	12H	20.01	21.22	20.43	21.60	22.02	19.72	20.93	20.15	21.31	21.74
4H	2H	16.97	18.39	17.37	18.74	19.11	16.91	18.33	17.31	18.68	19.05
	3H	19.13	20.33	19.54	20.73	21.12	19.00	20.20	19.41	20.60	21.00
	4H	20.04	21.12	20.47	21.54	21.97	19.86	20.95	20.29	21.36	21.79
	6H	20.79	21.74	21.24	22.18	22.63	20.55	21.50	21.01	21.94	22.40
	8H	21.07	21.96	21.53	22.40	22.87	20.80	21.69	21.26	22.13	22.60
	12H	21.28	22.09	21.76	22.56	23.03	20.99	21.80	21.47	22.27	22.74
8H	4H	20.38	21.27	20.84	21.71	22.18	20.22	21.11	20.68	21.56	22.02
	6H	21.27	22.01	21.76	22.50	22.98	21.05	21.80	21.55	22.28	22.76
	8H	21.64	22.31	22.15	22.81	23.30	21.39	22.05	21.89	22.56	23.04
	12H	21.95	22.54	22.45	23.03	23.59	21.67	22.26	22.17	22.75	23.31
12H	4H	20.42	21.23	20.90	21.70	22.17	20.28	21.08	20.75	21.55	22.02
	6H	21.34	22.01	21.85	22.52	23.00	21.14	21.81	21.64	22.31	22.79
	8H	21.78	22.37	22.28	22.86	23.42	21.54	22.13	22.04	22.62	23.18

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2510-566-15-R2

Test Date: 10/15/2025

Luminaire Tested: 22CGTX-50-L92765-W2A-5700K

Data in this report applies to families of products including 22CGTX

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05


Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2510-566-15-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**22CGTX-50-L92765-W2A-5700K**
Description:	*THIS IS A REVISION OF REPORT SP1-2512-566-15-R2 TO UPDATE THE CATALOG INFORMATION* 2X2 50000 Lumen CGTX TUNABLE WHITE FROM 2700K TO 6500K - 3 V

Spectral Parameters

CCT (K):	5464
CIE u':	0.2093
CIE v':	0.4752
Duv:	-0.0028
CIE x:	0.3332
CIE y:	0.3363
CIE z:	0.3306
Peak Wavelength (nm):	630
Dominant Wavelength (nm):	552
Purity:	0.8453147
Rf:	90.5
Rg:	100.7

CRI (Ra):	95.3				
R1:	97.1	R9:	81.4
R2:	97.2	R10:	91.8
R3:	93.9	R11:	95.7
R4:	97.1	R12:	72.4
R5:	96.2	R13:	98.1
R6:	92.3	R14:	96.0
R7:	95.5	R15:	97.9
R8:	93.3		



Test Conditions


Stabilization Time:	33M
Operation Time:	1H 33M
Sphere Temperature (°C):	25.0

REPORT NUMBER: SP1-2510-566-15-R2


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2510-566-15-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 5464K
CIE x = 0.3332
CIE y = 0.3363
Duv = -0.0028

Point lies inside the ANSI 5700K 7-step quadrangle

REPORT NUMBER: SP1-2510-566-15-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	237	NR	620	313	NR	750	7	NR	880	0	NR
365	0	NR	495	262	NR	625	315	NR	755	6	NR	885	0	NR
370	0	NR	500	293	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	319	NR	635	592	NR	765	4	NR	895	0	NR
380	1	NR	510	339	NR	640	199	NR	770	4	NR	900	0	NR
385	2	NR	515	355	NR	645	198	NR	775	3	NR	905	0	NR
390	2	NR	520	363	NR	650	166	NR	780	3	NR	910	0	NR
395	4	NR	525	366	NR	655	139	NR	785	2	NR	915	0	NR
400	5	NR	530	369	NR	660	118	NR	790	2	NR	920	0	NR
405	7	NR	535	371	NR	665	100	NR	795	2	NR	925	0	NR
410	10	NR	540	373	NR	670	92	NR	800	2	NR	930	0	NR
415	16	NR	545	372	NR	675	75	NR	805	1	NR	935	0	NR
420	28	NR	550	372	NR	680	64	NR	810	1	NR	940	0	NR
425	48	NR	555	374	NR	685	55	NR	815	1	NR	945	0	NR
430	86	NR	560	372	NR	690	48	NR	820	1	NR	950	0	NR
435	157	NR	565	371	NR	695	41	NR	825	1	NR	955	0	NR
440	274	NR	570	368	NR	700	35	NR	830	1	NR	960	0	NR
445	477	NR	575	364	NR	705	30	NR	835	1	NR	965	0	NR
450	736	NR	580	361	NR	710	25	NR	840	1	NR	970	0	NR
455	770	NR	585	356	NR	715	22	NR	845	0	NR	975	0	NR
460	547	NR	590	351	NR	720	19	NR	850	0	NR	980	0	NR
465	406	NR	595	341	NR	725	16	NR	855	0	NR	985	0	NR
470	327	NR	600	334	NR	730	14	NR	860	0	NR	990	0	NR
475	251	NR	605	327	NR	735	12	NR	865	0	NR	995	0	NR
480	215	NR	610	347	NR	740	10	NR	870	0	NR	1000	0	NR
485	218	NR	615	355	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2510-566-15-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 2.18**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	237	NR	620	313	NR	750	7	NR	880	0	NR
365	0	NR	495	262	NR	625	315	NR	755	6	NR	885	0	NR
370	0	NR	500	293	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	319	NR	635	592	NR	765	4	NR	895	0	NR
380	1	NR	510	339	NR	640	199	NR	770	4	NR	900	0	NR
385	2	NR	515	355	NR	645	198	NR	775	3	NR	905	0	NR
390	2	NR	520	363	NR	650	166	NR	780	3	NR	910	0	NR
395	4	NR	525	366	NR	655	139	NR	785	2	NR	915	0	NR
400	5	NR	530	369	NR	660	118	NR	790	2	NR	920	0	NR
405	7	NR	535	371	NR	665	100	NR	795	2	NR	925	0	NR
410	10	NR	540	373	NR	670	92	NR	800	2	NR	930	0	NR
415	16	NR	545	372	NR	675	75	NR	805	1	NR	935	0	NR
420	28	NR	550	372	NR	680	64	NR	810	1	NR	940	0	NR
425	48	NR	555	374	NR	685	55	NR	815	1	NR	945	0	NR
430	86	NR	560	372	NR	690	48	NR	820	1	NR	950	0	NR
435	157	NR	565	371	NR	695	41	NR	825	1	NR	955	0	NR
440	274	NR	570	368	NR	700	35	NR	830	1	NR	960	0	NR
445	477	NR	575	364	NR	705	30	NR	835	1	NR	965	0	NR
450	736	NR	580	361	NR	710	25	NR	840	1	NR	970	0	NR
455	770	NR	585	356	NR	715	22	NR	845	0	NR	975	0	NR
460	547	NR	590	351	NR	720	19	NR	850	0	NR	980	0	NR
465	406	NR	595	341	NR	725	16	NR	855	0	NR	985	0	NR
470	327	NR	600	334	NR	730	14	NR	860	0	NR	990	0	NR
475	251	NR	605	327	NR	735	12	NR	865	0	NR	995	0	NR
480	215	NR	610	347	NR	740	10	NR	870	0	NR	1000	0	NR
485	218	NR	615	355	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2510-566-15-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 4.82**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	237	NR	620	313	NR	750	7	NR	880	0	NR
365	0	NR	495	262	NR	625	315	NR	755	6	NR	885	0	NR
370	0	NR	500	293	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	319	NR	635	592	NR	765	4	NR	895	0	NR
380	1	NR	510	339	NR	640	199	NR	770	4	NR	900	0	NR
385	2	NR	515	355	NR	645	198	NR	775	3	NR	905	0	NR
390	2	NR	520	363	NR	650	166	NR	780	3	NR	910	0	NR
395	4	NR	525	366	NR	655	139	NR	785	2	NR	915	0	NR
400	5	NR	530	369	NR	660	118	NR	790	2	NR	920	0	NR
405	7	NR	535	371	NR	665	100	NR	795	2	NR	925	0	NR
410	10	NR	540	373	NR	670	92	NR	800	2	NR	930	0	NR
415	16	NR	545	372	NR	675	75	NR	805	1	NR	935	0	NR
420	28	NR	550	372	NR	680	64	NR	810	1	NR	940	0	NR
425	48	NR	555	374	NR	685	55	NR	815	1	NR	945	0	NR
430	86	NR	560	372	NR	690	48	NR	820	1	NR	950	0	NR
435	157	NR	565	371	NR	695	41	NR	825	1	NR	955	0	NR
440	274	NR	570	368	NR	700	35	NR	830	1	NR	960	0	NR
445	477	NR	575	364	NR	705	30	NR	835	1	NR	965	0	NR
450	736	NR	580	361	NR	710	25	NR	840	1	NR	970	0	NR
455	770	NR	585	356	NR	715	22	NR	845	0	NR	975	0	NR
460	547	NR	590	351	NR	720	19	NR	850	0	NR	980	0	NR
465	406	NR	595	341	NR	725	16	NR	855	0	NR	985	0	NR
470	327	NR	600	334	NR	730	14	NR	860	0	NR	990	0	NR
475	251	NR	605	327	NR	735	12	NR	865	0	NR	995	0	NR
480	215	NR	610	347	NR	740	10	NR	870	0	NR	1000	0	NR
485	218	NR	615	355	NR	745	8	NR	875	0	NR			


REPORT NUMBER: SP1-2510-566-15-R2

TM-30-18


Summary


R_f = 90.5
R_g = 100.7
CIE R_a = 95.3
R_9 = 81.4


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2510-566-15-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 92	CES51 = 96	CES76 = 83
CES02 = 61	CES27 = 90	CES52 = 98	CES77 = 86
CES03 = 31	CES28 = 94	CES53 = 97	CES78 = 80
CES04 = 68	CES29 = 96	CES54 = 92	CES79 = 94
CES05 = 48	CES30 = 90	CES55 = 90	CES80 = 91
CES06 = 50	CES31 = 96	CES56 = 94	CES81 = 86
CES07 = 41	CES32 = 88	CES57 = 92	CES82 = 96
CES08 = 40	CES33 = 98	CES58 = 92	CES83 = 97
CES09 = 29	CES34 = 90	CES59 = 97	CES84 = 92
CES10 = 73	CES35 = 94	CES60 = 91	CES85 = 83
CES11 = 56	CES36 = 78	CES61 = 90	CES86 = 89
CES12 = 62	CES37 = 92	CES62 = 82	CES87 = 91
CES13 = 42	CES38 = 84	CES63 = 91	CES88 = 98
CES14 = 74	CES39 = 99	CES64 = 87	CES89 = 89
CES15 = 71	CES40 = 98	CES65 = 87	CES90 = 96
CES16 = 46	CES41 = 96	CES66 = 83	CES91 = 70
CES17 = 48	CES42 = 90	CES67 = 82	CES92 = 80
CES18 = 56	CES43 = 92	CES68 = 85	CES93 = 87
CES19 = 70	CES44 = 99	CES69 = 85	CES94 = 81
CES20 = 65	CES45 = 95	CES70 = 82	CES95 = 83
CES21 = 84	CES46 = 98	CES71 = 74	CES96 = 93
CES22 = 77	CES47 = 95	CES72 = 92	CES97 = 96
CES23 = 91	CES48 = 91	CES73 = 76	CES98 = 97
CES24 = 90	CES49 = 96	CES74 = 90	CES99 = 96
CES25 = 70	CES50 = 97	CES75 = 77	





REPORT NUMBER: SP1-2510-566-15-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2510-566-15-R2

TM-30-18

Measure Comparisons





(END OF REPORT)