Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590901

Luminaire Tested: 14CGTX-42-L93050-W2A-3000K

Issue Date: 9/7/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590901
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/7/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	14CGTX-42-L93050-W2A-3000K
Description:	1X4 4200 LUMEN CGTX TROFFER WITH VividTune LEDS AT 3000K CCT
Light Source:	3000K CCT, 90 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	3985.1 lumens
Efficiency:	N/A
Efficacy:	100.4 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.26 / 1.38
Luminous Opening:	Rectangular (W 0.83' x L: 3.85' x H: 0')
CIE Type:	Direct
Input Watts (W):	39.7
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590901
CATALOG NUMBER: 14CGTX-42-L93050-W2A-3000K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590901
CATALOG NUMBER: 14CGTX-42-L93050-W2A-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	94	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	58
4	82	70	61	54	79	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	44	39	50	44	39	37
7	64	51	42	35	63	50	41	35	48	41	35	47	40	35	45	39	34	32
8	60	46	37	32	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	41	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	26	37	30	25	37	30	25	36	30	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4534	4534	4534
5°	4535	4528	4552
10°	4529	4529	4543
15°	4521	4514	4538
20°	4504	4504	4526
25°	4482	4478	4497
30°	4462	4454	4454
35°	4427	4414	4414
40°	4384	4384	4366
45°	4356	4341	4318
50°	4296	4291	4265
55°	4236	4224	4189
60°	4169	4149	4075
65°	4084	4044	3957
70°	3988	3900	3792
75°	3833	3742	3613
80°	3648	3513	3435
85°	3307	3153	2961

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
Vertical Angle: 45°
Luminance: 4360 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590901
CATALOG NUMBER: 14CGTX-42-L93050-W2A-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.3	3.2
10°-20°	368.2	9.2
20°-30°	559.1	14.0
30°-40°	676.3	17.0
40°-50°	706.6	17.7
50°-60°	645.9	16.2
60°-70°	503.6	12.6
70°-80°	305.1	7.7
80°-90°	92.2	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1055.5	26.5
0°-40°	1731.8	43.5
0°-60°	3084.2	77.4
0°-90°	3985.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3985.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1353	1353	1353	1353	1353	
5°	1348	1349	1346	1351	1353	128
15°	1303	1303	1301	1307	1308	368
25°	1212	1213	1211	1214	1216	559
35°	1082	1083	1079	1081	1079	677
45°	919	920	916	914	911	708
55°	725	729	723	719	717	649
65°	515	516	510	504	499	510
75°	296	296	289	283	279	312
85°	86	85	82	78	77	96
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590901
CATALOG NUMBER: 14CGTX-42-L93050-W2A-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1353	1353	1353	1353	*1353*
2.5°	*1354*	*1353*	*1351*	*1355*	*1357*
5°	1348	1349	1346	1351	*1353*
7.5°	1342	1342	1338	1346	*1344*
10°	1331	1333	1331	1335	*1335*
12.5°	1319	1320	1318	1323	*1325*
15°	1303	1303	1301	1307	*1308*
17.5°	1286	1285	1283	1288	*1288*
20°	1263	1264	1263	1265	*1269*
22.5°	1239	1240	1237	1241	*1243*
25°	1212	1213	1211	1214	*1216*
27.5°	1185	1184	1181	1185	*1185*
30°	1153	1153	1151	1152	*1151*
32.5°	1120	1118	1115	1117	*1116*
35°	1082	1083	1079	1081	*1079*
37.5°	1045	1044	1042	1042	*1041*
40°	1002	1005	1002	1001	*998*
42.5°	962	964	960	958	*956*
45°	919	920	916	914	*911*
47.5°	874	875	870	868	*863*
50°	824	827	823	819	*818*
52.5°	776	778	773	771	*767*
55°	725	729	723	719	*717*
57.5°	676	678	672	665	*661*
60°	622	625	619	612	*608*
62.5°	570	571	562	558	*557*
65°	515	516	510	504	*499*
67.5°	462	461	455	447	*446*
70°	407	404	398	393	*387*
72.5°	349	350	343	337	*335*
75°	296	296	289	283	*279*
77.5°	241	241	235	229	*227*
80°	189	188	182	177	*178*
82.5°	136	135	130	127	*126*
85°	86	85	82	78	*77*
87.5°	37	37	35	34	*32*
90°	0	0	0	0	*0*

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590901
CATALOG NUMBER: 14CGTX-42-L93050-W2A-3000K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.25	18.91	17.62	19.23	19.54	17.11	18.77	17.48	19.09	19.40
	3H	19.19	20.69	19.56	21.02	21.38	19.00	20.50	19.38	20.83	21.19
	4H	19.95	21.37	20.35	21.71	22.09	19.73	21.15	20.13	21.50	21.87
	6H	20.55	21.87	20.96	22.23	22.62	20.30	21.62	20.71	21.98	22.37
	8H	20.76	22.02	21.18	22.41	22.80	20.49	21.75	20.92	22.14	22.54
	12H	20.91	22.12	21.34	22.50	22.92	20.62	21.83	21.05	22.21	22.64
4H	2H	17.90	19.32	18.30	19.67	20.05	17.80	19.22	18.19	19.56	19.94
	3H	20.07	21.26	20.47	21.66	22.06	19.91	21.10	20.32	21.50	21.90
	4H	20.97	22.05	21.40	22.47	22.90	20.77	21.86	21.20	22.27	22.70
	6H	21.72	22.66	22.17	23.10	23.56	21.48	22.43	21.93	22.87	23.32
	8H	21.98	22.87	22.44	23.31	23.78	21.72	22.61	22.18	23.06	23.52
	12H	22.18	22.99	22.66	23.46	23.93	21.91	22.71	22.38	23.18	23.65
8H	4H	21.31	22.20	21.77	22.65	23.11	21.14	22.03	21.60	22.47	22.94
	6H	22.20	22.94	22.69	23.43	23.90	21.98	22.72	22.47	23.21	23.68
	8H	22.55	23.22	23.06	23.72	24.21	22.31	22.97	22.82	23.48	23.96
	12H	22.84	23.43	23.35	23.92	24.48	22.57	23.16	23.07	23.65	24.21
12H	4H	21.36	22.16	21.84	22.63	23.10	21.19	21.99	21.67	22.47	22.94
	6H	22.27	22.93	22.77	23.44	23.92	22.06	22.73	22.57	23.23	23.72
	8H	22.68	23.27	23.19	23.76	24.32	22.45	23.04	22.96	23.53	24.09

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2512-631-41-R2

Test Date: 02/05/2026

Luminaire Tested: 22CGTX-50-L93050-W2A-3000K

Data in this report applies to families of products including 22CGTX


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2512-631-41-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**22CGTX-50-L93050-W2A-3000K**
Description:	*THIS IS A REVISION OF REPORT SP1-2512-631-41-R2 TO UPDATE THE CATALOG INFORMATION* 2X2 5000 LUMEN HE CGTX TUNABLE WHITE FROM 3000K TO 5000K - 9.5 Volt

Spectral Parameters

CCT (K):	3066	CRI (Ra):	91.7		
CIE u':	0.2482	R1:	93.0	R9:	52.5
CIE v':	0.5206	R2:	94.0	R10:	85.0
Duv:	0.0004	R3:	94.3	R11:	94.8
CIE x:	0.4328	R4:	93.4	R12:	82.8
CIE y:	0.4036	R5:	92.4	R13:	92.9
CIE z:	0.1636	R6:	94.1	R14:	95.7
Peak Wavelength (nm):	630	R7:	91.5	R15:	87.8
Dominant Wavelength (nm):	582	R8:	80.7		
Purity:	51.0461				
Rf:	89.5				
Rg:	102				




Test Conditions

Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2512-631-41-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3066K
CIE x = 0.4328
CIE y = 0.4036
Duv = 0.0004

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2512-631-41-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	96	NR	620	317	NR	750	8	NR	880	0	NR
365	0	NR	495	121	NR	625	324	NR	755	7	NR	885	0	NR
370	0	NR	500	146	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	167	NR	635	572	NR	765	5	NR	895	0	NR
380	0	NR	510	183	NR	640	207	NR	770	4	NR	900	0	NR
385	1	NR	515	196	NR	645	215	NR	775	3	NR	905	0	NR
390	1	NR	520	205	NR	650	175	NR	780	3	NR	910	0	NR
395	2	NR	525	212	NR	655	147	NR	785	3	NR	915	0	NR
400	3	NR	530	218	NR	660	125	NR	790	2	NR	920	0	NR
405	4	NR	535	224	NR	665	106	NR	795	2	NR	925	0	NR
410	6	NR	540	230	NR	670	97	NR	800	2	NR	930	0	NR
415	11	NR	545	236	NR	675	80	NR	805	1	NR	935	0	NR
420	19	NR	550	244	NR	680	69	NR	810	1	NR	940	0	NR
425	34	NR	555	250	NR	685	59	NR	815	1	NR	945	0	NR
430	57	NR	560	260	NR	690	51	NR	820	1	NR	950	0	NR
435	92	NR	565	269	NR	695	44	NR	825	1	NR	955	0	NR
440	151	NR	570	277	NR	700	37	NR	830	1	NR	960	0	NR
445	208	NR	575	286	NR	705	32	NR	835	1	NR	965	0	NR
450	184	NR	580	294	NR	710	27	NR	840	1	NR	970	0	NR
455	122	NR	585	301	NR	715	23	NR	845	0	NR	975	0	NR
460	96	NR	590	307	NR	720	20	NR	850	0	NR	980	0	NR
465	76	NR	595	308	NR	725	17	NR	855	0	NR	985	0	NR
470	59	NR	600	312	NR	730	14	NR	860	0	NR	990	0	NR
475	57	NR	605	315	NR	735	12	NR	865	0	NR	995	0	NR
480	63	NR	610	347	NR	740	10	NR	870	0	NR	1000	0	NR
485	76	NR	615	356	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2512-631-41-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.41**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	96	NR	620	317	NR	750	8	NR	880	0	NR
365	0	NR	495	121	NR	625	324	NR	755	7	NR	885	0	NR
370	0	NR	500	146	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	167	NR	635	572	NR	765	5	NR	895	0	NR
380	0	NR	510	183	NR	640	207	NR	770	4	NR	900	0	NR
385	1	NR	515	196	NR	645	215	NR	775	3	NR	905	0	NR
390	1	NR	520	205	NR	650	175	NR	780	3	NR	910	0	NR
395	2	NR	525	212	NR	655	147	NR	785	3	NR	915	0	NR
400	3	NR	530	218	NR	660	125	NR	790	2	NR	920	0	NR
405	4	NR	535	224	NR	665	106	NR	795	2	NR	925	0	NR
410	6	NR	540	230	NR	670	97	NR	800	2	NR	930	0	NR
415	11	NR	545	236	NR	675	80	NR	805	1	NR	935	0	NR
420	19	NR	550	244	NR	680	69	NR	810	1	NR	940	0	NR
425	34	NR	555	250	NR	685	59	NR	815	1	NR	945	0	NR
430	57	NR	560	260	NR	690	51	NR	820	1	NR	950	0	NR
435	92	NR	565	269	NR	695	44	NR	825	1	NR	955	0	NR
440	151	NR	570	277	NR	700	37	NR	830	1	NR	960	0	NR
445	208	NR	575	286	NR	705	32	NR	835	1	NR	965	0	NR
450	184	NR	580	294	NR	710	27	NR	840	1	NR	970	0	NR
455	122	NR	585	301	NR	715	23	NR	845	0	NR	975	0	NR
460	96	NR	590	307	NR	720	20	NR	850	0	NR	980	0	NR
465	76	NR	595	308	NR	725	17	NR	855	0	NR	985	0	NR
470	59	NR	600	312	NR	730	14	NR	860	0	NR	990	0	NR
475	57	NR	605	315	NR	735	12	NR	865	0	NR	995	0	NR
480	63	NR	610	347	NR	740	10	NR	870	0	NR	1000	0	NR
485	76	NR	615	356	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2512-631-41-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.7**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	96	NR	620	317	NR	750	8	NR	880	0	NR
365	0	NR	495	121	NR	625	324	NR	755	7	NR	885	0	NR
370	0	NR	500	146	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	167	NR	635	572	NR	765	5	NR	895	0	NR
380	0	NR	510	183	NR	640	207	NR	770	4	NR	900	0	NR
385	1	NR	515	196	NR	645	215	NR	775	3	NR	905	0	NR
390	1	NR	520	205	NR	650	175	NR	780	3	NR	910	0	NR
395	2	NR	525	212	NR	655	147	NR	785	3	NR	915	0	NR
400	3	NR	530	218	NR	660	125	NR	790	2	NR	920	0	NR
405	4	NR	535	224	NR	665	106	NR	795	2	NR	925	0	NR
410	6	NR	540	230	NR	670	97	NR	800	2	NR	930	0	NR
415	11	NR	545	236	NR	675	80	NR	805	1	NR	935	0	NR
420	19	NR	550	244	NR	680	69	NR	810	1	NR	940	0	NR
425	34	NR	555	250	NR	685	59	NR	815	1	NR	945	0	NR
430	57	NR	560	260	NR	690	51	NR	820	1	NR	950	0	NR
435	92	NR	565	269	NR	695	44	NR	825	1	NR	955	0	NR
440	151	NR	570	277	NR	700	37	NR	830	1	NR	960	0	NR
445	208	NR	575	286	NR	705	32	NR	835	1	NR	965	0	NR
450	184	NR	580	294	NR	710	27	NR	840	1	NR	970	0	NR
455	122	NR	585	301	NR	715	23	NR	845	0	NR	975	0	NR
460	96	NR	590	307	NR	720	20	NR	850	0	NR	980	0	NR
465	76	NR	595	308	NR	725	17	NR	855	0	NR	985	0	NR
470	59	NR	600	312	NR	730	14	NR	860	0	NR	990	0	NR
475	57	NR	605	315	NR	735	12	NR	865	0	NR	995	0	NR
480	63	NR	610	347	NR	740	10	NR	870	0	NR	1000	0	NR
485	76	NR	615	356	NR	745	9	NR	875	0	NR			


REPORT NUMBER: SP1-2512-631-41-R2

TM-30-18


Summary


R_f = 89.5
R_g = 102
CIE R_a = 91.7
R_9 = 52.5


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2512-631-41-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 87	CES51 = 94	CES76 = 85
CES02 = 63	CES27 = 96	CES52 = 94	CES77 = 88
CES03 = 32	CES28 = 94	CES53 = 89	CES78 = 83
CES04 = 70	CES29 = 83	CES54 = 97	CES79 = 92
CES05 = 50	CES30 = 85	CES55 = 95	CES80 = 92
CES06 = 51	CES31 = 85	CES56 = 89	CES81 = 75
CES07 = 43	CES32 = 80	CES57 = 88	CES82 = 96
CES08 = 42	CES33 = 84	CES58 = 89	CES83 = 93
CES09 = 29	CES34 = 90	CES59 = 98	CES84 = 96
CES10 = 76	CES35 = 94	CES60 = 99	CES85 = 83
CES11 = 58	CES36 = 97	CES61 = 97	CES86 = 77
CES12 = 65	CES37 = 91	CES62 = 94	CES87 = 91
CES13 = 44	CES38 = 90	CES63 = 89	CES88 = 93
CES14 = 74	CES39 = 95	CES64 = 93	CES89 = 81
CES15 = 72	CES40 = 92	CES65 = 89	CES90 = 92
CES16 = 48	CES41 = 91	CES66 = 91	CES91 = 89
CES17 = 50	CES42 = 89	CES67 = 91	CES92 = 79
CES18 = 57	CES43 = 87	CES68 = 93	CES93 = 88
CES19 = 72	CES44 = 99	CES69 = 95	CES94 = 72
CES20 = 67	CES45 = 91	CES70 = 89	CES95 = 86
CES21 = 86	CES46 = 90	CES71 = 89	CES96 = 91
CES22 = 79	CES47 = 83	CES72 = 96	CES97 = 90
CES23 = 92	CES48 = 87	CES73 = 83	CES98 = 89
CES24 = 91	CES49 = 88	CES74 = 92	CES99 = 90
CES25 = 72	CES50 = 94	CES75 = 87	





REPORT NUMBER: SP1-2512-631-41-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2512-631-41-R2

TM-30-18

Measure Comparisons





(END OF REPORT)