Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590921

Luminaire Tested: 22CGTX-45-L93050-W2A-3000K

Issue Date: 9/7/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590921
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/7/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	22CGTX-45-L93050-W2A-3000K
Description:	2X2 4500 LUMEN CGTX TROFFER WITH VividTune LEDS AT 3000K CCT
Light Source:	3000K CCT, 90 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	4936.2 lumens
Efficiency:	N/A
Efficacy:	104.8 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.27 / 1.39
Luminous Opening:	Rectangular (W 1.81' x L: 1.81' x H: 0')
CIE Type:	Direct
Input Watts (W):	47.1
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590921
CATALOG NUMBER: 22CGTX-45-L93050-W2A-3000K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590921
CATALOG NUMBER: 22CGTX-45-L93050-W2A-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	68
3	89	79	70	63	87	77	69	63	74	67	62	71	65	61	69	64	60	57
4	82	69	60	54	79	68	60	53	66	58	52	63	57	52	61	55	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	39	51	44	39	50	43	39	37
7	64	50	41	35	62	50	41	35	48	40	35	47	40	35	45	39	34	32
8	60	46	37	31	58	45	37	31	44	36	31	43	36	31	41	35	31	29
9	56	42	34	28	54	42	34	28	40	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	25	37	30	25	36	30	25	35	29	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5439	5439	5439
5°	5453	5437	5443
10°	5456	5436	5436
15°	5441	5427	5434
20°	5422	5405	5412
25°	5405	5387	5390
30°	5369	5361	5369
35°	5344	5328	5340
40°	5312	5291	5299
45°	5259	5250	5255
50°	5199	5204	5215
55°	5118	5124	5130
60°	5020	5033	5039
65°	4908	4908	4962
70°	4742	4771	4819
75°	4557	4595	4608
80°	4264	4340	4378
85°	3910	3947	4023

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5259 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590921
CATALOG NUMBER: 22CGTX-45-L93050-W2A-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.3	3.2
10°-20°	452.0	9.2
20°-30°	687.4	13.9
30°-40°	834.2	16.9
40°-50°	874.4	17.7
50°-60°	802.5	16.3
60°-70°	627.9	12.7
70°-80°	382.6	7.8
80°-90°	117.8	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1296.8	26.3
0°-40°	2131.0	43.2
0°-60°	3807.9	77.1
0°-90°	4936.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4936.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1660	1660	1660	1660	1660	
5°	1658	1657	1653	1654	1655	158
15°	1604	1602	1600	1598	1602	453
25°	1495	1493	1490	1491	1491	689
35°	1336	1334	1332	1333	1335	836
45°	1135	1132	1133	1135	1134	875
55°	896	900	897	900	898	801
65°	633	629	633	637	640	625
75°	360	360	363	363	364	379
85°	104	103	105	106	107	116
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590921
CATALOG NUMBER: 22CGTX-45-L93050-W2A-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*1660*	1660	1660	1660	1660
2.5°	*1663*	*1660*	*1659*	*1657*	*1656*
5°	*1658*	1657	1653	1654	1655
7.5°	*1650*	1647	1645	1645	1646
10°	*1640*	1637	1634	1635	1634
12.5°	*1623*	1623	1619	1619	1620
15°	*1604*	1602	1600	1598	1602
17.5°	*1585*	1580	1578	1580	1579
20°	*1555*	1554	1550	1551	1552
22.5°	*1527*	1525	1522	1523	1525
25°	*1495*	1493	1490	1491	1491
27.5°	*1457*	1457	1454	1455	1457
30°	*1419*	1418	1417	1418	1419
32.5°	*1381*	1377	1375	1375	1375
35°	*1336*	1334	1332	1333	1335
37.5°	*1291*	1287	1287	1286	1291
40°	*1242*	1239	1237	1237	1239
42.5°	*1187*	1186	1187	1187	1190
45°	*1135*	1132	1133	1135	1134
47.5°	*1079*	1078	1075	1078	1082
50°	*1020*	1019	1021	1020	1023
52.5°	*959*	960	959	961	964
55°	*896*	900	897	900	898
57.5°	*832*	833	834	836	836
60°	*766*	770	768	769	769
62.5°	*700*	703	700	704	704
65°	*633*	629	633	637	640
67.5°	*564*	564	569	571	569
70°	*495*	496	498	501	503
72.5°	*425*	425	429	432	433
75°	*360*	360	363	363	364
77.5°	*292*	292	296	298	299
80°	*226*	230	230	231	232
82.5°	*164*	163	167	168	168
85°	*104*	103	105	106	107
87.5°	*46*	47	46	48	49
90°	*0*	0	0	0	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590921
CATALOG NUMBER: 22CGTX-45-L93050-W2A-3000K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.86	19.52	18.22	19.84	20.15	17.88	19.55	18.25	19.86	20.18
	3H	19.77	21.28	20.15	21.61	21.97	19.82	21.33	20.20	21.66	22.02
	4H	20.52	21.95	20.92	22.30	22.67	20.58	22.01	20.98	22.35	22.73
	6H	21.11	22.43	21.52	22.80	23.19	21.18	22.51	21.59	22.87	23.26
	8H	21.31	22.58	21.74	22.97	23.36	21.39	22.66	21.82	23.05	23.44
	12H	21.46	22.67	21.89	23.05	23.48	21.55	22.76	21.97	23.14	23.57
4H	2H	18.53	19.95	18.92	20.30	20.67	18.55	19.97	18.94	20.32	20.69
	3H	20.67	21.87	21.08	22.27	22.67	20.72	21.91	21.12	22.31	22.71
	4H	21.56	22.65	21.99	23.06	23.49	21.61	22.70	22.04	23.11	23.55
	6H	22.29	23.24	22.74	23.68	24.13	22.36	23.31	22.81	23.75	24.20
	8H	22.54	23.44	23.00	23.88	24.34	22.62	23.52	23.08	23.96	24.42
	12H	22.74	23.55	23.22	24.02	24.49	22.83	23.63	23.31	24.11	24.57
8H	4H	21.92	22.82	22.38	23.26	23.72	21.97	22.86	22.43	23.30	23.77
	6H	22.79	23.54	23.28	24.02	24.50	22.85	23.60	23.34	24.08	24.56
	8H	23.13	23.80	23.64	24.31	24.79	23.21	23.87	23.71	24.38	24.86
	12H	23.42	24.01	23.92	24.50	25.06	23.50	24.09	24.00	24.58	25.14
12H	4H	21.97	22.78	22.45	23.25	23.72	22.02	22.82	22.50	23.30	23.76
	6H	22.87	23.54	23.38	24.04	24.53	22.93	23.60	23.44	24.10	24.59
	8H	23.28	23.87	23.78	24.36	24.92	23.35	23.94	23.85	24.43	24.99

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2512-631-41-R2

Test Date: 02/05/2026

Luminaire Tested: 22CGTX-50-L93050-W2A-3000K

Data in this report applies to families of products including 22CGTX


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2512-631-41-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**22CGTX-50-L93050-W2A-3000K**
Description:	*THIS IS A REVISION OF REPORT SP1-2512-631-41-R2 TO UPDATE THE CATALOG INFORMATION* 2X2 5000 LUMEN HE CGTX TUNABLE WHITE FROM 3000K TO 5000K - 9.5 Volt

Spectral Parameters

CCT (K):	3066	CRI (Ra):	91.7		
CIE u':	0.2482	R1:	93.0	R9:	52.5
CIE v':	0.5206	R2:	94.0	R10:	85.0
Duv:	0.0004	R3:	94.3	R11:	94.8
CIE x:	0.4328	R4:	93.4	R12:	82.8
CIE y:	0.4036	R5:	92.4	R13:	92.9
CIE z:	0.1636	R6:	94.1	R14:	95.7
Peak Wavelength (nm):	630	R7:	91.5	R15:	87.8
Dominant Wavelength (nm):	582	R8:	80.7		
Purity:	51.0461				
Rf:	89.5				
Rg:	102				




Test Conditions

Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2512-631-41-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3066K
CIE x = 0.4328
CIE y = 0.4036
Duv = 0.0004

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2512-631-41-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	96	NR	620	317	NR	750	8	NR	880	0	NR
365	0	NR	495	121	NR	625	324	NR	755	7	NR	885	0	NR
370	0	NR	500	146	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	167	NR	635	572	NR	765	5	NR	895	0	NR
380	0	NR	510	183	NR	640	207	NR	770	4	NR	900	0	NR
385	1	NR	515	196	NR	645	215	NR	775	3	NR	905	0	NR
390	1	NR	520	205	NR	650	175	NR	780	3	NR	910	0	NR
395	2	NR	525	212	NR	655	147	NR	785	3	NR	915	0	NR
400	3	NR	530	218	NR	660	125	NR	790	2	NR	920	0	NR
405	4	NR	535	224	NR	665	106	NR	795	2	NR	925	0	NR
410	6	NR	540	230	NR	670	97	NR	800	2	NR	930	0	NR
415	11	NR	545	236	NR	675	80	NR	805	1	NR	935	0	NR
420	19	NR	550	244	NR	680	69	NR	810	1	NR	940	0	NR
425	34	NR	555	250	NR	685	59	NR	815	1	NR	945	0	NR
430	57	NR	560	260	NR	690	51	NR	820	1	NR	950	0	NR
435	92	NR	565	269	NR	695	44	NR	825	1	NR	955	0	NR
440	151	NR	570	277	NR	700	37	NR	830	1	NR	960	0	NR
445	208	NR	575	286	NR	705	32	NR	835	1	NR	965	0	NR
450	184	NR	580	294	NR	710	27	NR	840	1	NR	970	0	NR
455	122	NR	585	301	NR	715	23	NR	845	0	NR	975	0	NR
460	96	NR	590	307	NR	720	20	NR	850	0	NR	980	0	NR
465	76	NR	595	308	NR	725	17	NR	855	0	NR	985	0	NR
470	59	NR	600	312	NR	730	14	NR	860	0	NR	990	0	NR
475	57	NR	605	315	NR	735	12	NR	865	0	NR	995	0	NR
480	63	NR	610	347	NR	740	10	NR	870	0	NR	1000	0	NR
485	76	NR	615	356	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2512-631-41-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.41**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	96	NR	620	317	NR	750	8	NR	880	0	NR
365	0	NR	495	121	NR	625	324	NR	755	7	NR	885	0	NR
370	0	NR	500	146	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	167	NR	635	572	NR	765	5	NR	895	0	NR
380	0	NR	510	183	NR	640	207	NR	770	4	NR	900	0	NR
385	1	NR	515	196	NR	645	215	NR	775	3	NR	905	0	NR
390	1	NR	520	205	NR	650	175	NR	780	3	NR	910	0	NR
395	2	NR	525	212	NR	655	147	NR	785	3	NR	915	0	NR
400	3	NR	530	218	NR	660	125	NR	790	2	NR	920	0	NR
405	4	NR	535	224	NR	665	106	NR	795	2	NR	925	0	NR
410	6	NR	540	230	NR	670	97	NR	800	2	NR	930	0	NR
415	11	NR	545	236	NR	675	80	NR	805	1	NR	935	0	NR
420	19	NR	550	244	NR	680	69	NR	810	1	NR	940	0	NR
425	34	NR	555	250	NR	685	59	NR	815	1	NR	945	0	NR
430	57	NR	560	260	NR	690	51	NR	820	1	NR	950	0	NR
435	92	NR	565	269	NR	695	44	NR	825	1	NR	955	0	NR
440	151	NR	570	277	NR	700	37	NR	830	1	NR	960	0	NR
445	208	NR	575	286	NR	705	32	NR	835	1	NR	965	0	NR
450	184	NR	580	294	NR	710	27	NR	840	1	NR	970	0	NR
455	122	NR	585	301	NR	715	23	NR	845	0	NR	975	0	NR
460	96	NR	590	307	NR	720	20	NR	850	0	NR	980	0	NR
465	76	NR	595	308	NR	725	17	NR	855	0	NR	985	0	NR
470	59	NR	600	312	NR	730	14	NR	860	0	NR	990	0	NR
475	57	NR	605	315	NR	735	12	NR	865	0	NR	995	0	NR
480	63	NR	610	347	NR	740	10	NR	870	0	NR	1000	0	NR
485	76	NR	615	356	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2512-631-41-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.7**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	96	NR	620	317	NR	750	8	NR	880	0	NR
365	0	NR	495	121	NR	625	324	NR	755	7	NR	885	0	NR
370	0	NR	500	146	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	167	NR	635	572	NR	765	5	NR	895	0	NR
380	0	NR	510	183	NR	640	207	NR	770	4	NR	900	0	NR
385	1	NR	515	196	NR	645	215	NR	775	3	NR	905	0	NR
390	1	NR	520	205	NR	650	175	NR	780	3	NR	910	0	NR
395	2	NR	525	212	NR	655	147	NR	785	3	NR	915	0	NR
400	3	NR	530	218	NR	660	125	NR	790	2	NR	920	0	NR
405	4	NR	535	224	NR	665	106	NR	795	2	NR	925	0	NR
410	6	NR	540	230	NR	670	97	NR	800	2	NR	930	0	NR
415	11	NR	545	236	NR	675	80	NR	805	1	NR	935	0	NR
420	19	NR	550	244	NR	680	69	NR	810	1	NR	940	0	NR
425	34	NR	555	250	NR	685	59	NR	815	1	NR	945	0	NR
430	57	NR	560	260	NR	690	51	NR	820	1	NR	950	0	NR
435	92	NR	565	269	NR	695	44	NR	825	1	NR	955	0	NR
440	151	NR	570	277	NR	700	37	NR	830	1	NR	960	0	NR
445	208	NR	575	286	NR	705	32	NR	835	1	NR	965	0	NR
450	184	NR	580	294	NR	710	27	NR	840	1	NR	970	0	NR
455	122	NR	585	301	NR	715	23	NR	845	0	NR	975	0	NR
460	96	NR	590	307	NR	720	20	NR	850	0	NR	980	0	NR
465	76	NR	595	308	NR	725	17	NR	855	0	NR	985	0	NR
470	59	NR	600	312	NR	730	14	NR	860	0	NR	990	0	NR
475	57	NR	605	315	NR	735	12	NR	865	0	NR	995	0	NR
480	63	NR	610	347	NR	740	10	NR	870	0	NR	1000	0	NR
485	76	NR	615	356	NR	745	9	NR	875	0	NR			


REPORT NUMBER: SP1-2512-631-41-R2

TM-30-18


Summary


R_f = 89.5
R_g = 102
CIE R_a = 91.7
R_9 = 52.5


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2512-631-41-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 87	CES51 = 94	CES76 = 85
CES02 = 63	CES27 = 96	CES52 = 94	CES77 = 88
CES03 = 32	CES28 = 94	CES53 = 89	CES78 = 83
CES04 = 70	CES29 = 83	CES54 = 97	CES79 = 92
CES05 = 50	CES30 = 85	CES55 = 95	CES80 = 92
CES06 = 51	CES31 = 85	CES56 = 89	CES81 = 75
CES07 = 43	CES32 = 80	CES57 = 88	CES82 = 96
CES08 = 42	CES33 = 84	CES58 = 89	CES83 = 93
CES09 = 29	CES34 = 90	CES59 = 98	CES84 = 96
CES10 = 76	CES35 = 94	CES60 = 99	CES85 = 83
CES11 = 58	CES36 = 97	CES61 = 97	CES86 = 77
CES12 = 65	CES37 = 91	CES62 = 94	CES87 = 91
CES13 = 44	CES38 = 90	CES63 = 89	CES88 = 93
CES14 = 74	CES39 = 95	CES64 = 93	CES89 = 81
CES15 = 72	CES40 = 92	CES65 = 89	CES90 = 92
CES16 = 48	CES41 = 91	CES66 = 91	CES91 = 89
CES17 = 50	CES42 = 89	CES67 = 91	CES92 = 79
CES18 = 57	CES43 = 87	CES68 = 93	CES93 = 88
CES19 = 72	CES44 = 99	CES69 = 95	CES94 = 72
CES20 = 67	CES45 = 91	CES70 = 89	CES95 = 86
CES21 = 86	CES46 = 90	CES71 = 89	CES96 = 91
CES22 = 79	CES47 = 83	CES72 = 96	CES97 = 90
CES23 = 92	CES48 = 87	CES73 = 83	CES98 = 89
CES24 = 91	CES49 = 88	CES74 = 92	CES99 = 90
CES25 = 72	CES50 = 94	CES75 = 87	





REPORT NUMBER: SP1-2512-631-41-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2512-631-41-R2

TM-30-18

Measure Comparisons





(END OF REPORT)