Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590931

Luminaire Tested: 24CGTX-20-L93050-W2A-3000K

Issue Date: 9/7/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590931
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/7/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	24CGTX-20-L93050-W2A-3000K
Description:	2X4 2000 LUMEN CGTX TROFFER WITH VividTune LEDS AT 3000K CCT
Light Source:	3000K CCT, 90 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	2174.4 lumens
Efficiency:	N/A
Efficacy:	120.1 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.27 / 1.39
Luminous Opening:	Rectangular (W 1.81' x L: 3.83' x H: 0')
CIE Type:	Direct
Input Watts (W):	18.1
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590931
CATALOG NUMBER: 24CGTX-20-L93050-W2A-3000K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590931
CATALOG NUMBER: 24CGTX-20-L93050-W2A-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	57
4	82	70	61	54	79	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	44	39	50	44	39	37
7	64	51	42	35	62	50	41	35	48	41	35	47	40	35	45	39	34	32
8	60	46	37	32	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	40	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	26	37	30	25	36	30	25	36	30	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1139	1139	1139
5°	1141	1137	1134
10°	1142	1133	1141
15°	1142	1136	1131
20°	1141	1133	1134
25°	1132	1128	1125
30°	1127	1123	1125
35°	1122	1110	1116
40°	1114	1108	1110
45°	1104	1095	1098
50°	1092	1085	1082
55°	1072	1067	1061
60°	1053	1050	1032
65°	1037	1019	1004
70°	997	978	960
75°	964	934	910
80°	919	874	848
85°	853	818	764

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1104 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590931
CATALOG NUMBER: 24CGTX-20-L93050-W2A-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.6	3.2
10°-20°	200.0	9.2
20°-30°	304.4	14.0
30°-40°	369.2	17.0
40°-50°	386.1	17.8
50°-60°	353.0	16.2
60°-70°	274.8	12.6
70°-80°	165.8	7.6
80°-90°	51.4	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	574.0	26.4
0°-40°	943.2	43.4
0°-60°	1682.4	77.4
0°-90°	2174.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2174.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	735	735	735	735	735	
5°	734	734	731	731	729	70
15°	712	710	708	707	705	201
25°	662	659	660	659	658	306
35°	593	589	587	588	590	371
45°	504	501	500	499	501	388
55°	397	397	395	394	393	356
65°	283	281	278	276	274	279
75°	161	160	156	153	152	171
85°	48	48	46	44	43	53
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590931
CATALOG NUMBER: 24CGTX-20-L93050-W2A-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*735*	735	735	735	735
2.5°	*738*	*734*	*733*	*734*	*736*
5°	*734*	734	731	731	729
7.5°	*731*	729	728	727	730
10°	*726*	724	720	722	725
12.5°	*719*	716	717	716	719
15°	*712*	710	708	707	705
17.5°	*698*	700	698	700	700
20°	*692*	686	687	687	688
22.5°	*678*	675	674	674	676
25°	*662*	659	660	659	658
27.5°	*649*	645	645	643	647
30°	*630*	628	628	628	629
32.5°	*612*	611	611	609	608
35°	*593*	589	587	588	590
37.5°	*572*	571	568	568	570
40°	*551*	549	548	546	549
42.5°	*527*	526	525	524	521
45°	*504*	501	500	499	501
47.5°	*478*	477	474	474	473
50°	*453*	451	450	448	449
52.5°	*425*	425	422	420	418
55°	*397*	397	395	394	393
57.5°	*371*	368	368	365	365
60°	*340*	340	339	334	333
62.5°	*312*	311	307	306	304
65°	*283*	281	278	276	274
67.5°	*251*	250	248	244	243
70°	*220*	220	216	213	212
72.5°	*192*	190	186	184	183
75°	*161*	160	156	153	152
77.5°	*132*	131	128	125	123
80°	*103*	102	98	96	95
82.5°	*74*	74	72	71	68
85°	*48*	48	46	44	43
87.5°	*23*	22	22	21	21
90°	*0*	0	0	0	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590931
CATALOG NUMBER: 24CGTX-20-L93050-W2A-3000K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.44	14.10	12.81	14.42	14.73	12.37	14.03	12.74	14.35	14.66
	3H	14.37	15.88	14.75	16.20	16.56	14.24	15.74	14.61	16.07	16.43
	4H	15.13	16.56	15.53	16.90	17.28	14.96	16.38	15.35	16.73	17.10
	6H	15.74	17.06	16.15	17.42	17.81	15.51	16.83	15.92	17.20	17.59
	8H	15.95	17.21	16.37	17.60	18.00	15.70	16.96	16.13	17.35	17.75
	12H	16.11	17.31	16.53	17.70	18.12	15.84	17.05	16.27	17.43	17.86
4H	2H	13.10	14.52	13.50	14.87	15.24	13.04	14.46	13.44	14.81	15.19
	3H	15.25	16.45	15.66	16.85	17.24	15.13	16.33	15.54	16.73	17.13
	4H	16.16	17.24	16.59	17.65	18.09	15.99	17.07	16.42	17.48	17.92
	6H	16.90	17.86	17.36	18.29	18.75	16.68	17.63	17.13	18.07	18.52
	8H	17.17	18.06	17.63	18.50	18.97	16.93	17.82	17.39	18.26	18.72
	12H	17.38	18.18	17.86	18.66	19.13	17.11	17.92	17.59	18.39	18.86
8H	4H	16.50	17.39	16.96	17.83	18.29	16.35	17.24	16.81	17.68	18.15
	6H	17.38	18.13	17.88	18.61	19.09	17.18	17.92	17.67	18.41	18.88
	8H	17.74	18.41	18.25	18.91	19.40	17.51	18.18	18.02	18.68	19.17
	12H	18.04	18.63	18.55	19.12	19.68	17.78	18.38	18.29	18.86	19.42
12H	4H	16.54	17.34	17.02	17.82	18.29	16.40	17.20	16.88	17.68	18.14
	6H	17.45	18.12	17.96	18.63	19.11	17.26	17.93	17.77	18.43	18.92
	8H	17.88	18.47	18.38	18.96	19.52	17.66	18.25	18.16	18.74	19.30

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2512-631-41-R2

Test Date: 02/05/2026

Luminaire Tested: 22CGTX-50-L93050-W2A-3000K

Data in this report applies to families of products including 22CGTX


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2512-631-41-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**22CGTX-50-L93050-W2A-3000K**
Description:	*THIS IS A REVISION OF REPORT SP1-2512-631-41-R2 TO UPDATE THE CATALOG INFORMATION* 2X2 5000 LUMEN HE CGTX TUNABLE WHITE FROM 3000K TO 5000K - 9.5 Volt

Spectral Parameters

CCT (K):	3066	CRI (Ra):	91.7		
CIE u':	0.2482	R1:	93.0	R9:	52.5
CIE v':	0.5206	R2:	94.0	R10:	85.0
Duv:	0.0004	R3:	94.3	R11:	94.8
CIE x:	0.4328	R4:	93.4	R12:	82.8
CIE y:	0.4036	R5:	92.4	R13:	92.9
CIE z:	0.1636	R6:	94.1	R14:	95.7
Peak Wavelength (nm):	630	R7:	91.5	R15:	87.8
Dominant Wavelength (nm):	582	R8:	80.7		
Purity:	51.0461				
Rf:	89.5				
Rg:	102				




Test Conditions

Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2512-631-41-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3066K
CIE x = 0.4328
CIE y = 0.4036
Duv = 0.0004

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2512-631-41-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	96	NR	620	317	NR	750	8	NR	880	0	NR
365	0	NR	495	121	NR	625	324	NR	755	7	NR	885	0	NR
370	0	NR	500	146	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	167	NR	635	572	NR	765	5	NR	895	0	NR
380	0	NR	510	183	NR	640	207	NR	770	4	NR	900	0	NR
385	1	NR	515	196	NR	645	215	NR	775	3	NR	905	0	NR
390	1	NR	520	205	NR	650	175	NR	780	3	NR	910	0	NR
395	2	NR	525	212	NR	655	147	NR	785	3	NR	915	0	NR
400	3	NR	530	218	NR	660	125	NR	790	2	NR	920	0	NR
405	4	NR	535	224	NR	665	106	NR	795	2	NR	925	0	NR
410	6	NR	540	230	NR	670	97	NR	800	2	NR	930	0	NR
415	11	NR	545	236	NR	675	80	NR	805	1	NR	935	0	NR
420	19	NR	550	244	NR	680	69	NR	810	1	NR	940	0	NR
425	34	NR	555	250	NR	685	59	NR	815	1	NR	945	0	NR
430	57	NR	560	260	NR	690	51	NR	820	1	NR	950	0	NR
435	92	NR	565	269	NR	695	44	NR	825	1	NR	955	0	NR
440	151	NR	570	277	NR	700	37	NR	830	1	NR	960	0	NR
445	208	NR	575	286	NR	705	32	NR	835	1	NR	965	0	NR
450	184	NR	580	294	NR	710	27	NR	840	1	NR	970	0	NR
455	122	NR	585	301	NR	715	23	NR	845	0	NR	975	0	NR
460	96	NR	590	307	NR	720	20	NR	850	0	NR	980	0	NR
465	76	NR	595	308	NR	725	17	NR	855	0	NR	985	0	NR
470	59	NR	600	312	NR	730	14	NR	860	0	NR	990	0	NR
475	57	NR	605	315	NR	735	12	NR	865	0	NR	995	0	NR
480	63	NR	610	347	NR	740	10	NR	870	0	NR	1000	0	NR
485	76	NR	615	356	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2512-631-41-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.41**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	96	NR	620	317	NR	750	8	NR	880	0	NR
365	0	NR	495	121	NR	625	324	NR	755	7	NR	885	0	NR
370	0	NR	500	146	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	167	NR	635	572	NR	765	5	NR	895	0	NR
380	0	NR	510	183	NR	640	207	NR	770	4	NR	900	0	NR
385	1	NR	515	196	NR	645	215	NR	775	3	NR	905	0	NR
390	1	NR	520	205	NR	650	175	NR	780	3	NR	910	0	NR
395	2	NR	525	212	NR	655	147	NR	785	3	NR	915	0	NR
400	3	NR	530	218	NR	660	125	NR	790	2	NR	920	0	NR
405	4	NR	535	224	NR	665	106	NR	795	2	NR	925	0	NR
410	6	NR	540	230	NR	670	97	NR	800	2	NR	930	0	NR
415	11	NR	545	236	NR	675	80	NR	805	1	NR	935	0	NR
420	19	NR	550	244	NR	680	69	NR	810	1	NR	940	0	NR
425	34	NR	555	250	NR	685	59	NR	815	1	NR	945	0	NR
430	57	NR	560	260	NR	690	51	NR	820	1	NR	950	0	NR
435	92	NR	565	269	NR	695	44	NR	825	1	NR	955	0	NR
440	151	NR	570	277	NR	700	37	NR	830	1	NR	960	0	NR
445	208	NR	575	286	NR	705	32	NR	835	1	NR	965	0	NR
450	184	NR	580	294	NR	710	27	NR	840	1	NR	970	0	NR
455	122	NR	585	301	NR	715	23	NR	845	0	NR	975	0	NR
460	96	NR	590	307	NR	720	20	NR	850	0	NR	980	0	NR
465	76	NR	595	308	NR	725	17	NR	855	0	NR	985	0	NR
470	59	NR	600	312	NR	730	14	NR	860	0	NR	990	0	NR
475	57	NR	605	315	NR	735	12	NR	865	0	NR	995	0	NR
480	63	NR	610	347	NR	740	10	NR	870	0	NR	1000	0	NR
485	76	NR	615	356	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2512-631-41-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.7**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	96	NR	620	317	NR	750	8	NR	880	0	NR
365	0	NR	495	121	NR	625	324	NR	755	7	NR	885	0	NR
370	0	NR	500	146	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	167	NR	635	572	NR	765	5	NR	895	0	NR
380	0	NR	510	183	NR	640	207	NR	770	4	NR	900	0	NR
385	1	NR	515	196	NR	645	215	NR	775	3	NR	905	0	NR
390	1	NR	520	205	NR	650	175	NR	780	3	NR	910	0	NR
395	2	NR	525	212	NR	655	147	NR	785	3	NR	915	0	NR
400	3	NR	530	218	NR	660	125	NR	790	2	NR	920	0	NR
405	4	NR	535	224	NR	665	106	NR	795	2	NR	925	0	NR
410	6	NR	540	230	NR	670	97	NR	800	2	NR	930	0	NR
415	11	NR	545	236	NR	675	80	NR	805	1	NR	935	0	NR
420	19	NR	550	244	NR	680	69	NR	810	1	NR	940	0	NR
425	34	NR	555	250	NR	685	59	NR	815	1	NR	945	0	NR
430	57	NR	560	260	NR	690	51	NR	820	1	NR	950	0	NR
435	92	NR	565	269	NR	695	44	NR	825	1	NR	955	0	NR
440	151	NR	570	277	NR	700	37	NR	830	1	NR	960	0	NR
445	208	NR	575	286	NR	705	32	NR	835	1	NR	965	0	NR
450	184	NR	580	294	NR	710	27	NR	840	1	NR	970	0	NR
455	122	NR	585	301	NR	715	23	NR	845	0	NR	975	0	NR
460	96	NR	590	307	NR	720	20	NR	850	0	NR	980	0	NR
465	76	NR	595	308	NR	725	17	NR	855	0	NR	985	0	NR
470	59	NR	600	312	NR	730	14	NR	860	0	NR	990	0	NR
475	57	NR	605	315	NR	735	12	NR	865	0	NR	995	0	NR
480	63	NR	610	347	NR	740	10	NR	870	0	NR	1000	0	NR
485	76	NR	615	356	NR	745	9	NR	875	0	NR			


REPORT NUMBER: SP1-2512-631-41-R2

TM-30-18


Summary


R_f = 89.5
R_g = 102
CIE R_a = 91.7
R_9 = 52.5


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2512-631-41-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 87	CES51 = 94	CES76 = 85
CES02 = 63	CES27 = 96	CES52 = 94	CES77 = 88
CES03 = 32	CES28 = 94	CES53 = 89	CES78 = 83
CES04 = 70	CES29 = 83	CES54 = 97	CES79 = 92
CES05 = 50	CES30 = 85	CES55 = 95	CES80 = 92
CES06 = 51	CES31 = 85	CES56 = 89	CES81 = 75
CES07 = 43	CES32 = 80	CES57 = 88	CES82 = 96
CES08 = 42	CES33 = 84	CES58 = 89	CES83 = 93
CES09 = 29	CES34 = 90	CES59 = 98	CES84 = 96
CES10 = 76	CES35 = 94	CES60 = 99	CES85 = 83
CES11 = 58	CES36 = 97	CES61 = 97	CES86 = 77
CES12 = 65	CES37 = 91	CES62 = 94	CES87 = 91
CES13 = 44	CES38 = 90	CES63 = 89	CES88 = 93
CES14 = 74	CES39 = 95	CES64 = 93	CES89 = 81
CES15 = 72	CES40 = 92	CES65 = 89	CES90 = 92
CES16 = 48	CES41 = 91	CES66 = 91	CES91 = 89
CES17 = 50	CES42 = 89	CES67 = 91	CES92 = 79
CES18 = 57	CES43 = 87	CES68 = 93	CES93 = 88
CES19 = 72	CES44 = 99	CES69 = 95	CES94 = 72
CES20 = 67	CES45 = 91	CES70 = 89	CES95 = 86
CES21 = 86	CES46 = 90	CES71 = 89	CES96 = 91
CES22 = 79	CES47 = 83	CES72 = 96	CES97 = 90
CES23 = 92	CES48 = 87	CES73 = 83	CES98 = 89
CES24 = 91	CES49 = 88	CES74 = 92	CES99 = 90
CES25 = 72	CES50 = 94	CES75 = 87	





REPORT NUMBER: SP1-2512-631-41-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2512-631-41-R2

TM-30-18

Measure Comparisons





(END OF REPORT)