Signify Classified - Internal

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: METALUX

Report Number: P1590951

Luminaire Tested: 24CGTX-45-L93050-W2A-3000K

Issue Date: 9/7/2026

Report Generated By 670265710 / DESKTOP-98SHLC4

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1590951
Test Lab:	COOPER LIGHTING SOLUTIONS
Issue Date:	9/7/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	METALUX
Catalog Number:	24CGTX-45-L93050-W2A-3000K
Description:	2X4 4500 LUMEN CGTX TROFFER WITH VividTune LEDS AT 3000K CCT
Light Source:	3000K CCT, 90 CRI LEDS
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	5000.5 lumens
Efficiency:	N/A
Efficacy:	116.0 lumens/watt
Spacing Criteria (0/90/45):	1.27 / 1.27 / 1.39
Luminous Opening:	Rectangular (W 1.81' x L: 3.83' x H: 0')
CIE Type:	Direct
Input Watts (W):	43.1
Input Voltage (V):	120
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT




Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590951
CATALOG NUMBER: 24CGTX-45-L93050-W2A-3000K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590951
CATALOG NUMBER: 24CGTX-45-L93050-W2A-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90	93	90	88	89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74	81	76	72	78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62	71	66	61	69	64	60	57
4	82	70	61	54	79	68	60	53	66	58	53	63	57	52	61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45	57	50	45	55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40	51	44	39	50	44	39	37
7	64	51	42	35	62	50	41	35	48	41	35	47	40	35	45	39	34	32
8	60	46	37	31	58	45	37	31	44	37	31	43	36	31	42	35	31	29
9	56	42	34	28	54	42	34	28	40	33	28	39	33	28	38	32	28	26
10	52	39	31	26	51	38	31	26	37	30	25	36	30	25	36	30	25	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2612	2612	2612
5°	2625	2611	2622
10°	2626	2615	2618
15°	2622	2610	2616
20°	2616	2603	2611
25°	2602	2588	2602
30°	2592	2580	2583
35°	2580	2561	2565
40°	2562	2544	2538
45°	2535	2522	2515
50°	2514	2492	2487
55°	2477	2453	2447
60°	2429	2404	2380
65°	2372	2342	2298
70°	2301	2269	2210
75°	2215	2161	2077
80°	2106	2043	1918
85°	1955	1866	1742

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2535 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590951
CATALOG NUMBER: 24CGTX-45-L93050-W2A-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.0	3.2
10°-20°	459.9	9.2
20°-30°	699.8	14.0
30°-40°	848.4	17.0
40°-50°	888.1	17.8
50°-60°	812.6	16.3
60°-70°	632.3	12.6
70°-80°	381.0	7.6
80°-90°	118.4	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1319.7	26.4
0°-40°	2168.1	43.4
0°-60°	3868.9	77.4
0°-90°	5000.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5000.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1686	1686	1686	1686	1686	
5°	1688	1683	1679	1682	1686	161
15°	1635	1629	1627	1625	1631	461
25°	1522	1518	1514	1514	1522	702
35°	1364	1358	1354	1351	1356	852
45°	1157	1156	1151	1148	1148	893
55°	917	914	908	904	906	819
65°	647	646	639	634	627	641
75°	370	367	361	354	347	392
85°	110	109	105	102	98	124
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1590951
CATALOG NUMBER: 24CGTX-45-L93050-W2A-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	*1686*	1686	1686	1686	1686
2.5°	*1693*	*1687*	*1684*	*1686*	*1685*
5°	*1688*	1683	1679	1682	1686
7.5°	*1681*	1677	1673	1672	1674
10°	*1669*	1662	1662	1659	1664
12.5°	*1649*	1651	1645	1647	1651
15°	*1635*	1629	1627	1625	1631
17.5°	*1610*	1608	1608	1605	1610
20°	*1587*	1580	1579	1578	1584
22.5°	*1554*	1554	1551	1550	1550
25°	*1522*	1518	1514	1514	1522
27.5°	*1488*	1483	1483	1480	1483
30°	*1449*	1445	1442	1441	1444
32.5°	*1406*	1402	1399	1399	1402
35°	*1364*	1358	1354	1351	1356
37.5°	*1311*	1313	1307	1307	1307
40°	*1267*	1260	1258	1255	1255
42.5°	*1210*	1208	1206	1205	1205
45°	*1157*	1156	1151	1148	1148
47.5°	*1104*	1097	1093	1089	1092
50°	*1043*	1039	1034	1029	1032
52.5°	*981*	978	972	970	966
55°	*917*	914	908	904	906
57.5°	*850*	848	846	840	837
60°	*784*	783	776	771	768
62.5°	*716*	714	709	703	704
65°	*647*	646	639	634	627
67.5°	*580*	577	569	562	559
70°	*508*	505	501	491	488
72.5°	*443*	437	428	421	418
75°	*370*	367	361	354	347
77.5°	*303*	301	293	284	281
80°	*236*	234	229	220	215
82.5°	*174*	172	166	162	158
85°	*110*	109	105	102	98
87.5°	*52*	52	49	49	48
90°	*0*	0	0	0	0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

TEST NUMBER: P1590951
CATALOG NUMBER: 24CGTX-45-L93050-W2A-3000K

CIE UGR TABLE:

Reflectances:											
	Ceiling	0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
	Wall	0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
	Reference plane	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.34	17.00	15.71	17.32	17.63	15.27	16.93	15.63	17.24	17.56
	3H	17.28	18.78	17.65	19.11	19.47	17.13	18.64	17.51	18.97	19.33
	4H	18.04	19.46	18.44	19.81	20.18	17.85	19.27	18.25	19.62	19.99
	6H	18.64	19.96	19.05	20.32	20.71	18.39	19.71	18.80	20.08	20.47
	8H	18.85	20.12	19.28	20.50	20.90	18.59	19.85	19.01	20.23	20.63
	12H	19.01	20.22	19.44	20.60	21.03	18.72	19.93	19.15	20.31	20.74
4H	2H	16.00	17.42	16.40	17.77	18.14	15.94	17.36	16.34	17.71	18.08
	3H	18.16	19.35	18.57	19.75	20.15	18.03	19.23	18.44	19.62	20.02
	4H	19.06	20.14	19.49	20.55	20.99	18.88	19.97	19.31	20.38	20.82
	6H	19.80	20.75	20.25	21.19	21.64	19.56	20.51	20.02	20.95	21.41
	8H	20.07	20.96	20.53	21.41	21.87	19.81	20.70	20.27	21.14	21.61
	12H	20.29	21.09	20.77	21.56	22.03	20.00	20.80	20.48	21.27	21.74
8H	4H	19.40	20.29	19.86	20.73	21.19	19.25	20.14	19.71	20.58	21.04
	6H	20.28	21.03	20.77	21.51	21.99	20.06	20.81	20.56	21.29	21.77
	8H	20.65	21.31	21.15	21.82	22.30	20.40	21.06	20.90	21.57	22.05
	12H	20.95	21.54	21.45	22.03	22.59	20.67	21.26	21.17	21.75	22.31
12H	4H	19.44	20.24	19.92	20.72	21.19	19.30	20.10	19.78	20.57	21.04
	6H	20.35	21.02	20.86	21.53	22.01	20.15	20.81	20.65	21.32	21.80
	8H	20.78	21.37	21.29	21.86	22.42	20.54	21.13	21.05	21.62	22.18

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2512-631-41-R2

Test Date: 02/05/2026

Luminaire Tested: 22CGTX-50-L93050-W2A-3000K

Data in this report applies to families of products including 22CGTX


Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.05

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2512-631-41-R2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	07/28/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	Metalux
Catalog Number:	**22CGTX-50-L93050-W2A-3000K**
Description:	*THIS IS A REVISION OF REPORT SP1-2512-631-41-R2 TO UPDATE THE CATALOG INFORMATION* 2X2 5000 LUMEN HE CGTX TUNABLE WHITE FROM 3000K TO 5000K - 9.5 Volt

Spectral Parameters

CCT (K):	3066	CRI (Ra):	91.7		
CIE u':	0.2482	R1:	93.0	R9:	52.5
CIE v':	0.5206	R2:	94.0	R10:	85.0
Duv:	0.0004	R3:	94.3	R11:	94.8
CIE x:	0.4328	R4:	93.4	R12:	82.8
CIE y:	0.4036	R5:	92.4	R13:	92.9
CIE z:	0.1636	R6:	94.1	R14:	95.7
Peak Wavelength (nm):	630	R7:	91.5	R15:	87.8
Dominant Wavelength (nm):	582	R8:	80.7		
Purity:	51.0461				
Rf:	89.5				
Rg:	102				




Test Conditions

Stabilization Time:	20M
Operation Time:	1H 20M
Sphere Temperature (°C):	25.1


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2025	6/16/2026
Power Meter	XITRON INXT2011004	10/21/2025	10/21/2026
AC Power Source	CHROMA 61603 IN0063	10/21/2025	10/21/2026
DC Power Source	AGILENT E3634A IN0208	10/21/2025	10/21/2026
Sphere Thermometer	ONSET IN0085	10/21/2025	10/21/2026
Room Thermometer	ONSET IN0046	10/21/2025	10/21/2026

REPORT NUMBER: SP1-2512-631-41-R2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 3066K
CIE x = 0.4328
CIE y = 0.4036
Duv = 0.0004

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2512-631-41-R2

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	96	NR	620	317	NR	750	8	NR	880	0	NR
365	0	NR	495	121	NR	625	324	NR	755	7	NR	885	0	NR
370	0	NR	500	146	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	167	NR	635	572	NR	765	5	NR	895	0	NR
380	0	NR	510	183	NR	640	207	NR	770	4	NR	900	0	NR
385	1	NR	515	196	NR	645	215	NR	775	3	NR	905	0	NR
390	1	NR	520	205	NR	650	175	NR	780	3	NR	910	0	NR
395	2	NR	525	212	NR	655	147	NR	785	3	NR	915	0	NR
400	3	NR	530	218	NR	660	125	NR	790	2	NR	920	0	NR
405	4	NR	535	224	NR	665	106	NR	795	2	NR	925	0	NR
410	6	NR	540	230	NR	670	97	NR	800	2	NR	930	0	NR
415	11	NR	545	236	NR	675	80	NR	805	1	NR	935	0	NR
420	19	NR	550	244	NR	680	69	NR	810	1	NR	940	0	NR
425	34	NR	555	250	NR	685	59	NR	815	1	NR	945	0	NR
430	57	NR	560	260	NR	690	51	NR	820	1	NR	950	0	NR
435	92	NR	565	269	NR	695	44	NR	825	1	NR	955	0	NR
440	151	NR	570	277	NR	700	37	NR	830	1	NR	960	0	NR
445	208	NR	575	286	NR	705	32	NR	835	1	NR	965	0	NR
450	184	NR	580	294	NR	710	27	NR	840	1	NR	970	0	NR
455	122	NR	585	301	NR	715	23	NR	845	0	NR	975	0	NR
460	96	NR	590	307	NR	720	20	NR	850	0	NR	980	0	NR
465	76	NR	595	308	NR	725	17	NR	855	0	NR	985	0	NR
470	59	NR	600	312	NR	730	14	NR	860	0	NR	990	0	NR
475	57	NR	605	315	NR	735	12	NR	865	0	NR	995	0	NR
480	63	NR	610	347	NR	740	10	NR	870	0	NR	1000	0	NR
485	76	NR	615	356	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2512-631-41-R2

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR **S/P: 1.41**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	96	NR	620	317	NR	750	8	NR	880	0	NR
365	0	NR	495	121	NR	625	324	NR	755	7	NR	885	0	NR
370	0	NR	500	146	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	167	NR	635	572	NR	765	5	NR	895	0	NR
380	0	NR	510	183	NR	640	207	NR	770	4	NR	900	0	NR
385	1	NR	515	196	NR	645	215	NR	775	3	NR	905	0	NR
390	1	NR	520	205	NR	650	175	NR	780	3	NR	910	0	NR
395	2	NR	525	212	NR	655	147	NR	785	3	NR	915	0	NR
400	3	NR	530	218	NR	660	125	NR	790	2	NR	920	0	NR
405	4	NR	535	224	NR	665	106	NR	795	2	NR	925	0	NR
410	6	NR	540	230	NR	670	97	NR	800	2	NR	930	0	NR
415	11	NR	545	236	NR	675	80	NR	805	1	NR	935	0	NR
420	19	NR	550	244	NR	680	69	NR	810	1	NR	940	0	NR
425	34	NR	555	250	NR	685	59	NR	815	1	NR	945	0	NR
430	57	NR	560	260	NR	690	51	NR	820	1	NR	950	0	NR
435	92	NR	565	269	NR	695	44	NR	825	1	NR	955	0	NR
440	151	NR	570	277	NR	700	37	NR	830	1	NR	960	0	NR
445	208	NR	575	286	NR	705	32	NR	835	1	NR	965	0	NR
450	184	NR	580	294	NR	710	27	NR	840	1	NR	970	0	NR
455	122	NR	585	301	NR	715	23	NR	845	0	NR	975	0	NR
460	96	NR	590	307	NR	720	20	NR	850	0	NR	980	0	NR
465	76	NR	595	308	NR	725	17	NR	855	0	NR	985	0	NR
470	59	NR	600	312	NR	730	14	NR	860	0	NR	990	0	NR
475	57	NR	605	315	NR	735	12	NR	865	0	NR	995	0	NR
480	63	NR	610	347	NR	740	10	NR	870	0	NR	1000	0	NR
485	76	NR	615	356	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2512-631-41-R2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.7**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	96	NR	620	317	NR	750	8	NR	880	0	NR
365	0	NR	495	121	NR	625	324	NR	755	7	NR	885	0	NR
370	0	NR	500	146	NR	630	1000	NR	760	6	NR	890	0	NR
375	0	NR	505	167	NR	635	572	NR	765	5	NR	895	0	NR
380	0	NR	510	183	NR	640	207	NR	770	4	NR	900	0	NR
385	1	NR	515	196	NR	645	215	NR	775	3	NR	905	0	NR
390	1	NR	520	205	NR	650	175	NR	780	3	NR	910	0	NR
395	2	NR	525	212	NR	655	147	NR	785	3	NR	915	0	NR
400	3	NR	530	218	NR	660	125	NR	790	2	NR	920	0	NR
405	4	NR	535	224	NR	665	106	NR	795	2	NR	925	0	NR
410	6	NR	540	230	NR	670	97	NR	800	2	NR	930	0	NR
415	11	NR	545	236	NR	675	80	NR	805	1	NR	935	0	NR
420	19	NR	550	244	NR	680	69	NR	810	1	NR	940	0	NR
425	34	NR	555	250	NR	685	59	NR	815	1	NR	945	0	NR
430	57	NR	560	260	NR	690	51	NR	820	1	NR	950	0	NR
435	92	NR	565	269	NR	695	44	NR	825	1	NR	955	0	NR
440	151	NR	570	277	NR	700	37	NR	830	1	NR	960	0	NR
445	208	NR	575	286	NR	705	32	NR	835	1	NR	965	0	NR
450	184	NR	580	294	NR	710	27	NR	840	1	NR	970	0	NR
455	122	NR	585	301	NR	715	23	NR	845	0	NR	975	0	NR
460	96	NR	590	307	NR	720	20	NR	850	0	NR	980	0	NR
465	76	NR	595	308	NR	725	17	NR	855	0	NR	985	0	NR
470	59	NR	600	312	NR	730	14	NR	860	0	NR	990	0	NR
475	57	NR	605	315	NR	735	12	NR	865	0	NR	995	0	NR
480	63	NR	610	347	NR	740	10	NR	870	0	NR	1000	0	NR
485	76	NR	615	356	NR	745	9	NR	875	0	NR			


REPORT NUMBER: SP1-2512-631-41-R2

TM-30-18


Summary


R_f = 89.5
R_g = 102
CIE R_a = 91.7
R_9 = 52.5


Spectral Power Distribution Comparison




Color Vector Graphics










REPORT NUMBER: SP1-2512-631-41-R2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 87	CES51 = 94	CES76 = 85
CES02 = 63	CES27 = 96	CES52 = 94	CES77 = 88
CES03 = 32	CES28 = 94	CES53 = 89	CES78 = 83
CES04 = 70	CES29 = 83	CES54 = 97	CES79 = 92
CES05 = 50	CES30 = 85	CES55 = 95	CES80 = 92
CES06 = 51	CES31 = 85	CES56 = 89	CES81 = 75
CES07 = 43	CES32 = 80	CES57 = 88	CES82 = 96
CES08 = 42	CES33 = 84	CES58 = 89	CES83 = 93
CES09 = 29	CES34 = 90	CES59 = 98	CES84 = 96
CES10 = 76	CES35 = 94	CES60 = 99	CES85 = 83
CES11 = 58	CES36 = 97	CES61 = 97	CES86 = 77
CES12 = 65	CES37 = 91	CES62 = 94	CES87 = 91
CES13 = 44	CES38 = 90	CES63 = 89	CES88 = 93
CES14 = 74	CES39 = 95	CES64 = 93	CES89 = 81
CES15 = 72	CES40 = 92	CES65 = 89	CES90 = 92
CES16 = 48	CES41 = 91	CES66 = 91	CES91 = 89
CES17 = 50	CES42 = 89	CES67 = 91	CES92 = 79
CES18 = 57	CES43 = 87	CES68 = 93	CES93 = 88
CES19 = 72	CES44 = 99	CES69 = 95	CES94 = 72
CES20 = 67	CES45 = 91	CES70 = 89	CES95 = 86
CES21 = 86	CES46 = 90	CES71 = 89	CES96 = 91
CES22 = 79	CES47 = 83	CES72 = 96	CES97 = 90
CES23 = 92	CES48 = 87	CES73 = 83	CES98 = 89
CES24 = 91	CES49 = 88	CES74 = 92	CES99 = 90
CES25 = 72	CES50 = 94	CES75 = 87	





REPORT NUMBER: SP1-2512-631-41-R2

TM-30-18

Color Rendition by Hue-Angle Bin









REPORT NUMBER: SP1-2512-631-41-R2

TM-30-18

Measure Comparisons





(END OF REPORT)