

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1432790

Luminaire Tested: EHBR1-54-UNV-N-L835-UPL24

Issue Date: 3/20/2026

Test Information

Test Method: LM-79-2019
Report Number: P1432790
REPORT IS A COMBINATION OF REPORTS P1431879 AND P1431635
Test Lab: INNOVATION CENTER
Issue Date: 3/20/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-54-UNV-N-L835-UPL24
Description: Elevate Round Highbay at, 53500 lumens, 3500K 80CRI LEDs with N lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 55110.2 lumens
Efficiency: N/A
Efficacy: 176.4 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.8
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')
CIE Type: Direct

Input Watts (W): 312.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1432790
CATALOG NUMBER: EHBR1-54-UNV-N-L835-UPL24

Luminous Intensity Polar Plot





TEST NUMBER: P1432790

CATALOG NUMBER: EHBR1-54-UNV-N-L835-UPL24

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	118	118	118	118	115	115	115	115	109	109	109	103	103	103	98	98	98	98	98	98	96
1	111	108	105	102	108	105	103	100	101	98	96	96	94	93	92	91	89	89	89	89	87
2	105	99	94	90	102	97	93	89	93	89	86	89	86	84	86	84	82	82	82	82	80
3	99	91	86	81	96	90	84	80	86	82	78	83	80	76	80	77	75	75	75	75	73
4	93	85	78	74	91	83	77	73	80	75	72	78	74	70	75	72	69	69	69	69	67
5	88	79	72	67	86	77	71	67	75	70	66	73	68	65	71	67	64	64	64	64	62
6	83	74	67	62	81	72	66	62	71	65	61	69	64	60	67	63	60	60	60	60	58
7	79	69	62	58	77	68	62	58	66	61	57	65	60	56	63	59	56	56	56	56	54
8	75	65	58	54	74	64	58	54	63	57	53	61	56	53	60	56	52	52	52	52	51
9	71	61	55	51	70	61	55	50	59	54	50	58	53	50	57	53	49	49	49	49	48
10	68	58	52	48	67	57	51	48	56	51	47	55	50	47	54	50	47	47	47	47	45

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	289442	289442	289442
5°	283823	283823	283823
10°	269381	269381	269381
15°	245101	245101	245101
20°	210243	210243	210243
25°	165390	165390	165390
30°	113500	113500	113500
35°	67423	67423	67423
40°	39893	39893	39893
45°	28637	28637	28637
50°	23539	23539	23539
55°	21393	21393	21393
60°	20479	20479	20479
65°	19533	19533	19533
70°	18165	18165	18165
75°	16422	16422	16422
80°	13631	13631	13631
85°	8630	8630	8630

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 28637 cd/sqm



TEST NUMBER: P1432790
 CATALOG NUMBER: EHBR1-54-UNV-N-L835-UPL24

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	5677.5	10.3
10°-20°	14251.5	25.9
20°-30°	14901.5	27.0
30°-40°	8074.0	14.7
40°-50°	3714.5	6.7
50°-60°	2617.6	4.7
60°-70°	2014.5	3.7
70°-80°	1221.2	2.2
80°-90°	348.0	0.6
90°-100°	65.5	0.1
100°-110°	409.1	0.7
110°-120°	731.5	1.3
120°-130°	429.2	0.8
130°-140°	263.3	0.5
140°-150°	182.6	0.3
150°-160°	118.6	0.2
160°-170°	67.6	0.1
170°-180°	22.3	0.0
0°-30°	34830.5	63.2
0°-40°	42904.5	77.9
0°-60°	49236.6	89.3
0°-90°	52820.4	95.8
90°-120°	1206.1	2.2
90°-150°	2081.2	3.8
90°-180°	2290.0	4.2
0°-180°	55110.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	61635	61635	61635	61635	61635	
5°	60601	60601	60601	60601	60601	5678
15°	51421	51421	51421	51421	51421	14252
25°	33028	33028	33028	33028	33028	14901
35°	12374	12374	12374	12374	12374	8074
45°	4633	4633	4633	4633	4633	3714
55°	2891	2891	2891	2891	2891	2618
65°	2039	2039	2039	2039	2039	2014
75°	1157	1157	1157	1157	1157	1221
85°	297	297	297	297	297	329
90°	19	29	49	32	19	23
95°	29	48	106	52	33	28
105°	143	282	720	311	189	191
115°	658	692	851	815	810	606
125°	474	443	455	461	518	433
135°	346	336	347	326	325	271
145°	284	280	298	294	292	180
155°	249	246	258	258	258	116
165°	233	233	240	240	238	67
175°	231	231	235	235	235	22
180°	233	233	233	233	233	



TEST NUMBER: P1432790

CATALOG NUMBER: EHBR1-54-UNV-N-L835-UPL24

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	61634.6	61634.6	61634.6	61634.6	61634.6
2.5°	61416.1	61416.1	61416.1	61416.1	61416.1
5°	60600.7	60600.7	60600.7	60600.7	60600.7
7.5°	59208.7	59208.7	59208.7	59208.7	59208.7
10°	57233.8	57233.8	57233.8	57233.8	57233.8
12.5°	54681.6	54681.6	54681.6	54681.6	54681.6
15°	51421.0	51421.0	51421.0	51421.0	51421.0
17.5°	47638.2	47638.2	47638.2	47638.2	47638.2
20°	43211.1	43211.1	43211.1	43211.1	43211.1
22.5°	38282.0	38282.0	38282.0	38282.0	38282.0
25°	33028.2	33028.2	33028.2	33028.2	33028.2
27.5°	27458.4	27458.4	27458.4	27458.4	27458.4
30°	21831.6	21831.6	21831.6	21831.6	21831.6
32.5°	16755.0	16755.0	16755.0	16755.0	16755.0
35°	12374.5	12374.5	12374.5	12374.5	12374.5
37.5°	9085.8	9085.8	9085.8	9085.8	9085.8
40°	6914.4	6914.4	6914.4	6914.4	6914.4
42.5°	5544.3	5544.3	5544.3	5544.3	5544.3
45°	4633.3	4633.3	4633.3	4633.3	4633.3
47.5°	3976.8	3976.8	3976.8	3976.8	3976.8
50°	3508.1	3508.1	3508.1	3508.1	3508.1
52.5°	3165.8	3165.8	3165.8	3165.8	3165.8
55°	2891.1	2891.1	2891.1	2891.1	2891.1
57.5°	2668.2	2668.2	2668.2	2668.2	2668.2
60°	2461.9	2461.9	2461.9	2461.9	2461.9
62.5°	2255.6	2255.6	2255.6	2255.6	2255.6
65°	2038.8	2038.8	2038.8	2038.8	2038.8
67.5°	1817.7	1817.7	1817.7	1817.7	1817.7
70°	1593.9	1593.9	1593.9	1593.9	1593.9
72.5°	1376.2	1376.2	1376.2	1376.2	1376.2
75°	1156.8	1156.8	1156.8	1156.8	1156.8
77.5°	941.8	941.8	941.8	941.8	941.8
80°	717.1	717.1	717.1	717.1	717.1
82.5°	502.0	502.0	502.0	502.0	502.0
85°	296.6	296.6	296.6	296.6	296.6
87.5°	106.2	106.2	106.2	106.2	106.2
90°	18.8	29.3	49.0	31.9	18.8
92.5°	24.9	42.0	76.0	39.3	22.3
95°	28.8	48.5	106.2	52.5	32.8
97.5°	36.7	53.7	121.9	64.2	51.1
100°	48.5	62.9	190.1	78.6	68.2
102.5°	82.5	133.7	403.7	148.1	103.6
105°	142.8	281.8	719.5	310.6	188.7
107.5°	247.7	504.6	948.9	550.5	357.8
110°	462.6	669.7	994.7	756.3	572.7



TEST NUMBER: P1432790

CATALOG NUMBER: EHBR1-54-UNV-N-L835-UPL24

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	625.2	719.5	952.8	834.8	745.7
115°	657.9	692.0	850.6	815.2	810.0
117.5°	635.6	631.8	722.1	732.6	782.5
120°	588.5	562.2	602.9	639.6	706.4
122.5°	529.5	498.0	516.4	543.9	610.7
125°	474.5	443.0	454.8	461.4	517.7
127.5°	426.0	405.0	411.5	403.7	439.1
130°	393.2	374.8	384.0	365.7	382.7
132.5°	365.7	353.8	364.3	342.1	347.4
135°	346.0	335.5	347.4	326.3	325.0
137.5°	328.9	319.8	331.5	315.8	312.0
140°	313.2	305.4	318.5	306.7	304.1
142.5°	296.2	290.9	306.7	298.9	296.2
145°	284.4	280.4	297.5	293.6	292.3
147.5°	273.9	271.3	287.0	285.7	285.7
150°	264.7	262.1	277.8	276.6	277.8
152.5°	255.6	253.0	267.3	266.1	267.3
155°	249.0	246.4	258.2	258.2	258.2
157.5°	243.8	242.4	251.6	251.6	251.6
160°	239.8	238.5	246.4	246.4	245.0
162.5°	235.9	234.6	243.8	242.4	242.4
165°	233.3	233.3	239.8	239.8	238.5
167.5°	233.3	232.0	238.5	238.5	237.2
170°	232.0	232.0	237.2	235.9	234.6
172.5°	232.0	232.0	237.2	235.9	234.6
175°	230.7	230.7	234.6	234.6	234.6
177.5°	232.0	232.0	234.6	234.6	233.3
180°	233.3	233.3	233.3	233.3	233.3



TEST NUMBER: P1432790
 CATALOG NUMBER: EHBR1-54-UNV-N-L835-UPL24

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.78	19.88	19.23	20.28	20.71	18.78	19.88	19.23	20.28	20.71
	3H	20.56	21.54	21.02	21.96	22.43	20.56	21.54	21.02	21.96	22.43
	4H	21.22	22.13	21.70	22.57	23.06	21.22	22.13	21.70	22.57	23.06
	6H	21.68	22.52	22.17	22.98	23.47	21.68	22.52	22.17	22.98	23.47
	8H	21.81	22.60	22.31	23.07	23.58	21.81	22.60	22.31	23.07	23.58
	12H	21.86	22.61	22.37	23.08	23.61	21.86	22.61	22.37	23.08	23.61
4H	2H	19.33	20.24	19.81	20.68	21.16	19.33	20.24	19.81	20.68	21.16
	3H	21.30	22.05	21.79	22.54	23.04	21.30	22.05	21.79	22.54	23.04
	4H	22.07	22.75	22.58	23.25	23.79	22.07	22.75	22.58	23.25	23.79
	6H	22.64	23.22	23.18	23.75	24.32	22.64	23.22	23.18	23.75	24.32
	8H	22.80	23.34	23.34	23.87	24.44	22.80	23.34	23.34	23.87	24.44
	12H	22.88	23.36	23.44	23.92	24.49	22.88	23.36	23.44	23.92	24.49
8H	4H	22.30	22.84	22.84	23.37	23.94	22.30	22.84	22.84	23.37	23.94
	6H	22.98	23.42	23.56	24.00	24.57	22.98	23.42	23.56	24.00	24.57
	8H	23.20	23.59	23.80	24.18	24.77	23.20	23.59	23.80	24.18	24.77
	12H	23.34	23.68	23.93	24.25	24.92	23.34	23.68	23.93	24.25	24.92
12H	4H	22.30	22.77	22.86	23.33	23.91	22.30	22.77	22.86	23.33	23.91
	6H	23.01	23.40	23.60	23.99	24.58	23.01	23.40	23.60	23.99	24.58
	8H	23.27	23.61	23.86	24.18	24.85	23.27	23.61	23.86	24.18	24.85

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-3

Test Date: 07/31/2025

Luminaire Tested: EHBR-60-L835-N

Data in this report applies to families of products including EHBR-60-L835-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-3
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L835-N**
 Description: Elevate Round Highbay at, 60000 lumens, 3500K 80CRI LEDs with N lens

Spectral Parameters

CCT (K): 3468
 CIE u': 0.2375
 CIE v': 0.5091
 Duv: -0.0021
 CIE x: 0.4049
 CIE y: 0.3856
 CIE z: 0.2095
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 581
 Purity: 37.24544
 Rf: 80.1
 Rg: 101

CRI (Ra):	82.1		
R1:	82.9	R9:	27.6
R2:	85.6	R10:	63.8
R3:	85.9	R11:	81.2
R4:	82.8	R12:	57.2
R5:	81.0	R13:	82.6
R6:	79.7	R14:	91.0
R7:	86.5	R15:	79.4
R8:	72.1		



Test Conditions

Stabilization Time: 39M
 Operation Time: 1H 39M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-3

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-3

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	60	NR	620	327	NR	750	7	NR	880	0	NR
365	0	NR	495	82	NR	625	322	NR	755	6	NR	885	0	NR
370	0	NR	500	114	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	152	NR	635	645	NR	765	4	NR	895	0	NR
380	0	NR	510	189	NR	640	197	NR	770	4	NR	900	0	NR
385	1	NR	515	222	NR	645	189	NR	775	3	NR	905	0	NR
390	2	NR	520	248	NR	650	163	NR	780	3	NR	910	0	NR
395	3	NR	525	268	NR	655	134	NR	785	2	NR	915	0	NR
400	4	NR	530	283	NR	660	113	NR	790	2	NR	920	0	NR
405	6	NR	535	294	NR	665	94	NR	795	2	NR	925	0	NR
410	9	NR	540	305	NR	670	87	NR	800	2	NR	930	0	NR
415	18	NR	545	314	NR	675	70	NR	805	1	NR	935	0	NR
420	34	NR	550	323	NR	680	60	NR	810	1	NR	940	0	NR
425	62	NR	555	335	NR	685	51	NR	815	1	NR	945	0	NR
430	102	NR	560	346	NR	690	44	NR	820	1	NR	950	0	NR
435	159	NR	565	356	NR	695	38	NR	825	1	NR	955	0	NR
440	241	NR	570	364	NR	700	32	NR	830	1	NR	960	0	NR
445	363	NR	575	371	NR	705	28	NR	835	1	NR	965	0	NR
450	389	NR	580	375	NR	710	24	NR	840	1	NR	970	0	NR
455	245	NR	585	375	NR	715	20	NR	845	0	NR	975	0	NR
460	158	NR	590	373	NR	720	17	NR	850	0	NR	980	0	NR
465	120	NR	595	364	NR	725	15	NR	855	0	NR	985	0	NR
470	79	NR	600	357	NR	730	13	NR	860	0	NR	990	0	NR
475	57	NR	605	349	NR	735	11	NR	865	0	NR	995	0	NR
480	51	NR	610	371	NR	740	9	NR	870	0	NR	1000	0	NR
485	51	NR	615	387	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-3

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.43

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	60	NR	620	327	NR	750	7	NR	880	0	NR
365	0	NR	495	82	NR	625	322	NR	755	6	NR	885	0	NR
370	0	NR	500	114	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	152	NR	635	645	NR	765	4	NR	895	0	NR
380	0	NR	510	189	NR	640	197	NR	770	4	NR	900	0	NR
385	1	NR	515	222	NR	645	189	NR	775	3	NR	905	0	NR
390	2	NR	520	248	NR	650	163	NR	780	3	NR	910	0	NR
395	3	NR	525	268	NR	655	134	NR	785	2	NR	915	0	NR
400	4	NR	530	283	NR	660	113	NR	790	2	NR	920	0	NR
405	6	NR	535	294	NR	665	94	NR	795	2	NR	925	0	NR
410	9	NR	540	305	NR	670	87	NR	800	2	NR	930	0	NR
415	18	NR	545	314	NR	675	70	NR	805	1	NR	935	0	NR
420	34	NR	550	323	NR	680	60	NR	810	1	NR	940	0	NR
425	62	NR	555	335	NR	685	51	NR	815	1	NR	945	0	NR
430	102	NR	560	346	NR	690	44	NR	820	1	NR	950	0	NR
435	159	NR	565	356	NR	695	38	NR	825	1	NR	955	0	NR
440	241	NR	570	364	NR	700	32	NR	830	1	NR	960	0	NR
445	363	NR	575	371	NR	705	28	NR	835	1	NR	965	0	NR
450	389	NR	580	375	NR	710	24	NR	840	1	NR	970	0	NR
455	245	NR	585	375	NR	715	20	NR	845	0	NR	975	0	NR
460	158	NR	590	373	NR	720	17	NR	850	0	NR	980	0	NR
465	120	NR	595	364	NR	725	15	NR	855	0	NR	985	0	NR
470	79	NR	600	357	NR	730	13	NR	860	0	NR	990	0	NR
475	57	NR	605	349	NR	735	11	NR	865	0	NR	995	0	NR
480	51	NR	610	371	NR	740	9	NR	870	0	NR	1000	0	NR
485	51	NR	615	387	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-3

Melanopic Flux vs. Wavelength




Melanopic Lumens: NR

M/P: 2.75

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	60	NR	620	327	NR	750	7	NR	880	0	NR
365	0	NR	495	82	NR	625	322	NR	755	6	NR	885	0	NR
370	0	NR	500	114	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	152	NR	635	645	NR	765	4	NR	895	0	NR
380	0	NR	510	189	NR	640	197	NR	770	4	NR	900	0	NR
385	1	NR	515	222	NR	645	189	NR	775	3	NR	905	0	NR
390	2	NR	520	248	NR	650	163	NR	780	3	NR	910	0	NR
395	3	NR	525	268	NR	655	134	NR	785	2	NR	915	0	NR
400	4	NR	530	283	NR	660	113	NR	790	2	NR	920	0	NR
405	6	NR	535	294	NR	665	94	NR	795	2	NR	925	0	NR
410	9	NR	540	305	NR	670	87	NR	800	2	NR	930	0	NR
415	18	NR	545	314	NR	675	70	NR	805	1	NR	935	0	NR
420	34	NR	550	323	NR	680	60	NR	810	1	NR	940	0	NR
425	62	NR	555	335	NR	685	51	NR	815	1	NR	945	0	NR
430	102	NR	560	346	NR	690	44	NR	820	1	NR	950	0	NR
435	159	NR	565	356	NR	695	38	NR	825	1	NR	955	0	NR
440	241	NR	570	364	NR	700	32	NR	830	1	NR	960	0	NR
445	363	NR	575	371	NR	705	28	NR	835	1	NR	965	0	NR
450	389	NR	580	375	NR	710	24	NR	840	1	NR	970	0	NR
455	245	NR	585	375	NR	715	20	NR	845	0	NR	975	0	NR
460	158	NR	590	373	NR	720	17	NR	850	0	NR	980	0	NR
465	120	NR	595	364	NR	725	15	NR	855	0	NR	985	0	NR
470	79	NR	600	357	NR	730	13	NR	860	0	NR	990	0	NR
475	57	NR	605	349	NR	735	11	NR	865	0	NR	995	0	NR
480	51	NR	610	371	NR	740	9	NR	870	0	NR	1000	0	NR
485	51	NR	615	387	NR	745	8	NR	875	0	NR			

Summary

$R_f = 80.1$
 $R_g = 101$
 CIE $R_a = 82.1$
 $R_9 = 27.6$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 68	CES51 = 90	CES76 = 59
CES02 = 62	CES27 = 89	CES52 = 90	CES77 = 78
CES03 = 31	CES28 = 84	CES53 = 81	CES78 = 61
CES04 = 70	CES29 = 66	CES54 = 91	CES79 = 86
CES05 = 49	CES30 = 77	CES55 = 90	CES80 = 82
CES06 = 51	CES31 = 69	CES56 = 80	CES81 = 79
CES07 = 42	CES32 = 62	CES57 = 79	CES82 = 92
CES08 = 41	CES33 = 74	CES58 = 81	CES83 = 89
CES09 = 29	CES34 = 72	CES59 = 92	CES84 = 89
CES10 = 75	CES35 = 85	CES60 = 94	CES85 = 82
CES11 = 58	CES36 = 97	CES61 = 90	CES86 = 78
CES12 = 64	CES37 = 79	CES62 = 92	CES87 = 82
CES13 = 43	CES38 = 85	CES63 = 78	CES88 = 86
CES14 = 74	CES39 = 94	CES64 = 79	CES89 = 76
CES15 = 71	CES40 = 89	CES65 = 76	CES90 = 85
CES16 = 47	CES41 = 89	CES66 = 73	CES91 = 83
CES17 = 49	CES42 = 77	CES67 = 70	CES92 = 73
CES18 = 56	CES43 = 74	CES68 = 76	CES93 = 84
CES19 = 72	CES44 = 99	CES69 = 81	CES94 = 65
CES20 = 66	CES45 = 83	CES70 = 68	CES95 = 79
CES21 = 86	CES46 = 82	CES71 = 64	CES96 = 85
CES22 = 78	CES47 = 81	CES72 = 88	CES97 = 85
CES23 = 92	CES48 = 80	CES73 = 60	CES98 = 82
CES24 = 91	CES49 = 80	CES74 = 97	CES99 = 81
CES25 = 72	CES50 = 89	CES75 = 64	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)