

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1432303

Luminaire Tested: EHBR1-18-UNV-TASM-L830-UPL30

Issue Date: 3/20/2026

Test Information

Test Method: LM-79-2019
Report Number: P1432303
REPORT IS A COMBINATION OF REPORTS P1431680 AND P1431635
Test Lab: INNOVATION CENTER
Issue Date: 3/20/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-18-UNV-TASM-L830-UPL30
Description: Elevate Round Highbay at, 18000 lumens, 3000K 80CRI LEDs with TASM lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 20047.4 lumens
Efficiency: N/A
Efficacy: 171.8 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.84 / 0.9
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 116.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1432303
CATALOG NUMBER: EHBR1-18-UNV-TASM-L830-UPL30

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°



TEST NUMBER: P1432303
 CATALOG NUMBER: EHBR1-18-UNV-TASM-L830-UPL30

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 111 | 103 | 103 | 103 | 96 | 96 | 96 | 89 | 89 | 89 | 89 | 89 | 89 | 86 |
| 1 | 108 | 105 | 102 | 99 | 104 | 101 | 98 | 96 | 94 | 92 | 90 | 88 | 87 | 85 | 83 | 81 | 80 | 80 | 80 | 80 | 77 |
| 2 | 101 | 95 | 90 | 86 | 98 | 92 | 88 | 84 | 87 | 83 | 80 | 81 | 79 | 76 | 77 | 74 | 72 | 72 | 72 | 72 | 70 |
| 3 | 95 | 87 | 81 | 76 | 91 | 84 | 79 | 74 | 80 | 75 | 71 | 75 | 72 | 69 | 71 | 68 | 66 | 66 | 66 | 66 | 63 |
| 4 | 89 | 80 | 73 | 68 | 86 | 78 | 72 | 67 | 74 | 69 | 65 | 70 | 66 | 62 | 66 | 63 | 60 | 60 | 60 | 60 | 58 |
| 5 | 83 | 74 | 67 | 62 | 81 | 72 | 65 | 61 | 68 | 63 | 59 | 65 | 60 | 57 | 62 | 58 | 55 | 55 | 55 | 55 | 53 |
| 6 | 78 | 68 | 61 | 56 | 76 | 67 | 60 | 55 | 63 | 58 | 54 | 61 | 56 | 52 | 58 | 54 | 51 | 51 | 51 | 51 | 49 |
| 7 | 74 | 63 | 56 | 52 | 72 | 62 | 56 | 51 | 59 | 54 | 50 | 57 | 52 | 48 | 54 | 50 | 47 | 47 | 47 | 47 | 45 |
| 8 | 70 | 59 | 52 | 48 | 68 | 58 | 51 | 47 | 55 | 50 | 46 | 53 | 49 | 45 | 51 | 47 | 44 | 44 | 44 | 44 | 42 |
| 9 | 66 | 55 | 49 | 44 | 64 | 54 | 48 | 44 | 52 | 47 | 43 | 50 | 45 | 42 | 48 | 44 | 41 | 41 | 41 | 41 | 39 |
| 10 | 63 | 52 | 45 | 41 | 61 | 51 | 45 | 41 | 49 | 44 | 40 | 47 | 43 | 39 | 46 | 42 | 38 | 38 | 38 | 38 | 37 |

AVERAGE LUMINANCE (cd/sqm):

| | 0° | 90° | 180° | 270° |
|-----|-------|-------|-------|-------|
| 0° | 72198 | 72198 | 72198 | 72198 |
| 5° | 71759 | 76553 | 71759 | 68035 |
| 10° | 70876 | 78518 | 70876 | 64389 |
| 15° | 68784 | 72968 | 68784 | 59478 |
| 20° | 64330 | 58510 | 64330 | 52978 |
| 25° | 56937 | 40539 | 56937 | 44398 |
| 30° | 46231 | 26373 | 46231 | 33219 |
| 35° | 33158 | 17080 | 33158 | 22114 |
| 40° | 21438 | 11773 | 21438 | 13947 |
| 45° | 13602 | 9119 | 13602 | 9937 |
| 50° | 10101 | 7749 | 10101 | 8277 |
| 55° | 8247 | 7059 | 8247 | 7307 |
| 60° | 7141 | 6725 | 7141 | 6765 |
| 65° | 6510 | 6485 | 6510 | 6458 |
| 70° | 6170 | 6354 | 6170 | 6272 |
| 75° | 5769 | 6147 | 5769 | 5962 |
| 80° | 5070 | 5803 | 5070 | 5425 |
| 85° | 3279 | 4143 | 3279 | 3951 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 19123 cd/sqm



TEST NUMBER: P1432303

CATALOG NUMBER: EHBR1-18-UNV-TASM-L830-UPL30

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 1461.8 | 7.3 |
| 10°-20° | 3977.0 | 19.8 |
| 20°-30° | 4664.2 | 23.3 |
| 30°-40° | 3243.7 | 16.2 |
| 40°-50° | 1611.9 | 8.0 |
| 50°-60° | 964.1 | 4.8 |
| 60°-70° | 678.6 | 3.4 |
| 70°-80° | 437.1 | 2.2 |
| 80°-90° | 143.9 | 0.7 |
| 90°-100° | 76.0 | 0.4 |
| 100°-110° | 499.0 | 2.5 |
| 110°-120° | 922.3 | 4.6 |
| 120°-130° | 547.7 | 2.7 |
| 130°-140° | 330.7 | 1.6 |
| 140°-150° | 228.3 | 1.1 |
| 150°-160° | 148.4 | 0.7 |
| 160°-170° | 84.7 | 0.4 |
| 170°-180° | 28.0 | 0.1 |
| 0°-30° | 10103.1 | 50.4 |
| 0°-40° | 13346.7 | 66.6 |
| 0°-60° | 15922.8 | 79.4 |
| 0°-90° | 17182.4 | 85.7 |
| 90°-120° | 1497.3 | 7.5 |
| 90°-150° | 2603.9 | 13.0 |
| 90°-180° | 2865.0 | 14.3 |
| 0°-180° | 20047.4 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | 90° | 180° | 270° | 360° | Flux |
|------|-------|-------|-------|-------|-------|------|
| 0° | 15374 | 15374 | 15374 | 15374 | 15374 | |
| 5° | 15322 | 16345 | 15322 | 14526 | 15322 | 1454 |
| 15° | 14430 | 15308 | 14430 | 12478 | 14430 | 4033 |
| 25° | 11370 | 8096 | 11370 | 8866 | 11370 | 5148 |
| 35° | 6086 | 3135 | 6086 | 4059 | 6086 | 3799 |
| 45° | 2201 | 1475 | 2201 | 1608 | 2201 | 1801 |
| 55° | 1114 | 954 | 1114 | 987 | 1114 | 1019 |
| 65° | 680 | 677 | 680 | 674 | 680 | 682 |
| 75° | 406 | 433 | 406 | 420 | 406 | 427 |
| 85° | 113 | 142 | 113 | 136 | 113 | 125 |
| 90° | 21 | 23 | 21 | 21 | 21 | 15 |
| 95° | 40 | 37 | 40 | 35 | 40 | 43 |
| 105° | 229 | 115 | 229 | 174 | 229 | 309 |
| 115° | 982 | 837 | 982 | 797 | 982 | 895 |
| 125° | 628 | 657 | 628 | 575 | 628 | 578 |
| 135° | 396 | 457 | 396 | 420 | 396 | 314 |
| 145° | 357 | 374 | 357 | 348 | 357 | 224 |
| 155° | 317 | 330 | 317 | 307 | 317 | 148 |
| 165° | 297 | 305 | 297 | 291 | 297 | 85 |
| 175° | 294 | 298 | 294 | 289 | 294 | 28 |
| 180° | 293 | 293 | 293 | 293 | 293 | |



TEST NUMBER: P1432303
 CATALOG NUMBER: EHBR1-18-UNV-TASM-L830-UPL30

CANDELA DISTRIBUTION (FULL):

| | 0° | 22.5° | 45° | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° | 202.5° | 225° |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 15374.0 | 15374.0 | 15374.0 | 15374.0 | 15374.0 | 15374.0 | 15374.0 | 15374.0 | 15374.0 | 15374.0 | 15374.0 |
| 2.5° | 15365.0 | 15563.7 | 15724.5 | 15830.7 | 15883.1 | 15830.7 | 15724.5 | 15563.7 | 15365.0 | 15167.6 | 15031.8 |
| 5° | 15321.6 | 15719.4 | 16056.4 | 16276.9 | 16345.2 | 16276.9 | 16056.4 | 15719.4 | 15321.6 | 14945.7 | 14696.2 |
| 7.5° | 15217.5 | 15837.3 | 16338.1 | 16595.5 | 16658.3 | 16595.5 | 16338.1 | 15837.3 | 15217.5 | 14685.3 | 14370.2 |
| 10° | 15058.6 | 15911.7 | 16490.3 | 16674.7 | 16682.2 | 16674.7 | 16490.3 | 15911.7 | 15058.6 | 14341.7 | 13970.1 |
| 12.5° | 14805.2 | 15885.2 | 16439.2 | 16378.7 | 16241.1 | 16378.7 | 16439.2 | 15885.2 | 14805.2 | 13921.9 | 13453.2 |
| 15° | 14430.5 | 15728.0 | 16116.1 | 15623.4 | 15308.3 | 15623.4 | 16116.1 | 15728.0 | 14430.5 | 13355.1 | 12811.5 |
| 17.5° | 13902.4 | 15434.0 | 15441.5 | 14466.8 | 13872.3 | 14466.8 | 15441.5 | 15434.0 | 13902.4 | 12662.1 | 12063.3 |
| 20° | 13221.6 | 14962.3 | 14512.6 | 12729.9 | 12025.6 | 12729.9 | 14512.6 | 14962.3 | 13221.6 | 11842.8 | 11255.3 |
| 22.5° | 12368.3 | 14326.4 | 13219.0 | 10982.5 | 10021.7 | 10982.5 | 13219.0 | 14326.4 | 12368.3 | 10890.0 | 10278.5 |
| 25° | 11370.3 | 13547.2 | 11827.5 | 9078.7 | 8095.7 | 9078.7 | 11827.5 | 13547.2 | 11370.3 | 9754.7 | 9201.8 |
| 27.5° | 10196.4 | 12559.5 | 10345.8 | 7418.7 | 6511.8 | 7418.7 | 10345.8 | 12559.5 | 10196.4 | 8582.6 | 8017.9 |
| 30° | 8892.5 | 11293.3 | 8803.7 | 5908.1 | 5072.9 | 5908.1 | 8803.7 | 11293.3 | 8892.5 | 7265.7 | 6760.0 |
| 32.5° | 7432.6 | 10052.3 | 7322.7 | 4733.9 | 4026.5 | 4733.9 | 7322.7 | 10052.3 | 7432.6 | 6009.0 | 5480.6 |
| 35° | 6085.7 | 8499.5 | 5987.4 | 3719.8 | 3134.8 | 3719.8 | 5987.4 | 8499.5 | 6085.7 | 4822.7 | 4303.8 |
| 37.5° | 4776.0 | 7032.4 | 4772.9 | 2995.3 | 2542.7 | 2995.3 | 4772.9 | 7032.4 | 4776.0 | 3749.5 | 3328.2 |
| 40° | 3715.7 | 5498.8 | 3739.6 | 2391.0 | 2040.5 | 2391.0 | 3739.6 | 5498.8 | 3715.7 | 2852.8 | 2583.3 |
| 42.5° | 2815.4 | 4204.6 | 2939.4 | 1962.4 | 1733.2 | 1962.4 | 2939.4 | 4204.6 | 2815.4 | 2247.7 | 2046.0 |
| 45° | 2200.8 | 3094.1 | 2295.3 | 1655.6 | 1475.4 | 1655.6 | 2295.3 | 3094.1 | 2200.8 | 1810.2 | 1674.6 |
| 47.5° | 1792.3 | 2391.3 | 1860.3 | 1420.1 | 1293.8 | 1420.1 | 1860.3 | 2391.3 | 1792.3 | 1531.1 | 1429.6 |
| 50° | 1505.4 | 1834.9 | 1544.6 | 1239.6 | 1154.9 | 1239.6 | 1544.6 | 1834.9 | 1505.4 | 1311.1 | 1243.4 |
| 52.5° | 1293.2 | 1496.5 | 1315.4 | 1104.8 | 1047.6 | 1104.8 | 1315.4 | 1496.5 | 1293.2 | 1147.1 | 1105.0 |
| 55° | 1114.5 | 1258.1 | 1143.9 | 993.5 | 953.9 | 993.5 | 1143.9 | 1258.1 | 1114.5 | 1020.8 | 989.7 |
| 57.5° | 978.8 | 1067.2 | 993.5 | 898.6 | 872.4 | 898.6 | 993.5 | 1067.2 | 978.8 | 908.4 | 891.7 |
| 60° | 858.5 | 924.3 | 876.7 | 815.9 | 808.4 | 815.9 | 876.7 | 924.3 | 858.5 | 817.3 | 806.3 |
| 62.5° | 765.9 | 807.4 | 775.2 | 741.5 | 734.8 | 741.5 | 775.2 | 807.4 | 765.9 | 734.3 | 736.3 |
| 65° | 679.5 | 718.1 | 692.8 | 674.6 | 676.9 | 674.6 | 692.8 | 718.1 | 679.5 | 664.8 | 668.0 |
| 67.5° | 612.6 | 632.7 | 621.8 | 611.5 | 614.0 | 611.5 | 621.8 | 632.7 | 612.6 | 598.2 | 603.1 |
| 70° | 541.4 | 563.1 | 551.8 | 553.2 | 557.5 | 553.2 | 551.8 | 563.1 | 541.4 | 537.1 | 540.9 |
| 72.5° | 473.3 | 490.1 | 486.3 | 489.8 | 494.4 | 489.8 | 486.3 | 490.1 | 473.3 | 472.8 | 473.0 |
| 75° | 406.4 | 419.2 | 420.9 | 425.8 | 433.0 | 425.8 | 420.9 | 419.2 | 406.4 | 402.1 | 407.4 |
| 77.5° | 333.6 | 348.0 | 353.4 | 360.1 | 370.7 | 360.1 | 353.4 | 348.0 | 333.6 | 336.5 | 339.0 |
| 80° | 266.7 | 273.3 | 285.4 | 290.3 | 305.3 | 290.3 | 285.4 | 273.3 | 266.7 | 261.8 | 265.6 |
| 82.5° | 195.2 | 201.2 | 211.6 | 220.8 | 229.5 | 220.8 | 211.6 | 201.2 | 195.2 | 192.9 | 193.1 |
| 85° | 112.7 | 122.0 | 128.9 | 139.9 | 142.4 | 139.9 | 128.9 | 122.0 | 112.7 | 115.3 | 112.7 |
| 87.5° | 39.5 | 42.3 | 48.4 | 52.7 | 53.0 | 52.7 | 48.4 | 42.3 | 39.5 | 40.4 | 36.6 |
| 90° | 20.9 | 35.5 | 61.2 | 33.4 | 22.9 | 33.4 | 61.2 | 35.5 | 20.9 | 36.8 | 57.4 |
| 92.5° | 27.3 | 48.1 | 86.6 | 44.5 | 30.9 | 44.5 | 86.6 | 48.1 | 27.3 | 47.9 | 92.4 |
| 95° | 40.3 | 59.3 | 110.3 | 49.3 | 37.3 | 49.3 | 110.3 | 59.3 | 40.3 | 63.8 | 128.8 |
| 97.5° | 62.5 | 73.5 | 124.7 | 52.5 | 45.1 | 52.5 | 124.7 | 73.5 | 62.5 | 78.0 | 147.9 |
| 100° | 83.1 | 83.1 | 227.8 | 60.4 | 51.5 | 60.4 | 227.8 | 83.1 | 83.1 | 95.8 | 230.4 |
| 102.5° | 126.0 | 162.7 | 528.0 | 121.1 | 62.7 | 121.1 | 528.0 | 162.7 | 126.0 | 179.9 | 489.1 |
| 105° | 229.1 | 372.2 | 929.6 | 313.1 | 115.3 | 313.1 | 929.6 | 372.2 | 229.1 | 376.7 | 871.6 |
| 107.5° | 433.8 | 694.4 | 1197.8 | 617.9 | 269.2 | 617.9 | 1197.8 | 694.4 | 433.8 | 667.1 | 1149.6 |
| 110° | 694.1 | 970.5 | 1307.3 | 846.4 | 545.4 | 846.4 | 1307.3 | 970.5 | 694.1 | 916.3 | 1205.2 |



TEST NUMBER: P1432303
 CATALOG NUMBER: EHBR1-18-UNV-TASM-L830-UPL30

CANDELA DISTRIBUTION (continued):

| | 0° | 22.5° | 45° | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° | 202.5° | 225° |
|--------|-------|--------|--------|-------|-------|--------|--------|--------|-------|--------|--------|
| 112.5° | 903.6 | 1081.6 | 1277.1 | 938.4 | 754.9 | 938.4 | 1277.1 | 1081.6 | 903.6 | 1011.6 | 1154.4 |
| 115° | 981.7 | 1065.8 | 1140.6 | 935.3 | 837.4 | 935.3 | 1140.6 | 1065.8 | 981.7 | 987.8 | 1030.6 |
| 117.5° | 948.3 | 975.3 | 985.1 | 878.2 | 842.2 | 878.2 | 985.1 | 975.3 | 948.3 | 888.0 | 875.1 |
| 120° | 856.2 | 845.2 | 829.8 | 794.0 | 794.6 | 794.0 | 829.8 | 845.2 | 856.2 | 775.3 | 730.6 |
| 122.5° | 740.7 | 716.9 | 701.3 | 708.6 | 729.5 | 708.6 | 701.3 | 716.9 | 740.7 | 659.7 | 626.2 |
| 125° | 628.1 | 604.2 | 611.1 | 635.6 | 656.8 | 635.6 | 611.1 | 604.2 | 628.1 | 560.1 | 551.8 |
| 127.5° | 533.1 | 521.9 | 546.0 | 573.7 | 591.7 | 573.7 | 546.0 | 521.9 | 533.1 | 490.2 | 499.5 |
| 130° | 465.1 | 468.0 | 500.0 | 523.2 | 534.6 | 523.2 | 500.0 | 468.0 | 465.1 | 444.5 | 466.4 |
| 132.5° | 422.6 | 434.9 | 465.5 | 485.4 | 492.0 | 485.4 | 465.5 | 434.9 | 422.6 | 416.6 | 443.3 |
| 135° | 395.9 | 414.3 | 441.9 | 455.0 | 457.1 | 455.0 | 441.9 | 414.3 | 395.9 | 397.8 | 422.6 |
| 137.5° | 380.3 | 398.9 | 419.7 | 429.9 | 427.0 | 429.9 | 419.7 | 398.9 | 380.3 | 385.4 | 404.2 |
| 140° | 371.1 | 389.6 | 399.1 | 410.7 | 408.2 | 410.7 | 399.1 | 389.6 | 371.1 | 374.3 | 388.5 |
| 142.5° | 361.9 | 378.8 | 383.5 | 392.0 | 389.1 | 392.0 | 383.5 | 378.8 | 361.9 | 365.0 | 374.6 |
| 145° | 357.4 | 369.8 | 366.3 | 377.8 | 373.6 | 377.8 | 366.3 | 369.8 | 357.4 | 358.7 | 363.7 |
| 147.5° | 349.5 | 358.7 | 353.9 | 363.7 | 359.5 | 363.7 | 353.9 | 358.7 | 349.5 | 349.5 | 351.4 |
| 150° | 340.2 | 346.6 | 339.9 | 351.4 | 350.3 | 351.4 | 339.9 | 346.6 | 340.2 | 338.6 | 340.5 |
| 152.5° | 327.8 | 334.1 | 327.8 | 340.8 | 339.5 | 340.8 | 327.8 | 334.1 | 327.8 | 326.2 | 328.0 |
| 155° | 317.3 | 320.4 | 317.3 | 330.2 | 330.5 | 330.2 | 317.3 | 320.4 | 317.3 | 317.0 | 317.5 |
| 157.5° | 309.9 | 311.7 | 310.1 | 321.7 | 321.9 | 321.7 | 310.1 | 311.7 | 309.9 | 309.9 | 310.1 |
| 160° | 303.1 | 306.3 | 305.0 | 314.8 | 315.1 | 314.8 | 305.0 | 306.3 | 303.1 | 304.4 | 304.7 |
| 162.5° | 300.5 | 300.5 | 299.6 | 309.3 | 309.9 | 309.3 | 299.6 | 300.5 | 300.5 | 300.5 | 302.1 |
| 165° | 296.7 | 298.2 | 295.6 | 302.5 | 304.7 | 302.5 | 295.6 | 298.2 | 296.7 | 298.0 | 298.0 |
| 167.5° | 295.6 | 294.0 | 294.6 | 300.3 | 302.5 | 300.3 | 294.6 | 294.0 | 295.6 | 296.9 | 296.9 |
| 170° | 292.7 | 293.0 | 292.1 | 297.7 | 299.8 | 297.7 | 292.1 | 293.0 | 292.7 | 294.3 | 295.6 |
| 172.5° | 293.7 | 293.7 | 291.3 | 295.3 | 299.1 | 295.3 | 291.3 | 293.7 | 293.7 | 294.9 | 296.5 |
| 175° | 294.2 | 292.9 | 291.9 | 294.3 | 298.1 | 294.3 | 291.9 | 292.9 | 294.2 | 293.9 | 293.9 |
| 177.5° | 292.6 | 293.2 | 293.8 | 296.2 | 301.5 | 296.2 | 293.8 | 293.2 | 292.6 | 293.9 | 293.9 |
| 180° | 293.2 | 293.2 | 293.2 | 293.2 | 293.2 | 293.2 | 293.2 | 293.2 | 293.2 | 293.2 | 293.2 |



TEST NUMBER: P1432303

CATALOG NUMBER: EHBR1-18-UNV-TASM-L830-UPL30

CANDELA DISTRIBUTION (continued):

| | 247.5° | 270° | 292.5° | 315° | 337.5° | 360° |
|--------|---------|---------|---------|---------|---------|---------|
| 0° | 15374.0 | 15374.0 | 15374.0 | 15374.0 | 15374.0 | 15374.0 |
| 2.5° | 14927.5 | 14917.7 | 14927.5 | 15031.8 | 15167.6 | 15365.0 |
| 5° | 14580.6 | 14526.5 | 14580.6 | 14696.2 | 14945.7 | 15321.6 |
| 7.5° | 14176.7 | 14145.3 | 14176.7 | 14370.2 | 14685.3 | 15217.5 |
| 10° | 13751.5 | 13680.4 | 13751.5 | 13970.1 | 14341.7 | 15058.6 |
| 12.5° | 13227.5 | 13133.1 | 13227.5 | 13453.2 | 13921.9 | 14805.2 |
| 15° | 12560.9 | 12478.2 | 12560.9 | 12811.5 | 13355.1 | 14430.5 |
| 17.5° | 11845.7 | 11770.7 | 11845.7 | 12063.3 | 12662.1 | 13902.4 |
| 20° | 10947.4 | 10888.6 | 10947.4 | 11255.3 | 11842.8 | 13221.6 |
| 22.5° | 10005.0 | 9949.9 | 10005.0 | 10278.5 | 10890.0 | 12368.3 |
| 25° | 8896.2 | 8866.2 | 8896.2 | 9201.8 | 9754.7 | 11370.3 |
| 27.5° | 7698.1 | 7647.1 | 7698.1 | 8017.9 | 8582.6 | 10196.4 |
| 30° | 6474.1 | 6389.6 | 6474.1 | 6760.0 | 7265.7 | 8892.5 |
| 32.5° | 5276.8 | 5216.0 | 5276.8 | 5480.6 | 6009.0 | 7432.6 |
| 35° | 4119.6 | 4058.8 | 4119.6 | 4303.8 | 4822.7 | 6085.7 |
| 37.5° | 3210.1 | 3102.6 | 3210.1 | 3328.2 | 3749.5 | 4776.0 |
| 40° | 2434.6 | 2417.3 | 2434.6 | 2583.3 | 2852.8 | 3715.7 |
| 42.5° | 1982.0 | 1935.0 | 1982.0 | 2046.0 | 2247.7 | 2815.4 |
| 45° | 1626.2 | 1607.8 | 1626.2 | 1674.6 | 1810.2 | 2200.8 |
| 47.5° | 1398.5 | 1406.6 | 1398.5 | 1429.6 | 1531.1 | 1792.3 |
| 50° | 1228.7 | 1233.6 | 1228.7 | 1243.4 | 1311.1 | 1505.4 |
| 52.5° | 1103.5 | 1099.2 | 1103.5 | 1105.0 | 1147.1 | 1293.2 |
| 55° | 992.8 | 987.4 | 992.8 | 989.7 | 1020.8 | 1114.5 |
| 57.5° | 896.0 | 900.0 | 896.0 | 891.7 | 908.4 | 978.8 |
| 60° | 809.5 | 813.3 | 809.5 | 806.3 | 817.3 | 858.5 |
| 62.5° | 736.5 | 738.9 | 736.5 | 736.3 | 734.3 | 765.9 |
| 65° | 671.4 | 674.1 | 671.4 | 668.0 | 664.8 | 679.5 |
| 67.5° | 609.1 | 609.1 | 609.1 | 603.1 | 598.2 | 612.6 |
| 70° | 550.6 | 550.3 | 550.6 | 540.9 | 537.1 | 541.4 |
| 72.5° | 480.3 | 487.2 | 480.3 | 473.0 | 472.8 | 473.3 |
| 75° | 412.0 | 420.0 | 412.0 | 407.4 | 402.1 | 406.4 |
| 77.5° | 342.7 | 355.2 | 342.7 | 339.0 | 336.5 | 333.6 |
| 80° | 271.8 | 285.4 | 271.8 | 265.6 | 261.8 | 266.7 |
| 82.5° | 200.9 | 211.0 | 200.9 | 193.1 | 192.9 | 195.2 |
| 85° | 119.6 | 135.8 | 119.6 | 112.7 | 115.3 | 112.7 |
| 87.5° | 38.3 | 49.0 | 38.3 | 36.6 | 40.4 | 39.5 |
| 90° | 33.6 | 20.9 | 33.6 | 57.4 | 36.8 | 20.9 |
| 92.5° | 51.1 | 30.4 | 51.1 | 92.4 | 47.9 | 27.3 |
| 95° | 59.0 | 35.2 | 59.0 | 128.8 | 63.8 | 40.3 |
| 97.5° | 65.4 | 45.0 | 65.4 | 147.9 | 78.0 | 62.5 |
| 100° | 76.4 | 59.3 | 76.4 | 230.4 | 95.8 | 83.1 |
| 102.5° | 162.1 | 100.5 | 162.1 | 489.1 | 179.9 | 126.0 |
| 105° | 341.5 | 173.6 | 341.5 | 871.6 | 376.7 | 229.1 |
| 107.5° | 611.3 | 300.5 | 611.3 | 1149.6 | 667.1 | 433.8 |
| 110° | 811.3 | 560.8 | 811.3 | 1205.2 | 916.3 | 694.1 |



TEST NUMBER: P1432303

CATALOG NUMBER: EHBR1-18-UNV-TASM-L830-UPL30

CANDELA DISTRIBUTION (continued):

| | 247.5° | 270° | 292.5° | 315° | 337.5° | 360° |
|--------|--------|-------|--------|--------|--------|-------|
| 112.5° | 871.6 | 757.6 | 871.6 | 1154.4 | 1011.6 | 903.6 |
| 115° | 838.3 | 797.2 | 838.3 | 1030.6 | 987.8 | 981.7 |
| 117.5° | 765.3 | 770.3 | 765.3 | 875.1 | 888.0 | 948.3 |
| 120° | 681.2 | 713.1 | 681.2 | 730.6 | 775.3 | 856.2 |
| 122.5° | 603.6 | 641.7 | 603.6 | 626.2 | 659.7 | 740.7 |
| 125° | 537.0 | 575.3 | 537.0 | 551.8 | 560.1 | 628.1 |
| 127.5° | 490.9 | 516.7 | 490.9 | 499.5 | 490.2 | 533.1 |
| 130° | 454.8 | 477.0 | 454.8 | 466.4 | 444.5 | 465.1 |
| 132.5° | 429.7 | 443.9 | 429.7 | 443.3 | 416.6 | 422.6 |
| 135° | 407.7 | 420.1 | 407.7 | 422.6 | 397.8 | 395.9 |
| 137.5° | 388.9 | 399.8 | 388.9 | 404.2 | 385.4 | 380.3 |
| 140° | 372.2 | 381.3 | 372.2 | 388.5 | 374.3 | 371.1 |
| 142.5° | 354.9 | 361.3 | 354.9 | 374.6 | 365.0 | 361.9 |
| 145° | 342.8 | 347.6 | 342.8 | 363.7 | 358.7 | 357.4 |
| 147.5° | 332.3 | 335.4 | 332.3 | 351.4 | 349.5 | 349.5 |
| 150° | 321.8 | 324.9 | 321.8 | 340.5 | 338.6 | 340.2 |
| 152.5° | 310.9 | 314.4 | 310.9 | 328.0 | 326.2 | 327.8 |
| 155° | 303.5 | 307.0 | 303.5 | 317.5 | 317.0 | 317.3 |
| 157.5° | 299.4 | 301.5 | 299.4 | 310.1 | 309.9 | 309.9 |
| 160° | 295.5 | 297.4 | 295.5 | 304.7 | 304.4 | 303.1 |
| 162.5° | 291.3 | 293.2 | 291.3 | 302.1 | 300.5 | 300.5 |
| 165° | 290.3 | 290.6 | 290.3 | 298.0 | 298.0 | 296.7 |
| 167.5° | 289.0 | 290.6 | 289.0 | 296.9 | 296.9 | 295.6 |
| 170° | 289.3 | 289.5 | 289.3 | 295.6 | 294.3 | 292.7 |
| 172.5° | 289.8 | 290.1 | 289.8 | 296.5 | 294.9 | 293.7 |
| 175° | 288.9 | 289.2 | 288.9 | 293.9 | 293.9 | 294.2 |
| 177.5° | 290.8 | 291.0 | 290.8 | 293.9 | 293.9 | 292.6 |
| 180° | 293.2 | 293.2 | 293.2 | 293.2 | 293.2 | 293.2 |



TEST NUMBER: P1432303
 CATALOG NUMBER: EHBR1-18-UNV-TASM-L830-UPL30

CIE UGR TABLE:

| Reflectances: | | | | | | | | | | | |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|-------|-------|-------|-------|
| Ceiling | | 0.7 | 0.7 | 0.5 | 0.5 | 0.3 | 0.7 | 0.7 | 0.5 | 0.5 | 0.3 |
| Wall | | 0.5 | 0.3 | 0.5 | 0.3 | 0.3 | 0.5 | 0.3 | 0.5 | 0.3 | 0.3 |
| Reference plane | | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 |
| Room dimensions | | Viewed crosswise | | | | | Viewed endwise | | | | |
| X=2H | Y=2H | 14.90 | 15.91 | 15.50 | 16.50 | 17.16 | 14.22 | 15.23 | 14.82 | 15.82 | 16.47 |
| | 3H | 16.45 | 17.34 | 17.06 | 17.94 | 18.64 | 16.06 | 16.96 | 16.68 | 17.56 | 18.26 |
| | 4H | 17.08 | 17.92 | 17.71 | 18.53 | 19.24 | 16.84 | 17.68 | 17.48 | 18.30 | 19.01 |
| | 6H | 17.56 | 18.33 | 18.20 | 18.95 | 19.68 | 17.48 | 18.25 | 18.13 | 18.88 | 19.60 |
| | 8H | 17.71 | 18.44 | 18.36 | 19.08 | 19.81 | 17.70 | 18.43 | 18.36 | 19.08 | 19.81 |
| | 12H | 17.78 | 18.47 | 18.44 | 19.11 | 19.86 | 17.83 | 18.52 | 18.49 | 19.16 | 19.91 |
| 4H | 2H | 15.31 | 16.15 | 15.95 | 16.76 | 17.48 | 14.79 | 15.63 | 15.43 | 16.24 | 16.95 |
| | 3H | 17.10 | 17.80 | 17.75 | 18.45 | 19.18 | 16.84 | 17.54 | 17.49 | 18.19 | 18.92 |
| | 4H | 17.88 | 18.50 | 18.54 | 19.16 | 19.92 | 17.75 | 18.37 | 18.41 | 19.03 | 19.80 |
| | 6H | 18.49 | 19.03 | 19.17 | 19.71 | 20.49 | 18.52 | 19.06 | 19.20 | 19.74 | 20.52 |
| | 8H | 18.68 | 19.19 | 19.37 | 19.87 | 20.65 | 18.79 | 19.29 | 19.47 | 19.97 | 20.75 |
| | 12H | 18.78 | 19.23 | 19.49 | 19.94 | 20.73 | 18.95 | 19.40 | 19.66 | 20.10 | 20.89 |
| 8H | 4H | 18.12 | 18.63 | 18.81 | 19.31 | 20.09 | 18.02 | 18.53 | 18.71 | 19.21 | 19.99 |
| | 6H | 18.86 | 19.27 | 19.58 | 20.00 | 20.79 | 18.93 | 19.34 | 19.64 | 20.06 | 20.85 |
| | 8H | 19.13 | 19.50 | 19.87 | 20.23 | 21.03 | 19.28 | 19.65 | 20.02 | 20.38 | 21.18 |
| | 12H | 19.30 | 19.62 | 20.03 | 20.34 | 21.21 | 19.53 | 19.84 | 20.26 | 20.56 | 21.43 |
| 12H | 4H | 18.13 | 18.57 | 18.83 | 19.28 | 20.07 | 18.03 | 18.48 | 18.74 | 19.18 | 19.97 |
| | 6H | 18.91 | 19.27 | 19.64 | 20.00 | 20.81 | 18.97 | 19.34 | 19.71 | 20.07 | 20.87 |
| | 8H | 19.22 | 19.54 | 19.95 | 20.25 | 21.12 | 19.37 | 19.69 | 20.10 | 20.41 | 21.28 |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-2

Test Date: 07/31/2025

Luminaire Tested: EHBR-60-L830-N

Data in this report applies to families of products including EHBR-60-L830-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L830-N**
 Description: Elevate Round Highbay at, 60000 lumens, 3000K 80CRI LEDs with N lens

Spectral Parameters

CCT (K): 2983
 CIE u': 0.2516
 CIE v': 0.5201
 Duv: -0.0012
 CIE x: 0.4364
 CIE y: 0.4010
 CIE z: 0.1626
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 583
 Purity: 51.34918
 Rf: 81.2
 Rg: 101.5

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 83.4 | | |
| R1: | 84.0 | R9: | 29.4 |
| R2: | 87.5 | R10: | 68.6 |
| R3: | 88.9 | R11: | 82.2 |
| R4: | 83.8 | R12: | 61.6 |
| R5: | 81.9 | R13: | 83.9 |
| R6: | 83.1 | R14: | 92.5 |
| R7: | 87.1 | R15: | 79.8 |
| R8: | 70.9 | | |



Test Conditions


Stabilization Time: 38M
 Operation Time: 1H 38M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-2


| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | 76INCH SPHERE IN0058 | 6/16/2025 | 12/16/2025 |
| Power Meter | XITRON INXT2011004 | 1/21/2025 | 1/21/2026 |
| AC Power Source | CHROMA 61603 IN0063 | 10/22/2024 | 10/22/2025 |
| DC Power Source | AGILENT E3634A IN0208 | 10/22/2024 | 10/22/2025 |
| Sphere Thermometer | ONSET IN0085 | 10/22/2024 | 10/22/2025 |
| Room Thermometer | ONSET IN0046 | 10/22/2024 | 10/22/2025 |

REPORT NUMBER: SP1-2506-472-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-2

Photopic Flux vs. Wavelength



Photopic Lumens: NR

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 43 | NR | 620 | 294 | NR | 750 | 6 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 59 | NR | 625 | 294 | NR | 755 | 5 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 81 | NR | 630 | 1000 | NR | 760 | 4 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 109 | NR | 635 | 637 | NR | 765 | 4 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 135 | NR | 640 | 175 | NR | 770 | 3 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 160 | NR | 645 | 171 | NR | 775 | 3 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 180 | NR | 650 | 146 | NR | 780 | 2 | NR | 910 | 0 | NR |
| 395 | 1 | NR | 525 | 195 | NR | 655 | 119 | NR | 785 | 2 | NR | 915 | 0 | NR |
| 400 | 2 | NR | 530 | 207 | NR | 660 | 99 | NR | 790 | 2 | NR | 920 | 0 | NR |
| 405 | 3 | NR | 535 | 218 | NR | 665 | 82 | NR | 795 | 2 | NR | 925 | 0 | NR |
| 410 | 5 | NR | 540 | 227 | NR | 670 | 76 | NR | 800 | 1 | NR | 930 | 0 | NR |
| 415 | 10 | NR | 545 | 237 | NR | 675 | 61 | NR | 805 | 1 | NR | 935 | 0 | NR |
| 420 | 20 | NR | 550 | 247 | NR | 680 | 52 | NR | 810 | 1 | NR | 940 | 0 | NR |
| 425 | 35 | NR | 555 | 259 | NR | 685 | 44 | NR | 815 | 1 | NR | 945 | 0 | NR |
| 430 | 58 | NR | 560 | 271 | NR | 690 | 38 | NR | 820 | 1 | NR | 950 | 0 | NR |
| 435 | 90 | NR | 565 | 283 | NR | 695 | 33 | NR | 825 | 1 | NR | 955 | 0 | NR |
| 440 | 135 | NR | 570 | 293 | NR | 700 | 27 | NR | 830 | 1 | NR | 960 | 0 | NR |
| 445 | 204 | NR | 575 | 303 | NR | 705 | 24 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 233 | NR | 580 | 310 | NR | 710 | 20 | NR | 840 | 0 | NR | 970 | 0 | NR |
| 455 | 153 | NR | 585 | 313 | NR | 715 | 17 | NR | 845 | 0 | NR | 975 | 0 | NR |
| 460 | 98 | NR | 590 | 314 | NR | 720 | 15 | NR | 850 | 0 | NR | 980 | 0 | NR |
| 465 | 76 | NR | 595 | 310 | NR | 725 | 13 | NR | 855 | 0 | NR | 985 | 0 | NR |
| 470 | 53 | NR | 600 | 307 | NR | 730 | 11 | NR | 860 | 0 | NR | 990 | 0 | NR |
| 475 | 39 | NR | 605 | 303 | NR | 735 | 9 | NR | 865 | 0 | NR | 995 | 0 | NR |
| 480 | 35 | NR | 610 | 331 | NR | 740 | 8 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 36 | NR | 615 | 353 | NR | 745 | 7 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2506-472-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.27

| λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) |
|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|
| 360 | 0 | NR | 490 | 43 | NR | 620 | 294 | NR | 750 | 6 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 59 | NR | 625 | 294 | NR | 755 | 5 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 81 | NR | 630 | 1000 | NR | 760 | 4 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 109 | NR | 635 | 637 | NR | 765 | 4 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 135 | NR | 640 | 175 | NR | 770 | 3 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 160 | NR | 645 | 171 | NR | 775 | 3 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 180 | NR | 650 | 146 | NR | 780 | 2 | NR | 910 | 0 | NR |
| 395 | 1 | NR | 525 | 195 | NR | 655 | 119 | NR | 785 | 2 | NR | 915 | 0 | NR |
| 400 | 2 | NR | 530 | 207 | NR | 660 | 99 | NR | 790 | 2 | NR | 920 | 0 | NR |
| 405 | 3 | NR | 535 | 218 | NR | 665 | 82 | NR | 795 | 2 | NR | 925 | 0 | NR |
| 410 | 5 | NR | 540 | 227 | NR | 670 | 76 | NR | 800 | 1 | NR | 930 | 0 | NR |
| 415 | 10 | NR | 545 | 237 | NR | 675 | 61 | NR | 805 | 1 | NR | 935 | 0 | NR |
| 420 | 20 | NR | 550 | 247 | NR | 680 | 52 | NR | 810 | 1 | NR | 940 | 0 | NR |
| 425 | 35 | NR | 555 | 259 | NR | 685 | 44 | NR | 815 | 1 | NR | 945 | 0 | NR |
| 430 | 58 | NR | 560 | 271 | NR | 690 | 38 | NR | 820 | 1 | NR | 950 | 0 | NR |
| 435 | 90 | NR | 565 | 283 | NR | 695 | 33 | NR | 825 | 1 | NR | 955 | 0 | NR |
| 440 | 135 | NR | 570 | 293 | NR | 700 | 27 | NR | 830 | 1 | NR | 960 | 0 | NR |
| 445 | 204 | NR | 575 | 303 | NR | 705 | 24 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 233 | NR | 580 | 310 | NR | 710 | 20 | NR | 840 | 0 | NR | 970 | 0 | NR |
| 455 | 153 | NR | 585 | 313 | NR | 715 | 17 | NR | 845 | 0 | NR | 975 | 0 | NR |
| 460 | 98 | NR | 590 | 314 | NR | 720 | 15 | NR | 850 | 0 | NR | 980 | 0 | NR |
| 465 | 76 | NR | 595 | 310 | NR | 725 | 13 | NR | 855 | 0 | NR | 985 | 0 | NR |
| 470 | 53 | NR | 600 | 307 | NR | 730 | 11 | NR | 860 | 0 | NR | 990 | 0 | NR |
| 475 | 39 | NR | 605 | 303 | NR | 735 | 9 | NR | 865 | 0 | NR | 995 | 0 | NR |
| 480 | 35 | NR | 610 | 331 | NR | 740 | 8 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 36 | NR | 615 | 353 | NR | 745 | 7 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2506-472-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.34

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 43 | NR | 620 | 294 | NR | 750 | 6 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 59 | NR | 625 | 294 | NR | 755 | 5 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 81 | NR | 630 | 1000 | NR | 760 | 4 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 109 | NR | 635 | 637 | NR | 765 | 4 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 135 | NR | 640 | 175 | NR | 770 | 3 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 160 | NR | 645 | 171 | NR | 775 | 3 | NR | 905 | 0 | NR |
| 390 | 1 | NR | 520 | 180 | NR | 650 | 146 | NR | 780 | 2 | NR | 910 | 0 | NR |
| 395 | 1 | NR | 525 | 195 | NR | 655 | 119 | NR | 785 | 2 | NR | 915 | 0 | NR |
| 400 | 2 | NR | 530 | 207 | NR | 660 | 99 | NR | 790 | 2 | NR | 920 | 0 | NR |
| 405 | 3 | NR | 535 | 218 | NR | 665 | 82 | NR | 795 | 2 | NR | 925 | 0 | NR |
| 410 | 5 | NR | 540 | 227 | NR | 670 | 76 | NR | 800 | 1 | NR | 930 | 0 | NR |
| 415 | 10 | NR | 545 | 237 | NR | 675 | 61 | NR | 805 | 1 | NR | 935 | 0 | NR |
| 420 | 20 | NR | 550 | 247 | NR | 680 | 52 | NR | 810 | 1 | NR | 940 | 0 | NR |
| 425 | 35 | NR | 555 | 259 | NR | 685 | 44 | NR | 815 | 1 | NR | 945 | 0 | NR |
| 430 | 58 | NR | 560 | 271 | NR | 690 | 38 | NR | 820 | 1 | NR | 950 | 0 | NR |
| 435 | 90 | NR | 565 | 283 | NR | 695 | 33 | NR | 825 | 1 | NR | 955 | 0 | NR |
| 440 | 135 | NR | 570 | 293 | NR | 700 | 27 | NR | 830 | 1 | NR | 960 | 0 | NR |
| 445 | 204 | NR | 575 | 303 | NR | 705 | 24 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 233 | NR | 580 | 310 | NR | 710 | 20 | NR | 840 | 0 | NR | 970 | 0 | NR |
| 455 | 153 | NR | 585 | 313 | NR | 715 | 17 | NR | 845 | 0 | NR | 975 | 0 | NR |
| 460 | 98 | NR | 590 | 314 | NR | 720 | 15 | NR | 850 | 0 | NR | 980 | 0 | NR |
| 465 | 76 | NR | 595 | 310 | NR | 725 | 13 | NR | 855 | 0 | NR | 985 | 0 | NR |
| 470 | 53 | NR | 600 | 307 | NR | 730 | 11 | NR | 860 | 0 | NR | 990 | 0 | NR |
| 475 | 39 | NR | 605 | 303 | NR | 735 | 9 | NR | 865 | 0 | NR | 995 | 0 | NR |
| 480 | 35 | NR | 610 | 331 | NR | 740 | 8 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 36 | NR | 615 | 353 | NR | 745 | 7 | NR | 875 | 0 | NR | | | |

Summary

$R_f = 81.2$
 $R_g = 101.5$
 CIE $R_a = 83.4$
 $R_9 = 29.4$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)



| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 71 | CES51 = 89 | CES76 = 65 |
| CES02 = 63 | CES27 = 89 | CES52 = 89 | CES77 = 82 |
| CES03 = 31 | CES28 = 86 | CES53 = 80 | CES78 = 67 |
| CES04 = 70 | CES29 = 68 | CES54 = 92 | CES79 = 89 |
| CES05 = 50 | CES30 = 77 | CES55 = 90 | CES80 = 85 |
| CES06 = 51 | CES31 = 70 | CES56 = 81 | CES81 = 75 |
| CES07 = 43 | CES32 = 64 | CES57 = 79 | CES82 = 93 |
| CES08 = 41 | CES33 = 74 | CES58 = 81 | CES83 = 89 |
| CES09 = 29 | CES34 = 76 | CES59 = 92 | CES84 = 91 |
| CES10 = 76 | CES35 = 87 | CES60 = 96 | CES85 = 81 |
| CES11 = 59 | CES36 = 99 | CES61 = 91 | CES86 = 74 |
| CES12 = 65 | CES37 = 81 | CES62 = 93 | CES87 = 83 |
| CES13 = 44 | CES38 = 83 | CES63 = 79 | CES88 = 86 |
| CES14 = 74 | CES39 = 94 | CES64 = 81 | CES89 = 74 |
| CES15 = 72 | CES40 = 89 | CES65 = 78 | CES90 = 85 |
| CES16 = 48 | CES41 = 88 | CES66 = 76 | CES91 = 87 |
| CES17 = 50 | CES42 = 80 | CES67 = 74 | CES92 = 73 |
| CES18 = 57 | CES43 = 75 | CES68 = 79 | CES93 = 84 |
| CES19 = 72 | CES44 = 99 | CES69 = 83 | CES94 = 64 |
| CES20 = 67 | CES45 = 83 | CES70 = 72 | CES95 = 80 |
| CES21 = 87 | CES46 = 82 | CES71 = 70 | CES96 = 86 |
| CES22 = 79 | CES47 = 79 | CES72 = 90 | CES97 = 85 |
| CES23 = 92 | CES48 = 78 | CES73 = 65 | CES98 = 83 |
| CES24 = 91 | CES49 = 79 | CES74 = 94 | CES99 = 82 |
| CES25 = 72 | CES50 = 88 | CES75 = 70 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)