

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1432265

Luminaire Tested: EHBR1-12-UNV-A1-L830-UPL40

Issue Date: 3/20/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1432265  
REPORT IS A COMBINATION OF REPORTS P1431642 AND P1431635  
Test Lab: INNOVATION CENTER  
Issue Date: 3/20/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: EHBR1-12-UNV-A1-L830-UPL40  
Description: Elevate Round Highbay at, 12000 lumens, 3000K 80CRI LEDs with A lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 15128.8 lumens  
Efficiency: N/A  
Efficacy: 158.7 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 1.07 / 0.95  
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')  
CIE Type: Semi-Direct

Input Watts (W): 95.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1432265  
CATALOG NUMBER: EHBR1-12-UNV-A1-L830-UPL40

### Luminous Intensity Polar Plot





TEST NUMBER: P1432265  
 CATALOG NUMBER: EHBR1-12-UNV-A1-L830-UPL40

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|---|--|--|--|--|
| RF  | 20  |     |     |     |     | 20  |     |     |    |    | 20 |    |    |    |    | 20 |    |    |    |    | 20 |    |    |    |    |    |   |  |  |  |  |
| RC  | 80  |     |     |     |     | 70  |     |     |    |    | 50 |    |    |    |    | 30 |    |    |    |    | 10 |    |    |    |    | 0  |   |  |  |  |  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |  |  |  |  |
| RCR |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |
| 0   | 113 | 113 | 113 | 113 | 108 | 108 | 108 | 108 | 98 | 98 | 98 | 89 | 89 | 89 | 80 | 80 | 80 | 76 |    |    |    |    |    |    |    |    |   |  |  |  |  |
| 1   | 106 | 102 | 99  | 96  | 101 | 97  | 95  | 92  | 89 | 87 | 85 | 81 | 80 | 78 | 74 | 73 | 72 | 68 |    |    |    |    |    |    |    |    |   |  |  |  |  |
| 2   | 98  | 92  | 87  | 82  | 94  | 88  | 83  | 80  | 81 | 77 | 74 | 74 | 71 | 69 | 68 | 66 | 64 | 61 |    |    |    |    |    |    |    |    |   |  |  |  |  |
| 3   | 91  | 83  | 77  | 72  | 87  | 80  | 74  | 70  | 74 | 69 | 66 | 68 | 65 | 62 | 63 | 60 | 58 | 55 |    |    |    |    |    |    |    |    |   |  |  |  |  |
| 4   | 85  | 76  | 69  | 64  | 81  | 73  | 67  | 62  | 68 | 63 | 59 | 63 | 59 | 55 | 58 | 55 | 52 | 50 |    |    |    |    |    |    |    |    |   |  |  |  |  |
| 5   | 80  | 69  | 62  | 57  | 76  | 67  | 60  | 56  | 62 | 57 | 53 | 58 | 54 | 50 | 54 | 50 | 48 | 45 |    |    |    |    |    |    |    |    |   |  |  |  |  |
| 6   | 74  | 64  | 57  | 51  | 71  | 62  | 55  | 50  | 58 | 52 | 48 | 54 | 49 | 46 | 50 | 47 | 44 | 41 |    |    |    |    |    |    |    |    |   |  |  |  |  |
| 7   | 70  | 59  | 52  | 47  | 67  | 57  | 50  | 46  | 53 | 48 | 44 | 50 | 45 | 42 | 47 | 43 | 40 | 38 |    |    |    |    |    |    |    |    |   |  |  |  |  |
| 8   | 66  | 55  | 47  | 43  | 63  | 53  | 46  | 42  | 50 | 44 | 40 | 47 | 42 | 39 | 44 | 40 | 37 | 35 |    |    |    |    |    |    |    |    |   |  |  |  |  |
| 9   | 62  | 51  | 44  | 39  | 59  | 49  | 43  | 39  | 46 | 41 | 37 | 44 | 39 | 36 | 41 | 37 | 34 | 33 |    |    |    |    |    |    |    |    |   |  |  |  |  |
| 10  | 58  | 47  | 41  | 36  | 56  | 46  | 40  | 36  | 44 | 38 | 34 | 41 | 37 | 33 | 39 | 35 | 32 | 30 |    |    |    |    |    |    |    |    |   |  |  |  |  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°    | 45°   | 90°   | 135°  | 180°  |
|-----|-------|-------|-------|-------|-------|
| 0°  | 43453 | 43453 | 43453 | 43453 | 43453 |
| 5°  | 43166 | 43160 | 43162 | 43238 | 43212 |
| 10° | 42099 | 42590 | 42658 | 42537 | 41824 |
| 15° | 38219 | 40886 | 41728 | 40558 | 37342 |
| 20° | 31849 | 37405 | 39961 | 36701 | 30609 |
| 25° | 24631 | 32343 | 37071 | 31162 | 23355 |
| 30° | 17954 | 26340 | 32564 | 25340 | 17041 |
| 35° | 12941 | 20301 | 26763 | 19427 | 12097 |
| 40° | 9311  | 14994 | 19723 | 14361 | 9023  |
| 45° | 7336  | 10970 | 13775 | 10494 | 7083  |
| 50° | 6087  | 8242  | 9970  | 7970  | 5995  |
| 55° | 5317  | 6508  | 7551  | 6399  | 5244  |
| 60° | 4795  | 5433  | 6016  | 5399  | 4829  |
| 65° | 4485  | 4792  | 5056  | 4808  | 4527  |
| 70° | 4259  | 4360  | 4495  | 4384  | 4300  |
| 75° | 3973  | 3948  | 3973  | 3959  | 4012  |
| 80° | 3587  | 3330  | 3256  | 3382  | 3587  |
| 85° | 2485  | 2109  | 2089  | 2141  | 2560  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 67.5°  
 Vertical Angle: 45°  
 Luminance: 14432 cd/sqm



TEST NUMBER: P1432265  
 CATALOG NUMBER: EHBR1-12-UNV-A1-L830-UPL40

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 873.8   | 5.8       |
| 10°-20°   | 2348.5  | 15.5      |
| 20°-30°   | 2855.8  | 18.9      |
| 30°-40°   | 2326.2  | 15.4      |
| 40°-50°   | 1396.7  | 9.2       |
| 50°-60°   | 803.8   | 5.3       |
| 60°-70°   | 503.0   | 3.3       |
| 70°-80°   | 296.3   | 2.0       |
| 80°-90°   | 93.1    | 0.6       |
| 90°-100°  | 95.7    | 0.6       |
| 100°-110° | 633.4   | 4.2       |
| 110°-120° | 1171.8  | 7.7       |
| 120°-130° | 695.2   | 4.6       |
| 130°-140° | 419.0   | 2.8       |
| 140°-150° | 288.8   | 1.9       |
| 150°-160° | 187.0   | 1.2       |
| 160°-170° | 105.9   | 0.7       |
| 170°-180° | 34.9    | 0.2       |
| 0°-30°    | 6078.1  | 40.2      |
| 0°-40°    | 8404.3  | 55.6      |
| 0°-60°    | 10604.8 | 70.1      |
| 0°-90°    | 11497.1 | 76.0      |
| 90°-120°  | 1900.9  | 12.6      |
| 90°-150°  | 3303.8  | 21.8      |
| 90°-180°  | 3632.0  | 24.0      |
| 0°-180°   | 15128.8 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | 45°  | 90°  | 135° | 180° | Flux |
|------|------|------|------|------|------|------|
| 0°   | 9253 | 9253 | 9253 | 9253 | 9253 |      |
| 5°   | 9217 | 9215 | 9216 | 9232 | 9226 | 871  |
| 15°  | 8018 | 8578 | 8754 | 8509 | 7834 | 2206 |
| 25°  | 4919 | 6459 | 7403 | 6223 | 4664 | 2241 |
| 35°  | 2375 | 3726 | 4912 | 3566 | 2220 | 1503 |
| 45°  | 1187 | 1775 | 2229 | 1698 | 1146 | 936  |
| 55°  | 718  | 880  | 1020 | 865  | 709  | 649  |
| 65°  | 468  | 500  | 528  | 502  | 472  | 465  |
| 75°  | 280  | 278  | 280  | 279  | 283  | 296  |
| 85°  | 85   | 72   | 72   | 74   | 88   | 91   |
| 90°  | 27   | 73   | 26   | 77   | 26   | 17   |
| 95°  | 45   | 164  | 50   | 139  | 45   | 43   |
| 105° | 220  | 1108 | 291  | 1181 | 144  | 295  |
| 115° | 1014 | 1310 | 1247 | 1449 | 1062 | 934  |
| 125° | 731  | 700  | 797  | 775  | 832  | 667  |
| 135° | 534  | 536  | 501  | 560  | 578  | 418  |
| 145° | 440  | 460  | 452  | 464  | 472  | 279  |
| 155° | 386  | 400  | 400  | 400  | 417  | 180  |
| 165° | 364  | 373  | 371  | 369  | 380  | 104  |
| 175° | 361  | 366  | 366  | 362  | 369  | 35   |
| 180° | 365  | 365  | 365  | 365  | 365  |      |



TEST NUMBER: P1432265  
 CATALOG NUMBER: EHBR1-12-UNV-A1-L830-UPL40

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 22.5°  | 45°    | 67.5°  | 90°    | 112.5° | 135°   | 157.5° | 180°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 9253.1 | 9253.1 | 9253.1 | 9253.1 | 9253.1 | 9253.1 | 9253.1 | 9253.1 | 9253.1 |
| 2.5°   | 9232.8 | 9241.1 | 9244.6 | 9246.5 | 9248.7 | 9254.5 | 9256.9 | 9252.9 | 9256.4 |
| 5°     | 9216.7 | 9217.2 | 9215.3 | 9224.1 | 9215.7 | 9221.5 | 9232.0 | 9227.9 | 9226.4 |
| 7.5°   | 9122.9 | 9142.3 | 9153.7 | 9156.6 | 9158.1 | 9165.3 | 9172.6 | 9131.0 | 9124.8 |
| 10°    | 8944.5 | 8977.0 | 9048.8 | 9069.4 | 9063.2 | 9074.8 | 9037.6 | 8928.7 | 8886.0 |
| 12.5°  | 8553.7 | 8667.5 | 8854.2 | 8937.4 | 8922.2 | 8932.6 | 8805.8 | 8575.9 | 8443.8 |
| 15°    | 8018.2 | 8185.1 | 8577.7 | 8741.6 | 8754.3 | 8741.6 | 8508.9 | 8061.0 | 7834.1 |
| 17.5°  | 7306.3 | 7614.5 | 8192.6 | 8510.8 | 8492.6 | 8498.7 | 8056.7 | 7394.8 | 7135.0 |
| 20°    | 6545.9 | 6874.4 | 7687.9 | 8218.8 | 8213.2 | 8179.4 | 7543.2 | 6670.1 | 6291.0 |
| 22.5°  | 5685.8 | 6109.4 | 7109.6 | 7859.6 | 7857.5 | 7801.3 | 6917.8 | 5878.8 | 5470.7 |
| 25°    | 4918.8 | 5334.2 | 6458.9 | 7419.8 | 7403.1 | 7339.1 | 6223.0 | 5089.4 | 4663.9 |
| 27.5°  | 4125.6 | 4557.7 | 5764.0 | 6904.2 | 6892.8 | 6823.0 | 5558.8 | 4351.7 | 3946.6 |
| 30°    | 3453.4 | 3848.4 | 5066.4 | 6336.9 | 6263.7 | 6255.7 | 4874.2 | 3668.5 | 3277.8 |
| 32.5°  | 2877.4 | 3216.0 | 4408.6 | 5743.7 | 5614.1 | 5651.1 | 4191.8 | 3097.1 | 2709.9 |
| 35°    | 2375.2 | 2673.5 | 3726.0 | 5057.7 | 4911.9 | 4959.8 | 3565.6 | 2541.3 | 2220.2 |
| 37.5°  | 1927.7 | 2214.6 | 3147.5 | 4390.4 | 4167.5 | 4257.8 | 3014.8 | 2122.3 | 1865.0 |
| 40°    | 1613.8 | 1841.3 | 2598.9 | 3658.2 | 3418.5 | 3565.6 | 2489.2 | 1770.2 | 1564.0 |
| 42.5°  | 1390.5 | 1539.0 | 2145.0 | 2959.2 | 2775.3 | 2879.5 | 2051.6 | 1479.9 | 1325.6 |
| 45°    | 1187.0 | 1305.5 | 1774.9 | 2335.1 | 2228.7 | 2325.5 | 1697.9 | 1261.8 | 1146.0 |
| 47.5°  | 1036.8 | 1128.1 | 1461.1 | 1885.7 | 1819.7 | 1850.2 | 1418.1 | 1101.2 | 1007.0 |
| 50°    | 907.2  | 977.7  | 1228.3 | 1522.0 | 1485.9 | 1504.7 | 1187.8 | 958.2  | 893.4  |
| 52.5°  | 806.4  | 858.1  | 1030.3 | 1250.8 | 1233.0 | 1235.9 | 1012.2 | 842.9  | 795.9  |
| 55°    | 718.5  | 754.5  | 879.5  | 1024.7 | 1020.4 | 1021.1 | 864.8  | 746.9  | 708.7  |
| 57.5°  | 641.5  | 671.3  | 755.8  | 860.6  | 854.5  | 855.9  | 748.9  | 663.4  | 638.7  |
| 60°    | 576.4  | 596.3  | 653.1  | 727.4  | 723.2  | 721.5  | 649.0  | 589.0  | 580.5  |
| 62.5°  | 518.7  | 531.4  | 570.7  | 623.5  | 615.7  | 617.5  | 570.5  | 532.0  | 519.4  |
| 65°    | 468.1  | 472.5  | 500.2  | 532.8  | 527.7  | 532.0  | 501.8  | 475.4  | 472.5  |
| 67.5°  | 418.6  | 423.1  | 439.3  | 461.2  | 455.4  | 458.9  | 439.7  | 424.2  | 421.7  |
| 70°    | 373.7  | 373.5  | 382.6  | 394.4  | 394.4  | 395.0  | 384.7  | 375.4  | 377.3  |
| 72.5°  | 327.1  | 326.0  | 328.7  | 336.7  | 334.5  | 341.9  | 331.0  | 328.1  | 328.5  |
| 75°    | 279.9  | 276.5  | 278.1  | 282.1  | 279.9  | 283.7  | 278.9  | 282.6  | 282.6  |
| 77.5°  | 235.3  | 229.1  | 227.2  | 227.7  | 223.5  | 229.3  | 230.4  | 233.0  | 238.8  |
| 80°    | 188.7  | 180.0  | 175.2  | 175.0  | 171.3  | 175.0  | 177.9  | 183.1  | 188.7  |
| 82.5°  | 140.1  | 132.5  | 124.4  | 122.9  | 120.6  | 122.7  | 126.5  | 132.7  | 141.8  |
| 85°    | 85.4   | 77.6   | 72.5   | 69.8   | 71.8   | 71.8   | 73.6   | 82.3   | 88.0   |
| 87.5°  | 30.8   | 27.0   | 22.1   | 22.3   | 22.9   | 23.6   | 24.6   | 31.0   | 33.9   |
| 90°    | 26.6   | 42.4   | 72.7   | 46.5   | 26.2   | 44.4   | 76.7   | 40.4   | 26.4   |
| 92.5°  | 38.5   | 64.6   | 117.1  | 60.5   | 34.3   | 60.5   | 109.0  | 54.5   | 36.5   |
| 95°    | 44.8   | 74.7   | 163.5  | 80.7   | 50.5   | 74.7   | 139.3  | 60.5   | 44.6   |
| 97.5°  | 56.9   | 82.7   | 187.7  | 98.9   | 78.7   | 92.8   | 157.5  | 64.6   | 54.7   |
| 100°   | 75.0   | 96.9   | 292.7  | 121.1  | 105.0  | 105.0  | 288.6  | 74.7   | 62.9   |
| 102.5° | 127.6  | 205.9  | 621.7  | 228.1  | 159.4  | 205.9  | 670.1  | 151.4  | 77.1   |
| 105°   | 220.4  | 434.0  | 1108.1 | 478.4  | 290.7  | 472.3  | 1180.8 | 395.6  | 143.7  |
| 107.5° | 381.9  | 777.1  | 1461.4 | 847.7  | 551.1  | 882.1  | 1521.9 | 783.2  | 339.5  |
| 110°   | 712.9  | 1031.4 | 1532.0 | 1164.6 | 882.1  | 1233.3 | 1661.2 | 1073.8 | 690.7  |



TEST NUMBER: P1432265  
 CATALOG NUMBER: EHBR1-12-UNV-A1-L830-UPL40

**CANDELA DISTRIBUTION (continued):**

|        | 0°     | 22.5°  | 45°    | 67.5°  | 90°    | 112.5° | 135°   | 157.5° | 180°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 963.2  | 1108.1 | 1467.4 | 1285.7 | 1148.5 | 1374.5 | 1622.8 | 1190.9 | 957.1  |
| 115°   | 1013.6 | 1065.8 | 1310.0 | 1255.5 | 1247.4 | 1354.4 | 1449.3 | 1186.8 | 1062.0 |
| 117.5° | 979.5  | 972.9  | 1112.2 | 1128.4 | 1205.0 | 1239.4 | 1251.4 | 1114.2 | 1068.1 |
| 120°   | 906.6  | 865.9  | 928.5  | 985.0  | 1088.0 | 1073.8 | 1053.6 | 1007.4 | 1007.6 |
| 122.5° | 816.1  | 767.2  | 795.3  | 837.7  | 940.6  | 910.3  | 890.2  | 898.4  | 925.0  |
| 125°   | 731.2  | 682.4  | 700.4  | 710.5  | 797.3  | 767.0  | 775.3  | 805.6  | 832.2  |
| 127.5° | 656.5  | 623.8  | 633.8  | 621.7  | 676.2  | 662.1  | 692.5  | 727.0  | 749.4  |
| 130°   | 606.1  | 577.7  | 591.6  | 563.1  | 589.6  | 593.6  | 634.2  | 662.4  | 676.8  |
| 132.5° | 563.9  | 545.5  | 561.7  | 527.2  | 535.2  | 551.6  | 589.9  | 614.4  | 622.4  |
| 135°   | 533.8  | 517.4  | 535.6  | 503.2  | 501.3  | 525.6  | 559.9  | 576.0  | 578.2  |
| 137.5° | 507.6  | 493.5  | 511.6  | 487.4  | 481.4  | 505.5  | 531.8  | 543.9  | 540.0  |
| 140°   | 483.7  | 471.4  | 491.6  | 473.4  | 469.4  | 493.6  | 505.7  | 520.1  | 516.0  |
| 142.5° | 457.8  | 449.7  | 473.6  | 461.5  | 457.5  | 480.0  | 486.1  | 496.1  | 492.2  |
| 145°   | 439.8  | 433.7  | 459.7  | 453.7  | 451.7  | 468.1  | 464.0  | 478.3  | 472.3  |
| 147.5° | 424.2  | 420.0  | 443.8  | 441.8  | 441.8  | 453.9  | 448.0  | 460.3  | 454.5  |
| 150°   | 410.3  | 406.1  | 429.9  | 427.9  | 429.9  | 437.9  | 430.0  | 444.6  | 442.8  |
| 152.5° | 396.3  | 392.1  | 413.9  | 411.7  | 413.7  | 421.8  | 414.1  | 430.4  | 428.8  |
| 155°   | 386.4  | 382.2  | 400.0  | 399.6  | 399.6  | 403.8  | 400.2  | 416.6  | 416.8  |
| 157.5° | 378.9  | 376.5  | 390.2  | 389.9  | 389.9  | 392.1  | 390.4  | 404.9  | 405.1  |
| 160°   | 373.2  | 370.8  | 382.6  | 382.2  | 380.2  | 384.4  | 382.7  | 395.2  | 395.4  |
| 162.5° | 367.7  | 365.1  | 378.7  | 376.5  | 376.3  | 376.5  | 374.9  | 387.5  | 387.8  |
| 165°   | 363.8  | 363.3  | 373.0  | 372.6  | 370.7  | 372.6  | 369.2  | 377.7  | 379.9  |
| 167.5° | 364.0  | 361.8  | 371.2  | 370.8  | 368.8  | 366.8  | 367.4  | 373.8  | 376.1  |
| 170°   | 362.1  | 361.9  | 369.3  | 367.0  | 364.8  | 364.9  | 363.6  | 370.0  | 372.2  |
| 172.5° | 362.5  | 362.3  | 369.8  | 367.4  | 365.1  | 365.3  | 361.9  | 366.3  | 370.6  |
| 175°   | 361.1  | 360.7  | 366.3  | 365.8  | 365.6  | 363.8  | 362.3  | 364.8  | 369.2  |
| 177.5° | 363.3  | 362.9  | 366.5  | 366.0  | 363.8  | 364.0  | 364.6  | 366.9  | 373.4  |
| 180°   | 364.6  | 364.6  | 364.6  | 364.6  | 364.6  | 364.6  | 364.6  | 364.6  | 364.6  |



TEST NUMBER: P1432265  
 CATALOG NUMBER: EHBR1-12-UNV-A1-L830-UPL40

**CIE UGR TABLE:**

| Reflectances:   |      |                  |       |       |       |       |                |       |       |       |       |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|-------|-------|-------|-------|
| Ceiling         |      | 0.7              | 0.7   | 0.5   | 0.5   | 0.3   | 0.7            | 0.7   | 0.5   | 0.5   | 0.3   |
| Wall            |      | 0.5              | 0.3   | 0.5   | 0.3   | 0.3   | 0.5            | 0.3   | 0.5   | 0.3   | 0.3   |
| Reference plane |      | 0.2              | 0.2   | 0.2   | 0.2   | 0.2   | 0.2            | 0.2   | 0.2   | 0.2   | 0.2   |
| Room dimensions |      | Viewed crosswise |       |       |       |       | Viewed endwise |       |       |       |       |
| X=2H            | Y=2H | 13.13            | 14.07 | 13.85 | 14.79 | 15.65 | 14.11          | 15.05 | 14.83 | 15.77 | 16.63 |
|                 | 3H   | 14.59            | 15.43 | 15.33 | 16.17 | 17.05 | 15.36          | 16.20 | 16.09 | 16.93 | 17.82 |
|                 | 4H   | 15.18            | 15.97 | 15.94 | 16.72 | 17.62 | 15.85          | 16.64 | 16.60 | 17.38 | 18.28 |
|                 | 6H   | 15.64            | 16.37 | 16.41 | 17.12 | 18.03 | 16.20          | 16.92 | 16.96 | 17.67 | 18.59 |
|                 | 8H   | 15.78            | 16.47 | 16.56 | 17.24 | 18.16 | 16.29          | 16.97 | 17.06 | 17.74 | 18.66 |
|                 | 12H  | 15.85            | 16.51 | 16.64 | 17.27 | 18.21 | 16.32          | 16.98 | 17.10 | 17.74 | 18.68 |
| 4H              | 2H   | 13.62            | 14.41 | 14.38 | 15.16 | 16.06 | 14.40          | 15.19 | 15.16 | 15.94 | 16.84 |
|                 | 3H   | 15.29            | 15.95 | 16.06 | 16.73 | 17.64 | 15.88          | 16.53 | 16.65 | 17.31 | 18.23 |
|                 | 4H   | 16.01            | 16.60 | 16.79 | 17.38 | 18.32 | 16.50          | 17.09 | 17.28 | 17.87 | 18.81 |
|                 | 6H   | 16.58            | 17.08 | 17.38 | 17.89 | 18.84 | 16.97          | 17.47 | 17.77 | 18.28 | 19.23 |
|                 | 8H   | 16.76            | 17.24 | 17.57 | 18.04 | 19.00 | 17.10          | 17.57 | 17.90 | 18.37 | 19.34 |
|                 | 12H  | 16.86            | 17.28 | 17.68 | 18.10 | 19.07 | 17.16          | 17.58 | 17.98 | 18.40 | 19.37 |
| 8H              | 4H   | 16.22            | 16.69 | 17.02 | 17.49 | 18.46 | 16.67          | 17.14 | 17.47 | 17.94 | 18.90 |
|                 | 6H   | 16.91            | 17.29 | 17.74 | 18.14 | 19.10 | 17.25          | 17.63 | 18.08 | 18.48 | 19.44 |
|                 | 8H   | 17.16            | 17.50 | 18.00 | 18.35 | 19.33 | 17.44          | 17.79 | 18.29 | 18.63 | 19.61 |
|                 | 12H  | 17.32            | 17.62 | 18.16 | 18.45 | 19.49 | 17.55          | 17.86 | 18.40 | 18.69 | 19.73 |
| 12H             | 4H   | 16.21            | 16.63 | 17.03 | 17.46 | 18.42 | 16.66          | 17.08 | 17.48 | 17.90 | 18.87 |
|                 | 6H   | 16.93            | 17.28 | 17.78 | 18.12 | 19.10 | 17.27          | 17.61 | 18.11 | 18.46 | 19.44 |
|                 | 8H   | 17.22            | 17.52 | 18.06 | 18.35 | 19.39 | 17.50          | 17.80 | 18.34 | 18.63 | 19.67 |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-2

Test Date: 07/31/2025

Luminaire Tested: EHBR-60-L830-N

Data in this report applies to families of products including EHBR-60-L830-N

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2506-472-2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 08/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **EHBR-60-L830-N**  
 Description: Elevate Round Highbay at, 60000 lumens, 3000K 80CRI LEDs with N lens

**Spectral Parameters**

CCT (K): 2983  
 CIE u': 0.2516  
 CIE v': 0.5201  
 Duv: -0.0012  
 CIE x: 0.4364  
 CIE y: 0.4010  
 CIE z: 0.1626  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 583  
 Purity: 51.34918  
 Rf: 81.2  
 Rg: 101.5

|           |      |      |      |
|-----------|------|------|------|
| CRI (Ra): | 83.4 |      |      |
| R1:       | 84.0 | R9:  | 29.4 |
| R2:       | 87.5 | R10: | 68.6 |
| R3:       | 88.9 | R11: | 82.2 |
| R4:       | 83.8 | R12: | 61.6 |
| R5:       | 81.9 | R13: | 83.9 |
| R6:       | 83.1 | R14: | 92.5 |
| R7:       | 87.1 | R15: | 79.8 |
| R8:       | 70.9 |      |      |



**Test Conditions**

Stabilization Time: 38M  
 Operation Time: 1H 38M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-2

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | 76INCH SPHERE IN0058  | 6/16/2025        | 12/16/2025           |
| Power Meter                    | XITRON INXT2011004    | 1/21/2025        | 1/21/2026            |
| AC Power Source                | CHROMA 61603 IN0063   | 10/22/2024       | 10/22/2025           |
| DC Power Source                | AGILENT E3634A IN0208 | 10/22/2024       | 10/22/2025           |
| Sphere Thermometer             | ONSET IN0085          | 10/22/2024       | 10/22/2025           |
| Room Thermometer               | ONSET IN0046          | 10/22/2024       | 10/22/2025           |

REPORT NUMBER: SP1-2506-472-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-2

**Photopic Flux vs. Wavelength**



**Photopic Lumens: NR**

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 43                       | NR            | 620    | 294                      | NR            | 750    | 6                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 59                       | NR            | 625    | 294                      | NR            | 755    | 5                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 81                       | NR            | 630    | 1000                     | NR            | 760    | 4                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 109                      | NR            | 635    | 637                      | NR            | 765    | 4                        | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 135                      | NR            | 640    | 175                      | NR            | 770    | 3                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 160                      | NR            | 645    | 171                      | NR            | 775    | 3                        | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 180                      | NR            | 650    | 146                      | NR            | 780    | 2                        | NR            | 910    | 0                        | NR            |
| 395    | 1                        | NR            | 525    | 195                      | NR            | 655    | 119                      | NR            | 785    | 2                        | NR            | 915    | 0                        | NR            |
| 400    | 2                        | NR            | 530    | 207                      | NR            | 660    | 99                       | NR            | 790    | 2                        | NR            | 920    | 0                        | NR            |
| 405    | 3                        | NR            | 535    | 218                      | NR            | 665    | 82                       | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 5                        | NR            | 540    | 227                      | NR            | 670    | 76                       | NR            | 800    | 1                        | NR            | 930    | 0                        | NR            |
| 415    | 10                       | NR            | 545    | 237                      | NR            | 675    | 61                       | NR            | 805    | 1                        | NR            | 935    | 0                        | NR            |
| 420    | 20                       | NR            | 550    | 247                      | NR            | 680    | 52                       | NR            | 810    | 1                        | NR            | 940    | 0                        | NR            |
| 425    | 35                       | NR            | 555    | 259                      | NR            | 685    | 44                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 58                       | NR            | 560    | 271                      | NR            | 690    | 38                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 90                       | NR            | 565    | 283                      | NR            | 695    | 33                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 135                      | NR            | 570    | 293                      | NR            | 700    | 27                       | NR            | 830    | 1                        | NR            | 960    | 0                        | NR            |
| 445    | 204                      | NR            | 575    | 303                      | NR            | 705    | 24                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 233                      | NR            | 580    | 310                      | NR            | 710    | 20                       | NR            | 840    | 0                        | NR            | 970    | 0                        | NR            |
| 455    | 153                      | NR            | 585    | 313                      | NR            | 715    | 17                       | NR            | 845    | 0                        | NR            | 975    | 0                        | NR            |
| 460    | 98                       | NR            | 590    | 314                      | NR            | 720    | 15                       | NR            | 850    | 0                        | NR            | 980    | 0                        | NR            |
| 465    | 76                       | NR            | 595    | 310                      | NR            | 725    | 13                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 53                       | NR            | 600    | 307                      | NR            | 730    | 11                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 39                       | NR            | 605    | 303                      | NR            | 735    | 9                        | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 35                       | NR            | 610    | 331                      | NR            | 740    | 8                        | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 36                       | NR            | 615    | 353                      | NR            | 745    | 7                        | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2506-472-2

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: NR**

**S/P: 1.27**

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 43                       | NR            | 620    | 294                      | NR            | 750    | 6                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 59                       | NR            | 625    | 294                      | NR            | 755    | 5                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 81                       | NR            | 630    | 1000                     | NR            | 760    | 4                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 109                      | NR            | 635    | 637                      | NR            | 765    | 4                        | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 135                      | NR            | 640    | 175                      | NR            | 770    | 3                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 160                      | NR            | 645    | 171                      | NR            | 775    | 3                        | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 180                      | NR            | 650    | 146                      | NR            | 780    | 2                        | NR            | 910    | 0                        | NR            |
| 395    | 1                        | NR            | 525    | 195                      | NR            | 655    | 119                      | NR            | 785    | 2                        | NR            | 915    | 0                        | NR            |
| 400    | 2                        | NR            | 530    | 207                      | NR            | 660    | 99                       | NR            | 790    | 2                        | NR            | 920    | 0                        | NR            |
| 405    | 3                        | NR            | 535    | 218                      | NR            | 665    | 82                       | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 5                        | NR            | 540    | 227                      | NR            | 670    | 76                       | NR            | 800    | 1                        | NR            | 930    | 0                        | NR            |
| 415    | 10                       | NR            | 545    | 237                      | NR            | 675    | 61                       | NR            | 805    | 1                        | NR            | 935    | 0                        | NR            |
| 420    | 20                       | NR            | 550    | 247                      | NR            | 680    | 52                       | NR            | 810    | 1                        | NR            | 940    | 0                        | NR            |
| 425    | 35                       | NR            | 555    | 259                      | NR            | 685    | 44                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 58                       | NR            | 560    | 271                      | NR            | 690    | 38                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 90                       | NR            | 565    | 283                      | NR            | 695    | 33                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 135                      | NR            | 570    | 293                      | NR            | 700    | 27                       | NR            | 830    | 1                        | NR            | 960    | 0                        | NR            |
| 445    | 204                      | NR            | 575    | 303                      | NR            | 705    | 24                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 233                      | NR            | 580    | 310                      | NR            | 710    | 20                       | NR            | 840    | 0                        | NR            | 970    | 0                        | NR            |
| 455    | 153                      | NR            | 585    | 313                      | NR            | 715    | 17                       | NR            | 845    | 0                        | NR            | 975    | 0                        | NR            |
| 460    | 98                       | NR            | 590    | 314                      | NR            | 720    | 15                       | NR            | 850    | 0                        | NR            | 980    | 0                        | NR            |
| 465    | 76                       | NR            | 595    | 310                      | NR            | 725    | 13                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 53                       | NR            | 600    | 307                      | NR            | 730    | 11                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 39                       | NR            | 605    | 303                      | NR            | 735    | 9                        | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 35                       | NR            | 610    | 331                      | NR            | 740    | 8                        | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 36                       | NR            | 615    | 353                      | NR            | 745    | 7                        | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2506-472-2

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: NR**

**M/P: 2.34**


| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 43                       | NR            | 620    | 294                      | NR            | 750    | 6                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 59                       | NR            | 625    | 294                      | NR            | 755    | 5                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 81                       | NR            | 630    | 1000                     | NR            | 760    | 4                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 109                      | NR            | 635    | 637                      | NR            | 765    | 4                        | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 135                      | NR            | 640    | 175                      | NR            | 770    | 3                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 160                      | NR            | 645    | 171                      | NR            | 775    | 3                        | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 180                      | NR            | 650    | 146                      | NR            | 780    | 2                        | NR            | 910    | 0                        | NR            |
| 395    | 1                        | NR            | 525    | 195                      | NR            | 655    | 119                      | NR            | 785    | 2                        | NR            | 915    | 0                        | NR            |
| 400    | 2                        | NR            | 530    | 207                      | NR            | 660    | 99                       | NR            | 790    | 2                        | NR            | 920    | 0                        | NR            |
| 405    | 3                        | NR            | 535    | 218                      | NR            | 665    | 82                       | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 5                        | NR            | 540    | 227                      | NR            | 670    | 76                       | NR            | 800    | 1                        | NR            | 930    | 0                        | NR            |
| 415    | 10                       | NR            | 545    | 237                      | NR            | 675    | 61                       | NR            | 805    | 1                        | NR            | 935    | 0                        | NR            |
| 420    | 20                       | NR            | 550    | 247                      | NR            | 680    | 52                       | NR            | 810    | 1                        | NR            | 940    | 0                        | NR            |
| 425    | 35                       | NR            | 555    | 259                      | NR            | 685    | 44                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 58                       | NR            | 560    | 271                      | NR            | 690    | 38                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 90                       | NR            | 565    | 283                      | NR            | 695    | 33                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 135                      | NR            | 570    | 293                      | NR            | 700    | 27                       | NR            | 830    | 1                        | NR            | 960    | 0                        | NR            |
| 445    | 204                      | NR            | 575    | 303                      | NR            | 705    | 24                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 233                      | NR            | 580    | 310                      | NR            | 710    | 20                       | NR            | 840    | 0                        | NR            | 970    | 0                        | NR            |
| 455    | 153                      | NR            | 585    | 313                      | NR            | 715    | 17                       | NR            | 845    | 0                        | NR            | 975    | 0                        | NR            |
| 460    | 98                       | NR            | 590    | 314                      | NR            | 720    | 15                       | NR            | 850    | 0                        | NR            | 980    | 0                        | NR            |
| 465    | 76                       | NR            | 595    | 310                      | NR            | 725    | 13                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 53                       | NR            | 600    | 307                      | NR            | 730    | 11                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 39                       | NR            | 605    | 303                      | NR            | 735    | 9                        | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 35                       | NR            | 610    | 331                      | NR            | 740    | 8                        | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 36                       | NR            | 615    | 353                      | NR            | 745    | 7                        | NR            | 875    | 0                        | NR            |        |                          |               |

**Summary**

$R_f = 81.2$   
 $R_g = 101.5$   
 CIE  $R_a = 83.4$   
 $R_9 = 29.4$



**Color Vector Graphics**



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 71 | CES51 = 89 | CES76 = 65 |
| CES02 = 63 | CES27 = 89 | CES52 = 89 | CES77 = 82 |
| CES03 = 31 | CES28 = 86 | CES53 = 80 | CES78 = 67 |
| CES04 = 70 | CES29 = 68 | CES54 = 92 | CES79 = 89 |
| CES05 = 50 | CES30 = 77 | CES55 = 90 | CES80 = 85 |
| CES06 = 51 | CES31 = 70 | CES56 = 81 | CES81 = 75 |
| CES07 = 43 | CES32 = 64 | CES57 = 79 | CES82 = 93 |
| CES08 = 41 | CES33 = 74 | CES58 = 81 | CES83 = 89 |
| CES09 = 29 | CES34 = 76 | CES59 = 92 | CES84 = 91 |
| CES10 = 76 | CES35 = 87 | CES60 = 96 | CES85 = 81 |
| CES11 = 59 | CES36 = 99 | CES61 = 91 | CES86 = 74 |
| CES12 = 65 | CES37 = 81 | CES62 = 93 | CES87 = 83 |
| CES13 = 44 | CES38 = 83 | CES63 = 79 | CES88 = 86 |
| CES14 = 74 | CES39 = 94 | CES64 = 81 | CES89 = 74 |
| CES15 = 72 | CES40 = 89 | CES65 = 78 | CES90 = 85 |
| CES16 = 48 | CES41 = 88 | CES66 = 76 | CES91 = 87 |
| CES17 = 50 | CES42 = 80 | CES67 = 74 | CES92 = 73 |
| CES18 = 57 | CES43 = 75 | CES68 = 79 | CES93 = 84 |
| CES19 = 72 | CES44 = 99 | CES69 = 83 | CES94 = 64 |
| CES20 = 67 | CES45 = 83 | CES70 = 72 | CES95 = 80 |
| CES21 = 87 | CES46 = 82 | CES71 = 70 | CES96 = 86 |
| CES22 = 79 | CES47 = 79 | CES72 = 90 | CES97 = 85 |
| CES23 = 92 | CES48 = 78 | CES73 = 65 | CES98 = 83 |
| CES24 = 91 | CES49 = 79 | CES74 = 94 | CES99 = 82 |
| CES25 = 72 | CES50 = 88 | CES75 = 70 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)