

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number:

Luminaire Tested: EHBR1-54-UNV-TASM-L840-UPL40

Issue Date: 3/20/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: REPORT IS A COMBINATION OF REPORTS P1431874 AND P1431635  
Test Lab: INNOVATION CENTER  
Issue Date: 3/20/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: EHBR1-54-UNV-TASM-L840-UPL40  
Description: Elevate Round Highbay at, 54000 lumens, 4000K 80CRI LEDs with TASM lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 57620.0 lumens  
Efficiency: N/A  
Efficacy: 176.4 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.84 / 0.9  
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')  
CIE Type: Direct  
  
Input Watts (W): 326.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER:  
CATALOG NUMBER: EHBR1-54-UNV-TASM-L840-UPL40

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - · - 135°-315°



TEST NUMBER:

CATALOG NUMBER: EHBR1-54-UNV-TASM-L840-UPL40

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	96	96	96	96	96	96	93
1	110	107	104	101	107	104	101	99	99	96	94	94	92	90	89	88	86	86	86	86	84
2	103	97	92	88	100	95	90	87	90	87	84	86	83	81	83	80	78	78	78	78	76
3	97	89	83	78	94	87	82	77	83	79	75	80	76	73	77	74	71	71	71	71	69
4	91	82	75	70	88	80	74	70	77	72	68	74	70	66	72	68	65	65	65	65	63
5	85	76	69	64	83	74	68	63	72	66	62	69	64	61	67	63	60	60	60	60	58
6	81	70	63	58	78	69	63	58	67	61	57	65	60	56	63	58	55	55	55	55	53
7	76	65	59	54	74	64	58	53	62	57	53	61	56	52	59	54	51	51	51	51	49
8	72	61	54	50	70	60	54	49	59	53	49	57	52	48	55	51	48	48	48	48	46
9	68	57	51	46	67	57	50	46	55	49	45	54	49	45	52	48	44	44	44	44	43
10	65	54	47	43	63	53	47	43	52	46	43	51	46	42	49	45	42	42	42	42	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	225705	225705	225705	225705
5°	224331	239320	224331	212690
10°	221574	245464	221574	201293
15°	215032	228112	215032	185940
20°	201109	182915	201109	165621
25°	177997	126734	177997	138797
30°	144527	82450	144527	103848
35°	103659	53396	103659	69134
40°	67019	36804	67019	43600
45°	42523	28509	42523	31065
50°	31579	24225	31579	25876
55°	25782	22068	25782	22842
60°	22326	21021	22326	21149
65°	20351	20274	20351	20187
70°	19289	19864	19289	19608
75°	18040	19217	18040	18640
80°	15846	18142	15846	16960
85°	10253	12953	10253	12351

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 59785 cd/sqm



TEST NUMBER:

CATALOG NUMBER: EHBR1-54-UNV-TASM-L840-UPL40

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	4570.0	7.9
10°-20°	12433.0	21.6
20°-30°	14581.3	25.3
30°-40°	10140.4	17.6
40°-50°	5039.3	8.7
50°-60°	3014.0	5.2
60°-70°	2121.4	3.7
70°-80°	1366.5	2.4
80°-90°	440.9	0.8
90°-100°	104.6	0.2
100°-110°	679.2	1.2
110°-120°	1254.0	2.2
120°-130°	745.9	1.3
130°-140°	451.9	0.8
140°-150°	313.5	0.5
150°-160°	205.5	0.4
160°-170°	118.9	0.2
170°-180°	39.7	0.1
0°-30°	31584.3	54.8
0°-40°	41724.6	72.4
0°-60°	49778.0	86.4
0°-90°	53706.8	93.2
90°-120°	2037.8	3.5
90°-150°	3549.1	6.2
90°-180°	3913.0	6.8
0°-180°	57620.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	48062	48062	48062	48062	48062	
5°	47898	51099	47898	45413	47898	4546
15°	45113	47857	45113	39009	45113	12607
25°	35546	25309	35546	27718	35546	16093
35°	19025	9800	19025	12689	19025	11877
45°	6880	4613	6880	5026	6880	5630
55°	3484	2982	3484	3087	3484	3186
65°	2124	2116	2124	2107	2124	2133
75°	1271	1354	1271	1313	1271	1334
85°	352	445	352	424	352	392
90°	29	35	29	29	29	30
95°	56	55	56	48	56	59
105°	312	161	312	237	312	421
115°	1334	1142	1334	1084	1334	1216
125°	855	897	855	783	855	787
135°	542	626	542	572	542	429
145°	491	514	491	478	491	308
155°	439	458	439	426	439	205
165°	416	430	416	409	416	119
175°	417	427	417	410	417	40
180°	417	417	417	417	417	



TEST NUMBER:  
 CATALOG NUMBER: EHBR1-54-UNV-TASM-L840-UPL40

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	48062.3	48062.3	48062.3	48062.3	48062.3	48062.3	48062.3	48062.3	48062.3	48062.3	48062.3
2.5°	48034.4	48655.3	49158.2	49489.9	49653.9	49489.9	49158.2	48655.3	48034.4	47417.0	46992.5
5°	47898.3	49142.0	50195.6	50885.0	51098.6	50885.0	50195.6	49142.0	47898.3	46723.1	45943.5
7.5°	47572.9	49510.6	51076.1	51880.9	52077.4	51880.9	51076.1	49510.6	47572.9	45909.3	44924.2
10°	47076.4	49743.1	51551.9	52128.7	52152.2	52128.7	51551.9	49743.1	47076.4	44835.0	43673.3
12.5°	46284.2	49660.2	51392.4	51203.2	50773.3	51203.2	51392.4	49660.2	46284.2	43522.8	42057.3
15°	45112.6	49169.0	50382.1	48841.9	47856.8	48841.9	50382.1	49169.0	45112.6	41750.9	40051.2
17.5°	43461.5	48249.8	48273.2	45226.1	43367.8	45226.1	48273.2	48249.8	43461.5	39584.3	37712.5
20°	41333.7	46775.3	45369.4	39796.1	37594.4	39796.1	45369.4	46775.3	41333.7	37023.0	35186.3
22.5°	38666.0	44787.2	41325.5	34333.7	31329.9	34333.7	41325.5	44787.2	38666.0	34044.4	32132.9
25°	35545.9	42351.2	36975.2	28381.9	25308.7	28381.9	36975.2	42351.2	35545.9	30495.3	28766.7
27.5°	31876.0	39263.5	32342.9	23192.6	20357.2	23192.6	32342.9	39263.5	31876.0	26830.9	25065.3
30°	27799.7	35305.2	27522.1	18470.0	15859.2	18470.0	27522.1	35305.2	27799.7	22714.0	21133.2
32.5°	23235.8	31425.4	22892.4	14799.3	12587.6	14799.3	22892.4	31425.4	23235.8	18785.5	17133.5
35°	19025.2	26571.3	18717.9	11628.7	9800.1	11628.7	18717.9	26571.3	19025.2	15076.9	13454.6
37.5°	14930.9	21984.9	14921.0	9363.9	7949.0	9363.9	14921.0	21984.9	14930.9	11721.6	10404.8
40°	11616.1	17190.3	11690.9	7474.9	6379.0	7474.9	11690.9	17190.3	11616.1	8918.7	8076.0
42.5°	8801.5	13144.6	9189.1	6134.8	5418.3	6134.8	9189.1	13144.6	8801.5	7027.0	6396.1
45°	6880.1	9673.0	7175.7	5175.8	4612.6	5175.8	7175.7	9673.0	6880.1	5658.9	5235.3
47.5°	5603.0	7475.8	5815.7	4439.5	4044.8	4439.5	5815.7	7475.8	5603.0	4786.5	4469.3
50°	4706.3	5736.4	4828.9	3875.3	3610.4	3875.3	4828.9	5736.4	4706.3	4098.8	3887.1
52.5°	4043.0	4678.3	4112.4	3453.6	3275.1	3453.6	4112.4	4678.3	4043.0	3586.0	3454.5
55°	3484.2	3933.0	3576.1	3105.7	2982.2	3105.7	3576.1	3933.0	3484.2	3191.3	3094.0
57.5°	3059.7	3336.4	3105.7	2809.2	2727.2	2809.2	3105.7	3336.4	3059.7	2839.8	2787.5
60°	2683.9	2889.4	2740.7	2550.5	2527.1	2550.5	2740.7	2889.4	2683.9	2555.0	2520.8
62.5°	2394.6	2524.4	2423.4	2318.0	2297.3	2318.0	2423.4	2524.4	2394.6	2295.5	2301.8
65°	2124.2	2245.0	2165.7	2108.9	2116.1	2108.9	2165.7	2245.0	2124.2	2078.3	2088.2
67.5°	1915.1	1978.2	1944.0	1911.5	1919.6	1911.5	1944.0	1978.2	1915.1	1870.1	1885.4
70°	1692.5	1760.1	1725.0	1729.5	1743.0	1729.5	1725.0	1760.1	1692.5	1679.0	1690.7
72.5°	1479.8	1532.1	1520.4	1531.2	1545.6	1531.2	1520.4	1532.1	1479.8	1478.0	1478.9
75°	1270.8	1310.4	1315.8	1331.1	1353.7	1331.1	1315.8	1310.4	1270.8	1257.2	1273.5
77.5°	1042.7	1087.8	1104.9	1125.7	1159.0	1125.7	1104.9	1087.8	1042.7	1051.7	1059.9
80°	833.6	854.4	892.2	907.6	954.4	907.6	892.2	854.4	833.6	818.3	830.0
82.5°	610.1	629.1	661.5	690.4	717.4	690.4	661.5	629.1	610.1	602.9	603.8
85°	352.4	381.2	402.9	437.1	445.2	437.1	402.9	381.2	352.4	360.5	352.4
87.5°	123.5	132.5	151.4	164.9	165.8	164.9	151.4	132.5	123.5	126.2	114.5
90°	28.9	49.2	84.6	48.5	35.2	48.5	84.6	49.2	28.9	50.5	78.5
92.5°	37.5	66.4	119.1	63.6	46.0	63.6	119.1	66.4	37.5	65.5	125.9
95°	55.7	81.5	151.4	70.0	54.6	70.0	151.4	81.5	55.7	87.1	175.4
97.5°	85.8	100.9	170.8	74.4	65.4	74.4	170.8	100.9	85.8	106.5	201.3
100°	113.9	113.9	310.8	85.1	74.0	85.1	310.8	113.9	113.9	131.1	313.4
102.5°	172.0	222.5	719.0	167.9	89.1	167.9	719.0	222.5	172.0	245.3	664.6
105°	312.1	506.9	1264.2	428.6	161.1	428.6	1264.2	506.9	312.1	512.5	1183.9
107.5°	590.1	944.4	1628.3	842.4	370.1	842.4	1628.3	944.4	590.1	906.8	1561.9
110°	943.5	1319.3	1777.0	1152.7	745.1	1152.7	1777.0	1319.3	943.5	1245.1	1637.3



TEST NUMBER:

CATALOG NUMBER: EHBR1-54-UNV-TASM-L840-UPL40

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	1227.9	1470.1	1736.1	1277.7	1029.5	1277.7	1736.1	1470.1	1227.9	1374.4	1568.4
115°	1334.4	1448.6	1550.8	1273.3	1141.5	1273.3	1550.8	1448.6	1334.4	1342.1	1400.3
117.5°	1289.1	1325.8	1339.6	1195.8	1148.0	1195.8	1339.6	1325.8	1289.1	1207.3	1189.1
120°	1164.2	1149.1	1129.3	1081.6	1083.4	1081.6	1129.3	1149.1	1164.2	1054.3	993.0
122.5°	1007.8	975.4	954.8	966.1	995.0	966.1	954.8	975.4	1007.8	897.9	851.7
125°	854.8	822.4	832.9	867.0	896.8	867.0	832.9	822.4	854.8	763.0	751.3
127.5°	726.4	711.3	744.5	782.9	808.4	782.9	744.5	711.3	726.4	668.2	680.2
130°	634.6	638.0	682.0	714.9	730.9	714.9	682.0	638.0	634.6	606.6	635.9
132.5°	577.3	593.7	635.5	664.1	673.6	664.1	635.5	593.7	577.3	569.6	605.3
135°	541.6	565.7	604.1	622.2	626.2	622.2	604.1	565.7	541.6	544.7	577.3
137.5°	521.0	545.0	573.9	588.7	585.2	588.7	573.9	545.0	521.0	528.3	553.3
140°	508.9	533.0	545.9	562.8	560.3	562.8	545.9	533.0	508.9	513.2	532.6
142.5°	496.9	518.8	525.3	537.8	534.4	537.8	525.3	518.8	496.9	501.2	514.1
145°	491.3	507.7	502.5	518.4	513.8	518.4	502.5	507.7	491.3	492.6	499.9
147.5°	480.6	492.6	486.1	499.9	495.3	499.9	486.1	492.6	480.6	480.6	483.6
150°	468.5	477.1	467.6	483.6	483.3	483.6	467.6	477.1	468.5	466.4	469.4
152.5°	452.2	460.8	452.2	470.3	469.1	470.3	452.2	460.8	452.2	450.0	453.1
155°	438.9	443.2	438.9	457.0	457.9	457.0	438.9	443.2	438.9	438.0	439.8
157.5°	429.9	433.0	430.8	446.8	447.7	446.8	430.8	433.0	429.9	429.9	430.8
160°	422.8	427.1	425.8	439.6	440.5	439.6	425.8	427.1	422.8	424.0	424.9
162.5°	420.2	420.2	419.9	433.7	435.5	433.7	419.9	420.2	420.2	420.2	422.4
165°	416.5	418.6	416.1	426.5	430.5	426.5	416.1	418.6	416.5	417.7	417.7
167.5°	416.1	414.0	415.8	424.9	428.9	424.9	415.8	414.0	416.1	417.4	417.4
170°	412.7	413.6	413.3	422.4	426.4	422.4	413.3	413.6	412.7	414.9	416.1
172.5°	415.4	415.4	413.8	420.8	427.0	420.8	413.8	415.4	415.4	416.7	418.8
175°	417.2	416.0	415.6	420.6	426.7	420.6	415.6	416.0	417.2	416.3	416.3
177.5°	415.1	416.9	418.7	423.6	431.9	423.6	418.7	416.9	415.1	416.3	416.3
180°	416.9	416.9	416.9	416.9	416.9	416.9	416.9	416.9	416.9	416.9	416.9



TEST NUMBER:

CATALOG NUMBER: EHBR1-54-UNV-TASM-L840-UPL40

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
0°	48062.3	48062.3	48062.3	48062.3	48062.3	48062.3
2.5°	46666.3	46635.7	46666.3	46992.5	47417.0	48034.4
5°	45582.1	45412.7	45582.1	45943.5	46723.1	47898.3
7.5°	44319.5	44221.2	44319.5	44924.2	45909.3	47572.9
10°	42990.1	42767.5	42990.1	43673.3	44835.0	47076.4
12.5°	41351.7	41057.0	41351.7	42057.3	43522.8	46284.2
15°	39268.0	39009.3	39268.0	40051.2	41750.9	45112.6
17.5°	37032.0	36797.7	37032.0	37712.5	39584.3	43461.5
20°	34223.8	34039.9	34223.8	35186.3	37023.0	41333.7
22.5°	31277.6	31105.5	31277.6	32132.9	34044.4	38666.0
25°	27811.4	27717.7	27811.4	28766.7	30495.3	35545.9
27.5°	24065.9	23906.3	24065.9	25065.3	26830.9	31876.0
30°	20239.2	19975.1	20239.2	21133.2	22714.0	27799.7
32.5°	16496.3	16306.2	16496.3	17133.5	18785.5	23235.8
35°	12878.7	12688.6	12878.7	13454.6	15076.9	19025.2
37.5°	10035.3	9699.2	10035.3	10404.8	11721.6	14930.9
40°	7611.0	7556.9	7611.0	8076.0	8918.7	11616.1
42.5°	6196.0	6049.1	6196.0	6396.1	7027.0	8801.5
45°	5083.9	5026.2	5083.9	5235.3	5658.9	6880.1
47.5°	4371.9	4397.2	4371.9	4469.3	4786.5	5603.0
50°	3841.1	3856.4	3841.1	3887.1	4098.8	4706.3
52.5°	3450.0	3436.4	3450.0	3454.5	3586.0	4043.0
55°	3103.9	3086.8	3103.9	3094.0	3191.3	3484.2
57.5°	2801.1	2813.7	2801.1	2787.5	2839.8	3059.7
60°	2530.7	2542.4	2530.7	2520.8	2555.0	2683.9
62.5°	2302.7	2309.9	2302.7	2301.8	2295.5	2394.6
65°	2099.0	2107.1	2099.0	2088.2	2078.3	2124.2
67.5°	1904.3	1904.3	1904.3	1885.4	1870.1	1915.1
70°	1721.4	1720.5	1721.4	1690.7	1679.0	1692.5
72.5°	1501.5	1523.1	1501.5	1478.9	1478.0	1479.8
75°	1287.9	1313.1	1287.9	1273.5	1257.2	1270.8
77.5°	1071.6	1110.3	1071.6	1059.9	1051.7	1042.7
80°	849.9	892.2	849.9	830.0	818.3	833.6
82.5°	628.2	659.7	628.2	603.8	602.9	610.1
85°	374.0	424.5	374.0	352.4	360.5	352.4
87.5°	119.9	153.2	119.9	114.5	126.2	123.5
90°	46.2	28.9	46.2	78.5	50.5	28.9
92.5°	69.9	41.8	69.9	125.9	65.5	37.5
95°	80.6	48.3	80.6	175.4	87.1	55.7
97.5°	89.2	62.1	89.2	201.3	106.5	85.8
100°	104.3	81.5	104.3	313.4	131.1	113.9
102.5°	220.7	137.6	220.7	664.6	245.3	172.0
105°	464.2	236.7	464.2	1183.9	512.5	312.1
107.5°	830.5	409.1	830.5	1561.9	906.8	590.1
110°	1102.0	762.5	1102.0	1637.3	1245.1	943.5



TEST NUMBER:

CATALOG NUMBER: EHBR1-54-UNV-TASM-L840-UPL40

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	1183.9	1029.7	1183.9	1568.4	1374.4	1227.9
115°	1138.7	1083.5	1138.7	1400.3	1342.1	1334.4
117.5°	1039.5	1046.9	1039.5	1189.1	1207.3	1289.1
120°	925.3	969.3	925.3	993.0	1054.3	1164.2
122.5°	820.6	872.4	820.6	851.7	897.9	1007.8
125°	730.1	782.7	730.1	751.3	763.0	854.8
127.5°	667.6	703.0	667.6	680.2	668.2	726.4
130°	619.0	649.2	619.0	635.9	606.6	634.6
132.5°	585.4	604.8	585.4	605.3	569.6	577.3
135°	556.1	572.5	556.1	577.3	544.7	541.6
137.5°	531.2	545.4	531.2	553.3	528.3	521.0
140°	509.3	521.3	509.3	532.6	513.2	508.9
142.5°	486.5	495.1	486.5	514.1	501.2	496.9
145°	471.0	477.5	471.0	499.9	492.6	491.3
147.5°	457.8	462.1	457.8	483.6	480.6	480.6
150°	444.5	448.8	444.5	469.4	466.4	468.5
152.5°	430.3	435.5	430.3	453.1	450.0	452.2
155°	421.3	426.5	421.3	439.8	438.0	438.9
157.5°	416.6	420.6	416.6	430.8	429.9	429.9
160°	412.9	415.9	412.9	424.9	424.0	422.8
162.5°	408.2	411.3	408.2	422.4	420.2	420.2
165°	407.9	408.8	407.9	417.7	417.7	416.5
167.5°	406.6	408.8	406.6	417.4	417.4	416.1
170°	407.5	408.4	407.5	416.1	414.9	412.7
172.5°	409.3	410.2	409.3	418.8	416.7	415.4
175°	409.0	409.9	409.0	416.3	416.3	417.2
177.5°	412.0	412.9	412.0	416.3	416.3	415.1
180°	416.9	416.9	416.9	416.9	416.9	416.9



TEST NUMBER: CATALOG  
 CATALOG NUMBER: EHBR1-54-UNV-TASM-L840-UPL40

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.46	20.56	19.94	21.02	21.50	18.78	19.88	19.26	20.34	20.82
	3H	21.01	21.99	21.51	22.46	22.99	20.62	21.61	21.12	22.08	22.61
	4H	21.64	22.56	22.16	23.05	23.60	21.41	22.32	21.93	22.81	23.36
	6H	22.12	22.96	22.66	23.47	24.03	22.05	22.89	22.58	23.40	23.95
	8H	22.27	23.07	22.82	23.59	24.16	22.27	23.07	22.82	23.59	24.16
	12H	22.35	23.11	22.90	23.62	24.21	22.40	23.16	22.95	23.67	24.27
4H	2H	19.87	20.79	20.40	21.28	21.83	19.35	20.27	19.87	20.76	21.31
	3H	21.67	22.43	22.20	22.96	23.53	21.41	22.17	21.94	22.70	23.27
	4H	22.44	23.12	23.00	23.67	24.27	22.32	23.00	22.87	23.54	24.15
	6H	23.06	23.65	23.64	24.22	24.84	23.09	23.67	23.67	24.24	24.87
	8H	23.25	23.80	23.84	24.37	25.00	23.36	23.91	23.94	24.47	25.10
	12H	23.36	23.84	23.96	24.44	25.08	23.53	24.01	24.13	24.61	25.24
8H	4H	22.69	23.24	23.28	23.81	24.44	22.59	23.14	23.18	23.71	24.34
	6H	23.43	23.88	24.05	24.50	25.13	23.50	23.94	24.11	24.56	25.20
	8H	23.70	24.10	24.34	24.73	25.38	23.85	24.25	24.49	24.88	25.53
	12H	23.88	24.22	24.50	24.83	25.56	24.10	24.45	24.73	25.06	25.78
12H	4H	22.70	23.19	23.30	23.79	24.42	22.61	23.09	23.21	23.69	24.32
	6H	23.48	23.87	24.11	24.50	25.15	23.54	23.94	24.18	24.57	25.22
	8H	23.79	24.14	24.42	24.75	25.47	23.95	24.30	24.58	24.91	25.63