

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1444510

Luminaire Tested: EHBR1-18-UNV-TA-L835-UPL30

Issue Date: 5/1/2026

Test Information

Test Method: LM-79-2019
Report Number: P1444510
REPORT IS A COMBINATION OF REPORTS P1444337 AND P1431635
Test Lab: INNOVATION CENTER
Issue Date: 5/1/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-18-UNV-TA-L835-UPL30
Description: Elevate Round Highbay at, 18000 lumens, 3500K 80CRI LEDs with TA lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 20717.9 lumens
Efficiency: N/A
Efficacy: 177.5 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 0.77 / 0.88
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 116.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1444510
CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - 90°-270° - · - 135°-315°



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	116	116	116	116	111	111	111	111	103	103	103	95	95	95	88	88	88	88	88	88	85
1	108	105	102	99	104	101	98	96	94	92	90	88	86	85	82	81	80	80	80	80	77
2	101	95	90	86	98	92	88	84	87	83	80	81	79	76	76	74	72	72	72	72	70
3	95	87	81	77	92	85	79	75	80	75	72	75	72	69	71	68	66	66	66	66	64
4	89	80	74	69	86	78	72	67	74	69	65	70	66	63	67	63	61	61	61	61	58
5	84	74	67	62	81	72	66	61	69	63	59	65	61	58	62	59	56	56	56	56	54
6	79	69	62	57	76	67	61	56	64	59	55	61	57	53	58	55	52	52	52	52	50
7	74	64	57	52	72	62	56	52	60	54	50	57	53	49	55	51	48	48	48	48	46
8	70	60	53	48	68	58	52	48	56	51	47	54	49	46	52	48	45	45	45	45	43
9	67	56	49	45	65	55	49	44	53	47	44	51	46	43	49	45	42	42	42	42	40
10	63	52	46	42	61	51	45	41	50	44	41	48	43	40	46	42	39	39	39	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	72040	72040	72040	72040
5°	72389	74500	71376	75476
10°	72994	78219	71243	77702
15°	73351	70905	71119	68050
20°	72593	52822	70217	48873
25°	68712	33407	66441	30311
30°	60026	20075	57701	18346
35°	46196	12598	43539	11159
40°	29223	7902	26736	7425
45°	15062	6156	14812	6055
50°	8831	5475	8560	5390
55°	6766	5181	6515	5134
60°	5724	5292	5481	5223
65°	5377	5526	5171	5337
70°	5254	5787	4992	5570
75°	5616	6138	5313	5867
80°	5811	6796	5269	6205
85°	5473	6555	4422	5615

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 25°
 Vertical Angle: 45°
 Luminance: 23051 cd/sqm



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1511.8	7.3
10°-20°	4253.0	20.5
20°-30°	4843.8	23.4
30°-40°	3481.5	16.8
40°-50°	1605.7	7.8
50°-60°	768.4	3.7
60°-70°	560.6	2.7
70°-80°	425.9	2.1
80°-90°	199.0	1.0
90°-100°	84.1	0.4
100°-110°	520.0	2.5
110°-120°	961.4	4.6
120°-130°	578.7	2.8
130°-140°	359.6	1.7
140°-150°	256.9	1.2
150°-160°	172.6	0.8
160°-170°	100.9	0.5
170°-180°	33.9	0.2
0°-30°	10608.6	51.2
0°-40°	14090.1	68.0
0°-60°	16464.1	79.5
0°-90°	17649.7	85.2
90°-120°	1565.6	7.6
90°-150°	2760.7	13.3
90°-180°	3068.0	14.8
0°-180°	20717.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	15340	15340	15340	15340	15340	
5°	15456	15907	15240	16115	15456	1477
15°	15389	14876	14920	14277	15389	4336
25°	13722	6671	13268	6053	13722	6220
35°	8479	2312	7991	2048	8479	5204
45°	2437	996	2397	980	2437	2073
55°	914	700	880	694	914	844
65°	561	577	540	557	561	561
75°	396	432	374	413	396	411
85°	188	225	152	193	188	177
90°	64	78	28	31	64	38
95°	39	44	39	44	39	37
105°	184	240	122	240	184	245
115°	835	1020	875	1020	835	770
125°	614	658	697	658	614	560
135°	465	424	502	426	465	363
145°	398	397	425	399	398	252
155°	360	367	386	369	360	168
165°	349	352	363	354	349	99
175°	352	356	359	357	352	34
180°	356	356	356	356	356	



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5
2.5°	15399.1	15397.9	15397.7	15396.6	15396.3	15396.3	15395.7	15394.5	15393.7	15391.9	15390.0
5°	15456.2	15455.6	15455.9	15456.0	15455.0	15452.6	15448.9	15444.2	15438.5	15433.0	15428.1
7.5°	15500.4	15501.5	15502.9	15502.6	15499.2	15493.6	15485.9	15481.6	15484.2	15492.5	15511.6
10°	15508.5	15515.1	15517.6	15516.8	15510.1	15505.3	15507.2	15523.4	15555.8	15599.0	15658.0
12.5°	15477.1	15485.1	15484.8	15482.2	15475.7	15482.3	15505.9	15554.2	15623.6	15708.7	15808.5
15°	15388.7	15399.2	15396.3	15392.8	15388.5	15410.2	15457.2	15541.2	15648.3	15768.4	15891.2
17.5°	15217.3	15230.0	15223.8	15219.9	15216.3	15256.9	15337.6	15460.7	15595.6	15731.4	15847.8
20°	14920.0	14928.5	14913.8	14906.9	14912.8	14992.4	15111.3	15268.4	15410.7	15539.0	15618.6
22.5°	14434.7	14445.3	14417.9	14414.7	14448.5	14570.7	14721.3	14897.0	15030.6	15132.3	15162.9
25°	13721.8	13732.1	13699.6	13719.1	13776.7	13943.0	14122.4	14310.3	14424.3	14499.7	14478.9
27.5°	12759.5	12768.9	12738.0	12777.8	12869.0	13087.6	13298.6	13502.4	13604.1	13656.9	13590.0
30°	11545.9	11565.4	11528.9	11584.4	11723.6	12007.5	12249.2	12477.8	12579.1	12619.3	12515.2
32.5°	10104.4	10132.3	10092.0	10174.6	10368.7	10709.7	10984.4	11239.8	11351.8	11397.8	11280.1
35°	8478.6	8518.6	8472.4	8596.5	8835.9	9215.6	9519.7	9804.9	9937.5	10002.6	9884.1
37.5°	6756.1	6794.3	6769.3	6934.8	7197.7	7591.3	7901.7	8209.3	8359.2	8456.8	8363.4
40°	5065.1	5100.0	5118.9	5308.2	5555.4	5926.4	6224.7	6528.9	6696.6	6819.1	6761.5
42.5°	3575.0	3610.2	3674.5	3857.1	4063.3	4370.4	4625.9	4899.1	5059.3	5190.0	5167.7
45°	2436.9	2477.9	2558.4	2708.0	2857.1	3077.5	3265.0	3477.5	3608.3	3728.1	3729.5
47.5°	1707.7	1736.4	1808.4	1910.5	2007.8	2283.6	2294.9	2399.3	2487.3	2576.8	2588.4
50°	1316.1	1333.4	1371.6	1428.5	1483.6	1555.2	1620.7	1696.4	1750.6	1799.6	1811.3
52.5°	1081.7	1092.8	1112.2	1143.0	1175.0	1213.9	1249.0	1290.6	1319.9	1346.2	1351.7
55°	914.3	923.4	952.3	958.2	994.7	1001.7	1017.3	1042.6	1059.8	1075.5	1079.4
57.5°	787.9	794.5	800.6	813.7	825.0	841.3	854.5	872.7	883.5	894.9	895.8
60°	688.1	692.9	697.4	706.4	714.1	725.5	734.6	746.9	754.7	763.2	764.2
62.5°	614.0	617.4	620.3	626.3	631.8	640.5	647.7	658.0	665.3	671.8	673.3
65°	561.2	563.7	565.6	570.1	574.9	582.4	588.9	597.3	602.6	607.7	608.7
67.5°	514.5	516.9	518.7	522.9	526.2	531.8	536.2	542.5	546.5	550.6	550.6
70°	461.0	463.1	464.6	468.5	471.1	475.9	479.5	485.1	489.3	493.7	494.9
72.5°	423.8	425.2	427.1	430.7	434.4	439.4	444.2	450.1	455.0	459.7	461.7
75°	395.6	397.2	398.5	401.5	404.0	408.4	411.9	417.3	421.6	426.6	429.1
77.5°	355.0	356.7	357.8	360.9	363.0	367.2	369.8	374.7	378.2	382.7	384.9
80°	305.7	307.4	308.2	311.1	312.8	316.6	319.2	323.9	326.8	331.3	334.0
82.5°	251.2	252.8	253.3	256.0	256.9	260.1	261.9	266.7	270.3	276.2	280.3
85°	188.1	188.7	189.6	188.9	192.8	193.0	197.3	198.1	203.7	205.3	211.8
87.5°	115.0	116.7	117.6	120.2	121.3	123.9	124.7	127.5	129.1	132.3	133.7
90°	63.9	67.6	69.5	73.6	75.4	79.3	81.1	85.1	87.1	91.3	94.4
92.5°	33.7	36.1	38.5	41.0	43.4	46.1	48.7	51.1	53.6	56.2	61.0
95°	38.8	41.5	44.2	47.0	49.7	52.5	55.2	58.0	60.7	63.4	71.4
97.5°	48.9	51.3	53.6	56.0	58.4	60.8	63.1	65.5	67.9	70.3	79.8
100°	64.2	66.2	68.2	70.2	72.2	74.2	76.2	78.2	80.2	82.2	99.9
102.5°	107.4	114.5	121.7	128.8	135.9	142.9	150.2	157.2	164.4	171.4	209.0
105°	183.8	203.1	222.5	241.8	261.1	280.5	299.8	319.1	338.4	357.7	418.7
107.5°	316.1	351.8	387.6	423.3	459.1	494.9	530.7	566.4	602.1	637.8	699.7
110°	586.8	615.5	644.4	673.1	702.0	730.8	759.6	788.2	817.1	845.8	891.0



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	792.0	805.1	818.1	831.3	844.2	857.3	870.3	883.4	896.4	909.4	941.8
115°	834.7	839.4	844.1	848.6	853.4	857.9	862.6	867.1	871.8	876.2	898.3
117.5°	808.9	808.1	807.5	806.8	806.0	805.4	804.7	803.9	803.1	802.4	814.8
120°	751.9	748.1	744.4	740.4	736.6	732.6	728.9	725.0	721.1	717.0	722.5
122.5°	680.6	675.9	671.5	666.7	662.1	657.4	652.7	647.9	643.2	638.6	640.7
125°	614.2	609.5	605.0	600.3	595.6	590.8	586.1	581.4	576.6	571.9	573.1
127.5°	556.3	553.2	550.0	546.6	543.4	540.0	536.7	533.3	530.0	526.5	527.1
130°	518.1	515.3	512.3	509.4	506.6	503.5	500.5	497.5	494.5	491.4	492.3
132.5°	486.5	484.6	482.7	480.6	478.6	476.5	474.4	472.1	470.1	467.8	468.8
135°	464.8	463.0	461.3	459.5	457.7	455.5	453.6	451.6	449.5	447.5	448.6
137.5°	446.2	444.8	443.2	441.4	439.7	437.8	436.1	434.1	432.4	430.4	431.6
140°	429.2	427.8	426.4	424.8	423.3	421.8	420.1	418.4	416.7	415.0	416.5
142.5°	410.3	409.2	408.2	407.0	406.0	404.6	403.4	402.0	400.8	399.4	401.2
145°	397.7	396.9	396.1	395.1	394.1	393.1	392.0	390.8	389.9	388.7	390.6
147.5°	386.6	385.9	385.2	384.6	383.9	382.9	382.0	381.2	380.4	379.4	381.3
150°	376.9	376.2	375.6	375.0	374.2	373.4	372.5	371.8	371.0	370.0	371.8
152.5°	366.8	366.1	365.5	365.0	364.2	363.3	362.6	361.9	361.1	360.2	361.9
155°	360.3	359.6	359.0	358.4	357.7	356.9	356.1	355.5	354.7	353.8	355.2
157.5°	355.7	355.2	354.7	354.1	353.7	353.2	352.7	352.1	351.6	351.0	352.0
160°	352.9	352.5	352.0	351.4	350.9	350.4	349.9	349.4	348.9	348.3	349.1
162.5°	350.2	349.6	349.2	348.7	348.2	347.7	347.2	346.7	346.3	345.7	346.6
165°	349.0	348.8	348.5	348.2	347.9	347.6	347.3	347.0	346.7	346.3	347.0
167.5°	351.1	350.6	350.2	349.7	349.4	349.0	348.5	348.0	347.7	347.1	347.8
170°	351.2	350.9	350.7	350.5	350.3	350.1	349.9	349.6	349.5	349.3	349.8
172.5°	352.5	352.2	352.1	352.0	351.8	351.6	351.5	351.3	351.2	350.9	351.7
175°	351.8	351.6	351.5	351.4	351.3	351.2	351.1	351.0	351.0	350.8	351.3
177.5°	354.0	353.9	353.9	353.9	353.9	353.8	353.8	353.7	353.6	353.6	353.9
180°	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5
2.5°	15388.5	15386.6	15384.1	15380.8	15378.0	15374.8	15367.1	15364.8	15367.4	15369.1	15372.7
5°	15425.0	15426.1	15426.6	15433.5	15439.6	15454.6	15572.6	15619.5	15655.8	15678.9	15713.8
7.5°	15535.3	15570.7	15605.8	15653.1	15693.7	15748.7	15955.2	16043.1	16105.6	16150.5	16205.7
10°	15722.1	15799.6	15872.1	15957.2	16030.3	16114.0	16306.3	16391.9	16445.9	16485.3	16522.0
12.5°	15910.3	16017.6	16114.7	16209.4	16288.6	16361.2	16428.8	16458.7	16461.2	16462.5	16443.0
15°	16008.3	16111.0	16196.4	16259.1	16305.6	16326.2	16209.8	16148.7	16071.6	16008.0	15903.4
17.5°	15946.5	16008.0	16045.0	16041.3	16022.1	15957.7	15628.1	15446.8	15266.8	15104.6	14891.9
20°	15671.5	15666.7	15634.6	15543.6	15433.9	15263.4	14698.2	14372.2	14056.9	13780.0	13444.2
22.5°	15159.8	15079.3	14967.1	14770.8	14552.8	14254.8	13444.9	12965.3	12526.4	12138.8	11704.5
25°	14418.5	14252.9	14045.9	13734.3	13395.5	12960.9	11962.7	11366.2	10839.2	10382.2	9881.1
27.5°	13469.8	13220.3	12916.9	12485.7	12026.7	11469.9	10363.2	9704.8	9139.3	8649.3	8115.9
30°	12346.6	12022.1	11630.4	11095.2	10541.5	9910.0	8787.6	8120.8	7548.2	7044.2	6510.4
32.5°	11077.2	10697.2	10238.2	9637.5	9038.7	8389.4	7305.5	6660.0	6113.1	5628.2	5145.1
35°	9677.3	9269.8	8784.1	8171.4	7576.2	6945.0	5950.4	5368.4	4885.3	4456.8	4066.7
37.5°	8175.5	7775.4	7313.8	6736.3	6184.4	5612.5	4754.2	4266.5	3861.2	3505.5	3204.3
40°	6614.2	6264.0	5864.7	5365.4	4894.4	4418.0	3713.5	3326.4	3006.5	2735.2	2509.6
42.5°	5071.9	4800.6	4494.3	4099.7	3739.3	3376.6	2834.4	2547.6	2310.6	2115.3	1955.7
45°	3679.9	3498.3	3292.9	3018.6	2769.2	2516.3	2130.4	1928.8	1774.5	1648.5	1542.1
47.5°	2572.4	2467.1	2460.7	2207.2	2024.4	1869.6	1621.0	1493.7	1399.2	1322.9	1255.5
50°	1806.5	1755.6	1692.3	1601.8	1517.0	1429.5	1278.1	1201.1	1145.7	1099.5	1056.9
52.5°	1350.5	1324.1	1290.4	1242.4	1196.4	1147.2	1051.4	1002.3	984.9	941.9	908.1
55°	1078.7	1063.5	1044.4	1016.2	988.1	977.0	894.9	858.4	835.4	818.5	800.2
57.5°	896.0	884.7	873.3	854.2	838.0	818.5	774.8	756.1	742.4	732.5	719.8
60°	764.3	757.6	751.2	739.9	731.2	720.6	692.9	682.4	675.2	669.2	661.2
62.5°	674.6	671.1	667.8	661.9	657.4	651.7	632.7	627.6	624.0	621.0	616.2
65°	609.8	607.3	605.5	601.6	599.3	595.9	579.6	576.2	574.0	572.9	570.1
67.5°	550.9	548.3	547.2	544.3	543.4	541.3	528.0	526.1	525.3	525.7	524.7
70°	496.0	494.9	495.4	495.0	496.3	496.6	488.6	488.5	489.4	491.0	491.2
72.5°	463.0	463.0	463.6	463.9	465.0	465.6	458.9	458.6	459.0	460.3	460.3
75°	431.6	432.1	433.8	434.4	435.7	436.0	427.2	426.1	426.2	427.4	427.0
77.5°	388.1	390.0	393.3	394.9	397.7	398.2	388.2	387.1	387.1	388.3	387.3
80°	338.9	342.5	347.6	351.2	355.4	357.1	346.8	344.4	342.2	341.8	339.8
82.5°	286.5	290.9	297.1	300.3	304.8	305.8	288.7	285.5	283.5	283.7	281.9
85°	218.7	222.0	227.7	229.5	232.2	232.0	212.4	204.1	206.3	202.8	205.6
87.5°	137.2	139.1	142.6	143.1	144.4	144.1	124.5	120.6	119.5	119.6	118.1
90°	99.8	103.4	108.6	110.8	115.0	116.9	103.2	103.5	100.3	99.1	95.3
92.5°	65.9	70.7	75.6	80.5	85.4	90.3	93.3	97.5	92.6	87.4	82.5
95°	79.4	87.4	95.4	103.5	111.5	119.5	127.5	135.6	128.1	120.6	113.2
97.5°	89.3	98.8	108.2	117.6	127.1	136.6	146.1	155.6	147.6	139.4	131.4
100°	117.5	135.3	152.9	170.6	188.3	206.0	223.7	241.4	225.9	210.3	194.8
102.5°	246.6	284.1	321.6	359.2	396.8	434.3	472.0	509.6	474.0	438.3	402.6
105°	479.7	540.5	601.5	662.3	723.1	784.0	845.1	906.0	849.1	792.0	735.0
107.5°	761.3	823.3	885.0	946.7	1008.5	1070.4	1132.4	1194.2	1138.6	1082.9	1027.4
110°	936.2	981.4	1026.4	1071.5	1116.6	1161.8	1207.3	1252.5	1219.1	1185.7	1152.4



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	974.1	1006.5	1038.8	1071.1	1103.3	1135.6	1168.5	1200.9	1184.3	1167.5	1151.0
115°	920.1	942.0	963.8	985.7	1007.6	1029.3	1051.8	1073.9	1068.6	1063.4	1058.3
117.5°	827.1	839.4	851.8	864.0	876.2	888.7	901.7	914.3	915.3	916.5	917.6
120°	727.9	733.2	738.5	743.9	749.1	754.5	760.8	766.3	771.1	775.7	780.5
122.5°	643.1	645.2	647.4	649.6	651.8	653.9	657.3	659.7	663.0	666.5	669.9
125°	574.4	575.7	576.9	578.1	579.2	580.4	583.0	584.4	584.9	585.5	585.8
127.5°	527.6	528.1	528.5	529.0	529.4	529.9	531.8	532.5	531.0	529.3	527.8
130°	493.1	493.8	494.6	495.5	496.3	497.1	499.4	500.5	497.5	494.3	491.3
132.5°	469.8	470.8	471.6	472.7	473.7	474.6	477.2	478.5	474.9	471.3	467.7
135°	449.7	451.0	452.0	453.2	454.4	455.6	458.4	460.0	456.7	453.2	449.8
137.5°	432.6	433.9	435.0	436.2	437.4	438.6	441.7	443.2	440.6	437.9	435.3
140°	417.7	419.0	420.4	421.8	423.1	424.6	427.9	429.7	427.7	425.7	423.5
142.5°	402.8	404.6	406.4	408.1	410.0	411.8	415.7	417.9	416.5	414.9	413.5
145°	392.4	394.4	396.4	398.4	400.5	402.5	406.9	409.3	408.4	407.5	406.7
147.5°	382.8	384.7	386.6	388.3	390.3	392.3	396.6	399.1	398.6	398.1	397.6
150°	373.6	375.4	377.2	379.1	381.1	383.0	387.8	390.4	390.0	389.5	389.0
152.5°	363.4	365.1	366.8	368.5	370.2	372.0	377.3	379.9	379.5	379.0	378.7
155°	356.4	357.8	359.1	360.5	361.9	363.4	368.8	371.2	371.0	370.8	370.6
157.5°	352.8	353.9	354.8	355.9	356.8	358.0	363.3	365.5	365.3	365.1	365.0
160°	349.8	350.7	351.4	352.3	353.0	354.0	359.3	361.3	361.2	361.0	360.8
162.5°	347.5	348.7	349.5	350.6	351.6	352.7	358.2	360.4	360.0	359.6	359.3
165°	347.7	348.3	349.0	349.7	350.4	351.1	356.1	357.9	357.8	357.5	357.4
167.5°	348.5	349.2	349.8	350.5	351.3	352.1	356.8	358.5	358.4	358.2	358.1
170°	350.3	350.9	351.4	352.1	352.7	353.3	357.2	358.7	358.4	358.0	357.7
172.5°	352.2	352.8	353.4	354.1	354.7	355.4	358.8	360.1	359.9	359.6	359.2
175°	351.7	352.2	352.7	353.2	353.7	354.2	356.8	357.9	357.8	357.7	357.6
177.5°	354.3	354.6	355.0	355.4	355.8	356.0	357.7	358.4	358.3	358.3	358.2
180°	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5
2.5°	15373.4	15378.9	15379.6	15385.9	15385.4	15392.9	15391.8	15397.9	15394.3	15399.3	15395.0
5°	15734.5	15767.3	15784.4	15816.3	15826.4	15855.0	15863.1	15889.2	15890.2	15911.0	15906.2
7.5°	16245.0	16293.2	16321.9	16361.4	16381.4	16414.3	16428.9	16453.2	16461.0	16480.3	16481.8
10°	16549.9	16573.2	16589.6	16600.7	16610.8	16615.4	16620.9	16619.5	16620.9	16618.8	16623.6
12.5°	16429.9	16395.7	16373.1	16330.2	16305.3	16258.0	16234.7	16189.2	16172.7	16133.5	16127.9
15°	15822.7	15703.4	15619.1	15496.6	15419.5	15299.0	15228.4	15119.6	15069.9	14983.4	14960.8
17.5°	14715.8	14494.5	14323.1	14103.3	13950.8	13745.3	13616.2	13446.1	13353.0	13215.8	13168.4
20°	13164.1	12836.5	12579.5	12273.4	12054.2	11781.3	11606.5	11386.1	11258.1	11089.6	11021.4
22.5°	11342.3	10934.5	10613.5	10251.8	9987.5	9683.2	9473.8	9235.3	9096.1	8913.1	8832.1
25°	9464.7	9014.9	8658.0	8277.0	7997.6	7692.7	7483.2	7248.9	7104.8	6931.1	6850.7
27.5°	7668.8	7213.6	6868.7	6514.4	6258.1	5982.9	5794.0	5589.4	5461.6	5313.2	5237.5
30°	6084.1	5682.5	5389.0	5095.0	4881.8	4658.3	4501.3	4331.8	4219.6	4092.6	4020.4
32.5°	4792.9	4482.8	4253.0	4019.8	3845.3	3658.6	3522.8	3373.2	3272.0	3158.6	3093.3
35°	3795.9	3555.0	3371.8	3179.7	3029.8	2870.8	2751.1	2622.0	2531.2	2433.6	2377.1
37.5°	2999.1	2807.6	2656.8	2497.3	2374.1	2242.3	2197.9	2049.8	1955.6	1877.8	1823.9
40°	2353.8	2201.4	2076.6	1954.7	1854.2	1754.2	1674.0	1594.9	1534.1	1478.4	1439.9
42.5°	1838.1	1727.8	1636.6	1547.2	1474.0	1401.2	1343.0	1288.5	1247.6	1211.2	1186.3
45°	1461.2	1385.3	1322.0	1259.1	1207.4	1158.7	1119.6	1084.8	1058.3	1036.5	1021.0
47.5°	1200.4	1148.4	1103.7	1061.2	1026.2	994.3	968.2	959.6	931.2	912.0	904.8
50°	1020.1	988.8	954.9	923.6	900.1	876.8	859.8	843.2	832.5	823.7	821.0
52.5°	885.7	861.7	842.8	822.9	807.5	790.9	779.2	768.1	762.2	757.7	757.1
55°	785.7	768.9	756.4	743.1	733.8	724.1	718.0	712.2	709.6	707.2	707.4
57.5°	710.0	698.8	690.7	682.0	677.0	672.3	670.8	669.3	670.1	670.5	671.8
60°	654.9	647.6	642.5	637.5	635.4	633.9	635.1	636.4	639.1	641.2	643.1
62.5°	612.6	608.4	605.9	603.3	603.0	603.2	605.4	607.7	611.1	613.5	615.4
65°	569.1	566.7	566.0	564.2	565.1	565.6	568.3	570.0	573.3	575.4	577.7
67.5°	525.1	524.6	525.1	525.1	526.6	528.0	530.6	532.5	535.3	537.2	539.1
70°	492.7	493.0	494.1	494.3	496.0	496.9	499.2	500.4	502.9	504.5	506.8
72.5°	461.2	460.7	461.0	460.2	460.8	460.5	461.7	462.4	464.5	465.7	468.6
75°	427.5	426.1	425.8	424.2	424.3	423.2	423.7	423.6	425.1	425.7	427.7
77.5°	387.0	384.6	383.4	380.9	380.8	379.8	380.9	381.4	384.0	385.2	387.6
80°	338.4	334.6	333.0	330.0	330.4	330.3	332.8	334.7	337.8	338.3	341.3
82.5°	281.3	277.4	275.7	272.8	273.4	273.4	275.8	276.1	278.8	279.9	283.3
85°	201.4	202.8	198.8	199.1	198.3	199.8	201.4	203.3	205.6	209.2	212.1
87.5°	118.6	118.1	119.6	119.7	121.7	122.9	126.1	128.0	131.7	134.6	139.8
90°	93.4	89.7	88.8	86.3	86.4	84.0	84.3	81.8	82.5	81.3	82.7
92.5°	77.2	72.2	66.9	62.0	56.7	51.8	49.3	47.0	44.5	42.3	39.8
95°	105.7	98.1	90.7	83.2	75.7	68.3	65.5	62.8	60.0	57.3	54.6
97.5°	123.3	115.4	107.3	99.3	91.2	83.2	81.4	79.5	77.8	75.9	74.1
100°	179.2	163.7	148.2	132.5	117.0	101.5	100.1	98.6	97.2	95.7	94.2
102.5°	367.0	331.4	295.8	260.1	224.6	188.9	182.7	176.5	170.3	164.1	157.9
105°	678.0	620.9	563.9	507.0	450.0	393.0	376.0	359.0	342.0	325.0	308.0
107.5°	971.9	916.1	860.6	805.1	749.5	694.0	667.0	640.1	613.3	586.4	559.6
110°	1118.8	1085.6	1052.3	1018.9	985.6	952.4	926.7	901.2	875.4	849.9	824.3



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	1134.4	1117.8	1101.1	1084.5	1067.9	1051.4	1038.9	1026.4	1014.0	1001.5	989.0
115°	1053.1	1048.0	1042.7	1037.8	1032.6	1027.4	1026.5	1025.9	1024.9	1024.1	1023.3
117.5°	918.8	920.0	921.0	922.3	923.6	924.7	931.5	938.2	945.1	951.9	958.9
120°	785.3	789.9	794.7	799.5	804.3	809.1	818.2	827.3	836.4	845.6	854.8
122.5°	673.3	676.7	680.1	683.6	687.1	690.5	699.5	708.5	717.6	726.7	736.0
125°	586.3	586.7	587.2	587.6	588.1	588.7	596.1	603.6	611.2	618.8	626.4
127.5°	526.2	524.5	522.9	521.4	519.6	518.2	522.6	527.3	531.8	536.5	541.0
130°	488.2	485.1	482.0	479.0	475.8	472.8	474.6	476.7	478.6	480.7	482.7
132.5°	464.1	460.5	456.8	453.1	449.4	445.8	446.1	446.3	446.6	446.9	447.4
135°	446.3	442.9	439.3	435.9	432.4	429.1	428.4	427.6	427.0	426.3	425.9
137.5°	432.5	429.9	427.1	424.5	421.7	419.1	417.8	416.9	415.8	414.9	414.0
140°	421.4	419.5	417.2	415.1	413.0	410.9	410.0	409.2	408.3	407.6	406.9
142.5°	411.9	410.3	408.9	407.3	405.8	404.3	403.4	402.6	401.9	401.1	400.4
145°	405.7	404.8	403.8	402.9	402.0	401.0	400.4	399.8	399.2	398.7	398.3
147.5°	397.1	396.7	396.1	395.6	395.0	394.4	394.1	393.9	393.4	393.2	392.8
150°	388.5	388.1	387.6	387.2	386.6	386.1	385.9	385.8	385.7	385.7	385.5
152.5°	378.2	377.9	377.4	376.9	376.4	375.9	375.8	375.8	375.7	375.6	375.4
155°	370.3	370.0	369.8	369.5	369.2	369.0	368.7	368.5	368.3	368.0	367.7
157.5°	364.7	364.5	364.2	364.0	363.7	363.4	363.2	363.0	362.7	362.5	362.3
160°	360.6	360.4	360.1	359.9	359.6	359.4	359.0	358.6	358.1	357.7	357.4
162.5°	358.9	358.6	358.2	357.8	357.3	356.9	356.6	356.4	356.1	355.9	355.7
165°	357.1	356.9	356.7	356.4	356.2	356.0	355.6	355.2	354.7	354.4	354.0
167.5°	357.8	357.7	357.4	357.2	356.9	356.7	356.3	355.9	355.6	355.1	354.7
170°	357.4	357.0	356.7	356.3	355.9	355.6	355.2	354.8	354.3	354.0	353.6
172.5°	359.0	358.8	358.4	358.1	357.7	357.4	357.0	356.7	356.3	355.9	355.8
175°	357.5	357.5	357.4	357.2	357.2	357.1	357.0	356.9	356.8	356.7	356.5
177.5°	358.2	358.2	358.2	358.1	358.0	358.0	357.7	357.5	357.3	357.0	356.9
180°	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5
2.5°	15399.5	15395.6	15397.5	15390.2	15391.9	15383.2	15382.4	15372.7	15371.7	15362.4	15358.9
5°	15920.9	15912.3	15922.0	15906.9	15909.9	15890.2	15888.6	15863.3	15854.6	15822.7	15809.1
7.5°	16493.9	16490.7	16496.6	16484.0	16483.6	16466.1	16458.8	16436.1	16422.1	16388.7	16367.5
10°	16619.5	16622.4	16617.6	16618.8	16612.0	16610.1	16603.1	16598.6	16587.2	16578.6	16565.9
12.5°	16098.2	16101.3	16081.4	16094.0	16084.1	16107.3	16105.5	16132.8	16137.1	16171.7	16184.9
15°	14893.4	14889.7	14851.5	14875.5	14862.6	14913.7	14925.2	14993.8	15030.6	15118.7	15172.9
17.5°	13073.4	13063.6	13009.9	13039.2	13024.2	13099.5	13124.8	13234.5	13303.1	13445.1	13546.5
20°	10903.9	10885.1	10822.1	10856.5	10841.1	10926.6	10962.6	11095.4	11183.8	11371.9	11505.8
22.5°	8707.4	8677.6	8616.0	8648.0	8633.6	8722.1	8769.1	8902.3	9003.5	9196.7	9353.0
25°	6735.0	6708.4	6648.9	6671.4	6665.9	6740.9	6782.6	6908.5	7008.0	7192.1	7341.2
27.5°	5137.0	5109.3	5055.5	5071.4	5066.0	5129.8	5169.1	5274.3	5360.0	5514.9	5645.9
30°	3931.5	3898.3	3852.7	3861.4	3857.7	3909.4	3946.2	4034.8	4108.2	4239.1	4351.9
32.5°	3013.5	2980.1	2938.2	2942.3	2936.8	2977.4	3007.7	3084.7	3148.6	3260.0	3358.2
35°	2305.8	2344.8	2255.3	2312.1	2253.0	2339.6	2308.5	2356.7	2411.6	2505.4	2587.3
37.5°	1772.6	1745.3	1722.3	1719.9	1719.8	1739.8	1763.5	1809.9	1858.4	1928.3	2000.4
40°	1404.7	1385.6	1370.7	1369.6	1370.7	1384.9	1402.5	1434.6	1470.0	1520.2	1573.2
42.5°	1165.0	1152.4	1143.4	1142.8	1145.6	1155.7	1167.9	1186.9	1210.0	1242.6	1278.9
45°	1008.4	1001.3	996.3	996.0	997.4	1002.6	1009.6	1021.5	1036.1	1056.4	1079.4
47.5°	898.5	896.7	893.6	893.7	892.2	894.4	895.3	901.8	909.7	924.9	955.1
50°	818.4	818.4	816.2	816.0	814.0	813.9	812.3	814.9	818.5	828.0	837.6
52.5°	755.0	754.8	752.5	752.0	749.9	749.8	748.4	749.3	749.8	754.7	760.4
55°	705.6	704.1	701.0	700.1	699.3	700.5	700.0	700.0	699.4	701.3	703.1
57.5°	670.1	668.2	665.3	664.5	664.2	665.7	665.7	665.3	662.5	660.8	658.2
60°	642.1	640.1	636.9	636.2	636.7	638.7	638.6	636.8	632.9	629.4	625.4
62.5°	614.4	613.7	612.1	611.8	611.4	611.8	610.4	608.5	604.7	601.0	596.6
65°	577.5	577.9	576.6	576.8	575.4	575.2	573.0	571.3	567.3	563.9	559.5
67.5°	539.0	539.3	538.3	538.3	537.7	537.8	536.4	534.7	531.4	528.6	525.2
70°	507.4	508.2	507.6	507.8	506.8	506.5	504.5	502.8	499.5	497.1	494.0
72.5°	469.4	471.1	471.0	471.5	470.2	469.4	467.0	465.0	461.9	460.1	457.6
75°	428.5	430.7	431.4	432.4	430.4	429.3	426.7	425.1	422.6	421.5	419.8
77.5°	388.5	391.0	393.3	395.5	392.3	389.6	386.2	383.7	380.0	378.6	376.0
80°	343.6	348.0	353.1	357.5	351.9	346.2	340.6	336.6	331.7	329.8	326.6
82.5°	285.2	289.5	292.5	295.3	291.4	287.2	281.9	278.3	273.0	271.1	267.4
85°	216.6	222.1	223.9	225.3	222.8	220.7	215.6	208.9	205.6	200.4	197.7
87.5°	142.4	145.7	146.4	146.9	145.3	144.3	141.1	137.9	132.3	128.2	123.1
90°	80.9	81.4	78.3	77.5	77.1	78.8	77.2	77.7	74.6	74.5	71.8
92.5°	37.4	34.9	32.6	30.2	32.8	35.0	37.5	39.8	42.3	44.5	47.0
95°	51.9	49.1	46.3	43.6	45.9	48.0	50.2	52.4	54.6	56.7	59.0
97.5°	72.2	70.5	68.6	66.8	68.1	69.3	70.6	71.8	73.2	74.5	75.7
100°	92.7	91.2	89.8	88.3	88.3	88.3	88.3	88.3	88.3	88.3	88.3
102.5°	151.6	145.4	139.2	133.0	137.2	141.4	145.6	149.8	154.0	158.1	162.5
105°	291.0	274.0	257.0	240.1	256.5	272.9	289.3	305.8	322.2	338.8	355.2
107.5°	532.7	505.9	479.1	452.2	482.2	512.2	542.0	572.0	601.9	631.9	661.9
110°	798.8	773.2	747.7	722.1	753.9	785.6	817.4	849.1	880.9	912.6	944.6



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	976.6	964.2	951.8	939.4	959.8	980.3	1000.6	1021.2	1041.7	1062.2	1082.6
115°	1022.6	1021.8	1021.1	1020.3	1030.0	1039.7	1049.3	1059.1	1068.8	1078.5	1088.3
117.5°	965.6	972.5	979.4	986.4	989.5	992.6	995.8	998.9	1002.1	1005.2	1008.5
120°	864.0	873.2	882.5	891.9	890.6	889.3	888.1	886.8	885.7	884.5	883.4
122.5°	745.2	754.4	763.7	773.0	770.3	767.5	764.7	762.1	759.5	756.9	754.4
125°	634.2	641.9	649.7	657.5	654.8	652.0	649.4	646.7	644.0	641.5	639.1
127.5°	545.9	550.7	555.5	560.3	559.1	557.8	556.7	555.5	554.3	553.4	552.3
130°	484.9	487.0	489.4	491.6	492.0	492.4	492.8	493.2	493.9	494.5	495.1
132.5°	447.9	448.4	448.9	449.5	451.0	452.4	454.1	455.6	457.4	459.0	460.9
135°	425.5	425.1	424.7	424.4	426.6	428.7	431.0	433.2	435.7	438.2	440.8
137.5°	413.2	412.3	411.7	410.9	413.2	415.3	417.6	419.9	422.3	424.8	427.5
140°	406.2	405.6	405.1	404.4	406.7	408.8	411.1	413.3	415.9	418.2	420.8
142.5°	399.8	399.1	398.6	398.1	400.1	402.1	404.1	406.3	408.5	410.7	413.1
145°	397.8	397.4	397.1	396.7	398.1	399.6	401.0	402.6	404.3	405.9	407.7
147.5°	392.6	392.3	392.2	392.0	393.1	394.2	395.3	396.4	397.6	398.8	400.3
150°	385.6	385.5	385.5	385.6	386.3	386.9	387.8	388.3	389.3	390.0	391.0
152.5°	375.5	375.4	375.5	375.5	376.2	376.9	377.7	378.2	379.1	379.8	380.7
155°	367.6	367.4	367.3	367.1	367.4	367.7	368.0	368.2	368.6	368.9	369.3
157.5°	362.2	362.0	361.8	361.6	361.7	361.7	361.9	361.9	362.0	362.1	362.3
160°	357.0	356.5	356.2	355.9	356.1	356.2	356.5	356.6	357.0	357.3	357.5
162.5°	355.5	355.3	355.1	354.9	354.8	354.5	354.4	354.2	354.1	354.0	353.9
165°	353.5	353.1	352.7	352.3	352.4	352.4	352.5	352.5	352.5	352.5	352.6
167.5°	354.4	353.9	353.6	353.1	352.8	352.5	352.2	351.8	351.6	351.3	351.1
170°	353.3	352.9	352.7	352.3	352.2	352.0	351.9	351.8	351.7	351.6	351.6
172.5°	355.5	355.1	354.8	354.5	354.4	354.2	354.2	354.1	354.0	354.0	353.9
175°	356.5	356.4	356.3	356.2	355.9	355.8	355.6	355.4	355.3	355.0	354.8
177.5°	356.6	356.4	356.2	356.0	355.9	355.9	355.9	355.9	355.9	355.9	355.9
180°	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5
2.5°	15349.0	15344.9	15334.3	15329.1	15319.2	15314.3	15306.6	15301.7	15295.5	15290.9	15288.5
5°	15774.3	15754.6	15715.3	15691.1	15648.6	15620.6	15578.4	15547.5	15503.9	15471.8	15430.6
7.5°	16327.5	16297.4	16247.1	16208.9	16149.4	16103.9	16037.3	15984.0	15910.3	15849.1	15773.9
10°	16552.8	16535.2	16512.6	16488.0	16455.1	16422.8	16377.3	16330.9	16269.1	16207.5	16127.1
12.5°	16219.8	16236.4	16269.1	16284.3	16309.2	16317.7	16329.1	16323.8	16313.7	16288.6	16252.1
15°	15276.9	15346.0	15455.2	15530.7	15636.5	15710.8	15809.1	15872.4	15945.2	15988.8	16030.1
17.5°	13725.8	13859.5	14052.1	14205.7	14412.0	14579.8	14785.4	14946.8	15133.3	15276.3	15428.5
20°	11739.2	11926.2	12192.2	12418.0	12717.0	12970.4	13295.1	13567.2	13884.6	14149.1	14434.6
22.5°	9601.0	9821.0	10125.7	10398.1	10755.0	11073.9	11480.8	11840.5	12269.6	12653.8	13079.0
25°	7583.8	7799.4	8109.8	8391.9	8777.3	9128.5	9573.1	9985.6	10483.5	10947.8	11480.8
27.5°	5854.0	6045.6	6318.3	6572.3	6925.2	7270.0	7721.1	8161.2	8692.5	9191.3	9765.7
30°	4520.9	4676.3	4894.9	5099.1	5382.6	5664.5	6066.3	6473.3	7001.9	7518.9	8107.9
32.5°	3503.5	3636.1	3818.6	3984.4	4202.7	4415.4	4711.3	5036.4	5500.2	5995.4	6564.8
35°	2712.1	2825.5	2980.8	3123.6	3303.2	3472.0	3692.8	3924.9	4278.8	4695.4	5204.9
37.5°	2162.3	2208.5	2319.3	2436.4	2585.5	2724.2	2896.9	3068.6	3321.7	3650.4	4066.7
40°	1644.4	1717.8	1808.1	1900.2	2013.0	2124.3	2313.8	2405.0	2571.8	2807.7	3130.8
42.5°	1326.8	1378.4	1441.9	1506.0	1584.7	1662.2	1758.0	1855.7	1980.3	2140.0	2369.8
45°	1110.3	1144.0	1184.9	1227.5	1279.2	1332.2	1396.4	1463.4	1547.8	1646.0	1785.7
47.5°	965.6	984.3	1010.9	1040.1	1075.6	1112.2	1153.9	1196.6	1249.1	1307.3	1386.8
50°	852.8	868.3	889.0	908.5	933.0	970.5	987.1	1010.6	1042.1	1076.5	1120.9
52.5°	771.0	781.4	794.4	805.7	821.1	835.1	853.6	869.8	891.7	912.2	940.9
55°	707.4	711.2	718.6	725.8	736.5	746.1	758.7	769.3	783.3	795.6	813.7
57.5°	658.3	658.7	662.1	665.8	672.7	678.7	687.5	694.4	704.0	711.9	722.8
60°	623.0	621.1	621.8	623.1	627.0	630.9	636.5	641.0	647.1	651.6	657.6
62.5°	593.6	590.7	590.0	589.6	591.6	593.0	596.0	598.3	601.6	603.6	606.9
65°	556.5	553.0	551.6	550.1	550.6	550.2	551.3	551.3	553.2	553.6	555.4
67.5°	522.8	519.9	518.2	516.0	515.1	513.5	512.8	511.4	511.1	509.8	509.5
70°	492.1	489.3	487.8	485.8	484.8	482.8	481.5	479.0	477.5	475.2	473.9
72.5°	456.6	455.0	454.6	453.2	452.8	451.7	451.2	449.4	448.4	446.4	445.2
75°	419.5	418.2	418.0	416.6	416.5	415.2	414.9	413.0	412.0	410.1	409.2
77.5°	375.2	373.3	372.7	371.2	371.6	370.9	371.5	370.0	369.4	367.4	366.8
80°	325.4	322.9	321.9	319.8	320.4	319.4	320.4	320.3	321.0	319.4	319.1
82.5°	266.5	263.6	263.2	261.7	262.7	262.8	264.9	263.7	264.2	262.8	263.3
85°	193.8	191.8	189.0	188.6	186.7	188.7	186.2	187.8	185.2	187.0	184.5
87.5°	120.2	116.0	113.7	110.7	109.6	106.8	105.5	103.5	104.0	103.1	103.7
90°	72.5	70.4	72.1	71.8	74.1	74.1	77.0	77.8	80.9	81.6	84.9
92.5°	49.3	51.6	55.9	60.4	64.8	69.1	73.4	78.0	82.3	86.8	91.0
95°	61.1	63.3	69.1	75.0	80.9	86.7	92.5	98.3	104.2	110.1	115.9
97.5°	77.0	78.2	84.1	90.0	95.8	101.6	107.5	113.4	119.3	125.2	131.0
100°	88.3	88.4	105.0	121.7	138.3	154.9	171.6	188.2	204.9	221.6	238.1
102.5°	166.7	170.8	212.8	254.9	296.9	338.9	380.9	422.9	464.9	507.0	549.1
105°	371.7	388.1	452.2	516.3	580.3	644.5	708.6	772.8	836.9	901.1	965.2
107.5°	691.8	721.9	779.9	837.8	895.5	953.5	1011.6	1069.5	1127.4	1185.4	1243.4
110°	976.3	1008.1	1046.9	1085.7	1124.5	1163.3	1202.1	1240.9	1279.8	1318.6	1357.5



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	1103.0	1123.6	1146.2	1168.8	1191.4	1214.0	1236.6	1259.1	1281.8	1304.4	1327.1
115°	1098.1	1107.9	1116.4	1125.3	1134.0	1142.8	1151.5	1160.4	1169.3	1178.1	1186.9
117.5°	1011.6	1014.9	1016.2	1017.5	1018.8	1020.1	1021.6	1022.9	1024.4	1025.9	1027.2
120°	882.3	881.2	879.5	878.0	876.4	874.9	873.5	872.0	870.5	869.1	867.6
122.5°	751.6	749.2	747.7	746.1	744.8	743.3	741.9	740.5	739.1	737.8	736.3
125°	636.5	634.0	635.2	636.3	637.4	638.6	639.8	641.0	642.3	643.4	644.7
127.5°	551.2	550.4	553.5	556.7	560.0	563.2	566.4	569.7	572.9	576.2	579.4
130°	495.9	496.6	500.7	504.9	509.0	513.2	517.4	521.8	525.8	530.0	534.2
132.5°	462.6	464.6	468.5	472.5	476.5	480.5	484.5	488.6	492.6	496.7	500.6
135°	443.3	446.0	449.5	453.2	456.8	460.6	464.2	467.9	471.4	475.2	478.8
137.5°	429.9	432.6	435.5	438.4	441.2	444.2	447.1	450.1	452.8	455.8	458.6
140°	423.2	426.0	427.4	429.2	430.7	432.3	433.8	435.5	436.9	438.7	440.1
142.5°	415.3	417.8	418.7	419.7	420.6	421.7	422.7	423.6	424.5	425.4	426.3
145°	409.4	411.2	411.1	411.1	411.2	411.2	411.1	411.1	411.0	411.0	410.9
147.5°	401.5	402.9	402.5	402.3	402.0	401.7	401.5	401.1	400.7	400.6	400.2
150°	391.8	392.8	392.1	391.7	391.0	390.7	390.0	389.5	388.8	388.4	387.8
152.5°	381.4	382.3	381.5	381.2	380.4	379.8	379.1	378.6	377.9	377.3	376.7
155°	369.6	370.1	369.7	369.4	369.1	368.7	368.4	368.2	368.0	367.6	367.3
157.5°	362.3	362.4	362.3	362.1	361.9	361.7	361.6	361.5	361.4	361.3	361.3
160°	357.7	358.1	357.8	357.6	357.4	357.2	357.1	357.0	356.9	356.9	356.8
162.5°	353.7	353.7	353.4	353.2	353.1	353.0	352.8	352.8	352.8	352.7	352.7
165°	352.7	352.9	352.5	352.2	351.9	351.5	351.2	350.9	350.8	350.6	350.3
167.5°	350.8	350.6	350.6	350.7	350.7	350.8	350.8	351.1	351.1	351.3	351.4
170°	351.6	351.6	351.4	351.2	351.0	350.9	350.9	350.7	350.6	350.5	350.4
172.5°	353.9	353.9	353.5	353.1	352.8	352.6	352.2	351.9	351.6	351.3	350.9
175°	354.6	354.4	354.2	354.0	353.8	353.5	353.4	353.1	352.9	352.7	352.6
177.5°	355.8	355.7	355.6	355.6	355.6	355.5	355.5	355.5	355.5	355.5	355.4
180°	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5
2.5°	15285.4	15285.2	15283.7	15284.4	15284.7	15285.8	15287.1	15288.5	15288.8	15289.8	15290.0
5°	15399.8	15362.0	15334.1	15303.2	15280.1	15259.3	15245.4	15234.4	15230.1	15231.2	15233.8
7.5°	15710.0	15631.9	15567.5	15494.2	15433.3	15368.6	15315.0	15264.1	15226.9	15199.2	15183.8
10°	16050.4	15955.3	15864.3	15758.4	15657.8	15550.6	15453.4	15355.6	15273.9	15203.2	15151.1
12.5°	16201.4	16134.2	16055.7	15955.6	15848.1	15724.2	15599.3	15465.2	15340.7	15224.9	15131.6
15°	16041.5	16041.6	16013.0	15965.0	15890.2	15791.3	15672.3	15532.5	15385.5	15235.4	15098.4
17.5°	15533.8	15629.6	15682.8	15716.6	15706.2	15669.8	15594.0	15486.7	15349.7	15189.9	15022.6
20°	14661.9	14887.8	15049.0	15193.9	15275.0	15328.9	15323.6	15279.9	15182.3	15046.4	14872.2
22.5°	13440.6	13819.8	14119.0	14398.1	14593.8	14753.0	14828.6	14860.8	14816.6	14721.8	14558.3
25°	11957.2	12472.8	12912.8	13339.8	13660.1	13935.4	14100.9	14217.4	14226.7	14177.2	14031.3
27.5°	10308.8	10917.4	11474.3	12041.8	12492.3	12888.1	13147.7	13337.8	13398.1	13390.2	13257.6
30°	8662.6	9301.5	9915.3	10577.1	11134.5	11640.1	11983.1	12240.2	12339.2	12358.2	12230.7
32.5°	7107.9	7737.9	8350.1	9041.9	9655.3	10234.7	10640.0	10945.3	11060.5	11087.6	10947.8
35°	5696.8	6278.1	6859.9	7530.4	8140.3	8740.3	9167.3	9487.0	9594.5	9612.6	9450.8
37.5°	4473.2	4968.5	5475.4	6077.0	6637.1	7200.6	7606.4	7906.8	7985.1	7980.3	7797.1
40°	3443.0	3828.1	4235.3	4730.6	5196.3	5672.7	6015.2	6263.6	6304.8	6274.2	6081.8
42.5°	2589.0	2867.0	3162.3	3532.0	3877.5	4234.0	4483.3	4667.7	4673.6	4625.4	4452.6
45°	1928.8	2200.1	2323.9	2547.5	2770.0	3007.1	3159.2	3273.1	3255.5	3213.1	3081.8
47.5°	1470.3	1574.7	1685.2	1823.9	1953.4	2222.5	2202.5	2385.5	2253.7	2343.5	2145.8
50°	1167.6	1225.9	1285.4	1359.0	1426.7	1497.1	1541.0	1573.8	1569.5	1555.5	1517.6
52.5°	993.4	1011.4	1040.7	1082.6	1120.4	1158.4	1183.4	1203.8	1204.2	1198.5	1179.3
55°	830.2	853.1	874.2	901.6	948.1	955.3	991.1	983.9	986.7	976.7	986.9
57.5°	732.0	745.3	757.2	773.5	786.9	802.7	811.9	820.8	819.9	818.0	808.3
60°	662.4	669.7	676.3	685.8	693.2	702.1	706.4	710.9	709.4	706.1	697.4
62.5°	608.7	613.4	617.1	623.3	627.7	633.3	635.5	637.4	635.5	632.3	624.6
65°	555.8	558.8	561.1	565.8	569.0	573.6	575.6	577.3	575.6	573.1	567.3
67.5°	508.1	508.4	508.1	510.0	511.0	513.8	514.7	515.9	513.9	511.8	506.8
70°	471.8	471.0	470.2	470.9	471.0	472.5	472.7	472.5	470.0	466.4	461.0
72.5°	443.5	443.1	442.4	443.0	443.0	444.3	443.9	443.3	440.3	436.7	431.4
75°	407.1	406.9	405.5	405.5	404.4	404.8	403.4	402.5	399.1	396.2	391.3
77.5°	364.6	363.9	361.9	361.1	359.0	358.1	355.3	353.9	350.5	348.1	344.0
80°	317.0	316.3	313.7	312.3	308.9	306.7	302.6	300.3	296.4	294.1	290.1
82.5°	262.0	262.3	259.8	258.0	253.1	249.4	243.9	241.0	236.6	234.4	230.3
85°	186.4	183.6	185.1	185.0	181.9	178.7	174.2	171.1	167.5	165.3	162.4
87.5°	102.2	102.9	102.1	101.5	99.3	97.6	94.2	92.4	89.7	88.4	86.2
90°	79.4	76.5	71.2	68.3	63.1	59.3	53.6	50.2	44.8	43.3	40.3
92.5°	86.1	81.2	76.3	71.3	66.5	61.6	56.6	51.7	46.7	45.0	43.4
95°	108.8	101.7	94.6	87.5	80.4	73.2	66.2	59.0	52.0	50.5	49.1
97.5°	122.7	114.3	105.9	97.4	89.1	80.7	72.3	64.0	55.6	54.7	53.7
100°	218.7	199.5	180.2	160.9	141.6	122.3	102.9	83.6	64.3	63.2	62.1
102.5°	502.2	455.2	408.5	361.6	314.7	267.8	221.1	174.1	127.3	120.5	113.8
105°	894.3	823.2	752.4	681.5	610.5	539.6	468.7	397.6	326.8	304.0	281.1
107.5°	1176.7	1109.9	1043.3	976.6	909.9	843.3	776.5	709.8	643.0	602.9	562.9
110°	1304.4	1251.5	1198.6	1145.6	1092.7	1039.6	986.7	933.6	880.7	846.0	811.6



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	1288.2	1249.4	1210.6	1171.6	1132.9	1093.9	1055.0	1016.1	977.2	956.1	935.0
115°	1163.4	1140.1	1116.5	1093.1	1069.6	1046.0	1022.6	999.0	975.4	964.3	953.0
117.5°	1015.2	1003.1	991.0	978.8	966.7	954.5	942.4	930.3	918.0	914.1	910.0
120°	863.9	860.2	856.2	852.3	848.5	844.6	840.7	836.8	832.8	833.1	833.4
122.5°	737.6	738.7	739.8	740.8	742.1	743.0	744.3	745.2	746.3	748.9	751.7
125°	647.9	651.0	654.3	657.4	660.5	663.6	666.9	669.8	673.0	675.7	678.5
127.5°	583.1	586.6	590.2	593.7	597.4	600.9	604.5	608.0	611.4	613.9	616.4
130°	537.3	540.3	543.4	546.3	549.5	552.4	555.4	558.5	561.4	563.3	565.0
132.5°	503.4	506.0	508.8	511.4	514.1	516.7	519.5	522.0	524.9	526.0	527.4
135°	480.7	482.6	484.6	486.5	488.6	490.4	492.4	494.3	496.3	497.1	497.8
137.5°	460.2	461.7	463.3	464.7	466.4	467.8	469.5	471.1	472.8	472.9	473.2
140°	441.8	443.4	445.1	446.8	448.5	450.2	452.0	453.8	455.6	455.7	456.1
142.5°	427.6	428.9	430.1	431.4	432.7	434.1	435.5	436.9	438.3	438.5	438.7
145°	412.5	414.0	415.8	417.3	418.9	420.5	422.4	424.1	425.9	425.9	426.0
147.5°	401.5	402.9	404.3	405.7	407.1	408.5	410.1	411.6	413.3	413.2	413.2
150°	389.3	390.8	392.3	393.8	395.4	397.0	398.7	400.5	402.2	402.5	402.8
152.5°	378.3	380.0	381.6	383.4	385.2	387.0	388.9	390.8	392.6	392.8	393.2
155°	369.0	370.6	372.3	374.1	375.8	377.6	379.4	381.2	383.0	383.5	383.9
157.5°	362.7	364.1	365.7	367.3	368.8	370.4	372.1	373.7	375.3	375.7	376.0
160°	358.2	359.5	360.9	362.2	363.6	365.0	366.4	367.9	369.2	369.6	369.9
162.5°	354.0	355.4	356.8	358.0	359.4	360.8	362.3	363.6	365.0	365.3	365.6
165°	351.3	352.3	353.2	354.2	355.2	356.1	357.1	358.1	359.1	359.5	360.0
167.5°	352.3	352.8	353.6	354.4	355.2	355.9	356.7	357.4	358.3	358.7	359.1
170°	351.2	351.8	352.5	353.2	353.9	354.6	355.4	355.9	356.8	357.2	357.6
172.5°	351.4	351.8	352.3	352.7	353.1	353.6	354.1	354.6	355.1	355.7	356.1
175°	352.8	353.0	353.3	353.5	353.6	353.9	354.2	354.5	354.8	355.2	355.7
177.5°	355.6	355.8	355.9	356.1	356.3	356.5	356.7	356.9	357.2	357.8	358.3
180°	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5
2.5°	15289.6	15289.4	15288.9	15288.2	15287.5	15287.9	15288.6	15290.3	15293.4	15297.9	15303.6
5°	15235.9	15239.0	15240.8	15241.0	15239.4	15238.5	15239.9	15244.2	15252.6	15266.8	15286.1
7.5°	15179.6	15183.5	15189.4	15193.9	15194.6	15193.6	15193.9	15200.4	15216.1	15243.7	15282.6
10°	15119.5	15108.0	15114.1	15125.1	15133.9	15135.5	15136.5	15144.3	15167.2	15209.1	15271.4
12.5°	15064.0	15027.9	15020.9	15030.9	15044.1	15048.4	15047.1	15050.5	15077.3	15132.7	15219.6
15°	14991.0	14922.9	14899.7	14902.3	14918.7	14924.6	14920.3	14913.7	14939.8	15007.4	15119.9
17.5°	14872.9	14763.1	14720.4	14718.5	14737.7	14742.9	14732.3	14711.9	14737.5	14821.9	14961.5
20°	14693.2	14531.3	14450.8	14438.0	14458.9	14452.8	14431.7	14400.8	14434.5	14537.1	14703.2
22.5°	14370.4	14165.2	14027.6	13983.3	14008.2	13991.6	13960.8	13921.3	13966.2	14082.8	14267.8
25°	13842.8	13605.6	13417.4	13311.7	13331.6	13301.7	13268.3	13220.4	13273.9	13407.7	13611.3
27.5°	13067.3	12793.4	12560.1	12385.2	12391.6	12352.5	12314.0	12251.9	12318.7	12477.1	12706.8
30°	12036.1	11719.1	11435.0	11197.4	11176.0	11138.1	11098.7	11017.3	11100.9	11290.5	11558.8
32.5°	10741.1	10389.2	10060.9	9760.4	9703.7	9666.6	9631.4	9537.9	9647.3	9868.3	10176.7
35°	9226.6	8851.8	8495.8	8152.6	8058.7	8021.7	7990.9	7901.2	8037.8	8278.3	8611.4
37.5°	7564.3	7181.3	6827.9	6476.0	6343.3	6293.1	6270.7	6212.0	6369.5	6607.4	6941.8
40°	5857.7	5501.6	5184.8	4874.0	4722.6	4645.8	4634.1	4623.4	4775.8	4982.1	5285.7
42.5°	4261.3	3974.0	3729.6	3492.1	3355.0	3250.1	3250.1	3281.9	3419.0	3573.6	3807.7
45°	2947.6	2754.9	2599.2	2440.4	2482.9	2273.8	2396.6	2333.6	2401.4	2501.0	2653.2
47.5°	2026.2	1921.0	1835.5	1746.8	1682.1	1620.4	1625.8	1665.6	1729.4	1788.6	1867.8
50°	1476.7	1423.2	1379.6	1333.5	1301.4	1274.2	1275.7	1293.0	1326.5	1357.7	1399.1
52.5°	1157.1	1127.6	1103.9	1078.4	1061.5	1048.1	1048.7	1057.2	1075.3	1093.1	1116.8
55°	953.8	950.2	919.4	896.6	887.9	878.8	880.4	883.7	896.0	906.5	922.2
57.5°	799.3	785.4	776.2	764.2	758.6	752.3	753.7	754.9	763.2	770.2	781.5
60°	690.2	680.4	673.8	665.6	662.0	658.0	658.9	659.6	664.9	669.4	677.6
62.5°	617.6	608.9	603.2	596.9	594.4	591.7	592.2	592.4	595.7	599.1	605.2
65°	562.1	555.1	550.4	544.9	542.3	539.4	539.7	539.7	542.5	544.9	549.6
67.5°	503.2	498.0	495.0	490.6	488.8	486.0	485.9	485.0	486.7	487.7	490.9
70°	456.1	450.8	446.9	442.7	440.4	437.9	438.0	438.0	440.1	442.3	446.3
72.5°	426.9	421.9	418.4	414.7	412.6	410.4	410.1	409.8	411.3	412.6	415.2
75°	388.3	384.3	382.2	378.8	377.1	374.7	374.3	373.1	373.9	374.1	376.1
77.5°	341.5	337.6	336.0	332.6	331.1	328.3	328.1	326.9	327.4	327.1	328.6
80°	288.1	284.6	283.7	280.9	280.2	277.6	277.2	275.7	276.1	275.0	275.5
82.5°	228.5	225.3	224.7	222.0	222.0	219.7	219.5	217.2	217.2	215.3	212.1
85°	161.0	158.6	157.7	155.5	154.8	153.0	152.0	149.8	149.0	147.6	147.1
87.5°	84.9	83.5	82.1	81.2	79.2	75.9	75.6	73.3	73.5	71.8	71.9
90°	39.0	36.2	35.0	32.4	30.9	28.8	27.6	28.5	29.7	30.6	31.9
92.5°	41.8	40.1	38.6	36.9	35.3	33.6	32.0	33.6	35.3	36.9	38.6
95°	47.6	46.2	44.7	43.2	41.8	40.3	38.9	40.3	41.8	43.2	44.7
97.5°	52.8	51.9	51.0	50.0	49.2	48.2	47.3	48.3	49.3	50.1	51.1
100°	61.0	59.9	58.8	57.7	56.6	55.5	54.4	55.6	56.7	57.8	58.9
102.5°	107.0	100.3	93.6	86.8	80.0	73.3	66.5	73.3	80.0	86.9	93.7
105°	258.3	235.6	212.7	189.9	167.2	144.3	121.5	144.3	167.2	189.9	212.8
107.5°	522.6	482.6	442.4	402.3	362.1	321.9	281.8	322.0	362.2	402.4	442.5
110°	776.9	742.2	707.6	673.0	638.3	603.7	569.0	603.8	638.4	673.1	707.8



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	914.0	892.9	871.8	850.7	829.6	808.5	787.3	808.6	829.8	851.0	872.1
115°	942.0	930.7	919.6	908.3	897.2	885.9	874.6	886.1	897.5	908.7	920.1
117.5°	906.0	902.0	898.0	894.0	889.9	885.8	881.7	885.9	890.2	894.5	898.5
120°	833.6	833.9	834.2	834.4	834.6	834.7	834.8	834.9	834.9	834.9	834.8
122.5°	754.4	757.1	759.6	762.3	764.9	767.6	770.0	767.7	765.3	763.1	760.6
125°	681.3	684.0	686.7	689.4	692.0	694.7	697.2	695.0	692.7	690.3	687.8
127.5°	618.8	621.2	623.6	626.0	628.3	630.4	632.7	630.8	628.9	626.9	624.7
130°	566.7	568.6	570.1	571.9	573.5	575.1	576.5	575.4	574.1	572.9	571.5
132.5°	528.4	529.8	531.0	532.2	533.2	534.4	535.1	534.6	533.9	533.3	532.3
135°	498.6	499.4	499.8	500.6	501.2	501.7	502.1	502.1	501.9	501.7	501.3
137.5°	473.4	473.7	473.8	473.8	473.9	473.9	473.7	474.2	474.6	475.0	475.2
140°	456.2	456.4	456.7	456.7	456.8	456.9	456.7	457.3	457.6	458.0	458.1
142.5°	438.9	439.1	439.2	439.3	439.4	439.4	439.2	439.8	440.2	440.5	440.8
145°	425.9	425.9	425.9	425.8	425.6	425.4	425.0	425.8	426.2	426.8	427.4
147.5°	413.2	413.1	413.1	412.9	412.7	412.5	412.2	412.9	413.3	413.9	414.5
150°	403.1	403.4	403.7	403.8	403.9	404.0	404.0	404.4	404.7	404.9	405.1
152.5°	393.4	393.6	393.9	394.1	394.2	394.2	394.2	394.5	394.9	395.2	395.4
155°	384.3	384.6	384.9	385.3	385.5	385.8	386.0	386.3	386.4	386.6	386.7
157.5°	376.4	376.8	377.1	377.4	377.6	378.0	378.2	378.4	378.6	378.8	379.0
160°	370.2	370.6	370.9	371.2	371.5	371.8	371.9	372.2	372.5	372.6	372.9
162.5°	365.9	366.2	366.4	366.7	367.0	367.3	367.6	367.9	368.1	368.3	368.5
165°	360.5	361.0	361.3	361.8	362.3	362.7	363.1	363.2	363.2	363.2	363.2
167.5°	359.5	360.0	360.3	360.8	361.1	361.6	362.1	362.1	362.1	362.1	362.0
170°	358.0	358.5	358.8	359.1	359.5	359.9	360.2	360.2	360.2	360.2	360.2
172.5°	356.5	357.2	357.7	358.3	358.7	359.2	359.7	359.6	359.3	359.1	358.9
175°	355.9	356.5	357.0	357.5	357.9	358.4	358.9	358.5	358.3	358.1	357.8
177.5°	359.0	359.6	360.2	360.8	361.4	361.9	362.5	362.0	361.6	361.0	360.4
180°	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5
2.5°	15311.9	15319.5	15331.2	15341.8	15357.8	15370.4	15389.4	15403.8	15425.1	15439.1	15462.2
5°	15313.2	15343.2	15382.5	15421.0	15467.2	15509.2	15561.3	15605.7	15658.1	15700.9	15754.5
7.5°	15334.8	15392.6	15461.9	15531.7	15610.6	15684.4	15767.5	15842.8	15925.0	15994.8	16070.8
10°	15350.8	15439.9	15541.9	15644.6	15752.7	15853.2	15954.5	16042.2	16124.0	16191.4	16250.9
12.5°	15329.2	15452.0	15582.9	15709.3	15829.5	15933.4	16020.6	16088.0	16134.5	16166.1	16173.5
15°	15255.5	15403.3	15545.6	15671.6	15771.3	15848.2	15888.0	15906.6	15886.6	15853.4	15780.5
17.5°	15118.0	15273.8	15401.1	15500.4	15553.1	15574.0	15541.0	15483.7	15371.6	15247.1	15067.4
20°	14865.9	15011.0	15103.4	15157.6	15143.4	15091.3	14966.8	14815.4	14591.6	14353.1	14038.3
22.5°	14423.6	14550.5	14599.7	14603.7	14517.7	14387.1	14162.6	13903.0	13549.9	13182.8	12731.3
25°	13759.8	13870.9	13878.7	13835.0	13677.6	13466.0	13136.3	12769.0	12289.3	11800.1	11234.3
27.5°	12859.4	12966.0	12939.9	12858.4	12639.9	12356.8	11934.6	11460.2	10868.7	10291.0	9665.1
30°	11727.7	11841.6	11810.9	11706.4	11446.6	11111.9	10615.1	10064.0	9407.3	8790.2	8156.0
32.5°	10373.2	10517.3	10496.1	10396.9	10125.6	9767.6	9228.5	8644.0	7971.9	7363.9	6746.9
35°	8833.7	9008.7	9017.8	8952.8	8701.0	8347.1	7814.8	7249.0	6605.3	6031.6	5461.7
37.5°	7175.1	7377.9	7419.6	7402.1	7193.4	6881.0	6396.0	5888.4	5318.3	4815.4	4328.0
40°	5507.3	5712.6	5783.9	5805.0	5651.0	5409.0	5011.0	4601.3	4136.5	3729.1	3342.0
42.5°	3986.4	4168.4	4237.2	4280.6	4184.4	4023.1	3732.7	3435.2	3094.6	2800.7	2519.0
45°	2768.7	2897.4	2949.8	2993.3	2941.0	2850.0	2666.6	2480.5	2255.7	2063.6	1881.8
47.5°	1935.7	2006.7	2041.2	2062.4	2042.1	1994.7	1894.8	1787.1	1660.2	1548.0	1440.1
50°	1434.7	1472.6	1490.7	1502.9	1488.1	1461.7	1407.7	1349.0	1279.3	1215.8	1153.7
52.5°	1137.0	1158.7	1169.5	1176.1	1167.5	1151.4	1120.0	1085.2	1043.4	1004.1	983.5
55°	957.9	956.7	981.5	969.6	981.5	954.8	949.2	911.0	876.2	851.8	825.3
57.5°	789.9	801.2	805.9	811.3	807.8	802.9	789.6	775.9	757.6	742.2	726.0
60°	683.8	693.1	698.3	703.6	703.3	701.4	693.7	685.5	674.1	664.9	655.0
62.5°	610.7	618.7	623.9	628.9	629.4	628.6	622.8	617.1	609.3	603.6	596.7
65°	553.2	558.8	562.3	566.4	566.1	565.0	559.8	555.0	548.6	544.6	539.6
67.5°	493.0	497.2	499.9	503.7	504.5	504.7	501.8	499.5	496.4	495.3	493.6
70°	450.1	455.2	459.7	464.4	467.1	468.3	467.1	466.0	464.2	463.4	462.0
72.5°	417.7	422.1	425.5	429.8	432.4	434.1	433.1	432.5	430.9	430.7	429.7
75°	377.5	380.5	382.4	385.7	387.0	388.6	387.9	388.3	387.8	389.0	389.0
77.5°	329.1	331.3	332.2	334.6	334.8	336.8	337.2	339.6	341.2	344.9	346.8
80°	274.6	276.1	276.1	278.5	279.5	282.9	284.5	288.3	290.1	293.3	293.6
82.5°	213.3	211.7	213.3	212.2	215.4	219.1	219.7	222.9	223.7	225.7	224.1
85°	145.8	145.7	144.4	144.7	143.7	144.1	143.6	144.2	143.6	143.7	142.1
87.5°	69.9	70.5	68.9	69.5	68.0	68.6	67.4	68.4	66.9	67.1	64.8
90°	32.9	34.0	35.2	36.4	37.7	40.9	44.1	47.3	50.7	53.7	57.0
92.5°	40.1	41.9	43.5	45.2	46.8	51.8	56.7	61.7	66.6	71.5	76.4
95°	46.2	47.6	49.1	50.6	52.1	59.1	66.3	73.4	80.6	87.7	94.8
97.5°	52.1	53.0	53.9	54.9	55.8	64.2	72.5	81.0	89.4	97.7	106.2
100°	60.1	61.2	62.2	63.4	64.5	83.9	103.2	122.6	141.9	161.2	180.5
102.5°	100.4	107.1	113.9	120.8	127.6	174.5	221.5	268.3	315.0	362.0	408.9
105°	235.7	258.5	281.4	304.3	327.1	398.0	469.1	540.1	611.0	681.9	752.9
107.5°	482.8	522.9	563.2	603.3	643.4	710.2	777.1	843.8	910.6	977.3	1044.0
110°	742.5	777.2	812.0	846.6	881.3	934.3	987.5	1040.4	1093.4	1146.5	1199.5



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	893.4	914.4	935.6	956.7	977.9	1016.8	1055.9	1094.9	1133.9	1172.7	1211.6
115°	931.4	942.6	953.8	965.1	976.4	1000.1	1023.5	1047.2	1070.8	1094.2	1117.9
117.5°	902.7	906.9	911.0	915.0	919.1	931.3	943.6	955.9	968.1	980.3	992.5
120°	834.8	834.6	834.6	834.4	834.2	838.0	842.1	846.1	850.2	854.0	857.9
122.5°	758.1	755.5	753.1	750.4	748.0	746.8	745.9	744.8	743.9	742.8	741.9
125°	685.2	682.7	680.1	677.5	674.8	671.8	668.7	665.6	662.5	659.5	656.4
127.5°	622.7	620.4	618.2	615.9	613.6	610.1	606.6	603.1	599.7	596.1	592.6
130°	570.1	568.6	567.0	565.3	563.8	560.8	557.9	554.9	552.0	549.0	546.1
132.5°	531.5	530.5	529.6	528.3	527.4	524.7	522.2	519.5	516.9	514.3	511.8
135°	501.1	500.6	500.2	499.6	499.1	497.1	495.4	493.4	491.6	489.7	487.8
137.5°	475.5	475.6	475.6	475.6	475.7	474.1	472.6	471.1	469.7	468.1	466.7
140°	458.3	458.4	458.6	458.5	458.6	457.0	455.3	453.7	452.1	450.4	448.7
142.5°	441.0	441.2	441.3	441.3	441.4	440.1	438.9	437.7	436.4	435.2	433.9
145°	427.7	428.1	428.5	428.6	429.1	427.4	426.0	424.2	422.9	421.2	419.7
147.5°	414.9	415.3	415.8	416.0	416.5	415.1	413.8	412.5	411.3	409.9	408.7
150°	405.2	405.3	405.4	405.5	405.5	404.1	402.8	401.2	400.0	398.4	397.2
152.5°	395.5	395.7	395.9	396.0	396.2	394.7	393.2	391.6	390.1	388.4	387.0
155°	386.8	386.9	386.9	386.9	386.9	385.4	384.0	382.5	381.1	379.5	378.1
157.5°	379.1	379.2	379.3	379.4	379.4	378.2	376.9	375.5	374.3	373.0	371.8
160°	373.0	373.2	373.3	373.3	373.5	372.4	371.4	370.2	369.2	368.0	366.8
162.5°	368.6	368.8	368.9	368.9	369.1	368.1	367.1	365.9	364.9	363.7	362.6
165°	363.3	363.2	363.1	363.0	362.9	362.3	361.6	360.9	360.1	359.3	358.6
167.5°	362.1	362.0	361.9	361.8	361.7	361.1	360.8	360.1	359.5	359.1	358.5
170°	360.2	360.1	360.0	359.9	359.8	359.2	358.8	358.2	357.8	357.1	356.5
172.5°	358.6	358.3	358.1	357.8	357.5	357.1	356.7	356.4	356.1	355.8	355.4
175°	357.5	357.1	356.9	356.6	356.2	356.1	355.9	355.9	355.7	355.6	355.4
177.5°	360.0	359.5	359.0	358.5	358.0	357.8	357.7	357.5	357.4	357.3	357.1
180°	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5
2.5°	15476.7	15381.1	15368.5	15375.2	15391.2	15397.1	15414.2	15419.0	15436.4	15440.6	15457.3
5°	15796.0	15669.6	15675.9	15706.4	15752.4	15779.8	15825.0	15848.6	15891.8	15911.4	15950.4
7.5°	16132.7	16033.5	16064.5	16115.7	16178.6	16222.1	16276.4	16311.8	16358.6	16387.6	16425.1
10°	16298.1	16270.9	16304.9	16345.3	16381.2	16409.3	16432.3	16450.7	16462.7	16474.0	16479.0
12.5°	16172.3	16214.4	16220.1	16216.2	16192.5	16174.3	16133.5	16105.9	16056.7	16026.8	15968.2
15°	15705.8	15798.3	15747.1	15669.5	15556.1	15461.5	15327.9	15228.4	15089.2	14994.9	14855.3
17.5°	14887.3	15004.0	14870.6	14691.1	14462.9	14267.6	14024.4	13831.3	13589.6	13413.7	13188.1
20°	13734.9	13843.9	13605.9	13308.5	12955.4	12658.2	12307.8	12028.1	11702.4	11460.2	11167.9
22.5°	12300.1	12377.8	12042.4	11641.5	11191.6	10820.3	10401.3	10066.0	9694.5	9417.4	9105.7
25°	10712.8	10733.7	10331.4	9869.4	9368.0	8950.8	8503.5	8151.0	7772.0	7491.3	7185.4
27.5°	9110.6	9079.8	8645.0	8155.2	7627.7	7194.0	6757.8	6427.5	6095.5	5842.6	5579.1
30°	7598.4	7523.9	7072.4	6569.0	6056.9	5668.3	5306.1	5040.9	4776.7	4576.1	4364.6
32.5°	6211.7	6106.6	5667.1	5195.4	4764.0	4464.0	4195.4	3994.7	3781.5	3612.1	3434.5
35°	4983.4	4871.5	4482.2	4082.2	3755.7	3534.6	3323.5	3158.8	2977.8	2834.9	2680.6
37.5°	3929.3	3837.5	3511.4	3196.7	2949.8	2778.3	2605.5	2470.9	2321.3	2258.3	2093.6
40°	3033.4	2969.3	2714.3	2482.3	2296.8	2216.4	2040.8	1915.1	1803.2	1711.0	1621.7
42.5°	2366.1	2343.4	2095.3	1914.3	1783.7	1682.3	1584.5	1505.0	1427.7	1364.2	1304.1
45°	1736.4	1718.4	1608.2	1503.8	1414.8	1343.9	1277.8	1223.2	1172.6	1130.7	1092.6
47.5°	1352.1	1346.3	1282.9	1218.1	1162.1	1116.5	1073.7	1037.4	1003.8	975.8	966.7
50°	1099.7	1099.0	1061.7	1021.8	981.8	955.6	928.1	906.7	885.2	868.4	850.6
52.5°	934.4	930.4	905.2	880.5	856.9	839.6	822.0	808.4	794.1	783.7	772.7
55°	804.4	808.7	794.1	779.4	764.5	753.8	741.6	732.5	722.8	716.2	709.6
57.5°	714.1	719.7	712.2	703.8	694.7	687.7	679.2	673.0	666.4	662.3	658.5
60°	648.5	654.6	651.6	647.3	641.8	637.5	632.2	628.7	624.4	622.1	620.0
62.5°	592.7	600.4	599.3	597.4	593.8	591.5	588.5	586.9	584.2	583.1	582.2
65°	537.2	545.8	545.6	544.6	542.7	542.0	540.2	539.8	538.4	539.0	538.8
67.5°	493.4	500.9	502.6	503.8	503.7	504.2	504.0	504.8	504.8	505.9	506.5
70°	461.9	467.1	468.3	469.6	470.0	470.9	470.9	471.6	471.4	472.3	472.5
72.5°	430.0	436.9	438.1	439.1	439.1	440.1	439.6	439.4	438.1	437.8	436.8
75°	390.3	399.1	401.0	402.3	402.5	403.4	402.1	401.4	399.1	398.2	396.6
77.5°	348.9	358.0	359.3	359.8	359.1	359.2	356.7	355.1	352.2	351.0	349.5
80°	294.9	308.3	309.5	308.6	306.5	306.1	303.7	302.1	298.6	297.5	296.1
82.5°	224.4	240.2	242.4	243.4	241.7	242.1	239.8	238.8	235.6	235.1	233.0
85°	141.7	157.5	160.1	159.7	158.0	157.6	156.2	156.7	156.4	157.3	157.8
87.5°	65.1	80.4	84.1	82.9	82.7	81.6	79.2	80.1	81.5	82.5	82.6
90°	60.3	68.2	71.3	68.8	65.0	62.3	58.6	56.1	52.7	50.2	46.7
92.5°	81.4	86.3	91.2	86.9	82.5	78.1	73.7	69.2	65.0	60.4	56.1
95°	101.9	109.0	116.1	110.2	104.4	98.5	92.7	86.9	81.1	75.1	69.3
97.5°	114.6	122.9	131.2	125.4	119.5	113.5	107.7	101.8	96.0	90.2	84.3
100°	199.9	218.9	238.3	221.8	205.0	188.4	171.8	155.0	138.5	121.9	105.2
102.5°	455.6	502.4	549.2	507.2	465.1	423.1	381.2	339.1	297.1	255.0	213.0
105°	823.8	894.6	965.5	901.2	837.1	773.0	708.9	644.7	580.5	516.4	452.3
107.5°	1110.7	1177.0	1243.6	1185.7	1127.7	1069.8	1011.7	953.8	895.8	837.8	780.0
110°	1252.5	1304.9	1357.9	1318.9	1280.1	1241.2	1202.4	1163.4	1124.7	1085.9	1047.1



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	1250.5	1288.8	1327.5	1304.7	1282.1	1259.4	1236.8	1214.2	1191.7	1169.0	1146.5
115°	1141.3	1164.0	1187.4	1178.5	1169.7	1160.8	1151.9	1143.2	1134.3	1125.5	1116.8
117.5°	1004.7	1015.9	1027.8	1026.3	1024.9	1023.4	1022.1	1020.5	1019.3	1017.9	1016.5
120°	861.9	864.7	868.3	869.7	871.2	872.7	874.1	875.5	876.9	878.5	880.0
122.5°	740.7	738.6	737.1	738.5	739.9	741.2	742.5	744.0	745.4	746.8	748.3
125°	653.3	649.0	645.5	644.2	643.1	641.8	640.6	639.3	638.2	637.0	636.0
127.5°	589.1	584.3	580.4	577.2	574.0	570.6	567.4	564.1	560.9	557.5	554.4
130°	543.2	538.6	535.3	531.1	527.1	522.7	518.6	514.5	510.2	505.9	501.9
132.5°	509.1	504.9	501.9	497.9	493.9	489.9	486.0	481.9	477.8	473.9	469.9
135°	485.9	482.4	480.2	476.5	473.0	469.3	465.6	462.0	458.4	454.7	451.2
137.5°	465.1	461.8	460.0	457.2	454.4	451.6	448.7	445.8	442.9	440.0	437.2
140°	447.1	443.6	441.6	440.1	438.7	437.0	435.6	434.0	432.5	431.0	429.3
142.5°	432.7	429.4	427.9	426.9	426.1	425.2	424.5	423.5	422.7	421.6	420.7
145°	418.1	414.4	412.5	412.6	412.8	412.8	412.9	413.0	413.1	413.1	413.2
147.5°	407.3	403.7	401.8	402.2	402.5	402.8	403.3	403.5	403.9	404.2	404.5
150°	395.5	391.4	389.3	390.0	390.5	391.1	391.6	392.3	392.9	393.5	394.1
152.5°	385.3	380.4	378.0	378.6	379.3	379.9	380.6	381.3	381.9	382.6	383.3
155°	376.4	371.2	368.6	368.8	369.1	369.4	369.7	370.1	370.5	370.8	371.3
157.5°	370.2	364.9	362.5	362.5	362.6	362.8	362.9	363.0	363.2	363.4	363.7
160°	365.6	360.4	358.2	358.2	358.3	358.4	358.5	358.5	358.7	358.9	359.1
162.5°	361.3	356.2	354.1	354.0	354.0	354.0	354.2	354.2	354.4	354.4	354.7
165°	357.8	353.4	351.6	351.8	352.1	352.2	352.5	352.7	353.0	353.3	353.7
167.5°	357.8	354.0	352.6	352.5	352.3	352.1	352.1	351.9	351.9	351.8	351.8
170°	355.9	352.8	351.6	351.7	351.9	351.9	352.0	352.1	352.2	352.3	352.5
172.5°	355.0	352.7	351.8	352.2	352.6	352.7	353.1	353.4	353.8	354.1	354.5
175°	355.2	353.8	353.4	353.4	353.6	353.8	354.0	354.1	354.3	354.5	354.9
177.5°	356.9	356.4	356.1	356.1	356.1	356.1	356.1	356.1	356.1	356.2	356.2
180°	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5
2.5°	15460.4	15478.4	15477.1	15493.9	15493.1	15508.9	15505.7	15519.5	15516.3	15528.0	15521.1
5°	15967.5	16001.8	16013.2	16044.0	16050.5	16078.1	16078.7	16100.7	16098.1	16115.3	16106.2
7.5°	16447.3	16479.3	16494.5	16518.5	16530.5	16550.4	16558.2	16574.6	16578.5	16588.2	16587.9
10°	16487.7	16487.6	16495.2	16491.8	16498.5	16494.6	16502.8	16499.8	16512.0	16508.9	16518.0
12.5°	15943.0	15888.9	15869.2	15820.6	15809.9	15768.4	15771.3	15744.6	15757.5	15741.0	15769.0
15°	14772.2	14646.8	14584.8	14475.8	14441.5	14355.3	14348.3	14291.1	14306.6	14276.6	14320.4
17.5°	13042.1	12844.7	12736.3	12577.0	12513.8	12391.9	12367.4	12293.7	12305.2	12268.0	12321.0
20°	10979.3	10740.7	10604.1	10419.8	10337.7	10192.4	10153.9	10071.4	10081.7	10044.8	10104.6
22.5°	8893.0	8643.2	8488.9	8295.9	8191.1	8054.3	8013.3	7930.5	7935.3	7900.6	7958.1
25°	6975.7	6736.3	6586.5	6411.2	6320.2	6194.9	6151.8	6077.5	6081.7	6053.0	6104.6
27.5°	5396.2	5199.8	5074.5	4927.5	4846.0	4742.9	4700.9	4638.4	4638.2	4617.2	4660.4
30°	4216.9	4052.9	3940.4	3812.4	3735.8	3642.9	3602.2	3546.3	3543.9	3528.9	3563.3
32.5°	3301.8	3155.9	3053.2	2940.7	2871.8	2792.1	2753.6	2708.6	2704.6	2691.1	2719.3
35°	2566.7	2443.8	2355.6	2260.8	2267.7	2150.1	2169.6	2078.2	2053.5	2048.0	2069.0
37.5°	1983.7	1888.6	1817.0	1745.9	1697.8	1648.1	1621.3	1597.3	1594.5	1592.2	1606.9
40°	1552.7	1486.1	1434.1	1385.3	1352.2	1321.9	1305.1	1291.9	1288.7	1287.0	1295.9
42.5°	1256.7	1211.7	1178.2	1148.4	1128.3	1111.9	1102.7	1095.3	1092.9	1092.9	1098.1
45°	1061.7	1034.5	1012.9	994.3	981.5	987.2	970.6	979.2	967.8	979.6	971.8
47.5°	935.0	911.8	898.5	885.4	877.5	871.3	871.5	871.6	874.1	874.5	877.0
50°	837.3	823.8	814.5	806.1	802.1	798.8	799.9	800.8	803.1	803.3	805.2
52.5°	764.8	756.0	750.4	745.3	743.4	741.6	742.3	742.0	743.1	742.5	744.1
55°	706.0	701.8	700.1	698.1	698.4	697.8	698.2	696.4	695.2	693.8	695.1
57.5°	657.6	657.0	658.3	659.1	661.3	662.1	662.5	660.4	658.4	656.5	657.6
60°	620.4	621.3	624.2	626.7	629.9	631.3	632.2	630.9	629.5	627.9	628.9
62.5°	583.6	585.1	588.6	591.3	595.2	597.1	599.3	599.4	600.0	599.4	600.1
65°	541.0	542.8	546.0	548.2	551.8	553.6	555.8	556.2	557.4	557.1	558.2
67.5°	508.6	510.2	512.8	515.0	518.2	520.0	521.9	522.0	522.5	522.4	523.5
70°	474.0	474.8	477.2	479.0	482.2	484.0	486.4	487.0	488.4	488.7	489.8
72.5°	437.2	436.9	438.3	439.0	441.5	442.9	445.8	447.5	449.8	450.5	451.3
75°	397.1	396.8	398.4	399.1	401.1	402.7	405.9	408.0	411.7	413.3	412.8
77.5°	350.6	351.4	354.6	356.3	359.1	361.0	365.2	368.6	375.2	378.2	375.2
80°	298.6	299.5	302.8	304.5	308.0	310.3	315.0	318.9	325.0	326.4	324.6
82.5°	234.8	235.0	237.9	239.2	243.9	247.3	253.3	256.4	260.1	259.6	259.1
85°	160.1	162.2	166.0	169.7	175.3	180.8	186.5	191.1	187.8	193.0	187.1
87.5°	85.5	85.3	90.4	89.6	97.5	102.1	107.0	109.4	112.0	111.4	111.5
90°	44.6	42.4	41.4	39.1	38.5	36.1	35.9	33.5	33.6	31.0	34.7
92.5°	51.7	49.5	46.9	44.7	42.2	39.9	37.4	35.1	32.7	30.3	32.7
95°	63.5	61.3	59.1	56.8	54.7	52.5	50.3	48.1	46.0	43.7	46.4
97.5°	78.4	77.2	75.9	74.7	73.4	72.0	70.8	69.5	68.2	66.9	68.7
100°	88.6	88.6	88.6	88.6	88.5	88.5	88.5	88.5	88.5	88.5	90.0
102.5°	170.9	166.8	162.6	158.3	154.2	150.0	145.8	141.6	137.4	133.2	139.4
105°	388.2	371.8	355.3	338.9	322.4	306.0	289.5	273.1	256.7	240.3	257.2
107.5°	722.1	692.0	662.1	632.2	602.1	572.2	542.2	512.3	482.4	452.4	479.3
110°	1008.3	976.4	944.7	912.9	881.1	849.3	817.6	785.8	754.1	722.3	747.9



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	1123.9	1103.2	1082.7	1062.3	1041.8	1021.3	1000.8	980.5	960.0	939.6	952.0
115°	1108.1	1098.3	1088.5	1078.8	1069.1	1059.3	1049.5	1039.9	1030.2	1020.5	1021.3
117.5°	1015.2	1012.0	1008.7	1005.5	1002.3	999.2	996.0	992.9	989.7	986.7	979.7
120°	881.7	882.6	883.7	884.9	886.0	887.3	888.4	889.6	890.9	892.1	882.8
122.5°	749.7	752.2	754.8	757.3	759.9	762.6	765.1	767.8	770.7	773.4	764.1
125°	634.7	637.1	639.7	642.2	644.6	647.3	649.9	652.7	655.4	658.2	650.3
127.5°	551.2	552.2	553.1	554.1	555.2	556.3	557.4	558.8	560.1	561.3	556.4
130°	497.7	496.9	496.2	495.6	494.9	494.4	493.8	493.4	493.1	492.7	490.4
132.5°	465.8	464.0	462.1	460.4	458.6	457.0	455.3	453.9	452.3	451.0	450.2
135°	447.5	444.9	442.3	439.7	437.3	434.9	432.5	430.3	428.2	426.0	426.3
137.5°	434.3	431.8	429.2	426.6	424.1	421.9	419.4	417.1	415.0	412.8	413.5
140°	427.9	425.2	422.7	420.1	417.8	415.4	413.2	410.9	408.6	406.6	407.0
142.5°	419.7	417.5	415.1	412.9	410.5	408.4	406.3	404.3	402.2	400.4	400.8
145°	413.2	411.5	409.8	408.0	406.5	404.8	403.2	401.7	400.3	399.0	399.3
147.5°	404.9	403.7	402.3	401.0	399.8	398.7	397.5	396.4	395.3	394.4	394.4
150°	394.6	393.9	393.0	392.2	391.3	390.6	389.9	389.1	388.4	387.8	387.7
152.5°	384.0	383.2	382.4	381.6	380.9	380.2	379.5	378.8	378.2	377.6	377.5
155°	371.7	371.3	370.9	370.6	370.2	370.0	369.6	369.5	369.2	368.9	369.0
157.5°	363.9	363.8	363.6	363.6	363.5	363.5	363.3	363.4	363.2	363.3	363.4
160°	359.4	359.1	358.9	358.7	358.5	358.2	357.9	357.8	357.6	357.4	357.7
162.5°	354.9	355.1	355.1	355.2	355.4	355.5	355.7	355.9	356.0	356.2	356.4
165°	354.1	353.9	353.8	353.6	353.6	353.6	353.5	353.6	353.5	353.5	353.9
167.5°	351.7	352.0	352.1	352.4	352.6	352.7	353.0	353.4	353.7	354.1	354.4
170°	352.6	352.6	352.6	352.6	352.6	352.7	352.7	352.7	352.8	352.9	353.2
172.5°	354.9	354.9	354.8	354.9	354.8	354.9	354.9	354.9	354.9	355.0	355.2
175°	354.9	355.3	355.5	355.7	355.9	355.9	356.1	356.3	356.5	356.7	356.7
177.5°	356.2	356.2	356.2	356.2	356.2	356.3	356.3	356.3	356.3	356.2	356.4
180°	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5
2.5°	15532.5	15524.8	15532.7	15524.7	15532.7	15523.0	15529.6	15519.2	15521.8	15510.9	15513.7
5°	16119.8	16107.4	16114.0	16097.9	16099.7	16078.1	16077.8	16052.7	16046.1	16017.6	16005.1
7.5°	16594.8	16590.7	16593.0	16582.6	16581.5	16566.7	16559.8	16539.1	16526.1	16499.8	16482.0
10°	16519.6	16531.7	16534.8	16547.2	16549.7	16562.0	16564.5	16576.7	16579.2	16588.4	16588.5
12.5°	15767.7	15808.8	15818.7	15869.4	15890.8	15948.9	15980.0	16044.0	16082.1	16145.9	16185.2
15°	14319.2	14390.3	14418.6	14517.8	14572.7	14688.5	14761.1	14894.0	14987.9	15129.1	15229.7
17.5°	12325.6	12425.0	12469.8	12604.3	12692.0	12862.9	12986.0	13188.7	13343.8	13569.1	13747.7
20°	10114.9	10225.3	10286.2	10439.6	10543.2	10742.7	10896.5	11145.6	11353.2	11638.6	11882.7
22.5°	7976.1	8081.2	8148.9	8304.9	8421.4	8629.6	8801.4	9064.4	9297.1	9618.7	9911.3
25°	6124.1	6220.5	6281.6	6422.8	6532.2	6723.5	6887.6	7140.4	7368.1	7690.7	7990.8
27.5°	4681.8	4762.5	4821.4	4941.8	5038.3	5200.6	5341.5	5550.5	5746.6	6025.8	6292.9
30°	3584.3	3655.9	3713.2	3818.0	3907.5	4048.2	4172.1	4347.6	4510.0	4732.0	4944.6
32.5°	2739.1	2800.7	2851.7	2943.5	3024.6	3151.3	3263.0	3416.7	3556.2	3744.5	3919.4
35°	2088.4	2209.6	2200.9	2327.6	2347.9	2438.8	2538.4	2673.0	2796.4	2956.5	3105.3
37.5°	1620.9	1655.0	1691.5	1747.4	1806.2	1888.9	1973.1	2137.4	2197.7	2318.7	2442.0
40°	1307.1	1330.1	1354.3	1392.1	1433.2	1491.5	1552.7	1631.2	1711.5	1809.7	1909.9
42.5°	1105.1	1118.1	1133.4	1155.7	1181.0	1217.9	1259.0	1312.1	1368.0	1437.1	1507.6
45°	987.4	981.2	985.7	997.6	1012.9	1035.4	1061.2	1094.1	1130.6	1175.3	1222.9
47.5°	877.5	880.0	881.4	887.9	896.0	911.2	926.9	949.2	992.3	1005.5	1031.5
50°	805.1	806.2	805.9	809.1	813.3	823.1	833.3	848.4	863.4	883.5	902.6
52.5°	744.3	746.0	745.7	747.9	750.1	756.3	762.7	773.5	783.4	796.1	807.0
55°	696.3	698.6	699.5	701.3	702.4	705.7	708.2	713.3	717.5	724.8	731.4
57.5°	659.3	662.5	664.1	664.7	663.4	663.2	662.3	663.4	664.3	668.2	671.8
60°	630.4	632.9	633.3	632.9	630.5	628.8	626.1	625.2	624.7	626.7	628.7
62.5°	599.9	600.9	600.2	599.4	596.7	595.1	592.2	591.2	590.2	591.6	592.6
65°	557.8	558.6	557.8	557.4	554.9	553.7	551.2	550.5	549.1	549.4	549.2
67.5°	523.7	524.5	523.9	523.2	521.6	520.7	518.9	517.8	516.1	515.5	514.4
70°	489.7	490.2	489.3	488.7	486.7	486.0	484.3	484.0	482.7	482.4	481.1
72.5°	450.5	450.5	449.1	448.7	447.3	447.3	446.6	447.2	447.2	447.9	447.6
75°	410.3	409.8	408.1	407.8	406.8	407.2	406.5	407.4	407.6	409.1	409.3
77.5°	370.2	368.2	364.9	363.3	361.2	360.9	359.6	360.5	360.2	362.0	362.6
80°	319.5	317.0	312.8	310.9	308.2	307.9	306.7	307.9	307.3	309.3	310.7
82.5°	255.1	252.9	248.6	247.0	244.1	244.3	243.1	244.3	244.2	247.1	248.8
85°	188.7	187.2	182.8	178.9	174.5	171.9	169.4	169.0	168.2	169.4	170.5
87.5°	109.0	107.6	104.1	101.9	94.2	94.5	91.5	91.3	90.7	90.0	91.5
90°	35.5	38.8	39.7	42.8	43.8	47.2	48.6	51.9	53.1	56.8	58.5
92.5°	35.1	37.4	39.9	42.2	44.6	46.9	49.4	51.7	56.8	61.9	67.0
95°	49.2	52.0	54.7	57.4	60.1	62.9	65.6	68.4	75.8	83.3	90.8
97.5°	70.7	72.3	74.2	76.0	77.9	79.6	81.4	83.3	91.4	99.5	107.5
100°	91.4	92.9	94.3	95.9	97.3	98.8	100.3	101.7	117.3	132.8	148.4
102.5°	145.6	151.8	158.0	164.3	170.5	176.7	182.9	189.1	224.8	260.3	295.9
105°	274.2	291.2	308.1	325.2	342.2	359.1	376.2	393.2	450.1	507.1	564.1
107.5°	506.1	532.9	559.8	586.7	613.6	640.3	667.2	694.2	749.6	805.4	860.8
110°	773.4	799.0	824.5	850.2	875.7	901.3	926.9	952.6	985.9	1019.2	1052.5



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	964.4	976.8	989.3	1001.7	1014.2	1026.7	1039.2	1051.7	1068.3	1084.9	1101.5
115°	1022.1	1022.9	1023.6	1024.4	1025.2	1026.1	1026.9	1027.9	1033.0	1038.2	1043.2
117.5°	972.9	965.9	959.1	952.3	945.5	938.7	932.0	925.3	924.0	922.8	921.7
120°	873.7	864.5	855.3	846.0	837.0	827.8	818.7	809.7	805.0	800.2	795.5
122.5°	754.9	745.7	736.5	727.3	718.3	709.2	700.3	691.3	687.9	684.5	681.1
125°	642.6	634.9	627.2	619.6	612.1	604.6	597.1	589.6	589.2	588.7	588.4
127.5°	551.6	546.9	542.1	537.6	533.0	528.4	523.9	519.3	521.0	522.7	524.3
130°	488.2	486.2	484.0	481.9	480.1	478.1	476.1	474.2	477.4	480.4	483.6
132.5°	449.8	449.3	448.9	448.5	448.3	448.0	447.9	447.5	451.2	454.8	458.4
135°	426.7	427.1	427.7	428.2	428.9	429.4	430.2	430.9	434.4	437.8	441.3
137.5°	414.2	415.1	416.0	416.8	417.9	418.9	419.9	421.0	423.7	426.3	429.1
140°	407.7	408.1	408.9	409.7	410.4	411.1	412.1	412.9	415.1	417.1	419.3
142.5°	401.5	401.9	402.6	403.4	404.1	404.8	405.6	406.4	407.8	409.4	411.0
145°	399.7	400.1	400.6	400.9	401.4	402.0	402.6	403.1	404.0	404.8	405.9
147.5°	394.6	394.8	395.1	395.4	395.8	396.1	396.3	396.6	397.2	397.6	398.2
150°	387.7	387.7	387.8	387.8	387.9	388.0	388.1	388.2	388.7	389.1	389.6
152.5°	377.6	377.5	377.5	377.6	377.7	377.7	377.7	377.8	378.2	378.6	379.1
155°	369.2	369.4	369.6	369.8	370.1	370.2	370.5	370.7	371.0	371.2	371.5
157.5°	363.6	363.7	364.0	364.2	364.4	364.6	364.9	365.0	365.3	365.4	365.6
160°	358.1	358.6	358.9	359.2	359.6	360.0	360.4	360.9	361.1	361.3	361.5
162.5°	356.6	356.8	357.1	357.3	357.5	357.7	357.9	358.1	358.6	358.9	359.3
165°	354.3	354.7	355.2	355.4	355.9	356.3	356.6	357.1	357.2	357.5	357.7
167.5°	354.9	355.2	355.7	355.9	356.3	356.7	357.1	357.5	357.7	357.8	358.1
170°	353.6	354.0	354.3	354.6	355.0	355.3	355.7	356.0	356.4	356.7	357.1
172.5°	355.5	355.8	356.0	356.2	356.5	356.9	357.2	357.5	357.9	358.2	358.5
175°	356.7	356.7	356.8	356.8	356.9	356.9	357.0	357.1	357.1	357.2	357.2
177.5°	356.6	356.8	357.0	357.1	357.3	357.5	357.7	357.9	357.9	357.9	357.9
180°	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5
2.5°	15502.9	15503.5	15491.0	15490.4	15478.6	15477.2	15465.7	15462.2	15453.0	15449.6	15440.2
5°	15973.2	15958.0	15922.8	15902.1	15867.4	15844.3	15806.7	15782.1	15745.8	15718.3	15681.8
7.5°	16448.9	16425.3	16385.7	16353.7	16305.5	16266.9	16210.5	16164.2	16103.1	16050.1	15985.8
10°	16588.5	16584.8	16574.7	16560.0	16537.6	16512.3	16473.9	16433.8	16380.3	16322.0	16250.6
12.5°	16245.1	16282.3	16332.8	16362.7	16399.2	16415.2	16430.1	16426.3	16416.5	16387.1	16345.8
15°	15375.6	15479.7	15617.7	15724.5	15847.5	15936.9	16035.6	16097.2	16158.4	16186.7	16204.1
17.5°	13992.3	14189.5	14436.8	14641.8	14878.2	15068.2	15276.4	15433.2	15594.3	15709.8	15814.2
20°	12215.4	12501.1	12851.0	13160.0	13519.2	13831.4	14173.6	14454.5	14744.2	14970.7	15185.1
22.5°	10288.2	10627.5	11050.4	11442.1	11905.3	12321.5	12791.2	13200.0	13626.8	13983.4	14328.2
25°	8392.9	8765.2	9227.5	9664.6	10189.2	10673.4	11230.3	11739.9	12291.5	12770.4	13243.6
27.5°	6662.4	7027.8	7499.8	7965.1	8519.9	9035.8	9632.6	10193.9	10822.0	11401.2	11993.7
30°	5240.0	5549.9	5973.2	6423.8	6971.0	7496.0	8099.2	8676.5	9330.0	9962.5	10629.8
32.5°	4151.5	4387.6	4720.4	5101.5	5606.2	6106.0	6680.5	7237.7	7881.3	8520.1	9214.2
35°	3297.1	3481.2	3735.0	4032.3	4459.8	4890.6	5398.7	5905.5	6505.9	7112.1	7786.7
37.5°	2599.9	2749.4	2948.0	3171.4	3514.3	3867.9	4284.5	4704.6	5226.3	5763.6	6375.2
40°	2030.3	2151.2	2306.0	2472.5	2731.4	3003.9	3326.1	3651.9	4071.0	4510.2	5016.2
42.5°	1594.9	1684.1	1793.4	1915.2	2156.7	2301.4	2519.8	2755.6	3063.6	3382.4	3762.9
45°	1280.9	1341.8	1417.5	1499.1	1611.3	1734.0	1883.6	2040.6	2333.2	2476.8	2708.1
47.5°	1069.7	1110.5	1158.7	1210.2	1276.3	1347.7	1436.4	1527.2	1644.5	1766.1	1908.7
50°	927.4	968.9	985.5	1012.2	1050.4	1091.2	1141.2	1191.3	1254.2	1318.0	1391.4
52.5°	821.9	835.3	853.4	870.3	894.0	940.4	955.5	981.5	1016.8	1051.4	1090.0
55°	741.2	750.0	761.7	771.9	786.3	800.0	819.8	837.2	860.7	881.5	907.1
57.5°	678.4	684.1	692.2	698.9	708.2	715.9	727.5	736.9	750.5	762.2	777.7
60°	632.9	636.6	642.1	646.4	652.4	656.3	662.2	666.5	673.7	679.7	688.3
62.5°	595.6	597.6	601.1	603.7	607.5	609.5	612.5	614.4	618.4	621.4	626.3
65°	550.9	551.3	553.8	554.8	557.8	558.9	561.4	562.3	565.5	567.7	572.0
67.5°	514.3	513.3	513.3	512.4	512.8	512.1	512.3	511.4	512.6	513.3	516.6
70°	480.8	479.5	479.0	477.4	477.0	475.4	474.9	473.6	473.4	472.9	474.0
72.5°	448.3	447.9	448.0	446.9	446.8	445.7	445.8	445.2	445.8	446.2	447.7
75°	410.8	410.9	411.7	410.7	411.0	410.1	410.4	409.6	410.1	409.9	411.3
77.5°	365.3	366.3	368.3	367.9	368.6	367.5	368.0	366.8	367.1	366.3	366.9
80°	314.0	316.2	318.9	318.8	319.9	319.2	320.2	319.1	319.5	318.1	317.8
82.5°	253.1	255.0	257.8	257.9	260.4	260.9	263.6	263.5	265.3	264.2	263.4
85°	173.0	174.3	176.9	178.2	180.7	182.3	185.0	186.1	184.1	187.7	184.9
87.5°	90.4	93.7	91.8	96.2	95.2	99.6	98.6	102.8	101.9	105.5	105.0
90°	62.7	64.7	69.0	71.1	76.1	78.4	78.4	75.5	75.3	72.5	72.3
92.5°	72.0	77.3	82.4	87.5	92.6	97.8	93.0	88.2	83.5	78.8	74.0
95°	98.2	105.8	113.3	120.7	128.2	135.6	127.6	119.7	111.7	103.7	95.6
97.5°	115.6	123.5	131.6	139.6	147.7	155.7	146.2	136.7	127.2	117.8	108.4
100°	163.9	179.4	194.9	210.4	226.0	241.5	223.9	206.2	188.5	170.8	153.1
102.5°	331.6	367.2	402.9	438.5	474.0	509.7	472.1	434.6	397.1	359.5	321.9
105°	621.1	678.2	735.2	792.2	849.2	906.3	845.4	784.4	723.6	662.7	601.7
107.5°	916.4	972.0	1027.7	1083.2	1138.8	1194.5	1132.7	1070.9	1009.2	947.3	885.6
110°	1086.0	1119.2	1152.7	1186.0	1219.4	1252.8	1207.7	1162.6	1117.4	1072.2	1027.1



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	1118.1	1134.7	1151.3	1168.0	1184.7	1201.4	1169.0	1136.8	1104.4	1072.1	1039.6
115°	1048.5	1053.6	1058.8	1064.0	1069.2	1074.3	1052.5	1030.6	1008.8	987.0	965.0
117.5°	920.6	919.5	918.2	917.3	916.0	914.9	902.6	890.3	877.9	865.5	853.3
120°	790.7	786.1	781.3	776.6	771.9	767.1	761.8	756.4	751.1	745.7	740.2
122.5°	677.7	674.4	670.9	667.6	664.0	660.6	658.5	656.2	654.0	651.7	649.5
125°	587.9	587.4	586.9	586.5	585.9	585.6	584.3	583.0	581.7	580.4	579.2
127.5°	525.8	527.6	529.1	530.7	532.2	533.8	533.3	532.7	532.2	531.6	531.2
130°	486.6	489.9	492.9	495.8	498.8	501.9	501.0	500.1	499.4	498.5	497.5
132.5°	462.1	465.7	469.3	473.0	476.5	480.0	479.0	478.0	476.9	475.9	474.8
135°	444.7	448.2	451.5	454.9	458.2	461.5	460.3	459.1	457.9	456.7	455.4
137.5°	431.8	434.4	437.0	439.7	442.2	444.9	443.6	442.4	441.1	439.9	438.7
140°	421.3	423.3	425.3	427.4	429.3	431.4	429.9	428.5	427.1	425.7	424.1
142.5°	412.4	413.9	415.3	416.8	418.3	419.7	417.7	416.0	414.1	412.2	410.3
145°	406.8	407.6	408.5	409.5	410.1	411.0	409.0	406.9	404.7	402.7	400.6
147.5°	398.7	399.1	399.5	400.1	400.4	400.8	398.8	396.9	394.9	392.9	390.9
150°	390.0	390.5	390.8	391.2	391.6	392.0	390.0	387.9	385.9	383.9	381.8
152.5°	379.5	379.9	380.2	380.6	381.0	381.4	379.3	377.7	375.6	373.7	371.8
155°	371.6	371.8	371.9	372.2	372.2	372.4	370.8	369.3	367.7	366.1	364.5
157.5°	365.8	366.0	366.2	366.3	366.5	366.6	365.4	364.3	362.9	361.8	360.5
160°	361.7	361.8	362.0	362.1	362.3	362.3	361.3	360.4	359.3	358.3	357.2
162.5°	359.7	360.0	360.3	360.6	361.0	361.3	360.1	359.0	357.8	356.5	355.2
165°	357.8	358.0	358.2	358.4	358.4	358.6	357.7	356.9	356.0	355.2	354.3
167.5°	358.2	358.4	358.5	358.7	358.8	358.9	358.0	357.2	356.3	355.5	354.6
170°	357.4	357.6	358.0	358.3	358.6	358.8	358.1	357.5	356.7	356.1	355.4
172.5°	358.8	359.0	359.1	359.4	359.6	360.0	359.2	358.6	357.9	357.2	356.4
175°	357.2	357.3	357.4	357.4	357.4	357.5	356.9	356.4	355.9	355.3	354.8
177.5°	357.9	357.9	357.9	357.9	357.9	357.9	357.5	357.1	356.8	356.4	355.9
180°	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5	15340.5
2.5°	15436.8	15430.1	15425.9	15420.4	15417.0	15412.7	15409.6	15406.9	15404.7	15402.7	15401.3
5°	15653.9	15619.4	15592.7	15563.7	15539.8	15516.1	15497.7	15482.6	15472.1	15464.3	15459.6
7.5°	15930.3	15867.2	15810.9	15751.9	15698.8	15646.7	15601.8	15563.1	15534.0	15515.2	15503.7
10°	16177.1	16092.6	16008.9	15920.9	15837.5	15756.5	15681.8	15616.0	15564.1	15529.4	15509.3
12.5°	16287.8	16215.7	16130.3	16034.7	15932.4	15829.0	15728.1	15637.2	15560.9	15509.6	15480.0
15°	16190.3	16160.8	16102.8	16028.6	15931.5	15824.6	15706.1	15594.8	15492.4	15426.0	15387.5
17.5°	15873.4	15914.6	15910.2	15881.8	15812.1	15722.0	15601.3	15476.3	15348.2	15259.4	15210.9
20°	15338.4	15468.2	15534.0	15567.8	15540.4	15482.0	15372.7	15245.8	15096.5	14980.6	14909.9
22.5°	14586.8	14815.9	14958.6	15063.1	15085.3	15065.3	14968.8	14848.2	14681.7	14542.5	14438.0
25°	13619.1	13954.8	14180.3	14357.2	14425.9	14443.7	14361.5	14241.5	14056.0	13893.8	13750.3
27.5°	12479.4	12915.4	13216.7	13454.4	13561.6	13608.1	13532.5	13410.0	13190.6	12996.9	12809.6
30°	11196.3	11713.6	12076.3	12361.2	12492.0	12553.5	12473.2	12336.5	12081.2	11848.0	11612.0
32.5°	9822.9	10389.1	10784.2	11093.7	11223.3	11281.0	11176.0	11022.5	10727.4	10452.8	10177.5
35°	8385.0	8956.5	9355.0	9656.3	9764.8	9799.7	9665.4	9487.9	9160.9	8859.5	8559.3
37.5°	6917.9	7449.5	7811.7	8082.1	8149.3	8155.3	7993.5	7797.5	7453.8	7156.6	6857.7
40°	5463.3	5911.7	6204.1	6420.5	6443.9	6423.1	6247.2	6049.9	5728.3	5462.1	5199.8
42.5°	4093.3	4431.7	4640.4	4788.7	4779.8	4738.7	4577.5	4407.9	4142.6	3939.9	3733.4
45°	2919.5	3142.7	3264.7	3351.5	3323.6	3284.4	3158.9	3040.1	2859.8	2728.8	2590.0
47.5°	2028.3	2294.7	2248.4	2417.9	2271.8	2368.4	2167.3	2056.5	1960.9	1891.2	1812.8
50°	1452.0	1513.1	1542.6	1562.7	1552.1	1537.2	1501.1	1468.8	1425.1	1393.2	1356.1
52.5°	1121.4	1151.9	1168.6	1180.7	1178.4	1172.9	1157.2	1142.8	1122.3	1108.9	1092.6
55°	949.8	950.3	981.1	967.9	987.4	964.5	973.5	948.2	952.3	930.5	916.0
57.5°	789.3	801.8	807.4	812.9	811.4	810.4	804.3	801.2	794.3	792.3	787.3
60°	694.3	700.8	702.2	704.7	702.6	701.8	697.1	695.3	690.8	689.9	686.6
62.5°	629.2	632.5	632.5	632.5	629.8	627.2	621.8	619.1	615.1	614.4	612.4
65°	574.8	578.3	578.9	579.5	577.6	575.6	570.9	567.8	563.8	562.3	560.1
67.5°	518.6	522.3	523.6	525.5	524.4	524.0	520.8	519.6	516.9	516.3	514.3
70°	474.6	476.2	476.1	476.0	473.5	471.2	467.6	465.8	463.0	462.4	460.7
72.5°	448.4	449.5	448.8	447.9	444.6	441.3	437.0	433.8	430.1	427.9	425.3
75°	411.5	413.0	412.0	411.4	408.5	406.4	402.9	401.1	398.5	397.8	396.1
77.5°	366.2	366.9	365.4	365.3	363.0	361.7	359.1	358.6	356.7	356.7	355.1
80°	315.8	315.3	313.0	312.5	310.3	309.7	307.7	307.9	306.3	307.0	305.7
82.5°	259.9	258.4	255.3	254.3	251.8	251.6	250.3	251.3	250.5	251.8	251.0
85°	186.2	186.6	185.2	185.2	184.5	184.7	184.6	185.5	185.6	186.8	186.7
87.5°	103.8	105.3	105.0	106.4	106.3	107.8	108.4	110.6	110.9	113.1	113.1
90°	69.6	69.5	66.7	66.9	65.5	66.8	65.8	67.1	65.8	66.7	65.1
92.5°	69.2	64.5	59.8	55.0	52.7	50.1	48.0	45.4	43.1	40.6	38.3
95°	87.6	79.6	71.6	63.5	60.8	58.0	55.2	52.5	49.7	47.0	44.2
97.5°	98.9	89.4	79.9	70.4	68.0	65.6	63.1	60.8	58.4	56.0	53.6
100°	135.4	117.6	100.1	82.2	80.2	78.2	76.2	74.2	72.2	70.2	68.2
102.5°	284.4	246.9	209.2	171.6	164.5	157.4	150.3	143.0	135.9	128.8	121.7
105°	540.9	480.0	419.0	358.0	338.6	319.3	299.9	280.6	261.2	241.9	222.5
107.5°	823.7	761.7	700.0	638.1	602.4	566.6	530.9	495.0	459.3	423.4	387.7
110°	982.0	936.8	891.6	846.3	817.6	788.7	759.9	731.0	702.3	673.3	644.5



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	1007.3	975.0	942.6	910.1	897.0	883.9	870.8	857.7	844.6	831.4	818.4
115°	943.1	921.2	899.2	877.1	872.6	867.9	863.3	858.5	853.8	849.1	844.3
117.5°	840.9	828.4	815.9	803.5	804.2	804.9	805.6	806.1	806.7	807.2	807.9
120°	734.8	729.4	724.0	718.5	722.5	726.1	730.0	733.7	737.5	741.1	744.9
122.5°	647.1	644.8	642.6	640.2	644.9	649.5	654.1	658.7	663.1	667.5	671.9
125°	577.9	576.5	575.3	573.8	578.6	583.1	587.7	592.2	596.8	601.2	605.6
127.5°	530.6	530.0	529.4	528.8	532.1	535.2	538.5	541.5	544.7	547.6	550.6
130°	496.6	495.7	494.9	494.0	496.8	499.7	502.7	505.3	508.1	510.6	513.2
132.5°	473.9	472.7	471.7	470.7	472.7	474.6	476.6	478.3	480.2	481.8	483.5
135°	454.3	452.9	451.7	450.4	452.3	454.1	455.8	457.5	459.2	460.7	462.2
137.5°	437.5	436.1	434.9	433.6	435.3	436.8	438.5	439.8	441.3	442.6	444.0
140°	422.7	421.2	419.8	418.3	419.7	421.0	422.5	423.7	425.0	426.1	427.3
142.5°	408.4	406.5	404.8	402.8	403.8	404.7	405.7	406.6	407.5	408.3	409.1
145°	398.4	396.3	394.2	392.0	392.9	393.6	394.3	395.1	395.6	396.2	396.9
147.5°	388.9	386.8	384.8	382.8	383.5	384.0	384.4	384.8	385.4	385.8	386.1
150°	379.8	377.7	375.6	373.5	374.0	374.5	374.9	375.3	375.7	376.1	376.4
152.5°	369.9	367.9	366.0	364.0	364.4	364.8	365.1	365.4	365.8	366.1	366.4
155°	362.9	361.3	359.6	357.9	358.4	358.7	358.9	359.2	359.5	359.8	359.9
157.5°	359.2	357.8	356.6	355.3	355.4	355.6	355.7	355.7	355.7	355.8	355.8
160°	356.1	355.0	353.9	352.7	352.8	352.9	353.0	353.0	353.0	352.9	353.0
162.5°	353.9	352.7	351.4	350.0	350.1	350.2	350.3	350.3	350.3	350.2	350.2
165°	353.3	352.5	351.5	350.5	350.4	350.3	350.2	350.0	349.9	349.6	349.5
167.5°	353.6	352.7	351.7	350.7	350.8	351.0	351.1	351.1	351.1	351.0	351.1
170°	354.7	353.8	353.1	352.3	352.2	352.2	352.0	351.9	351.8	351.6	351.5
172.5°	355.7	354.9	354.2	353.2	353.2	353.2	353.1	353.0	352.8	352.7	352.7
175°	354.1	353.5	352.9	352.4	352.3	352.3	352.2	352.2	352.1	352.0	351.9
177.5°	355.6	355.3	354.8	354.4	354.4	354.4	354.3	354.2	354.2	354.2	354.1
180°	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0	356.0



TEST NUMBER: P1444510
 CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	15340.5	15340.5
2.5°	15399.9	15399.1
5°	15457.2	15456.2
7.5°	15500.7	15500.4
10°	15505.9	15508.5
12.5°	15474.9	15477.1
15°	15384.6	15388.7
17.5°	15211.8	15217.3
20°	14914.3	14920.0
22.5°	14432.4	14434.7
25°	13731.8	13721.8
27.5°	12776.6	12759.5
30°	11562.4	11545.9
32.5°	10114.7	10104.4
35°	8485.1	8478.6
37.5°	6769.5	6756.1
40°	5103.9	5065.1
42.5°	3643.1	3575.0
45°	2517.6	2436.9
47.5°	1757.5	1707.7
50°	1332.2	1316.1
52.5°	1085.5	1081.7
55°	915.9	914.3
57.5°	788.5	787.9
60°	688.3	688.1
62.5°	613.7	614.0
65°	561.1	561.2
67.5°	514.8	514.5
70°	461.3	461.0
72.5°	424.5	423.8
75°	396.1	395.6
77.5°	355.6	355.0
80°	306.6	305.7
82.5°	252.1	251.2
85°	188.1	188.1
87.5°	115.1	115.0
90°	65.8	63.9
92.5°	36.0	33.7
95°	41.5	38.8
97.5°	51.3	48.9
100°	66.2	64.2
102.5°	114.5	107.4
105°	203.2	183.8
107.5°	351.9	316.1
110°	615.6	586.8



TEST NUMBER: P1444510
CATALOG NUMBER: EHBR1-18-UNV-TA-L835-UPL30

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	805.2	792.0
115°	839.5	834.7
117.5°	808.3	808.9
120°	748.3	751.9
122.5°	676.2	680.6
125°	609.9	614.2
127.5°	553.5	556.3
130°	515.5	518.1
132.5°	485.0	486.5
135°	463.5	464.8
137.5°	445.2	446.2
140°	428.2	429.2
142.5°	409.7	410.3
145°	397.3	397.7
147.5°	386.2	386.6
150°	376.6	376.9
152.5°	366.5	366.8
155°	360.1	360.3
157.5°	355.7	355.7
160°	352.9	352.9
162.5°	350.1	350.2
165°	349.3	349.0
167.5°	351.0	351.1
170°	351.3	351.2
172.5°	352.6	352.5
175°	351.8	351.8
177.5°	354.1	354.0
180°	356.0	356.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-3

Test Date: 07/31/2025

Luminaire Tested: EHBR-60-L835-N

Data in this report applies to families of products including EHBR-60-L835-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-3
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L835-N**
 Description: Elevate Round Highbay at, 60000 lumens, 3500K 80CRI LEDs with N lens

Spectral Parameters

CCT (K): 3468
 CIE u': 0.2375
 CIE v': 0.5091
 Duv: -0.0021
 CIE x: 0.4049
 CIE y: 0.3856
 CIE z: 0.2095
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 581
 Purity: 37.24544
 R_f: 80.1
 R_g: 101

CRI (Ra):	82.1		
R1:	82.9	R9:	27.6
R2:	85.6	R10:	63.8
R3:	85.9	R11:	81.2
R4:	82.8	R12:	57.2
R5:	81.0	R13:	82.6
R6:	79.7	R14:	91.0
R7:	86.5	R15:	79.4
R8:	72.1		



Test Conditions

Stabilization Time: 39M
 Operation Time: 1H 39M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-3

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-3

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	60	NR	620	327	NR	750	7	NR	880	0	NR
365	0	NR	495	82	NR	625	322	NR	755	6	NR	885	0	NR
370	0	NR	500	114	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	152	NR	635	645	NR	765	4	NR	895	0	NR
380	0	NR	510	189	NR	640	197	NR	770	4	NR	900	0	NR
385	1	NR	515	222	NR	645	189	NR	775	3	NR	905	0	NR
390	2	NR	520	248	NR	650	163	NR	780	3	NR	910	0	NR
395	3	NR	525	268	NR	655	134	NR	785	2	NR	915	0	NR
400	4	NR	530	283	NR	660	113	NR	790	2	NR	920	0	NR
405	6	NR	535	294	NR	665	94	NR	795	2	NR	925	0	NR
410	9	NR	540	305	NR	670	87	NR	800	2	NR	930	0	NR
415	18	NR	545	314	NR	675	70	NR	805	1	NR	935	0	NR
420	34	NR	550	323	NR	680	60	NR	810	1	NR	940	0	NR
425	62	NR	555	335	NR	685	51	NR	815	1	NR	945	0	NR
430	102	NR	560	346	NR	690	44	NR	820	1	NR	950	0	NR
435	159	NR	565	356	NR	695	38	NR	825	1	NR	955	0	NR
440	241	NR	570	364	NR	700	32	NR	830	1	NR	960	0	NR
445	363	NR	575	371	NR	705	28	NR	835	1	NR	965	0	NR
450	389	NR	580	375	NR	710	24	NR	840	1	NR	970	0	NR
455	245	NR	585	375	NR	715	20	NR	845	0	NR	975	0	NR
460	158	NR	590	373	NR	720	17	NR	850	0	NR	980	0	NR
465	120	NR	595	364	NR	725	15	NR	855	0	NR	985	0	NR
470	79	NR	600	357	NR	730	13	NR	860	0	NR	990	0	NR
475	57	NR	605	349	NR	735	11	NR	865	0	NR	995	0	NR
480	51	NR	610	371	NR	740	9	NR	870	0	NR	1000	0	NR
485	51	NR	615	387	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-3

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.43

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	60	NR	620	327	NR	750	7	NR	880	0	NR
365	0	NR	495	82	NR	625	322	NR	755	6	NR	885	0	NR
370	0	NR	500	114	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	152	NR	635	645	NR	765	4	NR	895	0	NR
380	0	NR	510	189	NR	640	197	NR	770	4	NR	900	0	NR
385	1	NR	515	222	NR	645	189	NR	775	3	NR	905	0	NR
390	2	NR	520	248	NR	650	163	NR	780	3	NR	910	0	NR
395	3	NR	525	268	NR	655	134	NR	785	2	NR	915	0	NR
400	4	NR	530	283	NR	660	113	NR	790	2	NR	920	0	NR
405	6	NR	535	294	NR	665	94	NR	795	2	NR	925	0	NR
410	9	NR	540	305	NR	670	87	NR	800	2	NR	930	0	NR
415	18	NR	545	314	NR	675	70	NR	805	1	NR	935	0	NR
420	34	NR	550	323	NR	680	60	NR	810	1	NR	940	0	NR
425	62	NR	555	335	NR	685	51	NR	815	1	NR	945	0	NR
430	102	NR	560	346	NR	690	44	NR	820	1	NR	950	0	NR
435	159	NR	565	356	NR	695	38	NR	825	1	NR	955	0	NR
440	241	NR	570	364	NR	700	32	NR	830	1	NR	960	0	NR
445	363	NR	575	371	NR	705	28	NR	835	1	NR	965	0	NR
450	389	NR	580	375	NR	710	24	NR	840	1	NR	970	0	NR
455	245	NR	585	375	NR	715	20	NR	845	0	NR	975	0	NR
460	158	NR	590	373	NR	720	17	NR	850	0	NR	980	0	NR
465	120	NR	595	364	NR	725	15	NR	855	0	NR	985	0	NR
470	79	NR	600	357	NR	730	13	NR	860	0	NR	990	0	NR
475	57	NR	605	349	NR	735	11	NR	865	0	NR	995	0	NR
480	51	NR	610	371	NR	740	9	NR	870	0	NR	1000	0	NR
485	51	NR	615	387	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-3

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.75


λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	60	NR	620	327	NR	750	7	NR	880	0	NR
365	0	NR	495	82	NR	625	322	NR	755	6	NR	885	0	NR
370	0	NR	500	114	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	152	NR	635	645	NR	765	4	NR	895	0	NR
380	0	NR	510	189	NR	640	197	NR	770	4	NR	900	0	NR
385	1	NR	515	222	NR	645	189	NR	775	3	NR	905	0	NR
390	2	NR	520	248	NR	650	163	NR	780	3	NR	910	0	NR
395	3	NR	525	268	NR	655	134	NR	785	2	NR	915	0	NR
400	4	NR	530	283	NR	660	113	NR	790	2	NR	920	0	NR
405	6	NR	535	294	NR	665	94	NR	795	2	NR	925	0	NR
410	9	NR	540	305	NR	670	87	NR	800	2	NR	930	0	NR
415	18	NR	545	314	NR	675	70	NR	805	1	NR	935	0	NR
420	34	NR	550	323	NR	680	60	NR	810	1	NR	940	0	NR
425	62	NR	555	335	NR	685	51	NR	815	1	NR	945	0	NR
430	102	NR	560	346	NR	690	44	NR	820	1	NR	950	0	NR
435	159	NR	565	356	NR	695	38	NR	825	1	NR	955	0	NR
440	241	NR	570	364	NR	700	32	NR	830	1	NR	960	0	NR
445	363	NR	575	371	NR	705	28	NR	835	1	NR	965	0	NR
450	389	NR	580	375	NR	710	24	NR	840	1	NR	970	0	NR
455	245	NR	585	375	NR	715	20	NR	845	0	NR	975	0	NR
460	158	NR	590	373	NR	720	17	NR	850	0	NR	980	0	NR
465	120	NR	595	364	NR	725	15	NR	855	0	NR	985	0	NR
470	79	NR	600	357	NR	730	13	NR	860	0	NR	990	0	NR
475	57	NR	605	349	NR	735	11	NR	865	0	NR	995	0	NR
480	51	NR	610	371	NR	740	9	NR	870	0	NR	1000	0	NR
485	51	NR	615	387	NR	745	8	NR	875	0	NR			

Summary

$R_f = 80.1$
 $R_g = 101$
 $CIE R_a = 82.1$
 $R_9 = 27.6$




Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 86	CES26 = 68	CES51 = 90	CES76 = 59
CES02 = 62	CES27 = 89	CES52 = 90	CES77 = 78
CES03 = 31	CES28 = 84	CES53 = 81	CES78 = 61
CES04 = 70	CES29 = 66	CES54 = 91	CES79 = 86
CES05 = 49	CES30 = 77	CES55 = 90	CES80 = 82
CES06 = 51	CES31 = 69	CES56 = 80	CES81 = 79
CES07 = 42	CES32 = 62	CES57 = 79	CES82 = 92
CES08 = 41	CES33 = 74	CES58 = 81	CES83 = 89
CES09 = 29	CES34 = 72	CES59 = 92	CES84 = 89
CES10 = 75	CES35 = 85	CES60 = 94	CES85 = 82
CES11 = 58	CES36 = 97	CES61 = 90	CES86 = 78
CES12 = 64	CES37 = 79	CES62 = 92	CES87 = 82
CES13 = 43	CES38 = 85	CES63 = 78	CES88 = 86
CES14 = 74	CES39 = 94	CES64 = 79	CES89 = 76
CES15 = 71	CES40 = 89	CES65 = 76	CES90 = 85
CES16 = 47	CES41 = 89	CES66 = 73	CES91 = 83
CES17 = 49	CES42 = 77	CES67 = 70	CES92 = 73
CES18 = 56	CES43 = 74	CES68 = 76	CES93 = 84
CES19 = 72	CES44 = 99	CES69 = 81	CES94 = 65
CES20 = 66	CES45 = 83	CES70 = 68	CES95 = 79
CES21 = 86	CES46 = 82	CES71 = 64	CES96 = 85
CES22 = 78	CES47 = 81	CES72 = 88	CES97 = 85
CES23 = 92	CES48 = 80	CES73 = 60	CES98 = 82
CES24 = 91	CES49 = 80	CES74 = 97	CES99 = 81
CES25 = 72	CES50 = 89	CES75 = 64	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)