

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1432632

Luminaire Tested: EHBR1-24-UNV-N-L835-UPL36

Issue Date: 3/20/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1432632  
REPORT IS A COMBINATION OF REPORTS P1431721 AND P1431635  
Test Lab: INNOVATION CENTER  
Issue Date: 3/20/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: EHBR1-24-UNV-N-L835-UPL36  
Description: Elevate Round Highbay at, 24000 lumens, 3500K 80CRI LEDs with N lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 27820.8 lumens  
Efficiency: N/A  
Efficacy: 177.5 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.8  
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')  
CIE Type: Semi-Direct

Input Watts (W): 156.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1432632  
CATALOG NUMBER: EHBR1-24-UNV-N-L835-UPL36

### Luminous Intensity Polar Plot





TEST NUMBER: P1432632

CATALOG NUMBER: EHBR1-24-UNV-N-L835-UPL36

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	116	116	116	116	112	112	112	112	104	104	104	97	97	97	91	91	91	88		
1	109	106	103	100	105	102	100	97	96	94	92	90	89	87	85	84	82	80		
2	102	97	92	88	99	94	90	86	89	85	82	84	81	79	79	77	75	73		
3	96	89	83	78	93	86	81	77	82	78	74	78	74	71	74	71	69	67		
4	91	82	76	71	88	80	74	70	76	71	68	73	69	66	69	66	63	61		
5	86	76	70	65	83	74	68	64	71	66	62	68	64	60	65	62	59	57		
6	81	71	64	60	78	69	63	59	67	61	57	64	60	56	62	58	55	53		
7	77	66	60	55	74	65	59	55	63	57	53	60	56	52	58	54	51	50		
8	73	62	56	51	71	61	55	51	59	54	50	57	52	49	55	51	48	46		
9	69	59	52	48	67	58	52	48	56	51	47	54	49	46	52	48	45	44		
10	66	55	49	45	64	54	49	45	53	48	44	51	47	43	50	46	43	41		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	133439	133439	133439
5°	130848	130848	130848
10°	124191	124191	124191
15°	112997	112997	112997
20°	96926	96926	96926
25°	76248	76248	76248
30°	52326	52326	52326
35°	31083	31083	31083
40°	18391	18391	18391
45°	13202	13202	13202
50°	10852	10852	10852
55°	9863	9863	9863
60°	9441	9441	9441
65°	9005	9005	9005
70°	8374	8374	8374
75°	7571	7571	7571
80°	6284	6284	6284
85°	3977	3977	3977

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13202 cd/sqm



TEST NUMBER: P1432632  
 CATALOG NUMBER: EHBR1-24-UNV-N-L835-UPL36

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	2617.5	9.4
10°-20°	6570.3	23.6
20°-30°	6869.9	24.7
30°-40°	3722.3	13.4
40°-50°	1712.5	6.2
50°-60°	1206.8	4.3
60°-70°	928.7	3.3
70°-80°	563.0	2.0
80°-90°	164.9	0.6
90°-100°	98.9	0.4
100°-110°	619.1	2.2
110°-120°	1107.0	4.0
120°-130°	649.6	2.3
130°-140°	398.4	1.4
140°-150°	276.4	1.0
150°-160°	179.6	0.6
160°-170°	102.3	0.4
170°-180°	33.8	0.1
0°-30°	16057.6	57.7
0°-40°	19779.9	71.1
0°-60°	22699.2	81.6
0°-90°	24355.7	87.5
90°-120°	1825.0	6.6
90°-150°	3149.4	11.3
90°-180°	3465.0	12.5
0°-180°	27820.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	28415	28415	28415	28415	28415	
5°	27938	27938	27938	27938	27938	2617
15°	23706	23706	23706	23706	23706	6570
25°	15227	15227	15227	15227	15227	6870
35°	5705	5705	5705	5705	5705	3722
45°	2136	2136	2136	2136	2136	1712
55°	1333	1333	1333	1333	1333	1207
65°	940	940	940	940	940	929
75°	533	533	533	533	533	563
85°	137	137	137	137	137	152
90°	27	42	72	46	27	19
95°	44	73	161	79	50	42
105°	216	426	1089	470	286	289
115°	996	1047	1287	1234	1226	917
125°	718	670	688	698	783	655
135°	524	508	526	494	492	410
145°	430	424	450	444	442	273
155°	377	373	391	391	391	176
165°	353	353	363	363	361	101
175°	349	349	355	355	355	33
180°	353	353	353	353	353	



TEST NUMBER: P1432632

CATALOG NUMBER: EHBR1-24-UNV-N-L835-UPL36

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	28414.8	28414.8	28414.8	28414.8	28414.8
2.5°	28314.1	28314.1	28314.1	28314.1	28314.1
5°	27938.2	27938.2	27938.2	27938.2	27938.2
7.5°	27296.5	27296.5	27296.5	27296.5	27296.5
10°	26386.0	26386.0	26386.0	26386.0	26386.0
12.5°	25209.4	25209.4	25209.4	25209.4	25209.4
15°	23706.2	23706.2	23706.2	23706.2	23706.2
17.5°	21962.2	21962.2	21962.2	21962.2	21962.2
20°	19921.2	19921.2	19921.2	19921.2	19921.2
22.5°	17648.8	17648.8	17648.8	17648.8	17648.8
25°	15226.7	15226.7	15226.7	15226.7	15226.7
27.5°	12658.9	12658.9	12658.9	12658.9	12658.9
30°	10064.8	10064.8	10064.8	10064.8	10064.8
32.5°	7724.4	7724.4	7724.4	7724.4	7724.4
35°	5704.9	5704.9	5704.9	5704.9	5704.9
37.5°	4188.8	4188.8	4188.8	4188.8	4188.8
40°	3187.7	3187.7	3187.7	3187.7	3187.7
42.5°	2556.1	2556.1	2556.1	2556.1	2556.1
45°	2136.1	2136.1	2136.1	2136.1	2136.1
47.5°	1833.4	1833.4	1833.4	1833.4	1833.4
50°	1617.3	1617.3	1617.3	1617.3	1617.3
52.5°	1459.5	1459.5	1459.5	1459.5	1459.5
55°	1332.9	1332.9	1332.9	1332.9	1332.9
57.5°	1230.1	1230.1	1230.1	1230.1	1230.1
60°	1134.9	1134.9	1134.9	1134.9	1134.9
62.5°	1039.9	1039.9	1039.9	1039.9	1039.9
65°	939.9	939.9	939.9	939.9	939.9
67.5°	838.0	838.0	838.0	838.0	838.0
70°	734.8	734.8	734.8	734.8	734.8
72.5°	634.5	634.5	634.5	634.5	634.5
75°	533.3	533.3	533.3	533.3	533.3
77.5°	434.1	434.1	434.1	434.1	434.1
80°	330.6	330.6	330.6	330.6	330.6
82.5°	231.5	231.5	231.5	231.5	231.5
85°	136.7	136.7	136.7	136.7	136.7
87.5°	49.0	49.0	49.0	49.0	49.0
90°	26.6	42.5	72.1	46.4	26.6
92.5°	37.7	63.5	115.0	59.5	33.7
95°	43.6	73.4	160.7	79.3	49.6
97.5°	55.6	81.4	184.4	97.2	77.4
100°	73.4	95.2	287.6	119.0	103.2
102.5°	125.0	202.3	610.9	224.1	156.7
105°	216.1	426.5	1088.9	470.1	285.6
107.5°	374.9	763.6	1436.0	833.1	541.5
110°	700.1	1013.5	1505.5	1144.5	866.7



TEST NUMBER: P1432632

CATALOG NUMBER: EHBR1-24-UNV-N-L835-UPL36

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	946.1	1088.9	1442.0	1263.4	1128.5
115°	995.7	1047.3	1287.3	1233.7	1225.8
117.5°	962.0	956.0	1092.9	1108.8	1184.1
120°	890.6	850.9	912.4	968.0	1069.1
122.5°	801.3	753.8	781.5	823.1	924.3
125°	718.0	670.4	688.3	698.2	783.4
127.5°	644.7	612.9	622.8	610.9	664.4
130°	595.0	567.3	581.1	553.4	579.2
132.5°	553.4	535.6	551.4	517.6	525.6
135°	523.6	507.7	525.6	493.9	491.9
137.5°	497.8	484.0	501.8	478.0	472.1
140°	474.1	462.2	481.9	464.1	460.1
142.5°	448.3	440.3	464.1	452.3	448.3
145°	430.5	424.4	450.2	444.3	442.3
147.5°	414.6	410.6	434.3	432.4	432.4
150°	400.7	396.7	420.5	418.5	420.5
152.5°	386.8	382.8	404.7	402.6	404.7
155°	376.8	372.9	390.7	390.7	390.7
157.5°	368.9	366.9	380.8	380.8	380.8
160°	363.0	361.0	372.9	372.9	370.9
162.5°	357.0	355.0	368.9	366.9	366.9
165°	353.1	353.1	363.0	363.0	361.0
167.5°	353.1	351.0	361.0	361.0	359.0
170°	351.0	351.0	359.0	357.0	355.0
172.5°	351.0	351.0	359.0	357.0	355.0
175°	349.1	349.1	355.0	355.0	355.0
177.5°	351.0	351.0	355.0	355.0	353.1
180°	353.1	353.1	353.1	353.1	353.1



TEST NUMBER: P1432632  
 CATALOG NUMBER: EHBR1-24-UNV-N-L835-UPL36

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.42	16.42	16.00	16.97	17.59	15.42	16.42	16.00	16.97	17.59
	3H	17.20	18.09	17.79	18.66	19.32	17.20	18.09	17.79	18.66	19.32
	4H	17.86	18.68	18.47	19.27	19.94	17.86	18.68	18.47	19.27	19.94
	6H	18.31	19.07	18.93	19.67	20.36	18.31	19.07	18.93	19.67	20.36
	8H	18.43	19.15	19.07	19.77	20.46	18.43	19.15	19.07	19.77	20.46
	12H	18.49	19.17	19.12	19.78	20.50	18.49	19.17	19.12	19.78	20.50
4H	2H	15.96	16.79	16.57	17.37	18.05	15.96	16.79	16.57	17.37	18.05
	3H	17.93	18.61	18.55	19.24	19.93	17.93	18.61	18.55	19.24	19.93
	4H	18.70	19.32	19.34	19.95	20.68	18.70	19.32	19.34	19.95	20.68
	6H	19.27	19.80	19.93	20.46	21.20	19.27	19.80	19.93	20.46	21.20
	8H	19.43	19.92	20.09	20.58	21.32	19.43	19.92	20.09	20.58	21.32
	12H	19.50	19.94	20.19	20.62	21.38	19.50	19.94	20.19	20.62	21.38
8H	4H	18.93	19.42	19.59	20.08	20.82	18.93	19.42	19.59	20.08	20.82
	6H	19.61	20.01	20.30	20.71	21.46	19.61	20.01	20.30	20.71	21.46
	8H	19.83	20.19	20.54	20.90	21.66	19.83	20.19	20.54	20.90	21.66
	12H	19.97	20.28	20.68	20.97	21.81	19.97	20.28	20.68	20.97	21.81
12H	4H	18.92	19.36	19.60	20.04	20.79	18.92	19.36	19.60	20.04	20.79
	6H	19.63	19.99	20.35	20.70	21.47	19.63	19.99	20.35	20.70	21.47
	8H	19.89	20.20	20.60	20.90	21.73	19.89	20.20	20.60	20.90	21.73

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-3

Test Date: 07/31/2025

Luminaire Tested: EHBR-60-L835-N

Data in this report applies to families of products including EHBR-60-L835-N

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2506-472-3  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 08/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **EHBR-60-L835-N**  
 Description: Elevate Round Highbay at, 60000 lumens, 3500K 80CRI LEDs with N lens

**Spectral Parameters**

CCT (K): 3468  
 CIE u': 0.2375  
 CIE v': 0.5091  
 Duv: -0.0021  
 CIE x: 0.4049  
 CIE y: 0.3856  
 CIE z: 0.2095  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 581  
 Purity: 37.24544  
 R<sub>f</sub>: 80.1  
 R<sub>g</sub>: 101

CRI (Ra):	82.1		
R1:	82.9	R9:	27.6
R2:	85.6	R10:	63.8
R3:	85.9	R11:	81.2
R4:	82.8	R12:	57.2
R5:	81.0	R13:	82.6
R6:	79.7	R14:	91.0
R7:	86.5	R15:	79.4
R8:	72.1		



**Test Conditions**

Stabilization Time: 39M  
 Operation Time: 1H 39M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-3

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-3

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-3

**Photopic Flux vs. Wavelength**



**Photopic Lumens: NR**

$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)
360	0	NR	490	60	NR	620	327	NR	750	7	NR	880	0	NR
365	0	NR	495	82	NR	625	322	NR	755	6	NR	885	0	NR
370	0	NR	500	114	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	152	NR	635	645	NR	765	4	NR	895	0	NR
380	0	NR	510	189	NR	640	197	NR	770	4	NR	900	0	NR
385	1	NR	515	222	NR	645	189	NR	775	3	NR	905	0	NR
390	2	NR	520	248	NR	650	163	NR	780	3	NR	910	0	NR
395	3	NR	525	268	NR	655	134	NR	785	2	NR	915	0	NR
400	4	NR	530	283	NR	660	113	NR	790	2	NR	920	0	NR
405	6	NR	535	294	NR	665	94	NR	795	2	NR	925	0	NR
410	9	NR	540	305	NR	670	87	NR	800	2	NR	930	0	NR
415	18	NR	545	314	NR	675	70	NR	805	1	NR	935	0	NR
420	34	NR	550	323	NR	680	60	NR	810	1	NR	940	0	NR
425	62	NR	555	335	NR	685	51	NR	815	1	NR	945	0	NR
430	102	NR	560	346	NR	690	44	NR	820	1	NR	950	0	NR
435	159	NR	565	356	NR	695	38	NR	825	1	NR	955	0	NR
440	241	NR	570	364	NR	700	32	NR	830	1	NR	960	0	NR
445	363	NR	575	371	NR	705	28	NR	835	1	NR	965	0	NR
450	389	NR	580	375	NR	710	24	NR	840	1	NR	970	0	NR
455	245	NR	585	375	NR	715	20	NR	845	0	NR	975	0	NR
460	158	NR	590	373	NR	720	17	NR	850	0	NR	980	0	NR
465	120	NR	595	364	NR	725	15	NR	855	0	NR	985	0	NR
470	79	NR	600	357	NR	730	13	NR	860	0	NR	990	0	NR
475	57	NR	605	349	NR	735	11	NR	865	0	NR	995	0	NR
480	51	NR	610	371	NR	740	9	NR	870	0	NR	1000	0	NR
485	51	NR	615	387	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-3

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: NR**

**S/P: 1.43**

$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)
360	0	NR	490	60	NR	620	327	NR	750	7	NR	880	0	NR
365	0	NR	495	82	NR	625	322	NR	755	6	NR	885	0	NR
370	0	NR	500	114	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	152	NR	635	645	NR	765	4	NR	895	0	NR
380	0	NR	510	189	NR	640	197	NR	770	4	NR	900	0	NR
385	1	NR	515	222	NR	645	189	NR	775	3	NR	905	0	NR
390	2	NR	520	248	NR	650	163	NR	780	3	NR	910	0	NR
395	3	NR	525	268	NR	655	134	NR	785	2	NR	915	0	NR
400	4	NR	530	283	NR	660	113	NR	790	2	NR	920	0	NR
405	6	NR	535	294	NR	665	94	NR	795	2	NR	925	0	NR
410	9	NR	540	305	NR	670	87	NR	800	2	NR	930	0	NR
415	18	NR	545	314	NR	675	70	NR	805	1	NR	935	0	NR
420	34	NR	550	323	NR	680	60	NR	810	1	NR	940	0	NR
425	62	NR	555	335	NR	685	51	NR	815	1	NR	945	0	NR
430	102	NR	560	346	NR	690	44	NR	820	1	NR	950	0	NR
435	159	NR	565	356	NR	695	38	NR	825	1	NR	955	0	NR
440	241	NR	570	364	NR	700	32	NR	830	1	NR	960	0	NR
445	363	NR	575	371	NR	705	28	NR	835	1	NR	965	0	NR
450	389	NR	580	375	NR	710	24	NR	840	1	NR	970	0	NR
455	245	NR	585	375	NR	715	20	NR	845	0	NR	975	0	NR
460	158	NR	590	373	NR	720	17	NR	850	0	NR	980	0	NR
465	120	NR	595	364	NR	725	15	NR	855	0	NR	985	0	NR
470	79	NR	600	357	NR	730	13	NR	860	0	NR	990	0	NR
475	57	NR	605	349	NR	735	11	NR	865	0	NR	995	0	NR
480	51	NR	610	371	NR	740	9	NR	870	0	NR	1000	0	NR
485	51	NR	615	387	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-3

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: NR**

**M/P: 2.75**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	60	NR	620	327	NR	750	7	NR	880	0	NR
365	0	NR	495	82	NR	625	322	NR	755	6	NR	885	0	NR
370	0	NR	500	114	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	152	NR	635	645	NR	765	4	NR	895	0	NR
380	0	NR	510	189	NR	640	197	NR	770	4	NR	900	0	NR
385	1	NR	515	222	NR	645	189	NR	775	3	NR	905	0	NR
390	2	NR	520	248	NR	650	163	NR	780	3	NR	910	0	NR
395	3	NR	525	268	NR	655	134	NR	785	2	NR	915	0	NR
400	4	NR	530	283	NR	660	113	NR	790	2	NR	920	0	NR
405	6	NR	535	294	NR	665	94	NR	795	2	NR	925	0	NR
410	9	NR	540	305	NR	670	87	NR	800	2	NR	930	0	NR
415	18	NR	545	314	NR	675	70	NR	805	1	NR	935	0	NR
420	34	NR	550	323	NR	680	60	NR	810	1	NR	940	0	NR
425	62	NR	555	335	NR	685	51	NR	815	1	NR	945	0	NR
430	102	NR	560	346	NR	690	44	NR	820	1	NR	950	0	NR
435	159	NR	565	356	NR	695	38	NR	825	1	NR	955	0	NR
440	241	NR	570	364	NR	700	32	NR	830	1	NR	960	0	NR
445	363	NR	575	371	NR	705	28	NR	835	1	NR	965	0	NR
450	389	NR	580	375	NR	710	24	NR	840	1	NR	970	0	NR
455	245	NR	585	375	NR	715	20	NR	845	0	NR	975	0	NR
460	158	NR	590	373	NR	720	17	NR	850	0	NR	980	0	NR
465	120	NR	595	364	NR	725	15	NR	855	0	NR	985	0	NR
470	79	NR	600	357	NR	730	13	NR	860	0	NR	990	0	NR
475	57	NR	605	349	NR	735	11	NR	865	0	NR	995	0	NR
480	51	NR	610	371	NR	740	9	NR	870	0	NR	1000	0	NR
485	51	NR	615	387	NR	745	8	NR	875	0	NR			

**Summary**

$R_f = 80.1$   
 $R_g = 101$   
 CIE  $R_a = 82.1$   
 $R_9 = 27.6$



**Color Vector Graphics**



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

CES01 = 86	CES26 = 68	CES51 = 90	CES76 = 59
CES02 = 62	CES27 = 89	CES52 = 90	CES77 = 78
CES03 = 31	CES28 = 84	CES53 = 81	CES78 = 61
CES04 = 70	CES29 = 66	CES54 = 91	CES79 = 86
CES05 = 49	CES30 = 77	CES55 = 90	CES80 = 82
CES06 = 51	CES31 = 69	CES56 = 80	CES81 = 79
CES07 = 42	CES32 = 62	CES57 = 79	CES82 = 92
CES08 = 41	CES33 = 74	CES58 = 81	CES83 = 89
CES09 = 29	CES34 = 72	CES59 = 92	CES84 = 89
CES10 = 75	CES35 = 85	CES60 = 94	CES85 = 82
CES11 = 58	CES36 = 97	CES61 = 90	CES86 = 78
CES12 = 64	CES37 = 79	CES62 = 92	CES87 = 82
CES13 = 43	CES38 = 85	CES63 = 78	CES88 = 86
CES14 = 74	CES39 = 94	CES64 = 79	CES89 = 76
CES15 = 71	CES40 = 89	CES65 = 76	CES90 = 85
CES16 = 47	CES41 = 89	CES66 = 73	CES91 = 83
CES17 = 49	CES42 = 77	CES67 = 70	CES92 = 73
CES18 = 56	CES43 = 74	CES68 = 76	CES93 = 84
CES19 = 72	CES44 = 99	CES69 = 81	CES94 = 65
CES20 = 66	CES45 = 83	CES70 = 68	CES95 = 79
CES21 = 86	CES46 = 82	CES71 = 64	CES96 = 85
CES22 = 78	CES47 = 81	CES72 = 88	CES97 = 85
CES23 = 92	CES48 = 80	CES73 = 60	CES98 = 82
CES24 = 91	CES49 = 80	CES74 = 97	CES99 = 81
CES25 = 72	CES50 = 89	CES75 = 64	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)