

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1433370

Luminaire Tested: EHBR1-60-UNV-ASM-L850

Issue Date: 3/13/2026

Test Information

Test Method: LM-79-2019
Report Number: P1433370
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2601-654-4)
Test Lab: INNOVATION CENTER
Issue Date: 3/13/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-60-UNV-ASM-L850
Description: Elevate Round Highbay at, 60000 lumens, 3000K 90CRI LEDs with ASM lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 58342.8 lumens
Efficiency: N/A
Efficacy: 176.6 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.99 / 0.92
Luminous Opening: Circular (Dia: 1.71' x H: 0')
CIE Type: Direct

Input Watts (W): 330.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1433370
CATALOG NUMBER: EHBR1-60-UNV-ASM-L850

Luminous Intensity Polar Plot





TEST NUMBER: P1433370
 CATALOG NUMBER: EHBR1-60-UNV-ASM-L850

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	112	108	105	103	109	106	104	101	102	100	98	98	97	95	95	93	92	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74	74	74
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	72	69	67	67	67
5	87	78	71	66	86	77	70	65	75	69	65	73	68	64	71	67	64	62	62	62
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	57	57	57
7	78	67	60	56	76	67	60	56	65	59	55	64	59	55	63	58	55	53	53	53
8	74	63	56	52	72	62	56	52	61	55	51	60	55	51	59	54	51	49	49	49
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46	46	46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	245032	245032	245032	245032	245032
5°	232407	235125	245128	256885	261507
10°	221401	226091	243708	266877	269984
15°	205893	211393	238106	265920	252591
20°	184680	190900	224251	246147	203965
25°	155919	161820	199955	207995	142368
30°	117591	124409	163654	162020	93362
35°	78971	83738	118408	116495	60994
40°	50293	53748	77308	77806	42454
45°	36239	37746	49605	51736	33256
50°	30587	30830	37327	38299	28635
55°	27436	27501	30969	31786	26507
60°	25923	25703	27366	27946	25767
65°	25418	25191	25625	26125	25527
70°	25644	25202	25230	25713	25981
75°	25865	25085	25030	25919	26665
80°	26195	24372	24475	26195	28020
85°	24829	20615	20615	23562	26041

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 112.5°
 Vertical Angle: 45°
 Luminance: 69742 cd/sqm



TEST NUMBER: P1433370
 CATALOG NUMBER: EHBR1-60-UNV-ASM-L850

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	4961.3	8.5
10°-20°	13497.6	23.1
20°-30°	15829.9	27.1
30°-40°	11008.7	18.9
40°-50°	5470.8	9.4
50°-60°	3272.1	5.6
60°-70°	2303.0	3.9
70°-80°	1483.6	2.5
80°-90°	471.2	0.8
90°-100°	2.8	0.0
100°-110°	3.3	0.0
110°-120°	3.4	0.0
120°-130°	4.2	0.0
130°-140°	5.7	0.0
140°-150°	6.9	0.0
150°-160°	7.7	0.0
160°-170°	7.5	0.0
170°-180°	3.2	0.0
0°-30°	34288.7	58.8
0°-40°	45297.4	77.6
0°-60°	54040.3	92.6
0°-90°	58298.2	99.9
90°-120°	9.4	0.0
90°-150°	26.3	0.0
90°-180°	45.0	0.1
0°-180°	58342.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	52178	52178	52178	52178	52178	
5°	49301	49878	52000	54494	55474	4624
15°	42350	43481	48975	54696	51955	11810
25°	30091	31230	38590	40141	27476	13577
35°	13775	14607	20654	20321	10639	8775
45°	5457	5684	7469	7790	5008	4411
55°	3351	3359	3782	3882	3238	3041
65°	2288	2267	2306	2351	2297	2272
75°	1426	1382	1380	1428	1470	1505
85°	461	383	383	437	483	474
90°	1	1	1	3	8	23
95°	1	1	2	3	8	1
105°	2	1	2	4	9	2
115°	2	2	3	4	9	2
125°	3	4	4	6	10	2
135°	4	7	8	8	11	3
145°	11	12	12	10	13	7
155°	19	17	16	16	18	9
165°	27	25	26	28	32	7
175°	33	33	34	37	42	3
180°	36	36	36	36	36	



TEST NUMBER: P1433370
 CATALOG NUMBER: EHBR1-60-UNV-ASM-L850

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	52177.8	52177.8	52177.8	52177.8	52177.8	52177.8	52177.8	52177.8	52177.8
2.5°	50628.9	50662.2	51016.4	51477.2	52147.5	52821.6	53367.6	53727.6	53905.7
5°	49301.2	49485.2	49877.6	50723.9	51999.7	53349.9	54493.7	55242.2	55474.1
7.5°	48007.8	48114.4	48771.0	49840.3	51646.5	53750.1	55449.7	56323.3	56536.7
10°	46429.6	46671.3	47413.0	48674.1	51107.4	54002.5	55966.2	56592.4	56617.8
12.5°	44572.6	44892.5	45658.6	47249.5	50247.4	53912.6	55793.1	55587.6	55120.9
15°	42349.6	42630.4	43480.7	45326.0	48975.4	53379.3	54696.2	53024.2	51954.7
17.5°	39948.6	40203.0	40941.7	42973.9	47183.0	52381.3	52406.8	49098.7	47081.2
20°	36954.6	37154.2	38199.2	40193.3	44872.9	50780.6	49254.3	43203.8	40813.5
22.5°	33768.9	33955.9	34884.3	36959.5	41976.8	48622.3	44864.2	37273.7	34012.5
25°	30091.1	30192.9	31230.0	33106.6	38589.6	45977.6	40141.4	30812.2	27475.8
27.5°	25953.3	26126.5	27211.7	29128.3	34605.4	42625.5	35112.3	25178.5	22100.4
30°	21685.5	21972.2	22942.8	24659.0	30180.1	38328.4	29878.8	20051.6	17217.2
32.5°	17702.4	17908.9	18600.6	20394.0	25225.5	34116.3	24852.7	16066.5	13665.5
35°	13775.1	13981.6	14606.7	16367.9	20654.3	28846.5	20320.6	12624.4	10639.3
37.5°	10529.7	10894.6	11295.8	12725.2	16209.3	23867.4	16198.6	10165.7	8629.6
40°	8204.0	8262.7	8767.5	9682.3	12610.8	18662.2	12692.0	8115.0	6925.2
42.5°	6567.1	6726.6	6943.8	7628.6	9555.2	14270.2	9975.9	6660.1	5882.2
45°	5456.6	5519.2	5683.6	6143.5	7469.2	10501.3	7790.1	5619.1	5007.5
47.5°	4773.7	4746.3	4852.0	5196.4	6082.8	8116.0	6313.7	4819.7	4391.1
50°	4186.7	4170.0	4219.9	4449.8	5109.2	6227.6	5242.3	4207.2	3919.5
52.5°	3730.7	3745.4	3750.2	3893.1	4389.1	5079.0	4464.5	3749.2	3555.5
55°	3351.0	3369.7	3358.9	3464.6	3782.5	4269.8	3882.3	3371.6	3237.6
57.5°	3054.6	3040.9	3026.3	3082.9	3321.7	3622.1	3371.6	3049.7	2960.7
60°	2760.1	2747.4	2736.6	2773.8	2913.7	3136.8	2975.4	2768.9	2743.5
62.5°	2507.7	2499.9	2498.9	2492.0	2599.7	2740.5	2631.0	2516.5	2494.0
65°	2287.5	2278.7	2267.0	2256.2	2306.1	2437.2	2351.1	2289.4	2297.3
67.5°	2067.3	2067.3	2046.8	2030.2	2079.1	2147.6	2110.5	2075.2	2084.0
70°	1867.7	1868.7	1835.5	1822.8	1837.5	1910.9	1872.7	1877.6	1892.2
72.5°	1653.5	1630.0	1605.6	1604.6	1606.6	1663.3	1650.6	1662.3	1678.0
75°	1425.5	1398.1	1382.5	1364.9	1379.5	1422.6	1428.5	1445.2	1469.6
77.5°	1205.4	1163.3	1150.6	1141.8	1132.0	1180.9	1199.5	1222.1	1258.2
80°	968.6	922.7	901.2	888.4	905.0	927.5	968.6	985.2	1036.1
82.5°	716.2	681.9	655.5	654.6	662.4	682.9	718.2	749.5	778.9
85°	460.8	406.1	382.6	391.3	382.6	413.8	437.3	474.5	483.3
87.5°	166.3	130.2	124.3	136.9	134.1	143.8	164.3	179.1	180.1
90°	1.0	1.0	1.0	1.0	1.0	2.0	2.9	5.9	7.9
92.5°	1.0	1.0	1.0	1.0	1.0	2.0	2.9	5.9	7.9
95°	1.0	1.0	1.0	1.0	2.0	2.0	2.9	5.9	7.9
97.5°	2.0	1.0	1.0	1.0	2.0	2.0	2.9	5.9	7.9
100°	2.0	1.0	1.0	2.0	2.0	2.0	2.9	5.9	7.9
102.5°	2.0	1.0	1.0	2.0	2.0	2.9	3.9	6.9	7.9
105°	2.0	1.0	1.0	2.0	2.0	2.9	3.9	6.9	8.8
107.5°	2.0	1.0	2.0	2.0	2.0	2.9	3.9	6.9	8.8
110°	2.0	1.0	2.0	2.0	2.0	2.9	3.9	6.9	8.8



TEST NUMBER: P1433370
 CATALOG NUMBER: EHBR1-60-UNV-ASM-L850

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
112.5°	2.0	1.0	2.0	2.0	2.0	2.9	3.9	6.9	8.8
115°	2.0	1.0	2.0	2.0	2.9	2.9	3.9	6.9	8.8
117.5°	2.0	1.0	2.0	2.9	2.9	2.9	3.9	6.9	8.8
120°	2.0	1.0	2.0	2.9	2.9	2.9	4.9	6.9	8.8
122.5°	2.0	2.0	2.9	3.9	3.9	3.9	4.9	7.9	8.8
125°	2.9	2.0	3.9	4.9	3.9	3.9	5.9	7.9	9.8
127.5°	2.9	2.0	3.9	4.9	4.9	4.9	5.9	7.9	9.8
130°	2.9	2.9	4.9	5.9	5.9	4.9	5.9	8.8	9.8
132.5°	3.9	3.9	6.9	7.9	6.9	5.9	6.9	9.8	10.8
135°	3.9	4.9	6.9	8.8	7.9	5.9	7.9	8.8	10.8
137.5°	4.9	5.9	8.8	9.8	8.8	6.9	7.9	9.8	10.8
140°	6.9	7.9	9.8	9.8	9.8	7.9	7.9	9.8	11.8
142.5°	8.8	8.8	10.8	10.8	10.8	8.8	8.8	10.8	11.8
145°	10.8	10.8	11.8	10.8	11.8	10.8	9.8	10.8	12.7
147.5°	12.7	12.7	12.7	11.8	11.8	10.8	10.8	11.8	13.7
150°	14.6	14.6	13.7	12.7	12.7	12.7	11.8	12.7	14.6
152.5°	16.6	15.6	14.6	13.7	13.7	13.7	13.7	14.6	15.6
155°	18.6	17.6	16.6	14.6	15.6	15.6	15.6	16.6	17.6
157.5°	21.5	19.5	18.6	17.6	17.6	18.6	18.6	19.5	20.5
160°	23.5	22.5	21.5	20.5	21.5	21.5	22.5	23.5	24.5
162.5°	25.4	24.5	23.5	23.5	23.5	23.5	25.4	26.4	28.4
165°	27.4	26.4	25.4	25.4	26.4	26.4	28.4	30.4	32.3
167.5°	27.4	27.4	27.4	27.4	28.4	28.4	30.4	33.3	35.3
170°	29.4	28.4	28.4	29.4	29.4	30.4	32.3	35.3	37.1
172.5°	31.3	30.4	31.3	31.3	32.3	32.3	35.3	38.1	40.1
175°	33.3	32.3	33.3	33.3	34.3	35.3	37.1	40.1	42.0
177.5°	34.3	33.3	33.3	33.3	34.3	36.2	38.1	41.1	43.0
180°	36.2	36.2	36.2	36.2	36.2	36.2	36.2	36.2	36.2



TEST NUMBER: P1433370
 CATALOG NUMBER: EHBR1-60-UNV-ASM-L850

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.09	21.29	20.45	21.61	21.92	20.85	22.06	21.22	22.37	22.69
	3H	22.00	23.07	22.38	23.41	23.78	22.50	23.58	22.88	23.91	24.28
	4H	22.81	23.81	23.22	24.17	24.55	23.22	24.22	23.62	24.57	24.96
	6H	23.48	24.40	23.90	24.77	25.17	23.81	24.73	24.22	25.10	25.50
	8H	23.72	24.59	24.16	24.99	25.39	24.02	24.89	24.45	25.28	25.69
	12H	23.88	24.71	24.32	25.10	25.53	24.15	24.98	24.58	25.37	25.80
4H	2H	20.65	21.65	21.06	22.01	22.39	21.27	22.28	21.68	22.63	23.02
	3H	22.81	23.64	23.23	24.04	24.45	23.20	24.02	23.61	24.43	24.83
	4H	23.76	24.50	24.20	24.92	25.37	24.07	24.81	24.50	25.23	25.67
	6H	24.57	25.21	25.04	25.66	26.13	24.81	25.45	25.28	25.90	26.37
	8H	24.87	25.46	25.34	25.91	26.38	25.08	25.68	25.55	26.13	26.60
	12H	25.07	25.60	25.56	26.08	26.56	25.26	25.79	25.75	26.27	26.75
8H	4H	24.08	24.68	24.55	25.13	25.60	24.37	24.96	24.84	25.41	25.89
	6H	25.04	25.52	25.54	26.02	26.50	25.27	25.75	25.78	26.25	26.74
	8H	25.42	25.85	25.95	26.37	26.87	25.63	26.07	26.16	26.59	27.08
	12H	25.72	26.10	26.24	26.59	27.17	25.91	26.29	26.43	26.79	27.36
12H	4H	24.11	24.63	24.60	25.12	25.59	24.40	24.92	24.89	25.41	25.88
	6H	25.10	25.53	25.63	26.05	26.55	25.34	25.77	25.87	26.29	26.79
	8H	25.55	25.93	26.07	26.42	27.00	25.77	26.15	26.29	26.65	27.22

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-5

Test Date: 08/01/2025

Luminaire Tested: EHBR-60-L930-N

Data in this report applies to families of products including EHBR-60-L930-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-5
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L930-N**
 Description: Elevate Round Highbay at, 60000 lumens, 3000K 90CRI LEDs with N lens

Spectral Parameters

CCT (K): 2996
 CIE u': 0.2519
 CIE v': 0.5169
 Duv: -0.0033
 CIE x: 0.4325
 CIE y: 0.3945
 CIE z: 0.1730
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 584
 Purity: 48.21818
 Rf: 91.3
 Rg: 102

CRI (Ra):	94.4		
R1:	96.8	R9:	61.4
R2:	98.1	R10:	94.4
R3:	97.8	R11:	95.7
R4:	95.6	R12:	88.5
R5:	96.9	R13:	97.3
R6:	95.7	R14:	97.8
R7:	90.9	R15:	92.3
R8:	83.0		



Test Conditions


Stabilization Time: 40M
 Operation Time: 1H 40M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-5

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 7-step quadrangle

REPORT NUMBER: SP1-2506-472-5

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	101	NR	620	317	NR	750	7	NR	880	0	NR
365	0	NR	495	121	NR	625	320	NR	755	6	NR	885	0	NR
370	0	NR	500	141	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	158	NR	635	651	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	207	NR	770	4	NR	900	0	NR
385	0	NR	515	182	NR	645	201	NR	775	3	NR	905	0	NR
390	0	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	146	NR	785	2	NR	915	0	NR
400	1	NR	530	199	NR	660	124	NR	790	2	NR	920	0	NR
405	3	NR	535	205	NR	665	105	NR	795	2	NR	925	0	NR
410	4	NR	540	210	NR	670	96	NR	800	1	NR	930	0	NR
415	7	NR	545	216	NR	675	79	NR	805	1	NR	935	0	NR
420	13	NR	550	222	NR	680	67	NR	810	1	NR	940	0	NR
425	22	NR	555	230	NR	685	58	NR	815	1	NR	945	0	NR
430	37	NR	560	240	NR	690	49	NR	820	1	NR	950	0	NR
435	60	NR	565	248	NR	695	42	NR	825	1	NR	955	0	NR
440	101	NR	570	258	NR	700	36	NR	830	1	NR	960	0	NR
445	172	NR	575	268	NR	705	30	NR	835	1	NR	965	0	NR
450	223	NR	580	278	NR	710	26	NR	840	1	NR	970	0	NR
455	167	NR	585	287	NR	715	22	NR	845	0	NR	975	0	NR
460	126	NR	590	295	NR	720	19	NR	850	0	NR	980	0	NR
465	111	NR	595	298	NR	725	16	NR	855	0	NR	985	0	NR
470	86	NR	600	303	NR	730	14	NR	860	0	NR	990	0	NR
475	74	NR	605	307	NR	735	12	NR	865	0	NR	995	0	NR
480	77	NR	610	341	NR	740	10	NR	870	0	NR	1000	0	NR
485	86	NR	615	368	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-5

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.44

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	101	NR	620	317	NR	750	7	NR	880	0	NR
365	0	NR	495	121	NR	625	320	NR	755	6	NR	885	0	NR
370	0	NR	500	141	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	158	NR	635	651	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	207	NR	770	4	NR	900	0	NR
385	0	NR	515	182	NR	645	201	NR	775	3	NR	905	0	NR
390	0	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	146	NR	785	2	NR	915	0	NR
400	1	NR	530	199	NR	660	124	NR	790	2	NR	920	0	NR
405	3	NR	535	205	NR	665	105	NR	795	2	NR	925	0	NR
410	4	NR	540	210	NR	670	96	NR	800	1	NR	930	0	NR
415	7	NR	545	216	NR	675	79	NR	805	1	NR	935	0	NR
420	13	NR	550	222	NR	680	67	NR	810	1	NR	940	0	NR
425	22	NR	555	230	NR	685	58	NR	815	1	NR	945	0	NR
430	37	NR	560	240	NR	690	49	NR	820	1	NR	950	0	NR
435	60	NR	565	248	NR	695	42	NR	825	1	NR	955	0	NR
440	101	NR	570	258	NR	700	36	NR	830	1	NR	960	0	NR
445	172	NR	575	268	NR	705	30	NR	835	1	NR	965	0	NR
450	223	NR	580	278	NR	710	26	NR	840	1	NR	970	0	NR
455	167	NR	585	287	NR	715	22	NR	845	0	NR	975	0	NR
460	126	NR	590	295	NR	720	19	NR	850	0	NR	980	0	NR
465	111	NR	595	298	NR	725	16	NR	855	0	NR	985	0	NR
470	86	NR	600	303	NR	730	14	NR	860	0	NR	990	0	NR
475	74	NR	605	307	NR	735	12	NR	865	0	NR	995	0	NR
480	77	NR	610	341	NR	740	10	NR	870	0	NR	1000	0	NR
485	86	NR	615	368	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.85

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	101	NR	620	317	NR	750	7	NR	880	0	NR
365	0	NR	495	121	NR	625	320	NR	755	6	NR	885	0	NR
370	0	NR	500	141	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	158	NR	635	651	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	207	NR	770	4	NR	900	0	NR
385	0	NR	515	182	NR	645	201	NR	775	3	NR	905	0	NR
390	0	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	146	NR	785	2	NR	915	0	NR
400	1	NR	530	199	NR	660	124	NR	790	2	NR	920	0	NR
405	3	NR	535	205	NR	665	105	NR	795	2	NR	925	0	NR
410	4	NR	540	210	NR	670	96	NR	800	1	NR	930	0	NR
415	7	NR	545	216	NR	675	79	NR	805	1	NR	935	0	NR
420	13	NR	550	222	NR	680	67	NR	810	1	NR	940	0	NR
425	22	NR	555	230	NR	685	58	NR	815	1	NR	945	0	NR
430	37	NR	560	240	NR	690	49	NR	820	1	NR	950	0	NR
435	60	NR	565	248	NR	695	42	NR	825	1	NR	955	0	NR
440	101	NR	570	258	NR	700	36	NR	830	1	NR	960	0	NR
445	172	NR	575	268	NR	705	30	NR	835	1	NR	965	0	NR
450	223	NR	580	278	NR	710	26	NR	840	1	NR	970	0	NR
455	167	NR	585	287	NR	715	22	NR	845	0	NR	975	0	NR
460	126	NR	590	295	NR	720	19	NR	850	0	NR	980	0	NR
465	111	NR	595	298	NR	725	16	NR	855	0	NR	985	0	NR
470	86	NR	600	303	NR	730	14	NR	860	0	NR	990	0	NR
475	74	NR	605	307	NR	735	12	NR	865	0	NR	995	0	NR
480	77	NR	610	341	NR	740	10	NR	870	0	NR	1000	0	NR
485	86	NR	615	368	NR	745	8	NR	875	0	NR			

Summary

$R_f = 91.3$
 $R_g = 102$
 $CIE R_a = 94.4$
 $R_9 = 61.4$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 91	CES51 = 96	CES76 = 89
CES02 = 63	CES27 = 96	CES52 = 95	CES77 = 85
CES03 = 32	CES28 = 96	CES53 = 93	CES78 = 86
CES04 = 70	CES29 = 90	CES54 = 98	CES79 = 89
CES05 = 51	CES30 = 96	CES55 = 98	CES80 = 91
CES06 = 51	CES31 = 90	CES56 = 95	CES81 = 72
CES07 = 44	CES32 = 84	CES57 = 95	CES82 = 95
CES08 = 42	CES33 = 91	CES58 = 95	CES83 = 93
CES09 = 29	CES34 = 92	CES59 = 99	CES84 = 96
CES10 = 76	CES35 = 96	CES60 = 96	CES85 = 80
CES11 = 59	CES36 = 90	CES61 = 96	CES86 = 77
CES12 = 65	CES37 = 94	CES62 = 95	CES87 = 91
CES13 = 44	CES38 = 99	CES63 = 94	CES88 = 96
CES14 = 74	CES39 = 97	CES64 = 96	CES89 = 82
CES15 = 72	CES40 = 94	CES65 = 92	CES90 = 97
CES16 = 48	CES41 = 94	CES66 = 95	CES91 = 82
CES17 = 50	CES42 = 91	CES67 = 94	CES92 = 78
CES18 = 57	CES43 = 88	CES68 = 93	CES93 = 87
CES19 = 72	CES44 = 99	CES69 = 94	CES94 = 73
CES20 = 67	CES45 = 93	CES70 = 90	CES95 = 85
CES21 = 86	CES46 = 93	CES71 = 90	CES96 = 92
CES22 = 79	CES47 = 86	CES72 = 96	CES97 = 93
CES23 = 92	CES48 = 95	CES73 = 85	CES98 = 94
CES24 = 91	CES49 = 91	CES74 = 90	CES99 = 93
CES25 = 72	CES50 = 96	CES75 = 90	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)