

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1431675

Luminaire Tested: EHBR1-18-UNV-A1-L840

Issue Date: 3/13/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1431675  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2601-654-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/13/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: EHBR1-18-UNV-A1-L840  
Description: Elevate Round Highbay at, 18000 lumens, 4000K 80CRI LEDs with A lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 18317.0 lumens  
Efficiency: N/A  
Efficacy: 193.4 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 1.07 / 0.95  
Luminous Opening: Circular (Dia: 1.71' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 94.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1431675  
CATALOG NUMBER: EHBR1-18-UNV-A1-L840

### Luminous Intensity Polar Plot





TEST NUMBER: P1431675  
 CATALOG NUMBER: EHBR1-18-UNV-A1-L840

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100	
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	94	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	87	84	82	80
3	98	90	83	78	95	88	82	78	85	81	77	83	79	75	80	77	74	80	77	74	72
4	91	82	75	70	89	81	75	70	79	73	69	77	72	68	75	71	67	75	71	67	65
5	86	76	69	63	84	75	68	63	73	67	62	71	66	62	69	65	61	69	65	61	60
6	81	70	63	58	79	69	62	58	68	62	57	66	61	57	65	60	56	65	60	56	55
7	76	65	58	53	75	64	58	53	63	57	52	62	56	52	60	56	52	60	56	52	50
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	57	52	48	46
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	53	48	45	43
10	64	53	47	42	63	53	46	42	52	46	42	51	46	42	50	45	42	50	45	42	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	69240	69240	69240	69240	69240
5°	69231	69221	69224	69346	69304
10°	67964	68756	68865	68671	67519
15°	62116	66450	67818	65918	60690
20°	52126	61221	65403	60068	50096
25°	40611	53328	61123	51380	38507
30°	29839	43777	54122	42115	28322
35°	21698	34037	44870	32571	20281
40°	15764	25387	33392	24315	15277
45°	12562	18782	23585	17968	12127
50°	10561	14299	17298	13828	10401
55°	9373	11474	13312	11281	9246
60°	8626	9774	10824	9713	8687
65°	8287	8856	9344	8884	8366
70°	8175	8370	8628	8417	8256
75°	8091	8040	8091	8063	8169
80°	8135	7551	7383	7667	8135
85°	7339	6223	6159	6320	7554

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 67.5°  
 Vertical Angle: 45°  
 Luminance: 24712 cd/sqm



TEST NUMBER: P1431675  
 CATALOG NUMBER: EHBR1-18-UNV-A1-L840

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1392.4	7.6
10°-20°	3742.2	20.4
20°-30°	4550.5	24.8
30°-40°	3706.7	20.2
40°-50°	2225.5	12.1
50°-60°	1280.8	7.0
60°-70°	801.6	4.4
70°-80°	472.1	2.6
80°-90°	138.1	0.8
90°-100°	0.1	0.0
100°-110°	0.1	0.0
110°-120°	0.1	0.0
120°-130°	0.2	0.0
130°-140°	0.9	0.0
140°-150°	1.7	0.0
150°-160°	1.9	0.0
160°-170°	1.7	0.0
170°-180°	0.7	0.0
0°-30°	9685.0	52.9
0°-40°	13391.7	73.1
0°-60°	16898.0	92.3
0°-90°	18309.7	100.0
90°-120°	0.2	0.0
90°-150°	3.1	0.0
90°-180°	7.0	0.0
0°-180°	18317.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	14744	14744	14744	14744	14744	
5°	14686	14684	14685	14711	14702	1388
15°	12776	13668	13949	13558	12483	3515
25°	7838	10292	11796	9916	7432	3571
35°	3785	5937	7827	5682	3538	2395
45°	1892	2828	3551	2706	1826	1492
55°	1145	1401	1626	1378	1129	1035
65°	746	797	841	800	753	741
75°	446	443	446	444	450	472
85°	136	116	114	117	140	145
90°	1	0	0	0	0	7
95°	1	0	0	0	0	0
105°	1	0	0	0	1	1
115°	1	0	0	0	1	1
125°	1	0	0	0	1	1
135°	2	1	1	1	2	1
145°	3	2	2	3	3	2
155°	5	4	3	4	5	2
165°	7	6	5	6	7	2
175°	9	8	7	8	9	1
180°	8	8	8	8	8	



TEST NUMBER: P1431675  
 CATALOG NUMBER: EHBR1-18-UNV-A1-L840

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	14744.2	14744.2	14744.2	14744.2	14744.2	14744.2	14744.2	14744.2	14744.2
2.5°	14711.8	14725.1	14730.6	14733.7	14737.1	14746.4	14750.4	14743.9	14749.5
5°	14686.2	14687.1	14684.0	14697.9	14684.6	14693.9	14710.6	14704.1	14701.6
7.5°	14536.7	14567.6	14585.8	14590.4	14592.9	14604.3	14616.1	14549.7	14539.8
10°	14252.6	14304.2	14418.7	14451.5	14441.6	14460.1	14400.8	14227.3	14159.3
12.5°	13629.7	13811.0	14108.7	14241.2	14217.1	14233.4	14031.5	13665.2	13454.6
15°	12776.5	13042.4	13668.0	13929.3	13949.3	13929.3	13558.4	12844.7	12483.1
17.5°	11642.2	12133.2	13054.4	13561.5	13532.4	13542.0	12837.9	11783.0	11369.2
20°	10430.4	10953.9	12250.3	13096.1	13087.1	13033.4	12019.6	10628.4	10024.3
22.5°	9059.9	9735.0	11328.8	12523.9	12520.5	12430.9	11023.0	9367.5	8717.1
25°	7837.6	8499.7	10291.8	11822.9	11796.3	11694.4	9915.9	8109.7	7431.6
27.5°	6574.0	7262.3	9184.7	11001.4	10983.2	10872.0	8857.6	6934.1	6288.6
30°	5502.7	6132.1	8073.0	10097.5	9980.8	9968.1	7766.6	5845.5	5222.9
32.5°	4584.9	5124.4	7024.8	9152.3	8945.7	9004.6	6679.3	4935.1	4318.1
35°	3784.8	4260.1	5937.2	8059.1	7826.8	7903.1	5681.5	4049.4	3537.7
37.5°	3071.8	3528.8	5015.4	6995.8	6640.7	6784.6	4803.9	3381.8	2971.7
40°	2571.5	2934.0	4141.2	5829.1	5447.1	5681.5	3966.4	2820.7	2492.1
42.5°	2215.7	2452.3	3417.9	4715.2	4422.2	4588.3	3269.1	2358.1	2112.3
45°	1891.5	2080.2	2828.1	3720.9	3551.3	3705.4	2705.5	2010.7	1826.0
47.5°	1652.1	1797.6	2328.1	3004.7	2899.4	2948.2	2259.6	1754.7	1604.6
50°	1445.5	1558.0	1957.2	2425.1	2367.7	2397.6	1892.7	1526.8	1423.6
52.5°	1285.0	1367.4	1641.6	1993.1	1964.7	1969.3	1612.9	1343.0	1268.3
55°	1144.8	1202.2	1401.4	1632.7	1625.9	1627.1	1377.9	1190.2	1129.3
57.5°	1022.2	1069.7	1204.4	1371.4	1361.6	1363.7	1193.2	1057.1	1017.8
60°	918.4	950.2	1040.7	1159.0	1152.5	1149.7	1034.2	938.5	924.9
62.5°	826.4	846.8	909.5	993.4	981.1	983.9	909.1	847.7	827.6
65°	745.8	752.9	797.0	848.9	840.9	847.7	799.5	757.5	752.9
67.5°	667.0	674.1	700.1	735.0	725.7	731.3	700.7	676.0	672.0
70°	595.4	595.1	609.6	628.4	628.4	629.4	613.0	598.2	601.3
72.5°	521.3	519.4	523.7	536.4	533.0	544.7	527.5	522.8	523.4
75°	445.9	440.7	443.1	449.6	445.9	452.1	444.4	450.2	450.2
77.5°	374.9	365.0	361.9	362.9	356.1	365.3	367.2	371.2	380.5
80°	300.8	286.9	279.2	278.9	273.0	278.9	283.5	291.8	300.8
82.5°	223.3	211.2	198.3	195.8	192.1	195.5	201.7	211.5	226.1
85°	136.2	123.5	115.5	111.2	114.3	114.3	117.3	131.2	140.2
87.5°	49.1	42.9	35.2	35.5	36.4	37.7	39.2	49.4	54.0
90°	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.3
92.5°	0.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.3
95°	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.3
97.5°	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.3
100°	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.6
102.5°	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.6
105°	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.6
107.5°	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.6
110°	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.6



TEST NUMBER: P1431675  
 CATALOG NUMBER: EHBR1-18-UNV-A1-L840

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
112.5°	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.6
115°	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.6
117.5°	0.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.6
120°	0.6	0.0	0.0	0.0	0.0	0.0	0.0	0.3	0.6
122.5°	0.9	0.3	0.0	0.0	0.0	0.0	0.0	0.3	0.9
125°	0.9	0.3	0.0	0.0	0.0	0.0	0.3	0.3	0.9
127.5°	0.9	0.3	0.0	0.0	0.0	0.0	0.3	0.6	0.9
130°	0.9	0.6	0.3	0.0	0.3	0.3	0.6	0.6	0.9
132.5°	1.2	0.9	0.9	0.6	0.6	0.9	0.9	1.2	1.2
135°	1.5	1.2	1.2	0.9	1.2	1.2	1.2	1.2	1.5
137.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.9
140°	2.2	1.9	1.9	1.9	1.9	1.9	1.9	2.2	2.2
142.5°	2.5	2.5	2.2	2.2	2.2	2.5	2.5	2.5	2.8
145°	2.8	2.8	2.5	2.5	2.5	2.8	2.8	3.1	3.1
147.5°	3.7	3.4	2.8	2.8	2.8	2.8	3.1	3.4	3.7
150°	4.0	3.7	3.1	3.1	3.1	3.1	3.4	4.0	4.3
152.5°	4.3	4.0	3.4	3.1	3.1	3.1	3.7	4.0	4.6
155°	4.6	4.3	3.7	3.1	3.1	3.4	4.0	4.6	4.9
157.5°	5.6	4.9	4.3	3.7	3.7	4.0	4.6	5.2	5.6
160°	6.2	5.6	4.9	4.3	4.3	4.6	5.2	5.9	6.2
162.5°	6.8	6.2	5.2	4.9	4.6	4.9	5.6	6.5	6.8
165°	7.1	6.5	5.9	5.2	5.2	5.2	6.2	6.8	7.1
167.5°	7.4	7.1	6.2	5.6	5.6	5.6	6.5	7.1	7.4
170°	7.7	7.4	6.5	5.9	5.6	5.9	6.8	7.4	7.7
172.5°	8.3	8.0	7.1	6.5	6.2	6.5	7.4	8.0	8.3
175°	9.3	8.6	8.0	7.1	6.8	7.1	8.0	8.6	9.3
177.5°	9.6	9.0	8.3	7.4	7.1	7.4	8.3	9.0	9.6
180°	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3



TEST NUMBER: P1431675  
 CATALOG NUMBER: EHBR1-18-UNV-A1-L840

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.11	18.37	17.47	18.69	19.00	18.09	19.36	18.46	19.67	19.99
	3H	18.68	19.80	19.06	20.13	20.50	19.43	20.56	19.81	20.89	21.25
	4H	19.34	20.39	19.75	20.74	21.13	19.99	21.04	20.40	21.39	21.78
	6H	19.90	20.86	20.31	21.23	21.63	20.42	21.39	20.84	21.76	22.15
	8H	20.10	21.01	20.53	21.40	21.81	20.56	21.47	20.99	21.86	22.27
	12H	20.23	21.10	20.66	21.48	21.91	20.64	21.51	21.07	21.89	22.33
4H	2H	17.68	18.73	18.08	19.08	19.47	18.45	19.50	18.85	19.85	20.24
	3H	19.47	20.33	19.88	20.74	21.14	20.04	20.90	20.45	21.31	21.71
	4H	20.27	21.04	20.70	21.46	21.90	20.74	21.51	21.17	21.93	22.38
	6H	20.95	21.62	21.41	22.07	22.53	21.31	21.98	21.77	22.42	22.89
	8H	21.20	21.82	21.67	22.27	22.74	21.49	22.12	21.96	22.56	23.04
	12H	21.37	21.92	21.86	22.40	22.88	21.61	22.16	22.10	22.65	23.12
8H	4H	20.55	21.17	21.02	21.62	22.09	20.97	21.59	21.44	22.04	22.51
	6H	21.36	21.87	21.87	22.37	22.85	21.67	22.18	22.17	22.68	23.16
	8H	21.69	22.15	22.22	22.67	23.16	21.93	22.39	22.46	22.90	23.40
	12H	21.95	22.35	22.46	22.84	23.41	22.12	22.52	22.64	23.02	23.59
12H	4H	20.56	21.11	21.05	21.60	22.07	20.98	21.53	21.47	22.02	22.49
	6H	21.41	21.87	21.93	22.38	22.88	21.71	22.17	22.24	22.69	23.18
	8H	21.80	22.20	22.31	22.69	23.27	22.03	22.43	22.55	22.93	23.50

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-1

Test Date: 07/30/2025

Luminaire Tested: EHBR-60-L840-N

Data in this report applies to families of products including EHBR-60-L840-N

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2506-472-1  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 08/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **EHBR-60-L840-N**  
 Description: Elevate Round Highbay at, 60000 lumens, 4000K 80CRI LEDs with N lens

**Spectral Parameters**

CCT (K): 3898  
 CIE u': 0.2263  
 CIE v': 0.5052  
 Duv: 0.0013  
 CIE x: 0.3861  
 CIE y: 0.3831  
 CIE z: 0.2308  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 578  
 Purity: 30.85729  
 Rf: 80.7  
 Rg: 102.1

CRI (Ra):	82.1		
R1:	84.4	R9:	38.5
R2:	83.5	R10:	58.9
R3:	80.8	R11:	83.6
R4:	83.9	R12:	54.2
R5:	82.1	R13:	82.8
R6:	77.3	R14:	88.2
R7:	86.4	R15:	81.2
R8:	78.3		



**Test Conditions**

Stabilization Time: 42M  
 Operation Time: 1H 42M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-1

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-1

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 3898K  
 CIE x = 0.3861  
 CIE y = 0.3831  
 Duv = 0.0013

Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-1

**Photopic Flux vs. Wavelength**



**Photopic Lumens: NR**

$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)
360	0	NR	490	60	NR	620	277	NR	750	6	NR	880	0	NR
365	0	NR	495	87	NR	625	278	NR	755	5	NR	885	0	NR
370	0	NR	500	124	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	168	NR	635	623	NR	765	4	NR	895	0	NR
380	1	NR	510	209	NR	640	162	NR	770	3	NR	900	0	NR
385	1	NR	515	246	NR	645	158	NR	775	3	NR	905	0	NR
390	2	NR	520	273	NR	650	134	NR	780	2	NR	910	0	NR
395	4	NR	525	292	NR	655	109	NR	785	2	NR	915	0	NR
400	5	NR	530	305	NR	660	91	NR	790	2	NR	920	0	NR
405	7	NR	535	313	NR	665	75	NR	795	2	NR	925	0	NR
410	11	NR	540	319	NR	670	70	NR	800	1	NR	930	0	NR
415	21	NR	545	323	NR	675	56	NR	805	1	NR	935	0	NR
420	42	NR	550	326	NR	680	47	NR	810	1	NR	940	0	NR
425	76	NR	555	330	NR	685	41	NR	815	1	NR	945	0	NR
430	125	NR	560	333	NR	690	35	NR	820	1	NR	950	0	NR
435	193	NR	565	336	NR	695	30	NR	825	1	NR	955	0	NR
440	302	NR	570	336	NR	700	26	NR	830	1	NR	960	0	NR
445	432	NR	575	335	NR	705	22	NR	835	1	NR	965	0	NR
450	380	NR	580	332	NR	710	19	NR	840	0	NR	970	0	NR
455	213	NR	585	326	NR	715	16	NR	845	0	NR	975	0	NR
460	147	NR	590	319	NR	720	14	NR	850	0	NR	980	0	NR
465	104	NR	595	307	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	299	NR	730	10	NR	860	0	NR	990	0	NR
475	50	NR	605	291	NR	735	9	NR	865	0	NR	995	0	NR
480	46	NR	610	317	NR	740	8	NR	870	0	NR	1000	0	NR
485	47	NR	615	336	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-1

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: NR**

**S/P: 1.55**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	60	NR	620	277	NR	750	6	NR	880	0	NR
365	0	NR	495	87	NR	625	278	NR	755	5	NR	885	0	NR
370	0	NR	500	124	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	168	NR	635	623	NR	765	4	NR	895	0	NR
380	1	NR	510	209	NR	640	162	NR	770	3	NR	900	0	NR
385	1	NR	515	246	NR	645	158	NR	775	3	NR	905	0	NR
390	2	NR	520	273	NR	650	134	NR	780	2	NR	910	0	NR
395	4	NR	525	292	NR	655	109	NR	785	2	NR	915	0	NR
400	5	NR	530	305	NR	660	91	NR	790	2	NR	920	0	NR
405	7	NR	535	313	NR	665	75	NR	795	2	NR	925	0	NR
410	11	NR	540	319	NR	670	70	NR	800	1	NR	930	0	NR
415	21	NR	545	323	NR	675	56	NR	805	1	NR	935	0	NR
420	42	NR	550	326	NR	680	47	NR	810	1	NR	940	0	NR
425	76	NR	555	330	NR	685	41	NR	815	1	NR	945	0	NR
430	125	NR	560	333	NR	690	35	NR	820	1	NR	950	0	NR
435	193	NR	565	336	NR	695	30	NR	825	1	NR	955	0	NR
440	302	NR	570	336	NR	700	26	NR	830	1	NR	960	0	NR
445	432	NR	575	335	NR	705	22	NR	835	1	NR	965	0	NR
450	380	NR	580	332	NR	710	19	NR	840	0	NR	970	0	NR
455	213	NR	585	326	NR	715	16	NR	845	0	NR	975	0	NR
460	147	NR	590	319	NR	720	14	NR	850	0	NR	980	0	NR
465	104	NR	595	307	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	299	NR	730	10	NR	860	0	NR	990	0	NR
475	50	NR	605	291	NR	735	9	NR	865	0	NR	995	0	NR
480	46	NR	610	317	NR	740	8	NR	870	0	NR	1000	0	NR
485	47	NR	615	336	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.99

$\lambda$ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens $(\phi/\text{nm})$	$\lambda$ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens $(\phi/\text{nm})$	$\lambda$ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens $(\phi/\text{nm})$	$\lambda$ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens $(\phi/\text{nm})$	$\lambda$ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens $(\phi/\text{nm})$
360	0	NR	490	60	NR	620	277	NR	750	6	NR	880	0	NR
365	0	NR	495	87	NR	625	278	NR	755	5	NR	885	0	NR
370	0	NR	500	124	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	168	NR	635	623	NR	765	4	NR	895	0	NR
380	1	NR	510	209	NR	640	162	NR	770	3	NR	900	0	NR
385	1	NR	515	246	NR	645	158	NR	775	3	NR	905	0	NR
390	2	NR	520	273	NR	650	134	NR	780	2	NR	910	0	NR
395	4	NR	525	292	NR	655	109	NR	785	2	NR	915	0	NR
400	5	NR	530	305	NR	660	91	NR	790	2	NR	920	0	NR
405	7	NR	535	313	NR	665	75	NR	795	2	NR	925	0	NR
410	11	NR	540	319	NR	670	70	NR	800	1	NR	930	0	NR
415	21	NR	545	323	NR	675	56	NR	805	1	NR	935	0	NR
420	42	NR	550	326	NR	680	47	NR	810	1	NR	940	0	NR
425	76	NR	555	330	NR	685	41	NR	815	1	NR	945	0	NR
430	125	NR	560	333	NR	690	35	NR	820	1	NR	950	0	NR
435	193	NR	565	336	NR	695	30	NR	825	1	NR	955	0	NR
440	302	NR	570	336	NR	700	26	NR	830	1	NR	960	0	NR
445	432	NR	575	335	NR	705	22	NR	835	1	NR	965	0	NR
450	380	NR	580	332	NR	710	19	NR	840	0	NR	970	0	NR
455	213	NR	585	326	NR	715	16	NR	845	0	NR	975	0	NR
460	147	NR	590	319	NR	720	14	NR	850	0	NR	980	0	NR
465	104	NR	595	307	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	299	NR	730	10	NR	860	0	NR	990	0	NR
475	50	NR	605	291	NR	735	9	NR	865	0	NR	995	0	NR
480	46	NR	610	317	NR	740	8	NR	870	0	NR	1000	0	NR
485	47	NR	615	336	NR	745	7	NR	875	0	NR			

**Summary**

$R_f = 80.7$   
 $R_g = 102.1$   
 CIE  $R_a = 82.1$   
 $R_9 = 38.5$



**Color Vector Graphics**




**Individual Sample Fidelity Index ( $R_{f,i}$ )**

CES01 = 85	CES26 = 69	CES51 = 90	CES76 = 58
CES02 = 61	CES27 = 89	CES52 = 90	CES77 = 76
CES03 = 31	CES28 = 83	CES53 = 80	CES78 = 60
CES04 = 69	CES29 = 66	CES54 = 91	CES79 = 85
CES05 = 48	CES30 = 76	CES55 = 89	CES80 = 79
CES06 = 50	CES31 = 69	CES56 = 79	CES81 = 81
CES07 = 41	CES32 = 62	CES57 = 77	CES82 = 91
CES08 = 40	CES33 = 74	CES58 = 79	CES83 = 88
CES09 = 29	CES34 = 72	CES59 = 93	CES84 = 89
CES10 = 74	CES35 = 84	CES60 = 95	CES85 = 84
CES11 = 57	CES36 = 98	CES61 = 92	CES86 = 82
CES12 = 63	CES37 = 77	CES62 = 89	CES87 = 81
CES13 = 43	CES38 = 83	CES63 = 80	CES88 = 86
CES14 = 74	CES39 = 94	CES64 = 80	CES89 = 79
CES15 = 71	CES40 = 88	CES65 = 77	CES90 = 85
CES16 = 47	CES41 = 89	CES66 = 74	CES91 = 83
CES17 = 49	CES42 = 74	CES67 = 72	CES92 = 77
CES18 = 56	CES43 = 73	CES68 = 78	CES93 = 86
CES19 = 71	CES44 = 98	CES69 = 83	CES94 = 69
CES20 = 65	CES45 = 82	CES70 = 69	CES95 = 80
CES21 = 86	CES46 = 82	CES71 = 64	CES96 = 86
CES22 = 78	CES47 = 80	CES72 = 88	CES97 = 83
CES23 = 91	CES48 = 79	CES73 = 60	CES98 = 81
CES24 = 90	CES49 = 80	CES74 = 98	CES99 = 83
CES25 = 71	CES50 = 89	CES75 = 62	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)