

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number:

Luminaire Tested: EHBR1-24-UNV-TASM-L840-UPL36

Issue Date: 3/20/2026

Test Information

Test Method: LM-79-2019
Report Number: REPORT IS A COMBINATION OF REPORTS P1431713 AND P1431635
Test Lab: INNOVATION CENTER
Issue Date: 3/20/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-24-UNV-TASM-L840-UPL36
Description: Elevate Round Highbay at, 24000 lumens, 4000K 80CRI LEDs with TASM lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 28457.0 lumens
Efficiency: N/A
Efficacy: 181.6 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.84 / 0.9
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 156.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER:
CATALOG NUMBER: EHBR1-24-UNV-TASM-L840-UPL36

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°



TEST NUMBER:

CATALOG NUMBER: EHBR1-24-UNV-TASM-L840-UPL36

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 116 | 116 | 116 | 116 | 112 | 112 | 112 | 112 | 104 | 104 | 104 | 97 | 97 | 97 | 90 | 90 | 90 | 90 | 90 | 90 | 87 |
| 1 | 109 | 105 | 102 | 99 | 105 | 102 | 99 | 96 | 95 | 93 | 91 | 89 | 88 | 86 | 84 | 82 | 81 | 81 | 81 | 81 | 79 |
| 2 | 102 | 96 | 91 | 86 | 98 | 93 | 88 | 84 | 87 | 84 | 81 | 82 | 79 | 77 | 78 | 75 | 73 | 73 | 73 | 73 | 71 |
| 3 | 95 | 87 | 81 | 76 | 92 | 85 | 79 | 75 | 80 | 76 | 72 | 76 | 72 | 69 | 72 | 69 | 67 | 67 | 67 | 67 | 64 |
| 4 | 89 | 80 | 74 | 68 | 86 | 78 | 72 | 67 | 74 | 69 | 65 | 71 | 66 | 63 | 67 | 64 | 61 | 61 | 61 | 61 | 59 |
| 5 | 84 | 74 | 67 | 62 | 81 | 72 | 66 | 61 | 69 | 63 | 59 | 66 | 61 | 58 | 63 | 59 | 56 | 56 | 56 | 56 | 54 |
| 6 | 79 | 68 | 62 | 57 | 76 | 67 | 61 | 56 | 64 | 59 | 54 | 61 | 57 | 53 | 59 | 55 | 52 | 52 | 52 | 52 | 50 |
| 7 | 74 | 64 | 57 | 52 | 72 | 62 | 56 | 51 | 60 | 54 | 50 | 57 | 53 | 49 | 55 | 51 | 48 | 48 | 48 | 48 | 46 |
| 8 | 70 | 59 | 53 | 48 | 68 | 58 | 52 | 47 | 56 | 50 | 47 | 54 | 49 | 46 | 52 | 48 | 45 | 45 | 45 | 45 | 43 |
| 9 | 66 | 56 | 49 | 45 | 65 | 55 | 48 | 44 | 53 | 47 | 43 | 51 | 46 | 42 | 49 | 45 | 42 | 42 | 42 | 42 | 40 |
| 10 | 63 | 52 | 46 | 42 | 61 | 51 | 45 | 41 | 50 | 44 | 40 | 48 | 43 | 40 | 46 | 42 | 39 | 39 | 39 | 39 | 38 |

AVERAGE LUMINANCE (cd/sqm):

| | 0° | 90° | 180° | 270° |
|-----|--------|--------|--------|--------|
| 0° | 104052 | 104052 | 104052 | 104052 |
| 5° | 103419 | 110328 | 103419 | 98052 |
| 10° | 102147 | 113160 | 102147 | 92797 |
| 15° | 99131 | 105162 | 99131 | 85720 |
| 20° | 92712 | 84325 | 92712 | 76352 |
| 25° | 82058 | 58425 | 82058 | 63987 |
| 30° | 66628 | 38010 | 66628 | 47875 |
| 35° | 47788 | 24616 | 47788 | 31871 |
| 40° | 30896 | 16967 | 30896 | 20100 |
| 45° | 19604 | 13142 | 19604 | 14321 |
| 50° | 14558 | 11168 | 14558 | 11929 |
| 55° | 11885 | 10173 | 11885 | 10530 |
| 60° | 10292 | 9691 | 10292 | 9750 |
| 65° | 9382 | 9346 | 9382 | 9307 |
| 70° | 8893 | 9157 | 8893 | 9039 |
| 75° | 8316 | 8858 | 8316 | 8594 |
| 80° | 7305 | 8364 | 7305 | 7818 |
| 85° | 4728 | 5970 | 4728 | 5694 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 27561 cd/sqm



TEST NUMBER:

CATALOG NUMBER: EHBR1-24-UNV-TASM-L840-UPL36

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 2106.8 | 7.4 |
| 10°-20° | 5731.7 | 20.1 |
| 20°-30° | 6722.1 | 23.6 |
| 30°-40° | 4674.8 | 16.4 |
| 40°-50° | 2323.2 | 8.2 |
| 50°-60° | 1389.5 | 4.9 |
| 60°-70° | 978.0 | 3.4 |
| 70°-80° | 630.0 | 2.2 |
| 80°-90° | 206.6 | 0.7 |
| 90°-100° | 98.1 | 0.3 |
| 100°-110° | 643.2 | 2.3 |
| 110°-120° | 1188.8 | 4.2 |
| 120°-130° | 706.1 | 2.5 |
| 130°-140° | 426.4 | 1.5 |
| 140°-150° | 294.5 | 1.0 |
| 150°-160° | 191.6 | 0.7 |
| 160°-170° | 109.5 | 0.4 |
| 170°-180° | 36.3 | 0.1 |
| 0°-30° | 14560.6 | 51.2 |
| 0°-40° | 19235.4 | 67.6 |
| 0°-60° | 22948.0 | 80.6 |
| 0°-90° | 24762.6 | 87.0 |
| 90°-120° | 1930.0 | 6.8 |
| 90°-150° | 3357.1 | 11.8 |
| 90°-180° | 3694.0 | 13.0 |
| 0°-180° | 28457.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | 90° | 180° | 270° | 360° | Flux |
|------|-------|-------|-------|-------|-------|------|
| 0° | 22157 | 22157 | 22157 | 22157 | 22157 | |
| 5° | 22082 | 23557 | 22082 | 20936 | 22082 | 2096 |
| 15° | 20797 | 22062 | 20797 | 17984 | 20797 | 5812 |
| 25° | 16387 | 11668 | 16387 | 12778 | 16387 | 7419 |
| 35° | 8771 | 4518 | 8771 | 5850 | 8771 | 5475 |
| 45° | 3172 | 2126 | 3172 | 2317 | 3172 | 2595 |
| 55° | 1606 | 1375 | 1606 | 1423 | 1606 | 1469 |
| 65° | 979 | 976 | 979 | 971 | 979 | 984 |
| 75° | 586 | 624 | 586 | 605 | 586 | 615 |
| 85° | 162 | 205 | 162 | 196 | 162 | 181 |
| 90° | 27 | 30 | 27 | 27 | 27 | 20 |
| 95° | 52 | 48 | 52 | 45 | 52 | 55 |
| 105° | 295 | 149 | 295 | 224 | 295 | 398 |
| 115° | 1265 | 1080 | 1265 | 1028 | 1265 | 1153 |
| 125° | 810 | 847 | 810 | 742 | 810 | 745 |
| 135° | 511 | 590 | 511 | 542 | 511 | 405 |
| 145° | 461 | 482 | 461 | 448 | 461 | 289 |
| 155° | 410 | 427 | 410 | 396 | 410 | 191 |
| 165° | 384 | 394 | 384 | 376 | 384 | 109 |
| 175° | 381 | 386 | 381 | 374 | 381 | 36 |
| 180° | 380 | 380 | 380 | 380 | 380 | |



TEST NUMBER:
 CATALOG NUMBER: EHBR1-24-UNV-TASM-L840-UPL36

CANDELA DISTRIBUTION (FULL):

| | 0° | 22.5° | 45° | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° | 202.5° | 225° |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 22157.1 | 22157.1 | 22157.1 | 22157.1 | 22157.1 | 22157.1 | 22157.1 | 22157.1 | 22157.1 | 22157.1 | 22157.1 |
| 2.5° | 22144.2 | 22430.5 | 22662.3 | 22815.2 | 22890.8 | 22815.2 | 22662.3 | 22430.5 | 22144.2 | 21859.6 | 21663.9 |
| 5° | 22081.5 | 22654.8 | 23140.5 | 23458.4 | 23556.8 | 23458.4 | 23140.5 | 22654.8 | 22081.5 | 21539.7 | 21180.3 |
| 7.5° | 21931.5 | 22824.8 | 23546.4 | 23917.5 | 24008.0 | 23917.5 | 23546.4 | 22824.8 | 21931.5 | 21164.5 | 20710.4 |
| 10° | 21702.6 | 22932.0 | 23765.8 | 24031.7 | 24042.5 | 24031.7 | 23765.8 | 22932.0 | 21702.6 | 20669.3 | 20133.7 |
| 12.5° | 21337.3 | 22893.7 | 23692.3 | 23605.0 | 23406.8 | 23605.0 | 23692.3 | 22893.7 | 21337.3 | 20064.3 | 19388.8 |
| 15° | 20797.2 | 22667.3 | 23226.5 | 22516.5 | 22062.4 | 22516.5 | 23226.5 | 22667.3 | 20797.2 | 19247.5 | 18463.9 |
| 17.5° | 20036.1 | 22243.5 | 22254.3 | 20849.6 | 19992.9 | 20849.6 | 22254.3 | 22243.5 | 20036.1 | 18248.7 | 17385.7 |
| 20° | 19055.1 | 21563.8 | 20915.6 | 18346.3 | 17331.3 | 18346.3 | 20915.6 | 21563.8 | 19055.1 | 17067.9 | 16221.1 |
| 22.5° | 17825.3 | 20647.2 | 19051.4 | 15828.1 | 14443.3 | 15828.1 | 19051.4 | 20647.2 | 17825.3 | 15694.7 | 14813.5 |
| 25° | 16386.9 | 19524.2 | 17045.9 | 13084.3 | 11667.5 | 13084.3 | 17045.9 | 19524.2 | 16386.9 | 14058.6 | 13261.7 |
| 27.5° | 14695.1 | 18100.8 | 14910.3 | 10691.9 | 9384.8 | 10691.9 | 14910.3 | 18100.8 | 14695.1 | 12369.2 | 11555.3 |
| 30° | 12815.9 | 16276.0 | 12687.9 | 8514.8 | 7311.2 | 8514.8 | 12687.9 | 16276.0 | 12815.9 | 10471.3 | 9742.6 |
| 32.5° | 10711.9 | 14487.3 | 10553.6 | 6822.6 | 5803.0 | 6822.6 | 10553.6 | 14487.3 | 10711.9 | 8660.2 | 7898.7 |
| 35° | 8770.8 | 12249.6 | 8629.1 | 5360.9 | 4517.9 | 5360.9 | 8629.1 | 12249.6 | 8770.8 | 6950.6 | 6202.7 |
| 37.5° | 6883.2 | 10135.2 | 6878.7 | 4316.8 | 3664.5 | 4316.8 | 6878.7 | 10135.2 | 6883.2 | 5403.7 | 4796.7 |
| 40° | 5355.1 | 7924.8 | 5389.6 | 3446.0 | 2940.8 | 3446.0 | 5389.6 | 7924.8 | 5355.1 | 4111.6 | 3723.1 |
| 42.5° | 4057.6 | 6059.8 | 4236.2 | 2828.2 | 2497.9 | 2828.2 | 4236.2 | 6059.8 | 4057.6 | 3239.5 | 2948.7 |
| 45° | 3171.8 | 4459.3 | 3308.0 | 2386.1 | 2126.4 | 2386.1 | 3308.0 | 4459.3 | 3171.8 | 2608.8 | 2413.5 |
| 47.5° | 2583.0 | 3446.4 | 2681.1 | 2046.7 | 1864.7 | 2046.7 | 2681.1 | 3446.4 | 2583.0 | 2206.6 | 2060.4 |
| 50° | 2169.6 | 2644.5 | 2226.1 | 1786.6 | 1664.4 | 1786.6 | 2226.1 | 2644.5 | 2169.6 | 1889.6 | 1792.0 |
| 52.5° | 1863.8 | 2156.8 | 1895.8 | 1592.1 | 1509.9 | 1592.1 | 1895.8 | 2156.8 | 1863.8 | 1653.2 | 1592.5 |
| 55° | 1606.2 | 1813.2 | 1648.6 | 1431.7 | 1374.8 | 1431.7 | 1648.6 | 1813.2 | 1606.2 | 1471.2 | 1426.3 |
| 57.5° | 1410.6 | 1538.1 | 1431.7 | 1295.0 | 1257.2 | 1295.0 | 1431.7 | 1538.1 | 1410.6 | 1309.2 | 1285.1 |
| 60° | 1237.3 | 1332.0 | 1263.5 | 1175.8 | 1165.0 | 1175.8 | 1263.5 | 1332.0 | 1237.3 | 1177.9 | 1162.1 |
| 62.5° | 1103.9 | 1163.8 | 1117.2 | 1068.6 | 1059.1 | 1068.6 | 1117.2 | 1163.8 | 1103.9 | 1058.2 | 1061.1 |
| 65° | 979.3 | 1035.0 | 998.4 | 972.2 | 975.5 | 972.2 | 998.4 | 1035.0 | 979.3 | 958.1 | 962.7 |
| 67.5° | 882.9 | 912.0 | 896.2 | 881.2 | 885.0 | 881.2 | 896.2 | 912.0 | 882.9 | 862.1 | 869.2 |
| 70° | 780.3 | 811.4 | 795.2 | 797.3 | 803.5 | 797.3 | 795.2 | 811.4 | 780.3 | 774.0 | 779.4 |
| 72.5° | 682.2 | 706.3 | 700.9 | 705.9 | 712.5 | 705.9 | 700.9 | 706.3 | 682.2 | 681.4 | 681.8 |
| 75° | 585.8 | 604.1 | 606.6 | 613.7 | 624.0 | 613.7 | 606.6 | 604.1 | 585.8 | 579.6 | 587.1 |
| 77.5° | 480.7 | 501.5 | 509.4 | 518.9 | 534.3 | 518.9 | 509.4 | 501.5 | 480.7 | 484.9 | 488.6 |
| 80° | 384.3 | 393.9 | 411.3 | 418.4 | 440.0 | 418.4 | 411.3 | 393.9 | 384.3 | 377.3 | 382.7 |
| 82.5° | 281.3 | 290.0 | 305.0 | 318.3 | 330.7 | 318.3 | 305.0 | 290.0 | 281.3 | 278.0 | 278.4 |
| 85° | 162.5 | 175.7 | 185.7 | 201.5 | 205.2 | 201.5 | 185.7 | 175.7 | 162.5 | 166.2 | 162.5 |
| 87.5° | 56.9 | 61.1 | 69.8 | 76.0 | 76.4 | 76.0 | 69.8 | 61.1 | 56.9 | 58.2 | 52.8 |
| 90° | 27.0 | 45.8 | 78.9 | 43.4 | 29.9 | 43.4 | 78.9 | 45.8 | 27.0 | 47.4 | 74.0 |
| 92.5° | 35.2 | 62.2 | 111.7 | 57.7 | 40.1 | 57.7 | 111.7 | 62.2 | 35.2 | 61.8 | 119.0 |
| 95° | 51.9 | 76.5 | 142.3 | 63.9 | 48.3 | 63.9 | 142.3 | 76.5 | 51.9 | 82.2 | 166.1 |
| 97.5° | 80.6 | 94.9 | 160.7 | 68.0 | 58.5 | 68.0 | 160.7 | 94.9 | 80.6 | 100.6 | 190.6 |
| 100° | 107.2 | 107.2 | 293.7 | 78.2 | 66.7 | 78.2 | 293.7 | 107.2 | 107.2 | 123.5 | 297.0 |
| 102.5° | 162.4 | 209.8 | 680.8 | 156.3 | 81.0 | 156.3 | 680.8 | 209.8 | 162.4 | 231.9 | 630.4 |
| 105° | 295.3 | 479.8 | 1198.3 | 403.8 | 148.9 | 403.8 | 1198.3 | 479.8 | 295.3 | 485.6 | 1123.3 |
| 107.5° | 559.2 | 895.0 | 1543.9 | 796.5 | 347.3 | 796.5 | 1543.9 | 895.0 | 559.2 | 859.9 | 1481.7 |
| 110° | 894.6 | 1250.9 | 1685.1 | 1091.1 | 703.2 | 1091.1 | 1685.1 | 1250.9 | 894.6 | 1181.0 | 1553.3 |



TEST NUMBER:

CATALOG NUMBER: EHBR1-24-UNV-TASM-L840-UPL36

CANDELA DISTRIBUTION (continued):

| | 0° | 22.5° | 45° | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° | 202.5° | 225° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 1164.6 | 1394.1 | 1646.2 | 1209.7 | 973.2 | 1209.7 | 1646.2 | 1394.1 | 1164.6 | 1303.7 | 1487.8 |
| 115° | 1265.3 | 1373.7 | 1470.3 | 1205.6 | 1079.6 | 1205.6 | 1470.3 | 1373.7 | 1265.3 | 1273.0 | 1328.3 |
| 117.5° | 1222.3 | 1257.1 | 1269.8 | 1132.0 | 1085.7 | 1132.0 | 1269.8 | 1257.1 | 1222.3 | 1144.6 | 1127.8 |
| 120° | 1103.7 | 1089.4 | 1069.8 | 1023.6 | 1024.4 | 1023.6 | 1069.8 | 1089.4 | 1103.7 | 999.4 | 941.7 |
| 122.5° | 954.9 | 924.2 | 904.1 | 913.5 | 940.5 | 913.5 | 904.1 | 924.2 | 954.9 | 850.5 | 807.1 |
| 125° | 809.6 | 779.0 | 787.9 | 819.4 | 846.9 | 819.4 | 787.9 | 779.0 | 809.6 | 722.1 | 711.5 |
| 127.5° | 687.3 | 673.0 | 704.1 | 739.6 | 763.0 | 739.6 | 704.1 | 673.0 | 687.3 | 632.1 | 644.0 |
| 130° | 599.8 | 603.4 | 644.8 | 674.6 | 689.4 | 674.6 | 644.8 | 603.4 | 599.8 | 573.2 | 601.4 |
| 132.5° | 544.9 | 560.9 | 600.2 | 626.0 | 634.6 | 626.0 | 600.2 | 560.9 | 544.9 | 537.1 | 571.5 |
| 135° | 510.6 | 534.3 | 569.9 | 586.6 | 589.6 | 586.6 | 569.9 | 534.3 | 510.6 | 513.0 | 544.9 |
| 137.5° | 490.5 | 514.2 | 541.2 | 554.4 | 550.7 | 554.4 | 541.2 | 514.2 | 490.5 | 497.1 | 521.2 |
| 140° | 478.7 | 502.4 | 514.6 | 529.9 | 526.6 | 529.9 | 514.6 | 502.4 | 478.7 | 482.8 | 501.2 |
| 142.5° | 466.9 | 488.5 | 494.6 | 505.7 | 502.0 | 505.7 | 494.6 | 488.5 | 466.9 | 471.0 | 483.2 |
| 145° | 461.1 | 477.1 | 472.6 | 487.3 | 482.0 | 487.3 | 472.6 | 477.1 | 461.1 | 462.8 | 469.3 |
| 147.5° | 450.9 | 462.8 | 456.6 | 469.3 | 464.0 | 469.3 | 456.6 | 462.8 | 450.9 | 450.9 | 453.3 |
| 150° | 439.0 | 447.2 | 438.6 | 453.3 | 452.1 | 453.3 | 438.6 | 447.2 | 439.0 | 437.0 | 439.4 |
| 152.5° | 423.1 | 431.2 | 423.1 | 439.8 | 438.2 | 439.8 | 423.1 | 431.2 | 423.1 | 421.0 | 423.5 |
| 155° | 409.5 | 413.6 | 409.5 | 426.4 | 426.8 | 426.4 | 409.5 | 413.6 | 409.5 | 409.1 | 410.0 |
| 157.5° | 400.2 | 402.7 | 400.6 | 415.3 | 415.7 | 415.3 | 400.6 | 402.7 | 400.2 | 400.2 | 400.6 |
| 160° | 391.6 | 395.7 | 394.1 | 406.8 | 407.2 | 406.8 | 394.1 | 395.7 | 391.6 | 393.2 | 393.6 |
| 162.5° | 388.4 | 388.4 | 387.2 | 399.8 | 400.6 | 399.8 | 387.2 | 388.4 | 388.4 | 388.4 | 390.4 |
| 165° | 383.5 | 385.5 | 382.2 | 391.3 | 394.1 | 391.3 | 382.2 | 385.5 | 383.5 | 385.1 | 385.1 |
| 167.5° | 382.2 | 380.2 | 381.1 | 388.4 | 391.4 | 388.4 | 381.1 | 380.2 | 382.2 | 383.9 | 383.9 |
| 170° | 378.6 | 379.0 | 377.8 | 385.2 | 388.1 | 385.2 | 377.8 | 379.0 | 378.6 | 380.7 | 382.2 |
| 172.5° | 379.8 | 379.8 | 377.0 | 382.3 | 387.2 | 382.3 | 377.0 | 379.8 | 379.8 | 381.5 | 383.5 |
| 175° | 380.6 | 379.1 | 377.8 | 381.1 | 386.1 | 381.1 | 377.8 | 379.1 | 380.6 | 380.2 | 380.2 |
| 177.5° | 378.6 | 379.5 | 380.3 | 383.6 | 390.6 | 383.6 | 380.3 | 379.5 | 378.6 | 380.2 | 380.2 |
| 180° | 379.5 | 379.5 | 379.5 | 379.5 | 379.5 | 379.5 | 379.5 | 379.5 | 379.5 | 379.5 | 379.5 |



TEST NUMBER:

CATALOG NUMBER: EHBR1-24-UNV-TASM-L840-UPL36

CANDELA DISTRIBUTION (continued):

| | 247.5° | 270° | 292.5° | 315° | 337.5° | 360° |
|--------|---------|---------|---------|---------|---------|---------|
| 0° | 22157.1 | 22157.1 | 22157.1 | 22157.1 | 22157.1 | 22157.1 |
| 2.5° | 21513.5 | 21499.4 | 21513.5 | 21663.9 | 21859.6 | 22144.2 |
| 5° | 21013.7 | 20935.6 | 21013.7 | 21180.3 | 21539.7 | 22081.5 |
| 7.5° | 20431.6 | 20386.3 | 20431.6 | 20710.4 | 21164.5 | 21931.5 |
| 10° | 19818.8 | 19716.1 | 19818.8 | 20133.7 | 20669.3 | 21702.6 |
| 12.5° | 19063.4 | 18927.6 | 19063.4 | 19388.8 | 20064.3 | 21337.3 |
| 15° | 18102.8 | 17983.6 | 18102.8 | 18463.9 | 19247.5 | 20797.2 |
| 17.5° | 17072.0 | 16964.0 | 17072.0 | 17385.7 | 18248.7 | 20036.1 |
| 20° | 15777.4 | 15692.6 | 15777.4 | 16221.1 | 17067.9 | 19055.1 |
| 22.5° | 14419.2 | 14339.8 | 14419.2 | 14813.5 | 15694.7 | 17825.3 |
| 25° | 12821.3 | 12778.1 | 12821.3 | 13261.7 | 14058.6 | 16386.9 |
| 27.5° | 11094.5 | 11021.0 | 11094.5 | 11555.3 | 12369.2 | 14695.1 |
| 30° | 9330.4 | 9208.7 | 9330.4 | 9742.6 | 10471.3 | 12815.9 |
| 32.5° | 7604.9 | 7517.3 | 7604.9 | 7898.7 | 8660.2 | 10711.9 |
| 35° | 5937.2 | 5849.5 | 5937.2 | 6202.7 | 6950.6 | 8770.8 |
| 37.5° | 4626.4 | 4471.4 | 4626.4 | 4796.7 | 5403.7 | 6883.2 |
| 40° | 3508.7 | 3483.8 | 3508.7 | 3723.1 | 4111.6 | 5355.1 |
| 42.5° | 2856.4 | 2788.7 | 2856.4 | 2948.7 | 3239.5 | 4057.6 |
| 45° | 2343.7 | 2317.1 | 2343.7 | 2413.5 | 2608.8 | 3171.8 |
| 47.5° | 2015.5 | 2027.1 | 2015.5 | 2060.4 | 2206.6 | 2583.0 |
| 50° | 1770.8 | 1777.8 | 1770.8 | 1792.0 | 1889.6 | 2169.6 |
| 52.5° | 1590.5 | 1584.2 | 1590.5 | 1592.5 | 1653.2 | 1863.8 |
| 55° | 1430.9 | 1423.0 | 1430.9 | 1426.3 | 1471.2 | 1606.2 |
| 57.5° | 1291.3 | 1297.1 | 1291.3 | 1285.1 | 1309.2 | 1410.6 |
| 60° | 1166.7 | 1172.1 | 1166.7 | 1162.1 | 1177.9 | 1237.3 |
| 62.5° | 1061.5 | 1064.9 | 1061.5 | 1061.1 | 1058.2 | 1103.9 |
| 65° | 967.7 | 971.4 | 967.7 | 962.7 | 958.1 | 979.3 |
| 67.5° | 877.9 | 877.9 | 877.9 | 869.2 | 862.1 | 882.9 |
| 70° | 793.6 | 793.1 | 793.6 | 779.4 | 774.0 | 780.3 |
| 72.5° | 692.2 | 702.2 | 692.2 | 681.8 | 681.4 | 682.2 |
| 75° | 593.7 | 605.4 | 593.7 | 587.1 | 579.6 | 585.8 |
| 77.5° | 494.0 | 511.9 | 494.0 | 488.6 | 484.9 | 480.7 |
| 80° | 391.8 | 411.3 | 391.8 | 382.7 | 377.3 | 384.3 |
| 82.5° | 289.6 | 304.1 | 289.6 | 278.4 | 278.0 | 281.3 |
| 85° | 172.4 | 195.7 | 172.4 | 162.5 | 166.2 | 162.5 |
| 87.5° | 55.3 | 70.6 | 55.3 | 52.8 | 58.2 | 56.9 |
| 90° | 43.4 | 27.0 | 43.4 | 74.0 | 47.4 | 27.0 |
| 92.5° | 65.9 | 39.3 | 65.9 | 119.0 | 61.8 | 35.2 |
| 95° | 76.1 | 45.4 | 76.1 | 166.1 | 82.2 | 51.9 |
| 97.5° | 84.3 | 58.1 | 84.3 | 190.6 | 100.6 | 80.6 |
| 100° | 98.6 | 76.5 | 98.6 | 297.0 | 123.5 | 107.2 |
| 102.5° | 209.0 | 129.7 | 209.0 | 630.4 | 231.9 | 162.4 |
| 105° | 440.2 | 223.7 | 440.2 | 1123.3 | 485.6 | 295.3 |
| 107.5° | 787.9 | 387.4 | 787.9 | 1481.7 | 859.9 | 559.2 |
| 110° | 1045.6 | 722.8 | 1045.6 | 1553.3 | 1181.0 | 894.6 |



TEST NUMBER:

CATALOG NUMBER: EHBR1-24-UNV-TASM-L840-UPL36

CANDELA DISTRIBUTION (continued):

| | 247.5° | 270° | 292.5° | 315° | 337.5° | 360° |
|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 1123.3 | 976.5 | 1123.3 | 1487.8 | 1303.7 | 1164.6 |
| 115° | 1080.4 | 1027.6 | 1080.4 | 1328.3 | 1273.0 | 1265.3 |
| 117.5° | 986.3 | 992.8 | 986.3 | 1127.8 | 1144.6 | 1222.3 |
| 120° | 877.9 | 919.2 | 877.9 | 941.7 | 999.4 | 1103.7 |
| 122.5° | 778.1 | 827.1 | 778.1 | 807.1 | 850.5 | 954.9 |
| 125° | 692.1 | 741.6 | 692.1 | 711.5 | 722.1 | 809.6 |
| 127.5° | 632.8 | 666.0 | 632.8 | 644.0 | 632.1 | 687.3 |
| 130° | 586.2 | 614.8 | 586.2 | 601.4 | 573.2 | 599.8 |
| 132.5° | 554.0 | 572.4 | 554.0 | 571.5 | 537.1 | 544.9 |
| 135° | 525.7 | 541.7 | 525.7 | 544.9 | 513.0 | 510.6 |
| 137.5° | 501.6 | 515.5 | 501.6 | 521.2 | 497.1 | 490.5 |
| 140° | 479.9 | 491.8 | 479.9 | 501.2 | 482.8 | 478.7 |
| 142.5° | 457.8 | 466.0 | 457.8 | 483.2 | 471.0 | 466.9 |
| 145° | 442.3 | 448.5 | 442.3 | 469.3 | 462.8 | 461.1 |
| 147.5° | 428.8 | 432.9 | 428.8 | 453.3 | 450.9 | 450.9 |
| 150° | 415.3 | 419.4 | 415.3 | 439.4 | 437.0 | 439.0 |
| 152.5° | 401.4 | 406.0 | 401.4 | 423.5 | 421.0 | 423.1 |
| 155° | 392.0 | 396.5 | 392.0 | 410.0 | 409.1 | 409.5 |
| 157.5° | 386.7 | 389.5 | 386.7 | 400.6 | 400.2 | 400.2 |
| 160° | 381.9 | 384.3 | 381.9 | 393.6 | 393.2 | 391.6 |
| 162.5° | 376.5 | 379.0 | 376.5 | 390.4 | 388.4 | 388.4 |
| 165° | 375.3 | 375.7 | 375.3 | 385.1 | 385.1 | 383.5 |
| 167.5° | 373.6 | 375.7 | 373.6 | 383.9 | 383.9 | 382.2 |
| 170° | 374.0 | 374.5 | 374.0 | 382.2 | 380.7 | 378.6 |
| 172.5° | 374.9 | 375.3 | 374.9 | 383.5 | 381.5 | 379.8 |
| 175° | 373.7 | 374.1 | 373.7 | 380.2 | 380.2 | 380.6 |
| 177.5° | 376.1 | 376.5 | 376.1 | 380.2 | 380.2 | 378.6 |
| 180° | 379.5 | 379.5 | 379.5 | 379.5 | 379.5 | 379.5 |



TEST NUMBER: CATALOG
 CATALOG NUMBER: EHBR1-24-UNV-TASM-L840-UPL36

CIE UGR TABLE:

| Reflectances: | | | | | | | | | | | |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|-------|-------|-------|-------|
| Ceiling | | 0.7 | 0.7 | 0.5 | 0.5 | 0.3 | 0.7 | 0.7 | 0.5 | 0.5 | 0.3 |
| Wall | | 0.5 | 0.3 | 0.5 | 0.3 | 0.3 | 0.5 | 0.3 | 0.5 | 0.3 | 0.3 |
| Reference plane | | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 |
| Room dimensions | | Viewed crosswise | | | | | Viewed endwise | | | | |
| X=2H | Y=2H | 16.28 | 17.30 | 16.86 | 17.86 | 18.49 | 15.60 | 16.62 | 16.18 | 17.18 | 17.81 |
| | 3H | 17.82 | 18.73 | 18.42 | 19.31 | 19.98 | 17.44 | 18.35 | 18.04 | 18.93 | 19.60 |
| | 4H | 18.45 | 19.31 | 19.07 | 19.90 | 20.58 | 18.22 | 19.07 | 18.83 | 19.66 | 20.35 |
| | 6H | 18.93 | 19.72 | 19.56 | 20.32 | 21.02 | 18.86 | 19.64 | 19.49 | 20.25 | 20.94 |
| | 8H | 19.08 | 19.82 | 19.72 | 20.45 | 21.15 | 19.08 | 19.82 | 19.72 | 20.44 | 21.15 |
| | 12H | 19.15 | 19.86 | 19.79 | 20.48 | 21.20 | 19.20 | 19.91 | 19.85 | 20.53 | 21.25 |
| 4H | 2H | 16.68 | 17.54 | 17.30 | 18.13 | 18.82 | 16.16 | 17.02 | 16.78 | 17.61 | 18.29 |
| | 3H | 18.48 | 19.18 | 19.11 | 19.82 | 20.52 | 18.22 | 18.92 | 18.84 | 19.56 | 20.26 |
| | 4H | 19.25 | 19.89 | 19.90 | 20.53 | 21.26 | 19.12 | 19.76 | 19.77 | 20.40 | 21.14 |
| | 6H | 19.86 | 20.41 | 20.53 | 21.08 | 21.83 | 19.89 | 20.44 | 20.56 | 21.10 | 21.86 |
| | 8H | 20.06 | 20.57 | 20.73 | 21.23 | 21.99 | 20.16 | 20.67 | 20.83 | 21.33 | 22.09 |
| | 12H | 20.16 | 20.61 | 20.85 | 21.30 | 22.07 | 20.33 | 20.78 | 21.02 | 21.47 | 22.23 |
| 8H | 4H | 19.50 | 20.01 | 20.17 | 20.67 | 21.43 | 19.40 | 19.91 | 20.07 | 20.57 | 21.33 |
| | 6H | 20.24 | 20.65 | 20.94 | 21.36 | 22.12 | 20.30 | 20.72 | 21.00 | 21.43 | 22.19 |
| | 8H | 20.51 | 20.88 | 21.23 | 21.59 | 22.37 | 20.66 | 21.03 | 21.38 | 21.74 | 22.52 |
| | 12H | 20.68 | 21.00 | 21.39 | 21.70 | 22.55 | 20.90 | 21.23 | 21.62 | 21.92 | 22.77 |
| 12H | 4H | 19.50 | 19.96 | 20.19 | 20.65 | 21.41 | 19.41 | 19.86 | 20.10 | 20.55 | 21.31 |
| | 6H | 20.28 | 20.65 | 21.00 | 21.37 | 22.14 | 20.35 | 20.72 | 21.07 | 21.43 | 22.21 |
| | 8H | 20.60 | 20.92 | 21.31 | 21.62 | 22.46 | 20.75 | 21.07 | 21.46 | 21.77 | 22.62 |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-1

Test Date: 07/30/2025

Luminaire Tested: EHBR-60-L840-N

Data in this report applies to families of products including EHBR-60-L840-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-1
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L840-N**
 Description: Elevate Round Highbay at, 60000 lumens, 4000K 80CRI LEDs with N lens

Spectral Parameters

CCT (K): 3898
 CIE u': 0.2263
 CIE v': 0.5052
 Duv: 0.0013
 CIE x: 0.3861
 CIE y: 0.3831
 CIE z: 0.2308
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 578
 Purity: 30.85729
 Rf: 80.7
 Rg: 102.1

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 82.1 | | |
| R1: | 84.4 | R9: | 38.5 |
| R2: | 83.5 | R10: | 58.9 |
| R3: | 80.8 | R11: | 83.6 |
| R4: | 83.9 | R12: | 54.2 |
| R5: | 82.1 | R13: | 82.8 |
| R6: | 77.3 | R14: | 88.2 |
| R7: | 86.4 | R15: | 81.2 |
| R8: | 78.3 | | |



Test Conditions


Stabilization Time: 42M
 Operation Time: 1H 42M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-1


| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | 76INCH SPHERE IN0058 | 6/16/2025 | 12/16/2025 |
| Power Meter | XITRON INXT2011004 | 1/21/2025 | 1/21/2026 |
| AC Power Source | CHROMA 61603 IN0063 | 10/22/2024 | 10/22/2025 |
| DC Power Source | AGILENT E3634A IN0208 | 10/22/2024 | 10/22/2025 |
| Sphere Thermometer | ONSET IN0085 | 10/22/2024 | 10/22/2025 |
| Room Thermometer | ONSET IN0046 | 10/22/2024 | 10/22/2025 |

REPORT NUMBER: SP1-2506-472-1

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-1

Photopic Flux vs. Wavelength



Photopic Lumens: NR

| λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) |
|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|
| 360 | 0 | NR | 490 | 60 | NR | 620 | 277 | NR | 750 | 6 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 87 | NR | 625 | 278 | NR | 755 | 5 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 124 | NR | 630 | 1000 | NR | 760 | 4 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 168 | NR | 635 | 623 | NR | 765 | 4 | NR | 895 | 0 | NR |
| 380 | 1 | NR | 510 | 209 | NR | 640 | 162 | NR | 770 | 3 | NR | 900 | 0 | NR |
| 385 | 1 | NR | 515 | 246 | NR | 645 | 158 | NR | 775 | 3 | NR | 905 | 0 | NR |
| 390 | 2 | NR | 520 | 273 | NR | 650 | 134 | NR | 780 | 2 | NR | 910 | 0 | NR |
| 395 | 4 | NR | 525 | 292 | NR | 655 | 109 | NR | 785 | 2 | NR | 915 | 0 | NR |
| 400 | 5 | NR | 530 | 305 | NR | 660 | 91 | NR | 790 | 2 | NR | 920 | 0 | NR |
| 405 | 7 | NR | 535 | 313 | NR | 665 | 75 | NR | 795 | 2 | NR | 925 | 0 | NR |
| 410 | 11 | NR | 540 | 319 | NR | 670 | 70 | NR | 800 | 1 | NR | 930 | 0 | NR |
| 415 | 21 | NR | 545 | 323 | NR | 675 | 56 | NR | 805 | 1 | NR | 935 | 0 | NR |
| 420 | 42 | NR | 550 | 326 | NR | 680 | 47 | NR | 810 | 1 | NR | 940 | 0 | NR |
| 425 | 76 | NR | 555 | 330 | NR | 685 | 41 | NR | 815 | 1 | NR | 945 | 0 | NR |
| 430 | 125 | NR | 560 | 333 | NR | 690 | 35 | NR | 820 | 1 | NR | 950 | 0 | NR |
| 435 | 193 | NR | 565 | 336 | NR | 695 | 30 | NR | 825 | 1 | NR | 955 | 0 | NR |
| 440 | 302 | NR | 570 | 336 | NR | 700 | 26 | NR | 830 | 1 | NR | 960 | 0 | NR |
| 445 | 432 | NR | 575 | 335 | NR | 705 | 22 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 380 | NR | 580 | 332 | NR | 710 | 19 | NR | 840 | 0 | NR | 970 | 0 | NR |
| 455 | 213 | NR | 585 | 326 | NR | 715 | 16 | NR | 845 | 0 | NR | 975 | 0 | NR |
| 460 | 147 | NR | 590 | 319 | NR | 720 | 14 | NR | 850 | 0 | NR | 980 | 0 | NR |
| 465 | 104 | NR | 595 | 307 | NR | 725 | 12 | NR | 855 | 0 | NR | 985 | 0 | NR |
| 470 | 65 | NR | 600 | 299 | NR | 730 | 10 | NR | 860 | 0 | NR | 990 | 0 | NR |
| 475 | 50 | NR | 605 | 291 | NR | 735 | 9 | NR | 865 | 0 | NR | 995 | 0 | NR |
| 480 | 46 | NR | 610 | 317 | NR | 740 | 8 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 47 | NR | 615 | 336 | NR | 745 | 7 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2506-472-1

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.55

| λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) |
|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|
| 360 | 0 | NR | 490 | 60 | NR | 620 | 277 | NR | 750 | 6 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 87 | NR | 625 | 278 | NR | 755 | 5 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 124 | NR | 630 | 1000 | NR | 760 | 4 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 168 | NR | 635 | 623 | NR | 765 | 4 | NR | 895 | 0 | NR |
| 380 | 1 | NR | 510 | 209 | NR | 640 | 162 | NR | 770 | 3 | NR | 900 | 0 | NR |
| 385 | 1 | NR | 515 | 246 | NR | 645 | 158 | NR | 775 | 3 | NR | 905 | 0 | NR |
| 390 | 2 | NR | 520 | 273 | NR | 650 | 134 | NR | 780 | 2 | NR | 910 | 0 | NR |
| 395 | 4 | NR | 525 | 292 | NR | 655 | 109 | NR | 785 | 2 | NR | 915 | 0 | NR |
| 400 | 5 | NR | 530 | 305 | NR | 660 | 91 | NR | 790 | 2 | NR | 920 | 0 | NR |
| 405 | 7 | NR | 535 | 313 | NR | 665 | 75 | NR | 795 | 2 | NR | 925 | 0 | NR |
| 410 | 11 | NR | 540 | 319 | NR | 670 | 70 | NR | 800 | 1 | NR | 930 | 0 | NR |
| 415 | 21 | NR | 545 | 323 | NR | 675 | 56 | NR | 805 | 1 | NR | 935 | 0 | NR |
| 420 | 42 | NR | 550 | 326 | NR | 680 | 47 | NR | 810 | 1 | NR | 940 | 0 | NR |
| 425 | 76 | NR | 555 | 330 | NR | 685 | 41 | NR | 815 | 1 | NR | 945 | 0 | NR |
| 430 | 125 | NR | 560 | 333 | NR | 690 | 35 | NR | 820 | 1 | NR | 950 | 0 | NR |
| 435 | 193 | NR | 565 | 336 | NR | 695 | 30 | NR | 825 | 1 | NR | 955 | 0 | NR |
| 440 | 302 | NR | 570 | 336 | NR | 700 | 26 | NR | 830 | 1 | NR | 960 | 0 | NR |
| 445 | 432 | NR | 575 | 335 | NR | 705 | 22 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 380 | NR | 580 | 332 | NR | 710 | 19 | NR | 840 | 0 | NR | 970 | 0 | NR |
| 455 | 213 | NR | 585 | 326 | NR | 715 | 16 | NR | 845 | 0 | NR | 975 | 0 | NR |
| 460 | 147 | NR | 590 | 319 | NR | 720 | 14 | NR | 850 | 0 | NR | 980 | 0 | NR |
| 465 | 104 | NR | 595 | 307 | NR | 725 | 12 | NR | 855 | 0 | NR | 985 | 0 | NR |
| 470 | 65 | NR | 600 | 299 | NR | 730 | 10 | NR | 860 | 0 | NR | 990 | 0 | NR |
| 475 | 50 | NR | 605 | 291 | NR | 735 | 9 | NR | 865 | 0 | NR | 995 | 0 | NR |
| 480 | 46 | NR | 610 | 317 | NR | 740 | 8 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 47 | NR | 615 | 336 | NR | 745 | 7 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2506-472-1

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.99



| λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) |
|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|
| 360 | 0 | NR | 490 | 60 | NR | 620 | 277 | NR | 750 | 6 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 87 | NR | 625 | 278 | NR | 755 | 5 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 124 | NR | 630 | 1000 | NR | 760 | 4 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 168 | NR | 635 | 623 | NR | 765 | 4 | NR | 895 | 0 | NR |
| 380 | 1 | NR | 510 | 209 | NR | 640 | 162 | NR | 770 | 3 | NR | 900 | 0 | NR |
| 385 | 1 | NR | 515 | 246 | NR | 645 | 158 | NR | 775 | 3 | NR | 905 | 0 | NR |
| 390 | 2 | NR | 520 | 273 | NR | 650 | 134 | NR | 780 | 2 | NR | 910 | 0 | NR |
| 395 | 4 | NR | 525 | 292 | NR | 655 | 109 | NR | 785 | 2 | NR | 915 | 0 | NR |
| 400 | 5 | NR | 530 | 305 | NR | 660 | 91 | NR | 790 | 2 | NR | 920 | 0 | NR |
| 405 | 7 | NR | 535 | 313 | NR | 665 | 75 | NR | 795 | 2 | NR | 925 | 0 | NR |
| 410 | 11 | NR | 540 | 319 | NR | 670 | 70 | NR | 800 | 1 | NR | 930 | 0 | NR |
| 415 | 21 | NR | 545 | 323 | NR | 675 | 56 | NR | 805 | 1 | NR | 935 | 0 | NR |
| 420 | 42 | NR | 550 | 326 | NR | 680 | 47 | NR | 810 | 1 | NR | 940 | 0 | NR |
| 425 | 76 | NR | 555 | 330 | NR | 685 | 41 | NR | 815 | 1 | NR | 945 | 0 | NR |
| 430 | 125 | NR | 560 | 333 | NR | 690 | 35 | NR | 820 | 1 | NR | 950 | 0 | NR |
| 435 | 193 | NR | 565 | 336 | NR | 695 | 30 | NR | 825 | 1 | NR | 955 | 0 | NR |
| 440 | 302 | NR | 570 | 336 | NR | 700 | 26 | NR | 830 | 1 | NR | 960 | 0 | NR |
| 445 | 432 | NR | 575 | 335 | NR | 705 | 22 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 380 | NR | 580 | 332 | NR | 710 | 19 | NR | 840 | 0 | NR | 970 | 0 | NR |
| 455 | 213 | NR | 585 | 326 | NR | 715 | 16 | NR | 845 | 0 | NR | 975 | 0 | NR |
| 460 | 147 | NR | 590 | 319 | NR | 720 | 14 | NR | 850 | 0 | NR | 980 | 0 | NR |
| 465 | 104 | NR | 595 | 307 | NR | 725 | 12 | NR | 855 | 0 | NR | 985 | 0 | NR |
| 470 | 65 | NR | 600 | 299 | NR | 730 | 10 | NR | 860 | 0 | NR | 990 | 0 | NR |
| 475 | 50 | NR | 605 | 291 | NR | 735 | 9 | NR | 865 | 0 | NR | 995 | 0 | NR |
| 480 | 46 | NR | 610 | 317 | NR | 740 | 8 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 47 | NR | 615 | 336 | NR | 745 | 7 | NR | 875 | 0 | NR | | | |

Summary

$R_f = 80.7$
 $R_g = 102.1$
 CIE $R_a = 82.1$
 $R_9 = 38.5$




Color Vector Graphics





Individual Sample Fidelity Index ($R_{f,i}$)


| | | | |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 69 | CES51 = 90 | CES76 = 58 |
| CES02 = 61 | CES27 = 89 | CES52 = 90 | CES77 = 76 |
| CES03 = 31 | CES28 = 83 | CES53 = 80 | CES78 = 60 |
| CES04 = 69 | CES29 = 66 | CES54 = 91 | CES79 = 85 |
| CES05 = 48 | CES30 = 76 | CES55 = 89 | CES80 = 79 |
| CES06 = 50 | CES31 = 69 | CES56 = 79 | CES81 = 81 |
| CES07 = 41 | CES32 = 62 | CES57 = 77 | CES82 = 91 |
| CES08 = 40 | CES33 = 74 | CES58 = 79 | CES83 = 88 |
| CES09 = 29 | CES34 = 72 | CES59 = 93 | CES84 = 89 |
| CES10 = 74 | CES35 = 84 | CES60 = 95 | CES85 = 84 |
| CES11 = 57 | CES36 = 98 | CES61 = 92 | CES86 = 82 |
| CES12 = 63 | CES37 = 77 | CES62 = 89 | CES87 = 81 |
| CES13 = 43 | CES38 = 83 | CES63 = 80 | CES88 = 86 |
| CES14 = 74 | CES39 = 94 | CES64 = 80 | CES89 = 79 |
| CES15 = 71 | CES40 = 88 | CES65 = 77 | CES90 = 85 |
| CES16 = 47 | CES41 = 89 | CES66 = 74 | CES91 = 83 |
| CES17 = 49 | CES42 = 74 | CES67 = 72 | CES92 = 77 |
| CES18 = 56 | CES43 = 73 | CES68 = 78 | CES93 = 86 |
| CES19 = 71 | CES44 = 98 | CES69 = 83 | CES94 = 69 |
| CES20 = 65 | CES45 = 82 | CES70 = 69 | CES95 = 80 |
| CES21 = 86 | CES46 = 82 | CES71 = 64 | CES96 = 86 |
| CES22 = 78 | CES47 = 80 | CES72 = 88 | CES97 = 83 |
| CES23 = 91 | CES48 = 79 | CES73 = 60 | CES98 = 81 |
| CES24 = 90 | CES49 = 80 | CES74 = 98 | CES99 = 83 |
| CES25 = 71 | CES50 = 89 | CES75 = 62 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)