

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number:

Luminaire Tested: EHBR1-36-UNV-ASM-L840-UPL36

Issue Date: 3/20/2026

**Test Information**


Test Method: LM-79-2019  
Report Number:  
REPORT IS A COMBINATION OF REPORTS P1431777 AND P1431635  
Test Lab: INNOVATION CENTER  
Issue Date: 3/20/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: EHBR1-36-UNV-ASM-L840-UPL36  
Description: Elevate Round Highbay at, 36000 lumens, 4000K 80CRI LEDs with ASM lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 39752.9 lumens  
Efficiency: N/A  
Efficacy: 180.9 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.99 / 0.92  
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')  
CIE Type: Direct  
  
Input Watts (W): 219.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER:  
CATALOG NUMBER: EHBR1-36-UNV-ASM-L840-UPL36

### Luminous Intensity Polar Plot





TEST NUMBER:

CATALOG NUMBER: EHBR1-36-UNV-ASM-L840-UPL36

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	113	113	113	113	106	106	106	99	99	99	93	93	93	93	93	93	91
1	110	106	103	100	106	103	100	98	97	95	93	92	90	89	87	86	84	87	86	84	82
2	103	97	92	87	99	94	89	86	89	86	82	85	82	79	81	78	76	81	78	76	74
3	96	88	82	77	93	86	81	76	82	78	74	78	75	71	75	72	69	75	72	69	67
4	90	81	75	70	88	79	73	69	76	71	67	73	68	65	70	66	63	70	66	63	61
5	85	75	68	63	82	73	67	62	70	65	61	68	63	60	65	61	58	65	61	58	56
6	80	70	63	58	78	68	62	57	66	60	56	63	58	55	61	57	54	61	57	54	52
7	75	65	58	53	73	64	57	53	61	56	52	59	54	51	57	53	50	57	53	50	48
8	71	60	54	49	69	59	53	49	58	52	48	56	51	47	54	50	46	54	50	46	45
9	67	57	50	46	66	56	50	45	54	48	45	52	47	44	51	47	43	51	47	43	42
10	64	53	47	43	62	52	46	42	51	45	42	50	45	41	48	44	41	48	44	41	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	151494	151494	151494	151494	151494
5°	142758	144426	150572	157793	160632
10°	135108	137969	148720	162859	164756
15°	124803	128137	144330	161189	153109
20°	111165	114909	134984	148164	122773
25°	93161	96687	119472	124276	85064
30°	69703	73744	97007	96038	55340
35°	46403	49205	69576	68453	35839
40°	29264	31274	44983	45273	24703
45°	20851	21718	28542	29768	19135
50°	17368	17506	21196	21747	16260
55°	15331	15367	17305	17762	14812
60°	14195	14074	14985	15302	14110
65°	13550	13428	13660	13926	13607
70°	13161	12933	12947	13195	13333
75°	12512	12133	12108	12538	12898
80°	11384	10590	10635	11384	12177
85°	8289	6881	6881	7867	8694

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 112.5°

Vertical Angle: 45°

Luminance: 40128 cd/sqm



TEST NUMBER:

CATALOG NUMBER: EHBR1-36-UNV-ASM-L840-UPL36

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	3067.4	7.7
10°-20°	8345.0	21.0
20°-30°	9787.0	24.6
30°-40°	6806.2	17.1
40°-50°	3382.4	8.5
50°-60°	2023.0	5.1
60°-70°	1423.9	3.6
70°-80°	917.2	2.3
80°-90°	297.8	0.7
90°-100°	98.6	0.2
100°-110°	643.8	1.6
110°-120°	1189.4	3.0
120°-130°	706.9	1.8
130°-140°	427.5	1.1
140°-150°	295.8	0.7
150°-160°	193.1	0.5
160°-170°	110.9	0.3
170°-180°	36.9	0.1
0°-30°	21199.4	53.3
0°-40°	28005.6	70.4
0°-60°	33411.0	84.0
0°-90°	36049.9	90.7
90°-120°	1931.9	4.9
90°-150°	3362.1	8.5
90°-180°	3703.0	9.3
0°-180°	39752.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	32260	32260	32260	32260	32260	
5°	30481	30837	32149	33691	34297	2859
15°	26183	26882	30280	33816	32122	7302
25°	18604	19308	23858	24818	16987	8394
35°	8517	9031	12770	12564	6578	5425
45°	3374	3514	4618	4816	3096	2727
55°	2072	2077	2339	2400	2002	1880
65°	1414	1402	1426	1454	1420	1404
75°	881	855	853	883	909	930
85°	285	236	236	270	299	293
90°	27	74	27	80	31	27
95°	46	166	52	143	50	44
105°	224	1124	296	1199	151	300
115°	1028	1329	1266	1471	1081	947
125°	742	712	810	789	849	676
135°	542	546	512	571	592	425
145°	451	472	463	474	484	285
155°	400	413	413	413	430	187
165°	381	390	389	388	400	109
175°	381	387	387	385	394	36
180°	386	386	386	386	386	



TEST NUMBER:

CATALOG NUMBER: EHBR1-36-UNV-ASM-L840-UPL36

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	32259.5	32259.5	32259.5	32259.5	32259.5	32259.5	32259.5	32259.5	32259.5
2.5°	31301.9	31322.5	31541.4	31826.3	32240.7	32657.5	32995.0	33217.7	33327.7
5°	30481.0	30594.7	30837.3	31360.6	32149.4	32984.2	33691.3	34154.1	34297.4
7.5°	29681.3	29747.3	30153.2	30814.3	31931.0	33231.6	34282.3	34822.5	34954.4
10°	28705.6	28855.0	29313.5	30093.3	31597.7	33387.6	34601.7	34988.8	35004.6
12.5°	27557.5	27755.3	28228.9	29212.5	31066.0	33332.0	34494.6	34367.6	34079.0
15°	26183.1	26356.7	26882.4	28023.3	30279.6	33002.3	33816.5	32782.7	32121.5
17.5°	24698.6	24855.9	25312.6	26569.0	29171.4	32385.3	32401.0	30355.8	29108.5
20°	22847.6	22971.0	23617.1	24849.9	27743.2	31395.7	30452.0	26711.2	25233.4
22.5°	20878.0	20993.5	21567.6	22850.6	25952.6	30061.2	27737.7	23044.8	21028.6
25°	18604.1	18667.0	19308.3	20468.5	23858.4	28426.1	24817.8	19050.0	16987.2
27.5°	16046.0	16153.0	16823.9	18008.9	21395.2	26353.7	21708.6	15566.9	13663.8
30°	13407.3	13584.6	14184.6	15245.7	18659.2	23696.9	18472.9	12397.1	10644.7
32.5°	10944.7	11072.3	11500.0	12608.8	15595.9	21092.8	15365.4	9933.3	8448.8
35°	8516.6	8644.2	9030.8	10119.6	12769.7	17834.7	12563.5	7805.2	6577.8
37.5°	6510.1	6735.7	6983.7	7867.5	10021.6	14756.3	10015.0	6285.1	5335.3
40°	5072.2	5108.5	5420.6	5986.2	7796.7	11538.1	7846.9	5017.2	4281.6
42.5°	4060.2	4158.8	4293.1	4716.5	5907.6	8822.7	6167.7	4117.7	3636.7
45°	3373.6	3412.3	3513.9	3798.3	4617.9	6492.5	4816.3	3474.0	3096.0
47.5°	2951.4	2934.4	2999.8	3212.7	3760.8	5017.8	3903.5	2979.8	2714.9
50°	2588.4	2578.1	2609.0	2751.1	3158.9	3850.3	3241.1	2601.1	2423.3
52.5°	2306.5	2315.6	2318.6	2407.0	2713.6	3140.1	2760.2	2318.0	2198.3
55°	2071.8	2083.3	2076.7	2142.0	2338.6	2639.8	2400.3	2084.5	2001.7
57.5°	1888.5	1880.1	1871.0	1906.1	2053.7	2239.4	2084.5	1885.5	1830.5
60°	1706.5	1698.6	1691.9	1714.9	1801.4	1939.4	1839.5	1711.9	1696.2
62.5°	1550.4	1545.6	1545.0	1540.7	1607.3	1694.4	1626.6	1555.8	1541.9
65°	1414.3	1408.8	1401.6	1394.9	1425.8	1506.8	1453.6	1415.5	1420.3
67.5°	1278.2	1278.2	1265.5	1255.2	1285.4	1327.8	1304.8	1283.0	1288.5
70°	1154.8	1155.4	1134.8	1127.0	1136.0	1181.4	1157.8	1160.8	1169.9
72.5°	1022.3	1007.8	992.7	992.1	993.3	1028.4	1020.5	1027.7	1037.4
75°	881.4	864.4	854.7	843.9	852.9	879.5	883.2	893.5	908.6
77.5°	745.3	719.2	711.4	705.9	699.9	730.1	741.6	755.5	777.9
80°	598.9	570.4	557.1	549.3	559.5	573.5	598.9	609.1	640.6
82.5°	442.8	421.6	405.3	404.7	409.5	422.2	444.0	463.4	481.5
85°	284.9	251.0	236.5	242.0	236.5	255.9	270.4	293.4	298.8
87.5°	102.8	80.5	76.8	84.7	82.9	88.9	101.6	110.7	111.3
90°	27.2	43.6	74.2	47.6	27.2	46.2	79.5	44.5	31.4
92.5°	39.5	66.1	119.2	62.0	35.4	62.6	112.3	58.8	41.6
95°	45.6	76.3	166.3	82.4	52.3	76.9	142.9	65.0	49.8
97.5°	58.5	84.5	190.8	100.8	81.0	95.3	161.3	69.1	60.0
100°	76.9	98.8	297.2	123.9	107.6	107.6	294.3	79.3	68.2
102.5°	130.1	209.2	630.6	232.3	162.8	210.4	681.5	157.6	82.5
105°	224.1	440.4	1123.5	486.0	295.7	480.4	1199.0	405.1	150.6
107.5°	387.8	788.1	1482.1	860.3	559.6	895.6	1544.6	797.8	349.0
110°	723.2	1045.8	1553.7	1181.4	895.0	1251.5	1685.8	1092.4	704.9



TEST NUMBER:

CATALOG NUMBER: EHBR1-36-UNV-ASM-L840-UPL36

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
112.5°	976.9	1123.5	1488.2	1304.1	1165.0	1394.7	1646.9	1211.0	974.9
115°	1028.0	1080.6	1328.7	1273.4	1265.9	1374.3	1471.0	1206.9	1081.3
117.5°	993.2	986.5	1128.2	1145.2	1222.9	1257.7	1270.5	1133.3	1087.4
120°	919.6	878.1	942.1	1000.0	1104.3	1090.0	1070.7	1024.9	1026.1
122.5°	827.5	778.5	807.7	851.2	955.6	924.9	905.0	915.0	942.2
125°	742.2	692.5	712.2	723.0	810.3	779.7	789.0	820.9	848.7
127.5°	666.6	633.2	644.7	633.0	688.2	673.9	705.2	741.1	764.8
130°	615.4	586.8	602.3	574.3	600.9	604.3	645.9	676.3	691.2
132.5°	573.1	554.7	572.8	538.6	546.2	562.0	601.5	627.8	636.7
135°	542.4	526.6	546.2	514.7	512.1	535.4	571.4	588.3	591.7
137.5°	516.4	502.7	522.9	498.9	492.2	515.5	542.7	556.2	552.8
140°	493.1	481.4	503.0	484.6	480.5	503.9	516.1	531.7	528.9
142.5°	467.7	459.5	485.3	473.1	469.0	490.2	496.3	507.8	504.3
145°	450.6	444.4	471.6	464.9	463.4	479.2	474.4	489.4	484.5
147.5°	435.4	431.3	455.8	453.2	453.2	464.9	458.7	471.6	466.7
150°	422.3	418.2	442.1	439.5	441.5	449.7	440.9	455.8	455.0
152.5°	409.2	404.5	426.4	423.7	425.8	433.9	425.8	442.7	441.3
155°	400.1	395.4	413.2	412.0	412.6	416.7	412.6	429.6	430.2
157.5°	393.7	390.5	404.2	403.6	403.6	406.3	404.2	419.1	419.7
160°	388.8	386.2	397.8	397.2	395.8	399.9	398.4	411.3	411.9
162.5°	383.9	381.2	394.9	392.9	392.9	392.9	392.1	404.9	406.1
165°	381.0	380.4	390.0	390.0	388.6	390.6	387.7	397.2	400.4
167.5°	381.0	378.9	389.2	389.2	387.7	385.7	387.0	394.9	398.2
170°	380.1	379.5	387.7	386.3	384.2	384.9	384.1	392.0	395.3
172.5°	381.4	380.8	389.6	387.6	386.1	386.1	383.8	389.7	395.0
175°	380.6	380.0	386.7	386.7	387.3	385.9	385.0	388.9	394.2
177.5°	383.2	382.6	386.7	386.7	385.3	386.5	387.7	391.5	398.9
180°	386.5	386.5	386.5	386.5	386.5	386.5	386.5	386.5	386.5



TEST NUMBER: CATALOG  
 CATALOG NUMBER: EHBR1-36-UNV-ASM-L840-UPL36

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.19	18.26	17.72	18.76	19.31	17.96	19.03	18.48	19.53	20.08
	3H	19.01	19.96	19.55	20.47	21.07	19.52	20.47	20.06	20.98	21.57
	4H	19.74	20.63	20.30	21.16	21.77	20.16	21.05	20.72	21.58	22.19
	6H	20.31	21.13	20.88	21.67	22.29	20.66	21.47	21.23	22.02	22.64
	8H	20.49	21.26	21.08	21.83	22.46	20.81	21.58	21.40	22.15	22.78
	12H	20.59	21.33	21.18	21.89	22.53	20.89	21.63	21.48	22.19	22.84
4H	2H	17.71	18.60	18.27	19.13	19.73	18.33	19.22	18.90	19.76	20.36
	3H	19.74	20.48	20.32	21.06	21.68	20.14	20.88	20.71	21.45	22.08
	4H	20.61	21.27	21.20	21.85	22.51	20.93	21.59	21.52	22.17	22.83
	6H	21.30	21.87	21.92	22.48	23.16	21.56	22.13	22.18	22.74	23.42
	8H	21.53	22.06	22.15	22.67	23.35	21.76	22.30	22.38	22.90	23.59
	12H	21.66	22.13	22.30	22.77	23.45	21.88	22.35	22.52	22.99	23.67
8H	4H	20.86	21.40	21.48	22.00	22.69	21.17	21.70	21.79	22.31	22.99
	6H	21.68	22.11	22.33	22.77	23.46	21.93	22.36	22.58	23.02	23.71
	8H	21.98	22.37	22.65	23.03	23.73	22.21	22.60	22.88	23.26	23.97
	12H	22.18	22.52	22.85	23.17	23.94	22.40	22.73	23.06	23.38	24.15
12H	4H	20.87	21.34	21.51	21.98	22.66	21.18	21.65	21.81	22.29	22.97
	6H	21.72	22.10	22.39	22.77	23.47	21.98	22.36	22.64	23.03	23.73
	8H	22.06	22.40	22.73	23.05	23.82	22.30	22.64	22.97	23.29	24.06

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-1

Test Date: 07/30/2025

Luminaire Tested: EHBR-60-L840-N

Data in this report applies to families of products including EHBR-60-L840-N

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2506-472-1  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 08/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **EHBR-60-L840-N**  
 Description: Elevate Round Highbay at, 60000 lumens, 4000K 80CRI LEDs with N lens

**Spectral Parameters**

CCT (K): 3898  
 CIE u': 0.2263  
 CIE v': 0.5052  
 Duv: 0.0013  
 CIE x: 0.3861  
 CIE y: 0.3831  
 CIE z: 0.2308  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 578  
 Purity: 30.85729  
 Rf: 80.7  
 Rg: 102.1

CRI (Ra):	82.1		
R1:	84.4	R9:	38.5
R2:	83.5	R10:	58.9
R3:	80.8	R11:	83.6
R4:	83.9	R12:	54.2
R5:	82.1	R13:	82.8
R6:	77.3	R14:	88.2
R7:	86.4	R15:	81.2
R8:	78.3		



**Test Conditions**  
 Stabilization Time: 42M  
 Operation Time: 1H 42M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-1

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-1

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-1

**Photopic Flux vs. Wavelength**



**Photopic Lumens: NR**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	60	NR	620	277	NR	750	6	NR	880	0	NR
365	0	NR	495	87	NR	625	278	NR	755	5	NR	885	0	NR
370	0	NR	500	124	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	168	NR	635	623	NR	765	4	NR	895	0	NR
380	1	NR	510	209	NR	640	162	NR	770	3	NR	900	0	NR
385	1	NR	515	246	NR	645	158	NR	775	3	NR	905	0	NR
390	2	NR	520	273	NR	650	134	NR	780	2	NR	910	0	NR
395	4	NR	525	292	NR	655	109	NR	785	2	NR	915	0	NR
400	5	NR	530	305	NR	660	91	NR	790	2	NR	920	0	NR
405	7	NR	535	313	NR	665	75	NR	795	2	NR	925	0	NR
410	11	NR	540	319	NR	670	70	NR	800	1	NR	930	0	NR
415	21	NR	545	323	NR	675	56	NR	805	1	NR	935	0	NR
420	42	NR	550	326	NR	680	47	NR	810	1	NR	940	0	NR
425	76	NR	555	330	NR	685	41	NR	815	1	NR	945	0	NR
430	125	NR	560	333	NR	690	35	NR	820	1	NR	950	0	NR
435	193	NR	565	336	NR	695	30	NR	825	1	NR	955	0	NR
440	302	NR	570	336	NR	700	26	NR	830	1	NR	960	0	NR
445	432	NR	575	335	NR	705	22	NR	835	1	NR	965	0	NR
450	380	NR	580	332	NR	710	19	NR	840	0	NR	970	0	NR
455	213	NR	585	326	NR	715	16	NR	845	0	NR	975	0	NR
460	147	NR	590	319	NR	720	14	NR	850	0	NR	980	0	NR
465	104	NR	595	307	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	299	NR	730	10	NR	860	0	NR	990	0	NR
475	50	NR	605	291	NR	735	9	NR	865	0	NR	995	0	NR
480	46	NR	610	317	NR	740	8	NR	870	0	NR	1000	0	NR
485	47	NR	615	336	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-1

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: NR**

**S/P: 1.55**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	60	NR	620	277	NR	750	6	NR	880	0	NR
365	0	NR	495	87	NR	625	278	NR	755	5	NR	885	0	NR
370	0	NR	500	124	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	168	NR	635	623	NR	765	4	NR	895	0	NR
380	1	NR	510	209	NR	640	162	NR	770	3	NR	900	0	NR
385	1	NR	515	246	NR	645	158	NR	775	3	NR	905	0	NR
390	2	NR	520	273	NR	650	134	NR	780	2	NR	910	0	NR
395	4	NR	525	292	NR	655	109	NR	785	2	NR	915	0	NR
400	5	NR	530	305	NR	660	91	NR	790	2	NR	920	0	NR
405	7	NR	535	313	NR	665	75	NR	795	2	NR	925	0	NR
410	11	NR	540	319	NR	670	70	NR	800	1	NR	930	0	NR
415	21	NR	545	323	NR	675	56	NR	805	1	NR	935	0	NR
420	42	NR	550	326	NR	680	47	NR	810	1	NR	940	0	NR
425	76	NR	555	330	NR	685	41	NR	815	1	NR	945	0	NR
430	125	NR	560	333	NR	690	35	NR	820	1	NR	950	0	NR
435	193	NR	565	336	NR	695	30	NR	825	1	NR	955	0	NR
440	302	NR	570	336	NR	700	26	NR	830	1	NR	960	0	NR
445	432	NR	575	335	NR	705	22	NR	835	1	NR	965	0	NR
450	380	NR	580	332	NR	710	19	NR	840	0	NR	970	0	NR
455	213	NR	585	326	NR	715	16	NR	845	0	NR	975	0	NR
460	147	NR	590	319	NR	720	14	NR	850	0	NR	980	0	NR
465	104	NR	595	307	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	299	NR	730	10	NR	860	0	NR	990	0	NR
475	50	NR	605	291	NR	735	9	NR	865	0	NR	995	0	NR
480	46	NR	610	317	NR	740	8	NR	870	0	NR	1000	0	NR
485	47	NR	615	336	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-1

**Melanopic Flux vs. Wavelength**




**Melanopic Lumens: NR**

**M/P: 2.99**

$\lambda$ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens ( $\phi/\text{nm}$ )	$\lambda$ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens ( $\phi/\text{nm}$ )	$\lambda$ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens ( $\phi/\text{nm}$ )	$\lambda$ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens ( $\phi/\text{nm}$ )	$\lambda$ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens ( $\phi/\text{nm}$ )
360	0	NR	490	60	NR	620	277	NR	750	6	NR	880	0	NR
365	0	NR	495	87	NR	625	278	NR	755	5	NR	885	0	NR
370	0	NR	500	124	NR	630	1000	NR	760	4	NR	890	0	NR
375	0	NR	505	168	NR	635	623	NR	765	4	NR	895	0	NR
380	1	NR	510	209	NR	640	162	NR	770	3	NR	900	0	NR
385	1	NR	515	246	NR	645	158	NR	775	3	NR	905	0	NR
390	2	NR	520	273	NR	650	134	NR	780	2	NR	910	0	NR
395	4	NR	525	292	NR	655	109	NR	785	2	NR	915	0	NR
400	5	NR	530	305	NR	660	91	NR	790	2	NR	920	0	NR
405	7	NR	535	313	NR	665	75	NR	795	2	NR	925	0	NR
410	11	NR	540	319	NR	670	70	NR	800	1	NR	930	0	NR
415	21	NR	545	323	NR	675	56	NR	805	1	NR	935	0	NR
420	42	NR	550	326	NR	680	47	NR	810	1	NR	940	0	NR
425	76	NR	555	330	NR	685	41	NR	815	1	NR	945	0	NR
430	125	NR	560	333	NR	690	35	NR	820	1	NR	950	0	NR
435	193	NR	565	336	NR	695	30	NR	825	1	NR	955	0	NR
440	302	NR	570	336	NR	700	26	NR	830	1	NR	960	0	NR
445	432	NR	575	335	NR	705	22	NR	835	1	NR	965	0	NR
450	380	NR	580	332	NR	710	19	NR	840	0	NR	970	0	NR
455	213	NR	585	326	NR	715	16	NR	845	0	NR	975	0	NR
460	147	NR	590	319	NR	720	14	NR	850	0	NR	980	0	NR
465	104	NR	595	307	NR	725	12	NR	855	0	NR	985	0	NR
470	65	NR	600	299	NR	730	10	NR	860	0	NR	990	0	NR
475	50	NR	605	291	NR	735	9	NR	865	0	NR	995	0	NR
480	46	NR	610	317	NR	740	8	NR	870	0	NR	1000	0	NR
485	47	NR	615	336	NR	745	7	NR	875	0	NR			

**Summary**

$R_f = 80.7$   
 $R_g = 102.1$   
 CIE  $R_a = 82.1$   
 $R_9 = 38.5$



**Color Vector Graphics**



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

CES01 = 85	CES26 = 69	CES51 = 90	CES76 = 58
CES02 = 61	CES27 = 89	CES52 = 90	CES77 = 76
CES03 = 31	CES28 = 83	CES53 = 80	CES78 = 60
CES04 = 69	CES29 = 66	CES54 = 91	CES79 = 85
CES05 = 48	CES30 = 76	CES55 = 89	CES80 = 79
CES06 = 50	CES31 = 69	CES56 = 79	CES81 = 81
CES07 = 41	CES32 = 62	CES57 = 77	CES82 = 91
CES08 = 40	CES33 = 74	CES58 = 79	CES83 = 88
CES09 = 29	CES34 = 72	CES59 = 93	CES84 = 89
CES10 = 74	CES35 = 84	CES60 = 95	CES85 = 84
CES11 = 57	CES36 = 98	CES61 = 92	CES86 = 82
CES12 = 63	CES37 = 77	CES62 = 89	CES87 = 81
CES13 = 43	CES38 = 83	CES63 = 80	CES88 = 86
CES14 = 74	CES39 = 94	CES64 = 80	CES89 = 79
CES15 = 71	CES40 = 88	CES65 = 77	CES90 = 85
CES16 = 47	CES41 = 89	CES66 = 74	CES91 = 83
CES17 = 49	CES42 = 74	CES67 = 72	CES92 = 77
CES18 = 56	CES43 = 73	CES68 = 78	CES93 = 86
CES19 = 71	CES44 = 98	CES69 = 83	CES94 = 69
CES20 = 65	CES45 = 82	CES70 = 69	CES95 = 80
CES21 = 86	CES46 = 82	CES71 = 64	CES96 = 86
CES22 = 78	CES47 = 80	CES72 = 88	CES97 = 83
CES23 = 91	CES48 = 79	CES73 = 60	CES98 = 81
CES24 = 90	CES49 = 80	CES74 = 98	CES99 = 83
CES25 = 71	CES50 = 89	CES75 = 62	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)