

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1436472

Luminaire Tested: EHBR1-54-UNV-M-L930-UPL36

Issue Date: 3/25/2026

Test Information

Test Method: LM-79-2019
Report Number: P1436472
REPORT IS A COMBINATION OF REPORTS P1436112 AND P1431635
Test Lab: INNOVATION CENTER
Issue Date: 3/25/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-54-UNV-M-L930-UPL36
Description: Elevate Round Highbay at, 54000 lumens, 3000K 90CRI LEDs with M lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 51335.6 lumens
Efficiency: N/A
Efficacy: 158.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.15
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')
CIE Type: Direct

Input Watts (W): 324.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1436472
CATALOG NUMBER: EHBR1-54-UNV-M-L930-UPL36

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1436472

CATALOG NUMBER: EHBR1-54-UNV-M-L930-UPL36

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	118	118	118	118	114	114	114	114	108	108	108	102	102	102	96	96	96	96	96	96	94
1	110	106	103	100	107	104	101	98	98	96	94	94	92	90	89	88	86	86	86	86	84
2	103	96	91	87	100	94	89	85	90	86	82	86	82	80	82	79	77	77	77	77	75
3	96	87	81	76	93	85	80	75	82	77	73	78	74	71	75	72	69	69	69	69	67
4	89	80	73	67	87	78	71	66	75	69	65	72	67	63	69	65	62	62	62	62	60
5	83	73	65	60	81	71	65	60	69	63	58	66	61	57	64	60	56	56	56	56	54
6	78	67	59	54	76	66	59	54	63	57	53	61	56	52	59	55	51	51	51	51	49
7	73	62	54	49	71	61	54	49	59	52	48	57	51	47	55	50	47	47	47	47	45
8	68	57	50	45	67	56	49	44	54	48	44	53	47	43	51	46	43	43	43	43	41
9	64	53	46	41	63	52	45	41	51	45	40	49	44	40	48	43	39	39	39	39	38
10	61	49	42	38	59	49	42	38	47	41	37	46	41	37	45	40	36	36	36	36	35

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	133584	133584	133584
5°	133355	133355	133355
10°	133980	133980	133980
15°	134750	134750	134750
20°	134343	134343	134343
25°	131206	131206	131206
30°	122687	122687	122687
35°	106849	106849	106849
40°	81888	81888	81888
45°	53495	53495	53495
50°	33723	33723	33723
55°	25139	25139	25139
60°	21164	21164	21164
65°	19245	19245	19245
70°	17532	17532	17532
75°	15008	15008	15008
80°	11557	11557	11557
85°	6061	6061	6061

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 53495 cd/sqm



TEST NUMBER: P1436472
 CATALOG NUMBER: EHBR1-54-UNV-M-L930-UPL36

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2716.8	5.3
10°-20°	7978.5	15.5
20°-30°	11971.4	23.3
30°-40°	12044.5	23.5
40°-50°	6894.6	13.4
50°-60°	3153.4	6.1
60°-70°	2000.7	3.9
70°-80°	1122.3	2.2
80°-90°	269.0	0.5
90°-100°	90.8	0.2
100°-110°	568.9	1.1
110°-120°	1017.3	2.0
120°-130°	596.9	1.2
130°-140°	366.2	0.7
140°-150°	254.0	0.5
150°-160°	165.0	0.3
160°-170°	94.0	0.2
170°-180°	31.1	0.1
0°-30°	22666.7	44.2
0°-40°	34711.3	67.6
0°-60°	44759.3	87.2
0°-90°	48151.3	93.8
90°-120°	1677.0	3.3
90°-150°	2894.1	5.6
90°-180°	3184.0	6.2
0°-180°	51335.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	28446	28446	28446	28446	28446	
5°	28473	28473	28473	28473	28473	2717
15°	28270	28270	28270	28270	28270	7978
25°	26202	26202	26202	26202	26202	11971
35°	19611	19611	19611	19611	19611	12045
45°	8655	8655	8655	8655	8655	6895
55°	3397	3397	3397	3397	3397	3153
65°	2009	2009	2009	2009	2009	2001
75°	1057	1057	1057	1057	1057	1122
85°	208	208	208	208	208	255
90°	24	38	66	42	24	19
95°	40	68	148	73	46	39
105°	199	392	1001	432	262	266
115°	915	962	1183	1134	1126	843
125°	660	616	632	642	720	601
135°	481	467	483	454	452	376
145°	396	390	414	408	406	251
155°	346	343	359	359	359	162
165°	324	324	334	334	332	93
175°	321	321	326	326	326	31
180°	324	324	324	324	324	



TEST NUMBER: P1436472

CATALOG NUMBER: EHBR1-54-UNV-M-L930-UPL36

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	28445.7	28445.7	28445.7	28445.7	28445.7
2.5°	28459.5	28459.5	28459.5	28459.5	28459.5
5°	28473.3	28473.3	28473.3	28473.3	28473.3
7.5°	28453.8	28453.8	28453.8	28453.8	28453.8
10°	28466.0	28466.0	28466.0	28466.0	28466.0
12.5°	28417.2	28417.2	28417.2	28417.2	28417.2
15°	28269.9	28269.9	28269.9	28269.9	28269.9
17.5°	28026.5	28026.5	28026.5	28026.5	28026.5
20°	27611.4	27611.4	27611.4	27611.4	27611.4
22.5°	27040.8	27040.8	27040.8	27040.8	27040.8
25°	26201.7	26201.7	26201.7	26201.7	26201.7
27.5°	25072.8	25072.8	25072.8	25072.8	25072.8
30°	23598.8	23598.8	23598.8	23598.8	23598.8
32.5°	21853.8	21853.8	21853.8	21853.8	21853.8
35°	19610.6	19610.6	19610.6	19610.6	19610.6
37.5°	17069.5	17069.5	17069.5	17069.5	17069.5
40°	14193.2	14193.2	14193.2	14193.2	14193.2
42.5°	11342.0	11342.0	11342.0	11342.0	11342.0
45°	8655.2	8655.2	8655.2	8655.2	8655.2
47.5°	6515.4	6515.4	6515.4	6515.4	6515.4
50°	5025.9	5025.9	5025.9	5025.9	5025.9
52.5°	4060.7	4060.7	4060.7	4060.7	4060.7
55°	3397.3	3397.3	3397.3	3397.3	3397.3
57.5°	2908.9	2908.9	2908.9	2908.9	2908.9
60°	2544.3	2544.3	2544.3	2544.3	2544.3
62.5°	2262.7	2262.7	2262.7	2262.7	2262.7
65°	2008.7	2008.7	2008.7	2008.7	2008.7
67.5°	1775.1	1775.1	1775.1	1775.1	1775.1
70°	1538.3	1538.3	1538.3	1538.3	1538.3
72.5°	1299.8	1299.8	1299.8	1299.8	1299.8
75°	1057.2	1057.2	1057.2	1057.2	1057.2
77.5°	827.0	827.0	827.0	827.0	827.0
80°	608.0	608.0	608.0	608.0	608.0
82.5°	396.4	396.4	396.4	396.4	396.4
85°	208.3	208.3	208.3	208.3	208.3
87.5°	59.4	59.4	59.4	59.4	59.4
90°	23.7	38.3	65.6	41.9	23.7
92.5°	34.7	58.4	105.7	54.7	31.0
95°	40.1	67.5	147.7	72.9	45.5
97.5°	51.1	74.8	169.5	89.3	71.1
100°	67.5	87.5	264.3	109.3	94.8
102.5°	114.9	185.9	561.4	205.9	144.0
105°	198.6	391.9	1000.7	432.0	262.4
107.5°	344.5	701.8	1319.7	765.6	497.6
110°	643.4	931.4	1383.5	1051.7	796.5



TEST NUMBER: P1436472
 CATALOG NUMBER: EHBR1-54-UNV-M-L930-UPL36

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	869.5	1000.7	1325.1	1161.1	1037.1
115°	915.0	962.4	1183.0	1133.7	1126.5
117.5°	884.0	878.6	1004.3	1018.9	1088.2
120°	818.4	782.0	838.5	889.5	982.5
122.5°	736.3	692.7	718.2	756.4	849.4
125°	659.8	616.0	632.5	641.6	720.0
127.5°	592.4	563.2	572.4	561.4	610.6
130°	546.8	521.3	534.1	508.6	532.3
132.5°	508.6	492.2	506.7	475.7	483.0
135°	481.2	466.6	483.0	453.9	452.1
137.5°	457.5	444.8	461.2	439.2	433.8
140°	435.7	424.7	442.9	426.5	422.8
142.5°	412.0	404.7	426.5	415.6	412.0
145°	395.6	390.1	413.8	408.3	406.4
147.5°	381.0	377.3	399.1	397.4	397.4
150°	368.2	364.6	386.4	384.6	386.4
152.5°	355.5	351.8	371.9	370.0	371.9
155°	346.3	342.6	359.0	359.0	359.0
157.5°	339.0	337.2	350.0	350.0	350.0
160°	333.6	331.8	342.6	342.6	340.9
162.5°	328.1	326.2	339.0	337.2	337.2
165°	324.5	324.5	333.6	333.6	331.8
167.5°	324.5	322.6	331.8	331.8	329.9
170°	322.6	322.6	329.9	328.1	326.2
172.5°	322.6	322.6	329.9	328.1	326.2
175°	320.8	320.8	326.2	326.2	326.2
177.5°	322.6	322.6	326.2	326.2	324.5
180°	324.5	324.5	324.5	324.5	324.5



TEST NUMBER: P1436472
 CATALOG NUMBER: EHBR1-54-UNV-M-L930-UPL36

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.39	20.56	19.86	21.00	21.48	19.39	20.56	19.86	21.00	21.48
	3H	20.88	21.91	21.36	22.37	22.89	20.88	21.91	21.36	22.37	22.89
	4H	21.40	22.37	21.91	22.84	23.38	21.40	22.37	21.91	22.84	23.38
	6H	21.72	22.61	22.25	23.11	23.65	21.72	22.61	22.25	23.11	23.65
	8H	21.79	22.64	22.33	23.15	23.70	21.79	22.64	22.33	23.15	23.70
	12H	21.81	22.61	22.35	23.11	23.69	21.81	22.61	22.35	23.11	23.69
4H	2H	19.83	20.80	20.34	21.27	21.81	19.83	20.80	20.34	21.27	21.81
	3H	21.53	22.32	22.05	22.85	23.40	21.53	22.32	22.05	22.85	23.40
	4H	22.16	22.87	22.70	23.40	23.99	22.16	22.87	22.70	23.40	23.99
	6H	22.58	23.20	23.15	23.76	24.36	22.58	23.20	23.15	23.76	24.36
	8H	22.67	23.25	23.25	23.81	24.42	22.67	23.25	23.25	23.81	24.42
	12H	22.70	23.21	23.29	23.80	24.42	22.70	23.21	23.29	23.80	24.42
8H	4H	22.33	22.91	22.91	23.47	24.08	22.33	22.91	22.91	23.47	24.08
	6H	22.84	23.31	23.45	23.92	24.54	22.84	23.31	23.45	23.92	24.54
	8H	22.98	23.40	23.60	24.02	24.65	22.98	23.40	23.60	24.02	24.65
	12H	23.05	23.42	23.66	24.02	24.72	23.05	23.42	23.66	24.02	24.72
12H	4H	22.32	22.83	22.91	23.42	24.04	22.32	22.83	22.91	23.42	24.04
	6H	22.85	23.26	23.47	23.88	24.52	22.85	23.26	23.47	23.88	24.52
	8H	23.02	23.39	23.63	23.99	24.69	23.02	23.39	23.63	23.99	24.69

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-5

Test Date: 08/01/2025

Luminaire Tested: EHBR-60-L930-N

Data in this report applies to families of products including EHBR-60-L930-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-5
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L930-N**
 Description: Elevate Round Highbay at, 60000 lumens, 3000K 90CRI LEDs with N lens

Spectral Parameters

CCT (K): 2996
 CIE u': 0.2519
 CIE v': 0.5169
 Duv: -0.0033
 CIE x: 0.4325
 CIE y: 0.3945
 CIE z: 0.1730
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 584
 Purity: 48.21818
 Rf: 91.3
 Rg: 102

CRI (Ra):	94.4		
R1:	96.8	R9:	61.4
R2:	98.1	R10:	94.4
R3:	97.8	R11:	95.7
R4:	95.6	R12:	88.5
R5:	96.9	R13:	97.3
R6:	95.7	R14:	97.8
R7:	90.9	R15:	92.3
R8:	83.0		



Test Conditions

Stabilization Time: 40M
 Operation Time: 1H 40M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-5

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-5

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 7-step quadrangle

REPORT NUMBER: SP1-2506-472-5

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	101	NR	620	317	NR	750	7	NR	880	0	NR
365	0	NR	495	121	NR	625	320	NR	755	6	NR	885	0	NR
370	0	NR	500	141	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	158	NR	635	651	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	207	NR	770	4	NR	900	0	NR
385	0	NR	515	182	NR	645	201	NR	775	3	NR	905	0	NR
390	0	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	146	NR	785	2	NR	915	0	NR
400	1	NR	530	199	NR	660	124	NR	790	2	NR	920	0	NR
405	3	NR	535	205	NR	665	105	NR	795	2	NR	925	0	NR
410	4	NR	540	210	NR	670	96	NR	800	1	NR	930	0	NR
415	7	NR	545	216	NR	675	79	NR	805	1	NR	935	0	NR
420	13	NR	550	222	NR	680	67	NR	810	1	NR	940	0	NR
425	22	NR	555	230	NR	685	58	NR	815	1	NR	945	0	NR
430	37	NR	560	240	NR	690	49	NR	820	1	NR	950	0	NR
435	60	NR	565	248	NR	695	42	NR	825	1	NR	955	0	NR
440	101	NR	570	258	NR	700	36	NR	830	1	NR	960	0	NR
445	172	NR	575	268	NR	705	30	NR	835	1	NR	965	0	NR
450	223	NR	580	278	NR	710	26	NR	840	1	NR	970	0	NR
455	167	NR	585	287	NR	715	22	NR	845	0	NR	975	0	NR
460	126	NR	590	295	NR	720	19	NR	850	0	NR	980	0	NR
465	111	NR	595	298	NR	725	16	NR	855	0	NR	985	0	NR
470	86	NR	600	303	NR	730	14	NR	860	0	NR	990	0	NR
475	74	NR	605	307	NR	735	12	NR	865	0	NR	995	0	NR
480	77	NR	610	341	NR	740	10	NR	870	0	NR	1000	0	NR
485	86	NR	615	368	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-5

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.44

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	101	NR	620	317	NR	750	7	NR	880	0	NR
365	0	NR	495	121	NR	625	320	NR	755	6	NR	885	0	NR
370	0	NR	500	141	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	158	NR	635	651	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	207	NR	770	4	NR	900	0	NR
385	0	NR	515	182	NR	645	201	NR	775	3	NR	905	0	NR
390	0	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	146	NR	785	2	NR	915	0	NR
400	1	NR	530	199	NR	660	124	NR	790	2	NR	920	0	NR
405	3	NR	535	205	NR	665	105	NR	795	2	NR	925	0	NR
410	4	NR	540	210	NR	670	96	NR	800	1	NR	930	0	NR
415	7	NR	545	216	NR	675	79	NR	805	1	NR	935	0	NR
420	13	NR	550	222	NR	680	67	NR	810	1	NR	940	0	NR
425	22	NR	555	230	NR	685	58	NR	815	1	NR	945	0	NR
430	37	NR	560	240	NR	690	49	NR	820	1	NR	950	0	NR
435	60	NR	565	248	NR	695	42	NR	825	1	NR	955	0	NR
440	101	NR	570	258	NR	700	36	NR	830	1	NR	960	0	NR
445	172	NR	575	268	NR	705	30	NR	835	1	NR	965	0	NR
450	223	NR	580	278	NR	710	26	NR	840	1	NR	970	0	NR
455	167	NR	585	287	NR	715	22	NR	845	0	NR	975	0	NR
460	126	NR	590	295	NR	720	19	NR	850	0	NR	980	0	NR
465	111	NR	595	298	NR	725	16	NR	855	0	NR	985	0	NR
470	86	NR	600	303	NR	730	14	NR	860	0	NR	990	0	NR
475	74	NR	605	307	NR	735	12	NR	865	0	NR	995	0	NR
480	77	NR	610	341	NR	740	10	NR	870	0	NR	1000	0	NR
485	86	NR	615	368	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-5

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.85

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	101	NR	620	317	NR	750	7	NR	880	0	NR
365	0	NR	495	121	NR	625	320	NR	755	6	NR	885	0	NR
370	0	NR	500	141	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	158	NR	635	651	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	207	NR	770	4	NR	900	0	NR
385	0	NR	515	182	NR	645	201	NR	775	3	NR	905	0	NR
390	0	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	146	NR	785	2	NR	915	0	NR
400	1	NR	530	199	NR	660	124	NR	790	2	NR	920	0	NR
405	3	NR	535	205	NR	665	105	NR	795	2	NR	925	0	NR
410	4	NR	540	210	NR	670	96	NR	800	1	NR	930	0	NR
415	7	NR	545	216	NR	675	79	NR	805	1	NR	935	0	NR
420	13	NR	550	222	NR	680	67	NR	810	1	NR	940	0	NR
425	22	NR	555	230	NR	685	58	NR	815	1	NR	945	0	NR
430	37	NR	560	240	NR	690	49	NR	820	1	NR	950	0	NR
435	60	NR	565	248	NR	695	42	NR	825	1	NR	955	0	NR
440	101	NR	570	258	NR	700	36	NR	830	1	NR	960	0	NR
445	172	NR	575	268	NR	705	30	NR	835	1	NR	965	0	NR
450	223	NR	580	278	NR	710	26	NR	840	1	NR	970	0	NR
455	167	NR	585	287	NR	715	22	NR	845	0	NR	975	0	NR
460	126	NR	590	295	NR	720	19	NR	850	0	NR	980	0	NR
465	111	NR	595	298	NR	725	16	NR	855	0	NR	985	0	NR
470	86	NR	600	303	NR	730	14	NR	860	0	NR	990	0	NR
475	74	NR	605	307	NR	735	12	NR	865	0	NR	995	0	NR
480	77	NR	610	341	NR	740	10	NR	870	0	NR	1000	0	NR
485	86	NR	615	368	NR	745	8	NR	875	0	NR			

Summary

$R_f = 91.3$
 $R_g = 102$
 $CIE R_a = 94.4$
 $R_9 = 61.4$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 91	CES51 = 96	CES76 = 89
CES02 = 63	CES27 = 96	CES52 = 95	CES77 = 85
CES03 = 32	CES28 = 96	CES53 = 93	CES78 = 86
CES04 = 70	CES29 = 90	CES54 = 98	CES79 = 89
CES05 = 51	CES30 = 96	CES55 = 98	CES80 = 91
CES06 = 51	CES31 = 90	CES56 = 95	CES81 = 72
CES07 = 44	CES32 = 84	CES57 = 95	CES82 = 95
CES08 = 42	CES33 = 91	CES58 = 95	CES83 = 93
CES09 = 29	CES34 = 92	CES59 = 99	CES84 = 96
CES10 = 76	CES35 = 96	CES60 = 96	CES85 = 80
CES11 = 59	CES36 = 90	CES61 = 96	CES86 = 77
CES12 = 65	CES37 = 94	CES62 = 95	CES87 = 91
CES13 = 44	CES38 = 99	CES63 = 94	CES88 = 96
CES14 = 74	CES39 = 97	CES64 = 96	CES89 = 82
CES15 = 72	CES40 = 94	CES65 = 92	CES90 = 97
CES16 = 48	CES41 = 94	CES66 = 95	CES91 = 82
CES17 = 50	CES42 = 91	CES67 = 94	CES92 = 78
CES18 = 57	CES43 = 88	CES68 = 93	CES93 = 87
CES19 = 72	CES44 = 99	CES69 = 94	CES94 = 73
CES20 = 67	CES45 = 93	CES70 = 90	CES95 = 85
CES21 = 86	CES46 = 93	CES71 = 90	CES96 = 92
CES22 = 79	CES47 = 86	CES72 = 96	CES97 = 93
CES23 = 92	CES48 = 95	CES73 = 85	CES98 = 94
CES24 = 91	CES49 = 91	CES74 = 90	CES99 = 93
CES25 = 72	CES50 = 96	CES75 = 90	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)