

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1433602

Luminaire Tested: EHBR1-42-UNV-W-L935

Issue Date: 3/13/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1433602  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2601-654-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/13/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: EHBR1-42-UNV-W-L935  
Description: Elevate Round Highbay at, 42000 lumens, 3500K 90CRI LEDs with W lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 37444.2 lumens  
Efficiency: N/A  
Efficacy: 166.9 lumens/watt  
Spacing Criteria (0/90/45): 1.54 / 1.54 / 1.31  
Luminous Opening: Circular (Dia: 1.71' x H: 0')  
CIE Type: Direct

Input Watts (W): 224.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1433602  
CATALOG NUMBER: EHBR1-42-UNV-W-L935

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°



TEST NUMBER: P1433602  
 CATALOG NUMBER: EHBR1-42-UNV-W-L935

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78
3	96	88	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69
4	89	79	72	67	87	78	71	66	76	70	65	74	69	64	72	67	64	62
5	83	72	65	59	81	71	64	59	69	63	58	67	62	58	66	61	57	55
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50
7	72	61	53	48	71	60	53	47	58	52	47	57	51	47	56	51	47	45
8	68	56	48	43	66	55	48	43	54	47	43	53	47	43	52	46	42	41
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37
10	60	48	41	36	59	47	40	36	46	40	36	45	40	35	45	39	35	34

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	73521	73521	73521
5°	74492	74492	74492
10°	77587	77587	77587
15°	83060	83060	83060
20°	90670	90670	90670
25°	99300	99300	99300
30°	104916	104916	104916
35°	100739	100739	100739
40°	80722	80722	80722
45°	50456	50456	50456
50°	29605	29605	29605
55°	22763	22763	22763
60°	19926	19926	19926
65°	18487	18487	18487
70°	17664	17664	17664
75°	16559	16559	16559
80°	15020	15020	15020
85°	11525	11525	11525

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 50456 cd/sqm



TEST NUMBER: P1433602  
 CATALOG NUMBER: EHBR1-42-UNV-W-L935

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1523.2	4.1
10°-20°	4883.3	13.0
20°-30°	8814.6	23.5
30°-40°	10651.5	28.4
40°-50°	6085.5	16.3
50°-60°	2577.4	6.9
60°-70°	1662.4	4.4
70°-80°	966.6	2.6
80°-90°	255.8	0.7
90°-100°	1.2	0.0
100°-110°	1.5	0.0
110°-120°	1.9	0.0
120°-130°	2.1	0.0
130°-140°	3.8	0.0
140°-150°	5.1	0.0
150°-160°	4.3	0.0
160°-170°	3.0	0.0
170°-180°	1.1	0.0
0°-30°	15221.1	40.7
0°-40°	25872.6	69.1
0°-60°	34535.5	92.2
0°-90°	37420.3	99.9
90°-120°	4.6	0.0
90°-150°	15.6	0.0
90°-180°	24.0	0.1
0°-180°	37444.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	15656	15656	15656	15656	15656	
5°	15802	15802	15802	15802	15802	1523
15°	17084	17084	17084	17084	17084	4883
25°	19164	19164	19164	19164	19164	8815
35°	17572	17572	17572	17572	17572	10651
45°	7597	7597	7597	7597	7597	6085
55°	2780	2780	2780	2780	2780	2577
65°	1664	1664	1664	1664	1664	1662
75°	913	913	913	913	913	967
85°	214	214	214	214	214	246
90°	1	1	1	1	1	10
95°	1	1	1	1	1	1
105°	1	1	1	1	1	1
115°	2	2	2	2	2	2
125°	2	2	2	2	2	2
135°	5	5	5	5	5	4
145°	8	8	8	8	8	5
155°	9	9	9	9	9	4
165°	11	11	11	11	11	3
175°	12	12	12	12	12	1
180°	12	12	12	12	12	



TEST NUMBER: P1433602  
 CATALOG NUMBER: EHBR1-42-UNV-W-L935

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	15655.8	15655.8	15655.8	15655.8	15655.8
2.5°	15708.3	15708.3	15708.3	15708.3	15708.3
5°	15802.1	15802.1	15802.1	15802.1	15802.1
7.5°	15986.7	15986.7	15986.7	15986.7	15986.7
10°	16270.6	16270.6	16270.6	16270.6	16270.6
12.5°	16639.6	16639.6	16639.6	16639.6	16639.6
15°	17084.3	17084.3	17084.3	17084.3	17084.3
17.5°	17593.4	17593.4	17593.4	17593.4	17593.4
20°	18143.2	18143.2	18143.2	18143.2	18143.2
22.5°	18696.8	18696.8	18696.8	18696.8	18696.8
25°	19164.0	19164.0	19164.0	19164.0	19164.0
27.5°	19415.4	19415.4	19415.4	19415.4	19415.4
30°	19347.9	19347.9	19347.9	19347.9	19347.9
32.5°	18774.3	18774.3	18774.3	18774.3	18774.3
35°	17572.2	17572.2	17572.2	17572.2	17572.2
37.5°	15697.7	15697.7	15697.7	15697.7	15697.7
40°	13167.7	13167.7	13167.7	13167.7	13167.7
42.5°	10306.2	10306.2	10306.2	10306.2	10306.2
45°	7597.4	7597.4	7597.4	7597.4	7597.4
47.5°	5430.2	5430.2	5430.2	5430.2	5430.2
50°	4052.3	4052.3	4052.3	4052.3	4052.3
52.5°	3281.1	3281.1	3281.1	3281.1	3281.1
55°	2780.2	2780.2	2780.2	2780.2	2780.2
57.5°	2414.3	2414.3	2414.3	2414.3	2414.3
60°	2121.5	2121.5	2121.5	2121.5	2121.5
62.5°	1877.6	1877.6	1877.6	1877.6	1877.6
65°	1663.7	1663.7	1663.7	1663.7	1663.7
67.5°	1474.8	1474.8	1474.8	1474.8	1474.8
70°	1286.5	1286.5	1286.5	1286.5	1286.5
72.5°	1098.9	1098.9	1098.9	1098.9	1098.9
75°	912.6	912.6	912.6	912.6	912.6
77.5°	733.0	733.0	733.0	733.0	733.0
80°	555.4	555.4	555.4	555.4	555.4
82.5°	380.9	380.9	380.9	380.9	380.9
85°	213.9	213.9	213.9	213.9	213.9
87.5°	67.5	67.5	67.5	67.5	67.5
90°	1.3	1.3	1.3	1.3	1.3
92.5°	0.6	0.6	0.6	0.6	0.6
95°	1.3	1.3	1.3	1.3	1.3
97.5°	1.3	1.3	1.3	1.3	1.3
100°	1.3	1.3	1.3	1.3	1.3
102.5°	1.3	1.3	1.3	1.3	1.3
105°	1.3	1.3	1.3	1.3	1.3
107.5°	1.3	1.3	1.3	1.3	1.3
110°	1.9	1.9	1.9	1.9	1.9



TEST NUMBER: P1433602  
 CATALOG NUMBER: EHBR1-42-UNV-W-L935

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	1.9	1.9	1.9	1.9	1.9
115°	1.9	1.9	1.9	1.9	1.9
117.5°	1.9	1.9	1.9	1.9	1.9
120°	1.9	1.9	1.9	1.9	1.9
122.5°	1.9	1.9	1.9	1.9	1.9
125°	2.5	2.5	2.5	2.5	2.5
127.5°	2.5	2.5	2.5	2.5	2.5
130°	3.2	3.2	3.2	3.2	3.2
132.5°	4.4	4.4	4.4	4.4	4.4
135°	5.0	5.0	5.0	5.0	5.0
137.5°	5.6	5.6	5.6	5.6	5.6
140°	6.9	6.9	6.9	6.9	6.9
142.5°	7.5	7.5	7.5	7.5	7.5
145°	8.2	8.2	8.2	8.2	8.2
147.5°	8.8	8.8	8.8	8.8	8.8
150°	8.8	8.8	8.8	8.8	8.8
152.5°	8.8	8.8	8.8	8.8	8.8
155°	9.4	9.4	9.4	9.4	9.4
157.5°	9.4	9.4	9.4	9.4	9.4
160°	10.0	10.0	10.0	10.0	10.0
162.5°	10.6	10.6	10.6	10.6	10.6
165°	10.6	10.6	10.6	10.6	10.6
167.5°	10.6	10.6	10.6	10.6	10.6
170°	10.6	10.6	10.6	10.6	10.6
172.5°	11.2	11.2	11.2	11.2	11.2
175°	11.9	11.9	11.9	11.9	11.9
177.5°	11.9	11.9	11.9	11.9	11.9
180°	12.5	12.5	12.5	12.5	12.5



TEST NUMBER: P1433602  
 CATALOG NUMBER: EHBR1-42-UNV-W-L935

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.89	21.20	20.26	21.51	21.83	19.89	21.20	20.26	21.51	21.83
	3H	21.48	22.64	21.86	22.98	23.34	21.48	22.64	21.86	22.98	23.34
	4H	22.10	23.19	22.51	23.54	23.93	22.10	23.19	22.51	23.54	23.93
	6H	22.57	23.57	22.98	23.94	24.33	22.57	23.57	22.98	23.94	24.33
	8H	22.71	23.65	23.14	24.04	24.45	22.71	23.65	23.14	24.04	24.45
	12H	22.78	23.68	23.21	24.07	24.50	22.78	23.68	23.21	24.07	24.50
4H	2H	20.38	21.47	20.79	21.82	22.21	20.38	21.47	20.79	21.82	22.21
	3H	22.21	23.11	22.63	23.51	23.92	22.21	23.11	22.63	23.51	23.92
	4H	22.97	23.77	23.40	24.19	24.63	22.97	23.77	23.40	24.19	24.63
	6H	23.56	24.25	24.02	24.70	25.16	23.56	24.25	24.02	24.70	25.16
	8H	23.74	24.38	24.21	24.83	25.30	23.74	24.38	24.21	24.83	25.30
	12H	23.85	24.42	24.33	24.90	25.38	23.85	24.42	24.33	24.90	25.38
8H	4H	23.22	23.87	23.70	24.32	24.79	23.22	23.87	23.70	24.32	24.79
	6H	23.94	24.46	24.44	24.96	25.44	23.94	24.46	24.44	24.96	25.44
	8H	24.19	24.66	24.71	25.18	25.67	24.19	24.66	24.71	25.18	25.67
	12H	24.36	24.78	24.88	25.27	25.85	24.36	24.78	24.88	25.27	25.85
12H	4H	23.24	23.81	23.72	24.29	24.77	23.24	23.81	23.72	24.29	24.77
	6H	23.97	24.45	24.50	24.96	25.46	23.97	24.45	24.50	24.96	25.46
	8H	24.28	24.69	24.79	25.19	25.76	24.28	24.69	24.79	25.19	25.76

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-6

Test Date: 08/01/2025

Luminaire Tested: EHBR-60-L935-N

Data in this report applies to families of products including EHBR-60-L935-N

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2506-472-6  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 08/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **EHBR-60-L935-N**  
 Description: Elevate Round Highbay at, 60000 lumens, 3500K 90CRI LEDs with N lens

**Spectral Parameters**

CCT (K): 3406  
 CIE u': 0.2394  
 CIE v': 0.5094  
 Duv: -0.0028  
 CIE x: 0.4076  
 CIE y: 0.3856  
 CIE z: 0.2068  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 582  
 Purity: 38.0517  
 Rf: 91.3  
 Rg: 100

CRI (Ra):	94.6		
R1:	96.6	R9:	63.8
R2:	98.4	R10:	94.7
R3:	98.1	R11:	96.6
R4:	95.8	R12:	80.9
R5:	96.2	R13:	97.4
R6:	95.4	R14:	98.3
R7:	91.8	R15:	93.1
R8:	84.4		



**Test Conditions**

Stabilization Time: 35M  
 Operation Time: 1H 35M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-6

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-6

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



CCT = 3406K  
 CIE x = 0.4076  
 CIE y = 0.3856  
 Duv = -0.0028

Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-6

**Photopic Flux vs. Wavelength**



**Photopic Lumens: NR**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-6

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: NR**

**S/P: 1.62**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-6

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: NR**

**M/P: 3.3**

$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

**Summary**

$R_f = 91.3$   
 $R_g = 100$   
 $CIE R_a = 94.6$   
 $R_9 = 63.8$



**Color Vector Graphics**



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

CES01 = 86	CES26 = 94	CES51 = 97	CES76 = 90
CES02 = 63	CES27 = 92	CES52 = 98	CES77 = 86
CES03 = 31	CES28 = 97	CES53 = 98	CES78 = 86
CES04 = 70	CES29 = 97	CES54 = 93	CES79 = 90
CES05 = 50	CES30 = 92	CES55 = 92	CES80 = 91
CES06 = 51	CES31 = 97	CES56 = 96	CES81 = 74
CES07 = 43	CES32 = 89	CES57 = 94	CES82 = 96
CES08 = 41	CES33 = 99	CES58 = 95	CES83 = 94
CES09 = 29	CES34 = 94	CES59 = 98	CES84 = 95
CES10 = 75	CES35 = 97	CES60 = 92	CES85 = 79
CES11 = 58	CES36 = 81	CES61 = 93	CES86 = 79
CES12 = 64	CES37 = 96	CES62 = 86	CES87 = 92
CES13 = 44	CES38 = 87	CES63 = 94	CES88 = 98
CES14 = 74	CES39 = 99	CES64 = 91	CES89 = 84
CES15 = 72	CES40 = 97	CES65 = 90	CES90 = 96
CES16 = 48	CES41 = 96	CES66 = 89	CES91 = 75
CES17 = 49	CES42 = 94	CES67 = 88	CES92 = 76
CES18 = 56	CES43 = 93	CES68 = 89	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 90	CES94 = 74
CES20 = 67	CES45 = 97	CES70 = 88	CES95 = 83
CES21 = 86	CES46 = 97	CES71 = 83	CES96 = 92
CES22 = 78	CES47 = 91	CES72 = 94	CES97 = 96
CES23 = 91	CES48 = 91	CES73 = 83	CES98 = 95
CES24 = 90	CES49 = 96	CES74 = 90	CES99 = 92
CES25 = 71	CES50 = 98	CES75 = 85	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)