

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1433348

Luminaire Tested: EHBR1-60-UNV-A1-L850-UPL15

Issue Date: 3/20/2026

Test Information

Test Method: LM-79-2019
Report Number: P1433348
REPORT IS A COMBINATION OF REPORTS P1431893 AND P1431635
Test Lab: INNOVATION CENTER
Issue Date: 3/20/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-60-UNV-A1-L850-UPL15
Description: Elevate Round Highbay at, 60000 lumens, 3000K 90CRI LEDs with A lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 59694.4 lumens
Efficiency: N/A
Efficacy: 175.7 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 1.07 / 0.95
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')
CIE Type: Direct

Input Watts (W): 339.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1433348
CATALOG NUMBER: EHBR1-60-UNV-A1-L850-UPL15

Luminous Intensity Polar Plot





TEST NUMBER: P1433348
 CATALOG NUMBER: EHBR1-60-UNV-A1-L850-UPL15

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	118	118	118	118	115	115	115	115	110	110	110	105	105	105	100	100	100	100	100	100	98
1	111	108	104	101	108	105	102	100	100	98	96	96	94	93	92	91	90	92	91	90	88
2	104	98	92	88	101	96	91	87	92	88	85	88	85	82	85	83	80	85	83	80	78
3	97	89	83	78	95	87	82	77	84	79	75	81	77	74	79	75	72	79	75	72	70
4	91	82	75	70	89	80	74	69	78	72	68	75	70	67	73	69	66	73	69	66	64
5	85	75	68	63	83	74	67	62	72	66	61	70	65	61	68	63	60	68	63	60	58
6	80	69	62	57	78	68	62	57	67	61	56	65	60	56	63	59	55	63	59	55	53
7	75	64	57	52	74	64	57	52	62	56	52	60	55	51	59	54	51	59	54	51	49
8	71	60	53	48	70	59	53	48	58	52	48	57	51	47	55	50	47	55	50	47	45
9	67	56	49	45	66	55	49	44	54	48	44	53	48	44	52	47	44	52	47	44	42
10	64	53	46	41	62	52	46	41	51	45	41	50	45	41	49	44	41	49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	220126	220126	220126	220126	220126
5°	218671	218639	218648	219034	218901
10°	213266	215752	216094	215484	211870
15°	193611	207121	211384	205459	189165
20°	161340	189489	202434	185921	155058
25°	124773	163842	187794	157859	118308
30°	90950	133430	164963	128367	86325
35°	65559	102843	135574	98414	61280
40°	47166	75958	99912	72752	45711
45°	37165	55570	69781	53161	35880
50°	30836	41751	50506	40374	30368
55°	26931	32967	38249	32416	26567
60°	24288	27522	30478	27351	24459
65°	22716	24276	25612	24352	22932
70°	21572	22087	22770	22210	21785
75°	20125	19999	20125	20054	20320
80°	18178	16870	16498	17133	18178
85°	12598	10684	10570	10855	12971

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 67.5°
 Vertical Angle: 45°
 Luminance: 73112 cd/sqm



TEST NUMBER: P1433348
 CATALOG NUMBER: EHBR1-60-UNV-A1-L850-UPL15

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	4426.5	7.4
10°-20°	11897.0	19.9
20°-30°	14466.7	24.2
30°-40°	11784.2	19.7
40°-50°	7075.2	11.9
50°-60°	4071.8	6.8
60°-70°	2548.3	4.3
70°-80°	1500.8	2.5
80°-90°	441.5	0.7
90°-100°	38.7	0.1
100°-110°	255.0	0.4
110°-120°	471.6	0.8
120°-130°	280.3	0.5
130°-140°	171.3	0.3
140°-150°	121.1	0.2
150°-160°	80.7	0.1
160°-170°	47.5	0.1
170°-180°	16.1	0.0
0°-30°	30790.2	51.6
0°-40°	42574.3	71.3
0°-60°	53721.4	90.0
0°-90°	58212.0	97.5
90°-120°	765.4	1.3
90°-150°	1338.1	2.2
90°-180°	1482.0	2.5
0°-180°	59694.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	46874	46874	46874	46874	46874	
5°	46690	46683	46685	46767	46739	4413
15°	40618	43453	44347	43104	39686	11175
25°	24917	32719	37502	31524	23626	11353
35°	12032	18875	24883	18062	11247	7613
45°	6013	8991	11290	8601	5805	4743
55°	3639	4455	5169	4381	3590	3290
65°	2371	2534	2673	2542	2394	2357
75°	1418	1409	1418	1413	1431	1502
85°	433	367	363	373	446	462
90°	12	29	10	31	12	27
95°	20	66	20	56	19	19
105°	90	446	117	475	60	121
115°	410	527	502	583	429	378
125°	297	282	321	313	338	270
135°	219	219	205	229	237	171
145°	185	192	189	195	199	118
155°	169	172	170	173	182	79
165°	167	167	164	167	174	48
175°	172	171	167	169	176	16
180°	171	171	171	171	171	



TEST NUMBER: P1433348
 CATALOG NUMBER: EHBR1-60-UNV-A1-L850-UPL15

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	46874.3	46874.3	46874.3	46874.3	46874.3	46874.3	46874.3	46874.3	46874.3
2.5°	46771.1	46813.4	46831.1	46840.9	46851.7	46881.2	46893.9	46873.3	46891.0
5°	46689.7	46692.6	46682.8	46727.0	46684.8	46714.3	46767.2	46746.6	46738.8
7.5°	46214.5	46312.7	46370.7	46385.3	46393.1	46429.5	46466.8	46255.7	46224.3
10°	45311.2	45475.3	45839.5	45943.5	45912.1	45971.1	45782.5	45230.8	45014.8
12.5°	43331.1	43907.3	44853.8	45275.0	45198.4	45250.4	44608.3	43444.0	42774.4
15°	40618.5	41463.8	43452.8	44283.4	44347.2	44283.4	43104.3	40835.4	39685.8
17.5°	37012.5	38573.4	41502.1	43114.1	43021.8	43052.2	40813.9	37460.1	36144.6
20°	33160.0	34824.1	38945.5	41634.6	41606.1	41435.3	38212.2	33789.4	31869.0
22.5°	28802.9	30949.1	36015.9	39815.4	39804.6	39519.9	35044.0	29780.8	27713.2
25°	24917.1	27022.0	32719.2	37586.8	37502.3	37178.4	31524.4	25782.0	23626.1
27.5°	20899.8	23088.1	29199.6	34975.3	34917.3	34563.9	28159.9	22044.5	19992.7
30°	17494.1	19494.8	25665.2	32101.7	31730.5	31690.3	24691.3	18583.7	16604.5
32.5°	14576.3	16291.3	22333.2	29096.5	28439.7	28627.2	21234.6	15689.6	13727.9
35°	12032.5	13543.5	18875.4	25621.0	24882.7	25125.3	18062.4	12873.8	11247.0
37.5°	9765.6	11218.6	15944.8	22240.8	21111.8	21569.3	15272.3	10751.3	9447.5
40°	8175.1	9327.7	13165.5	18531.8	17317.3	18062.4	12609.8	8967.4	7922.8
42.5°	7044.2	7796.2	10866.1	14990.5	14058.9	14587.1	10392.9	7496.7	6715.3
45°	6013.2	6613.1	8991.0	11829.2	11290.3	11780.1	8601.2	6392.2	5805.2
47.5°	5252.5	5714.8	7401.5	9552.6	9217.8	9372.9	7183.6	5578.4	5101.3
50°	4595.6	4953.0	6222.4	7709.8	7527.2	7622.5	6017.2	4853.8	4525.9
52.5°	4085.1	4347.3	5219.1	6336.3	6246.0	6260.7	5127.7	4269.7	4032.1
55°	3639.4	3822.0	4455.2	5190.6	5169.0	5172.9	4380.7	3783.7	3590.3
57.5°	3249.6	3400.8	3828.9	4360.0	4328.6	4335.5	3793.5	3360.5	3235.9
60°	2919.8	3020.9	3308.6	3684.5	3664.0	3655.1	3288.0	2983.5	2940.4
62.5°	2627.2	2692.0	2891.3	3158.3	3119.1	3127.9	2890.3	2694.9	2631.1
65°	2371.0	2393.6	2533.9	2698.9	2673.3	2694.9	2541.8	2408.3	2393.6
67.5°	2120.6	2143.2	2225.7	2336.6	2307.1	2324.8	2227.7	2149.1	2136.3
70°	1892.8	1891.8	1938.0	1997.9	1997.9	2000.8	1948.8	1901.6	1911.5
72.5°	1657.2	1651.3	1665.1	1705.3	1694.6	1731.8	1676.9	1662.1	1664.1
75°	1417.7	1401.0	1408.8	1429.4	1417.7	1437.3	1412.7	1431.4	1431.4
77.5°	1191.8	1160.5	1150.7	1153.6	1132.0	1161.5	1167.3	1180.0	1209.5
80°	956.3	912.1	887.5	886.5	867.9	886.5	901.3	927.8	956.3
82.5°	709.8	671.5	630.2	622.5	610.7	621.5	641.0	672.5	718.7
85°	433.0	392.7	367.2	353.4	363.3	363.3	373.1	417.3	445.8
87.5°	156.1	136.4	111.9	112.9	115.8	119.7	124.7	157.1	171.8
90°	12.5	17.1	29.3	18.7	10.5	17.9	30.8	16.2	11.5
92.5°	16.4	26.0	47.1	24.4	13.9	24.4	43.8	21.9	15.6
95°	19.8	30.1	65.8	32.5	20.3	30.1	56.0	24.4	18.9
97.5°	24.7	33.3	75.5	39.8	31.6	37.3	63.4	26.0	22.9
100°	32.0	39.0	117.8	48.7	42.2	42.2	116.1	30.1	27.1
102.5°	53.1	82.8	250.1	91.7	64.1	82.8	269.5	60.9	32.8
105°	90.5	174.6	445.8	192.4	116.9	190.0	475.0	159.1	59.6
107.5°	155.4	312.6	587.9	341.1	221.7	354.8	612.3	315.0	138.4
110°	288.6	414.9	616.3	468.5	354.8	496.2	668.3	432.0	279.7



TEST NUMBER: P1433348
 CATALOG NUMBER: EHBR1-60-UNV-A1-L850-UPL15

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
112.5°	389.3	445.8	590.3	517.2	462.0	552.9	652.8	479.1	386.8
115°	409.6	428.7	527.0	505.0	501.8	544.9	583.0	477.4	429.1
117.5°	396.8	391.3	447.4	453.9	484.8	498.5	503.4	448.2	431.5
120°	366.5	348.3	373.5	396.3	437.6	432.0	423.9	406.2	407.2
122.5°	330.9	309.5	319.9	336.9	378.4	366.2	358.0	362.3	374.8
125°	296.9	275.4	281.7	285.8	320.7	308.5	312.8	324.9	337.5
127.5°	266.8	251.9	255.0	250.1	272.0	266.3	279.5	294.3	304.2
130°	246.6	234.2	238.9	226.5	238.1	239.7	257.0	268.3	274.9
132.5°	230.4	222.2	228.7	213.8	217.1	224.7	240.1	250.8	254.0
135°	219.2	211.8	219.1	205.1	205.3	215.0	228.9	235.4	237.1
137.5°	208.7	203.0	210.3	200.6	198.1	208.0	218.5	223.4	222.7
140°	201.0	195.1	203.2	195.9	194.3	204.0	208.9	215.5	213.9
142.5°	191.4	188.1	196.9	192.0	190.4	200.3	202.7	206.8	206.2
145°	185.1	182.6	192.1	189.8	188.9	196.4	194.8	201.5	199.0
147.5°	181.5	178.9	186.6	185.9	185.9	190.8	189.3	195.1	193.7
150°	176.8	174.2	181.9	181.1	181.9	185.2	182.9	190.6	190.8
152.5°	172.1	169.4	176.4	174.7	175.4	178.7	177.4	184.9	186.0
155°	169.1	166.4	171.7	169.7	169.7	172.4	172.7	181.2	182.2
157.5°	168.7	165.9	169.6	167.7	167.7	169.4	170.6	178.3	179.3
160°	168.3	165.4	168.4	166.4	165.6	168.2	169.3	176.2	177.2
162.5°	167.8	165.0	167.7	165.9	164.9	165.9	167.1	174.9	175.9
165°	167.1	165.1	167.3	165.3	164.4	165.3	166.6	171.8	173.6
167.5°	168.1	166.3	167.4	165.4	164.6	163.8	166.8	171.2	173.0
170°	168.3	167.3	167.6	164.8	163.1	164.0	166.1	170.5	172.3
172.5°	170.2	169.3	169.5	166.8	165.0	166.0	167.3	170.9	173.5
175°	172.4	170.4	170.9	168.0	167.0	167.1	169.3	172.0	175.6
177.5°	174.2	172.2	171.9	169.0	167.1	168.1	171.0	173.9	178.2
180°	171.0	171.0	171.0	171.0	171.0	171.0	171.0	171.0	171.0



TEST NUMBER: P1433348
 CATALOG NUMBER: EHBR1-60-UNV-A1-L850-UPL15

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.45	21.67	20.86	22.04	22.42	21.43	22.66	21.84	23.02	23.40
	3H	21.93	23.02	22.36	23.40	23.83	22.70	23.78	23.12	24.17	24.60
	4H	22.54	23.55	22.98	23.95	24.40	23.20	24.21	23.65	24.62	25.06
	6H	23.00	23.93	23.46	24.36	24.81	23.56	24.49	24.02	24.91	25.37
	8H	23.15	24.03	23.63	24.48	24.94	23.65	24.54	24.13	24.98	25.45
	12H	23.23	24.07	23.71	24.51	25.00	23.69	24.54	24.17	24.97	25.46
4H	2H	20.97	21.99	21.42	22.39	22.84	21.75	22.77	22.20	23.17	23.62
	3H	22.66	23.50	23.12	23.95	24.42	23.25	24.08	23.71	24.54	25.00
	4H	23.38	24.13	23.86	24.60	25.10	23.87	24.62	24.35	25.09	25.59
	6H	23.96	24.61	24.47	25.10	25.63	24.35	25.00	24.86	25.49	26.02
	8H	24.15	24.75	24.66	25.25	25.78	24.48	25.09	25.00	25.58	26.11
	12H	24.26	24.79	24.79	25.32	25.85	24.55	25.09	25.08	25.61	26.15
8H	4H	23.61	24.21	24.12	24.70	25.23	24.05	24.66	24.57	25.15	25.68
	6H	24.30	24.79	24.84	25.33	25.87	24.64	25.13	25.18	25.67	26.21
	8H	24.55	24.99	25.11	25.55	26.10	24.83	25.27	25.39	25.83	26.38
	12H	24.72	25.10	25.27	25.64	26.27	24.95	25.34	25.51	25.88	26.51
12H	4H	23.61	24.14	24.14	24.67	25.20	24.05	24.58	24.58	25.11	25.65
	6H	24.32	24.76	24.88	25.32	25.87	24.66	25.10	25.22	25.66	26.21
	8H	24.62	25.00	25.17	25.54	26.17	24.89	25.28	25.45	25.82	26.45

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-4

Test Date: 07/31/2025

Luminaire Tested: EHBR-60-L850-N

Data in this report applies to families of products including EHBR-60-L850-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L850-N**
 Description: Elevate Round Highbay at, 60000 lumens, 5000K 80CRI LEDs with N lens

Spectral Parameters

CCT (K): 4875
 CIE u': 0.2124
 CIE v': 0.4871
 Duv: 0.0005
 CIE x: 0.3488
 CIE y: 0.3555
 CIE z: 0.2957
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 573
 Purity: 11.33556
 Rf: 80
 Rg: 102.3

CRI (Ra):	82.3		
R1:	85.0	R9:	43.9
R2:	83.1	R10:	57.4
R3:	78.8	R11:	83.1
R4:	84.0	R12:	51.0
R5:	83.0	R13:	83.4
R6:	76.3	R14:	87.4
R7:	86.8	R15:	83.4
R8:	81.7		



Test Conditions

Stabilization Time: 39M
 Operation Time: 1H 39M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-4

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 4875K
 CIE x = 0.3488
 CIE y = 0.3555
 Duv = 0.0005

Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-4

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	89	NR	620	280	NR	750	6	NR	880	0	NR
365	0	NR	495	121	NR	625	280	NR	755	5	NR	885	0	NR
370	0	NR	500	168	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	224	NR	635	626	NR	765	4	NR	895	0	NR
380	1	NR	510	275	NR	640	163	NR	770	4	NR	900	0	NR
385	2	NR	515	321	NR	645	160	NR	775	3	NR	905	0	NR
390	3	NR	520	354	NR	650	136	NR	780	3	NR	910	0	NR
395	5	NR	525	375	NR	655	111	NR	785	2	NR	915	0	NR
400	7	NR	530	388	NR	660	93	NR	790	2	NR	920	0	NR
405	10	NR	535	395	NR	665	76	NR	795	2	NR	925	0	NR
410	15	NR	540	397	NR	670	72	NR	800	2	NR	930	0	NR
415	28	NR	545	398	NR	675	57	NR	805	1	NR	935	0	NR
420	53	NR	550	396	NR	680	49	NR	810	1	NR	940	0	NR
425	97	NR	555	395	NR	685	42	NR	815	1	NR	945	0	NR
430	163	NR	560	392	NR	690	37	NR	820	1	NR	950	0	NR
435	261	NR	565	388	NR	695	32	NR	825	1	NR	955	0	NR
440	409	NR	570	381	NR	700	27	NR	830	1	NR	960	0	NR
445	637	NR	575	374	NR	705	23	NR	835	1	NR	965	0	NR
450	699	NR	580	365	NR	710	20	NR	840	1	NR	970	0	NR
455	436	NR	585	354	NR	715	17	NR	845	0	NR	975	0	NR
460	274	NR	590	342	NR	720	15	NR	850	0	NR	980	0	NR
465	205	NR	595	325	NR	725	13	NR	855	0	NR	985	0	NR
470	130	NR	600	313	NR	730	11	NR	860	0	NR	990	0	NR
475	90	NR	605	301	NR	735	10	NR	865	0	NR	995	0	NR
480	78	NR	610	323	NR	740	8	NR	870	0	NR	1000	0	NR
485	77	NR	615	340	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-4

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.82

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	89	NR	620	280	NR	750	6	NR	880	0	NR
365	0	NR	495	121	NR	625	280	NR	755	5	NR	885	0	NR
370	0	NR	500	168	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	224	NR	635	626	NR	765	4	NR	895	0	NR
380	1	NR	510	275	NR	640	163	NR	770	4	NR	900	0	NR
385	2	NR	515	321	NR	645	160	NR	775	3	NR	905	0	NR
390	3	NR	520	354	NR	650	136	NR	780	3	NR	910	0	NR
395	5	NR	525	375	NR	655	111	NR	785	2	NR	915	0	NR
400	7	NR	530	388	NR	660	93	NR	790	2	NR	920	0	NR
405	10	NR	535	395	NR	665	76	NR	795	2	NR	925	0	NR
410	15	NR	540	397	NR	670	72	NR	800	2	NR	930	0	NR
415	28	NR	545	398	NR	675	57	NR	805	1	NR	935	0	NR
420	53	NR	550	396	NR	680	49	NR	810	1	NR	940	0	NR
425	97	NR	555	395	NR	685	42	NR	815	1	NR	945	0	NR
430	163	NR	560	392	NR	690	37	NR	820	1	NR	950	0	NR
435	261	NR	565	388	NR	695	32	NR	825	1	NR	955	0	NR
440	409	NR	570	381	NR	700	27	NR	830	1	NR	960	0	NR
445	637	NR	575	374	NR	705	23	NR	835	1	NR	965	0	NR
450	699	NR	580	365	NR	710	20	NR	840	1	NR	970	0	NR
455	436	NR	585	354	NR	715	17	NR	845	0	NR	975	0	NR
460	274	NR	590	342	NR	720	15	NR	850	0	NR	980	0	NR
465	205	NR	595	325	NR	725	13	NR	855	0	NR	985	0	NR
470	130	NR	600	313	NR	730	11	NR	860	0	NR	990	0	NR
475	90	NR	605	301	NR	735	10	NR	865	0	NR	995	0	NR
480	78	NR	610	323	NR	740	8	NR	870	0	NR	1000	0	NR
485	77	NR	615	340	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.71


λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	89	NR	620	280	NR	750	6	NR	880	0	NR
365	0	NR	495	121	NR	625	280	NR	755	5	NR	885	0	NR
370	0	NR	500	168	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	224	NR	635	626	NR	765	4	NR	895	0	NR
380	1	NR	510	275	NR	640	163	NR	770	4	NR	900	0	NR
385	2	NR	515	321	NR	645	160	NR	775	3	NR	905	0	NR
390	3	NR	520	354	NR	650	136	NR	780	3	NR	910	0	NR
395	5	NR	525	375	NR	655	111	NR	785	2	NR	915	0	NR
400	7	NR	530	388	NR	660	93	NR	790	2	NR	920	0	NR
405	10	NR	535	395	NR	665	76	NR	795	2	NR	925	0	NR
410	15	NR	540	397	NR	670	72	NR	800	2	NR	930	0	NR
415	28	NR	545	398	NR	675	57	NR	805	1	NR	935	0	NR
420	53	NR	550	396	NR	680	49	NR	810	1	NR	940	0	NR
425	97	NR	555	395	NR	685	42	NR	815	1	NR	945	0	NR
430	163	NR	560	392	NR	690	37	NR	820	1	NR	950	0	NR
435	261	NR	565	388	NR	695	32	NR	825	1	NR	955	0	NR
440	409	NR	570	381	NR	700	27	NR	830	1	NR	960	0	NR
445	637	NR	575	374	NR	705	23	NR	835	1	NR	965	0	NR
450	699	NR	580	365	NR	710	20	NR	840	1	NR	970	0	NR
455	436	NR	585	354	NR	715	17	NR	845	0	NR	975	0	NR
460	274	NR	590	342	NR	720	15	NR	850	0	NR	980	0	NR
465	205	NR	595	325	NR	725	13	NR	855	0	NR	985	0	NR
470	130	NR	600	313	NR	730	11	NR	860	0	NR	990	0	NR
475	90	NR	605	301	NR	735	10	NR	865	0	NR	995	0	NR
480	78	NR	610	323	NR	740	8	NR	870	0	NR	1000	0	NR
485	77	NR	615	340	NR	745	7	NR	875	0	NR			

Summary

$R_f = 80$
 $R_g = 102.3$
 $CIE R_a = 82.3$
 $R_9 = 43.9$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 67	CES51 = 92	CES76 = 54
CES02 = 60	CES27 = 88	CES52 = 91	CES77 = 71
CES03 = 31	CES28 = 81	CES53 = 82	CES78 = 55
CES04 = 69	CES29 = 66	CES54 = 92	CES79 = 81
CES05 = 47	CES30 = 80	CES55 = 90	CES80 = 75
CES06 = 50	CES31 = 69	CES56 = 81	CES81 = 79
CES07 = 40	CES32 = 61	CES57 = 80	CES82 = 90
CES08 = 39	CES33 = 76	CES58 = 81	CES83 = 87
CES09 = 29	CES34 = 68	CES59 = 93	CES84 = 87
CES10 = 73	CES35 = 82	CES60 = 94	CES85 = 82
CES11 = 56	CES36 = 95	CES61 = 91	CES86 = 83
CES12 = 62	CES37 = 75	CES62 = 89	CES87 = 78
CES13 = 42	CES38 = 87	CES63 = 80	CES88 = 85
CES14 = 74	CES39 = 94	CES64 = 79	CES89 = 81
CES15 = 71	CES40 = 87	CES65 = 75	CES90 = 86
CES16 = 46	CES41 = 91	CES66 = 72	CES91 = 80
CES17 = 48	CES42 = 71	CES67 = 69	CES92 = 77
CES18 = 56	CES43 = 72	CES68 = 75	CES93 = 86
CES19 = 70	CES44 = 99	CES69 = 80	CES94 = 71
CES20 = 65	CES45 = 81	CES70 = 66	CES95 = 79
CES21 = 85	CES46 = 83	CES71 = 59	CES96 = 86
CES22 = 77	CES47 = 83	CES72 = 87	CES97 = 85
CES23 = 91	CES48 = 83	CES73 = 56	CES98 = 82
CES24 = 90	CES49 = 82	CES74 = 95	CES99 = 84
CES25 = 71	CES50 = 91	CES75 = 58	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)