

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1433000

Luminaire Tested: EHBR1-42-UNV-A1-L850-UPL36

Issue Date: 3/20/2026

Test Information

Test Method: LM-79-2019
Report Number: P1433000
REPORT IS A COMBINATION OF REPORTS P1431801 AND P1431635
Test Lab: INNOVATION CENTER
Issue Date: 3/20/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-42-UNV-A1-L850-UPL36
Description: Elevate Round Highbay at, 42000 lumens, 5000K 80CRI LEDs with A lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 44276.2 lumens
Efficiency: N/A
Efficacy: 175.1 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 1.07 / 0.95
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')
CIE Type: Direct

Input Watts (W): 252.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1433000
CATALOG NUMBER: EHBR1-42-UNV-A1-L850-UPL36

Luminous Intensity Polar Plot





TEST NUMBER: P1433000
 CATALOG NUMBER: EHBR1-42-UNV-A1-L850-UPL36

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	113	113	113	113	107	107	107	100	100	100	95	95	95	95	95	95	92
1	110	106	103	100	106	103	100	98	97	95	93	92	90	89	88	86	85	85	85	85	82
2	102	96	91	87	99	94	89	85	89	85	82	85	82	79	81	78	76	76	76	76	74
3	96	87	81	76	93	85	80	75	81	77	73	78	74	71	74	71	68	68	68	68	66
4	89	80	73	68	87	78	72	67	75	70	65	72	67	64	69	65	62	62	62	62	60
5	84	74	66	61	81	72	65	61	69	64	59	67	62	58	64	60	57	57	57	57	55
6	79	68	61	56	76	67	60	55	64	58	54	62	57	53	60	55	52	52	52	52	50
7	74	63	56	51	72	62	55	50	60	54	50	58	53	49	56	51	48	48	48	48	46
8	70	59	52	47	68	58	51	46	56	50	46	54	49	45	52	48	44	44	44	44	43
9	66	55	48	43	64	54	47	43	52	46	42	51	45	42	49	45	41	41	41	41	40
10	62	51	45	40	61	50	44	40	49	43	39	48	42	39	46	42	38	38	38	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	153697	153697	153697	153697	153697
5°	152681	152658	152665	152934	152842
10°	148907	150643	150882	150456	147933
15°	135183	144616	147593	143456	132079
20°	112651	132305	141344	129814	108265
25°	87120	114399	131122	110221	82606
30°	63503	93164	115181	89629	60274
35°	45775	71807	94661	68715	42787
40°	32932	53036	69761	50798	31916
45°	25950	38800	48723	37118	25052
50°	21531	29152	35264	28191	21204
55°	18804	23018	26706	22634	18550
60°	16959	19216	21280	19096	17078
65°	15861	16950	17883	17003	16011
70°	15062	15421	15898	15508	15211
75°	14052	13964	14052	14003	14189
80°	12692	11778	11519	11962	12692
85°	8796	7460	7379	7579	9054

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 67.5°
 Vertical Angle: 45°
 Luminance: 51049 cd/sqm



TEST NUMBER: P1433000
 CATALOG NUMBER: EHBR1-42-UNV-A1-L850-UPL36

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	3090.7	7.0
10°-20°	8306.7	18.8
20°-30°	10100.9	22.8
30°-40°	8228.0	18.6
40°-50°	4940.1	11.2
50°-60°	2843.0	6.4
60°-70°	1779.3	4.0
70°-80°	1047.9	2.4
80°-90°	312.9	0.7
90°-100°	95.4	0.2
100°-110°	630.6	1.4
110°-120°	1166.6	2.6
120°-130°	692.3	1.6
130°-140°	418.6	0.9
140°-150°	290.2	0.7
150°-160°	189.2	0.4
160°-170°	108.1	0.2
170°-180°	35.8	0.1
0°-30°	21498.4	48.6
0°-40°	29726.4	67.1
0°-60°	37509.5	84.7
0°-90°	40649.5	91.8
90°-120°	1892.5	4.3
90°-150°	3293.6	7.4
90°-180°	3627.0	8.2
0°-180°	44276.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	32729	32729	32729	32729	32729	
5°	32600	32595	32596	32654	32634	3081
15°	28361	30340	30964	30096	27710	7802
25°	17398	22845	26185	22011	16496	7927
35°	8401	13179	17374	12612	7853	5315
45°	4199	6278	7883	6006	4053	3312
55°	2541	3111	3609	3059	2507	2297
65°	1656	1769	1867	1775	1671	1646
75°	990	984	990	986	1000	1048
85°	302	256	254	260	311	323
90°	28	72	26	76	27	28
95°	46	163	50	139	45	44
105°	220	1103	289	1175	144	295
115°	1010	1304	1242	1443	1058	931
125°	729	697	794	772	830	665
135°	534	535	501	559	578	417
145°	442	462	454	466	475	280
155°	392	404	403	405	423	183
165°	374	381	377	377	390	107
175°	374	377	375	373	382	36
180°	376	376	376	376	376	



TEST NUMBER: P1433000
 CATALOG NUMBER: EHBR1-42-UNV-A1-L850-UPL36

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	32728.7	32728.7	32728.7	32728.7	32728.7	32728.7	32728.7	32728.7	32728.7
2.5°	32656.7	32686.1	32698.5	32705.3	32712.8	32733.5	32742.3	32728.0	32740.3
5°	32599.8	32601.8	32595.0	32625.8	32596.3	32616.9	32653.9	32639.6	32634.1
7.5°	32268.0	32336.5	32377.0	32387.2	32392.7	32418.2	32444.2	32296.7	32274.8
10°	31637.3	31751.9	32006.1	32078.8	32056.9	32098.0	31966.4	31581.1	31430.4
12.5°	30254.7	30657.1	31317.9	31612.0	31558.5	31594.8	31146.6	30333.5	29866.0
15°	28360.7	28950.9	30339.7	30919.7	30964.2	30919.7	30096.4	28512.2	27709.5
17.5°	25842.9	26932.8	28977.7	30103.2	30038.7	30060.0	28497.1	26155.5	25237.0
20°	23153.0	24315.0	27192.6	29070.2	29050.3	28931.0	26680.5	23592.5	22251.6
22.5°	20110.8	21609.3	25147.2	27800.0	27792.4	27593.7	24468.5	20793.6	19349.9
25°	17397.7	18867.3	22845.3	26243.9	26185.0	25958.8	22011.0	18001.6	16496.3
27.5°	14592.7	16120.6	20387.8	24420.6	24380.1	24133.3	19661.8	15392.0	13959.3
30°	12214.7	13611.7	17920.0	22414.1	22155.0	22126.9	17240.1	12975.6	11593.7
32.5°	10177.4	11375.0	15593.5	20315.8	19857.2	19988.1	14826.4	10954.8	9585.2
35°	8401.3	9456.3	13179.2	17889.2	17373.7	17543.0	12611.7	8988.8	7853.0
37.5°	6818.5	7833.1	11133.0	15529.1	14740.8	15060.1	10663.5	7506.7	6596.4
40°	5708.0	6512.8	9192.4	12939.2	12091.3	12611.7	8804.5	6261.3	5531.9
42.5°	4918.4	5443.4	7587.0	10466.7	9816.2	10185.0	7256.5	5234.4	4688.7
45°	4198.6	4617.5	6277.7	8259.5	7883.2	8225.2	6005.6	4463.2	4053.3
47.5°	3667.3	3990.2	5167.9	6669.8	6436.0	6544.4	5015.7	3894.9	3561.8
50°	3208.8	3458.3	4344.6	5383.1	5255.6	5322.1	4201.4	3389.0	3160.1
52.5°	2852.3	3035.3	3644.0	4424.2	4361.1	4371.3	3580.3	2981.2	2815.3
55°	2541.1	2668.6	3110.7	3624.2	3609.1	3611.8	3058.7	2641.9	2506.8
57.5°	2269.0	2374.5	2673.4	3044.2	3022.3	3027.2	2648.8	2346.4	2259.4
60°	2038.7	2109.3	2310.1	2572.6	2558.2	2552.1	2295.7	2083.2	2053.0
62.5°	1834.3	1879.6	2018.7	2205.3	2177.8	2183.9	2018.0	1881.7	1837.1
65°	1655.5	1671.2	1769.2	1884.4	1866.6	1881.7	1774.7	1681.5	1671.2
67.5°	1480.6	1496.4	1554.0	1631.5	1610.9	1623.3	1555.4	1500.6	1491.6
70°	1321.6	1320.9	1353.1	1395.0	1395.0	1397.0	1360.7	1327.8	1334.7
72.5°	1157.1	1153.0	1162.6	1190.6	1183.2	1209.2	1170.8	1160.5	1161.9
75°	989.9	978.2	983.7	998.1	989.9	1003.5	986.4	999.5	999.5
77.5°	832.2	810.2	803.4	805.5	790.4	810.9	815.0	824.0	844.5
80°	667.7	636.8	619.6	618.9	606.0	618.9	629.3	647.8	667.7
82.5°	495.6	468.9	440.1	434.6	426.4	433.9	447.6	469.5	501.8
85°	302.3	274.2	256.4	246.8	253.6	253.6	260.5	291.4	311.2
87.5°	109.0	95.3	78.2	78.9	80.8	83.6	87.0	109.7	119.9
90°	27.5	42.2	72.3	46.2	26.1	44.2	76.3	40.2	26.8
92.5°	38.9	64.3	116.5	60.3	34.2	60.3	108.5	54.2	36.8
95°	45.6	74.4	162.8	80.4	50.2	74.4	138.6	60.3	44.9
97.5°	57.7	82.4	186.8	98.4	78.4	92.4	156.7	64.3	54.9
100°	75.7	96.5	291.4	120.5	104.5	104.5	287.3	74.4	63.7
102.5°	128.0	204.9	618.8	227.0	158.7	204.9	667.1	150.7	77.7
105°	220.3	432.0	1103.0	476.2	289.3	470.1	1175.4	393.8	144.0
107.5°	381.1	773.6	1454.7	843.9	548.5	878.0	1514.9	779.6	338.9
110°	710.6	1026.7	1525.0	1159.3	878.0	1227.6	1653.6	1068.9	688.5



TEST NUMBER: P1433000
 CATALOG NUMBER: EHBR1-42-UNV-A1-L850-UPL36

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
112.5°	959.8	1103.0	1460.7	1279.8	1143.2	1368.2	1615.4	1185.4	953.7
115°	1010.0	1060.9	1304.0	1249.7	1241.7	1348.2	1442.6	1181.4	1058.2
117.5°	976.5	968.4	1107.1	1123.2	1199.5	1233.7	1245.7	1109.1	1064.2
120°	903.5	862.0	924.2	980.5	1083.0	1068.9	1048.8	1003.3	1004.0
122.5°	813.7	764.2	791.6	833.8	936.3	906.2	886.0	894.8	922.3
125°	729.4	679.8	697.2	707.3	793.6	763.5	772.2	802.3	829.8
127.5°	655.1	621.5	630.9	618.8	673.1	659.0	689.9	724.6	747.4
130°	604.8	576.0	589.4	560.6	587.4	591.3	632.3	660.4	675.1
132.5°	563.3	544.6	560.6	525.7	533.8	550.6	588.8	613.5	621.6
135°	533.9	517.1	535.2	502.3	501.1	525.1	559.3	575.3	578.1
137.5°	507.8	493.7	511.8	487.6	481.6	505.7	531.8	543.9	540.6
140°	485.1	472.3	492.3	474.3	470.2	494.4	506.4	521.2	517.2
142.5°	459.6	451.6	474.9	463.0	458.9	481.7	487.7	497.7	494.4
145°	442.2	436.1	461.6	455.6	453.5	470.3	466.3	481.0	475.0
147.5°	428.2	423.5	446.2	444.2	444.2	456.3	450.9	463.6	458.3
150°	414.8	410.1	432.8	430.8	432.8	440.9	433.5	448.9	447.6
152.5°	401.5	396.8	417.5	414.7	416.8	424.7	418.2	434.9	434.3
155°	392.0	387.3	404.0	402.6	402.6	407.4	404.7	422.2	422.9
157.5°	386.0	382.7	395.4	394.0	394.0	396.8	396.1	411.5	412.2
160°	381.4	378.1	388.7	387.3	385.4	390.1	389.4	402.8	403.5
162.5°	376.8	373.4	385.4	382.7	382.0	382.7	382.1	396.2	396.8
165°	373.5	372.1	380.7	379.4	377.4	379.4	377.4	386.8	389.5
167.5°	374.1	371.4	379.5	378.1	376.0	374.1	376.1	383.5	386.1
170°	372.7	372.0	378.1	374.7	372.0	372.7	372.8	380.1	382.8
172.5°	374.1	373.4	379.5	376.1	373.4	374.1	372.0	377.4	382.1
175°	374.2	372.8	377.4	375.4	374.7	373.5	373.4	376.8	382.2
177.5°	376.8	375.4	378.1	376.0	373.5	374.1	376.1	379.5	386.9
180°	376.1	376.1	376.1	376.1	376.1	376.1	376.1	376.1	376.1



TEST NUMBER: P1433000
 CATALOG NUMBER: EHBR1-42-UNV-A1-L850-UPL36

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.76	19.89	19.26	20.37	20.89	19.74	20.87	20.24	21.35	21.87
	3H	20.23	21.24	20.75	21.74	22.30	21.00	22.01	21.52	22.50	23.06
	4H	20.83	21.77	21.37	22.29	22.87	21.50	22.44	22.04	22.95	23.53
	6H	21.30	22.16	21.85	22.69	23.28	21.85	22.72	22.40	23.24	23.83
	8H	21.44	22.26	22.01	22.81	23.41	21.95	22.77	22.51	23.31	23.91
	12H	21.52	22.30	22.09	22.84	23.46	21.98	22.77	22.55	23.31	23.93
4H	2H	19.27	20.21	19.81	20.72	21.31	20.05	20.99	20.59	21.50	22.09
	3H	20.95	21.73	21.51	22.29	22.88	21.54	22.31	22.09	22.87	23.47
	4H	21.67	22.37	22.24	22.93	23.57	22.16	22.86	22.73	23.42	24.06
	6H	22.25	22.85	22.84	23.44	24.09	22.64	23.24	23.23	23.83	24.48
	8H	22.43	23.00	23.04	23.59	24.24	22.77	23.33	23.37	23.92	24.58
	12H	22.54	23.04	23.16	23.66	24.32	22.84	23.33	23.46	23.95	24.62
8H	4H	21.89	22.45	22.49	23.04	23.70	22.34	22.90	22.94	23.49	24.15
	6H	22.58	23.04	23.21	23.68	24.34	22.92	23.38	23.55	24.02	24.68
	8H	22.83	23.24	23.48	23.89	24.57	23.11	23.52	23.77	24.17	24.85
	12H	23.00	23.36	23.64	23.99	24.74	23.23	23.59	23.88	24.22	24.97
12H	4H	21.89	22.39	22.51	23.01	23.67	22.33	22.83	22.95	23.45	24.11
	6H	22.60	23.01	23.26	23.66	24.34	22.94	23.35	23.59	24.00	24.68
	8H	22.90	23.26	23.54	23.89	24.64	23.18	23.54	23.82	24.17	24.91

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-4

Test Date: 07/31/2025

Luminaire Tested: EHBR-60-L850-N

Data in this report applies to families of products including EHBR-60-L850-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-4
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L850-N**
 Description: Elevate Round Highbay at, 60000 lumens, 5000K 80CRI LEDs with N lens

Spectral Parameters

CCT (K): 4875
 CIE u': 0.2124
 CIE v': 0.4871
 Duv: 0.0005
 CIE x: 0.3488
 CIE y: 0.3555
 CIE z: 0.2957
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 573
 Purity: 11.33556
 Rf: 80
 Rg: 102.3

CRI (Ra):	82.3		
R1:	85.0	R9:	43.9
R2:	83.1	R10:	57.4
R3:	78.8	R11:	83.1
R4:	84.0	R12:	51.0
R5:	83.0	R13:	83.4
R6:	76.3	R14:	87.4
R7:	86.8	R15:	83.4
R8:	81.7		



Test Conditions

Stabilization Time: 39M
 Operation Time: 1H 39M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-4

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-4

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	89	NR	620	280	NR	750	6	NR	880	0	NR
365	0	NR	495	121	NR	625	280	NR	755	5	NR	885	0	NR
370	0	NR	500	168	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	224	NR	635	626	NR	765	4	NR	895	0	NR
380	1	NR	510	275	NR	640	163	NR	770	4	NR	900	0	NR
385	2	NR	515	321	NR	645	160	NR	775	3	NR	905	0	NR
390	3	NR	520	354	NR	650	136	NR	780	3	NR	910	0	NR
395	5	NR	525	375	NR	655	111	NR	785	2	NR	915	0	NR
400	7	NR	530	388	NR	660	93	NR	790	2	NR	920	0	NR
405	10	NR	535	395	NR	665	76	NR	795	2	NR	925	0	NR
410	15	NR	540	397	NR	670	72	NR	800	2	NR	930	0	NR
415	28	NR	545	398	NR	675	57	NR	805	1	NR	935	0	NR
420	53	NR	550	396	NR	680	49	NR	810	1	NR	940	0	NR
425	97	NR	555	395	NR	685	42	NR	815	1	NR	945	0	NR
430	163	NR	560	392	NR	690	37	NR	820	1	NR	950	0	NR
435	261	NR	565	388	NR	695	32	NR	825	1	NR	955	0	NR
440	409	NR	570	381	NR	700	27	NR	830	1	NR	960	0	NR
445	637	NR	575	374	NR	705	23	NR	835	1	NR	965	0	NR
450	699	NR	580	365	NR	710	20	NR	840	1	NR	970	0	NR
455	436	NR	585	354	NR	715	17	NR	845	0	NR	975	0	NR
460	274	NR	590	342	NR	720	15	NR	850	0	NR	980	0	NR
465	205	NR	595	325	NR	725	13	NR	855	0	NR	985	0	NR
470	130	NR	600	313	NR	730	11	NR	860	0	NR	990	0	NR
475	90	NR	605	301	NR	735	10	NR	865	0	NR	995	0	NR
480	78	NR	610	323	NR	740	8	NR	870	0	NR	1000	0	NR
485	77	NR	615	340	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-4

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.82

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	89	NR	620	280	NR	750	6	NR	880	0	NR
365	0	NR	495	121	NR	625	280	NR	755	5	NR	885	0	NR
370	0	NR	500	168	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	224	NR	635	626	NR	765	4	NR	895	0	NR
380	1	NR	510	275	NR	640	163	NR	770	4	NR	900	0	NR
385	2	NR	515	321	NR	645	160	NR	775	3	NR	905	0	NR
390	3	NR	520	354	NR	650	136	NR	780	3	NR	910	0	NR
395	5	NR	525	375	NR	655	111	NR	785	2	NR	915	0	NR
400	7	NR	530	388	NR	660	93	NR	790	2	NR	920	0	NR
405	10	NR	535	395	NR	665	76	NR	795	2	NR	925	0	NR
410	15	NR	540	397	NR	670	72	NR	800	2	NR	930	0	NR
415	28	NR	545	398	NR	675	57	NR	805	1	NR	935	0	NR
420	53	NR	550	396	NR	680	49	NR	810	1	NR	940	0	NR
425	97	NR	555	395	NR	685	42	NR	815	1	NR	945	0	NR
430	163	NR	560	392	NR	690	37	NR	820	1	NR	950	0	NR
435	261	NR	565	388	NR	695	32	NR	825	1	NR	955	0	NR
440	409	NR	570	381	NR	700	27	NR	830	1	NR	960	0	NR
445	637	NR	575	374	NR	705	23	NR	835	1	NR	965	0	NR
450	699	NR	580	365	NR	710	20	NR	840	1	NR	970	0	NR
455	436	NR	585	354	NR	715	17	NR	845	0	NR	975	0	NR
460	274	NR	590	342	NR	720	15	NR	850	0	NR	980	0	NR
465	205	NR	595	325	NR	725	13	NR	855	0	NR	985	0	NR
470	130	NR	600	313	NR	730	11	NR	860	0	NR	990	0	NR
475	90	NR	605	301	NR	735	10	NR	865	0	NR	995	0	NR
480	78	NR	610	323	NR	740	8	NR	870	0	NR	1000	0	NR
485	77	NR	615	340	NR	745	7	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-4

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.71

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	89	NR	620	280	NR	750	6	NR	880	0	NR
365	0	NR	495	121	NR	625	280	NR	755	5	NR	885	0	NR
370	0	NR	500	168	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	224	NR	635	626	NR	765	4	NR	895	0	NR
380	1	NR	510	275	NR	640	163	NR	770	4	NR	900	0	NR
385	2	NR	515	321	NR	645	160	NR	775	3	NR	905	0	NR
390	3	NR	520	354	NR	650	136	NR	780	3	NR	910	0	NR
395	5	NR	525	375	NR	655	111	NR	785	2	NR	915	0	NR
400	7	NR	530	388	NR	660	93	NR	790	2	NR	920	0	NR
405	10	NR	535	395	NR	665	76	NR	795	2	NR	925	0	NR
410	15	NR	540	397	NR	670	72	NR	800	2	NR	930	0	NR
415	28	NR	545	398	NR	675	57	NR	805	1	NR	935	0	NR
420	53	NR	550	396	NR	680	49	NR	810	1	NR	940	0	NR
425	97	NR	555	395	NR	685	42	NR	815	1	NR	945	0	NR
430	163	NR	560	392	NR	690	37	NR	820	1	NR	950	0	NR
435	261	NR	565	388	NR	695	32	NR	825	1	NR	955	0	NR
440	409	NR	570	381	NR	700	27	NR	830	1	NR	960	0	NR
445	637	NR	575	374	NR	705	23	NR	835	1	NR	965	0	NR
450	699	NR	580	365	NR	710	20	NR	840	1	NR	970	0	NR
455	436	NR	585	354	NR	715	17	NR	845	0	NR	975	0	NR
460	274	NR	590	342	NR	720	15	NR	850	0	NR	980	0	NR
465	205	NR	595	325	NR	725	13	NR	855	0	NR	985	0	NR
470	130	NR	600	313	NR	730	11	NR	860	0	NR	990	0	NR
475	90	NR	605	301	NR	735	10	NR	865	0	NR	995	0	NR
480	78	NR	610	323	NR	740	8	NR	870	0	NR	1000	0	NR
485	77	NR	615	340	NR	745	7	NR	875	0	NR			

Summary

$R_f = 80$
 $R_g = 102.3$
 $CIE R_a = 82.3$
 $R_9 = 43.9$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 67	CES51 = 92	CES76 = 54
CES02 = 60	CES27 = 88	CES52 = 91	CES77 = 71
CES03 = 31	CES28 = 81	CES53 = 82	CES78 = 55
CES04 = 69	CES29 = 66	CES54 = 92	CES79 = 81
CES05 = 47	CES30 = 80	CES55 = 90	CES80 = 75
CES06 = 50	CES31 = 69	CES56 = 81	CES81 = 79
CES07 = 40	CES32 = 61	CES57 = 80	CES82 = 90
CES08 = 39	CES33 = 76	CES58 = 81	CES83 = 87
CES09 = 29	CES34 = 68	CES59 = 93	CES84 = 87
CES10 = 73	CES35 = 82	CES60 = 94	CES85 = 82
CES11 = 56	CES36 = 95	CES61 = 91	CES86 = 83
CES12 = 62	CES37 = 75	CES62 = 89	CES87 = 78
CES13 = 42	CES38 = 87	CES63 = 80	CES88 = 85
CES14 = 74	CES39 = 94	CES64 = 79	CES89 = 81
CES15 = 71	CES40 = 87	CES65 = 75	CES90 = 86
CES16 = 46	CES41 = 91	CES66 = 72	CES91 = 80
CES17 = 48	CES42 = 71	CES67 = 69	CES92 = 77
CES18 = 56	CES43 = 72	CES68 = 75	CES93 = 86
CES19 = 70	CES44 = 99	CES69 = 80	CES94 = 71
CES20 = 65	CES45 = 81	CES70 = 66	CES95 = 79
CES21 = 85	CES46 = 83	CES71 = 59	CES96 = 86
CES22 = 77	CES47 = 83	CES72 = 87	CES97 = 85
CES23 = 91	CES48 = 83	CES73 = 56	CES98 = 82
CES24 = 90	CES49 = 82	CES74 = 95	CES99 = 84
CES25 = 71	CES50 = 91	CES75 = 58	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)