

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1433465

Luminaire Tested: EHBR1-18-UNV-N-L935-UPL40

Issue Date: 3/20/2026

Test Information

Test Method: LM-79-2019
Report Number: P1433465
REPORT IS A COMBINATION OF REPORTS P1431690 AND P1431635
Test Lab: INNOVATION CENTER
Issue Date: 3/20/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-18-UNV-N-L935-UPL40
Description: Elevate Round Highbay at, 19000 lumens, 3500K 90CRI LEDs with N lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 20275.8 lumens
Efficiency: N/A
Efficacy: 161.8 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.8
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 125.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1433465
CATALOG NUMBER: EHBR1-18-UNV-N-L935-UPL40

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1433465

CATALOG NUMBER: EHBR1-18-UNV-N-L935-UPL40

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	115	115	115	115	110	110	110	110	102	102	102	94	94	94	87	87	87	87	87	87	83
1	108	105	102	99	104	101	98	96	94	92	90	87	85	84	81	80	79	79	79	79	76
2	101	95	91	87	97	92	88	84	86	83	80	81	78	76	76	74	72	72	72	72	69
3	95	88	82	77	92	85	80	75	80	75	72	75	72	69	71	68	66	66	66	66	63
4	89	81	74	70	86	78	73	68	74	69	66	70	66	63	66	63	61	61	61	61	58
5	84	75	68	63	81	73	67	62	69	64	60	66	61	58	62	59	56	56	56	56	54
6	80	70	63	58	77	68	62	57	65	59	56	62	57	54	59	55	52	52	52	52	50
7	75	65	58	54	73	64	57	53	61	55	52	58	54	50	55	52	49	49	49	49	47
8	71	61	54	50	69	60	54	49	57	52	48	55	50	47	53	49	46	46	46	46	44
9	68	57	51	47	66	56	50	46	54	49	45	52	47	44	50	46	43	43	43	43	42
10	64	54	48	44	63	53	47	43	51	46	42	49	45	42	47	43	41	41	41	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	92383	92383	92383
5°	90590	90590	90590
10°	85980	85980	85980
15°	78231	78231	78231
20°	67105	67105	67105
25°	52789	52789	52789
30°	36226	36226	36226
35°	21520	21520	21520
40°	12733	12733	12733
45°	9141	9141	9141
50°	7513	7513	7513
55°	6828	6828	6828
60°	6537	6537	6537
65°	6234	6234	6234
70°	5798	5798	5798
75°	5241	5241	5241
80°	4349	4349	4349
85°	2755	2755	2755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9141 cd/sqm



TEST NUMBER: P1433465

CATALOG NUMBER: EHBR1-18-UNV-N-L935-UPL40

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1812.1	8.9
10°-20°	4548.8	22.4
20°-30°	4756.2	23.5
30°-40°	2577.1	12.7
40°-50°	1185.6	5.8
50°-60°	835.5	4.1
60°-70°	643.0	3.2
70°-80°	389.8	1.9
80°-90°	116.0	0.6
90°-100°	97.3	0.5
100°-110°	609.6	3.0
110°-120°	1090.0	5.4
120°-130°	639.6	3.2
130°-140°	392.3	1.9
140°-150°	272.1	1.3
150°-160°	176.8	0.9
160°-170°	100.8	0.5
170°-180°	33.3	0.2
0°-30°	11117.1	54.8
0°-40°	13694.2	67.5
0°-60°	15715.2	77.5
0°-90°	16863.9	83.2
90°-120°	1796.9	8.9
90°-150°	3101.0	15.3
90°-180°	3412.0	16.8
0°-180°	20275.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	19672	19672	19672	19672	19672	
5°	19342	19342	19342	19342	19342	1812
15°	16412	16412	16412	16412	16412	4549
25°	10542	10542	10542	10542	10542	4756
35°	3950	3950	3950	3950	3950	2577
45°	1479	1479	1479	1479	1479	1186
55°	923	923	923	923	923	835
65°	651	651	651	651	651	643
75°	369	369	369	369	369	390
85°	95	95	95	95	95	105
90°	26	42	71	46	26	17
95°	43	72	158	78	49	41
105°	213	420	1072	463	281	285
115°	980	1031	1268	1215	1207	903
125°	707	660	678	688	772	644
135°	516	500	518	486	484	403
145°	424	418	443	438	436	268
155°	371	367	385	385	385	173
165°	348	348	357	357	356	99
175°	344	344	350	350	350	33
180°	348	348	348	348	348	



TEST NUMBER: P1433465

CATALOG NUMBER: EHBR1-18-UNV-N-L935-UPL40

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	19672.3	19672.3	19672.3	19672.3	19672.3
2.5°	19602.6	19602.6	19602.6	19602.6	19602.6
5°	19342.4	19342.4	19342.4	19342.4	19342.4
7.5°	18898.1	18898.1	18898.1	18898.1	18898.1
10°	18267.7	18267.7	18267.7	18267.7	18267.7
12.5°	17453.1	17453.1	17453.1	17453.1	17453.1
15°	16412.4	16412.4	16412.4	16412.4	16412.4
17.5°	15205.0	15205.0	15205.0	15205.0	15205.0
20°	13792.0	13792.0	13792.0	13792.0	13792.0
22.5°	12218.8	12218.8	12218.8	12218.8	12218.8
25°	10541.9	10541.9	10541.9	10541.9	10541.9
27.5°	8764.1	8764.1	8764.1	8764.1	8764.1
30°	6968.1	6968.1	6968.1	6968.1	6968.1
32.5°	5347.8	5347.8	5347.8	5347.8	5347.8
35°	3949.7	3949.7	3949.7	3949.7	3949.7
37.5°	2900.0	2900.0	2900.0	2900.0	2900.0
40°	2206.9	2206.9	2206.9	2206.9	2206.9
42.5°	1769.6	1769.6	1769.6	1769.6	1769.6
45°	1478.9	1478.9	1478.9	1478.9	1478.9
47.5°	1269.3	1269.3	1269.3	1269.3	1269.3
50°	1119.7	1119.7	1119.7	1119.7	1119.7
52.5°	1010.5	1010.5	1010.5	1010.5	1010.5
55°	922.7	922.7	922.7	922.7	922.7
57.5°	851.6	851.6	851.6	851.6	851.6
60°	785.8	785.8	785.8	785.8	785.8
62.5°	720.0	720.0	720.0	720.0	720.0
65°	650.7	650.7	650.7	650.7	650.7
67.5°	580.1	580.1	580.1	580.1	580.1
70°	508.7	508.7	508.7	508.7	508.7
72.5°	439.3	439.3	439.3	439.3	439.3
75°	369.2	369.2	369.2	369.2	369.2
77.5°	300.6	300.6	300.6	300.6	300.6
80°	228.8	228.8	228.8	228.8	228.8
82.5°	160.2	160.2	160.2	160.2	160.2
85°	94.7	94.7	94.7	94.7	94.7
87.5°	33.9	33.9	33.9	33.9	33.9
90°	25.9	41.6	70.9	45.5	25.9
92.5°	37.1	62.5	113.3	58.5	33.2
95°	43.0	72.2	158.2	78.1	48.9
97.5°	54.7	80.0	181.6	95.7	76.1
100°	72.2	93.7	283.2	117.2	101.6
102.5°	123.1	199.2	601.5	220.7	154.3
105°	212.9	419.9	1072.2	462.9	281.2
107.5°	369.1	751.9	1414.0	820.2	533.2
110°	689.4	998.0	1482.3	1126.8	853.5



TEST NUMBER: P1433465

CATALOG NUMBER: EHBR1-18-UNV-N-L935-UPL40

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	931.6	1072.2	1419.9	1244.0	1111.3
115°	980.4	1031.2	1267.5	1214.8	1207.0
117.5°	947.2	941.3	1076.1	1091.8	1165.9
120°	876.9	837.8	898.4	953.1	1052.7
122.5°	789.1	742.1	769.5	810.5	910.1
125°	706.9	660.1	677.7	687.5	771.5
127.5°	634.7	603.4	613.2	601.5	654.3
130°	585.9	558.6	572.3	544.9	570.3
132.5°	544.9	527.3	542.9	509.7	517.5
135°	515.6	499.9	517.5	486.3	484.3
137.5°	490.2	476.5	494.1	470.7	464.9
140°	466.8	455.1	474.6	457.0	453.1
142.5°	441.4	433.6	457.0	445.3	441.4
145°	423.8	417.9	443.3	437.5	435.5
147.5°	408.2	404.3	427.7	425.8	425.8
150°	394.5	390.6	414.0	412.1	414.0
152.5°	380.8	376.9	398.4	396.4	398.4
155°	371.1	367.2	384.7	384.7	384.7
157.5°	363.3	361.3	374.9	374.9	374.9
160°	357.4	355.5	367.2	367.2	365.3
162.5°	351.6	349.6	363.3	361.3	361.3
165°	347.7	347.7	357.4	357.4	355.5
167.5°	347.7	345.7	355.5	355.5	353.5
170°	345.7	345.7	353.5	351.6	349.6
172.5°	345.7	345.7	353.5	351.6	349.6
175°	343.8	343.8	349.6	349.6	349.6
177.5°	345.7	345.7	349.6	349.6	347.7
180°	347.7	347.7	347.7	347.7	347.7



TEST NUMBER: P1433465
 CATALOG NUMBER: EHBR1-18-UNV-N-L935-UPL40

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.80	14.74	14.43	15.37	16.08	13.80	14.74	14.43	15.37	16.08
	3H	15.57	16.41	16.22	17.05	17.80	15.57	16.41	16.22	17.05	17.80
	4H	16.22	17.01	16.90	17.66	18.43	16.22	17.01	16.90	17.66	18.43
	6H	16.68	17.41	17.36	18.07	18.84	16.68	17.41	17.36	18.07	18.84
	8H	16.80	17.49	17.50	18.17	18.95	16.80	17.49	17.50	18.17	18.95
	12H	16.85	17.51	17.55	18.18	18.98	16.85	17.51	17.55	18.18	18.98
4H	2H	14.33	15.12	15.00	15.77	16.54	14.33	15.12	15.00	15.77	16.54
	3H	16.29	16.95	16.98	17.64	18.42	16.29	16.95	16.98	17.64	18.42
	4H	17.06	17.66	17.76	18.35	19.16	17.06	17.66	17.76	18.35	19.16
	6H	17.63	18.14	18.35	18.86	19.69	17.63	18.14	18.35	18.86	19.69
	8H	17.79	18.26	18.51	18.98	19.81	17.79	18.26	18.51	18.98	19.81
	12H	17.87	18.28	18.61	19.03	19.86	17.87	18.28	18.61	19.03	19.86
8H	4H	17.29	17.76	18.01	18.48	19.31	17.29	17.76	18.01	18.48	19.31
	6H	17.97	18.36	18.72	19.12	19.95	17.97	18.36	18.72	19.12	19.95
	8H	18.20	18.54	18.96	19.30	20.15	18.20	18.54	18.96	19.30	20.15
	12H	18.33	18.63	19.09	19.37	20.29	18.33	18.63	19.09	19.37	20.29
12H	4H	17.28	17.70	18.02	18.44	19.28	17.28	17.70	18.02	18.44	19.28
	6H	18.00	18.34	18.77	19.10	19.95	18.00	18.34	18.77	19.10	19.95
	8H	18.26	18.55	19.02	19.30	20.22	18.26	18.55	19.02	19.30	20.22

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-6

Test Date: 08/01/2025

Luminaire Tested: EHBR-60-L935-N

Data in this report applies to families of products including EHBR-60-L935-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-6
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L935-N**
 Description: Elevate Round Highbay at, 60000 lumens, 3500K 90CRI LEDs with N lens

Spectral Parameters

CCT (K): 3406
 CIE u': 0.2394
 CIE v': 0.5094
 Duv: -0.0028
 CIE x: 0.4076
 CIE y: 0.3856
 CIE z: 0.2068
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 582
 Purity: 38.0517
 Rf: 91.3
 Rg: 100

CRI (Ra):	94.6		
R1:	96.6	R9:	63.8
R2:	98.4	R10:	94.7
R3:	98.1	R11:	96.6
R4:	95.8	R12:	80.9
R5:	96.2	R13:	97.4
R6:	95.4	R14:	98.3
R7:	91.8	R15:	93.1
R8:	84.4		



Test Conditions

Stabilization Time: 35M
 Operation Time: 1H 35M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-6

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 3406K
 CIE x = 0.4076
 CIE y = 0.3856
 Duv = -0.0028

Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-6

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-6

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.62

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-6

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.3

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

Summary

$R_f = 91.3$
 $R_g = 100$
 $CIE R_a = 94.6$
 $R_9 = 63.8$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 94	CES51 = 97	CES76 = 90
CES02 = 63	CES27 = 92	CES52 = 98	CES77 = 86
CES03 = 31	CES28 = 97	CES53 = 98	CES78 = 86
CES04 = 70	CES29 = 97	CES54 = 93	CES79 = 90
CES05 = 50	CES30 = 92	CES55 = 92	CES80 = 91
CES06 = 51	CES31 = 97	CES56 = 96	CES81 = 74
CES07 = 43	CES32 = 89	CES57 = 94	CES82 = 96
CES08 = 41	CES33 = 99	CES58 = 95	CES83 = 94
CES09 = 29	CES34 = 94	CES59 = 98	CES84 = 95
CES10 = 75	CES35 = 97	CES60 = 92	CES85 = 79
CES11 = 58	CES36 = 81	CES61 = 93	CES86 = 79
CES12 = 64	CES37 = 96	CES62 = 86	CES87 = 92
CES13 = 44	CES38 = 87	CES63 = 94	CES88 = 98
CES14 = 74	CES39 = 99	CES64 = 91	CES89 = 84
CES15 = 72	CES40 = 97	CES65 = 90	CES90 = 96
CES16 = 48	CES41 = 96	CES66 = 89	CES91 = 75
CES17 = 49	CES42 = 94	CES67 = 88	CES92 = 76
CES18 = 56	CES43 = 93	CES68 = 89	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 90	CES94 = 74
CES20 = 67	CES45 = 97	CES70 = 88	CES95 = 83
CES21 = 86	CES46 = 97	CES71 = 83	CES96 = 92
CES22 = 78	CES47 = 91	CES72 = 94	CES97 = 96
CES23 = 91	CES48 = 91	CES73 = 83	CES98 = 95
CES24 = 90	CES49 = 96	CES74 = 90	CES99 = 92
CES25 = 71	CES50 = 98	CES75 = 85	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)