

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1444707

Luminaire Tested: EHBR1-60-UNV-TA-L930-UPL15

Issue Date: 5/1/2026

Test Information

Test Method: LM-79-2019
Report Number: P1444707
REPORT IS A COMBINATION OF REPORTS P1444317 AND P1431635
Test Lab: INNOVATION CENTER
Issue Date: 5/1/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-60-UNV-TA-L930-UPL15
Description: Elevate Round Highbay at, 60000 lumens, 3000K 90CRI LEDs with TA lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 54154.5 lumens
Efficiency: N/A
Efficacy: 159.4 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 0.77 / 0.88
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')
CIE Type: Direct

Input Watts (W): 339.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1444707
CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	118	118	118	118	115	115	115	115	109	109	109	104	104	104	99	99	99	99	99	99	97
1	111	108	105	102	108	105	103	100	101	98	96	96	95	93	92	91	90	92	91	90	88
2	104	99	94	90	102	97	92	88	93	89	86	89	86	84	86	84	81	86	84	81	79
3	98	91	85	80	96	89	84	79	86	81	77	83	79	76	80	77	74	80	77	74	72
4	92	84	77	72	90	82	76	72	80	74	70	77	73	69	75	71	68	75	71	68	66
5	87	78	71	66	85	76	70	65	74	69	65	72	67	64	70	66	63	70	66	63	61
6	82	72	65	60	80	71	65	60	69	64	59	67	63	59	66	62	58	66	62	58	56
7	78	67	61	56	76	66	60	56	65	59	55	63	58	55	62	57	54	62	57	54	52
8	74	63	56	52	72	62	56	52	61	55	51	60	54	51	58	54	50	58	54	50	49
9	70	59	53	48	68	59	52	48	57	52	48	56	51	47	55	50	47	55	50	47	46
10	66	56	49	45	65	55	49	45	54	49	45	53	48	44	52	47	44	52	47	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	214284	214284	214284	214284
5°	215321	221599	212307	224502
10°	217118	232663	211912	231123
15°	218183	210907	211541	202415
20°	215928	157118	208861	145372
25°	204384	99368	197629	90160
30°	178545	59713	171629	54572
35°	137409	37470	129505	33192
40°	86923	23504	79528	22087
45°	44802	18311	44060	18010
50°	26268	16287	25461	16033
55°	20124	15409	19379	15271
60°	17027	15741	16302	15537
65°	15993	16438	15381	15878
70°	15625	17212	14847	16565
75°	16706	18254	15804	17448
80°	17289	20214	15675	18452
85°	16279	19503	13157	16701

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 25°
 Vertical Angle: 45°
 Luminance: 68564 cd/sqm



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	4497.0	8.3
10°-20°	12650.4	23.4
20°-30°	14407.8	26.6
30°-40°	10355.7	19.1
40°-50°	4776.0	8.8
50°-60°	2285.5	4.2
60°-70°	1667.6	3.1
70°-80°	1266.9	2.3
80°-90°	578.6	1.1
90°-100°	53.6	0.1
100°-110°	244.6	0.5
110°-120°	450.7	0.8
120°-130°	292.2	0.5
130°-140°	209.4	0.4
140°-150°	172.5	0.3
150°-160°	131.3	0.2
160°-170°	84.6	0.2
170°-180°	30.1	0.1
0°-30°	31555.2	58.3
0°-40°	41910.8	77.4
0°-60°	48972.4	90.4
0°-90°	52485.6	96.9
90°-120°	748.9	1.4
90°-150°	1423.0	2.6
90°-180°	1669.0	3.1
0°-180°	54154.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	45630	45630	45630	45630	45630	
5°	45974	47315	45331	47935	45974	4393
15°	45774	44247	44380	42466	45774	12897
25°	40815	19844	39466	18005	40815	18503
35°	25220	6877	23769	6092	25220	15478
45°	7249	2963	7129	2914	7249	6165
55°	2720	2082	2619	2064	2720	2510
65°	1669	1716	1605	1657	1669	1667
75°	1177	1286	1113	1229	1177	1224
85°	560	670	452	574	560	526
90°	136	177	28	38	136	87
95°	24	26	24	26	24	23
105°	94	116	67	117	94	123
115°	400	470	419	471	400	371
125°	325	316	364	318	325	295
135°	287	233	306	238	287	223
145°	282	254	297	262	282	178
155°	283	274	298	280	283	132
165°	299	292	308	296	299	85
175°	316	317	320	318	316	30
180°	320	320	320	320	320	



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2
2.5°	45804.5	45800.8	45800.1	45796.9	45796.0	45796.0	45794.5	45790.8	45788.4	45783.2	45777.3
5°	45974.4	45972.4	45973.6	45974.0	45970.8	45963.6	45952.5	45938.8	45921.6	45905.3	45890.7
7.5°	46105.9	46109.1	46113.2	46112.3	46102.3	46085.5	46062.7	46049.9	46057.5	46082.3	46139.2
10°	46129.8	46149.5	46157.1	46154.7	46134.8	46120.4	46126.0	46174.4	46270.5	46398.9	46574.5
12.5°	46036.3	46060.4	46059.5	46051.6	46032.3	46051.9	46121.9	46265.8	46472.1	46725.3	47022.3
15°	45773.7	45804.8	45796.0	45785.8	45772.8	45837.3	45977.2	46227.1	46545.7	46902.7	47268.2
17.5°	45263.8	45301.4	45283.2	45271.5	45260.6	45381.4	45621.7	45987.7	46389.0	46792.7	47139.1
20°	44379.4	44404.6	44361.2	44340.7	44357.9	44594.5	44948.4	45415.8	45838.9	46220.7	46457.4
22.5°	42936.1	42967.3	42885.6	42876.2	42977.0	43340.4	43788.2	44310.7	44708.2	45010.8	45102.0
25°	40815.4	40846.2	40749.1	40807.1	40978.6	41473.5	42007.0	42565.9	42904.9	43129.2	43067.2
27.5°	37953.0	37981.1	37889.1	38007.4	38278.5	38929.0	39556.7	40162.9	40465.1	40622.2	40423.2
30°	34343.0	34401.4	34292.6	34457.9	34871.6	35716.1	36435.2	37115.1	37416.4	37536.0	37226.2
32.5°	30055.4	30138.4	30018.5	30264.4	30841.7	31856.1	32673.1	33432.7	33766.0	33902.5	33552.6
35°	25219.5	25338.6	25201.1	25570.1	26282.2	27411.7	28316.4	29164.5	29559.2	29752.6	29400.1
37.5°	20096.1	20209.6	20135.2	20627.5	21409.4	22580.2	23503.7	24418.6	24864.4	25154.7	24876.7
40°	15066.0	15170.0	15226.2	15789.2	16524.7	17628.1	18515.1	19420.3	19919.0	20283.5	20112.0
42.5°	10633.7	10738.4	10929.8	11473.0	12086.3	12999.7	13759.5	14572.3	15048.7	15437.5	15371.3
45°	7248.8	7370.3	7610.2	8054.9	8498.5	9153.8	9711.7	10343.8	10733.0	11089.1	11093.3
47.5°	5079.6	5165.0	5379.3	5683.0	5972.1	6792.5	6826.1	7136.8	7398.4	7664.6	7699.1
50°	3914.8	3966.2	4079.8	4249.0	4412.9	4625.8	4820.9	5045.9	5206.9	5352.9	5387.7
52.5°	3217.6	3250.3	3308.2	3399.8	3494.9	3610.7	3715.0	3838.7	3926.3	4004.3	4020.8
55°	2719.5	2746.5	2832.6	2850.0	2958.8	2979.7	3026.0	3101.3	3152.2	3199.1	3210.8
57.5°	2343.5	2363.1	2381.4	2420.5	2453.9	2502.7	2541.9	2595.9	2628.0	2661.8	2664.7
60°	2046.9	2061.1	2074.1	2101.2	2124.0	2157.9	2184.9	2221.6	2244.6	2270.0	2272.9
62.5°	1826.2	1836.4	1845.0	1862.9	1879.1	1905.2	1926.6	1957.3	1978.8	1998.4	2002.7
65°	1669.3	1676.8	1682.3	1695.8	1710.0	1732.2	1751.6	1776.7	1792.4	1807.5	1810.7
67.5°	1530.3	1537.4	1543.1	1555.5	1565.3	1581.9	1594.9	1613.7	1625.5	1637.5	1637.8
70°	1371.0	1377.6	1382.0	1393.5	1401.4	1415.7	1426.1	1443.0	1455.2	1468.6	1472.0
72.5°	1260.7	1264.6	1270.5	1281.0	1292.0	1307.2	1321.3	1338.8	1353.6	1367.5	1373.3
75°	1176.8	1181.4	1185.3	1194.2	1201.9	1214.7	1225.2	1241.3	1254.1	1269.0	1276.3
77.5°	1055.7	1061.0	1064.4	1073.4	1080.0	1092.3	1100.0	1114.5	1124.9	1138.4	1145.0
80°	909.5	914.4	916.7	925.2	930.4	941.8	949.4	963.2	972.1	985.6	993.5
82.5°	747.3	752.0	753.4	761.3	764.2	773.5	779.1	793.3	804.2	821.7	833.9
85°	559.5	561.2	564.0	562.0	573.3	574.0	586.8	589.2	606.1	610.5	629.8
87.5°	342.1	347.2	349.7	357.5	360.9	368.7	371.1	379.4	383.9	393.3	397.7
90°	136.2	143.4	145.5	154.1	155.9	163.5	164.9	173.5	175.6	184.5	187.1
92.5°	21.6	22.6	23.5	25.1	26.2	28.3	29.9	31.3	32.5	34.4	36.7
95°	24.0	25.2	26.5	27.6	28.9	30.1	31.4	32.5	33.8	35.0	38.4
97.5°	29.4	30.5	31.5	32.6	33.7	34.8	35.8	36.9	38.0	38.9	43.1
100°	37.2	38.1	39.0	39.9	40.8	41.8	42.7	43.6	44.5	45.4	53.1
102.5°	58.3	61.5	64.7	67.8	71.0	74.1	77.4	80.4	83.6	86.8	103.3
105°	94.4	102.8	111.7	120.2	128.9	137.6	146.2	154.5	163.3	171.7	199.1
107.5°	155.9	171.8	187.9	203.9	219.9	235.8	251.8	267.7	283.6	299.2	327.0
110°	280.5	293.1	306.0	318.8	331.5	344.5	357.3	369.6	382.6	395.2	415.4



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	376.2	381.8	387.5	393.2	398.9	404.4	410.1	415.6	421.3	426.7	440.9
115°	399.8	401.5	403.5	405.1	407.1	408.7	410.5	412.0	413.8	415.3	424.8
117.5°	393.3	392.5	391.9	391.4	390.4	389.7	388.9	388.0	387.1	386.1	391.2
120°	373.5	371.2	369.2	366.7	364.7	362.1	359.9	357.5	354.9	352.4	354.3
122.5°	347.6	345.0	342.6	339.7	337.0	334.1	331.4	328.1	325.5	322.5	322.7
125°	324.6	321.8	319.6	316.5	313.6	310.6	307.6	304.5	301.5	298.2	297.9
127.5°	305.7	303.6	301.7	299.2	296.8	294.4	291.8	289.2	286.9	283.9	283.4
130°	295.9	294.1	292.1	289.7	287.6	285.2	282.7	279.9	277.6	274.7	273.9
132.5°	289.2	287.8	286.2	284.3	282.4	280.0	278.0	275.5	273.3	271.1	270.2
135°	286.9	285.3	283.9	282.1	280.3	277.9	275.7	273.4	271.2	268.8	268.1
137.5°	285.7	284.4	282.8	281.0	279.2	276.8	274.8	272.4	270.3	267.9	267.1
140°	284.8	283.5	282.0	280.1	278.5	276.4	274.3	272.1	269.9	267.5	267.0
142.5°	282.7	281.2	280.2	278.5	276.9	274.9	273.0	270.8	269.0	266.8	266.5
145°	282.5	281.3	280.3	278.9	277.2	275.3	273.7	271.6	270.0	268.1	267.6
147.5°	282.5	281.5	280.6	279.3	278.0	276.3	274.7	272.9	271.4	269.7	269.5
150°	282.6	281.7	280.9	279.7	278.3	276.9	275.4	273.8	272.2	270.5	270.4
152.5°	281.8	280.8	280.1	278.9	277.7	276.1	275.1	273.4	272.1	270.5	270.2
155°	283.4	282.4	281.3	280.4	279.1	277.9	276.5	275.2	273.9	272.4	272.2
157.5°	286.1	285.0	284.3	283.0	282.2	281.1	279.9	278.7	277.6	276.4	276.0
160°	290.2	289.3	288.4	287.3	286.1	284.9	283.9	282.7	282.0	280.6	280.4
162.5°	294.6	293.5	292.6	291.5	290.5	289.4	288.4	287.5	286.5	285.3	285.0
165°	299.3	298.7	297.8	297.0	296.1	295.3	294.4	293.5	292.6	291.6	291.3
167.5°	305.6	304.7	304.1	303.2	302.2	301.6	300.6	299.7	299.1	298.0	297.7
170°	309.9	309.1	308.6	308.1	307.4	306.7	306.3	305.6	304.9	304.2	304.1
172.5°	313.7	313.1	312.7	312.3	311.6	311.4	310.8	310.3	309.9	309.3	309.5
175°	315.8	315.4	315.2	314.8	314.5	314.1	313.9	313.7	313.7	313.1	313.1
177.5°	318.4	318.2	318.2	318.0	318.0	318.0	317.8	317.4	317.2	317.2	317.2
180°	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2
2.5°	45772.8	45767.3	45759.6	45750.0	45741.7	45732.1	45709.3	45702.5	45710.1	45715.2	45725.7
5°	45881.6	45884.8	45886.0	45906.8	45924.8	45969.5	46320.6	46460.2	46568.0	46636.5	46740.5
7.5°	46209.5	46315.0	46419.4	46559.7	46680.8	46844.3	47458.6	47720.0	47905.9	48039.4	48203.9
10°	46765.2	46995.6	47211.5	47464.5	47681.9	47931.1	48502.8	48757.5	48918.4	49035.4	49144.6
12.5°	47324.9	47644.4	47933.1	48214.6	48450.1	48666.0	48867.1	48956.2	48963.8	48967.6	48909.6
15°	47616.5	47921.9	48176.2	48362.5	48500.8	48562.0	48215.8	48034.2	47804.7	47615.7	47304.7
17.5°	47432.5	47615.7	47725.6	47714.8	47657.6	47466.2	46485.7	45946.3	45410.9	44928.5	44295.9
20°	46614.5	46600.5	46505.0	46234.2	45908.0	45400.7	43719.7	42749.8	41812.2	40988.6	39989.4
22.5°	45092.7	44853.3	44519.4	43935.7	43287.1	42400.8	39991.8	38565.2	37259.9	36106.6	34814.8
25°	42887.7	42395.1	41779.3	40852.6	39844.7	38552.0	35582.9	33808.5	32241.2	30881.8	29391.3
27.5°	40065.7	39323.7	38421.3	37138.6	35773.2	34117.1	30825.3	28867.0	27184.6	25727.2	24140.7
30°	36724.7	35759.6	34594.5	33002.5	31355.5	29477.2	26138.6	24155.1	22452.2	20952.8	19365.2
32.5°	32949.2	31818.8	30453.4	28666.6	26885.6	24954.3	21730.1	19810.1	18183.3	16740.9	15304.0
35°	28785.0	27572.8	26128.3	24305.8	22535.4	20657.8	17699.3	15968.1	14531.5	13256.6	12096.3
37.5°	24318.1	23127.9	21754.9	20037.3	18395.5	16694.1	14141.4	12690.7	11485.2	10427.0	9531.1
40°	19673.9	18632.3	17444.3	15959.3	14558.3	13141.3	11045.8	9894.3	8942.9	8135.9	7464.5
42.5°	15086.4	14279.2	13368.2	12194.7	11122.6	10043.7	8430.9	7577.7	6873.0	6292.1	5817.4
45°	10945.7	10405.7	9794.7	8978.9	8237.1	7484.5	6336.6	5737.1	5278.1	4903.5	4586.8
47.5°	7651.6	7338.4	7319.3	6565.4	6021.3	5561.2	4821.7	4443.0	4161.8	3934.8	3734.3
50°	5373.5	5222.0	5033.8	4764.7	4512.2	4252.2	3801.6	3572.7	3407.9	3270.4	3143.6
52.5°	4017.1	3938.4	3838.1	3695.4	3558.6	3412.4	3127.2	2981.4	2929.7	2801.7	2701.2
55°	3208.5	3163.4	3106.4	3022.5	2939.3	2906.0	2661.7	2553.4	2484.9	2434.3	2380.4
57.5°	2665.2	2631.5	2597.7	2540.9	2492.7	2434.3	2304.7	2249.1	2208.4	2178.7	2141.3
60°	2273.4	2253.2	2234.3	2200.9	2174.9	2143.5	2061.1	2029.8	2008.5	1990.6	1966.7
62.5°	2006.5	1996.2	1986.3	1968.6	1955.4	1938.3	1882.0	1867.0	1856.3	1847.3	1832.8
65°	1813.9	1806.4	1801.0	1789.2	1782.6	1772.7	1724.3	1714.1	1707.5	1704.3	1695.8
67.5°	1638.9	1631.1	1627.5	1619.1	1616.3	1610.1	1570.5	1564.9	1562.8	1563.8	1560.7
70°	1475.2	1472.0	1473.6	1472.3	1476.0	1477.2	1453.2	1453.0	1455.5	1460.6	1461.1
72.5°	1377.1	1377.1	1378.9	1379.8	1383.3	1385.0	1365.0	1364.1	1365.2	1369.0	1369.1
75°	1283.7	1285.2	1290.3	1292.0	1296.3	1297.1	1270.7	1267.6	1267.8	1271.4	1270.2
77.5°	1154.6	1160.1	1169.7	1174.8	1182.9	1184.4	1154.8	1151.3	1151.4	1155.0	1152.0
80°	1007.9	1018.6	1033.9	1044.6	1057.1	1062.1	1031.8	1024.5	1017.7	1016.7	1010.6
82.5°	852.1	865.2	883.6	893.3	906.6	909.7	858.7	849.1	843.4	843.8	838.3
85°	650.5	660.3	677.1	682.5	690.8	690.1	632.0	607.1	613.7	603.4	611.5
87.5°	408.1	413.8	424.3	425.6	429.5	428.7	370.2	358.7	355.3	355.5	351.3
90°	196.1	199.4	208.1	207.8	213.5	212.1	164.3	158.4	154.7	157.4	151.9
92.5°	39.6	41.6	44.3	46.6	49.2	51.6	48.7	49.5	47.7	45.1	43.4
95°	42.1	45.6	49.3	52.8	56.5	60.1	63.7	67.3	63.9	60.4	57.0
97.5°	47.4	51.6	55.7	60.0	64.3	68.4	72.7	77.0	73.4	69.4	65.9
100°	61.0	69.0	76.7	84.7	92.5	100.4	108.4	116.3	109.3	102.0	95.1
102.5°	119.9	136.9	153.5	170.2	187.0	203.9	220.8	237.7	221.6	205.3	189.2
105°	226.3	253.4	280.5	307.4	334.6	361.7	389.4	416.6	390.9	365.2	339.4
107.5°	354.5	382.0	409.3	436.7	464.3	491.7	520.0	547.5	522.4	497.0	471.9
110°	435.3	455.0	475.0	494.8	514.6	534.5	555.5	575.5	560.3	544.9	529.6



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	454.8	469.0	483.2	497.0	510.9	525.0	540.6	554.9	546.9	538.7	530.9
115°	433.9	443.5	452.5	461.8	471.0	480.1	491.2	500.9	497.9	494.8	491.9
117.5°	396.1	400.9	405.9	410.6	415.4	420.2	427.6	432.6	432.2	432.1	431.8
120°	355.9	357.5	359.1	360.8	362.2	363.7	368.1	370.3	371.6	372.7	373.9
122.5°	322.8	322.9	322.9	322.9	322.9	322.9	326.2	327.1	327.5	327.9	328.6
125°	297.5	297.0	296.6	296.1	295.3	294.9	298.4	298.4	297.6	296.7	295.9
127.5°	282.3	281.6	280.7	279.9	278.7	277.9	281.0	280.9	279.0	277.2	275.2
130°	273.2	272.4	271.5	270.6	269.9	269.1	272.6	272.9	270.3	267.4	264.9
132.5°	269.4	268.7	267.6	267.2	266.3	265.4	269.3	269.6	267.0	264.0	261.1
135°	267.1	266.5	265.7	264.9	264.1	263.8	268.0	268.4	265.8	262.9	260.2
137.5°	266.1	265.5	264.7	264.2	263.4	262.9	267.8	268.3	266.2	263.5	261.4
140°	266.3	265.6	265.0	264.7	264.0	263.9	269.0	269.8	268.1	265.9	263.9
142.5°	265.7	265.6	265.2	265.1	264.8	264.8	270.8	272.0	270.5	268.6	267.2
145°	267.2	267.3	266.9	266.9	266.8	267.0	273.8	275.5	274.3	273.0	271.6
147.5°	268.8	268.7	268.5	268.5	268.4	268.9	276.3	277.9	277.2	276.1	275.2
150°	270.0	270.0	269.7	269.9	270.2	270.5	279.1	281.2	280.5	279.7	278.8
152.5°	269.9	269.7	269.7	269.8	269.8	270.2	280.9	283.5	282.9	282.0	281.4
155°	271.8	271.6	271.3	271.4	271.2	271.7	283.6	286.3	285.8	285.3	284.6
157.5°	275.5	275.1	274.7	274.6	274.5	274.4	287.2	290.4	289.7	289.3	288.7
160°	279.7	279.5	278.9	278.7	278.3	278.2	291.5	294.6	294.3	293.5	293.0
162.5°	284.5	284.6	284.1	283.9	283.6	283.6	296.9	300.3	299.6	299.0	298.4
165°	290.9	290.4	290.1	289.9	289.5	289.4	302.0	304.9	304.6	304.0	303.4
167.5°	297.3	297.2	296.7	296.7	296.3	296.4	308.1	310.9	310.6	309.9	309.6
170°	303.7	303.7	303.3	303.3	303.3	303.5	313.2	315.6	315.4	314.6	314.1
172.5°	309.2	309.4	309.4	309.4	309.4	309.6	317.8	320.0	319.7	319.3	318.8
175°	313.1	313.1	313.1	313.4	313.5	313.5	320.0	321.6	321.4	321.2	320.8
177.5°	317.4	317.4	317.6	317.7	317.9	318.0	322.0	322.9	322.8	322.8	322.7
180°	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2
2.5°	45728.1	45744.1	45746.5	45765.3	45763.7	45786.0	45782.5	45800.8	45790.1	45805.2	45792.5
5°	46802.1	46899.5	46950.4	47045.5	47075.5	47160.6	47184.6	47262.2	47265.4	47327.0	47313.0
7.5°	48320.5	48464.1	48549.4	48666.9	48726.4	48824.3	48867.4	48939.9	48963.1	49020.7	49025.0
10°	49227.3	49296.9	49345.7	49378.5	49408.4	49422.5	49438.9	49434.4	49438.9	49432.4	49446.5
12.5°	48870.6	48768.8	48701.6	48574.0	48500.2	48359.3	48290.1	48154.7	48105.4	47989.1	47972.3
15°	47064.4	46709.6	46458.9	46094.4	45865.2	45506.6	45296.7	44973.1	44825.4	44568.1	44500.6
17.5°	43772.1	43113.6	42603.9	41950.1	41496.4	40885.4	40501.2	39995.4	39718.3	39310.5	39169.2
20°	39156.6	38182.2	37417.6	36506.9	35855.2	35043.2	34523.3	33867.7	33487.0	32986.1	32783.0
22.5°	33737.7	32524.5	31569.8	30493.9	29707.6	28802.6	28179.8	27470.3	27056.2	26512.0	26271.1
25°	28152.5	26814.7	25753.2	24619.7	23788.8	22881.7	22258.7	21561.8	21133.3	20616.6	20377.1
27.5°	22810.8	21456.6	20430.8	19376.8	18614.7	17796.2	17234.1	16625.6	16245.3	15804.3	15579.0
30°	18096.9	16902.4	16029.5	15154.9	14520.8	13856.1	13389.0	12884.7	12551.1	12173.4	11958.8
32.5°	14256.4	13334.2	12650.7	11956.7	11437.8	10882.2	10478.6	10033.7	9732.5	9395.3	9201.0
35°	11290.8	10574.3	10029.1	9457.8	9012.1	8538.9	8183.2	7799.3	7529.0	7238.6	7070.8
37.5°	8920.9	8351.2	7902.5	7428.0	7061.9	6669.9	6337.8	6097.1	5817.1	5585.4	5424.9
40°	7001.1	6548.2	6176.9	5814.1	5515.3	5218.1	4979.5	4744.1	4563.3	4397.6	4282.9
42.5°	5467.3	5139.1	4868.0	4602.2	4384.4	4167.8	3994.9	3832.7	3711.0	3602.6	3528.6
45°	4346.4	4120.5	3932.2	3744.9	3591.2	3446.7	3330.3	3226.8	3148.1	3083.1	3036.9
47.5°	3570.6	3416.0	3283.1	3156.8	3052.4	2957.8	2879.8	2854.4	2769.8	2712.9	2691.2
50°	3034.5	2941.2	2840.2	2747.0	2677.3	2608.0	2557.5	2507.9	2476.3	2450.1	2442.2
52.5°	2634.4	2563.0	2506.9	2447.9	2401.9	2352.5	2317.7	2284.7	2267.2	2253.6	2251.9
55°	2336.9	2287.0	2249.9	2210.3	2182.8	2153.8	2135.7	2118.2	2110.7	2103.7	2104.2
57.5°	2111.8	2078.6	2054.3	2028.7	2013.8	1999.9	1995.3	1991.0	1993.3	1994.3	1998.2
60°	1947.9	1926.2	1911.0	1896.3	1890.0	1885.6	1888.9	1892.9	1900.8	1907.2	1913.0
62.5°	1822.2	1809.8	1802.4	1794.4	1793.8	1794.1	1800.9	1807.5	1817.4	1824.9	1830.5
65°	1692.8	1685.7	1683.4	1678.3	1680.8	1682.3	1690.4	1695.5	1705.5	1711.4	1718.5
67.5°	1562.1	1560.4	1561.9	1561.9	1566.4	1570.4	1578.1	1583.9	1592.4	1597.7	1603.5
70°	1465.5	1466.2	1469.8	1470.4	1475.3	1478.0	1484.8	1488.5	1496.1	1500.7	1507.6
72.5°	1371.6	1370.1	1371.0	1368.8	1370.5	1369.8	1373.5	1375.4	1381.8	1385.4	1393.8
75°	1271.7	1267.5	1266.5	1261.9	1262.0	1258.8	1260.3	1260.2	1264.4	1266.1	1272.2
77.5°	1151.0	1143.9	1140.5	1132.9	1132.7	1129.8	1132.9	1134.8	1142.2	1145.7	1152.7
80°	1006.5	995.4	990.3	981.5	983.0	982.6	990.0	995.6	1004.7	1006.4	1015.2
82.5°	836.6	825.3	819.8	811.2	813.3	813.4	820.2	821.4	829.3	832.7	842.8
85°	599.0	603.4	591.4	592.3	589.7	594.4	599.0	604.7	611.3	622.4	630.7
87.5°	352.8	351.3	355.5	356.0	362.1	365.3	375.1	380.7	391.7	400.3	415.8
90°	152.5	147.2	150.9	149.3	155.5	154.1	159.7	157.2	164.0	164.9	173.5
92.5°	40.5	38.7	35.9	34.0	31.4	29.7	28.0	27.4	25.8	25.4	23.8
95°	53.6	50.3	47.0	43.6	40.3	36.9	35.6	34.4	33.2	32.0	30.7
97.5°	62.2	58.6	55.0	51.2	47.6	44.0	43.2	42.4	41.5	40.7	39.9
100°	88.0	81.0	74.1	66.9	60.0	53.0	52.4	51.7	51.1	50.4	49.7
102.5°	173.2	157.0	141.1	124.9	109.0	92.9	90.1	87.3	84.5	81.7	79.0
105°	313.6	287.8	262.2	236.4	210.9	185.3	177.7	169.7	162.1	154.4	146.9
107.5°	446.6	421.4	396.5	371.3	346.3	321.3	309.0	297.0	284.6	272.6	260.6
110°	514.0	498.8	483.8	468.3	453.2	438.2	426.3	414.9	403.1	391.6	380.1



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	522.9	515.1	507.0	499.3	491.6	483.7	478.0	472.2	466.6	460.8	454.9
115°	488.8	486.0	483.1	480.3	477.7	474.7	474.0	473.6	472.7	472.2	471.8
117.5°	431.5	431.4	431.0	431.0	431.0	430.9	433.5	435.9	438.7	441.6	444.6
120°	375.1	376.3	377.5	378.8	380.2	381.7	385.0	388.6	392.1	396.1	399.9
122.5°	328.9	329.4	329.7	330.5	331.1	331.7	334.9	338.4	341.8	345.4	349.1
125°	294.6	293.6	292.7	291.7	290.7	290.1	292.4	295.0	297.6	300.7	303.3
127.5°	273.2	271.0	268.9	267.1	264.9	263.2	264.1	265.3	266.3	267.7	269.0
130°	262.1	259.5	256.5	254.0	250.9	248.4	248.2	248.1	247.9	248.0	248.0
132.5°	258.0	255.1	252.0	248.9	245.9	242.9	241.8	240.7	239.5	238.9	238.1
135°	257.2	254.6	251.4	248.5	245.4	242.7	241.1	239.5	238.1	236.8	235.6
137.5°	258.9	256.4	253.9	251.5	248.7	246.3	244.2	242.7	240.9	239.8	238.2
140°	261.6	259.7	257.3	255.2	252.9	250.9	249.1	247.7	246.1	245.0	243.5
142.5°	265.1	263.4	261.5	259.9	258.1	256.4	254.7	253.4	251.8	250.7	249.3
145°	270.2	269.0	267.5	266.1	264.8	263.4	261.8	260.7	259.5	258.3	257.5
147.5°	274.1	273.0	272.0	270.8	269.6	268.5	267.3	266.6	265.3	264.6	263.6
150°	277.7	276.9	275.7	275.0	273.7	272.8	271.9	271.1	270.2	269.7	268.8
152.5°	280.3	279.6	278.7	277.9	276.8	275.9	275.1	274.5	273.8	273.1	272.2
155°	283.7	283.1	282.2	281.5	280.5	280.0	279.2	278.3	277.7	277.0	276.2
157.5°	288.0	287.4	286.5	286.1	285.0	284.4	283.6	282.9	282.1	281.6	280.8
160°	292.4	291.8	291.0	290.3	289.7	289.0	288.0	287.5	286.5	286.0	285.1
162.5°	297.6	296.9	296.3	295.6	294.6	294.1	293.2	292.5	291.8	291.1	290.3
165°	302.7	302.1	301.4	300.8	300.2	299.5	298.6	298.0	297.1	296.5	295.6
167.5°	308.9	308.4	307.7	307.2	306.4	305.7	305.0	304.3	303.5	302.8	301.9
170°	313.8	313.1	312.6	311.9	311.3	310.5	309.9	309.1	308.3	308.0	307.1
172.5°	318.3	318.1	317.5	317.1	316.4	315.9	315.5	314.9	314.3	313.7	313.3
175°	320.6	320.5	320.3	319.7	319.6	319.3	318.9	318.8	318.4	318.2	317.8
177.5°	322.7	322.5	322.5	322.1	322.0	322.0	321.7	321.6	321.3	321.1	321.0
180°	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2
2.5°	45805.7	45794.0	45799.6	45778.1	45783.2	45757.3	45754.9	45725.7	45722.8	45695.2	45685.0
5°	47356.6	47331.1	47359.8	47314.9	47323.8	47265.4	47260.5	47185.1	47159.1	47064.7	47024.0
7.5°	49061.0	49051.4	49069.0	49031.5	49030.3	48978.2	48956.7	48889.1	48847.2	48748.1	48684.8
10°	49434.4	49443.3	49428.9	49432.4	49412.2	49406.5	49385.8	49372.6	49338.5	49312.9	49275.0
12.5°	47883.9	47893.2	47834.0	47871.6	47842.0	47911.1	47905.5	47987.0	47999.5	48102.7	48141.7
15°	44300.2	44289.1	44175.6	44247.1	44208.8	44360.6	44394.6	44598.9	44708.2	44970.5	45131.6
17.5°	38886.6	38857.4	38697.6	38784.7	38740.4	38964.3	39039.4	39366.1	39569.9	39992.5	40293.7
20°	32433.5	32377.4	32190.4	32292.4	32246.7	32501.1	32608.3	33003.2	33266.0	33825.7	34223.9
22.5°	25900.0	25811.6	25628.4	25723.6	25680.5	25943.9	26083.5	26479.7	26780.7	27355.4	27820.2
25°	20033.0	19954.2	19777.1	19843.8	19827.8	20050.6	20174.8	20549.5	20845.3	21392.7	21836.4
27.5°	15279.7	15197.7	15037.7	15084.8	15068.6	15258.5	15375.5	15688.6	15943.1	16403.9	16793.5
30°	11694.3	11595.4	11459.8	11485.8	11474.7	11628.6	11737.8	12001.4	12219.6	12609.1	12944.8
32.5°	8963.7	8864.3	8739.7	8751.8	8735.4	8856.1	8946.1	9175.4	9365.5	9696.7	9988.9
35°	6858.5	6974.7	6708.5	6877.1	6701.5	6959.3	6866.6	7009.8	7173.3	7452.3	7696.1
37.5°	5272.5	5191.5	5123.1	5115.8	5115.4	5175.1	5245.7	5383.6	5527.7	5735.6	5950.3
40°	4178.2	4121.4	4077.1	4073.8	4077.1	4119.6	4171.6	4267.0	4372.6	4521.8	4679.6
42.5°	3465.5	3427.7	3400.9	3399.2	3407.5	3437.7	3473.8	3530.5	3599.2	3695.9	3804.2
45°	2999.3	2978.4	2963.5	2962.7	2966.5	2982.3	3003.1	3038.4	3081.9	3142.2	3210.8
47.5°	2672.3	2667.2	2657.9	2658.3	2654.0	2660.4	2662.8	2682.6	2705.8	2751.3	2840.7
50°	2434.1	2434.1	2427.7	2427.4	2421.3	2421.0	2415.9	2423.7	2434.5	2462.8	2491.4
52.5°	2245.9	2245.3	2238.4	2237.0	2230.6	2230.3	2225.8	2228.9	2230.4	2244.6	2261.7
55°	2098.8	2094.4	2085.3	2082.4	2079.9	2083.6	2081.9	2082.1	2080.3	2086.2	2091.2
57.5°	1993.3	1987.6	1979.0	1976.4	1975.7	1980.1	1980.3	1978.8	1970.8	1965.4	1957.8
60°	1909.8	1904.0	1894.7	1892.3	1893.7	1899.8	1899.5	1894.4	1882.5	1872.2	1860.3
62.5°	1827.7	1825.4	1820.7	1820.0	1818.8	1819.8	1815.6	1810.2	1798.5	1787.5	1774.4
65°	1717.7	1718.8	1715.3	1715.8	1711.6	1710.9	1704.5	1699.2	1687.4	1677.4	1664.0
67.5°	1603.3	1604.2	1601.3	1601.3	1599.1	1599.4	1595.6	1590.7	1580.7	1572.6	1562.3
70°	1509.1	1511.6	1509.9	1510.3	1507.6	1506.6	1500.5	1495.8	1485.4	1478.7	1469.4
72.5°	1396.3	1401.4	1401.2	1402.5	1398.4	1396.3	1389.1	1383.1	1373.9	1368.4	1361.0
75°	1274.6	1281.2	1283.1	1285.9	1280.2	1277.1	1269.2	1264.4	1256.9	1253.7	1248.8
77.5°	1155.7	1162.9	1169.9	1176.3	1167.0	1158.7	1148.8	1141.2	1130.3	1126.1	1118.5
80°	1022.3	1035.1	1050.5	1063.4	1046.6	1029.7	1013.3	1001.1	986.8	980.9	971.3
82.5°	848.1	861.3	870.1	878.4	866.7	854.3	838.5	827.8	812.3	806.5	795.5
85°	644.3	660.7	665.9	670.3	662.9	656.3	641.4	621.3	611.5	596.1	588.2
87.5°	423.8	433.6	435.5	437.0	432.4	429.2	419.5	410.1	393.3	381.1	366.3
90°	172.7	178.8	174.6	176.6	171.3	172.3	163.1	160.4	147.2	142.5	130.7
92.5°	23.1	21.5	20.6	19.3	21.2	21.7	23.3	23.8	25.2	25.8	27.4
95°	29.5	28.3	27.1	25.8	26.8	27.8	28.8	29.8	30.7	31.7	32.7
97.5°	39.1	38.2	37.4	36.6	37.2	37.8	38.3	38.9	39.5	40.1	40.8
100°	49.1	48.5	47.8	47.1	47.1	47.1	47.1	47.1	47.1	47.1	47.1
102.5°	76.2	73.3	70.6	67.8	69.7	71.6	73.4	75.3	77.3	79.1	81.2
105°	139.2	131.6	124.0	116.4	123.8	131.1	138.5	145.9	153.2	160.9	168.3
107.5°	248.4	236.3	224.3	212.3	225.9	239.3	252.7	266.1	279.6	292.9	306.7
110°	368.7	357.2	345.8	334.3	348.5	362.8	377.0	391.3	405.6	419.8	434.4



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	449.3	443.8	438.2	432.6	441.8	451.0	460.2	469.7	478.8	488.2	497.3
115°	471.2	470.9	470.6	470.3	474.6	479.0	483.3	487.8	492.4	496.7	501.3
117.5°	447.4	450.3	453.4	456.5	458.0	459.3	460.9	462.2	464.0	465.4	467.2
120°	404.0	407.6	411.8	416.0	415.4	414.8	414.4	413.8	413.8	413.4	413.6
122.5°	353.0	356.9	361.1	365.1	363.9	362.6	361.6	360.6	359.8	358.9	358.2
125°	306.6	309.6	313.1	316.4	315.1	313.9	312.9	312.1	311.2	310.3	309.9
127.5°	270.9	272.8	274.5	276.5	276.0	275.4	275.4	274.9	274.8	274.9	275.2
130°	248.4	249.0	249.9	250.5	250.7	250.9	251.4	251.9	252.8	253.4	254.6
132.5°	238.0	237.5	237.4	237.3	237.9	238.6	239.7	240.8	242.3	243.5	245.4
135°	234.9	234.1	233.5	233.1	234.1	234.9	236.2	237.5	239.4	241.1	243.2
137.5°	237.2	236.2	235.6	234.6	235.6	236.6	237.9	239.3	241.0	242.8	245.0
140°	242.6	241.6	241.1	240.3	241.2	242.0	243.4	244.7	246.3	248.2	250.1
142.5°	248.5	247.3	246.8	246.3	246.8	247.7	249.2	250.2	251.8	253.3	255.1
145°	256.5	255.6	255.1	254.5	255.0	255.7	256.5	257.5	258.7	259.7	261.3
147.5°	262.9	262.3	261.9	261.4	261.9	262.2	262.9	263.3	264.4	265.2	266.4
150°	268.5	267.7	267.3	267.1	267.3	267.3	267.9	268.1	268.7	269.2	270.2
152.5°	271.9	271.2	271.1	270.6	270.6	270.7	271.1	271.4	271.7	272.1	273.0
155°	275.8	275.3	274.8	274.3	274.1	273.9	274.1	273.9	274.2	274.2	274.6
157.5°	280.4	279.7	279.5	278.7	278.5	278.0	278.0	277.8	277.8	277.3	277.4
160°	284.6	283.7	283.1	282.5	282.4	281.9	281.8	281.3	281.3	281.2	281.1
162.5°	289.8	289.2	288.6	287.9	287.6	286.9	286.6	285.9	285.6	285.3	285.1
165°	294.8	294.0	293.5	292.5	292.2	291.8	291.4	291.0	290.7	290.3	290.2
167.5°	301.5	300.6	300.0	299.2	298.8	298.0	297.7	297.2	296.8	296.4	296.3
170°	306.6	305.9	305.5	304.9	304.6	304.1	303.9	303.3	303.2	303.0	303.0
172.5°	313.0	312.3	311.9	311.5	311.2	310.8	310.7	310.5	310.1	310.1	309.9
175°	317.6	317.2	317.1	316.7	316.4	316.4	316.1	316.0	315.9	315.6	315.6
177.5°	320.6	320.4	320.3	320.2	320.0	320.0	320.0	320.0	320.0	319.8	319.7
180°	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2
2.5°	45655.4	45643.3	45611.7	45596.1	45566.9	45552.2	45529.4	45514.7	45496.2	45482.5	45475.4
5°	46920.3	46862.0	46744.9	46672.9	46546.5	46463.4	46337.9	46245.8	46116.4	46020.7	45898.4
7.5°	48566.1	48476.5	48326.6	48212.9	48036.2	47901.1	47702.8	47544.1	47324.9	47143.0	46919.1
10°	49236.1	49183.8	49116.6	49043.5	48945.6	48849.5	48714.0	48576.1	48392.1	48209.1	47969.9
12.5°	48245.7	48295.0	48392.1	48437.3	48511.7	48536.8	48570.8	48554.9	48524.8	48450.1	48341.6
15°	45441.1	45646.6	45971.2	46195.9	46510.5	46731.5	47024.0	47212.2	47429.0	47558.5	47681.7
17.5°	40827.4	41224.8	41797.7	42254.9	42868.5	43367.5	43978.8	44459.0	45013.6	45439.0	45891.9
20°	34918.0	35474.6	36265.4	36937.2	37826.4	38580.4	39546.4	40355.6	41299.6	42086.5	42935.7
22.5°	28557.9	29212.5	30118.8	30929.0	31990.8	32939.3	34149.5	35219.5	36495.6	37638.8	38903.4
25°	22557.9	23199.5	24122.6	24961.6	26107.8	27152.6	28474.8	29702.3	31183.2	32564.1	34149.5
27.5°	17412.5	17982.4	18793.9	19549.0	20598.9	21624.6	22966.4	24275.3	25855.5	27339.6	29048.2
30°	13447.4	13909.7	14560.0	15167.4	16010.2	16849.0	18044.3	19254.8	20827.2	22365.1	24116.7
32.5°	10421.2	10815.5	11358.3	11851.4	12500.8	13133.3	14013.5	14980.9	16360.2	17833.2	19526.9
35°	8067.2	8404.4	8866.5	9291.3	9825.3	10327.4	10984.3	11674.7	12727.3	13966.4	15482.1
37.5°	6431.6	6569.1	6898.8	7246.9	7690.4	8103.1	8616.9	9127.4	9880.5	10858.1	12096.3
40°	4891.2	5109.5	5377.8	5652.1	5987.8	6318.8	6882.4	7153.9	7649.7	8351.6	9312.6
42.5°	3946.5	4100.1	4289.0	4479.6	4713.6	4944.1	5229.2	5519.6	5890.3	6365.7	7049.2
45°	3302.6	3402.6	3524.5	3651.4	3805.2	3962.5	4153.3	4352.8	4603.9	4896.1	5311.3
47.5°	2872.3	2927.7	3007.1	3093.9	3199.3	3308.2	3432.3	3559.3	3715.3	3888.7	4125.1
50°	2536.4	2582.7	2644.4	2702.4	2775.1	2886.8	2935.9	3006.1	3100.0	3202.0	3334.2
52.5°	2293.4	2324.3	2362.9	2396.3	2442.3	2484.1	2538.9	2587.2	2652.2	2713.3	2798.8
55°	2104.2	2115.4	2137.4	2158.9	2190.7	2219.2	2256.8	2288.4	2329.8	2366.5	2420.3
57.5°	1958.1	1959.2	1969.3	1980.5	2000.9	2018.9	2044.7	2065.5	2094.3	2117.6	2149.9
60°	1853.1	1847.5	1849.6	1853.5	1865.0	1876.7	1893.2	1906.7	1924.9	1938.0	1956.1
62.5°	1765.7	1756.9	1754.8	1753.9	1759.6	1763.8	1772.8	1779.4	1789.7	1795.5	1805.1
65°	1655.3	1645.0	1640.9	1636.1	1637.8	1636.5	1639.9	1640.1	1645.3	1646.5	1652.1
67.5°	1555.1	1546.5	1541.3	1534.8	1532.0	1527.4	1525.4	1521.0	1520.3	1516.6	1515.7
70°	1463.8	1455.4	1451.0	1445.1	1442.0	1435.9	1432.2	1424.8	1420.4	1413.4	1409.5
72.5°	1358.1	1353.4	1352.0	1348.0	1347.0	1343.6	1342.1	1336.8	1333.8	1327.9	1324.5
75°	1247.7	1243.9	1243.5	1239.4	1239.0	1235.0	1234.0	1228.4	1225.6	1219.6	1217.1
77.5°	1116.2	1110.4	1108.7	1103.9	1105.1	1103.1	1104.8	1100.6	1098.7	1092.8	1090.9
80°	968.0	960.6	957.5	951.3	952.9	950.0	952.9	952.6	954.8	950.0	949.2
82.5°	792.5	784.3	782.8	778.4	781.3	781.6	787.9	784.5	785.9	781.4	783.3
85°	576.7	570.6	562.1	561.0	555.5	561.2	553.8	558.7	550.8	556.3	548.9
87.5°	357.5	345.0	338.4	329.5	326.1	317.4	313.9	307.6	309.5	306.6	308.2
90°	128.5	118.0	115.9	107.4	106.9	99.6	100.7	95.6	97.6	92.2	94.8
92.5°	28.0	29.1	30.8	33.3	34.9	36.9	38.7	41.2	42.8	45.1	46.7
95°	33.7	34.7	37.2	39.9	42.5	45.1	47.9	50.5	53.1	55.8	58.4
97.5°	41.4	42.0	44.6	47.2	49.8	52.5	55.1	58.1	60.7	63.4	65.9
100°	47.1	47.3	54.8	62.2	69.7	77.2	84.7	92.1	99.9	107.3	114.8
102.5°	83.1	84.9	103.7	122.7	141.6	160.4	179.4	198.4	217.3	236.4	255.3
105°	175.6	183.1	211.8	240.8	269.5	298.4	327.3	356.5	385.3	414.3	443.2
107.5°	320.1	333.7	359.8	386.0	412.0	438.2	464.5	490.6	516.8	543.1	569.5
110°	448.7	463.1	480.7	498.3	516.1	533.6	551.2	568.9	586.8	604.5	622.5



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	506.6	516.1	526.4	537.0	547.4	557.9	568.4	579.0	589.7	600.4	611.1
115°	506.0	510.7	514.7	519.3	523.4	527.9	532.4	537.0	541.7	546.2	550.9
117.5°	468.7	470.9	471.8	472.8	473.9	475.3	476.6	478.0	479.6	481.0	482.3
120°	413.2	413.2	413.1	413.1	413.0	413.1	413.4	413.6	413.8	414.3	414.5
122.5°	357.4	357.1	357.0	357.2	357.3	357.7	358.1	358.8	359.0	359.6	360.0
125°	309.4	309.1	310.6	312.0	313.5	315.2	316.7	318.8	320.5	322.2	324.1
127.5°	275.3	275.9	278.4	281.0	283.5	286.2	289.0	291.9	294.4	297.6	300.1
130°	255.8	257.1	259.9	263.3	266.3	269.7	273.0	276.5	279.5	282.8	286.0
132.5°	247.0	249.2	251.8	255.1	258.2	261.5	264.7	268.0	271.2	274.6	277.5
135°	245.3	247.6	250.4	253.4	256.4	259.7	262.5	265.8	268.6	271.8	274.6
137.5°	246.9	249.3	251.9	254.5	256.9	259.9	262.4	265.1	267.5	270.3	272.7
140°	252.2	254.5	256.2	258.3	260.2	262.2	264.0	266.1	267.8	269.9	271.6
142.5°	256.9	259.1	260.2	261.9	263.2	265.2	266.6	268.2	269.5	270.9	272.2
145°	262.7	264.5	265.1	266.2	267.1	268.1	268.8	269.7	270.4	271.2	271.9
147.5°	267.5	268.9	269.1	269.8	270.5	270.9	271.5	272.1	272.4	273.0	273.4
150°	270.8	271.9	271.9	272.4	272.4	272.7	272.8	273.1	273.1	273.5	273.5
152.5°	273.4	274.1	273.8	274.1	273.9	273.9	273.8	274.0	273.8	273.8	274.0
155°	274.6	274.9	274.7	274.7	274.6	274.6	274.5	274.8	274.8	274.8	274.9
157.5°	277.3	277.2	277.1	277.1	276.8	276.9	276.9	277.0	277.1	277.5	277.8
160°	280.7	280.7	280.4	280.4	280.3	280.2	280.2	280.4	280.5	281.2	281.4
162.5°	284.5	284.4	284.1	284.0	283.9	284.0	284.2	284.6	284.7	285.2	285.5
165°	290.2	290.2	289.7	289.9	289.7	289.7	289.8	290.0	290.2	290.6	291.0
167.5°	296.0	295.9	295.9	296.1	296.1	296.3	296.5	297.1	297.3	298.0	298.2
170°	302.9	303.0	302.8	302.8	302.7	302.8	302.9	303.0	303.3	303.5	303.6
172.5°	309.9	309.9	309.8	309.6	309.4	309.4	309.3	309.5	309.3	309.3	309.1
175°	315.4	315.3	315.2	315.1	315.0	314.8	314.8	314.3	314.2	314.1	314.0
177.5°	319.5	319.1	318.9	318.9	318.8	318.7	318.7	318.5	318.5	318.5	318.1
180°	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2
2.5°	45466.3	45465.7	45461.4	45463.4	45464.2	45467.4	45471.4	45475.4	45476.3	45479.5	45480.2
5°	45806.5	45694.1	45610.8	45519.4	45450.5	45388.7	45347.4	45314.6	45301.9	45305.1	45312.7
7.5°	46729.2	46497.0	46305.4	46087.6	45906.0	45713.7	45554.2	45402.7	45292.2	45209.9	45163.9
10°	47741.6	47458.9	47188.3	46873.1	46574.1	46255.0	45966.0	45675.0	45432.2	45221.6	45066.9
12.5°	48191.0	47991.1	47757.2	47459.8	47139.8	46771.6	46399.7	46001.1	45630.5	45286.4	45008.9
15°	47715.2	47715.6	47630.4	47487.7	47265.4	46971.1	46616.9	46201.4	45764.1	45317.8	44910.0
17.5°	46205.1	46490.1	46648.6	46748.8	46718.1	46609.6	46384.2	46065.1	45657.3	45182.0	44684.5
20°	43611.8	44283.8	44762.9	45193.9	45435.4	45595.9	45579.7	45449.9	45159.6	44755.3	44237.2
22.5°	39979.0	41106.9	41997.0	42827.0	43409.1	43882.5	44107.6	44203.2	44071.6	43790.0	43303.5
25°	35566.5	37100.2	38408.9	39679.1	40631.9	41450.7	41942.9	42289.5	42317.1	42170.0	41735.9
27.5°	30663.5	32473.8	34130.3	35818.4	37158.2	38335.4	39107.7	39673.1	39852.6	39828.9	39434.8
30°	25766.8	27667.2	29493.1	31461.5	33119.5	34623.4	35643.6	36408.2	36702.8	36759.2	36380.1
32.5°	21142.2	23016.3	24837.1	26895.0	28719.5	30443.2	31648.5	32556.7	32899.3	32980.0	32564.1
35°	16945.3	18674.3	20404.6	22399.1	24213.1	25997.9	27268.1	28218.8	28538.8	28592.7	28111.3
37.5°	13305.6	14778.7	16286.5	18076.0	19742.0	21418.2	22625.0	23518.6	23751.6	23737.3	23192.3
40°	10241.2	11386.4	12597.9	14071.2	15456.2	16873.2	17892.3	18631.0	18753.4	18662.7	18090.3
42.5°	7700.8	8527.9	9406.2	10506.0	11533.7	12594.2	13335.5	13883.9	13901.4	13758.0	13244.3
45°	5737.1	6544.1	6912.4	7577.4	8239.2	8944.5	9397.2	9735.9	9683.5	9557.3	9166.8
47.5°	4373.5	4683.6	5012.6	5424.9	5810.5	6610.7	6551.4	7095.3	6703.6	6970.8	6382.6
50°	3473.0	3646.4	3823.6	4042.4	4243.9	4453.0	4583.8	4681.3	4668.7	4626.7	4514.1
52.5°	2954.7	3008.3	3095.6	3220.0	3332.5	3445.6	3520.0	3580.6	3581.8	3564.8	3507.9
55°	2469.5	2537.5	2600.3	2681.6	2820.1	2841.4	2948.1	2926.5	2934.9	2905.3	2935.6
57.5°	2177.3	2216.9	2252.2	2300.6	2340.7	2387.4	2414.9	2441.5	2439.0	2433.2	2404.1
60°	1970.3	1992.1	2011.7	2040.0	2062.0	2088.4	2101.0	2114.6	2110.1	2100.3	2074.5
62.5°	1810.7	1824.3	1835.6	1853.7	1867.1	1883.5	1890.2	1895.9	1890.2	1880.8	1858.0
65°	1653.2	1662.1	1669.1	1682.8	1692.3	1706.4	1711.9	1717.3	1712.1	1704.8	1687.4
67.5°	1511.2	1512.0	1511.4	1516.9	1519.8	1528.2	1530.8	1534.7	1528.6	1522.3	1507.6
70°	1403.5	1401.2	1398.6	1400.8	1401.2	1405.3	1406.0	1405.3	1398.0	1387.2	1371.1
72.5°	1319.2	1318.1	1316.0	1317.9	1317.9	1321.6	1320.4	1318.5	1309.6	1299.1	1283.2
75°	1211.0	1210.2	1206.1	1206.2	1202.9	1204.1	1199.7	1197.2	1187.2	1178.4	1164.2
77.5°	1084.3	1082.3	1076.4	1074.2	1067.8	1065.1	1056.8	1052.7	1042.5	1035.5	1023.3
80°	943.0	940.8	933.1	928.9	918.8	912.3	900.1	893.3	881.6	874.7	862.8
82.5°	779.4	780.3	772.7	767.4	752.9	741.7	725.5	716.7	703.8	697.0	684.9
85°	554.4	546.4	550.6	550.3	541.2	531.5	518.3	509.0	498.2	491.7	483.2
87.5°	304.1	305.9	303.7	301.8	295.4	290.5	280.2	274.8	266.9	263.0	256.6
90°	86.7	86.4	78.9	78.8	71.3	68.5	59.8	58.2	50.3	49.0	43.3
92.5°	44.5	42.2	40.5	37.9	36.0	33.8	31.6	29.4	27.2	26.1	25.8
95°	55.2	52.1	49.0	45.8	42.6	39.4	36.4	33.2	30.0	29.4	28.7
97.5°	62.4	58.6	54.8	51.2	47.5	43.8	40.1	36.4	32.6	32.2	31.8
100°	106.3	97.8	89.1	80.5	71.9	63.3	54.8	46.1	37.6	37.1	36.6
102.5°	234.3	213.4	192.6	171.7	151.0	130.0	109.2	88.1	67.3	64.3	61.2
105°	411.5	379.7	348.4	316.8	285.1	253.4	222.0	190.1	158.4	148.3	138.0
107.5°	539.9	510.1	480.6	451.0	421.2	391.7	361.9	332.1	302.4	284.5	266.7
110°	599.0	575.6	552.3	528.9	505.6	482.2	458.6	435.1	411.7	396.3	381.3



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	594.1	577.2	560.4	543.3	526.5	509.4	492.4	475.3	458.1	449.0	440.0
115°	541.1	531.1	521.3	511.3	501.4	491.4	481.5	471.1	461.0	456.4	451.9
117.5°	477.9	473.1	468.7	463.8	459.2	454.2	449.6	444.6	439.8	438.6	437.2
120°	414.1	413.2	412.2	411.3	410.5	409.6	408.5	407.5	406.4	407.2	408.1
122.5°	361.7	363.1	364.8	366.1	367.7	368.9	370.6	371.5	372.9	375.0	377.0
125°	326.7	329.2	331.7	334.1	336.5	339.0	341.5	343.5	346.1	348.1	350.5
127.5°	303.3	305.8	308.8	311.4	314.2	316.8	319.6	322.0	324.7	326.8	329.2
130°	288.8	291.1	293.9	296.2	299.0	301.5	303.9	306.4	308.9	310.9	313.1
132.5°	280.0	282.5	285.0	287.2	289.9	292.0	294.5	296.8	299.5	301.2	303.2
135°	276.9	278.8	281.0	282.8	285.2	286.9	289.1	291.3	293.6	295.2	297.0
137.5°	274.6	276.3	278.3	279.9	282.0	283.6	285.8	287.7	290.0	291.2	293.0
140°	273.3	275.2	276.9	278.6	280.5	282.3	284.5	286.5	288.7	290.1	291.8
142.5°	273.8	275.0	276.6	278.0	279.8	281.2	283.1	285.0	287.0	288.6	290.0
145°	273.4	274.8	276.4	277.9	279.5	281.2	283.3	285.3	287.3	288.6	290.0
147.5°	274.6	275.7	277.2	278.6	280.1	281.4	283.4	285.1	287.0	288.4	289.7
150°	274.8	276.0	277.2	278.5	280.1	281.7	283.4	285.3	287.5	288.7	290.0
152.5°	275.2	276.3	277.7	279.2	280.7	282.3	284.2	286.1	288.0	289.1	290.6
155°	276.3	277.3	278.7	280.4	282.0	283.4	285.2	286.9	288.7	290.1	291.2
157.5°	278.9	279.9	281.2	282.8	284.1	285.6	287.3	288.8	290.5	291.5	292.6
160°	282.6	283.6	284.9	286.2	287.6	288.9	290.4	291.8	293.3	294.3	295.3
162.5°	286.8	287.8	289.3	290.2	291.8	293.0	294.6	295.7	297.3	298.1	299.2
165°	291.9	292.9	294.1	295.0	296.1	296.9	298.4	299.2	300.7	301.2	302.4
167.5°	299.2	299.9	300.6	301.4	302.5	303.3	304.2	305.0	306.1	306.9	307.7
170°	304.3	304.9	305.5	306.3	307.0	307.8	308.5	309.0	310.2	310.8	311.5
172.5°	309.7	309.8	310.5	310.8	311.3	311.6	312.3	312.8	313.3	314.0	314.6
175°	314.5	314.6	314.8	314.9	315.0	315.3	315.7	316.2	316.4	316.8	317.2
177.5°	318.2	318.3	318.4	318.5	318.9	319.0	319.3	319.4	319.6	319.8	320.2
180°	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2
2.5°	45478.6	45478.1	45476.6	45474.6	45472.5	45473.7	45475.7	45481.0	45490.2	45503.4	45520.6
5°	45319.0	45328.2	45333.5	45334.2	45329.5	45326.5	45331.0	45343.5	45368.7	45410.9	45468.2
7.5°	45151.5	45163.0	45180.7	45193.9	45196.4	45193.1	45193.9	45213.5	45260.0	45342.3	45457.8
10°	44972.8	44938.8	44956.7	44989.5	45015.6	45020.4	45023.6	45046.7	45114.7	45239.1	45424.7
12.5°	44807.7	44700.2	44679.4	44709.0	44748.6	44761.2	44757.7	44767.7	44847.3	45012.1	45270.6
15°	44590.6	44388.2	44319.0	44326.6	44375.5	44393.1	44380.2	44360.6	44438.3	44639.3	44974.0
17.5°	44239.2	43912.8	43785.7	43780.1	43837.2	43852.4	43821.0	43760.1	43836.6	44087.5	44503.0
20°	43704.9	43223.2	42983.7	42945.7	43007.7	42989.6	42926.9	42834.9	42935.4	43240.5	43734.6
22.5°	42744.6	42134.1	41725.0	41593.1	41667.4	41617.8	41526.4	41408.8	41542.2	41888.9	42439.2
25°	41175.3	40469.9	39909.8	39595.6	39654.8	39566.0	39466.4	39324.0	39483.2	39881.1	40486.8
27.5°	38868.6	38053.8	37359.8	36839.6	36858.7	36742.4	36627.7	36443.4	36642.0	37113.0	37796.2
30°	35801.3	34858.4	34013.3	33306.3	33243.1	33130.3	33012.8	32770.9	33019.6	33583.4	34381.8
32.5°	31949.2	30902.5	29925.9	29032.1	28863.5	28753.4	28648.7	28370.4	28695.9	29353.2	30270.5
35°	27444.5	26329.3	25270.6	24249.8	23970.4	23860.3	23768.8	23502.2	23908.4	24623.7	25614.4
37.5°	22499.8	21360.7	20309.5	19262.7	18868.0	18718.7	18652.3	18477.5	18946.2	19653.7	20648.4
40°	17423.6	16364.5	15422.1	14497.5	14047.6	13819.1	13784.2	13752.4	14205.5	14819.4	15722.2
42.5°	12675.0	11820.5	11093.8	10387.1	9979.4	9667.3	9667.3	9761.9	10169.8	10629.6	11325.8
45°	8767.7	8194.3	7731.3	7259.0	7385.2	6763.2	7128.7	6941.2	7142.7	7439.1	7891.9
47.5°	6027.0	5713.9	5459.6	5195.8	5003.5	4819.8	4835.9	4954.3	5144.2	5320.0	5555.6
50°	4392.7	4233.2	4103.6	3966.6	3870.9	3789.9	3794.6	3845.9	3945.7	4038.4	4161.6
52.5°	3441.9	3354.0	3283.6	3207.8	3157.7	3117.4	3119.6	3144.5	3198.4	3251.3	3322.0
55°	2837.0	2826.3	2734.8	2666.9	2641.0	2614.0	2618.9	2628.7	2665.4	2696.3	2743.1
57.5°	2377.4	2336.3	2308.9	2273.0	2256.6	2237.7	2241.9	2245.6	2270.2	2290.9	2324.6
60°	2052.8	2023.8	2004.3	1979.9	1969.2	1957.1	1959.8	1962.0	1977.8	1991.3	2015.5
62.5°	1837.3	1811.2	1794.3	1775.5	1767.8	1759.7	1761.6	1762.3	1772.1	1782.1	1800.4
65°	1671.9	1651.2	1637.2	1620.9	1613.0	1604.5	1605.4	1605.4	1613.7	1620.9	1634.6
67.5°	1496.9	1481.4	1472.3	1459.4	1454.0	1445.4	1445.2	1442.5	1447.9	1450.8	1460.1
70°	1356.6	1340.9	1329.2	1316.8	1310.1	1302.5	1302.7	1302.8	1309.1	1315.7	1327.7
72.5°	1269.9	1254.8	1244.5	1233.7	1227.3	1220.8	1219.6	1219.0	1223.5	1227.1	1235.0
75°	1155.0	1143.0	1136.9	1126.8	1121.7	1114.5	1113.3	1109.9	1112.1	1112.8	1118.6
77.5°	1015.7	1004.3	999.4	989.2	984.9	976.6	976.0	972.2	973.9	972.8	977.3
80°	856.9	846.6	843.8	835.4	833.4	825.7	824.6	820.0	821.4	817.8	819.5
82.5°	679.7	670.2	668.2	660.3	660.3	653.5	653.1	646.2	646.2	640.3	630.7
85°	478.7	471.9	468.9	462.5	460.6	455.1	452.2	445.6	443.3	439.0	437.6
87.5°	252.6	248.3	244.4	241.3	235.7	225.7	224.9	218.0	218.5	213.6	214.0
90°	42.8	37.6	37.2	32.5	31.8	28.7	28.3	27.6	28.0	27.4	27.9
92.5°	25.0	24.2	23.5	22.8	22.0	21.3	20.6	21.3	22.0	22.8	23.5
95°	28.1	27.4	26.7	26.1	25.5	24.8	24.1	24.8	25.5	26.3	26.9
97.5°	31.4	30.9	30.6	30.1	29.7	29.3	28.9	29.4	29.8	30.2	30.7
100°	36.1	35.6	35.1	34.7	34.1	33.7	33.2	34.0	34.5	35.0	35.5
102.5°	58.4	55.3	52.3	49.3	46.3	43.2	40.2	43.2	46.3	49.5	52.5
105°	127.9	117.8	107.6	97.3	87.2	76.9	66.7	77.1	87.3	97.5	107.9
107.5°	248.7	231.1	213.1	195.2	177.1	159.2	141.2	159.3	177.3	195.3	213.3
110°	365.7	350.4	334.9	319.6	304.0	288.6	273.0	288.8	304.3	319.9	335.4



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	430.6	421.5	412.2	403.1	393.5	384.3	374.8	384.7	394.2	403.9	413.1
115°	447.3	442.5	438.1	433.3	428.4	423.6	418.6	424.2	429.3	434.3	439.4
117.5°	435.9	434.7	433.2	431.8	430.3	428.9	427.2	429.3	431.1	433.4	434.9
120°	408.5	409.6	410.2	410.7	411.4	411.9	412.2	412.6	412.6	412.6	412.4
122.5°	379.0	381.1	382.8	384.7	386.5	388.3	389.6	388.9	387.8	386.9	385.5
125°	352.4	354.9	356.7	358.9	360.6	362.7	363.9	363.5	362.4	361.4	359.9
127.5°	331.3	333.4	335.3	337.6	339.2	340.9	342.3	341.9	341.0	340.1	338.9
130°	314.8	317.2	318.7	320.6	322.1	323.5	324.6	324.6	323.9	323.7	322.6
132.5°	304.9	307.0	308.6	310.3	311.5	313.0	313.7	313.9	313.7	313.5	312.6
135°	298.8	300.4	301.8	303.6	304.7	305.7	306.4	307.0	306.9	306.8	306.2
137.5°	294.3	296.0	297.4	298.5	299.5	300.3	300.8	301.6	301.7	302.2	301.9
140°	293.2	294.9	296.2	297.4	298.6	299.6	300.0	300.8	301.0	301.1	300.8
142.5°	291.6	293.1	294.5	295.9	296.7	297.7	298.3	299.0	299.2	299.2	299.1
145°	291.5	292.7	294.1	295.3	296.1	296.8	297.1	298.1	298.4	298.5	298.6
147.5°	291.0	292.4	293.4	294.4	295.2	296.0	296.5	297.0	297.4	297.6	297.7
150°	291.4	292.7	293.9	295.0	295.9	296.7	296.9	297.6	297.9	298.2	298.1
152.5°	291.7	292.7	293.9	294.9	295.8	296.4	296.7	297.4	298.0	298.4	298.5
155°	292.3	293.5	294.4	295.5	296.1	297.0	297.6	298.4	298.9	299.2	299.5
157.5°	293.5	294.7	295.6	296.6	297.3	298.3	299.0	299.8	300.3	301.0	301.3
160°	296.1	297.4	298.0	299.1	299.9	300.8	301.4	302.3	302.9	303.4	304.1
162.5°	300.0	301.0	301.5	302.5	303.3	304.2	304.9	305.7	306.4	307.1	307.6
165°	303.3	304.2	304.9	305.8	306.7	307.7	308.2	309.0	309.5	310.0	310.5
167.5°	308.4	309.4	309.8	310.8	311.4	312.3	313.1	313.7	314.1	314.6	314.9
170°	312.2	313.0	313.6	314.2	314.9	315.7	316.2	316.6	317.0	317.4	317.9
172.5°	315.0	315.8	316.4	317.2	317.6	318.3	318.8	319.3	319.5	319.7	319.7
175°	317.5	318.1	318.4	318.9	319.3	319.8	320.3	320.3	320.6	320.6	320.8
177.5°	320.6	321.3	321.6	321.9	322.3	322.5	322.9	322.7	322.7	322.6	322.3
180°	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2
2.5°	45544.9	45567.8	45602.5	45634.2	45681.8	45719.3	45775.6	45818.4	45881.9	45923.2	45992.4
5°	45549.0	45638.1	45755.3	45869.6	46007.1	46131.9	46286.9	46419.1	46574.9	46702.1	46861.6
7.5°	45613.4	45785.2	45991.2	46198.7	46433.4	46652.9	46900.3	47124.2	47369.0	47576.1	47802.4
10°	45660.9	45925.9	46229.5	46534.8	46856.4	47155.0	47456.6	47717.1	47960.7	48161.1	48338.2
12.5°	45596.5	45961.6	46351.1	46727.2	47084.7	47393.8	47653.2	47853.6	47991.9	48085.8	48107.8
15°	45377.5	45816.9	46240.3	46614.9	46911.5	47140.3	47258.7	47314.1	47254.6	47155.9	46938.7
17.5°	44968.4	45431.8	45810.4	46105.9	46262.6	46324.7	46226.6	46055.9	45722.5	45352.3	44817.7
20°	44218.4	44650.2	44924.8	45085.9	45044.0	44888.9	44518.6	44068.4	43402.6	42693.1	41756.6
22.5°	42902.9	43280.3	43426.6	43438.7	43182.7	42794.5	42126.5	41354.4	40304.0	39212.1	37869.1
25°	40928.2	41258.8	41281.9	41152.1	40683.8	40054.6	39073.7	37981.4	36554.2	35099.1	33416.3
27.5°	38250.2	38567.3	38489.6	38247.3	37597.3	36755.2	35499.4	34088.3	32328.7	30610.2	28748.7
30°	34883.6	35222.7	35131.6	34820.7	34047.6	33052.4	31574.7	29935.3	27981.8	26146.2	24259.8
32.5°	30854.9	31283.6	31220.7	30925.3	30118.5	29053.4	27450.0	25711.2	23712.5	21903.8	20068.7
35°	26275.8	26796.3	26823.2	26630.0	25881.1	24828.3	23245.1	21562.1	19647.7	17940.9	16245.8
37.5°	21342.3	21945.6	22069.6	22017.6	21396.7	20467.5	19024.9	17515.2	15819.1	14323.4	12873.6
40°	16381.5	16992.2	17204.2	17267.1	16808.9	16089.2	14905.3	13686.7	12304.0	11092.0	9940.8
42.5°	11857.4	12398.9	12603.6	12732.5	12446.5	11966.6	11103.0	10218.0	9205.0	8330.9	7492.8
45°	8235.2	8618.2	8774.0	8903.6	8748.0	8477.1	7931.8	7378.3	6709.7	6138.3	5597.6
47.5°	5757.7	5968.9	6071.8	6134.7	6074.3	5933.1	5636.3	5315.6	4938.2	4604.3	4283.4
50°	4267.7	4380.1	4434.0	4470.3	4426.3	4347.9	4187.2	4012.6	3805.3	3616.2	3431.4
52.5°	3382.1	3446.5	3478.5	3498.1	3472.9	3424.8	3331.3	3227.8	3103.5	2986.7	2925.3
55°	2849.2	2845.8	2919.7	2884.0	2919.7	2840.1	2823.3	2709.5	2606.3	2533.6	2455.0
57.5°	2349.7	2383.1	2397.3	2413.2	2402.9	2388.3	2348.6	2307.9	2253.4	2207.9	2159.4
60°	2033.9	2061.5	2077.0	2092.8	2091.8	2086.3	2063.3	2038.9	2005.0	1977.8	1948.3
62.5°	1816.4	1840.3	1855.6	1870.7	1872.0	1869.9	1852.4	1835.6	1812.4	1795.3	1775.0
65°	1645.3	1662.1	1672.5	1684.5	1683.8	1680.6	1664.9	1650.8	1631.8	1619.9	1605.0
67.5°	1466.2	1478.8	1487.0	1498.4	1500.5	1501.2	1492.6	1486.0	1476.7	1473.3	1468.2
70°	1338.8	1354.3	1367.3	1381.6	1389.4	1393.1	1389.4	1386.0	1380.6	1378.2	1374.4
72.5°	1242.4	1255.4	1265.6	1278.6	1285.9	1291.2	1288.3	1286.4	1281.7	1281.0	1278.3
75°	1122.7	1131.7	1137.5	1147.3	1151.2	1156.1	1153.8	1155.0	1153.5	1157.2	1157.1
77.5°	978.8	985.4	988.1	995.2	995.9	1001.8	1003.2	1010.1	1015.0	1025.8	1031.6
80°	816.8	821.0	821.0	828.3	831.5	841.5	846.2	857.5	862.8	872.4	873.3
82.5°	634.5	629.6	634.5	631.5	640.7	652.0	653.5	663.1	665.3	671.4	666.7
85°	433.8	433.5	429.5	430.2	427.3	428.7	427.0	428.9	427.2	427.3	422.9
87.5°	207.8	209.7	205.1	206.7	202.3	204.2	200.4	203.4	198.9	199.5	192.8
90°	27.8	28.1	27.9	28.3	29.2	30.3	31.5	32.7	34.5	35.5	36.9
92.5°	24.2	25.0	25.8	26.6	27.3	29.5	31.7	33.9	36.3	38.3	40.5
95°	27.6	28.2	28.9	29.9	30.6	33.8	37.0	40.1	43.3	46.5	49.7
97.5°	31.4	31.8	32.3	32.6	33.2	37.0	40.7	44.6	48.3	52.0	55.6
100°	36.1	36.5	37.1	37.7	38.2	46.9	55.6	64.3	72.9	81.5	90.1
102.5°	55.6	58.6	61.7	65.1	68.1	89.1	110.1	131.2	151.9	172.9	193.8
105°	118.2	128.4	138.9	149.2	159.4	191.2	223.1	255.0	286.4	318.1	350.0
107.5°	231.5	249.5	267.7	285.7	303.7	333.6	363.4	393.3	423.2	453.0	482.5
110°	351.4	366.5	382.5	398.0	413.6	437.0	460.8	484.3	507.9	531.5	554.9



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	422.8	432.1	441.6	450.7	460.3	477.6	495.0	512.2	529.5	546.4	563.6
115°	444.4	449.0	454.0	458.8	463.8	474.2	484.3	494.6	504.9	514.9	525.2
117.5°	436.7	438.4	440.0	441.3	443.0	448.0	453.1	458.1	463.2	468.3	473.2
120°	412.2	411.7	411.4	410.7	410.4	411.4	413.0	413.9	415.4	416.4	417.5
122.5°	384.3	382.6	381.1	379.4	377.8	376.4	375.5	374.1	373.3	372.0	370.8
125°	358.5	356.8	355.2	353.3	351.4	349.3	347.2	345.0	342.7	340.5	338.3
127.5°	337.7	336.0	334.6	332.8	331.0	328.4	326.1	323.4	321.2	318.5	316.0
130°	321.7	320.2	319.2	317.2	316.0	313.3	311.3	308.9	306.6	304.2	301.8
132.5°	312.1	310.8	309.8	308.2	307.0	304.7	302.8	300.3	298.2	295.9	293.8
135°	305.8	304.9	304.1	302.9	301.7	299.6	297.9	295.9	294.2	292.2	290.4
137.5°	301.7	300.8	300.1	299.3	298.4	296.6	295.1	293.3	291.8	289.9	288.5
140°	300.6	300.0	299.3	298.5	297.6	295.9	294.3	292.6	291.0	289.3	287.7
142.5°	298.7	298.2	297.6	296.8	296.1	294.5	293.5	292.0	290.6	289.2	287.9
145°	298.4	297.9	297.6	296.8	296.7	295.1	293.8	292.2	291.1	289.5	288.3
147.5°	297.7	297.4	297.3	296.7	296.7	295.4	294.5	293.3	292.4	291.1	290.2
150°	298.1	298.0	297.9	297.6	297.3	296.2	295.4	294.3	293.6	292.4	291.6
152.5°	298.5	298.6	298.7	298.6	298.7	297.9	297.0	296.0	295.2	294.2	293.5
155°	299.9	300.0	300.2	300.2	300.2	299.6	298.9	298.1	297.4	296.6	295.9
157.5°	301.7	302.0	302.4	302.5	302.7	302.2	301.6	301.0	300.4	299.7	299.1
160°	304.4	304.9	305.3	305.5	305.7	305.2	305.1	304.2	304.1	303.3	302.7
162.5°	308.1	308.6	309.0	309.1	309.4	308.9	308.8	308.2	307.8	306.9	306.5
165°	311.1	311.2	311.6	311.7	312.0	311.6	311.5	311.2	310.8	310.4	310.0
167.5°	315.5	315.6	316.0	316.0	316.3	316.0	316.3	315.9	315.6	315.4	315.1
170°	318.1	318.4	318.7	318.8	319.0	318.8	318.7	318.5	318.5	318.0	317.7
172.5°	320.1	320.0	320.3	320.5	320.5	320.3	320.3	320.1	320.1	320.0	319.8
175°	320.9	320.9	321.0	321.0	321.0	321.1	321.0	321.1	321.0	321.0	320.9
177.5°	322.4	322.3	322.1	322.1	322.0	321.9	322.0	321.9	322.1	322.1	322.0
180°	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2
2.5°	46035.2	45750.9	45713.3	45733.3	45780.9	45798.4	45849.6	45863.7	45915.2	45928.0	45977.5
5°	46985.0	46609.3	46628.1	46718.3	46855.2	46936.7	47071.1	47141.4	47269.9	47328.2	47444.2
7.5°	47986.7	47691.6	47783.6	47936.0	48123.0	48252.5	48414.1	48519.2	48658.4	48744.8	48856.3
10°	48478.5	48397.7	48498.9	48618.9	48725.5	48809.1	48877.6	48932.4	48968.2	49001.9	49016.6
12.5°	48104.2	48229.3	48246.6	48235.0	48164.3	48110.3	47989.1	47906.8	47760.4	47671.3	47497.3
15°	46716.8	46992.0	46839.6	46609.0	46271.4	45990.0	45592.6	45296.7	44882.9	44602.1	44186.8
17.5°	44282.0	44629.3	44232.2	43698.5	43019.6	42438.7	41715.4	41141.2	40422.1	39899.0	39227.8
20°	40854.3	41178.8	40470.7	39585.9	38535.6	37651.7	36609.2	35777.5	34808.9	34088.3	33218.7
22.5°	36586.4	36817.6	35820.1	34627.3	33289.1	32184.8	30938.5	29941.4	28835.9	28012.2	27084.9
25°	31864.8	31927.3	30730.7	29356.4	27865.0	26623.9	25293.4	24245.0	23117.6	22282.7	21372.7
27.5°	27099.4	27007.8	25714.4	24257.4	22688.6	21398.6	20100.8	19118.5	18131.0	17379.0	16595.0
30°	22601.3	22379.8	21036.9	19539.2	18016.3	16860.2	15782.8	14993.9	14208.3	13611.7	12982.5
32.5°	18476.5	18164.0	16856.8	15453.7	14170.5	13278.2	12479.3	11882.4	11248.0	10744.1	10216.0
35°	14823.0	14490.1	13332.0	12142.5	11171.3	10513.6	9885.7	9396.0	8857.4	8432.2	7973.6
37.5°	11687.6	11414.6	10444.6	9508.6	8774.0	8264.2	7749.9	7349.6	6904.5	6717.4	6227.4
40°	9022.7	8832.0	8073.5	7383.5	6831.9	6592.5	6070.3	5696.3	5363.7	5089.4	4823.7
42.5°	7037.9	6970.4	6232.3	5694.1	5305.7	5004.0	4713.0	4476.7	4246.7	4057.6	3879.0
45°	5164.8	5111.4	4783.6	4473.0	4208.3	3997.5	3800.8	3638.3	3487.9	3363.2	3250.0
47.5°	4021.8	4004.7	3815.9	3623.4	3456.6	3321.2	3193.5	3085.6	2985.9	2902.6	2875.5
50°	3271.1	3268.9	3158.1	3039.2	2920.5	2842.3	2760.7	2696.9	2632.9	2583.0	2530.2
52.5°	2779.4	2767.3	2692.6	2619.1	2548.7	2497.2	2445.2	2404.4	2362.0	2331.2	2298.4
55°	2392.7	2405.5	2362.1	2318.3	2274.2	2242.2	2205.7	2178.8	2149.7	2130.3	2110.5
57.5°	2124.2	2141.0	2118.2	2093.5	2066.6	2045.5	2020.4	2001.8	1982.3	1970.0	1958.5
60°	1928.9	1947.1	1938.0	1925.5	1908.9	1896.4	1880.3	1870.1	1857.5	1850.5	1844.1
62.5°	1763.1	1786.0	1782.7	1776.8	1766.1	1759.3	1750.5	1745.9	1737.6	1734.6	1731.5
65°	1597.7	1623.5	1622.9	1620.1	1614.1	1612.2	1606.7	1605.7	1601.5	1603.2	1602.8
67.5°	1467.7	1490.1	1495.0	1498.5	1498.4	1499.7	1499.2	1501.4	1501.4	1504.6	1506.6
70°	1373.9	1389.4	1393.1	1396.9	1397.8	1400.9	1400.9	1402.7	1402.3	1405.0	1405.3
72.5°	1279.0	1299.5	1303.2	1306.2	1306.2	1309.1	1307.6	1307.0	1303.0	1302.1	1299.3
75°	1161.0	1187.2	1192.9	1196.6	1197.2	1199.7	1196.1	1193.9	1187.2	1184.4	1179.7
77.5°	1037.6	1064.9	1068.9	1070.3	1068.1	1068.7	1061.2	1056.1	1047.4	1043.9	1039.3
80°	877.1	917.2	920.5	918.0	911.6	910.7	903.3	898.6	888.4	884.8	880.9
82.5°	667.5	714.5	721.1	724.0	718.9	720.0	713.2	710.4	701.0	699.3	693.0
85°	421.4	468.5	476.2	475.1	470.0	468.7	464.7	466.1	465.3	467.8	469.1
87.5°	193.6	239.1	250.1	246.6	246.0	242.8	235.5	238.3	242.7	245.5	245.7
90°	38.2	53.2	54.2	54.4	50.3	49.7	45.9	46.3	43.1	43.3	40.4
92.5°	42.7	44.9	47.1	45.2	43.2	41.3	39.3	37.2	35.4	33.3	31.5
95°	52.8	55.7	58.9	56.3	53.5	50.9	48.3	45.6	43.0	40.5	37.8
97.5°	59.4	62.8	66.5	63.9	61.2	58.5	55.8	53.2	50.5	47.8	45.1
100°	98.7	106.8	115.3	107.8	100.3	92.8	85.4	77.7	70.3	62.8	55.3
102.5°	214.7	235.2	255.8	236.9	217.9	198.8	180.0	161.1	142.3	123.1	104.3
105°	381.4	412.5	444.0	414.7	385.9	357.0	328.0	299.2	270.2	241.1	212.4
107.5°	512.3	540.9	570.2	543.9	517.7	491.5	465.0	438.9	412.6	386.2	360.2
110°	578.4	600.4	623.5	605.4	587.8	569.8	552.1	534.2	516.5	498.9	481.4



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	580.6	595.6	612.2	601.3	590.7	580.0	569.3	558.7	548.2	537.4	527.3
115°	535.0	542.8	552.2	547.3	542.9	538.2	533.5	529.1	524.4	519.9	515.7
117.5°	478.0	480.1	484.1	482.4	481.1	479.3	478.1	476.5	475.4	474.0	472.9
120°	418.5	416.5	416.7	416.1	415.9	415.4	415.2	414.8	414.6	414.5	414.5
122.5°	369.4	364.7	362.3	361.8	361.3	360.6	360.3	359.7	359.3	359.0	358.8
125°	336.0	329.9	326.5	324.6	322.9	321.1	319.2	317.4	315.9	314.2	312.7
127.5°	313.4	306.8	303.2	300.4	297.6	294.8	292.0	289.1	286.5	283.6	281.2
130°	299.6	292.8	289.4	286.1	283.0	279.6	276.5	273.2	269.8	266.7	263.5
132.5°	291.5	284.6	281.2	278.2	275.3	271.9	268.9	265.6	262.4	259.1	256.1
135°	288.5	281.6	278.7	275.5	273.0	269.9	267.0	264.0	261.1	257.9	255.3
137.5°	286.5	279.6	277.0	274.4	272.1	269.5	267.3	264.6	262.2	259.2	257.0
140°	286.0	278.7	276.0	274.3	272.9	270.8	269.1	267.3	265.6	263.8	262.0
142.5°	286.5	279.4	276.8	275.5	274.4	273.0	272.1	270.6	269.3	267.6	266.4
145°	287.0	279.1	276.6	275.7	275.5	274.6	274.0	273.3	272.7	271.7	271.1
147.5°	288.9	280.8	278.1	277.9	277.7	277.0	277.0	276.3	276.3	275.6	275.4
150°	290.3	281.2	278.0	278.0	277.9	277.9	277.9	277.6	277.9	277.7	277.6
152.5°	292.3	281.2	277.8	277.8	278.0	277.9	278.0	278.2	278.6	278.7	278.8
155°	294.7	282.7	278.8	278.5	278.5	278.6	278.6	278.7	278.8	279.0	279.4
157.5°	298.2	285.3	281.6	281.1	281.0	280.9	280.8	280.8	280.9	281.0	281.4
160°	302.0	289.2	285.3	284.7	284.6	284.4	284.1	283.9	284.0	284.1	284.4
162.5°	305.7	293.2	289.4	288.8	288.5	288.2	288.1	287.6	287.7	287.6	287.8
165°	309.3	298.2	294.6	294.2	294.0	293.6	293.5	293.3	293.3	293.3	293.5
167.5°	314.6	304.5	301.7	301.2	300.7	300.2	300.2	299.5	299.5	299.2	299.2
170°	317.3	309.4	307.0	306.7	306.8	306.6	306.3	306.2	306.1	305.9	306.0
172.5°	319.5	313.7	311.8	311.8	312.0	312.0	312.2	312.2	312.3	312.5	312.7
175°	320.8	317.3	316.5	316.4	316.4	316.5	316.6	316.6	316.7	316.8	317.2
177.5°	322.1	321.1	320.6	320.6	320.6	320.6	320.6	320.6	320.6	320.8	320.8
180°	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2
2.5°	45986.8	46040.4	46036.3	46086.4	46083.8	46131.1	46121.5	46162.3	46153.0	46187.8	46167.4
5°	47495.2	47597.3	47630.9	47722.9	47742.0	47824.3	47826.0	47891.5	47883.6	47934.8	47907.6
7.5°	48922.2	49017.5	49062.6	49134.1	49169.8	49229.0	49252.2	49300.9	49312.5	49341.3	49340.4
10°	49042.6	49042.3	49064.6	49054.6	49074.6	49063.1	49087.4	49078.7	49114.7	49105.3	49132.6
12.5°	47422.2	47261.4	47202.7	47058.3	47026.7	46902.7	46911.5	46832.0	46870.4	46821.5	46904.8
15°	43939.7	43566.6	43382.4	43058.0	42956.1	42699.8	42679.0	42508.7	42554.7	42465.5	42595.8
17.5°	38793.5	38206.2	37883.8	37410.2	37222.1	36859.6	36786.9	36567.6	36601.7	36491.3	36648.5
20°	32657.8	31948.1	31541.5	30993.7	30749.4	30317.2	30202.5	29957.3	29988.1	29878.1	30056.1
22.5°	26452.1	25709.2	25250.3	24676.1	24364.1	23957.6	23835.7	23589.3	23603.3	23500.1	23671.2
25°	20749.4	20037.1	19591.6	19070.1	18799.4	18426.6	18298.5	18077.3	18089.8	18004.8	18158.3
27.5°	16051.1	15466.7	15093.9	14656.8	14414.2	14107.7	13982.8	13796.7	13796.3	13733.8	13862.2
30°	12543.1	12055.4	11720.7	11340.1	11112.1	10835.6	10714.9	10548.4	10541.2	10496.9	10598.9
32.5°	9821.0	9387.2	9082.0	8746.9	8542.3	8305.1	8190.7	8057.0	8044.8	8004.7	8088.4
35°	7634.5	7269.2	7006.8	6724.7	6745.5	6395.4	6453.6	6181.7	6108.0	6091.9	6154.1
37.5°	5900.6	5617.7	5404.4	5193.2	5050.2	4902.2	4822.5	4751.0	4742.9	4736.0	4779.5
40°	4618.6	4420.6	4265.4	4120.5	4022.2	3931.8	3882.0	3842.7	3833.4	3828.2	3854.5
42.5°	3738.1	3604.4	3504.5	3416.0	3356.2	3307.1	3279.7	3257.9	3250.6	3250.8	3266.4
45°	3158.1	3077.1	3012.7	2957.8	2919.6	2936.3	2886.8	2912.8	2878.6	2913.9	2890.6
47.5°	2781.2	2712.2	2672.3	2633.4	2610.2	2591.6	2592.3	2592.7	2599.9	2601.1	2608.7
50°	2490.3	2450.5	2422.7	2397.8	2385.8	2376.0	2379.4	2381.9	2389.1	2389.5	2395.1
52.5°	2275.1	2248.9	2232.1	2216.7	2211.3	2205.7	2208.1	2207.1	2210.3	2208.6	2213.1
55°	2099.9	2087.5	2082.2	2076.5	2077.3	2075.8	2076.9	2071.3	2067.9	2063.7	2067.5
57.5°	1956.1	1954.4	1957.9	1960.3	1966.9	1969.3	1970.8	1964.4	1958.3	1952.8	1956.0
60°	1845.4	1848.0	1856.9	1863.9	1873.4	1877.8	1880.5	1876.8	1872.4	1867.8	1870.5
62.5°	1736.1	1740.3	1750.8	1758.8	1770.2	1776.1	1782.7	1783.1	1784.8	1783.1	1785.0
65°	1609.2	1614.5	1624.0	1630.6	1641.2	1646.5	1653.2	1654.4	1658.1	1657.3	1660.5
67.5°	1512.9	1517.6	1525.5	1531.8	1541.3	1546.7	1552.6	1553.0	1554.3	1554.0	1557.0
70°	1410.0	1412.5	1419.5	1424.8	1434.2	1439.8	1446.6	1448.6	1452.8	1453.5	1456.9
72.5°	1300.4	1299.5	1303.6	1306.1	1313.2	1317.5	1326.2	1330.9	1338.0	1339.8	1342.4
75°	1181.0	1180.0	1185.1	1187.2	1193.2	1197.6	1207.3	1213.6	1224.5	1229.1	1227.9
77.5°	1042.9	1045.3	1054.8	1060.0	1068.1	1073.6	1086.2	1096.2	1116.3	1125.1	1116.2
80°	888.4	890.9	900.7	905.6	916.3	923.0	937.0	948.7	966.8	970.7	965.6
82.5°	698.4	699.1	707.9	711.6	725.5	735.5	753.2	762.5	773.7	772.0	770.7
85°	476.2	482.6	493.6	504.7	521.5	537.8	554.6	568.4	558.6	574.0	556.7
87.5°	254.5	253.8	268.7	266.4	290.1	303.7	318.2	325.2	333.0	331.4	331.6
90°	41.3	38.9	40.1	37.3	39.8	36.6	40.4	37.6	42.1	38.3	44.6
92.5°	29.4	28.4	27.3	26.3	25.1	24.2	23.1	22.0	20.9	19.9	20.9
95°	35.2	34.2	33.2	32.1	31.1	30.1	29.1	28.2	27.2	26.2	27.4
97.5°	42.5	42.0	41.3	40.8	40.2	39.7	39.0	38.5	37.7	37.2	38.0
100°	47.8	47.8	47.8	47.8	47.4	47.4	47.4	47.4	47.4	47.4	48.0
102.5°	85.3	83.4	81.5	79.5	77.6	75.7	73.8	71.9	70.0	68.2	70.9
105°	183.5	176.1	168.6	161.2	153.6	146.3	138.9	131.5	124.2	116.8	124.4
107.5°	334.3	320.6	307.1	293.6	280.1	266.6	253.3	239.8	226.4	213.0	225.0
110°	463.7	449.2	434.8	420.5	406.1	391.7	377.5	363.2	349.0	334.7	346.2



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	516.9	507.1	497.8	488.4	479.1	470.0	460.7	451.5	442.4	433.2	438.7
115°	511.2	506.7	502.0	497.5	493.0	488.3	483.8	479.5	475.2	470.8	471.1
117.5°	471.7	469.8	468.1	466.3	464.6	463.0	461.5	460.1	458.6	457.3	454.2
120°	414.6	414.5	414.4	414.6	414.8	415.3	415.3	415.8	416.4	417.0	412.8
122.5°	358.6	359.0	359.6	360.2	361.0	361.9	362.8	363.9	365.2	366.4	362.2
125°	311.0	311.5	311.8	312.3	312.7	313.8	314.7	315.8	317.0	318.3	314.8
127.5°	278.7	278.1	277.6	277.4	277.2	277.4	277.7	278.0	278.7	279.4	277.1
130°	260.4	259.1	257.8	256.8	255.7	255.1	254.6	254.2	253.9	253.9	253.1
132.5°	252.9	251.0	249.2	247.6	246.0	244.9	243.5	242.8	241.9	241.5	241.3
135°	252.0	249.9	247.7	245.7	243.7	242.4	240.8	239.8	238.6	237.8	238.4
137.5°	254.4	252.4	250.1	248.2	246.2	244.8	243.2	242.0	241.1	240.3	241.0
140°	260.0	257.9	255.8	253.9	252.3	250.8	249.3	248.3	247.0	246.5	246.8
142.5°	264.8	263.3	261.2	259.7	257.9	256.6	255.4	254.5	253.3	252.9	253.4
145°	270.2	268.9	267.3	266.1	264.9	264.0	262.8	262.3	261.5	261.5	261.7
147.5°	274.8	273.9	272.6	271.8	270.6	270.1	269.3	268.9	268.5	268.3	268.5
150°	277.4	276.9	276.2	275.6	274.9	274.6	274.1	273.9	273.7	273.7	273.8
152.5°	279.0	278.7	278.0	277.7	277.1	277.1	276.7	276.7	276.6	276.6	276.6
155°	279.6	279.4	279.2	279.1	278.9	279.4	279.2	279.6	279.6	279.8	280.0
157.5°	281.5	281.7	281.6	282.0	282.1	282.5	282.6	283.1	283.2	283.8	284.2
160°	284.8	285.0	285.0	285.3	285.5	285.7	286.1	286.4	286.8	287.1	287.5
162.5°	287.9	288.5	288.6	289.0	289.4	289.8	290.3	291.0	291.3	292.0	292.5
165°	293.6	293.7	293.8	293.9	294.3	294.5	294.8	295.4	295.6	296.2	296.8
167.5°	299.0	299.2	299.2	299.4	299.7	300.0	300.3	300.9	301.3	302.1	302.5
170°	305.7	305.7	305.7	305.7	305.7	306.1	306.3	306.4	306.6	307.1	307.4
172.5°	312.7	312.7	312.3	312.7	312.3	312.7	312.7	312.9	312.9	313.0	313.1
175°	317.0	317.3	317.4	317.7	317.6	317.7	317.8	317.9	318.0	318.2	318.2
177.5°	320.8	321.0	321.0	321.0	321.0	321.2	321.2	321.2	321.2	321.0	321.1
180°	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2
2.5°	46201.4	46178.2	46201.9	46177.9	46201.9	46173.1	46192.6	46161.5	46169.5	46137.1	46145.4
5°	47948.3	47911.5	47931.1	47883.2	47888.3	47824.3	47823.2	47748.8	47729.2	47644.4	47607.2
7.5°	49360.9	49348.9	49355.7	49324.9	49321.3	49277.7	49256.9	49195.3	49156.6	49078.7	49025.4
10°	49137.3	49173.3	49182.7	49219.3	49227.0	49263.3	49270.9	49307.3	49314.9	49341.8	49342.1
12.5°	46900.8	47023.1	47052.3	47203.4	47267.0	47439.8	47532.5	47722.9	47836.0	48025.9	48142.6
15°	42592.3	42803.8	42888.2	43183.1	43346.3	43690.6	43906.9	44302.3	44581.3	45001.2	45300.7
17.5°	36662.4	36958.0	37091.4	37491.4	37752.3	38260.4	38626.8	39229.6	39691.2	40361.1	40892.2
20°	30086.5	30415.1	30596.2	31052.5	31360.4	31954.1	32411.4	33152.3	33770.1	34619.0	35345.0
22.5°	23724.9	24037.6	24238.6	24702.8	25049.6	25668.8	26179.9	26961.9	27654.0	28610.6	29481.1
25°	18216.3	18502.7	18684.5	19104.4	19430.0	19999.0	20487.1	21239.1	21916.4	22876.0	23768.6
27.5°	13926.1	14166.1	14341.3	14699.3	14986.5	15469.1	15888.3	16509.8	17093.4	17923.6	18718.4
30°	10661.6	10874.3	11044.8	11356.6	11622.8	12041.2	12409.8	12931.9	13414.9	14075.5	14707.7
32.5°	8147.2	8330.4	8482.2	8755.2	8996.7	9373.4	9705.6	10163.2	10577.7	11138.0	11658.2
35°	6212.0	6572.3	6546.8	6923.3	6983.8	7254.1	7550.4	7950.6	8317.7	8794.1	9236.8
37.5°	4821.5	4922.8	5031.4	5197.7	5372.7	5618.7	5869.0	6357.9	6537.1	6897.2	7263.7
40°	3888.0	3956.5	4028.2	4140.7	4263.1	4436.4	4618.8	4852.0	5090.9	5382.8	5680.9
42.5°	3287.0	3325.7	3371.4	3437.5	3513.0	3622.8	3744.7	3902.9	4069.1	4274.6	4484.3
45°	2936.7	2918.3	2931.8	2967.4	3012.9	3079.7	3156.6	3254.5	3362.8	3495.9	3637.5
47.5°	2610.2	2617.6	2621.7	2641.0	2665.4	2710.1	2756.8	2823.3	2951.6	2990.8	3068.0
50°	2394.6	2398.1	2397.0	2406.8	2419.1	2448.2	2478.5	2523.4	2568.4	2628.0	2684.8
52.5°	2213.9	2218.9	2218.2	2224.6	2231.2	2249.7	2268.8	2300.6	2330.0	2367.8	2400.6
55°	2071.1	2078.0	2080.7	2086.2	2089.4	2099.0	2106.7	2121.8	2134.4	2155.8	2175.6
57.5°	1961.3	1970.8	1975.2	1977.1	1973.2	1972.7	1970.1	1973.3	1975.9	1987.4	1998.6
60°	1875.0	1882.5	1883.7	1882.5	1875.4	1870.3	1862.2	1859.7	1858.4	1863.9	1870.1
62.5°	1784.4	1787.2	1785.3	1783.1	1775.0	1770.1	1761.6	1758.6	1755.7	1759.6	1762.9
65°	1659.3	1661.7	1659.3	1658.0	1650.7	1646.8	1639.7	1637.3	1633.3	1634.3	1633.6
67.5°	1557.7	1560.0	1558.2	1556.3	1551.3	1548.9	1543.6	1540.2	1535.3	1533.5	1530.1
70°	1456.4	1458.3	1455.4	1453.5	1447.7	1445.5	1440.6	1439.6	1435.7	1434.9	1431.0
72.5°	1339.8	1340.0	1336.0	1334.7	1330.6	1330.4	1328.3	1330.2	1330.0	1332.1	1331.3
75°	1220.7	1219.0	1213.9	1213.0	1209.8	1211.3	1209.1	1212.0	1212.4	1216.8	1217.3
77.5°	1101.3	1095.0	1085.3	1080.8	1074.4	1073.6	1069.8	1072.3	1071.5	1076.6	1078.5
80°	950.4	942.8	930.4	924.6	916.9	915.7	912.3	915.7	914.0	919.9	924.2
82.5°	758.8	752.2	739.4	734.7	725.8	726.6	723.0	726.6	726.2	734.9	740.0
85°	561.2	556.9	543.7	532.0	519.0	511.4	503.9	502.6	500.4	503.9	507.0
87.5°	324.2	320.1	309.8	303.1	280.2	281.2	272.2	271.8	269.6	267.5	272.2
90°	42.2	47.6	45.4	50.2	48.7	54.4	53.5	58.7	56.8	61.5	60.6
92.5°	22.0	23.1	24.1	25.1	26.2	27.3	28.3	29.4	31.7	33.6	36.3
95°	28.7	29.9	31.1	32.3	33.6	34.8	36.0	37.2	40.6	43.9	47.3
97.5°	38.9	39.7	40.5	41.3	42.1	43.0	43.8	44.6	48.3	52.0	55.5
100°	48.7	49.4	50.0	50.7	51.3	52.0	52.7	53.3	60.6	67.5	74.5
102.5°	73.7	76.5	79.3	82.1	85.0	87.9	90.6	93.4	109.5	125.5	141.4
105°	132.1	139.6	147.5	155.1	162.7	170.3	178.1	185.7	211.5	237.0	262.9
107.5°	237.0	249.1	261.1	273.3	285.3	297.6	309.6	321.8	346.7	372.0	397.1
110°	357.6	369.3	380.7	392.4	403.8	415.4	427.0	438.9	454.0	469.1	484.4



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	444.4	449.9	455.7	461.4	467.2	473.1	478.9	484.8	492.6	500.3	508.2
115°	471.5	471.9	472.6	473.0	473.7	474.3	475.2	475.9	478.8	481.6	484.4
117.5°	451.3	448.3	445.6	442.7	440.0	437.5	434.9	432.5	432.5	432.5	432.8
120°	409.1	405.2	401.3	397.3	393.8	390.1	386.8	383.5	382.2	380.9	379.9
122.5°	358.4	354.6	350.8	347.3	343.8	340.4	337.2	334.1	333.6	333.0	332.7
125°	311.6	308.7	305.7	302.8	300.3	297.8	295.4	293.2	294.1	294.9	296.1
127.5°	275.5	273.8	272.2	270.9	269.8	268.7	267.9	266.8	269.0	271.0	273.2
130°	252.5	252.2	252.1	251.7	252.2	252.3	252.5	252.8	255.8	258.3	261.4
132.5°	241.9	242.2	242.8	243.6	244.6	245.6	247.0	248.0	251.1	254.0	257.1
135°	239.0	239.8	241.1	242.0	243.6	245.0	246.8	248.2	251.4	254.0	257.2
137.5°	241.9	242.8	244.1	245.3	247.1	248.5	250.5	252.1	254.6	257.1	259.6
140°	247.9	248.4	249.9	251.0	252.4	253.7	255.6	256.9	259.3	261.3	263.3
142.5°	254.4	255.0	256.1	257.3	258.6	259.8	261.3	262.5	264.3	265.8	268.0
145°	262.5	263.1	264.2	264.9	266.1	267.2	268.4	269.6	271.0	272.1	273.5
147.5°	269.1	269.7	270.5	271.4	272.3	273.2	274.0	274.9	276.2	277.1	278.2
150°	274.3	274.7	275.4	275.8	276.8	277.5	278.5	279.0	280.0	280.7	281.9
152.5°	277.4	277.7	278.2	278.7	279.6	280.1	280.7	281.4	282.4	282.9	283.9
155°	280.5	281.2	281.9	282.4	283.2	283.6	284.5	284.9	285.8	286.4	287.3
157.5°	284.8	285.2	286.1	286.3	287.2	287.7	288.4	288.9	289.7	290.2	291.0
160°	288.3	289.1	289.6	290.3	291.1	291.7	292.5	293.2	293.9	294.4	295.1
162.5°	293.2	293.9	294.5	295.1	295.8	296.4	296.9	297.6	298.5	299.0	299.9
165°	297.6	298.2	299.1	299.5	300.5	301.2	301.8	302.6	303.1	303.8	304.2
167.5°	303.3	303.7	304.7	305.1	305.9	306.6	307.3	307.9	308.5	308.9	309.6
170°	308.0	308.5	309.1	309.7	310.2	310.7	311.5	311.9	312.6	313.1	313.9
172.5°	313.5	313.9	314.4	314.6	315.0	315.6	316.0	316.3	316.9	317.2	317.7
175°	318.2	318.2	318.4	318.6	318.8	318.8	318.9	319.3	319.5	319.6	319.7
177.5°	321.2	321.3	321.3	321.4	321.5	321.6	321.7	321.8	321.8	321.8	321.8
180°	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2
2.5°	46113.2	46115.1	46078.0	46075.9	46041.1	46036.7	46002.7	45992.4	45964.8	45954.8	45926.7
5°	47512.2	47466.9	47362.2	47300.6	47197.1	47128.6	47016.7	46943.6	46835.6	46754.1	46645.3
7.5°	48927.1	48856.8	48739.3	48644.0	48500.4	48385.8	48217.9	48080.3	47898.3	47740.8	47549.7
10°	49342.1	49331.3	49301.4	49257.7	49191.0	49115.9	49001.5	48882.3	48722.9	48549.7	48337.3
12.5°	48321.0	48431.3	48581.6	48670.7	48779.2	48826.7	48871.1	48860.0	48830.8	48743.2	48620.4
15°	45734.5	46044.3	46454.6	46772.5	47138.2	47404.2	47697.7	47880.6	48063.1	48147.4	48199.0
17.5°	41619.9	42206.5	42942.1	43551.8	44255.1	44820.1	45439.4	45905.6	46385.0	46728.5	47039.1
20°	36334.6	37184.6	38225.0	39144.1	40212.8	41141.6	42159.4	42994.9	43856.5	44530.2	45167.9
22.5°	30602.0	31611.4	32869.2	34034.4	35412.1	36650.3	38047.4	39263.3	40532.8	41593.5	42618.9
25°	24964.8	26071.8	27447.2	28747.2	30307.6	31747.8	33404.6	34920.0	36560.9	37985.5	39392.8
27.5°	19817.2	20904.1	22308.2	23692.1	25342.1	26876.8	28651.9	30321.5	32189.9	33912.8	35675.2
30°	15586.5	16508.3	17767.3	19107.6	20735.0	22296.7	24091.1	25808.4	27751.9	29633.1	31618.3
32.5°	12348.6	13050.9	14040.8	15174.1	16675.7	18162.3	19871.0	21528.7	23442.7	25342.9	27407.6
35°	9807.1	10354.9	11109.6	11994.0	13265.6	14547.0	16058.4	17565.9	19351.5	21154.8	23161.6
37.5°	7733.4	8177.9	8768.9	9433.3	10453.2	11505.0	12744.2	13993.9	15545.5	17143.9	18962.7
40°	6039.0	6398.8	6858.9	7354.5	8124.6	8935.0	9893.3	10862.5	12109.0	13415.4	14920.6
42.5°	4744.1	5009.5	5334.6	5696.7	6415.2	6845.5	7495.3	8196.3	9112.7	10061.1	11192.8
45°	3809.9	3991.1	4216.4	4459.3	4792.7	5157.7	5602.8	6069.5	6940.1	7367.1	8055.5
47.5°	3181.6	3303.3	3446.7	3599.7	3796.3	4008.6	4272.6	4542.5	4891.6	5253.3	5677.4
50°	2758.5	2882.1	2931.4	3010.7	3124.5	3245.7	3394.5	3543.3	3730.6	3920.3	4138.6
52.5°	2444.5	2484.8	2538.3	2588.8	2659.2	2797.3	2841.9	2919.7	3024.7	3127.4	3242.1
55°	2204.7	2230.9	2265.7	2296.2	2338.8	2379.5	2438.4	2490.2	2560.2	2622.1	2698.2
57.5°	2018.0	2034.7	2058.9	2078.8	2106.5	2129.5	2164.0	2192.0	2232.3	2267.2	2313.4
60°	1882.4	1893.5	1909.8	1922.8	1940.4	1952.4	1969.5	1982.7	2004.0	2021.7	2047.4
62.5°	1771.6	1777.4	1788.0	1795.6	1806.8	1812.8	1822.0	1827.7	1839.4	1848.4	1862.7
65°	1638.7	1640.1	1647.2	1650.4	1659.1	1662.3	1669.8	1672.5	1682.1	1688.7	1701.5
67.5°	1529.8	1526.7	1526.9	1524.4	1525.5	1523.0	1523.7	1521.0	1524.8	1526.9	1536.5
70°	1430.4	1426.1	1424.8	1420.2	1418.9	1414.1	1412.7	1408.5	1408.0	1406.7	1410.0
72.5°	1333.4	1332.3	1332.6	1329.4	1329.0	1325.8	1326.0	1324.0	1326.2	1327.2	1331.5
75°	1222.0	1222.4	1224.5	1221.7	1222.5	1219.8	1220.8	1218.3	1219.6	1219.1	1223.5
77.5°	1086.4	1089.6	1095.5	1094.3	1096.2	1093.2	1094.5	1090.9	1091.9	1089.6	1091.3
80°	933.8	940.6	948.5	948.2	951.6	949.4	952.4	949.1	950.4	946.3	945.3
82.5°	752.7	758.4	766.9	767.3	774.7	776.1	784.3	784.0	789.3	785.9	783.5
85°	514.6	518.5	526.0	530.0	537.6	542.3	550.3	553.5	547.8	558.2	549.9
87.5°	268.7	278.7	273.1	286.1	283.1	296.3	293.4	305.6	303.3	313.7	312.3
90°	67.2	66.9	73.9	74.1	82.8	84.0	90.7	89.0	95.4	94.0	100.4
92.5°	38.2	40.8	43.1	45.4	47.7	50.1	47.9	45.7	43.7	41.6	39.4
95°	50.7	54.0	57.4	60.8	64.1	67.5	63.9	60.4	56.9	53.2	49.6
97.5°	59.2	62.7	66.4	70.0	73.8	77.4	73.1	68.8	64.6	60.5	56.2
100°	81.5	88.7	95.6	102.6	109.7	116.7	108.9	101.0	93.2	85.3	77.3
102.5°	157.7	173.8	189.8	205.9	221.9	238.0	221.4	204.9	187.9	171.3	154.4
105°	288.6	314.3	340.0	365.7	391.3	417.4	390.2	363.1	336.0	309.0	281.6
107.5°	422.3	447.4	472.7	497.8	523.0	548.4	521.0	493.4	466.2	438.5	411.0
110°	499.8	515.1	530.4	545.9	561.2	576.7	556.7	536.9	517.0	497.0	477.0



TEST NUMBER: P1444707

CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	516.1	524.3	532.0	540.2	548.1	556.2	542.1	528.2	514.0	500.0	485.8
115°	487.5	490.3	493.4	496.5	499.4	502.4	493.2	484.0	474.7	465.5	455.9
117.5°	433.1	433.5	433.5	434.3	434.3	434.7	429.9	425.1	420.1	415.1	410.1
120°	378.6	377.4	376.2	375.3	373.9	372.7	371.2	369.6	367.8	366.0	364.2
122.5°	332.1	331.9	331.4	331.0	330.3	329.8	329.6	329.7	329.4	329.3	328.8
125°	297.0	298.0	299.0	300.0	300.8	301.7	302.0	302.5	302.7	303.2	303.3
127.5°	275.0	277.2	279.0	281.1	282.8	284.8	285.3	286.3	286.9	287.7	288.3
130°	263.9	266.8	269.4	271.9	274.2	277.1	277.5	278.3	278.9	279.5	280.1
132.5°	260.0	262.9	265.7	268.9	271.4	274.1	274.6	275.5	275.7	276.6	277.1
135°	259.9	262.6	265.1	268.1	270.5	273.1	273.6	274.2	274.5	275.3	275.7
137.5°	261.7	264.4	266.6	268.9	270.9	273.2	273.6	274.2	274.4	275.2	275.5
140°	265.3	267.4	269.1	271.2	273.0	274.9	275.1	275.5	275.6	276.0	276.1
142.5°	269.6	271.2	272.6	274.4	275.7	277.3	277.1	277.1	277.1	277.1	277.1
145°	274.7	276.1	277.2	278.5	279.2	280.6	280.3	280.2	279.6	279.6	279.3
147.5°	279.1	280.2	280.8	281.9	282.3	283.4	282.9	282.6	282.3	281.9	281.3
150°	282.4	283.5	284.0	284.8	285.4	286.3	285.7	285.3	284.6	284.1	283.6
152.5°	284.6	285.3	286.0	286.5	287.1	287.7	287.0	286.8	286.1	285.3	284.7
155°	287.7	288.5	288.8	289.5	289.7	290.2	289.4	289.3	288.6	288.1	287.4
157.5°	291.4	292.1	292.7	292.9	293.3	293.8	293.5	293.2	292.7	292.3	291.8
160°	295.6	296.1	296.6	296.9	297.5	297.6	297.3	297.3	296.9	296.5	295.9
162.5°	300.3	301.0	301.4	301.8	302.5	302.9	302.5	302.2	301.8	301.5	300.8
165°	304.8	305.3	305.8	306.3	306.5	307.0	306.7	306.7	306.3	306.1	305.7
167.5°	309.9	310.6	310.9	311.5	311.6	311.9	311.6	311.8	311.4	311.2	310.7
170°	314.0	314.4	315.0	315.5	315.7	316.0	315.9	315.8	315.5	315.3	315.0
172.5°	318.1	318.5	318.6	319.0	319.1	319.5	319.3	319.0	318.8	318.5	318.2
175°	319.7	319.9	320.3	320.3	320.3	320.5	320.2	319.9	319.7	319.5	319.2
177.5°	321.8	321.8	321.8	321.6	321.6	321.6	321.4	321.3	321.1	320.9	320.6
180°	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2	45630.2
2.5°	45916.8	45896.8	45884.0	45867.6	45857.6	45844.9	45835.6	45827.6	45821.2	45815.3	45810.9
5°	46562.5	46459.8	46380.1	46293.9	46223.0	46152.4	46097.9	46052.7	46021.6	45998.3	45984.4
7.5°	47384.5	47196.6	47029.5	46853.7	46696.1	46541.0	46407.4	46292.2	46205.8	46149.8	46115.8
10°	48118.6	47867.1	47618.4	47356.6	47108.4	46867.5	46645.3	46449.8	46295.1	46192.3	46132.2
12.5°	48447.7	48233.4	47979.5	47695.2	47391.0	47083.2	46783.1	46512.6	46285.4	46133.1	46045.2
15°	48157.9	48069.9	47897.6	47676.9	47388.2	47070.0	46717.7	46386.6	46082.0	45884.5	45770.0
17.5°	47215.1	47337.9	47324.7	47240.3	47032.7	46764.8	46405.9	46033.9	45653.0	45389.0	45244.7
20°	45624.0	46010.0	46205.8	46306.3	46224.7	46051.0	45726.0	45348.6	44904.5	44559.8	44349.5
22.5°	43388.2	44069.6	44494.2	44804.9	44870.8	44811.6	44524.7	44165.7	43670.6	43256.3	42945.7
25°	40509.9	41508.2	42179.2	42705.4	42909.7	42962.4	42718.2	42361.2	41809.4	41326.8	40900.1
27.5°	37119.8	38416.9	39312.9	40019.7	40338.8	40477.1	40252.4	39888.2	39235.3	38659.2	38101.8
30°	33303.1	34842.0	35920.8	36768.4	37157.4	37340.2	37101.4	36694.8	35935.2	35241.8	34539.7
32.5°	29218.1	30902.1	32077.6	32998.1	33383.5	33555.5	33243.1	32786.5	31908.5	31091.7	30272.9
35°	24941.1	26640.9	27826.4	28722.3	29045.3	29149.0	28749.5	28221.8	27249.0	26352.5	25459.7
37.5°	20577.0	22158.4	23235.8	24039.9	24239.8	24257.8	23776.5	23193.5	22171.1	21287.2	20398.3
40°	16250.7	17584.3	18454.2	19097.8	19167.2	19105.3	18582.0	17995.4	17038.9	16247.0	15466.7
42.5°	12175.5	13182.2	13802.9	14243.9	14217.7	14095.4	13615.6	13111.3	12322.2	11719.0	11105.0
45°	8684.2	9348.0	9710.8	9968.9	9886.0	9769.6	9396.2	9042.7	8506.5	8116.9	7704.2
47.5°	6033.0	6825.7	6687.6	7192.3	6757.5	7044.6	6446.7	6117.0	5832.4	5625.5	5392.3
50°	4319.1	4500.7	4588.5	4648.4	4616.5	4572.4	4465.1	4369.0	4239.0	4144.2	4033.8
52.5°	3335.5	3426.3	3476.1	3512.1	3505.0	3488.9	3442.1	3399.3	3338.4	3298.4	3250.0
55°	2825.4	2826.7	2918.2	2878.9	2936.9	2868.9	2895.7	2820.5	2832.6	2768.0	2724.6
57.5°	2347.8	2385.0	2401.7	2417.9	2413.4	2410.5	2392.4	2383.3	2362.9	2356.5	2342.0
60°	2065.2	2084.6	2088.7	2096.1	2089.9	2087.5	2073.3	2068.2	2054.5	2052.0	2042.3
62.5°	1871.4	1881.4	1881.4	1881.4	1873.3	1865.4	1849.7	1841.5	1829.8	1827.3	1821.7
65°	1709.7	1720.0	1721.7	1723.9	1718.0	1711.9	1698.1	1689.1	1677.0	1672.5	1666.1
67.5°	1542.8	1553.8	1557.5	1563.1	1559.7	1558.5	1549.1	1545.5	1537.6	1535.7	1529.8
70°	1411.7	1416.3	1415.9	1415.8	1408.4	1401.8	1390.8	1385.5	1377.3	1375.6	1370.1
72.5°	1333.8	1337.0	1334.9	1332.1	1322.5	1312.6	1299.8	1290.3	1279.5	1272.7	1265.2
75°	1224.0	1228.3	1225.6	1223.7	1215.1	1208.7	1198.3	1193.1	1185.5	1183.3	1178.0
77.5°	1089.2	1091.3	1086.8	1086.4	1079.8	1075.7	1067.9	1066.6	1061.0	1061.2	1056.1
80°	939.3	938.0	931.0	929.6	923.0	921.3	915.2	915.6	911.2	913.1	909.5
82.5°	772.8	768.6	759.3	756.6	749.0	748.3	744.3	747.7	744.9	749.0	746.6
85°	553.8	555.0	551.0	551.0	548.8	549.5	549.1	551.6	552.0	555.7	555.5
87.5°	308.8	313.2	312.3	316.4	316.3	320.8	322.3	329.1	329.9	336.2	336.2
90°	99.0	106.1	104.5	111.7	111.5	118.9	119.8	127.2	127.2	133.6	132.3
92.5°	37.2	35.2	33.2	30.9	29.9	28.4	28.0	26.3	25.6	24.1	23.1
95°	46.0	42.4	38.8	35.2	34.0	32.5	31.4	30.1	28.9	27.6	26.5
97.5°	52.0	47.8	43.5	39.2	38.1	37.1	35.8	34.8	33.7	32.6	31.5
100°	69.3	61.4	53.6	45.5	44.6	43.8	42.9	42.0	41.0	39.9	39.0
102.5°	137.8	120.8	104.0	87.2	83.9	80.7	77.6	74.2	71.0	67.8	64.7
105°	254.4	227.2	199.9	172.5	163.9	155.1	146.5	137.8	129.0	120.4	111.7
107.5°	383.4	355.7	328.0	300.3	284.5	268.4	252.4	236.2	220.3	204.1	188.0
110°	457.1	437.0	416.9	396.6	384.0	371.1	358.1	345.2	332.4	319.3	306.4



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	471.6	457.4	443.1	428.5	423.0	417.1	411.6	405.7	399.9	393.9	388.2
115°	446.5	437.1	427.6	417.9	416.2	414.2	412.5	410.4	408.6	406.4	404.4
117.5°	405.1	400.0	394.8	389.7	390.3	390.9	391.6	392.0	392.5	392.7	393.1
120°	362.3	360.5	358.8	356.7	359.0	361.1	363.3	365.1	367.1	368.8	370.5
122.5°	328.7	328.2	328.1	327.4	330.3	332.8	335.3	337.8	340.1	342.1	344.2
125°	303.8	303.9	304.1	304.1	307.1	309.8	312.3	314.7	317.2	319.1	321.3
127.5°	289.1	289.6	290.4	290.9	293.4	295.1	297.3	299.0	300.9	302.3	303.7
130°	280.7	281.2	281.9	282.4	284.5	286.5	288.7	290.2	291.9	293.1	294.4
132.5°	277.8	278.2	278.8	279.2	281.2	282.7	284.5	285.5	286.9	287.7	288.6
135°	276.3	276.6	277.2	277.5	279.3	281.1	282.5	283.6	285.1	285.7	286.5
137.5°	276.2	276.3	276.9	277.1	278.8	280.4	281.7	282.8	283.9	284.9	285.4
140°	276.6	276.5	277.1	277.1	278.7	280.0	281.4	282.3	283.6	284.0	284.7
142.5°	277.1	276.8	277.1	276.8	278.0	279.0	280.0	280.9	281.7	282.1	282.5
145°	279.0	278.5	278.5	278.0	279.0	279.7	280.6	281.4	281.9	282.1	282.5
147.5°	281.2	280.6	280.1	279.6	280.7	281.2	281.7	282.0	282.7	282.8	283.0
150°	283.0	282.2	281.5	280.9	281.4	281.8	282.1	282.7	282.8	282.9	283.1
152.5°	284.0	283.3	282.6	281.7	282.0	282.1	282.3	282.4	282.5	282.5	282.5
155°	286.9	286.1	285.3	284.5	284.8	284.8	284.8	284.8	284.5	284.4	284.3
157.5°	291.1	290.3	290.0	289.2	289.1	289.0	288.9	288.3	288.1	287.7	287.3
160°	295.7	295.0	294.5	293.8	293.6	293.4	293.3	292.7	292.4	291.8	291.4
162.5°	300.3	299.8	299.0	298.3	298.1	298.0	297.7	297.1	296.7	296.2	295.8
165°	305.5	304.9	304.5	303.8	303.6	303.3	303.1	302.4	302.1	301.4	300.8
167.5°	310.4	309.9	309.4	308.6	308.5	308.4	308.2	307.8	307.4	306.8	306.6
170°	314.7	314.1	313.9	313.3	313.1	312.9	312.5	312.2	311.6	311.4	310.8
172.5°	317.7	317.3	316.9	316.3	316.3	316.1	315.7	315.6	315.0	314.7	314.6
175°	318.8	318.6	318.0	317.7	317.5	317.3	317.2	317.1	316.7	316.5	316.2
177.5°	320.5	320.3	319.8	319.7	319.5	319.5	319.3	319.1	319.1	318.9	318.8
180°	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4	320.4



TEST NUMBER: P1444707
 CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	45630.2	45630.2
2.5°	45806.9	45804.5
5°	45977.2	45974.4
7.5°	46106.7	46105.9
10°	46121.9	46129.8
12.5°	46029.9	46036.3
15°	45761.2	45773.7
17.5°	45247.4	45263.8
20°	44362.3	44379.4
22.5°	42928.9	42936.1
25°	40845.0	40815.4
27.5°	38003.9	37953.0
30°	34392.2	34343.0
32.5°	30086.2	30055.4
35°	25238.9	25219.5
37.5°	20135.6	20096.1
40°	15181.4	15066.0
42.5°	10836.1	10633.7
45°	7488.7	7248.8
47.5°	5227.9	5079.6
50°	3962.6	3914.8
52.5°	3228.9	3217.6
55°	2724.4	2719.5
57.5°	2345.2	2343.5
60°	2047.4	2046.9
62.5°	1825.4	1826.2
65°	1668.9	1669.3
67.5°	1531.3	1530.3
70°	1372.2	1371.0
72.5°	1262.6	1260.7
75°	1178.0	1176.8
77.5°	1057.6	1055.7
80°	911.8	909.5
82.5°	750.0	747.3
85°	559.5	559.5
87.5°	342.3	342.1
90°	138.3	136.2
92.5°	22.4	21.6
95°	25.2	24.0
97.5°	30.5	29.4
100°	38.1	37.2
102.5°	61.5	58.3
105°	103.0	94.4
107.5°	172.0	155.9
110°	293.5	280.5



TEST NUMBER: P1444707
CATALOG NUMBER: EHBR1-60-UNV-TA-L930-UPL15

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	382.1	376.2
115°	401.9	399.8
117.5°	393.2	393.3
120°	371.9	373.5
122.5°	345.9	347.6
125°	322.9	324.6
127.5°	304.7	305.7
130°	295.0	295.9
132.5°	289.0	289.2
135°	286.7	286.9
137.5°	285.5	285.7
140°	284.6	284.8
142.5°	282.7	282.7
145°	282.6	282.5
147.5°	282.5	282.5
150°	282.8	282.6
152.5°	282.0	281.8
155°	283.7	283.4
157.5°	286.5	286.1
160°	290.7	290.2
162.5°	295.1	294.6
165°	300.0	299.3
167.5°	305.8	305.6
170°	310.3	309.9
172.5°	314.0	313.7
175°	316.0	315.8
177.5°	318.8	318.4
180°	320.4	320.4

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-5

Test Date: 08/01/2025

Luminaire Tested: EHBR-60-L930-N

Data in this report applies to families of products including EHBR-60-L930-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-5
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L930-N**
 Description: Elevate Round Highbay at, 60000 lumens, 3000K 90CRI LEDs with N lens

Spectral Parameters

CCT (K): 2996
 CIE u': 0.2519
 CIE v': 0.5169
 Duv: -0.0033
 CIE x: 0.4325
 CIE y: 0.3945
 CIE z: 0.1730
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 584
 Purity: 48.21818
 Rf: 91.3
 Rg: 102

CRI (Ra):	94.4		
R1:	96.8	R9:	61.4
R2:	98.1	R10:	94.4
R3:	97.8	R11:	95.7
R4:	95.6	R12:	88.5
R5:	96.9	R13:	97.3
R6:	95.7	R14:	97.8
R7:	90.9	R15:	92.3
R8:	83.0		



Test Conditions

Stabilization Time: 40M
 Operation Time: 1H 40M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-5


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-5

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 7-step quadrangle

REPORT NUMBER: SP1-2506-472-5

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	101	NR	620	317	NR	750	7	NR	880	0	NR
365	0	NR	495	121	NR	625	320	NR	755	6	NR	885	0	NR
370	0	NR	500	141	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	158	NR	635	651	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	207	NR	770	4	NR	900	0	NR
385	0	NR	515	182	NR	645	201	NR	775	3	NR	905	0	NR
390	0	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	146	NR	785	2	NR	915	0	NR
400	1	NR	530	199	NR	660	124	NR	790	2	NR	920	0	NR
405	3	NR	535	205	NR	665	105	NR	795	2	NR	925	0	NR
410	4	NR	540	210	NR	670	96	NR	800	1	NR	930	0	NR
415	7	NR	545	216	NR	675	79	NR	805	1	NR	935	0	NR
420	13	NR	550	222	NR	680	67	NR	810	1	NR	940	0	NR
425	22	NR	555	230	NR	685	58	NR	815	1	NR	945	0	NR
430	37	NR	560	240	NR	690	49	NR	820	1	NR	950	0	NR
435	60	NR	565	248	NR	695	42	NR	825	1	NR	955	0	NR
440	101	NR	570	258	NR	700	36	NR	830	1	NR	960	0	NR
445	172	NR	575	268	NR	705	30	NR	835	1	NR	965	0	NR
450	223	NR	580	278	NR	710	26	NR	840	1	NR	970	0	NR
455	167	NR	585	287	NR	715	22	NR	845	0	NR	975	0	NR
460	126	NR	590	295	NR	720	19	NR	850	0	NR	980	0	NR
465	111	NR	595	298	NR	725	16	NR	855	0	NR	985	0	NR
470	86	NR	600	303	NR	730	14	NR	860	0	NR	990	0	NR
475	74	NR	605	307	NR	735	12	NR	865	0	NR	995	0	NR
480	77	NR	610	341	NR	740	10	NR	870	0	NR	1000	0	NR
485	86	NR	615	368	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-5

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.44

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	101	NR	620	317	NR	750	7	NR	880	0	NR
365	0	NR	495	121	NR	625	320	NR	755	6	NR	885	0	NR
370	0	NR	500	141	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	158	NR	635	651	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	207	NR	770	4	NR	900	0	NR
385	0	NR	515	182	NR	645	201	NR	775	3	NR	905	0	NR
390	0	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	146	NR	785	2	NR	915	0	NR
400	1	NR	530	199	NR	660	124	NR	790	2	NR	920	0	NR
405	3	NR	535	205	NR	665	105	NR	795	2	NR	925	0	NR
410	4	NR	540	210	NR	670	96	NR	800	1	NR	930	0	NR
415	7	NR	545	216	NR	675	79	NR	805	1	NR	935	0	NR
420	13	NR	550	222	NR	680	67	NR	810	1	NR	940	0	NR
425	22	NR	555	230	NR	685	58	NR	815	1	NR	945	0	NR
430	37	NR	560	240	NR	690	49	NR	820	1	NR	950	0	NR
435	60	NR	565	248	NR	695	42	NR	825	1	NR	955	0	NR
440	101	NR	570	258	NR	700	36	NR	830	1	NR	960	0	NR
445	172	NR	575	268	NR	705	30	NR	835	1	NR	965	0	NR
450	223	NR	580	278	NR	710	26	NR	840	1	NR	970	0	NR
455	167	NR	585	287	NR	715	22	NR	845	0	NR	975	0	NR
460	126	NR	590	295	NR	720	19	NR	850	0	NR	980	0	NR
465	111	NR	595	298	NR	725	16	NR	855	0	NR	985	0	NR
470	86	NR	600	303	NR	730	14	NR	860	0	NR	990	0	NR
475	74	NR	605	307	NR	735	12	NR	865	0	NR	995	0	NR
480	77	NR	610	341	NR	740	10	NR	870	0	NR	1000	0	NR
485	86	NR	615	368	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-5

Melanopic Flux vs. Wavelength




Melanopic Lumens: NR

M/P: 2.85





λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	101	NR	620	317	NR	750	7	NR	880	0	NR
365	0	NR	495	121	NR	625	320	NR	755	6	NR	885	0	NR
370	0	NR	500	141	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	158	NR	635	651	NR	765	4	NR	895	0	NR
380	0	NR	510	171	NR	640	207	NR	770	4	NR	900	0	NR
385	0	NR	515	182	NR	645	201	NR	775	3	NR	905	0	NR
390	0	NR	520	189	NR	650	174	NR	780	3	NR	910	0	NR
395	1	NR	525	194	NR	655	146	NR	785	2	NR	915	0	NR
400	1	NR	530	199	NR	660	124	NR	790	2	NR	920	0	NR
405	3	NR	535	205	NR	665	105	NR	795	2	NR	925	0	NR
410	4	NR	540	210	NR	670	96	NR	800	1	NR	930	0	NR
415	7	NR	545	216	NR	675	79	NR	805	1	NR	935	0	NR
420	13	NR	550	222	NR	680	67	NR	810	1	NR	940	0	NR
425	22	NR	555	230	NR	685	58	NR	815	1	NR	945	0	NR
430	37	NR	560	240	NR	690	49	NR	820	1	NR	950	0	NR
435	60	NR	565	248	NR	695	42	NR	825	1	NR	955	0	NR
440	101	NR	570	258	NR	700	36	NR	830	1	NR	960	0	NR
445	172	NR	575	268	NR	705	30	NR	835	1	NR	965	0	NR
450	223	NR	580	278	NR	710	26	NR	840	1	NR	970	0	NR
455	167	NR	585	287	NR	715	22	NR	845	0	NR	975	0	NR
460	126	NR	590	295	NR	720	19	NR	850	0	NR	980	0	NR
465	111	NR	595	298	NR	725	16	NR	855	0	NR	985	0	NR
470	86	NR	600	303	NR	730	14	NR	860	0	NR	990	0	NR
475	74	NR	605	307	NR	735	12	NR	865	0	NR	995	0	NR
480	77	NR	610	341	NR	740	10	NR	870	0	NR	1000	0	NR
485	86	NR	615	368	NR	745	8	NR	875	0	NR			

Summary

$R_f = 91.3$
 $R_g = 102$
 $CIE R_a = 94.4$
 $R_9 = 61.4$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 86	CES26 = 91	CES51 = 96	CES76 = 89
CES02 = 63	CES27 = 96	CES52 = 95	CES77 = 85
CES03 = 32	CES28 = 96	CES53 = 93	CES78 = 86
CES04 = 70	CES29 = 90	CES54 = 98	CES79 = 89
CES05 = 51	CES30 = 96	CES55 = 98	CES80 = 91
CES06 = 51	CES31 = 90	CES56 = 95	CES81 = 72
CES07 = 44	CES32 = 84	CES57 = 95	CES82 = 95
CES08 = 42	CES33 = 91	CES58 = 95	CES83 = 93
CES09 = 29	CES34 = 92	CES59 = 99	CES84 = 96
CES10 = 76	CES35 = 96	CES60 = 96	CES85 = 80
CES11 = 59	CES36 = 90	CES61 = 96	CES86 = 77
CES12 = 65	CES37 = 94	CES62 = 95	CES87 = 91
CES13 = 44	CES38 = 99	CES63 = 94	CES88 = 96
CES14 = 74	CES39 = 97	CES64 = 96	CES89 = 82
CES15 = 72	CES40 = 94	CES65 = 92	CES90 = 97
CES16 = 48	CES41 = 94	CES66 = 95	CES91 = 82
CES17 = 50	CES42 = 91	CES67 = 94	CES92 = 78
CES18 = 57	CES43 = 88	CES68 = 93	CES93 = 87
CES19 = 72	CES44 = 99	CES69 = 94	CES94 = 73
CES20 = 67	CES45 = 93	CES70 = 90	CES95 = 85
CES21 = 86	CES46 = 93	CES71 = 90	CES96 = 92
CES22 = 79	CES47 = 86	CES72 = 96	CES97 = 93
CES23 = 92	CES48 = 95	CES73 = 85	CES98 = 94
CES24 = 91	CES49 = 91	CES74 = 90	CES99 = 93
CES25 = 72	CES50 = 96	CES75 = 90	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)