

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1433938

Luminaire Tested: EHBR1-54-UNV-TASM-L940

Issue Date: 3/13/2026

Test Information

Test Method: LM-79-2019
Report Number: P1433938
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2601-654-4)
Test Lab: INNOVATION CENTER
Issue Date: 3/13/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-54-UNV-TASM-L940
Description: Elevate Round Highbay at, 54000 lumens, 4000K 90CRI LEDs with TASM lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 50067.5 lumens
Efficiency: N/A
Efficacy: 169.1 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.84 / 0.9
Luminous Opening: Circular (Dia: 1.71' x H: 0')
CIE Type: Direct

Input Watts (W): 296
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1433938
CATALOG NUMBER: EHBR1-54-UNV-TASM-L940

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°



TEST NUMBER: P1433938
 CATALOG NUMBER: EHBR1-54-UNV-TASM-L940

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	112	108	105	103	109	106	104	101	102	100	98	98	97	95	95	93	92	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74	74	74
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	72	69	67	67	67
5	87	78	71	66	86	77	70	65	75	69	65	73	68	64	71	67	64	62	62	62
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	57	57	57
7	78	67	60	56	76	67	60	56	65	59	55	64	59	55	63	58	55	53	53	53
8	74	63	56	52	72	62	56	52	61	55	51	60	55	51	59	54	51	49	49	49
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46	46	46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	210277	210277	210277	210277
5°	210360	224415	210360	199444
10°	209141	231691	209141	189999
15°	204335	216764	204335	176690
20°	192445	175035	192445	158486
25°	171594	122175	171594	133804
30°	140442	80120	140442	100913
35°	101614	52342	101614	67770
40°	66343	36432	66343	43160
45°	42569	28540	42569	31098
50°	32033	24574	32033	26248
55°	26576	22748	26576	23545
60°	23484	22113	23484	22246
65°	21990	21907	21990	21814
70°	21650	22297	21650	22009
75°	21481	22884	21481	22196
80°	21002	24047	21002	22479
85°	17689	22350	17689	21310

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 59850 cd/sqm



TEST NUMBER: P1433938
 CATALOG NUMBER: EHBR1-54-UNV-TASM-L940

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	4257.6	8.5
10°-20°	11583.1	23.1
20°-30°	13584.6	27.1
30°-40°	9447.2	18.9
40°-50°	4694.8	9.4
50°-60°	2808.0	5.6
60°-70°	1976.4	3.9
70°-80°	1273.1	2.5
80°-90°	404.4	0.8
90°-100°	2.3	0.0
100°-110°	2.8	0.0
110°-120°	2.9	0.0
120°-130°	3.6	0.0
130°-140°	4.9	0.0
140°-150°	5.9	0.0
150°-160°	6.6	0.0
160°-170°	6.4	0.0
170°-180°	2.8	0.0
0°-30°	29425.3	58.8
0°-40°	38872.6	77.6
0°-60°	46375.4	92.6
0°-90°	50029.4	99.9
90°-120°	8.0	0.0
90°-150°	22.4	0.0
90°-180°	38.0	0.1
0°-180°	50067.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	44777	44777	44777	44777	44777	
5°	44624	47606	44624	42309	44624	4235
15°	42029	44586	42029	36343	42029	11746
25°	33116	23579	33116	25823	33116	14993
35°	17725	9130	17725	11821	17725	11065
45°	6410	4297	6410	4683	6410	5245
55°	3246	2778	3246	2876	3246	2968
65°	1979	1972	1979	1963	1979	1988
75°	1184	1261	1184	1223	1184	1243
85°	328	415	328	396	328	365
90°	1	7	1	1	1	16
95°	2	7	2	1	2	1
105°	2	8	2	2	2	2
115°	2	8	2	2	2	2
125°	3	8	3	2	3	3
135°	7	9	7	3	7	5
145°	10	11	10	9	10	6
155°	13	15	13	16	13	6
165°	23	28	23	24	23	6
175°	29	36	29	28	29	3
180°	31	31	31	31	31	



TEST NUMBER: P1433938
 CATALOG NUMBER: EHBR1-54-UNV-TASM-L940

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	44777.0	44777.0	44777.0	44777.0	44777.0	44777.0	44777.0	44777.0	44777.0	44777.0	44777.0
2.5°	44751.1	45329.5	45798.0	46107.1	46259.9	46107.1	45798.0	45329.5	44751.1	44175.9	43780.4
5°	44624.3	45782.9	46764.5	47406.8	47605.8	47406.8	46764.5	45782.9	44624.3	43529.4	42803.1
7.5°	44321.1	46126.4	47584.8	48334.6	48517.7	48334.6	47584.8	46126.4	44321.1	42771.2	41853.5
10°	43858.5	46343.0	48028.1	48565.5	48587.4	48565.5	48028.1	46343.0	43858.5	41770.3	40688.1
12.5°	43120.5	46265.7	47879.5	47703.3	47302.7	47703.3	47879.5	46265.7	43120.5	40547.8	39182.5
15°	42029.0	45808.1	46938.3	45503.4	44585.6	45503.4	46938.3	45808.1	42029.0	38897.1	37313.5
17.5°	40490.7	44951.7	44973.5	42134.7	40403.4	42134.7	44973.5	44951.7	40490.7	36878.6	35134.7
20°	38508.4	43578.0	42268.2	37075.9	35024.7	37075.9	42268.2	43578.0	38508.4	34492.3	32781.2
22.5°	36023.0	41725.8	38500.7	31986.9	29188.4	31986.9	38500.7	41725.8	36023.0	31717.3	29936.5
25°	33116.2	39456.3	34447.8	26441.9	23578.7	26441.9	34447.8	39456.3	33116.2	28410.8	26800.4
27.5°	29697.1	36579.7	30132.1	21607.3	18965.7	21607.3	30132.1	36579.7	29697.1	24996.9	23352.0
30°	25899.5	32891.9	25640.9	17207.5	14775.2	17207.5	25640.9	32891.9	25899.5	21161.4	19688.7
32.5°	21647.5	29277.3	21327.6	13787.7	11727.2	13787.7	21327.6	29277.3	21647.5	17501.4	15962.4
35°	17724.8	24755.0	17438.5	10833.8	9130.2	10833.8	17438.5	24755.0	17724.8	14046.3	12534.9
37.5°	13910.3	20482.1	13901.1	8723.8	7405.7	8723.8	13901.1	20482.1	13910.3	10920.4	9693.6
40°	10822.1	16015.3	10891.8	6964.0	5943.0	6964.0	10891.8	16015.3	10822.1	8309.1	7524.0
42.5°	8199.9	12246.1	8561.0	5715.5	5047.9	5715.5	8561.0	12246.1	8199.9	6546.7	5958.9
45°	6409.8	9011.8	6685.2	4822.0	4297.3	4822.0	6685.2	9011.8	6409.8	5272.1	4877.4
47.5°	5220.0	6964.8	5418.2	4136.0	3768.3	4136.0	5418.2	6964.8	5220.0	4459.3	4163.8
50°	4384.6	5344.3	4498.8	3610.4	3363.6	3610.4	4498.8	5344.3	4384.6	3818.6	3621.4
52.5°	3766.6	4358.5	3831.3	3217.5	3051.2	3217.5	3831.3	4358.5	3766.6	3340.9	3218.4
55°	3246.0	3664.2	3331.7	2893.4	2778.4	2893.4	3331.7	3664.2	3246.0	2973.2	2882.5
57.5°	2850.6	3108.3	2893.4	2617.2	2540.8	2617.2	2893.4	3108.3	2850.6	2645.7	2597.0
60°	2500.4	2691.9	2553.4	2376.2	2354.4	2376.2	2553.4	2691.9	2500.4	2380.4	2348.5
62.5°	2230.9	2351.8	2257.8	2159.6	2140.3	2159.6	2257.8	2351.8	2230.9	2138.6	2144.5
65°	1979.0	2091.5	2017.7	1964.7	1971.5	1964.7	2017.7	2091.5	1979.0	1936.2	1945.5
67.5°	1784.2	1843.0	1811.1	1780.8	1788.4	1780.8	1811.1	1843.0	1784.2	1742.3	1756.5
70°	1576.8	1639.8	1607.1	1611.3	1623.9	1611.3	1607.1	1639.8	1576.8	1564.2	1575.1
72.5°	1378.6	1427.4	1416.5	1426.5	1440.0	1426.5	1416.5	1427.4	1378.6	1377.0	1377.8
75°	1183.9	1220.8	1225.9	1240.1	1261.2	1240.1	1225.9	1220.8	1183.9	1171.3	1186.5
77.5°	971.4	1013.4	1029.4	1048.8	1079.8	1048.8	1029.4	1013.4	971.4	979.8	987.5
80°	776.6	796.0	831.2	845.6	889.2	845.6	831.2	796.0	776.6	762.4	773.3
82.5°	568.4	586.1	616.3	643.2	668.4	643.2	616.3	586.1	568.4	561.7	562.5
85°	328.3	355.1	375.4	407.2	414.8	407.2	375.4	355.1	328.3	335.9	328.3
87.5°	115.1	123.4	141.1	153.6	154.5	153.6	141.1	123.4	115.1	117.6	106.7
90°	0.8	1.7	2.5	5.0	6.7	5.0	2.5	1.7	0.8	0.8	0.8
92.5°	0.8	1.7	2.5	5.0	6.7	5.0	2.5	1.7	0.8	0.8	0.8
95°	1.7	1.7	2.5	5.0	6.7	5.0	2.5	1.7	1.7	0.8	0.8
97.5°	1.7	1.7	2.5	5.0	6.7	5.0	2.5	1.7	1.7	0.8	0.8
100°	1.7	1.7	2.5	5.0	6.7	5.0	2.5	1.7	1.7	1.7	0.8
102.5°	1.7	2.5	3.4	5.9	6.7	5.9	3.4	2.5	1.7	1.7	0.8
105°	1.7	2.5	3.4	5.9	7.5	5.9	3.4	2.5	1.7	1.7	0.8
107.5°	1.7	2.5	3.4	5.9	7.5	5.9	3.4	2.5	1.7	1.7	1.7
110°	1.7	2.5	3.4	5.9	7.5	5.9	3.4	2.5	1.7	1.7	1.7



TEST NUMBER: P1433938
 CATALOG NUMBER: EHBR1-54-UNV-TASM-L940

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	1.7	2.5	3.4	5.9	7.5	5.9	3.4	2.5	1.7	1.7	1.7
115°	2.5	2.5	3.4	5.9	7.5	5.9	3.4	2.5	2.5	1.7	1.7
117.5°	2.5	2.5	3.4	5.9	7.5	5.9	3.4	2.5	2.5	2.5	1.7
120°	2.5	2.5	4.2	5.9	7.5	5.9	4.2	2.5	2.5	2.5	1.7
122.5°	3.4	3.4	4.2	6.7	7.5	6.7	4.2	3.4	3.4	3.4	2.5
125°	3.4	3.4	5.0	6.7	8.4	6.7	5.0	3.4	3.4	4.2	3.4
127.5°	4.2	4.2	5.0	6.7	8.4	6.7	5.0	4.2	4.2	4.2	3.4
130°	5.0	4.2	5.0	7.5	8.4	7.5	5.0	4.2	5.0	5.0	4.2
132.5°	5.9	5.0	5.9	8.4	9.2	8.4	5.9	5.0	5.9	6.7	5.9
135°	6.7	5.0	6.7	7.5	9.2	7.5	6.7	5.0	6.7	7.5	5.9
137.5°	7.5	5.9	6.7	8.4	9.2	8.4	6.7	5.9	7.5	8.4	7.5
140°	8.4	6.7	6.7	8.4	10.1	8.4	6.7	6.7	8.4	8.4	8.4
142.5°	9.2	7.5	7.5	9.2	10.1	9.2	7.5	7.5	9.2	9.2	9.2
145°	10.1	9.2	8.4	9.2	10.9	9.2	8.4	9.2	10.1	9.2	10.1
147.5°	10.1	9.2	9.2	10.1	11.7	10.1	9.2	9.2	10.1	10.1	10.9
150°	10.9	10.9	10.1	10.9	12.6	10.9	10.1	10.9	10.9	10.9	11.7
152.5°	11.7	11.7	11.7	12.6	13.4	12.6	11.7	11.7	11.7	11.7	12.6
155°	13.4	13.4	13.4	14.3	15.1	14.3	13.4	13.4	13.4	12.6	14.3
157.5°	15.1	15.9	15.9	16.8	17.6	16.8	15.9	15.9	15.1	15.1	15.9
160°	18.4	18.4	19.3	20.1	21.0	20.1	19.3	18.4	18.4	17.6	18.4
162.5°	20.1	20.1	21.8	22.6	24.3	22.6	21.8	20.1	20.1	20.1	20.1
165°	22.6	22.6	24.3	26.0	27.7	26.0	24.3	22.6	22.6	21.8	21.8
167.5°	24.3	24.3	26.0	28.5	30.2	28.5	26.0	24.3	24.3	23.5	23.5
170°	25.2	26.0	27.7	30.2	31.9	30.2	27.7	26.0	25.2	25.2	24.3
172.5°	27.7	27.7	30.2	32.7	34.5	32.7	30.2	27.7	27.7	26.8	26.8
175°	29.3	30.2	31.9	34.5	36.1	34.5	31.9	30.2	29.3	28.5	28.5
177.5°	29.3	31.0	32.7	35.3	37.0	35.3	32.7	31.0	29.3	28.5	28.5
180°	31.0	31.0	31.0	31.0	31.0	31.0	31.0	31.0	31.0	31.0	31.0



TEST NUMBER: P1433938
 CATALOG NUMBER: EHBR1-54-UNV-TASM-L940

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	44777.0	44777.0	44777.0	44777.0	44777.0	44777.0
2.5°	43476.5	43448.0	43476.5	43780.4	44175.9	44751.1
5°	42466.4	42308.6	42466.4	42803.1	43529.4	44624.3
7.5°	41290.1	41198.5	41290.1	41853.5	42771.2	44321.1
10°	40051.6	39844.2	40051.6	40688.1	41770.3	43858.5
12.5°	38525.1	38250.6	38525.1	39182.5	40547.8	43120.5
15°	36583.9	36342.9	36583.9	37313.5	38897.1	42029.0
17.5°	34500.7	34282.4	34500.7	35134.7	36878.6	40490.7
20°	31884.5	31713.1	31884.5	32781.2	34492.3	38508.4
22.5°	29139.7	28979.3	29139.7	29936.5	31717.3	36023.0
25°	25910.4	25823.1	25910.4	26800.4	28410.8	33116.2
27.5°	22420.9	22272.2	22420.9	23352.0	24996.9	29697.1
30°	18855.8	18609.7	18855.8	19688.7	21161.4	25899.5
32.5°	15368.7	15191.6	15368.7	15962.4	17501.4	21647.5
35°	11998.4	11821.3	11998.4	12534.9	14046.3	17724.8
37.5°	9349.3	9036.2	9349.3	9693.6	10920.4	13910.3
40°	7090.8	7040.4	7090.8	7524.0	8309.1	10822.1
42.5°	5772.5	5635.6	5772.5	5958.9	6546.7	8199.9
45°	4736.4	4682.6	4736.4	4877.4	5272.1	6409.8
47.5°	4073.1	4096.6	4073.1	4163.8	4459.3	5220.0
50°	3578.5	3592.8	3578.5	3621.4	3818.6	4384.6
52.5°	3214.2	3201.5	3214.2	3218.4	3340.9	3766.6
55°	2891.7	2875.8	2891.7	2882.5	2973.2	3246.0
57.5°	2609.6	2621.4	2609.6	2597.0	2645.7	2850.6
60°	2357.7	2368.6	2357.7	2348.5	2380.4	2500.4
62.5°	2145.3	2152.0	2145.3	2144.5	2138.6	2230.9
65°	1955.5	1963.1	1955.5	1945.5	1936.2	1979.0
67.5°	1774.1	1774.1	1774.1	1756.5	1742.3	1784.2
70°	1603.7	1602.9	1603.7	1575.1	1564.2	1576.8
72.5°	1398.9	1419.0	1398.9	1377.8	1377.0	1378.6
75°	1199.9	1223.3	1199.9	1186.5	1171.3	1183.9
77.5°	998.4	1034.4	998.4	987.5	979.8	971.4
80°	791.8	831.2	791.8	773.3	762.4	776.6
82.5°	585.3	614.6	585.3	562.5	561.7	568.4
85°	348.4	395.5	348.4	328.3	335.9	328.3
87.5°	111.7	142.7	111.7	106.7	117.6	115.1
90°	0.8	0.8	0.8	0.8	0.8	0.8
92.5°	0.8	0.8	0.8	0.8	0.8	0.8
95°	0.8	0.8	0.8	0.8	0.8	1.7
97.5°	0.8	1.7	0.8	0.8	0.8	1.7
100°	0.8	1.7	0.8	0.8	1.7	1.7
102.5°	0.8	1.7	0.8	0.8	1.7	1.7
105°	0.8	1.7	0.8	0.8	1.7	1.7
107.5°	0.8	1.7	0.8	1.7	1.7	1.7
110°	0.8	1.7	0.8	1.7	1.7	1.7



TEST NUMBER: P1433938
 CATALOG NUMBER: EHBR1-54-UNV-TASM-L940

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.8	1.7	0.8	1.7	1.7	1.7
115°	0.8	1.7	0.8	1.7	1.7	2.5
117.5°	0.8	1.7	0.8	1.7	2.5	2.5
120°	0.8	1.7	0.8	1.7	2.5	2.5
122.5°	1.7	1.7	1.7	2.5	3.4	3.4
125°	1.7	2.5	1.7	3.4	4.2	3.4
127.5°	1.7	2.5	1.7	3.4	4.2	4.2
130°	2.5	2.5	2.5	4.2	5.0	5.0
132.5°	3.4	3.4	3.4	5.9	6.7	5.9
135°	4.2	3.4	4.2	5.9	7.5	6.7
137.5°	5.0	4.2	5.0	7.5	8.4	7.5
140°	6.7	5.9	6.7	8.4	8.4	8.4
142.5°	7.5	7.5	7.5	9.2	9.2	9.2
145°	9.2	9.2	9.2	10.1	9.2	10.1
147.5°	10.9	10.9	10.9	10.9	10.1	10.1
150°	12.6	12.6	12.6	11.7	10.9	10.9
152.5°	13.4	14.3	13.4	12.6	11.7	11.7
155°	15.1	15.9	15.1	14.3	12.6	13.4
157.5°	16.8	18.4	16.8	15.9	15.1	15.1
160°	19.3	20.1	19.3	18.4	17.6	18.4
162.5°	21.0	21.8	21.0	20.1	20.1	20.1
165°	22.6	23.5	22.6	21.8	21.8	22.6
167.5°	23.5	23.5	23.5	23.5	23.5	24.3
170°	24.3	25.2	24.3	24.3	25.2	25.2
172.5°	26.0	26.8	26.0	26.8	26.8	27.7
175°	27.7	28.5	27.7	28.5	28.5	29.3
177.5°	28.5	29.3	28.5	28.5	28.5	29.3
180°	31.0	31.0	31.0	31.0	31.0	31.0



TEST NUMBER: P1433938
 CATALOG NUMBER: EHBR1-54-UNV-TASM-L940

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.23	21.44	20.60	21.75	22.07	19.55	20.76	19.92	21.07	21.39
	3H	21.87	22.94	22.25	23.28	23.65	21.50	22.57	21.88	22.91	23.28
	4H	22.58	23.58	22.98	23.93	24.32	22.36	23.36	22.77	23.72	24.10
	6H	23.15	24.07	23.57	24.44	24.84	23.11	24.03	23.53	24.41	24.80
	8H	23.35	24.22	23.79	24.62	25.02	23.40	24.27	23.83	24.66	25.07
	12H	23.47	24.31	23.91	24.69	25.12	23.60	24.43	24.03	24.81	25.24
4H	2H	20.70	21.70	21.10	22.05	22.44	20.18	21.18	20.59	21.54	21.92
	3H	22.61	23.43	23.02	23.84	24.24	22.36	23.18	22.77	23.59	24.00
	4H	23.46	24.20	23.90	24.62	25.07	23.36	24.10	23.79	24.52	24.96
	6H	24.19	24.82	24.65	25.27	25.74	24.25	24.89	24.72	25.34	25.81
	8H	24.44	25.04	24.92	25.49	25.96	24.60	25.19	25.07	25.64	26.12
	12H	24.61	25.14	25.10	25.62	26.10	24.85	25.37	25.34	25.86	26.33
8H	4H	23.77	24.37	24.24	24.82	25.29	23.70	24.29	24.17	24.74	25.22
	6H	24.65	25.13	25.15	25.63	26.12	24.75	25.23	25.25	25.73	26.22
	8H	25.00	25.43	25.53	25.95	26.44	25.20	25.63	25.72	26.15	26.64
	12H	25.26	25.64	25.78	26.13	26.71	25.55	25.93	26.07	26.43	27.00
12H	4H	23.80	24.32	24.29	24.81	25.29	23.73	24.25	24.22	24.74	25.21
	6H	24.72	25.15	25.24	25.67	26.16	24.82	25.25	25.35	25.77	26.27
	8H	25.13	25.51	25.65	26.01	26.59	25.34	25.72	25.86	26.21	26.79

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-6

Test Date: 08/01/2025

Luminaire Tested: EHBR-60-L935-N

Data in this report applies to families of products including EHBR-60-L935-N


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-6
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L935-N**
 Description: Elevate Round Highbay at, 60000 lumens, 3500K 90CRI LEDs with N lens

Spectral Parameters

CCT (K): 3406
 CIE u': 0.2394
 CIE v': 0.5094
 Duv: -0.0028
 CIE x: 0.4076
 CIE y: 0.3856
 CIE z: 0.2068
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 582
 Purity: 38.0517
 Rf: 91.3
 Rg: 100

CRI (Ra):	94.6		
R1:	96.6	R9:	63.8
R2:	98.4	R10:	94.7
R3:	98.1	R11:	96.6
R4:	95.8	R12:	80.9
R5:	96.2	R13:	97.4
R6:	95.4	R14:	98.3
R7:	91.8	R15:	93.1
R8:	84.4		



Test Conditions


Stabilization Time: 35M
 Operation Time: 1H 35M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-6


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-6

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-6

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.62

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-6

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.3

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

Summary

$R_f = 91.3$
 $R_g = 100$
 $CIE R_a = 94.6$
 $R_9 = 63.8$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 94	CES51 = 97	CES76 = 90
CES02 = 63	CES27 = 92	CES52 = 98	CES77 = 86
CES03 = 31	CES28 = 97	CES53 = 98	CES78 = 86
CES04 = 70	CES29 = 97	CES54 = 93	CES79 = 90
CES05 = 50	CES30 = 92	CES55 = 92	CES80 = 91
CES06 = 51	CES31 = 97	CES56 = 96	CES81 = 74
CES07 = 43	CES32 = 89	CES57 = 94	CES82 = 96
CES08 = 41	CES33 = 99	CES58 = 95	CES83 = 94
CES09 = 29	CES34 = 94	CES59 = 98	CES84 = 95
CES10 = 75	CES35 = 97	CES60 = 92	CES85 = 79
CES11 = 58	CES36 = 81	CES61 = 93	CES86 = 79
CES12 = 64	CES37 = 96	CES62 = 86	CES87 = 92
CES13 = 44	CES38 = 87	CES63 = 94	CES88 = 98
CES14 = 74	CES39 = 99	CES64 = 91	CES89 = 84
CES15 = 72	CES40 = 97	CES65 = 90	CES90 = 96
CES16 = 48	CES41 = 96	CES66 = 89	CES91 = 75
CES17 = 49	CES42 = 94	CES67 = 88	CES92 = 76
CES18 = 56	CES43 = 93	CES68 = 89	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 90	CES94 = 74
CES20 = 67	CES45 = 97	CES70 = 88	CES95 = 83
CES21 = 86	CES46 = 97	CES71 = 83	CES96 = 92
CES22 = 78	CES47 = 91	CES72 = 94	CES97 = 96
CES23 = 91	CES48 = 91	CES73 = 83	CES98 = 95
CES24 = 90	CES49 = 96	CES74 = 90	CES99 = 92
CES25 = 71	CES50 = 98	CES75 = 85	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)