

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1433835

Luminaire Tested: EHBR1-36-UNV-TASM-L940-UPL12

Issue Date: 3/20/2026

Test Information

Test Method: LM-79-2019
Report Number: P1433835
REPORT IS A COMBINATION OF REPORTS P1431772 AND P1431635
Test Lab: INNOVATION CENTER
Issue Date: 3/20/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-36-UNV-TASM-L940-UPL12
Description: Elevate Round Highbay at, 36000 lumens, 4000K 90CRI LEDs with TASM lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 34731.7 lumens
Efficiency: N/A
Efficacy: 174.7 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.84 / 0.9
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')
CIE Type: Direct

Input Watts (W): 198.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1433835
CATALOG NUMBER: EHBR1-36-UNV-TASM-L940-UPL12

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°



TEST NUMBER: P1433835

CATALOG NUMBER: EHBR1-36-UNV-TASM-L940-UPL12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 118 | 118 | 118 | 118 | 115 | 115 | 115 | 115 | 109 | 109 | 109 | 104 | 104 | 104 | 99 | 99 | 99 | 99 | 97 | |
| 1 | 111 | 108 | 105 | 102 | 108 | 105 | 102 | 100 | 100 | 98 | 96 | 96 | 94 | 93 | 92 | 91 | 89 | 89 | 87 | |
| 2 | 104 | 98 | 93 | 89 | 102 | 96 | 92 | 88 | 92 | 89 | 85 | 89 | 86 | 83 | 85 | 83 | 81 | 81 | 79 | |
| 3 | 98 | 90 | 84 | 79 | 95 | 88 | 83 | 78 | 85 | 80 | 77 | 82 | 78 | 75 | 79 | 76 | 73 | 73 | 72 | |
| 4 | 92 | 83 | 76 | 71 | 90 | 81 | 75 | 71 | 79 | 74 | 69 | 76 | 72 | 68 | 74 | 70 | 67 | 67 | 65 | |
| 5 | 86 | 77 | 70 | 65 | 84 | 75 | 69 | 64 | 73 | 68 | 63 | 71 | 66 | 63 | 69 | 65 | 62 | 62 | 60 | |
| 6 | 81 | 71 | 64 | 59 | 80 | 70 | 64 | 59 | 68 | 63 | 58 | 66 | 61 | 58 | 65 | 60 | 57 | 57 | 55 | |
| 7 | 77 | 66 | 60 | 55 | 75 | 66 | 59 | 54 | 64 | 58 | 54 | 62 | 57 | 53 | 61 | 56 | 53 | 53 | 51 | |
| 8 | 73 | 62 | 55 | 51 | 71 | 61 | 55 | 51 | 60 | 54 | 50 | 59 | 53 | 50 | 57 | 53 | 49 | 49 | 48 | |
| 9 | 69 | 58 | 52 | 47 | 68 | 58 | 51 | 47 | 56 | 51 | 47 | 55 | 50 | 46 | 54 | 49 | 46 | 46 | 45 | |
| 10 | 66 | 55 | 48 | 44 | 64 | 54 | 48 | 44 | 53 | 48 | 44 | 52 | 47 | 43 | 51 | 46 | 43 | 43 | 42 | |

AVERAGE LUMINANCE (cd/sqm):

| | 0° | 90° | 180° | 270° |
|-----|--------|--------|--------|--------|
| 0° | 141138 | 141138 | 141138 | 141138 |
| 5° | 140280 | 149652 | 140280 | 133000 |
| 10° | 138555 | 153494 | 138555 | 125873 |
| 15° | 134464 | 142644 | 134464 | 116273 |
| 20° | 125757 | 114381 | 125757 | 103566 |
| 25° | 111305 | 79250 | 111305 | 86793 |
| 30° | 90376 | 51558 | 90376 | 64939 |
| 35° | 64820 | 33390 | 64820 | 43231 |
| 40° | 41908 | 23014 | 41908 | 27264 |
| 45° | 26590 | 17827 | 26590 | 19426 |
| 50° | 19747 | 15149 | 19747 | 16181 |
| 55° | 16122 | 13800 | 16122 | 14283 |
| 60° | 13961 | 13145 | 13961 | 13225 |
| 65° | 12726 | 12677 | 12726 | 12623 |
| 70° | 12061 | 12421 | 12061 | 12262 |
| 75° | 11280 | 12017 | 11280 | 11658 |
| 80° | 9909 | 11345 | 9909 | 10607 |
| 85° | 6410 | 8100 | 6410 | 7722 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 37385 cd/sqm



TEST NUMBER: P1433835

CATALOG NUMBER: EHBR1-36-UNV-TASM-L940-UPL12

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 2857.7 | 8.2 |
| 10°-20° | 7774.6 | 22.4 |
| 20°-30° | 9118.0 | 26.3 |
| 30°-40° | 6341.0 | 18.3 |
| 40°-50° | 3151.2 | 9.1 |
| 50°-60° | 1884.7 | 5.4 |
| 60°-70° | 1326.6 | 3.8 |
| 70°-80° | 854.5 | 2.5 |
| 80°-90° | 273.4 | 0.8 |
| 90°-100° | 31.2 | 0.1 |
| 100°-110° | 198.2 | 0.6 |
| 110°-120° | 365.2 | 1.1 |
| 120°-130° | 217.9 | 0.6 |
| 130°-140° | 133.0 | 0.4 |
| 140°-150° | 93.2 | 0.3 |
| 150°-160° | 62.1 | 0.2 |
| 160°-170° | 36.8 | 0.1 |
| 170°-180° | 12.5 | 0.0 |
| 0°-30° | 19750.3 | 56.9 |
| 0°-40° | 26091.3 | 75.1 |
| 0°-60° | 31127.2 | 89.6 |
| 0°-90° | 33581.7 | 96.7 |
| 90°-120° | 594.6 | 1.7 |
| 90°-150° | 1038.5 | 3.0 |
| 90°-180° | 1150.0 | 3.3 |
| 0°-180° | 34731.7 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | 90° | 180° | 270° | 360° | Flux |
|------|-------|-------|-------|-------|-------|-------|
| 0° | 30054 | 30054 | 30054 | 30054 | 30054 | |
| 5° | 29952 | 31953 | 29952 | 28398 | 29952 | 2842 |
| 15° | 28210 | 29926 | 28210 | 24393 | 28210 | 7884 |
| 25° | 22228 | 15826 | 22228 | 17332 | 22228 | 10063 |
| 35° | 11897 | 6128 | 11897 | 7934 | 11897 | 7427 |
| 45° | 4302 | 2884 | 4302 | 3143 | 4302 | 3521 |
| 55° | 2179 | 1865 | 2179 | 1930 | 2179 | 1992 |
| 65° | 1328 | 1323 | 1328 | 1318 | 1328 | 1334 |
| 75° | 795 | 846 | 795 | 821 | 795 | 834 |
| 85° | 220 | 278 | 220 | 265 | 220 | 245 |
| 90° | 9 | 13 | 9 | 9 | 9 | 14 |
| 95° | 17 | 18 | 17 | 14 | 17 | 18 |
| 105° | 91 | 50 | 91 | 69 | 91 | 123 |
| 115° | 388 | 334 | 388 | 315 | 388 | 354 |
| 125° | 249 | 263 | 249 | 228 | 249 | 230 |
| 135° | 160 | 185 | 160 | 167 | 160 | 127 |
| 145° | 146 | 153 | 146 | 142 | 146 | 92 |
| 155° | 132 | 138 | 132 | 130 | 132 | 62 |
| 165° | 129 | 135 | 129 | 127 | 129 | 37 |
| 175° | 132 | 137 | 132 | 129 | 132 | 12 |
| 180° | 132 | 132 | 132 | 132 | 132 | |



TEST NUMBER: P1433835
 CATALOG NUMBER: EHBR1-36-UNV-TASM-L940-UPL12

CANDELA DISTRIBUTION (FULL):

| | 0° | 22.5° | 45° | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° | 202.5° | 225° |
|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 30054.4 | 30054.4 | 30054.4 | 30054.4 | 30054.4 | 30054.4 | 30054.4 | 30054.4 | 30054.4 | 30054.4 | 30054.4 |
| 2.5° | 30036.9 | 30425.2 | 30739.7 | 30947.1 | 31049.6 | 30947.1 | 30739.7 | 30425.2 | 30036.9 | 29650.8 | 29385.4 |
| 5° | 29951.9 | 30729.6 | 31388.4 | 31819.5 | 31953.0 | 31819.5 | 31388.4 | 30729.6 | 29951.9 | 29217.0 | 28729.4 |
| 7.5° | 29748.4 | 30960.1 | 31939.0 | 32442.2 | 32565.1 | 32442.2 | 31939.0 | 30960.1 | 29748.4 | 28708.0 | 28092.1 |
| 10° | 29437.9 | 31105.4 | 32236.5 | 32597.2 | 32611.9 | 32597.2 | 32236.5 | 31105.4 | 29437.9 | 28036.3 | 27309.8 |
| 12.5° | 28942.5 | 31053.6 | 32136.8 | 32018.4 | 31749.6 | 32018.4 | 32136.8 | 31053.6 | 28942.5 | 27215.7 | 26299.3 |
| 15° | 28209.9 | 30746.5 | 31505.0 | 30541.9 | 29925.9 | 30541.9 | 31505.0 | 30746.5 | 28209.9 | 26107.8 | 25044.9 |
| 17.5° | 27177.4 | 30171.6 | 30186.3 | 28280.9 | 27118.8 | 28280.9 | 30186.3 | 30171.6 | 27177.4 | 24752.9 | 23582.4 |
| 20° | 25846.8 | 29249.7 | 28370.5 | 24885.4 | 23508.6 | 24885.4 | 28370.5 | 29249.7 | 25846.8 | 23151.3 | 22002.8 |
| 22.5° | 24178.6 | 28006.4 | 25841.7 | 21469.6 | 19591.2 | 21469.6 | 25841.7 | 28006.4 | 24178.6 | 21288.7 | 20093.4 |
| 25° | 22227.6 | 26483.1 | 23121.4 | 17747.9 | 15826.1 | 17747.9 | 23121.4 | 26483.1 | 22227.6 | 19069.4 | 17988.5 |
| 27.5° | 19932.8 | 24552.3 | 20224.7 | 14502.8 | 12729.8 | 14502.8 | 20224.7 | 24552.3 | 19932.8 | 16777.9 | 15673.9 |
| 30° | 17383.8 | 22077.1 | 17210.2 | 11549.7 | 9917.1 | 11549.7 | 17210.2 | 22077.1 | 17383.8 | 14203.6 | 13215.0 |
| 32.5° | 14529.9 | 19651.0 | 14315.1 | 9254.3 | 7871.3 | 9254.3 | 14315.1 | 19651.0 | 14529.9 | 11746.9 | 10713.9 |
| 35° | 11896.8 | 16615.6 | 11704.7 | 7271.7 | 6128.2 | 7271.7 | 11704.7 | 16615.6 | 11896.8 | 9427.9 | 8413.5 |
| 37.5° | 9336.6 | 13747.6 | 9330.4 | 5855.5 | 4970.6 | 5855.5 | 9330.4 | 13747.6 | 9336.6 | 7329.7 | 6506.3 |
| 40° | 7263.8 | 10749.4 | 7310.5 | 4674.3 | 3988.9 | 4674.3 | 7310.5 | 10749.4 | 7263.8 | 5577.0 | 5050.1 |
| 42.5° | 5503.8 | 8219.6 | 5746.1 | 3836.2 | 3388.1 | 3836.2 | 5746.1 | 8219.6 | 5503.8 | 4394.1 | 3999.6 |
| 45° | 4302.2 | 6048.7 | 4487.1 | 3236.5 | 2884.4 | 3236.5 | 4487.1 | 6048.7 | 4302.2 | 3538.7 | 3273.7 |
| 47.5° | 3503.7 | 4674.8 | 3636.7 | 2776.1 | 2529.3 | 2776.1 | 3636.7 | 4674.8 | 3503.7 | 2993.1 | 2794.8 |
| 50° | 2943.0 | 3587.1 | 3019.6 | 2423.3 | 2257.7 | 2423.3 | 3019.6 | 3587.1 | 2943.0 | 2563.1 | 2430.7 |
| 52.5° | 2528.1 | 2925.5 | 2571.5 | 2159.6 | 2048.0 | 2159.6 | 2571.5 | 2925.5 | 2528.1 | 2242.5 | 2160.1 |
| 55° | 2178.7 | 2459.4 | 2236.2 | 1942.0 | 1864.9 | 1942.0 | 2236.2 | 2459.4 | 2178.7 | 1995.6 | 1934.7 |
| 57.5° | 1913.3 | 2086.3 | 1942.0 | 1756.6 | 1705.4 | 1756.6 | 1942.0 | 2086.3 | 1913.3 | 1775.8 | 1743.1 |
| 60° | 1678.3 | 1806.8 | 1713.8 | 1594.9 | 1580.3 | 1594.9 | 1713.8 | 1806.8 | 1678.3 | 1597.7 | 1576.3 |
| 62.5° | 1497.4 | 1578.6 | 1515.4 | 1449.5 | 1436.5 | 1449.5 | 1515.4 | 1578.6 | 1497.4 | 1435.4 | 1439.4 |
| 65° | 1328.3 | 1403.8 | 1354.2 | 1318.7 | 1323.2 | 1318.7 | 1354.2 | 1403.8 | 1328.3 | 1299.6 | 1305.8 |
| 67.5° | 1197.5 | 1237.0 | 1215.6 | 1195.3 | 1200.4 | 1195.3 | 1215.6 | 1237.0 | 1197.5 | 1169.4 | 1179.0 |
| 70° | 1058.3 | 1100.6 | 1078.7 | 1081.5 | 1089.9 | 1081.5 | 1078.7 | 1100.6 | 1058.3 | 1050.0 | 1057.2 |
| 72.5° | 925.4 | 958.1 | 950.7 | 957.5 | 966.5 | 957.5 | 950.7 | 958.1 | 925.4 | 924.3 | 924.8 |
| 75° | 794.6 | 819.4 | 822.8 | 832.4 | 846.5 | 832.4 | 822.8 | 819.4 | 794.6 | 786.2 | 796.3 |
| 77.5° | 652.1 | 680.2 | 690.9 | 703.9 | 724.7 | 703.9 | 690.9 | 680.2 | 652.1 | 657.6 | 662.8 |
| 80° | 521.3 | 534.3 | 558.0 | 567.5 | 596.8 | 567.5 | 558.0 | 534.3 | 521.3 | 511.8 | 519.0 |
| 82.5° | 381.5 | 393.3 | 413.7 | 431.7 | 448.6 | 431.7 | 413.7 | 393.3 | 381.5 | 377.0 | 377.6 |
| 85° | 220.3 | 238.4 | 251.9 | 273.3 | 278.4 | 273.3 | 251.9 | 238.4 | 220.3 | 225.5 | 220.3 |
| 87.5° | 77.2 | 82.8 | 94.7 | 103.1 | 103.7 | 103.1 | 94.7 | 82.8 | 77.2 | 78.9 | 71.6 |
| 90° | 8.7 | 14.9 | 25.4 | 15.8 | 12.6 | 15.8 | 25.4 | 14.9 | 8.7 | 14.9 | 23.1 |
| 92.5° | 11.2 | 19.8 | 35.5 | 20.2 | 15.7 | 20.2 | 35.5 | 19.8 | 11.2 | 19.3 | 36.9 |
| 95° | 16.8 | 24.2 | 44.8 | 22.1 | 18.3 | 22.1 | 44.8 | 24.2 | 16.8 | 25.6 | 51.2 |
| 97.5° | 25.5 | 29.9 | 50.5 | 23.4 | 21.3 | 23.4 | 50.5 | 29.9 | 25.5 | 31.2 | 58.8 |
| 100° | 33.6 | 33.6 | 91.1 | 26.5 | 23.9 | 26.5 | 91.1 | 33.6 | 33.6 | 38.7 | 91.3 |
| 102.5° | 50.6 | 65.5 | 210.0 | 50.9 | 28.2 | 50.9 | 210.0 | 65.5 | 50.6 | 71.8 | 193.3 |
| 105° | 91.2 | 148.1 | 368.3 | 126.5 | 49.5 | 126.5 | 368.3 | 148.1 | 91.2 | 149.4 | 344.1 |
| 107.5° | 172.0 | 275.1 | 474.0 | 246.7 | 110.1 | 246.7 | 474.0 | 275.1 | 172.0 | 263.9 | 454.1 |
| 110° | 274.6 | 384.0 | 517.2 | 336.8 | 219.0 | 336.8 | 517.2 | 384.0 | 274.6 | 362.1 | 476.1 |



TEST NUMBER: P1433835

CATALOG NUMBER: EHBR1-36-UNV-TASM-L940-UPL12

CANDELA DISTRIBUTION (continued):

| | 0° | 22.5° | 45° | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° | 202.5° | 225° |
|--------|-------|-------|-------|-------|-------|--------|-------|--------|-------|--------|-------|
| 112.5° | 357.1 | 427.8 | 505.3 | 373.1 | 301.6 | 373.1 | 505.3 | 427.8 | 357.1 | 399.7 | 456.0 |
| 115° | 388.4 | 421.6 | 451.5 | 371.8 | 334.2 | 371.8 | 451.5 | 421.6 | 388.4 | 390.3 | 407.2 |
| 117.5° | 375.3 | 385.9 | 390.2 | 349.3 | 336.0 | 349.3 | 390.2 | 385.9 | 375.3 | 351.4 | 345.9 |
| 120° | 338.9 | 334.6 | 329.4 | 316.1 | 317.2 | 316.1 | 329.4 | 334.6 | 338.9 | 307.0 | 288.9 |
| 122.5° | 293.8 | 284.4 | 278.7 | 282.9 | 291.6 | 282.9 | 278.7 | 284.4 | 293.8 | 261.9 | 248.2 |
| 125° | 249.4 | 240.0 | 243.6 | 254.2 | 263.4 | 254.2 | 243.6 | 240.0 | 249.4 | 223.0 | 219.4 |
| 127.5° | 212.4 | 208.0 | 218.0 | 229.7 | 237.8 | 229.7 | 218.0 | 208.0 | 212.4 | 195.6 | 198.7 |
| 130° | 186.0 | 186.8 | 199.8 | 210.3 | 215.2 | 210.3 | 199.8 | 186.8 | 186.0 | 177.9 | 186.1 |
| 132.5° | 169.7 | 174.2 | 186.6 | 195.8 | 199.0 | 195.8 | 186.6 | 174.2 | 169.7 | 167.8 | 177.9 |
| 135° | 159.7 | 166.0 | 177.8 | 183.3 | 185.2 | 183.3 | 177.8 | 166.0 | 159.7 | 160.8 | 169.7 |
| 137.5° | 153.9 | 160.3 | 169.0 | 173.9 | 173.3 | 173.9 | 169.0 | 160.3 | 153.9 | 156.4 | 163.3 |
| 140° | 150.7 | 157.2 | 160.9 | 166.4 | 166.4 | 166.4 | 160.9 | 157.2 | 150.7 | 152.0 | 157.6 |
| 142.5° | 147.7 | 153.3 | 155.2 | 159.5 | 158.8 | 159.5 | 155.2 | 153.3 | 147.7 | 148.9 | 152.7 |
| 145° | 146.4 | 150.7 | 148.9 | 153.9 | 153.2 | 153.9 | 148.9 | 150.7 | 146.4 | 146.4 | 148.9 |
| 147.5° | 143.2 | 146.4 | 144.5 | 148.9 | 148.0 | 148.9 | 144.5 | 146.4 | 143.2 | 143.2 | 144.4 |
| 150° | 140.0 | 142.5 | 139.5 | 144.4 | 144.9 | 144.4 | 139.5 | 142.5 | 140.0 | 139.4 | 140.6 |
| 152.5° | 135.6 | 138.1 | 135.6 | 141.1 | 141.1 | 141.1 | 135.6 | 138.1 | 135.6 | 134.9 | 136.1 |
| 155° | 132.3 | 133.6 | 132.3 | 137.9 | 138.4 | 137.9 | 132.3 | 133.6 | 132.3 | 131.7 | 132.9 |
| 157.5° | 130.3 | 131.5 | 130.9 | 135.8 | 136.4 | 135.8 | 130.9 | 131.5 | 130.3 | 130.3 | 130.9 |
| 160° | 129.4 | 130.6 | 130.6 | 134.9 | 135.5 | 134.9 | 130.6 | 130.6 | 129.4 | 129.5 | 130.1 |
| 162.5° | 129.2 | 129.2 | 129.8 | 134.1 | 135.2 | 134.1 | 129.8 | 129.2 | 129.2 | 129.2 | 129.9 |
| 165° | 129.0 | 129.7 | 129.6 | 133.2 | 135.0 | 133.2 | 129.6 | 129.7 | 129.0 | 129.1 | 129.1 |
| 167.5° | 129.6 | 128.9 | 130.2 | 133.7 | 135.5 | 133.7 | 130.2 | 128.9 | 129.6 | 129.6 | 129.6 |
| 170° | 128.8 | 129.5 | 130.0 | 133.6 | 135.3 | 133.6 | 130.0 | 129.5 | 128.8 | 129.5 | 129.6 |
| 172.5° | 130.6 | 130.6 | 131.1 | 134.0 | 136.4 | 134.0 | 131.1 | 130.6 | 130.6 | 130.7 | 131.4 |
| 175° | 131.7 | 131.6 | 132.2 | 134.4 | 136.9 | 134.4 | 132.2 | 131.6 | 131.7 | 131.2 | 131.2 |
| 177.5° | 131.1 | 132.2 | 133.3 | 135.6 | 138.6 | 135.6 | 133.3 | 132.2 | 131.1 | 131.2 | 131.2 |
| 180° | 132.2 | 132.2 | 132.2 | 132.2 | 132.2 | 132.2 | 132.2 | 132.2 | 132.2 | 132.2 | 132.2 |



TEST NUMBER: P1433835

CATALOG NUMBER: EHBR1-36-UNV-TASM-L940-UPL12

CANDELA DISTRIBUTION (continued):

| | 247.5° | 270° | 292.5° | 315° | 337.5° | 360° |
|--------|---------|---------|---------|---------|---------|---------|
| 0° | 30054.4 | 30054.4 | 30054.4 | 30054.4 | 30054.4 | 30054.4 |
| 2.5° | 29181.5 | 29162.3 | 29181.5 | 29385.4 | 29650.8 | 30036.9 |
| 5° | 28503.4 | 28397.5 | 28503.4 | 28729.4 | 29217.0 | 29951.9 |
| 7.5° | 27714.0 | 27652.5 | 27714.0 | 28092.1 | 28708.0 | 29748.4 |
| 10° | 26882.6 | 26743.5 | 26882.6 | 27309.8 | 28036.3 | 29437.9 |
| 12.5° | 25858.1 | 25673.8 | 25858.1 | 26299.3 | 27215.7 | 28942.5 |
| 15° | 24555.1 | 24393.4 | 24555.1 | 25044.9 | 26107.8 | 28209.9 |
| 17.5° | 23156.9 | 23010.4 | 23156.9 | 23582.4 | 24752.9 | 27177.4 |
| 20° | 21400.8 | 21285.9 | 21400.8 | 22002.8 | 23151.3 | 25846.8 |
| 22.5° | 19558.5 | 19450.9 | 19558.5 | 20093.4 | 21288.7 | 24178.6 |
| 25° | 17391.0 | 17332.4 | 17391.0 | 17988.5 | 19069.4 | 22227.6 |
| 27.5° | 15048.9 | 14949.2 | 15048.9 | 15673.9 | 16777.9 | 19932.8 |
| 30° | 12656.0 | 12490.9 | 12656.0 | 13215.0 | 14203.6 | 17383.8 |
| 32.5° | 10315.5 | 10196.6 | 10315.5 | 10713.9 | 11746.9 | 14529.9 |
| 35° | 8053.3 | 7934.5 | 8053.3 | 8413.5 | 9427.9 | 11896.8 |
| 37.5° | 6275.3 | 6065.1 | 6275.3 | 6506.3 | 7329.7 | 9336.6 |
| 40° | 4759.3 | 4725.5 | 4759.3 | 5050.1 | 5577.0 | 7263.8 |
| 42.5° | 3874.5 | 3782.7 | 3874.5 | 3999.6 | 4394.1 | 5503.8 |
| 45° | 3179.1 | 3143.0 | 3179.1 | 3273.7 | 3538.7 | 4302.2 |
| 47.5° | 2733.8 | 2749.7 | 2733.8 | 2794.8 | 2993.1 | 3503.7 |
| 50° | 2401.9 | 2411.5 | 2401.9 | 2430.7 | 2563.1 | 2943.0 |
| 52.5° | 2157.3 | 2148.8 | 2157.3 | 2160.1 | 2242.5 | 2528.1 |
| 55° | 1940.9 | 1930.2 | 1940.9 | 1934.7 | 1995.6 | 2178.7 |
| 57.5° | 1751.6 | 1759.4 | 1751.6 | 1743.1 | 1775.8 | 1913.3 |
| 60° | 1582.5 | 1589.9 | 1582.5 | 1576.3 | 1597.7 | 1678.3 |
| 62.5° | 1440.0 | 1444.4 | 1440.0 | 1439.4 | 1435.4 | 1497.4 |
| 65° | 1312.5 | 1317.6 | 1312.5 | 1305.8 | 1299.6 | 1328.3 |
| 67.5° | 1190.8 | 1190.8 | 1190.8 | 1179.0 | 1169.4 | 1197.5 |
| 70° | 1076.4 | 1075.9 | 1076.4 | 1057.2 | 1050.0 | 1058.3 |
| 72.5° | 938.9 | 952.4 | 938.9 | 924.8 | 924.3 | 925.4 |
| 75° | 805.3 | 821.2 | 805.3 | 796.3 | 786.2 | 794.6 |
| 77.5° | 670.0 | 694.4 | 670.0 | 662.8 | 657.6 | 652.1 |
| 80° | 531.4 | 558.0 | 531.4 | 519.0 | 511.8 | 521.3 |
| 82.5° | 392.8 | 412.5 | 392.8 | 377.6 | 377.0 | 381.5 |
| 85° | 233.8 | 265.4 | 233.8 | 220.3 | 225.5 | 220.3 |
| 87.5° | 75.0 | 95.8 | 75.0 | 71.6 | 78.9 | 77.2 |
| 90° | 13.7 | 8.7 | 13.7 | 23.1 | 14.9 | 8.7 |
| 92.5° | 20.6 | 12.5 | 20.6 | 36.9 | 19.3 | 11.2 |
| 95° | 23.7 | 14.3 | 23.7 | 51.2 | 25.6 | 16.8 |
| 97.5° | 26.2 | 18.6 | 26.2 | 58.8 | 31.2 | 25.5 |
| 100° | 30.6 | 24.2 | 30.6 | 91.3 | 38.7 | 33.6 |
| 102.5° | 64.4 | 40.5 | 64.4 | 193.3 | 71.8 | 50.6 |
| 105° | 135.1 | 69.3 | 135.1 | 344.1 | 149.4 | 91.2 |
| 107.5° | 241.5 | 119.3 | 241.5 | 454.1 | 263.9 | 172.0 |
| 110° | 320.3 | 222.0 | 320.3 | 476.1 | 362.1 | 274.6 |



TEST NUMBER: P1433835

CATALOG NUMBER: EHBR1-36-UNV-TASM-L940-UPL12

CANDELA DISTRIBUTION (continued):

| | 247.5° | 270° | 292.5° | 315° | 337.5° | 360° |
|--------|--------|-------|--------|-------|--------|-------|
| 112.5° | 344.1 | 299.6 | 344.1 | 456.0 | 399.7 | 357.1 |
| 115° | 330.9 | 315.3 | 330.9 | 407.2 | 390.3 | 388.4 |
| 117.5° | 302.1 | 304.6 | 302.1 | 345.9 | 351.4 | 375.3 |
| 120° | 269.0 | 282.1 | 269.0 | 288.9 | 307.0 | 338.9 |
| 122.5° | 238.9 | 253.9 | 238.9 | 248.2 | 261.9 | 293.8 |
| 125° | 212.6 | 228.2 | 212.6 | 219.4 | 223.0 | 249.4 |
| 127.5° | 194.4 | 205.1 | 194.4 | 198.7 | 195.6 | 212.4 |
| 130° | 180.6 | 189.4 | 180.6 | 186.1 | 177.9 | 186.0 |
| 132.5° | 171.1 | 176.8 | 171.1 | 177.9 | 167.8 | 169.7 |
| 135° | 162.9 | 167.4 | 162.9 | 169.7 | 160.8 | 159.7 |
| 137.5° | 156.1 | 159.9 | 156.1 | 163.3 | 156.4 | 153.9 |
| 140° | 150.3 | 153.4 | 150.3 | 157.6 | 152.0 | 150.7 |
| 142.5° | 143.9 | 146.5 | 143.9 | 152.7 | 148.9 | 147.7 |
| 145° | 140.1 | 142.0 | 140.1 | 148.9 | 146.4 | 146.4 |
| 147.5° | 136.9 | 138.2 | 136.9 | 144.4 | 143.2 | 143.2 |
| 150° | 133.6 | 134.9 | 133.6 | 140.6 | 139.4 | 140.0 |
| 152.5° | 129.8 | 131.6 | 129.8 | 136.1 | 134.9 | 135.6 |
| 155° | 127.8 | 129.6 | 127.8 | 132.9 | 131.7 | 132.3 |
| 157.5° | 127.0 | 128.8 | 127.0 | 130.9 | 130.3 | 130.3 |
| 160° | 126.8 | 128.0 | 126.8 | 130.1 | 129.5 | 129.4 |
| 162.5° | 126.1 | 127.3 | 126.1 | 129.9 | 129.2 | 129.2 |
| 165° | 126.5 | 127.1 | 126.5 | 129.1 | 129.1 | 129.0 |
| 167.5° | 126.5 | 127.1 | 126.5 | 129.6 | 129.6 | 129.6 |
| 170° | 127.1 | 127.6 | 127.1 | 129.6 | 129.5 | 128.8 |
| 172.5° | 128.3 | 128.8 | 128.3 | 131.4 | 130.7 | 130.6 |
| 175° | 128.8 | 129.3 | 128.8 | 131.2 | 131.2 | 131.7 |
| 177.5° | 130.0 | 130.5 | 130.0 | 131.2 | 131.2 | 131.1 |
| 180° | 132.2 | 132.2 | 132.2 | 132.2 | 132.2 | 132.2 |



TEST NUMBER: P1433835
 CATALOG NUMBER: EHBR1-36-UNV-TASM-L940-UPL12

CIE UGR TABLE:

| Reflectances: | | | | | | | | | | | |
|-----------------|------|------------------|-------|-------|-------|-------|----------------|-------|-------|-------|-------|
| Ceiling | | 0.7 | 0.7 | 0.5 | 0.5 | 0.3 | 0.7 | 0.7 | 0.5 | 0.5 | 0.3 |
| Wall | | 0.5 | 0.3 | 0.5 | 0.3 | 0.3 | 0.5 | 0.3 | 0.5 | 0.3 | 0.3 |
| Reference plane | | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 |
| Room dimensions | | Viewed crosswise | | | | | Viewed endwise | | | | |
| X=2H | Y=2H | 18.10 | 19.26 | 18.53 | 19.64 | 20.05 | 17.42 | 18.58 | 17.85 | 18.96 | 19.36 |
| | 3H | 19.65 | 20.68 | 20.10 | 21.08 | 21.53 | 19.27 | 20.30 | 19.71 | 20.70 | 21.15 |
| | 4H | 20.29 | 21.25 | 20.76 | 21.67 | 22.14 | 20.06 | 21.01 | 20.52 | 21.44 | 21.90 |
| | 6H | 20.77 | 21.65 | 21.25 | 22.09 | 22.57 | 20.70 | 21.58 | 21.18 | 22.02 | 22.50 |
| | 8H | 20.93 | 21.76 | 21.42 | 22.22 | 22.71 | 20.92 | 21.76 | 21.41 | 22.21 | 22.70 |
| | 12H | 21.00 | 21.80 | 21.49 | 22.25 | 22.76 | 21.05 | 21.85 | 21.54 | 22.30 | 22.81 |
| 4H | 2H | 18.52 | 19.48 | 18.99 | 19.90 | 20.37 | 18.00 | 18.96 | 18.47 | 19.38 | 19.85 |
| | 3H | 20.32 | 21.11 | 20.80 | 21.58 | 22.07 | 20.06 | 20.85 | 20.54 | 21.32 | 21.81 |
| | 4H | 21.10 | 21.81 | 21.59 | 22.29 | 22.82 | 20.97 | 21.68 | 21.46 | 22.16 | 22.69 |
| | 6H | 21.71 | 22.33 | 22.24 | 22.84 | 23.38 | 21.74 | 22.35 | 22.26 | 22.86 | 23.41 |
| | 8H | 21.91 | 22.48 | 22.44 | 22.99 | 23.54 | 22.01 | 22.58 | 22.54 | 23.09 | 23.64 |
| | 12H | 22.02 | 22.52 | 22.56 | 23.06 | 23.62 | 22.18 | 22.69 | 22.73 | 23.23 | 23.78 |
| 8H | 4H | 21.35 | 21.92 | 21.88 | 22.43 | 22.98 | 21.25 | 21.82 | 21.78 | 22.33 | 22.88 |
| | 6H | 22.09 | 22.55 | 22.65 | 23.11 | 23.67 | 22.15 | 22.62 | 22.71 | 23.18 | 23.74 |
| | 8H | 22.36 | 22.77 | 22.94 | 23.35 | 23.92 | 22.51 | 22.92 | 23.09 | 23.50 | 24.07 |
| | 12H | 22.53 | 22.90 | 23.11 | 23.45 | 24.10 | 22.76 | 23.12 | 23.33 | 23.67 | 24.32 |
| 12H | 4H | 21.36 | 21.86 | 21.90 | 22.41 | 22.96 | 21.26 | 21.77 | 21.81 | 22.31 | 22.86 |
| | 6H | 22.13 | 22.55 | 22.71 | 23.12 | 23.69 | 22.20 | 22.61 | 22.78 | 23.19 | 23.76 |
| | 8H | 22.45 | 22.81 | 23.03 | 23.37 | 24.02 | 22.61 | 22.97 | 23.18 | 23.52 | 24.17 |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-6

Test Date: 08/01/2025

Luminaire Tested: EHBR-60-L935-N

Data in this report applies to families of products including EHBR-60-L935-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-6
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L935-N**
 Description: Elevate Round Highbay at, 60000 lumens, 3500K 90CRI LEDs with N lens

Spectral Parameters

CCT (K): 3406
 CIE u': 0.2394
 CIE v': 0.5094
 Duv: -0.0028
 CIE x: 0.4076
 CIE y: 0.3856
 CIE z: 0.2068
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 582
 Purity: 38.0517
 Rf: 91.3
 Rg: 100

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 94.6 | | |
| R1: | 96.6 | R9: | 63.8 |
| R2: | 98.4 | R10: | 94.7 |
| R3: | 98.1 | R11: | 96.6 |
| R4: | 95.8 | R12: | 80.9 |
| R5: | 96.2 | R13: | 97.4 |
| R6: | 95.4 | R14: | 98.3 |
| R7: | 91.8 | R15: | 93.1 |
| R8: | 84.4 | | |



Test Conditions

Stabilization Time: 35M
 Operation Time: 1H 35M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-6

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | 76INCH SPHERE IN0058 | 6/16/2025 | 12/16/2025 |
| Power Meter | XITRON INXT2011004 | 1/21/2025 | 1/21/2026 |
| AC Power Source | CHROMA 61603 IN0063 | 10/22/2024 | 10/22/2025 |
| DC Power Source | AGILENT E3634A IN0208 | 10/22/2024 | 10/22/2025 |
| Sphere Thermometer | ONSET IN0085 | 10/22/2024 | 10/22/2025 |
| Room Thermometer | ONSET IN0046 | 10/22/2024 | 10/22/2025 |

REPORT NUMBER: SP1-2506-472-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-6

Photopic Flux vs. Wavelength




Photopic Lumens: NR

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 140 | NR | 620 | 338 | NR | 750 | 8 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 159 | NR | 625 | 339 | NR | 755 | 7 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 182 | NR | 630 | 1000 | NR | 760 | 5 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 202 | NR | 635 | 653 | NR | 765 | 5 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 216 | NR | 640 | 222 | NR | 770 | 4 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 228 | NR | 645 | 214 | NR | 775 | 3 | NR | 905 | 0 | NR |
| 390 | 0 | NR | 520 | 236 | NR | 650 | 185 | NR | 780 | 3 | NR | 910 | 0 | NR |
| 395 | 1 | NR | 525 | 242 | NR | 655 | 157 | NR | 785 | 3 | NR | 915 | 0 | NR |
| 400 | 2 | NR | 530 | 248 | NR | 660 | 133 | NR | 790 | 2 | NR | 920 | 0 | NR |
| 405 | 3 | NR | 535 | 253 | NR | 665 | 113 | NR | 795 | 2 | NR | 925 | 0 | NR |
| 410 | 4 | NR | 540 | 258 | NR | 670 | 103 | NR | 800 | 2 | NR | 930 | 0 | NR |
| 415 | 7 | NR | 545 | 264 | NR | 675 | 85 | NR | 805 | 1 | NR | 935 | 0 | NR |
| 420 | 13 | NR | 550 | 270 | NR | 680 | 72 | NR | 810 | 1 | NR | 940 | 0 | NR |
| 425 | 22 | NR | 555 | 278 | NR | 685 | 62 | NR | 815 | 1 | NR | 945 | 0 | NR |
| 430 | 38 | NR | 560 | 286 | NR | 690 | 53 | NR | 820 | 1 | NR | 950 | 0 | NR |
| 435 | 65 | NR | 565 | 295 | NR | 695 | 45 | NR | 825 | 1 | NR | 955 | 0 | NR |
| 440 | 108 | NR | 570 | 303 | NR | 700 | 39 | NR | 830 | 1 | NR | 960 | 0 | NR |
| 445 | 193 | NR | 575 | 311 | NR | 705 | 33 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 312 | NR | 580 | 319 | NR | 710 | 28 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 300 | NR | 585 | 326 | NR | 715 | 24 | NR | 845 | 0 | NR | 975 | 0 | NR |
| 460 | 214 | NR | 590 | 332 | NR | 720 | 20 | NR | 850 | 0 | NR | 980 | 0 | NR |
| 465 | 184 | NR | 595 | 333 | NR | 725 | 17 | NR | 855 | 0 | NR | 985 | 0 | NR |
| 470 | 153 | NR | 600 | 336 | NR | 730 | 15 | NR | 860 | 0 | NR | 990 | 0 | NR |
| 475 | 122 | NR | 605 | 337 | NR | 735 | 12 | NR | 865 | 0 | NR | 995 | 0 | NR |
| 480 | 115 | NR | 610 | 367 | NR | 740 | 10 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 125 | NR | 615 | 390 | NR | 745 | 9 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2506-472-6

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.62

| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 140 | NR | 620 | 338 | NR | 750 | 8 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 159 | NR | 625 | 339 | NR | 755 | 7 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 182 | NR | 630 | 1000 | NR | 760 | 5 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 202 | NR | 635 | 653 | NR | 765 | 5 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 216 | NR | 640 | 222 | NR | 770 | 4 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 228 | NR | 645 | 214 | NR | 775 | 3 | NR | 905 | 0 | NR |
| 390 | 0 | NR | 520 | 236 | NR | 650 | 185 | NR | 780 | 3 | NR | 910 | 0 | NR |
| 395 | 1 | NR | 525 | 242 | NR | 655 | 157 | NR | 785 | 3 | NR | 915 | 0 | NR |
| 400 | 2 | NR | 530 | 248 | NR | 660 | 133 | NR | 790 | 2 | NR | 920 | 0 | NR |
| 405 | 3 | NR | 535 | 253 | NR | 665 | 113 | NR | 795 | 2 | NR | 925 | 0 | NR |
| 410 | 4 | NR | 540 | 258 | NR | 670 | 103 | NR | 800 | 2 | NR | 930 | 0 | NR |
| 415 | 7 | NR | 545 | 264 | NR | 675 | 85 | NR | 805 | 1 | NR | 935 | 0 | NR |
| 420 | 13 | NR | 550 | 270 | NR | 680 | 72 | NR | 810 | 1 | NR | 940 | 0 | NR |
| 425 | 22 | NR | 555 | 278 | NR | 685 | 62 | NR | 815 | 1 | NR | 945 | 0 | NR |
| 430 | 38 | NR | 560 | 286 | NR | 690 | 53 | NR | 820 | 1 | NR | 950 | 0 | NR |
| 435 | 65 | NR | 565 | 295 | NR | 695 | 45 | NR | 825 | 1 | NR | 955 | 0 | NR |
| 440 | 108 | NR | 570 | 303 | NR | 700 | 39 | NR | 830 | 1 | NR | 960 | 0 | NR |
| 445 | 193 | NR | 575 | 311 | NR | 705 | 33 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 312 | NR | 580 | 319 | NR | 710 | 28 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 300 | NR | 585 | 326 | NR | 715 | 24 | NR | 845 | 0 | NR | 975 | 0 | NR |
| 460 | 214 | NR | 590 | 332 | NR | 720 | 20 | NR | 850 | 0 | NR | 980 | 0 | NR |
| 465 | 184 | NR | 595 | 333 | NR | 725 | 17 | NR | 855 | 0 | NR | 985 | 0 | NR |
| 470 | 153 | NR | 600 | 336 | NR | 730 | 15 | NR | 860 | 0 | NR | 990 | 0 | NR |
| 475 | 122 | NR | 605 | 337 | NR | 735 | 12 | NR | 865 | 0 | NR | 995 | 0 | NR |
| 480 | 115 | NR | 610 | 367 | NR | 740 | 10 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 125 | NR | 615 | 390 | NR | 745 | 9 | NR | 875 | 0 | NR | | | |

REPORT NUMBER: SP1-2506-472-6

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.3


| λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) | λ (nm) | Power W [^] /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360 | 0 | NR | 490 | 140 | NR | 620 | 338 | NR | 750 | 8 | NR | 880 | 0 | NR |
| 365 | 0 | NR | 495 | 159 | NR | 625 | 339 | NR | 755 | 7 | NR | 885 | 0 | NR |
| 370 | 0 | NR | 500 | 182 | NR | 630 | 1000 | NR | 760 | 5 | NR | 890 | 0 | NR |
| 375 | 0 | NR | 505 | 202 | NR | 635 | 653 | NR | 765 | 5 | NR | 895 | 0 | NR |
| 380 | 0 | NR | 510 | 216 | NR | 640 | 222 | NR | 770 | 4 | NR | 900 | 0 | NR |
| 385 | 0 | NR | 515 | 228 | NR | 645 | 214 | NR | 775 | 3 | NR | 905 | 0 | NR |
| 390 | 0 | NR | 520 | 236 | NR | 650 | 185 | NR | 780 | 3 | NR | 910 | 0 | NR |
| 395 | 1 | NR | 525 | 242 | NR | 655 | 157 | NR | 785 | 3 | NR | 915 | 0 | NR |
| 400 | 2 | NR | 530 | 248 | NR | 660 | 133 | NR | 790 | 2 | NR | 920 | 0 | NR |
| 405 | 3 | NR | 535 | 253 | NR | 665 | 113 | NR | 795 | 2 | NR | 925 | 0 | NR |
| 410 | 4 | NR | 540 | 258 | NR | 670 | 103 | NR | 800 | 2 | NR | 930 | 0 | NR |
| 415 | 7 | NR | 545 | 264 | NR | 675 | 85 | NR | 805 | 1 | NR | 935 | 0 | NR |
| 420 | 13 | NR | 550 | 270 | NR | 680 | 72 | NR | 810 | 1 | NR | 940 | 0 | NR |
| 425 | 22 | NR | 555 | 278 | NR | 685 | 62 | NR | 815 | 1 | NR | 945 | 0 | NR |
| 430 | 38 | NR | 560 | 286 | NR | 690 | 53 | NR | 820 | 1 | NR | 950 | 0 | NR |
| 435 | 65 | NR | 565 | 295 | NR | 695 | 45 | NR | 825 | 1 | NR | 955 | 0 | NR |
| 440 | 108 | NR | 570 | 303 | NR | 700 | 39 | NR | 830 | 1 | NR | 960 | 0 | NR |
| 445 | 193 | NR | 575 | 311 | NR | 705 | 33 | NR | 835 | 1 | NR | 965 | 0 | NR |
| 450 | 312 | NR | 580 | 319 | NR | 710 | 28 | NR | 840 | 1 | NR | 970 | 0 | NR |
| 455 | 300 | NR | 585 | 326 | NR | 715 | 24 | NR | 845 | 0 | NR | 975 | 0 | NR |
| 460 | 214 | NR | 590 | 332 | NR | 720 | 20 | NR | 850 | 0 | NR | 980 | 0 | NR |
| 465 | 184 | NR | 595 | 333 | NR | 725 | 17 | NR | 855 | 0 | NR | 985 | 0 | NR |
| 470 | 153 | NR | 600 | 336 | NR | 730 | 15 | NR | 860 | 0 | NR | 990 | 0 | NR |
| 475 | 122 | NR | 605 | 337 | NR | 735 | 12 | NR | 865 | 0 | NR | 995 | 0 | NR |
| 480 | 115 | NR | 610 | 367 | NR | 740 | 10 | NR | 870 | 0 | NR | 1000 | 0 | NR |
| 485 | 125 | NR | 615 | 390 | NR | 745 | 9 | NR | 875 | 0 | NR | | | |

Summary

$R_f = 91.3$
 $R_g = 100$
 $CIE R_a = 94.6$
 $R_9 = 63.8$



Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)



| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 94 | CES51 = 97 | CES76 = 90 |
| CES02 = 63 | CES27 = 92 | CES52 = 98 | CES77 = 86 |
| CES03 = 31 | CES28 = 97 | CES53 = 98 | CES78 = 86 |
| CES04 = 70 | CES29 = 97 | CES54 = 93 | CES79 = 90 |
| CES05 = 50 | CES30 = 92 | CES55 = 92 | CES80 = 91 |
| CES06 = 51 | CES31 = 97 | CES56 = 96 | CES81 = 74 |
| CES07 = 43 | CES32 = 89 | CES57 = 94 | CES82 = 96 |
| CES08 = 41 | CES33 = 99 | CES58 = 95 | CES83 = 94 |
| CES09 = 29 | CES34 = 94 | CES59 = 98 | CES84 = 95 |
| CES10 = 75 | CES35 = 97 | CES60 = 92 | CES85 = 79 |
| CES11 = 58 | CES36 = 81 | CES61 = 93 | CES86 = 79 |
| CES12 = 64 | CES37 = 96 | CES62 = 86 | CES87 = 92 |
| CES13 = 44 | CES38 = 87 | CES63 = 94 | CES88 = 98 |
| CES14 = 74 | CES39 = 99 | CES64 = 91 | CES89 = 84 |
| CES15 = 72 | CES40 = 97 | CES65 = 90 | CES90 = 96 |
| CES16 = 48 | CES41 = 96 | CES66 = 89 | CES91 = 75 |
| CES17 = 49 | CES42 = 94 | CES67 = 88 | CES92 = 76 |
| CES18 = 56 | CES43 = 93 | CES68 = 89 | CES93 = 86 |
| CES19 = 71 | CES44 = 99 | CES69 = 90 | CES94 = 74 |
| CES20 = 67 | CES45 = 97 | CES70 = 88 | CES95 = 83 |
| CES21 = 86 | CES46 = 97 | CES71 = 83 | CES96 = 92 |
| CES22 = 78 | CES47 = 91 | CES72 = 94 | CES97 = 96 |
| CES23 = 91 | CES48 = 91 | CES73 = 83 | CES98 = 95 |
| CES24 = 90 | CES49 = 96 | CES74 = 90 | CES99 = 92 |
| CES25 = 71 | CES50 = 98 | CES75 = 85 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)