

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1433554

Luminaire Tested: EHBR1-36-UNV-TASM-L935

Issue Date: 3/13/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1433554  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2601-654-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/13/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: EHBR1-36-UNV-TASM-L935  
Description: Elevate Round Highbay at, 36000 lumens, 3500K 90CRI LEDs with TASM lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 32692.1 lumens  
Efficiency: N/A  
Efficacy: 170.8 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.84 / 0.9  
Luminous Opening: Circular (Dia: 1.71' x H: 0')  
CIE Type: Direct

Input Watts (W): 191.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1433554  
CATALOG NUMBER: EHBR1-36-UNV-TASM-L935

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - · - 90°-270°    - · - 135°-315°



TEST NUMBER: P1433554  
 CATALOG NUMBER: EHBR1-36-UNV-TASM-L935

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	103	109	106	104	101	102	100	98	98	97	95	95	93	92	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	72	69	67
5	87	78	71	66	86	77	70	65	75	69	65	73	68	64	71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	57
7	78	67	60	56	76	67	60	56	65	59	55	64	59	55	63	58	55	53
8	74	63	56	52	72	62	56	52	61	55	51	60	55	51	59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	137303	137303	137303	137303
5°	137357	146535	137357	130229
10°	136561	151285	136561	124062
15°	133423	141539	133423	115372
20°	125659	114291	125659	103485
25°	112044	79775	112044	87369
30°	91703	52315	91703	65892
35°	66350	34178	66350	44251
40°	43319	23789	43319	28182
45°	27796	18635	27796	20306
50°	20917	16046	20917	17139
55°	17353	14854	17353	15373
60°	15335	14439	15335	14527
65°	14359	14304	14359	14243
70°	14137	14558	14137	14370
75°	14026	14942	14026	14494
80°	13714	15702	13714	14679
85°	11547	14591	11547	13912

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 39079 cd/sqm



TEST NUMBER: P1433554  
 CATALOG NUMBER: EHBR1-36-UNV-TASM-L935

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	2780.1	8.5
10°-20°	7563.3	23.1
20°-30°	8870.2	27.1
30°-40°	6168.7	18.9
40°-50°	3065.6	9.4
50°-60°	1833.5	5.6
60°-70°	1290.5	3.9
70°-80°	831.3	2.5
80°-90°	264.0	0.8
90°-100°	1.5	0.0
100°-110°	1.8	0.0
110°-120°	1.9	0.0
120°-130°	2.4	0.0
130°-140°	3.2	0.0
140°-150°	3.9	0.0
150°-160°	4.3	0.0
160°-170°	4.2	0.0
170°-180°	1.8	0.0
0°-30°	19213.6	58.8
0°-40°	25382.3	77.6
0°-60°	30281.4	92.6
0°-90°	32667.2	99.9
90°-120°	5.2	0.0
90°-150°	14.6	0.0
90°-180°	25.0	0.1
0°-180°	32692.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	29238	29238	29238	29238	29238	
5°	29138	31085	29138	27626	29138	2765
15°	27443	29113	27443	23730	27443	7669
25°	21624	15396	21624	16862	21624	9790
35°	11574	5962	11574	7719	11574	7225
45°	4185	2806	4185	3058	4185	3425
55°	2120	1814	2120	1878	2120	1938
65°	1292	1287	1292	1282	1292	1298
75°	773	824	773	799	773	811
85°	214	271	214	258	214	238
90°	0	4	0	0	0	10
95°	1	4	1	0	1	1
105°	1	5	1	1	1	1
115°	2	5	2	1	2	1
125°	2	5	2	2	2	2
135°	4	6	4	2	4	3
145°	7	7	7	6	7	4
155°	9	10	9	10	9	4
165°	15	18	15	15	15	4
175°	19	24	19	19	19	2
180°	20	20	20	20	20	



TEST NUMBER: P1433554  
 CATALOG NUMBER: EHBR1-36-UNV-TASM-L935

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	29237.8	29237.8	29237.8	29237.8	29237.8	29237.8	29237.8	29237.8	29237.8	29237.8	29237.8
2.5°	29220.7	29598.5	29904.4	30106.2	30205.9	30106.2	29904.4	29598.5	29220.7	28845.1	28586.9
5°	29138.0	29894.6	30535.4	30954.9	31084.8	30954.9	30535.4	29894.6	29138.0	28423.1	27948.8
7.5°	28940.0	30118.8	31071.1	31560.7	31680.2	31560.7	31071.1	30118.8	28940.0	27927.9	27328.7
10°	28637.9	30260.2	31360.6	31711.4	31725.7	31711.4	31360.6	30260.2	28637.9	27274.5	26567.7
12.5°	28156.0	30209.8	31263.5	31148.4	30886.8	31148.4	31263.5	30209.8	28156.0	26476.2	25584.7
15°	27443.3	29911.0	30648.9	29711.9	29112.7	29711.9	30648.9	29911.0	27443.3	25398.4	24364.3
17.5°	26438.9	29351.8	29366.0	27512.4	26381.9	27512.4	29366.0	29351.8	26438.9	24080.3	22941.6
20°	25144.5	28454.9	27599.6	24209.2	22869.8	24209.2	27599.6	28454.9	25144.5	22522.2	21404.9
22.5°	23521.6	27245.4	25139.5	20886.2	19058.9	20886.2	25139.5	27245.4	23521.6	20710.2	19547.4
25°	21623.6	25763.4	22493.1	17265.6	15396.0	17265.6	22493.1	25763.4	21623.6	18551.2	17499.7
27.5°	19391.1	23885.1	19675.2	14108.7	12383.9	14108.7	19675.2	23885.1	19391.1	16322.0	15248.0
30°	16911.4	21477.2	16742.5	11235.9	9647.6	11235.9	16742.5	21477.2	16911.4	13817.6	12855.9
32.5°	14135.0	19117.0	13926.1	9002.8	7657.4	9002.8	13926.1	19117.0	14135.0	11427.7	10422.8
35°	11573.6	16164.1	11386.7	7074.1	5961.7	7074.1	11386.7	16164.1	11573.6	9171.7	8184.9
37.5°	9082.9	13374.1	9076.9	5696.4	4835.5	5696.4	9076.9	13374.1	9082.9	7130.6	6329.5
40°	7066.4	10457.3	7111.9	4547.2	3880.5	4547.2	7111.9	10457.3	7066.4	5425.5	4912.9
42.5°	5354.2	7996.3	5590.0	3732.0	3296.1	3732.0	5590.0	7996.3	5354.2	4274.7	3891.0
45°	4185.3	5884.3	4365.2	3148.6	2806.0	3148.6	4365.2	5884.3	4185.3	3442.5	3184.8
47.5°	3408.5	4547.8	3537.9	2700.7	2460.6	2700.7	3537.9	4547.8	3408.5	2911.8	2718.8
50°	2863.0	3489.6	2937.5	2357.5	2196.3	2357.5	2937.5	3489.6	2863.0	2493.4	2364.6
52.5°	2459.4	2846.0	2501.7	2100.9	1992.4	2100.9	2501.7	2846.0	2459.4	2181.5	2101.4
55°	2119.5	2392.5	2175.5	1889.2	1814.2	1889.2	2175.5	2392.5	2119.5	1941.4	1882.2
57.5°	1861.3	2029.6	1889.2	1708.9	1659.0	1708.9	1889.2	2029.6	1861.3	1727.6	1695.7
60°	1632.7	1757.7	1667.2	1551.5	1537.3	1551.5	1667.2	1757.7	1632.7	1554.3	1533.4
62.5°	1456.7	1535.7	1474.2	1410.1	1397.5	1410.1	1474.2	1535.7	1456.7	1396.4	1400.3
65°	1292.2	1365.7	1317.4	1282.9	1287.3	1282.9	1317.4	1365.7	1292.2	1264.2	1270.3
67.5°	1165.0	1203.4	1182.6	1162.8	1167.8	1162.8	1182.6	1203.4	1165.0	1137.6	1147.0
70°	1029.6	1070.7	1049.3	1052.1	1060.3	1052.1	1049.3	1070.7	1029.6	1021.4	1028.5
72.5°	900.3	932.1	924.9	931.4	940.2	931.4	924.9	932.1	900.3	899.2	899.7
75°	773.0	797.1	800.5	809.8	823.5	809.8	800.5	797.1	773.0	764.9	774.6
77.5°	634.3	661.7	672.1	684.7	705.0	684.7	672.1	661.7	634.3	639.8	644.8
80°	507.1	519.8	542.8	552.0	580.6	552.0	542.8	519.8	507.1	497.8	504.9
82.5°	371.1	382.7	402.4	420.0	436.4	420.0	402.4	382.7	371.1	366.8	367.3
85°	214.3	231.9	245.1	265.9	270.8	265.9	245.1	231.9	214.3	219.3	214.3
87.5°	75.1	80.6	92.1	100.3	100.9	100.3	92.1	80.6	75.1	76.8	69.6
90°	0.5	1.1	1.6	3.3	4.4	3.3	1.6	1.1	0.5	0.5	0.5
92.5°	0.5	1.1	1.6	3.3	4.4	3.3	1.6	1.1	0.5	0.5	0.5
95°	1.1	1.1	1.6	3.3	4.4	3.3	1.6	1.1	1.1	0.5	0.5
97.5°	1.1	1.1	1.6	3.3	4.4	3.3	1.6	1.1	1.1	0.5	0.5
100°	1.1	1.1	1.6	3.3	4.4	3.3	1.6	1.1	1.1	1.1	0.5
102.5°	1.1	1.6	2.2	3.8	4.4	3.8	2.2	1.6	1.1	1.1	0.5
105°	1.1	1.6	2.2	3.8	4.9	3.8	2.2	1.6	1.1	1.1	0.5
107.5°	1.1	1.6	2.2	3.8	4.9	3.8	2.2	1.6	1.1	1.1	1.1
110°	1.1	1.6	2.2	3.8	4.9	3.8	2.2	1.6	1.1	1.1	1.1



TEST NUMBER: P1433554  
 CATALOG NUMBER: EHBR1-36-UNV-TASM-L935

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	1.1	1.6	2.2	3.8	4.9	3.8	2.2	1.6	1.1	1.1	1.1
115°	1.6	1.6	2.2	3.8	4.9	3.8	2.2	1.6	1.6	1.1	1.1
117.5°	1.6	1.6	2.2	3.8	4.9	3.8	2.2	1.6	1.6	1.6	1.1
120°	1.6	1.6	2.7	3.8	4.9	3.8	2.7	1.6	1.6	1.6	1.1
122.5°	2.2	2.2	2.7	4.4	4.9	4.4	2.7	2.2	2.2	2.2	1.6
125°	2.2	2.2	3.3	4.4	5.4	4.4	3.3	2.2	2.2	2.7	2.2
127.5°	2.7	2.7	3.3	4.4	5.4	4.4	3.3	2.7	2.7	2.7	2.2
130°	3.3	2.7	3.3	4.9	5.4	4.9	3.3	2.7	3.3	3.3	2.7
132.5°	3.8	3.3	3.8	5.4	6.1	5.4	3.8	3.3	3.8	4.4	3.8
135°	4.4	3.3	4.4	4.9	6.1	4.9	4.4	3.3	4.4	4.9	3.8
137.5°	4.9	3.8	4.4	5.4	6.1	5.4	4.4	3.8	4.9	5.4	4.9
140°	5.4	4.4	4.4	5.4	6.6	5.4	4.4	4.4	5.4	5.4	5.4
142.5°	6.1	4.9	4.9	6.1	6.6	6.1	4.9	4.9	6.1	6.1	6.1
145°	6.6	6.1	5.4	6.1	7.2	6.1	5.4	6.1	6.6	6.1	6.6
147.5°	6.6	6.1	6.1	6.6	7.7	6.6	6.1	6.1	6.6	6.6	7.2
150°	7.2	7.2	6.6	7.2	8.2	7.2	6.6	7.2	7.2	7.2	7.7
152.5°	7.7	7.7	7.7	8.2	8.8	8.2	7.7	7.7	7.7	7.7	8.2
155°	8.8	8.8	8.8	9.3	9.9	9.3	8.8	8.8	8.8	8.2	9.3
157.5°	9.9	10.4	10.4	11.0	11.5	11.0	10.4	10.4	9.9	9.9	10.4
160°	12.1	12.1	12.6	13.1	13.7	13.1	12.6	12.1	12.1	11.5	12.1
162.5°	13.1	13.1	14.2	14.8	15.9	14.8	14.2	13.1	13.1	13.1	13.1
165°	14.8	14.8	15.9	17.0	18.1	17.0	15.9	14.8	14.8	14.2	14.2
167.5°	15.9	15.9	17.0	18.7	19.8	18.7	17.0	15.9	15.9	15.3	15.3
170°	16.4	17.0	18.1	19.8	20.8	19.8	18.1	17.0	16.4	16.4	15.9
172.5°	18.1	18.1	19.8	21.4	22.5	21.4	19.8	18.1	18.1	17.6	17.6
175°	19.2	19.8	20.8	22.5	23.6	22.5	20.8	19.8	19.2	18.7	18.7
177.5°	19.2	20.3	21.4	23.0	24.1	23.0	21.4	20.3	19.2	18.7	18.7
180°	20.3	20.3	20.3	20.3	20.3	20.3	20.3	20.3	20.3	20.3	20.3



TEST NUMBER: P1433554

CATALOG NUMBER: EHBR1-36-UNV-TASM-L935

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
0°	29237.8	29237.8	29237.8	29237.8	29237.8	29237.8
2.5°	28388.5	28369.9	28388.5	28586.9	28845.1	29220.7
5°	27728.9	27625.8	27728.9	27948.8	28423.1	29138.0
7.5°	26960.9	26901.1	26960.9	27328.7	27927.9	28940.0
10°	26152.2	26016.7	26152.2	26567.7	27274.5	28637.9
12.5°	25155.5	24976.2	25155.5	25584.7	26476.2	28156.0
15°	23887.9	23730.5	23887.9	24364.3	25398.4	27443.3
17.5°	22527.6	22385.1	22527.6	22941.6	24080.3	26438.9
20°	20819.3	20707.5	20819.3	21404.9	22522.2	25144.5
22.5°	19027.0	18922.4	19027.0	19547.4	20710.2	23521.6
25°	16918.5	16861.5	16918.5	17499.7	18551.2	21623.6
27.5°	14639.9	14543.0	14639.9	15248.0	16322.0	19391.1
30°	12312.1	12151.4	12312.1	12855.9	13817.6	16911.4
32.5°	10035.2	9919.5	10035.2	10422.8	11427.7	14135.0
35°	7834.5	7718.9	7834.5	8184.9	9171.7	11573.6
37.5°	6104.8	5900.3	6104.8	6329.5	7130.6	9082.9
40°	4630.0	4597.1	4630.0	4912.9	5425.5	7066.4
42.5°	3769.2	3679.9	3769.2	3891.0	4274.7	5354.2
45°	3092.7	3057.6	3092.7	3184.8	3442.5	4185.3
47.5°	2659.5	2674.9	2659.5	2718.8	2911.8	3408.5
50°	2336.6	2345.9	2336.6	2364.6	2493.4	2863.0
52.5°	2098.7	2090.5	2098.7	2101.4	2181.5	2459.4
55°	1888.2	1877.7	1888.2	1882.2	1941.4	2119.5
57.5°	1704.0	1711.6	1704.0	1695.7	1727.6	1861.3
60°	1539.5	1546.7	1539.5	1533.4	1554.3	1632.7
62.5°	1400.8	1405.2	1400.8	1400.3	1396.4	1456.7
65°	1276.8	1281.8	1276.8	1270.3	1264.2	1292.2
67.5°	1158.5	1158.5	1158.5	1147.0	1137.6	1165.0
70°	1047.2	1046.6	1047.2	1028.5	1021.4	1029.6
72.5°	913.4	926.5	913.4	899.7	899.2	900.3
75°	783.4	798.8	783.4	774.6	764.9	773.0
77.5°	651.8	675.5	651.8	644.8	639.8	634.3
80°	517.0	542.8	517.0	504.9	497.8	507.1
82.5°	382.1	401.3	382.1	367.3	366.8	371.1
85°	227.5	258.2	227.5	214.3	219.3	214.3
87.5°	73.0	93.2	73.0	69.6	76.8	75.1
90°	0.5	0.5	0.5	0.5	0.5	0.5
92.5°	0.5	0.5	0.5	0.5	0.5	0.5
95°	0.5	0.5	0.5	0.5	0.5	1.1
97.5°	0.5	1.1	0.5	0.5	0.5	1.1
100°	0.5	1.1	0.5	0.5	1.1	1.1
102.5°	0.5	1.1	0.5	0.5	1.1	1.1
105°	0.5	1.1	0.5	0.5	1.1	1.1
107.5°	0.5	1.1	0.5	1.1	1.1	1.1
110°	0.5	1.1	0.5	1.1	1.1	1.1



TEST NUMBER: P1433554  
 CATALOG NUMBER: EHBR1-36-UNV-TASM-L935

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.5	1.1	0.5	1.1	1.1	1.1
115°	0.5	1.1	0.5	1.1	1.1	1.6
117.5°	0.5	1.1	0.5	1.1	1.6	1.6
120°	0.5	1.1	0.5	1.1	1.6	1.6
122.5°	1.1	1.1	1.1	1.6	2.2	2.2
125°	1.1	1.6	1.1	2.2	2.7	2.2
127.5°	1.1	1.6	1.1	2.2	2.7	2.7
130°	1.6	1.6	1.6	2.7	3.3	3.3
132.5°	2.2	2.2	2.2	3.8	4.4	3.8
135°	2.7	2.2	2.7	3.8	4.9	4.4
137.5°	3.3	2.7	3.3	4.9	5.4	4.9
140°	4.4	3.8	4.4	5.4	5.4	5.4
142.5°	4.9	4.9	4.9	6.1	6.1	6.1
145°	6.1	6.1	6.1	6.6	6.1	6.6
147.5°	7.2	7.2	7.2	7.2	6.6	6.6
150°	8.2	8.2	8.2	7.7	7.2	7.2
152.5°	8.8	9.3	8.8	8.2	7.7	7.7
155°	9.9	10.4	9.9	9.3	8.2	8.8
157.5°	11.0	12.1	11.0	10.4	9.9	9.9
160°	12.6	13.1	12.6	12.1	11.5	12.1
162.5°	13.7	14.2	13.7	13.1	13.1	13.1
165°	14.8	15.3	14.8	14.2	14.2	14.8
167.5°	15.3	15.3	15.3	15.3	15.3	15.9
170°	15.9	16.4	15.9	15.9	16.4	16.4
172.5°	17.0	17.6	17.0	17.6	17.6	18.1
175°	18.1	18.7	18.1	18.7	18.7	19.2
177.5°	18.7	19.2	18.7	18.7	18.7	19.2
180°	20.3	20.3	20.3	20.3	20.3	20.3



TEST NUMBER: P1433554  
 CATALOG NUMBER: EHBR1-36-UNV-TASM-L935

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.75	19.96	19.12	20.27	20.59	18.07	19.28	18.44	19.59	19.91
	3H	20.39	21.46	20.77	21.80	22.16	20.02	21.09	20.40	21.43	21.79
	4H	21.10	22.10	21.50	22.45	22.84	20.88	21.88	21.29	22.23	22.62
	6H	21.67	22.59	22.09	22.96	23.36	21.63	22.55	22.05	22.92	23.32
	8H	21.87	22.74	22.31	23.13	23.54	21.92	22.79	22.35	23.18	23.59
	12H	21.99	22.83	22.43	23.21	23.64	22.11	22.95	22.55	23.33	23.76
4H	2H	19.21	20.21	19.62	20.57	20.96	18.70	19.70	19.11	20.05	20.44
	3H	21.12	21.95	21.54	22.36	22.76	20.88	21.70	21.29	22.11	22.52
	4H	21.98	22.72	22.42	23.14	23.59	21.87	22.61	22.31	23.04	23.48
	6H	22.71	23.34	23.17	23.79	24.26	22.77	23.41	23.24	23.86	24.33
	8H	22.96	23.56	23.44	24.01	24.48	23.11	23.71	23.59	24.16	24.63
	12H	23.13	23.66	23.62	24.14	24.62	23.37	23.89	23.85	24.37	24.85
8H	4H	22.29	22.89	22.76	23.34	23.81	22.21	22.81	22.69	23.26	23.73
	6H	23.17	23.65	23.67	24.15	24.63	23.27	23.75	23.77	24.25	24.74
	8H	23.52	23.95	24.04	24.47	24.96	23.72	24.15	24.24	24.67	25.16
	12H	23.78	24.16	24.30	24.65	25.23	24.07	24.45	24.59	24.95	25.52
12H	4H	22.32	22.84	22.81	23.33	23.81	22.25	22.77	22.73	23.26	23.73
	6H	23.24	23.67	23.76	24.19	24.68	23.34	23.77	23.87	24.29	24.79
	8H	23.65	24.03	24.17	24.53	25.10	23.86	24.23	24.38	24.73	25.31

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-6

Test Date: 08/01/2025

Luminaire Tested: EHBR-60-L935-N

Data in this report applies to families of products including EHBR-60-L935-N

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2506-472-6  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 08/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **EHBR-60-L935-N**  
 Description: Elevate Round Highbay at, 60000 lumens, 3500K 90CRI LEDs with N lens

**Spectral Parameters**

CCT (K): 3406  
 CIE u': 0.2394  
 CIE v': 0.5094  
 Duv: -0.0028  
 CIE x: 0.4076  
 CIE y: 0.3856  
 CIE z: 0.2068  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 582  
 Purity: 38.0517  
 Rf: 91.3  
 Rg: 100

CRI (Ra):	94.6		
R1:	96.6	R9:	63.8
R2:	98.4	R10:	94.7
R3:	98.1	R11:	96.6
R4:	95.8	R12:	80.9
R5:	96.2	R13:	97.4
R6:	95.4	R14:	98.3
R7:	91.8	R15:	93.1
R8:	84.4		



**Test Conditions**

Stabilization Time: 35M  
 Operation Time: 1H 35M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-6

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-6

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-6

**Photopic Flux vs. Wavelength**




**Photopic Lumens: NR**

$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)	$\lambda$ (nm)	Power W <sup>^</sup> /nm	Lumens ( $\phi$ /nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-6

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: NR**

**S/P: 1.62**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-6

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.3

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

**Summary**

$R_f = 91.3$   
 $R_g = 100$   
 $CIE R_a = 94.6$   
 $R_9 = 63.8$



**Color Vector Graphics**




**Individual Sample Fidelity Index ( $R_{f,i}$ )**

CES01 = 86	CES26 = 94	CES51 = 97	CES76 = 90
CES02 = 63	CES27 = 92	CES52 = 98	CES77 = 86
CES03 = 31	CES28 = 97	CES53 = 98	CES78 = 86
CES04 = 70	CES29 = 97	CES54 = 93	CES79 = 90
CES05 = 50	CES30 = 92	CES55 = 92	CES80 = 91
CES06 = 51	CES31 = 97	CES56 = 96	CES81 = 74
CES07 = 43	CES32 = 89	CES57 = 94	CES82 = 96
CES08 = 41	CES33 = 99	CES58 = 95	CES83 = 94
CES09 = 29	CES34 = 94	CES59 = 98	CES84 = 95
CES10 = 75	CES35 = 97	CES60 = 92	CES85 = 79
CES11 = 58	CES36 = 81	CES61 = 93	CES86 = 79
CES12 = 64	CES37 = 96	CES62 = 86	CES87 = 92
CES13 = 44	CES38 = 87	CES63 = 94	CES88 = 98
CES14 = 74	CES39 = 99	CES64 = 91	CES89 = 84
CES15 = 72	CES40 = 97	CES65 = 90	CES90 = 96
CES16 = 48	CES41 = 96	CES66 = 89	CES91 = 75
CES17 = 49	CES42 = 94	CES67 = 88	CES92 = 76
CES18 = 56	CES43 = 93	CES68 = 89	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 90	CES94 = 74
CES20 = 67	CES45 = 97	CES70 = 88	CES95 = 83
CES21 = 86	CES46 = 97	CES71 = 83	CES96 = 92
CES22 = 78	CES47 = 91	CES72 = 94	CES97 = 96
CES23 = 91	CES48 = 91	CES73 = 83	CES98 = 95
CES24 = 90	CES49 = 96	CES74 = 90	CES99 = 92
CES25 = 71	CES50 = 98	CES75 = 85	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)