

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: METALUX

Report Number:

Luminaire Tested: EHBR1-24-UNV-N-L950-UPL12

Issue Date: 3/20/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: REPORT IS A COMBINATION OF REPORTS P1431716 AND P1431635  
Test Lab: INNOVATION CENTER  
Issue Date: 3/20/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: METALUX  
Catalog Number: EHBR1-24-UNV-N-L950-UPL12  
Description: Elevate Round Highbay at, 24000 lumens, 5000K 90CRI LEDs with N lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 24422.3 lumens  
Efficiency: N/A  
Efficacy: 180.0 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.8  
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')  
CIE Type: Direct  
  
Input Watts (W): 135.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER:  
CATALOG NUMBER: EHBR1-24-UNV-N-L950-UPL12

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°



TEST NUMBER:

CATALOG NUMBER: EHBR1-24-UNV-N-L950-UPL12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	118	118	118	118	115	115	115	115	109	109	109	103	103	103	98	98	98	98	98	98	96
1	111	108	105	102	108	105	103	100	100	98	96	96	94	93	92	90	89	89	89	89	87
2	105	99	94	90	102	97	93	89	93	89	86	89	86	84	86	83	81	81	81	81	79
3	99	91	85	81	96	89	84	80	86	82	78	83	79	76	80	77	75	75	75	75	73
4	93	84	78	73	91	83	77	73	80	75	71	78	73	70	75	72	69	69	69	69	67
5	88	79	72	67	86	77	71	67	75	70	66	73	68	65	71	67	64	64	64	64	62
6	83	73	67	62	81	72	66	62	70	65	61	68	64	60	67	63	59	59	59	59	58
7	79	69	62	58	77	68	62	57	66	61	57	65	60	56	63	59	56	56	56	56	54
8	75	65	58	54	73	64	58	54	62	57	53	61	56	53	60	55	52	52	52	52	51
9	71	61	55	51	70	60	54	50	59	54	50	58	53	50	57	52	49	49	49	49	48
10	68	58	52	48	67	57	51	47	56	51	47	55	50	47	54	50	46	46	46	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	127853	127853	127853
5°	125371	125371	125371
10°	118992	118992	118992
15°	108267	108267	108267
20°	92869	92869	92869
25°	73056	73056	73056
30°	50135	50135	50135
35°	29782	29782	29782
40°	17622	17622	17622
45°	12650	12650	12650
50°	10398	10398	10398
55°	9450	9450	9450
60°	9045	9045	9045
65°	8628	8628	8628
70°	8024	8024	8024
75°	7254	7254	7254
80°	6020	6020	6020
85°	3811	3811	3811

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12650 cd/sqm



TEST NUMBER:

CATALOG NUMBER: EHBR1-24-UNV-N-L950-UPL12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	2507.9	10.3
10°-20°	6295.2	25.8
20°-30°	6582.3	27.0
30°-40°	3566.5	14.6
40°-50°	1640.8	6.7
50°-60°	1156.3	4.7
60°-70°	889.8	3.6
70°-80°	539.4	2.2
80°-90°	153.9	0.6
90°-100°	31.2	0.1
100°-110°	194.8	0.8
110°-120°	348.3	1.4
120°-130°	204.4	0.8
130°-140°	125.4	0.5
140°-150°	86.9	0.4
150°-160°	56.5	0.2
160°-170°	32.2	0.1
170°-180°	10.6	0.0
0°-30°	15385.4	63.0
0°-40°	18951.8	77.6
0°-60°	21748.9	89.1
0°-90°	23332.1	95.5
90°-120°	574.2	2.4
90°-150°	990.9	4.1
90°-180°	1090.0	4.5
0°-180°	24422.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	27225	27225	27225	27225	27225	
5°	26769	26769	26769	26769	26769	2508
15°	22714	22714	22714	22714	22714	6295
25°	14589	14589	14589	14589	14589	6582
35°	5466	5466	5466	5466	5466	3566
45°	2047	2047	2047	2047	2047	1641
55°	1277	1277	1277	1277	1277	1156
65°	901	901	901	901	901	890
75°	511	511	511	511	511	539
85°	131	131	131	131	131	145
90°	9	14	23	15	9	10
95°	14	23	50	25	16	13
105°	68	134	343	148	90	91
115°	313	330	405	388	386	289
125°	226	211	217	220	246	206
135°	165	160	165	155	155	129
145°	135	134	142	140	139	86
155°	119	117	123	123	123	55
165°	111	111	114	114	114	32
175°	110	110	112	112	112	11
180°	111	111	111	111	111	



TEST NUMBER:

CATALOG NUMBER: EHBR1-24-UNV-N-L950-UPL12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	27225.3	27225.3	27225.3	27225.3	27225.3
2.5°	27128.7	27128.7	27128.7	27128.7	27128.7
5°	26768.6	26768.6	26768.6	26768.6	26768.6
7.5°	26153.7	26153.7	26153.7	26153.7	26153.7
10°	25281.4	25281.4	25281.4	25281.4	25281.4
12.5°	24154.0	24154.0	24154.0	24154.0	24154.0
15°	22713.8	22713.8	22713.8	22713.8	22713.8
17.5°	21042.8	21042.8	21042.8	21042.8	21042.8
20°	19087.3	19087.3	19087.3	19087.3	19087.3
22.5°	16910.0	16910.0	16910.0	16910.0	16910.0
25°	14589.2	14589.2	14589.2	14589.2	14589.2
27.5°	12128.9	12128.9	12128.9	12128.9	12128.9
30°	9643.5	9643.5	9643.5	9643.5	9643.5
32.5°	7401.0	7401.0	7401.0	7401.0	7401.0
35°	5466.1	5466.1	5466.1	5466.1	5466.1
37.5°	4013.4	4013.4	4013.4	4013.4	4013.4
40°	3054.3	3054.3	3054.3	3054.3	3054.3
42.5°	2449.1	2449.1	2449.1	2449.1	2449.1
45°	2046.7	2046.7	2046.7	2046.7	2046.7
47.5°	1756.7	1756.7	1756.7	1756.7	1756.7
50°	1549.6	1549.6	1549.6	1549.6	1549.6
52.5°	1398.4	1398.4	1398.4	1398.4	1398.4
55°	1277.1	1277.1	1277.1	1277.1	1277.1
57.5°	1178.6	1178.6	1178.6	1178.6	1178.6
60°	1087.4	1087.4	1087.4	1087.4	1087.4
62.5°	996.4	996.4	996.4	996.4	996.4
65°	900.6	900.6	900.6	900.6	900.6
67.5°	802.9	802.9	802.9	802.9	802.9
70°	704.1	704.1	704.1	704.1	704.1
72.5°	607.9	607.9	607.9	607.9	607.9
75°	511.0	511.0	511.0	511.0	511.0
77.5°	416.0	416.0	416.0	416.0	416.0
80°	316.7	316.7	316.7	316.7	316.7
82.5°	221.8	221.8	221.8	221.8	221.8
85°	131.0	131.0	131.0	131.0	131.0
87.5°	46.9	46.9	46.9	46.9	46.9
90°	8.8	13.8	23.2	15.1	8.8
92.5°	11.9	20.0	36.2	18.7	10.6
95°	13.8	23.0	50.5	25.0	15.6
97.5°	17.5	25.6	58.1	30.6	24.3
100°	23.0	29.9	90.5	37.4	32.4
102.5°	39.3	63.6	192.2	70.5	49.3
105°	68.0	134.2	342.6	147.9	89.8
107.5°	117.9	240.3	451.7	262.1	170.4
110°	220.3	318.9	473.7	360.0	272.7



TEST NUMBER:

CATALOG NUMBER: EHBR1-24-UNV-N-L950-UPL12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	297.7	342.6	453.7	397.5	355.0
115°	313.3	329.5	405.0	388.1	385.7
117.5°	302.6	300.8	343.9	348.8	372.6
120°	280.2	267.7	287.0	304.5	336.3
122.5°	252.1	237.1	245.8	258.9	290.8
125°	225.9	210.9	216.6	219.6	246.5
127.5°	202.8	192.8	196.0	192.2	209.1
130°	187.2	178.5	182.8	174.1	182.2
132.5°	174.1	168.4	173.5	162.9	165.4
135°	164.7	159.7	165.4	155.3	154.8
137.5°	156.6	152.3	157.9	150.4	148.5
140°	149.1	145.4	151.6	146.1	144.8
142.5°	141.0	138.5	146.1	142.2	141.0
145°	135.4	133.5	141.7	139.7	139.2
147.5°	130.4	129.1	136.7	136.0	136.0
150°	126.1	124.8	132.3	131.7	132.3
152.5°	121.7	120.4	127.3	126.6	127.3
155°	118.6	117.3	122.9	122.9	122.9
157.5°	116.0	115.4	119.9	119.9	119.9
160°	114.2	113.5	117.3	117.3	116.7
162.5°	112.3	111.7	116.0	115.4	115.4
165°	111.0	111.0	114.2	114.2	113.5
167.5°	111.0	110.5	113.5	113.5	113.0
170°	110.5	110.5	113.0	112.3	111.7
172.5°	110.5	110.5	113.0	112.3	111.7
175°	109.8	109.8	111.7	111.7	111.7
177.5°	110.5	110.5	111.7	111.7	111.0
180°	111.0	111.0	111.0	111.0	111.0



TEST NUMBER: CATALOG  
 CATALOG NUMBER: EHBR1-24-UNV-N-L950-UPL12

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.92	17.01	16.37	17.42	17.85	15.92	17.01	16.37	17.42	17.85
	3H	17.70	18.67	18.16	19.10	19.58	17.70	18.67	18.16	19.10	19.58
	4H	18.36	19.27	18.84	19.71	20.21	18.36	19.27	18.84	19.71	20.21
	6H	18.82	19.65	19.31	20.11	20.62	18.82	19.65	19.31	20.11	20.62
	8H	18.94	19.73	19.45	20.21	20.73	18.94	19.73	19.45	20.21	20.73
	12H	18.99	19.75	19.51	20.22	20.76	18.99	19.75	19.51	20.22	20.76
4H	2H	16.46	17.37	16.95	17.81	18.31	16.46	17.37	16.95	17.81	18.31
	3H	18.43	19.18	18.93	19.68	20.19	18.43	19.18	18.93	19.68	20.19
	4H	19.21	19.88	19.72	20.38	20.94	19.21	19.88	19.72	20.38	20.94
	6H	19.78	20.36	20.32	20.89	21.46	19.78	20.36	20.32	20.89	21.46
	8H	19.94	20.48	20.48	21.01	21.58	19.94	20.48	20.48	21.01	21.58
12H	20.02	20.49	20.58	21.06	21.64	20.02	20.49	20.58	21.06	21.64	
8H	4H	19.44	19.98	19.98	20.51	21.08	19.44	19.98	19.98	20.51	21.08
	6H	20.12	20.55	20.70	21.13	21.72	20.12	20.55	20.70	21.13	21.72
	8H	20.34	20.73	20.94	21.32	21.92	20.34	20.73	20.94	21.32	21.92
	12H	20.48	20.82	21.07	21.39	22.07	20.48	20.82	21.07	21.39	22.07
12H	4H	19.43	19.91	20.00	20.47	21.05	19.43	19.91	20.00	20.47	21.05
	6H	20.14	20.53	20.74	21.12	21.72	20.14	20.53	20.74	21.12	21.72
	8H	20.41	20.74	21.00	21.32	21.99	20.41	20.74	21.00	21.32	21.99

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-8

Test Date: 08/04/2025

Luminaire Tested: EHBR-60-L950-N

Data in this report applies to families of products including EHBR-60-L950-N

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2506-472-8  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 08/05/2025  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: Metalux  
 Catalog Number: **EHBR-60-L950-N**  
 Description: Elevate Round Highbay at, 60000 lumens, 5000K 90CRI LEDs with N lens

**Spectral Parameters**

CCT (K): 4901  
 CIE u': 0.2131  
 CIE v': 0.4853  
 Duv: -0.0008  
 CIE x: 0.3477  
 CIE y: 0.3520  
 CIE z: 0.3003  
 Peak Wavelength (nm): 630  
 Dominant Wavelength (nm): 574  
 Purity: 9.953987  
 Rf: 90.7  
 Rg: 100.5

CRI (Ra):	94.3		
R1:	95.8	R9:	72.3
R2:	96.5	R10:	89.1
R3:	94.4	R11:	94.9
R4:	95.3	R12:	68.4
R5:	94.1	R13:	96.4
R6:	92.5	R14:	96.4
R7:	95.5	R15:	93.9
R8:	90.1		



**Test Conditions**

Stabilization Time: 35M  
 Operation Time: 1H 35M  
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-8

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-8

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-8

**Photopic Flux vs. Wavelength**



**Photopic Lumens: NR**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	221	NR	620	326	NR	750	7	NR	880	0	NR
365	0	NR	495	250	NR	625	325	NR	755	6	NR	885	0	NR
370	0	NR	500	284	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	311	NR	635	643	NR	765	4	NR	895	0	NR
380	0	NR	510	329	NR	640	206	NR	770	4	NR	900	0	NR
385	1	NR	515	344	NR	645	199	NR	775	3	NR	905	0	NR
390	2	NR	520	353	NR	650	172	NR	780	3	NR	910	0	NR
395	3	NR	525	357	NR	655	143	NR	785	2	NR	915	0	NR
400	5	NR	530	362	NR	660	122	NR	790	2	NR	920	0	NR
405	6	NR	535	365	NR	665	102	NR	795	2	NR	925	0	NR
410	9	NR	540	367	NR	670	94	NR	800	2	NR	930	0	NR
415	15	NR	545	369	NR	675	76	NR	805	1	NR	935	0	NR
420	26	NR	550	370	NR	680	65	NR	810	1	NR	940	0	NR
425	47	NR	555	372	NR	685	56	NR	815	1	NR	945	0	NR
430	81	NR	560	372	NR	690	48	NR	820	1	NR	950	0	NR
435	143	NR	565	371	NR	695	41	NR	825	1	NR	955	0	NR
440	243	NR	570	370	NR	700	35	NR	830	1	NR	960	0	NR
445	434	NR	575	367	NR	705	30	NR	835	1	NR	965	0	NR
450	675	NR	580	365	NR	710	25	NR	840	1	NR	970	0	NR
455	615	NR	585	361	NR	715	22	NR	845	0	NR	975	0	NR
460	418	NR	590	356	NR	720	19	NR	850	0	NR	980	0	NR
465	344	NR	595	348	NR	725	16	NR	855	0	NR	985	0	NR
470	272	NR	600	343	NR	730	13	NR	860	0	NR	990	0	NR
475	206	NR	605	337	NR	735	11	NR	865	0	NR	995	0	NR
480	190	NR	610	362	NR	740	10	NR	870	0	NR	1000	0	NR
485	202	NR	615	381	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-8

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: NR**

**S/P: 2.04**

λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	221	NR	620	326	NR	750	7	NR	880	0	NR
365	0	NR	495	250	NR	625	325	NR	755	6	NR	885	0	NR
370	0	NR	500	284	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	311	NR	635	643	NR	765	4	NR	895	0	NR
380	0	NR	510	329	NR	640	206	NR	770	4	NR	900	0	NR
385	1	NR	515	344	NR	645	199	NR	775	3	NR	905	0	NR
390	2	NR	520	353	NR	650	172	NR	780	3	NR	910	0	NR
395	3	NR	525	357	NR	655	143	NR	785	2	NR	915	0	NR
400	5	NR	530	362	NR	660	122	NR	790	2	NR	920	0	NR
405	6	NR	535	365	NR	665	102	NR	795	2	NR	925	0	NR
410	9	NR	540	367	NR	670	94	NR	800	2	NR	930	0	NR
415	15	NR	545	369	NR	675	76	NR	805	1	NR	935	0	NR
420	26	NR	550	370	NR	680	65	NR	810	1	NR	940	0	NR
425	47	NR	555	372	NR	685	56	NR	815	1	NR	945	0	NR
430	81	NR	560	372	NR	690	48	NR	820	1	NR	950	0	NR
435	143	NR	565	371	NR	695	41	NR	825	1	NR	955	0	NR
440	243	NR	570	370	NR	700	35	NR	830	1	NR	960	0	NR
445	434	NR	575	367	NR	705	30	NR	835	1	NR	965	0	NR
450	675	NR	580	365	NR	710	25	NR	840	1	NR	970	0	NR
455	615	NR	585	361	NR	715	22	NR	845	0	NR	975	0	NR
460	418	NR	590	356	NR	720	19	NR	850	0	NR	980	0	NR
465	344	NR	595	348	NR	725	16	NR	855	0	NR	985	0	NR
470	272	NR	600	343	NR	730	13	NR	860	0	NR	990	0	NR
475	206	NR	605	337	NR	735	11	NR	865	0	NR	995	0	NR
480	190	NR	610	362	NR	740	10	NR	870	0	NR	1000	0	NR
485	202	NR	615	381	NR	745	8	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-8

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: NR**

**M/P: 4.41**


λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)	λ (nm)	Power W <sup>^</sup> /nm	Lumens (φ/nm)
360	0	NR	490	221	NR	620	326	NR	750	7	NR	880	0	NR
365	0	NR	495	250	NR	625	325	NR	755	6	NR	885	0	NR
370	0	NR	500	284	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	311	NR	635	643	NR	765	4	NR	895	0	NR
380	0	NR	510	329	NR	640	206	NR	770	4	NR	900	0	NR
385	1	NR	515	344	NR	645	199	NR	775	3	NR	905	0	NR
390	2	NR	520	353	NR	650	172	NR	780	3	NR	910	0	NR
395	3	NR	525	357	NR	655	143	NR	785	2	NR	915	0	NR
400	5	NR	530	362	NR	660	122	NR	790	2	NR	920	0	NR
405	6	NR	535	365	NR	665	102	NR	795	2	NR	925	0	NR
410	9	NR	540	367	NR	670	94	NR	800	2	NR	930	0	NR
415	15	NR	545	369	NR	675	76	NR	805	1	NR	935	0	NR
420	26	NR	550	370	NR	680	65	NR	810	1	NR	940	0	NR
425	47	NR	555	372	NR	685	56	NR	815	1	NR	945	0	NR
430	81	NR	560	372	NR	690	48	NR	820	1	NR	950	0	NR
435	143	NR	565	371	NR	695	41	NR	825	1	NR	955	0	NR
440	243	NR	570	370	NR	700	35	NR	830	1	NR	960	0	NR
445	434	NR	575	367	NR	705	30	NR	835	1	NR	965	0	NR
450	675	NR	580	365	NR	710	25	NR	840	1	NR	970	0	NR
455	615	NR	585	361	NR	715	22	NR	845	0	NR	975	0	NR
460	418	NR	590	356	NR	720	19	NR	850	0	NR	980	0	NR
465	344	NR	595	348	NR	725	16	NR	855	0	NR	985	0	NR
470	272	NR	600	343	NR	730	13	NR	860	0	NR	990	0	NR
475	206	NR	605	337	NR	735	11	NR	865	0	NR	995	0	NR
480	190	NR	610	362	NR	740	10	NR	870	0	NR	1000	0	NR
485	202	NR	615	381	NR	745	8	NR	875	0	NR			

**Summary**

$R_f = 90.7$   
 $R_g = 100.5$   
 $CIE R_a = 94.3$   
 $R_9 = 72.3$



**Color Vector Graphics**



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

CES01 = 85	CES26 = 91	CES51 = 98	CES76 = 83
CES02 = 61	CES27 = 92	CES52 = 98	CES77 = 87
CES03 = 31	CES28 = 94	CES53 = 97	CES78 = 80
CES04 = 69	CES29 = 94	CES54 = 93	CES79 = 94
CES05 = 48	CES30 = 93	CES55 = 92	CES80 = 91
CES06 = 50	CES31 = 95	CES56 = 95	CES81 = 84
CES07 = 41	CES32 = 86	CES57 = 94	CES82 = 96
CES08 = 40	CES33 = 99	CES58 = 94	CES83 = 96
CES09 = 29	CES34 = 90	CES59 = 97	CES84 = 93
CES10 = 73	CES35 = 94	CES60 = 92	CES85 = 83
CES11 = 56	CES36 = 81	CES61 = 92	CES86 = 86
CES12 = 62	CES37 = 92	CES62 = 86	CES87 = 91
CES13 = 43	CES38 = 88	CES63 = 92	CES88 = 98
CES14 = 74	CES39 = 99	CES64 = 89	CES89 = 87
CES15 = 71	CES40 = 97	CES65 = 88	CES90 = 98
CES16 = 47	CES41 = 97	CES66 = 85	CES91 = 73
CES17 = 48	CES42 = 90	CES67 = 84	CES92 = 79
CES18 = 56	CES43 = 91	CES68 = 86	CES93 = 87
CES19 = 70	CES44 = 99	CES69 = 87	CES94 = 78
CES20 = 65	CES45 = 95	CES70 = 83	CES95 = 83
CES21 = 85	CES46 = 97	CES71 = 77	CES96 = 92
CES22 = 77	CES47 = 95	CES72 = 92	CES97 = 95
CES23 = 91	CES48 = 93	CES73 = 77	CES98 = 95
CES24 = 90	CES49 = 95	CES74 = 92	CES99 = 94
CES25 = 70	CES50 = 98	CES75 = 79	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)