

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P1433612

Luminaire Tested: EHBR1-48-UNV-TASM-L935-UPL15

Issue Date: 3/20/2026

Test Information

Test Method: LM-79-2019
Report Number: P1433612
REPORT IS A COMBINATION OF REPORTS P1431837 AND P1431635
Test Lab: INNOVATION CENTER
Issue Date: 3/20/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: EHBR1-48-UNV-TASM-L935-UPL15
Description: Elevate Round Highbay at, 48000 lumens, 3500K 90CRI LEDs with TASM lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 44374.9 lumens
Efficiency: N/A
Efficacy: 165.6 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.84 / 0.9
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 0.1')
CIE Type: Direct

Input Watts (W): 267.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1433612
CATALOG NUMBER: EHBR1-48-UNV-TASM-L935-UPL15

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°



TEST NUMBER: P1433612
 CATALOG NUMBER: EHBR1-48-UNV-TASM-L935-UPL15

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	118	118	118	118	115	115	115	115	109	109	109	104	104	104	99	99	99	99	99	99	97
1	111	108	105	102	108	105	102	100	101	98	96	96	94	93	92	91	90	92	91	90	87
2	104	98	93	89	102	96	92	88	92	89	85	89	86	83	86	83	81	86	83	81	79
3	98	90	84	79	95	88	83	78	85	81	77	82	78	75	80	76	74	80	76	74	72
4	92	83	76	71	90	82	75	71	79	74	70	76	72	68	74	70	67	74	70	67	65
5	86	77	70	65	84	76	69	64	73	68	64	71	66	63	69	65	62	69	65	62	60
6	82	71	64	59	80	70	64	59	68	63	58	67	62	58	65	61	57	65	61	57	55
7	77	66	60	55	75	66	59	55	64	58	54	62	57	54	61	56	53	61	56	53	51
8	73	62	55	51	71	61	55	51	60	54	50	59	54	50	57	53	49	57	53	49	48
9	69	58	52	47	68	58	51	47	56	51	47	55	50	46	54	50	46	54	50	46	45
10	66	55	48	44	64	54	48	44	53	48	44	52	47	43	51	47	43	51	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	180704	180704	180704	180704
5°	179605	191605	179605	170284
10°	177397	196524	177397	161160
15°	172159	182632	172159	148868
20°	161012	146446	161012	132600
25°	142508	101466	142508	111124
30°	115711	66011	115711	83143
35°	82992	42750	82992	55351
40°	53657	29466	53657	34907
45°	34045	22824	34045	24871
50°	25283	19395	25283	20717
55°	20642	17668	20642	18287
60°	17874	16830	17874	16932
65°	16294	16231	16294	16162
70°	15444	15904	15444	15698
75°	14443	15385	14443	14924
80°	12687	14525	12687	13580
85°	8208	10373	8208	9890

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 47865 cd/sqm



TEST NUMBER: P1433612
 CATALOG NUMBER: EHBR1-48-UNV-TASM-L935-UPL15

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	3658.8	8.2
10°-20°	9954.1	22.4
20°-30°	11674.1	26.3
30°-40°	8118.6	18.3
40°-50°	4034.6	9.1
50°-60°	2413.1	5.4
60°-70°	1698.4	3.8
70°-80°	1094.1	2.5
80°-90°	349.9	0.8
90°-100°	37.5	0.1
100°-110°	237.5	0.5
110°-120°	437.4	1.0
120°-130°	261.1	0.6
130°-140°	159.5	0.4
140°-150°	111.9	0.3
150°-160°	74.6	0.2
160°-170°	44.5	0.1
170°-180°	15.2	0.0
0°-30°	25287.0	57.0
0°-40°	33405.7	75.3
0°-60°	39853.3	89.8
0°-90°	42995.7	96.9
90°-120°	712.4	1.6
90°-150°	1244.9	2.8
90°-180°	1379.0	3.1
0°-180°	44374.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	38480	38480	38480	38480	38480	
5°	38348	40911	38348	36358	38348	3639
15°	36118	38315	36118	31232	36118	10094
25°	28459	20263	28459	22191	28459	12884
35°	15232	7846	15232	10159	15232	9509
45°	5508	3693	5508	4024	5508	4507
55°	2790	2388	2790	2471	2790	2551
65°	1701	1694	1701	1687	1701	1708
75°	1017	1084	1017	1051	1017	1068
85°	282	356	282	340	282	314
90°	10	16	10	10	10	18
95°	20	22	20	17	20	21
105°	109	60	109	83	109	147
115°	465	401	465	378	465	424
125°	299	316	299	273	299	275
135°	192	222	192	201	192	152
145°	176	184	176	171	176	110
155°	159	167	159	156	159	74
165°	156	163	156	154	156	44
175°	159	166	159	156	159	15
180°	160	160	160	160	160	



TEST NUMBER: P1433612
 CATALOG NUMBER: EHBR1-48-UNV-TASM-L935-UPL15

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	38479.7	38479.7	38479.7	38479.7	38479.7	38479.7	38479.7	38479.7	38479.7	38479.7	38479.7
2.5°	38457.4	38954.5	39357.1	39622.7	39754.0	39622.7	39357.1	38954.5	38457.4	37963.1	37623.2
5°	38348.5	39344.1	40187.7	40739.6	40910.6	40739.6	40187.7	39344.1	38348.5	37407.5	36783.4
7.5°	38087.9	39639.2	40892.6	41536.9	41694.3	41536.9	40892.6	39639.2	38087.9	36755.9	35967.3
10°	37690.4	39825.4	41273.5	41735.4	41754.2	41735.4	41273.5	39825.4	37690.4	35895.8	34965.8
12.5°	37056.1	39759.1	41145.8	40994.3	40650.2	40994.3	41145.8	39759.1	37056.1	34845.3	33672.1
15°	36118.1	39365.8	40337.0	39103.9	38315.2	39103.9	40337.0	39365.8	36118.1	33426.7	32065.9
17.5°	34796.2	38629.8	38648.5	36209.0	34721.1	36209.0	38648.5	38629.8	34796.2	31692.1	30193.4
20°	33092.6	37449.4	36323.7	31861.7	30098.9	31861.7	36323.7	37449.4	33092.6	29641.4	28170.9
22.5°	30956.8	35857.6	33086.1	27488.3	25083.4	27488.3	33086.1	35857.6	30956.8	27256.7	25726.3
25°	28458.8	33907.3	29603.2	22723.1	20262.6	22723.1	29603.2	33907.3	28458.8	24415.2	23031.3
27.5°	25520.6	31435.2	25894.4	18568.4	16298.4	18568.4	25894.4	31435.2	25520.6	21481.4	20067.9
30°	22257.0	28266.2	22034.8	14787.5	12697.1	14787.5	22034.8	28266.2	22257.0	18185.3	16919.7
32.5°	18603.1	25159.8	18328.2	11848.6	10077.9	11848.6	18328.2	25159.8	18603.1	15040.1	13717.5
35°	15232.0	21273.6	14986.0	9310.2	7846.2	9310.2	14986.0	21273.6	15232.0	12070.9	10772.1
37.5°	11953.9	17601.6	11946.1	7497.0	6364.1	7497.0	11946.1	17601.6	11953.9	9384.5	8330.4
40°	9300.1	13762.9	9360.0	5984.6	5107.2	5984.6	9360.0	13762.9	9300.1	7140.5	6465.8
42.5°	7046.7	10523.9	7357.0	4911.6	4338.0	4911.6	7357.0	10523.9	7046.7	5626.0	5120.9
45°	5508.3	7744.4	5745.0	4143.9	3692.9	4143.9	5745.0	7744.4	5508.3	4530.7	4191.5
47.5°	4485.9	5985.3	4656.2	3554.4	3238.3	3554.4	4656.2	5985.3	4485.9	3832.1	3578.2
50°	3768.0	4592.6	3866.0	3102.6	2890.6	3102.6	3866.0	4592.6	3768.0	3281.6	3112.1
52.5°	3236.9	3745.6	3292.4	2765.0	2622.1	2765.0	3292.4	3745.6	3236.9	2871.1	2765.8
55°	2789.5	3148.9	2863.1	2486.5	2387.6	2486.5	2863.1	3148.9	2789.5	2555.0	2477.1
57.5°	2449.7	2671.2	2486.5	2249.1	2183.4	2249.1	2486.5	2671.2	2449.7	2273.6	2231.7
60°	2148.8	2313.3	2194.2	2042.0	2023.2	2042.0	2194.2	2313.3	2148.8	2045.6	2018.2
62.5°	1917.2	2021.1	1940.3	1855.8	1839.2	1855.8	1940.3	2021.1	1917.2	1837.8	1842.8
65°	1700.7	1797.4	1733.9	1688.4	1694.2	1688.4	1733.9	1797.4	1700.7	1663.9	1671.8
67.5°	1533.3	1583.8	1556.3	1530.4	1537.0	1530.4	1556.3	1583.8	1533.3	1497.3	1509.5
70°	1355.1	1409.2	1381.1	1384.7	1395.5	1384.7	1381.1	1409.2	1355.1	1344.3	1353.6
72.5°	1184.8	1226.6	1217.3	1225.9	1237.5	1225.9	1217.3	1226.6	1184.8	1183.3	1184.0
75°	1017.4	1049.2	1053.4	1065.8	1083.8	1065.8	1053.4	1049.2	1017.4	1006.6	1019.5
77.5°	834.8	870.9	884.7	901.3	927.9	901.3	884.7	870.9	834.8	842.1	848.5
80°	667.4	684.0	714.4	726.6	764.1	726.6	714.4	684.0	667.4	655.2	664.5
82.5°	488.5	503.6	529.7	552.7	574.3	552.7	529.7	503.6	488.5	482.7	483.4
85°	282.1	305.3	322.6	349.9	356.5	349.9	322.6	305.3	282.1	288.7	282.1
87.5°	98.9	106.0	121.2	132.1	132.8	132.1	121.2	106.0	98.9	101.1	91.6
90°	10.4	17.9	30.6	19.3	15.5	19.3	30.6	17.9	10.4	17.9	27.7
92.5°	13.5	23.9	42.6	24.6	19.3	24.6	42.6	23.9	13.5	23.2	44.1
95°	20.2	29.2	53.8	26.8	22.3	26.8	53.8	29.2	20.2	30.7	61.4
97.5°	30.6	35.9	60.6	28.4	26.0	28.4	60.6	35.9	30.6	37.4	70.4
100°	40.4	40.4	109.3	32.1	29.0	32.1	109.3	40.4	40.4	46.4	109.4
102.5°	60.6	78.6	251.6	61.3	34.3	61.3	251.6	78.6	60.6	86.1	231.5
105°	109.3	177.5	441.2	151.9	59.7	151.9	441.2	177.5	109.3	179.0	412.0
107.5°	206.0	329.5	567.8	295.7	132.4	295.7	567.8	329.5	206.0	316.1	543.9
110°	328.8	460.0	619.5	403.7	262.7	403.7	619.5	460.0	328.8	433.7	570.1



TEST NUMBER: P1433612
 CATALOG NUMBER: EHBR1-48-UNV-TASM-L935-UPL15

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	427.7	512.3	605.2	447.1	361.6	447.1	605.2	512.3	427.7	478.6	546.1
115°	465.1	504.9	540.8	445.6	400.6	445.6	540.8	504.9	465.1	467.4	487.7
117.5°	449.4	462.1	467.4	418.6	402.9	418.6	467.4	462.1	449.4	421.0	414.3
120°	405.9	400.8	394.7	378.9	380.4	378.9	394.7	400.8	405.9	367.8	346.0
122.5°	352.0	340.8	334.0	339.1	349.7	339.1	334.0	340.8	352.0	313.8	297.4
125°	298.8	287.6	292.0	304.7	315.9	304.7	292.0	287.6	298.8	267.4	262.8
127.5°	254.6	249.3	261.3	275.5	285.2	275.5	261.3	249.3	254.6	234.4	238.2
130°	223.1	223.9	239.6	252.2	258.2	252.2	239.6	223.9	223.1	213.4	223.1
132.5°	203.6	208.9	223.9	235.0	238.7	235.0	223.9	208.9	203.6	201.3	213.4
135°	191.6	199.1	213.4	220.1	222.2	220.1	213.4	199.1	191.6	193.0	203.6
137.5°	184.8	192.4	202.8	208.8	208.0	208.8	202.8	192.4	184.8	187.8	196.0
140°	181.1	188.6	193.1	199.8	199.8	199.8	193.1	188.6	181.1	182.5	189.3
142.5°	177.3	184.1	186.3	191.5	190.8	191.5	186.3	184.1	177.3	178.8	183.3
145°	175.7	181.0	178.8	184.8	183.9	184.8	178.8	181.0	175.7	175.8	178.7
147.5°	172.0	175.8	173.6	178.7	177.9	178.7	173.6	175.8	172.0	172.0	173.4
150°	168.1	171.1	167.5	173.4	174.1	173.4	167.5	171.1	168.1	167.4	168.8
152.5°	162.9	165.9	162.9	169.6	169.6	169.6	162.9	165.9	162.9	162.1	163.6
155°	159.1	160.6	159.1	165.9	166.6	165.9	159.1	160.6	159.1	158.3	159.8
157.5°	156.8	158.2	157.5	163.5	164.2	163.5	157.5	158.2	156.8	156.8	157.5
160°	156.0	157.4	157.4	162.7	163.4	162.7	157.4	157.4	156.0	156.0	156.7
162.5°	155.9	155.9	156.6	161.9	163.3	161.9	156.6	155.9	155.9	155.9	156.6
165°	155.8	156.6	156.5	161.0	163.1	161.0	156.5	156.6	155.8	155.9	155.9
167.5°	156.5	155.8	157.2	161.7	163.9	161.7	157.2	155.8	156.5	156.5	156.5
170°	155.8	156.5	157.2	161.6	163.8	161.6	157.2	156.5	155.8	156.5	156.5
172.5°	158.0	158.0	158.6	162.2	165.1	162.2	158.6	158.0	158.0	158.0	158.7
175°	159.4	159.3	160.1	162.9	165.9	162.9	160.1	159.3	159.4	158.7	158.7
177.5°	158.6	160.1	161.4	164.4	168.0	164.4	161.4	160.1	158.6	158.7	158.7
180°	160.1	160.1	160.1	160.1	160.1	160.1	160.1	160.1	160.1	160.1	160.1



TEST NUMBER: P1433612
 CATALOG NUMBER: EHBR1-48-UNV-TASM-L935-UPL15

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	38479.7	38479.7	38479.7	38479.7	38479.7	38479.7
2.5°	37362.0	37337.5	37362.0	37623.2	37963.1	38457.4
5°	36494.0	36358.3	36494.0	36783.4	37407.5	38348.5
7.5°	35483.1	35404.5	35483.1	35967.3	36755.9	38087.9
10°	34418.8	34240.6	34418.8	34965.8	35895.8	37690.4
12.5°	33107.1	32871.1	33107.1	33672.1	34845.3	37056.1
15°	31438.8	31231.8	31438.8	32065.9	33426.7	36118.1
17.5°	29648.7	29461.1	29648.7	30193.4	31692.1	34796.2
20°	27400.3	27253.1	27400.3	28170.9	29641.4	33092.6
22.5°	25041.5	24903.7	25041.5	25726.3	27256.7	30956.8
25°	22266.4	22191.4	22266.4	23031.3	24415.2	28458.8
27.5°	19267.7	19140.0	19267.7	20067.9	21481.4	25520.6
30°	16203.9	15992.6	16203.9	16919.7	18185.3	22257.0
32.5°	13207.3	13055.0	13207.3	13717.5	15040.1	18603.1
35°	10311.0	10158.8	10311.0	10772.1	12070.9	15232.0
37.5°	8034.5	7765.3	8034.5	8330.4	9384.5	11953.9
40°	6093.5	6050.2	6093.5	6465.8	7140.5	9300.1
42.5°	4960.7	4843.1	4960.7	5120.9	5626.0	7046.7
45°	4070.3	4024.1	4070.3	4191.5	4530.7	5508.3
47.5°	3500.2	3520.5	3500.2	3578.2	3832.1	4485.9
50°	3075.3	3087.5	3075.3	3112.1	3281.6	3768.0
52.5°	2762.1	2751.3	2762.1	2765.8	2871.1	3236.9
55°	2485.1	2471.3	2485.1	2477.1	2555.0	2789.5
57.5°	2242.6	2252.7	2242.6	2231.7	2273.6	2449.7
60°	2026.1	2035.5	2026.1	2018.2	2045.6	2148.8
62.5°	1843.6	1849.4	1843.6	1842.8	1837.8	1917.2
65°	1680.5	1687.0	1680.5	1671.8	1663.9	1700.7
67.5°	1524.6	1524.6	1524.6	1509.5	1497.3	1533.3
70°	1378.2	1377.4	1378.2	1353.6	1344.3	1355.1
72.5°	1202.1	1219.5	1202.1	1184.0	1183.3	1184.8
75°	1031.1	1051.3	1031.1	1019.5	1006.6	1017.4
77.5°	857.9	888.9	857.9	848.5	842.1	834.8
80°	680.4	714.4	680.4	664.5	655.2	667.4
82.5°	502.9	528.2	502.9	483.4	482.7	488.5
85°	299.5	339.9	299.5	282.1	288.7	282.1
87.5°	96.0	122.6	96.0	91.6	101.1	98.9
90°	16.5	10.4	16.5	27.7	17.9	10.4
92.5°	24.7	15.0	24.7	44.1	23.2	13.5
95°	28.5	17.2	28.5	61.4	30.7	20.2
97.5°	31.4	22.4	31.4	70.4	37.4	30.6
100°	36.7	29.2	36.7	109.4	46.4	40.4
102.5°	77.1	48.7	77.1	231.5	86.1	60.6
105°	161.8	83.1	161.8	412.0	179.0	109.3
107.5°	289.1	143.0	289.1	543.9	316.1	206.0
110°	383.6	265.9	383.6	570.1	433.7	328.8



TEST NUMBER: P1433612

CATALOG NUMBER: EHBR1-48-UNV-TASM-L935-UPL15

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	412.0	358.8	412.0	546.1	478.6	427.7
115°	396.2	377.6	396.2	487.7	467.4	465.1
117.5°	361.8	364.8	361.8	414.3	421.0	449.4
120°	322.1	337.8	322.1	346.0	367.8	405.9
122.5°	286.1	304.1	286.1	297.4	313.8	352.0
125°	254.7	273.3	254.7	262.8	267.4	298.8
127.5°	232.9	245.6	232.9	238.2	234.4	254.6
130°	216.4	226.9	216.4	223.1	213.4	223.1
132.5°	205.2	211.9	205.2	213.4	201.3	203.6
135°	195.4	200.7	195.4	203.6	193.0	191.6
137.5°	187.2	191.7	187.2	196.0	187.8	184.8
140°	180.4	184.2	180.4	189.3	182.5	181.1
142.5°	172.8	175.8	172.8	183.3	178.8	177.3
145°	168.3	170.6	168.3	178.7	175.8	175.7
147.5°	164.4	165.9	164.4	173.4	172.0	172.0
150°	160.6	162.1	160.6	168.8	167.4	168.1
152.5°	156.1	158.3	156.1	163.6	162.1	162.9
155°	153.8	156.1	153.8	159.8	158.3	159.1
157.5°	153.0	155.2	153.0	157.5	156.8	156.8
160°	152.9	154.4	152.9	156.7	156.0	156.0
162.5°	152.2	153.6	152.2	156.6	155.9	155.9
165°	152.8	153.5	152.8	155.9	155.9	155.8
167.5°	152.8	153.5	152.8	156.5	156.5	156.5
170°	153.5	154.3	153.5	156.5	156.5	155.8
172.5°	155.0	155.7	155.0	158.7	158.0	158.0
175°	155.7	156.4	155.7	158.7	158.7	159.4
177.5°	157.2	157.9	157.2	158.7	158.7	158.6
180°	160.1	160.1	160.1	160.1	160.1	160.1



TEST NUMBER: P1433612
 CATALOG NUMBER: EHBR1-48-UNV-TASM-L935-UPL15

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.98	20.14	19.40	20.52	20.91	18.30	19.46	18.72	19.84	20.23
	3H	20.53	21.56	20.97	21.96	22.40	20.15	21.18	20.59	21.58	22.02
	4H	21.17	22.13	21.63	22.54	23.01	20.93	21.89	21.39	22.31	22.77
	6H	21.65	22.53	22.12	22.97	23.44	21.58	22.46	22.05	22.89	23.37
	8H	21.80	22.64	22.29	23.09	23.57	21.80	22.63	22.29	23.09	23.57
	12H	21.87	22.67	22.36	23.12	23.63	21.93	22.72	22.42	23.17	23.68
4H	2H	19.40	20.36	19.86	20.78	21.24	18.88	19.84	19.34	20.25	20.72
	3H	21.20	21.99	21.67	22.46	22.94	20.94	21.73	21.41	22.20	22.68
	4H	21.97	22.68	22.46	23.16	23.68	21.85	22.56	22.34	23.04	23.56
	6H	22.59	23.20	23.11	23.71	24.25	22.62	23.23	23.14	23.74	24.28
	8H	22.79	23.36	23.31	23.86	24.41	22.89	23.46	23.41	23.97	24.51
	12H	22.89	23.40	23.43	23.94	24.49	23.06	23.56	23.60	24.10	24.65
8H	4H	22.22	22.80	22.75	23.30	23.85	22.13	22.70	22.65	23.21	23.75
	6H	22.97	23.43	23.52	23.99	24.54	23.03	23.50	23.59	24.05	24.60
	8H	23.24	23.65	23.81	24.22	24.79	23.38	23.80	23.96	24.37	24.94
	12H	23.41	23.77	23.98	24.32	24.97	23.63	24.00	24.20	24.55	25.19
12H	4H	22.24	22.74	22.78	23.28	23.83	22.14	22.64	22.68	23.18	23.73
	6H	23.01	23.42	23.58	23.99	24.56	23.08	23.49	23.65	24.06	24.63
	8H	23.33	23.69	23.90	24.24	24.89	23.48	23.84	24.05	24.40	25.04

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP1-2506-472-6

Test Date: 08/01/2025

Luminaire Tested: EHBR-60-L935-N

Data in this report applies to families of products including EHBR-60-L935-N

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2506-472-6
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 08/05/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **EHBR-60-L935-N**
 Description: Elevate Round Highbay at, 60000 lumens, 3500K 90CRI LEDs with N lens

Spectral Parameters

CCT (K): 3406
 CIE u': 0.2394
 CIE v': 0.5094
 Duv: -0.0028
 CIE x: 0.4076
 CIE y: 0.3856
 CIE z: 0.2068
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 582
 Purity: 38.0517
 Rf: 91.3
 Rg: 100

CRI (Ra):	94.6		
R1:	96.6	R9:	63.8
R2:	98.4	R10:	94.7
R3:	98.1	R11:	96.6
R4:	95.8	R12:	80.9
R5:	96.2	R13:	97.4
R6:	95.4	R14:	98.3
R7:	91.8	R15:	93.1
R8:	84.4		



Test Conditions


Stabilization Time: 35M
 Operation Time: 1H 35M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2506-472-6

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2506-472-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2506-472-6

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-6

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.62

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

REPORT NUMBER: SP1-2506-472-6

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.3

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	140	NR	620	338	NR	750	8	NR	880	0	NR
365	0	NR	495	159	NR	625	339	NR	755	7	NR	885	0	NR
370	0	NR	500	182	NR	630	1000	NR	760	5	NR	890	0	NR
375	0	NR	505	202	NR	635	653	NR	765	5	NR	895	0	NR
380	0	NR	510	216	NR	640	222	NR	770	4	NR	900	0	NR
385	0	NR	515	228	NR	645	214	NR	775	3	NR	905	0	NR
390	0	NR	520	236	NR	650	185	NR	780	3	NR	910	0	NR
395	1	NR	525	242	NR	655	157	NR	785	3	NR	915	0	NR
400	2	NR	530	248	NR	660	133	NR	790	2	NR	920	0	NR
405	3	NR	535	253	NR	665	113	NR	795	2	NR	925	0	NR
410	4	NR	540	258	NR	670	103	NR	800	2	NR	930	0	NR
415	7	NR	545	264	NR	675	85	NR	805	1	NR	935	0	NR
420	13	NR	550	270	NR	680	72	NR	810	1	NR	940	0	NR
425	22	NR	555	278	NR	685	62	NR	815	1	NR	945	0	NR
430	38	NR	560	286	NR	690	53	NR	820	1	NR	950	0	NR
435	65	NR	565	295	NR	695	45	NR	825	1	NR	955	0	NR
440	108	NR	570	303	NR	700	39	NR	830	1	NR	960	0	NR
445	193	NR	575	311	NR	705	33	NR	835	1	NR	965	0	NR
450	312	NR	580	319	NR	710	28	NR	840	1	NR	970	0	NR
455	300	NR	585	326	NR	715	24	NR	845	0	NR	975	0	NR
460	214	NR	590	332	NR	720	20	NR	850	0	NR	980	0	NR
465	184	NR	595	333	NR	725	17	NR	855	0	NR	985	0	NR
470	153	NR	600	336	NR	730	15	NR	860	0	NR	990	0	NR
475	122	NR	605	337	NR	735	12	NR	865	0	NR	995	0	NR
480	115	NR	610	367	NR	740	10	NR	870	0	NR	1000	0	NR
485	125	NR	615	390	NR	745	9	NR	875	0	NR			

Summary

$R_f = 91.3$
 $R_g = 100$
 $CIE R_a = 94.6$
 $R_9 = 63.8$



Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 94	CES51 = 97	CES76 = 90
CES02 = 63	CES27 = 92	CES52 = 98	CES77 = 86
CES03 = 31	CES28 = 97	CES53 = 98	CES78 = 86
CES04 = 70	CES29 = 97	CES54 = 93	CES79 = 90
CES05 = 50	CES30 = 92	CES55 = 92	CES80 = 91
CES06 = 51	CES31 = 97	CES56 = 96	CES81 = 74
CES07 = 43	CES32 = 89	CES57 = 94	CES82 = 96
CES08 = 41	CES33 = 99	CES58 = 95	CES83 = 94
CES09 = 29	CES34 = 94	CES59 = 98	CES84 = 95
CES10 = 75	CES35 = 97	CES60 = 92	CES85 = 79
CES11 = 58	CES36 = 81	CES61 = 93	CES86 = 79
CES12 = 64	CES37 = 96	CES62 = 86	CES87 = 92
CES13 = 44	CES38 = 87	CES63 = 94	CES88 = 98
CES14 = 74	CES39 = 99	CES64 = 91	CES89 = 84
CES15 = 72	CES40 = 97	CES65 = 90	CES90 = 96
CES16 = 48	CES41 = 96	CES66 = 89	CES91 = 75
CES17 = 49	CES42 = 94	CES67 = 88	CES92 = 76
CES18 = 56	CES43 = 93	CES68 = 89	CES93 = 86
CES19 = 71	CES44 = 99	CES69 = 90	CES94 = 74
CES20 = 67	CES45 = 97	CES70 = 88	CES95 = 83
CES21 = 86	CES46 = 97	CES71 = 83	CES96 = 92
CES22 = 78	CES47 = 91	CES72 = 94	CES97 = 96
CES23 = 91	CES48 = 91	CES73 = 83	CES98 = 95
CES24 = 90	CES49 = 96	CES74 = 90	CES99 = 92
CES25 = 71	CES50 = 98	CES75 = 85	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)